

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599569

Luminaire Tested: **IFLD-L-SA8A-760-U-SLL-HSS**

Issue Date: 05/04/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P599569
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/04/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-L-SA8A-760-U-SLL-HSS
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens with House Side Shield
 Light Source: (128) 5700K CCT, 70 CRI LEDS
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 25521.5 lumens
 Efficiency: N/A
 Efficacy: 103.0 lumens/watt
 Spacing Criteria (0/90/45): 0.53 / 0.46 / 0.63
 Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
 CIE Type: Direct

Input Watts (W): 247.8
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599569
CATALOG NUMBER: IFLD-L-SA8A-760-U-SLL-HSS

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ··· 90°-270° - · 135°-315°

TEST NUMBER: P599569
 CATALOG NUMBER: IFLD-L-SA8A-760-U-SLL-HSS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	106	100	95	90	103	98	93	89	94	90	86	90	86	83	86	83	81	79				79
2	94	84	76	69	91	82	75	68	78	72	66	75	70	65	72	67	63	61				61
3	84	72	62	54	81	70	61	53	67	59	52	64	57	51	61	55	50	48				48
4	76	62	51	44	73	60	51	43	58	49	43	55	48	42	53	46	41	39				39
5	69	54	44	36	67	53	43	36	51	42	35	48	41	35	46	40	34	32				32
6	63	48	38	30	61	47	37	30	45	36	30	43	35	30	41	35	29	27				27
7	58	43	33	26	56	42	33	26	40	32	26	39	31	26	37	31	25	23				23
8	54	39	29	23	52	38	29	23	37	28	23	35	28	22	34	27	22	20				20
9	50	35	26	20	49	35	26	20	34	26	20	32	25	20	31	25	20	18				18
10	47	33	24	18	46	32	24	18	31	23	18	30	23	18	29	23	18	16				16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	51645	51645	51645	51645
5°	54272	51658	37740	37961
10°	46668	44881	20634	20150
15°	45379	43138	13405	10101
20°	52305	50119	7182	3591
25°	65766	61516	4654	2793
30°	78990	73611	3770	2287
35°	93540	87764	3090	1836
40°	112857	106250	2729	1388
45°	128489	122886	2541	934
50°	144142	138550	2511	571
55°	163006	162430	2494	256
60°	201151	205919	2274	73
65°	224442	247529	2083	0
70°	228858	279370	1931	0
75°	186219	206059	1842	0
80°	135398	86180	1900	0
85°	87538	36192	2526	0

TEST NUMBER: P599569
 CATALOG NUMBER: IFLD-L-SA8A-760-U-SLL-HSS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	729.0	2.9
10°-20°	1429.5	5.6
20°-30°	1978.2	7.8
30°-40°	2795.8	11.0
40°-50°	3806.5	14.9
50°-60°	5041.4	19.8
60°-70°	5853.5	22.9
70°-80°	3314.9	13.0
80°-90°	572.8	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4136.8	16.2
0°-40°	6932.5	27.2
0°-60°	15780.4	61.8
0°-90°	25521.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	25521.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	9596	9596	9596	9596	9596	
5°	10046	9562	6986	7027	10046	902
15°	8144	7742	2406	1813	8144	2389
25°	11075	10359	784	470	11075	5165
35°	14237	13358	470	279	14237	8975
45°	16882	16145	334	123	16882	13088
55°	17372	17311	266	27	17372	15739
65°	17624	19437	164	0	17624	17181
75°	8955	9909	89	0	8955	9774
85°	1418	586	41	0	1418	1703
90°	0	0	0	0	0	

TEST NUMBER: P599569
 CATALOG NUMBER: IFLD-L-SA8A-760-U-SLL-HSS

CANDELA DISTRIBUTION (FULL):

	0°	2°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9
2.5°	9970.8	10182.0	10188.8	10284.3	10379.7	10379.7	10604.6	10550.1	10352.4	10318.3	10175.2
5°	10045.7	10120.7	10175.2	10659.1	11068.0	11027.1	11149.8	11068.0	10686.4	10195.7	9861.7
7.5°	9398.3	9480.1	9698.1	10522.8	11074.8	11258.8	11490.6	10979.4	10577.3	9691.3	9050.7
10°	8539.5	8696.3	9098.4	10038.9	10720.4	11306.6	11306.6	10897.6	10120.7	9255.2	8471.4
12.5°	8062.5	8376.0	8594.1	9548.2	10434.2	10836.3	10822.7	10604.6	10100.2	9009.8	8123.8
15°	8144.3	8232.9	8696.3	9439.2	10025.3	10004.8	10250.2	10182.0	9827.6	9227.9	8253.3
17.5°	8519.1	8655.4	9057.5	9439.2	9718.6	9636.8	9630.0	9957.1	9977.6	9595.9	8737.2
20°	9132.5	9534.6	9725.4	9841.3	9500.5	9152.9	9112.0	9568.7	9923.1	10066.2	9316.5
22.5°	10113.9	10379.7	10768.1	10175.2	9289.2	8853.1	8771.3	9275.6	9991.2	10625.0	10066.2
25°	11074.8	11279.3	11654.1	10890.8	9527.8	8791.7	8648.6	9084.8	10250.2	11402.0	10972.6
27.5°	12090.3	12267.5	12308.4	11415.6	9657.3	8669.0	8498.7	9084.8	10468.3	11810.9	12056.2
30°	12710.5	12921.8	12962.7	11879.0	9868.5	8771.3	8689.5	9125.7	10618.2	12158.5	12833.2
32.5°	13405.7	13460.2	13426.1	11960.8	10100.2	9071.1	8730.4	9398.3	10788.6	12574.2	13542.0
35°	14237.1	14332.5	13985.0	12335.7	10618.2	9262.0	9139.3	9732.2	11081.6	12765.0	14400.7
37.5°	14870.9	15170.8	14387.1	12478.8	10720.4	9664.1	9684.5	10427.4	11286.1	12996.7	15348.0
40°	16063.6	15559.3	15068.6	12969.5	11108.9	10345.6	10236.6	11143.0	11974.5	13146.7	15968.2
42.5°	16717.9	16452.1	15334.4	13017.2	11708.7	11286.1	11313.4	11954.0	12335.7	13569.2	16138.6
45°	16881.5	16602.0	15695.6	13051.3	12301.6	12397.0	12867.3	12989.9	12867.3	13848.7	16458.9
47.5°	17297.2	16690.6	15654.7	13507.9	13262.5	13630.6	14230.3	14496.1	13589.7	13746.4	16608.8
50°	17215.4	16867.8	15566.1	13698.7	14434.8	15409.4	15811.5	15702.4	14393.9	13535.2	16445.3
52.5°	16874.6	16499.8	15838.7	14216.7	15532.0	16711.1	17269.9	16997.3	15109.5	14012.2	16336.2
55°	17372.2	17085.9	16193.1	14918.7	16356.7	17856.0	18251.3	18046.9	15988.7	14455.2	16956.4
57.5°	17910.6	17849.2	17154.1	15743.3	17331.3	19035.1	19035.1	18782.9	16752.0	15095.8	17876.5
60°	18687.5	18823.8	17862.9	16288.5	17665.2	18966.9	19955.1	19662.1	17522.1	16220.4	18919.2
62.5°	18435.3	18871.5	18776.1	17460.8	18046.9	19300.9	19839.3	20057.4	18476.2	17590.2	20309.5
65°	17624.3	18087.8	18769.3	18230.9	17760.6	18489.9	18762.5	19423.6	18953.3	18878.3	20882.0
67.5°	16656.5	17160.9	17583.4	18748.8	17181.3	17665.2	17426.7	17637.9	18435.3	20289.1	21209.2
70°	14543.8	15027.7	15695.6	17597.1	15647.9	15211.7	15150.4	15048.1	16288.5	19784.8	19723.4
72.5°	11960.8	12185.7	13289.8	14305.3	11579.2	11497.4	11592.8	11476.9	12915.0	17910.6	16895.1
75°	8955.3	9180.2	9807.2	10986.2	7885.3	7415.0	7960.2	8498.7	9861.7	13903.2	12138.0
77.5°	6733.5	7019.7	7415.0	8219.2	5786.2	5050.1	5125.1	5636.2	7128.8	11136.2	6801.7
80°	4368.6	4334.5	5097.8	5656.7	4355.0	4491.3	4300.4	4675.3	5166.0	5956.6	3475.8
82.5°	2521.7	2555.7	2876.0	3244.1	3032.8	3469.0	2501.2	4177.8	3687.1	2426.2	1294.9
85°	1417.6	1478.9	1772.0	2249.0	1901.5	1274.5	1042.7	2071.8	2317.2	995.0	627.0
87.5°	143.1	122.7	238.5	851.9	518.0	211.3	313.5	497.5	558.9	374.8	184.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599569
 CATALOG NUMBER: IFLD-L-SA8A-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9
2.5°	9970.8	9970.8	9800.4	9514.1	9398.3	9193.8	8914.4	9003.0	8907.6	8560.0	8471.4
5°	9561.8	9234.7	8880.3	8444.1	8192.0	7674.0	7510.4	7217.4	7265.1	6972.0	6985.7
7.5°	8709.9	8450.9	7851.2	7278.7	6781.2	6331.4	5697.6	5459.0	5227.3	5111.5	5247.8
10°	8212.4	7728.5	6910.7	6161.0	5499.9	5097.8	4675.3	4348.1	4048.3	3823.4	3775.7
12.5°	7851.2	7421.8	6433.6	5520.4	5002.4	4675.3	4286.8	3837.0	3543.9	3155.5	3039.6
15°	7742.2	7217.4	6174.6	5268.2	4763.9	4225.5	3782.5	3339.5	2957.8	2548.9	2405.8
17.5°	8117.0	7510.4	6167.8	5063.8	4355.0	3775.7	3162.3	2664.8	2276.3	1901.5	1812.9
20°	8750.8	7823.9	6365.5	4941.1	3966.5	3189.6	2494.4	1996.9	1560.7	1315.3	1254.0
22.5°	9473.2	8355.5	6385.9	4613.9	3578.0	2603.4	1819.7	1315.3	1070.0	954.1	920.1
25°	10359.2	9207.4	6631.3	4348.1	3121.4	1976.4	1294.9	1008.7	865.5	797.4	783.8
27.5°	11088.5	9800.4	6897.1	4068.7	2671.6	1465.3	1015.5	824.6	749.7	681.5	674.7
30°	11845.0	10481.9	6972.0	3898.3	2283.1	1206.3	872.4	729.2	647.5	613.4	606.6
32.5°	12506.0	11224.8	7210.6	3618.9	1915.1	1063.2	790.6	654.3	599.7	545.2	538.4
35°	13358.0	11654.1	7326.4	3469.0	1778.8	961.0	722.4	599.7	518.0	483.9	470.3
37.5°	14271.2	12069.9	7401.4	3353.1	1662.9	899.6	681.5	565.7	490.7	443.0	429.4
40°	15123.1	12656.0	7292.4	3210.0	1574.3	824.6	654.3	524.8	456.6	408.9	388.5
42.5°	15777.4	13228.5	7258.3	3073.7	1478.9	797.4	620.2	504.3	429.4	374.8	368.0
45°	16145.4	13616.9	7019.7	2964.6	1403.9	811.0	606.6	477.1	408.9	361.2	333.9
47.5°	16056.8	13916.8	7081.1	2930.6	1301.7	756.5	599.7	456.6	374.8	333.9	313.5
50°	16547.5	14523.4	6978.8	2821.5	1226.8	681.5	654.3	456.6	368.0	320.3	299.9
52.5°	16629.3	15075.4	7196.9	2623.9	1110.9	627.0	647.5	449.8	354.4	306.7	279.4
55°	17310.8	15716.0	7619.5	2514.8	1015.5	545.2	592.9	436.2	320.3	279.4	265.8
57.5°	18237.7	17045.0	7892.1	2412.6	886.0	477.1	497.5	429.4	293.1	259.0	238.5
60°	19130.5	17576.6	7912.5	2228.6	763.3	429.4	388.5	429.4	272.6	231.7	211.3
62.5°	19798.4	17576.6	7776.2	2071.8	667.9	381.7	340.8	408.9	245.4	204.5	190.8
65°	19437.2	17106.4	7421.8	1942.4	606.6	333.9	293.1	313.5	218.1	177.2	163.6
67.5°	18789.7	15641.1	6638.1	1785.6	599.7	293.1	252.2	231.7	190.8	156.8	143.1
70°	17753.8	13664.6	5527.2	1608.4	586.1	265.8	224.9	197.6	170.4	136.3	122.7
72.5°	14305.3	11286.1	4539.0	1506.2	572.5	231.7	190.8	170.4	143.1	115.9	102.2
75°	9909.4	7210.6	3496.2	1288.1	558.9	211.3	177.2	149.9	122.7	95.4	88.6
77.5°	5942.9	4818.4	2255.9	967.8	368.0	170.4	149.9	115.9	102.2	81.8	75.0
80°	2780.6	2276.3	913.2	374.8	177.2	122.7	102.2	88.6	81.8	68.2	61.3
82.5°	1090.4	961.0	443.0	218.1	143.1	95.4	81.8	75.0	68.2	54.5	47.7
85°	586.1	518.0	211.3	149.9	102.2	68.2	68.2	61.3	54.5	47.7	40.9
87.5°	129.5	95.4	88.6	88.6	75.0	54.5	54.5	47.7	40.9	34.1	27.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599569
 CATALOG NUMBER: IFLD-L-SA8A-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9
2.5°	8423.7	8525.9	8362.4	8464.6	8321.5	8430.5	8444.1	8341.9	8369.2	8505.5	8566.8
5°	7176.5	7108.3	6958.4	6910.7	6917.5	6828.9	6863.0	6910.7	6985.7	7026.6	7149.2
7.5°	5172.8	5329.6	5322.7	5438.6	5445.4	5431.8	5336.4	5131.9	5200.1	5145.5	5213.7
10°	3700.7	3768.9	3898.3	3973.3	4109.6	4034.6	3816.6	3734.8	3693.9	3687.1	3755.2
12.5°	2957.8	2794.3	2780.6	2807.9	2876.0	2787.5	2678.4	2583.0	2630.7	2726.1	2801.1
15°	2289.9	2153.6	1976.4	1949.2	1962.8	1921.9	1806.0	1683.4	1717.5	1812.9	1867.4
17.5°	1758.3	1601.6	1478.9	1397.1	1369.9	1226.8	1056.4	954.1	926.9	920.1	967.8
20°	1185.9	1158.6	1138.2	1035.9	1035.9	831.5	688.3	613.4	613.4	627.0	633.8
22.5°	886.0	851.9	858.7	838.3	783.8	620.2	545.2	524.8	524.8	538.4	538.4
25°	770.1	722.4	708.8	702.0	647.5	531.6	477.1	456.6	456.6	470.3	470.3
27.5°	654.3	640.6	620.2	592.9	545.2	456.6	422.5	402.1	408.9	415.7	408.9
30°	599.7	565.7	538.4	538.4	483.9	408.9	381.7	368.0	354.4	368.0	374.8
32.5°	531.6	511.1	497.5	477.1	415.7	361.2	333.9	320.3	313.5	313.5	320.3
35°	456.6	456.6	443.0	415.7	361.2	327.1	293.1	279.4	272.6	279.4	279.4
37.5°	408.9	388.5	395.3	368.0	320.3	286.2	252.2	238.5	238.5	231.7	238.5
40°	381.7	347.6	327.1	313.5	286.2	245.4	218.1	204.5	197.6	197.6	197.6
42.5°	340.8	313.5	272.6	265.8	259.0	211.3	177.2	170.4	163.6	156.8	156.8
45°	320.3	279.4	245.4	211.3	211.3	177.2	149.9	136.3	129.5	122.7	129.5
47.5°	293.1	252.2	211.3	177.2	170.4	143.1	115.9	102.2	95.4	95.4	95.4
50°	279.4	224.9	184.0	149.9	129.5	115.9	88.6	75.0	68.2	68.2	68.2
52.5°	259.0	211.3	163.6	129.5	102.2	88.6	68.2	54.5	47.7	47.7	47.7
55°	231.7	190.8	143.1	109.0	88.6	68.2	47.7	34.1	27.3	27.3	27.3
57.5°	218.1	170.4	122.7	95.4	68.2	47.7	27.3	20.4	20.4	13.6	20.4
60°	197.6	149.9	102.2	75.0	54.5	34.1	20.4	6.8	6.8	6.8	6.8
62.5°	170.4	129.5	88.6	61.3	40.9	20.4	6.8	0.0	0.0	0.0	0.0
65°	143.1	102.2	68.2	47.7	27.3	6.8	0.0	0.0	0.0	0.0	0.0
67.5°	122.7	88.6	54.5	34.1	20.4	0.0	0.0	0.0	0.0	0.0	0.0
70°	109.0	75.0	40.9	27.3	6.8	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	88.6	61.3	34.1	13.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	75.0	47.7	20.4	6.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	61.3	34.1	13.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	47.7	27.3	6.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	40.9	20.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	27.3	6.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	20.4	6.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599569
 CATALOG NUMBER: IFLD-L-SA8A-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	358°	360°
0°	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9	9595.9
2.5°	8655.4	8614.5	8819.0	9152.9	9323.3	9657.3	9739.0	9950.3	9895.8	9970.8
5°	7162.9	7244.6	7544.5	8035.2	8212.4	8696.3	9152.9	9609.5	9902.6	10045.7
7.5°	5315.9	5588.5	5956.6	6406.4	6863.0	7496.8	8273.8	8805.3	9091.6	9398.3
10°	3959.7	4252.7	4675.3	5118.3	5861.1	6569.9	7346.9	8008.0	8253.3	8539.5
12.5°	3114.6	3571.2	4061.9	4539.0	4982.0	5656.7	6617.6	7578.6	7844.4	8062.5
15°	2167.3	2726.1	3428.1	4048.3	4668.5	5254.6	6249.6	7415.0	7776.2	8144.3
17.5°	1199.5	1642.5	2446.7	3319.0	4232.3	5131.9	6372.3	7714.9	8260.1	8519.1
20°	695.2	872.4	1444.8	2480.8	3687.1	4866.1	6433.6	8280.6	9003.0	9132.5
22.5°	572.5	633.8	817.8	1553.9	3019.2	4695.7	6747.1	9071.1	9807.2	10113.9
25°	490.7	538.4	633.8	933.7	2283.1	4334.5	6944.8	10059.4	10740.9	11074.8
27.5°	436.2	483.9	558.9	688.3	1553.9	3837.0	7271.9	10952.2	11633.7	12090.3
30°	381.7	422.5	497.5	586.1	1076.8	3278.2	7551.3	11606.4	12567.4	12710.5
32.5°	340.8	374.8	429.4	504.3	797.4	2487.6	7776.2	12281.1	13092.2	13405.7
35°	293.1	333.9	368.0	429.4	606.6	1874.2	7639.9	12805.9	13862.3	14237.1
37.5°	259.0	286.2	320.3	361.2	511.1	1465.3	7360.5	13432.9	14523.4	14870.9
40°	218.1	238.5	279.4	320.3	463.4	1131.3	7040.2	14189.4	15450.2	16063.6
42.5°	184.0	204.5	231.7	299.9	381.7	838.3	6392.7	14775.5	16199.9	16717.9
45°	143.1	170.4	211.3	299.9	306.7	620.2	5724.8	15211.7	16622.5	16881.5
47.5°	109.0	136.3	204.5	259.0	245.4	429.4	4934.3	15709.2	17058.7	17297.2
50°	81.8	109.0	231.7	224.9	204.5	327.1	4436.7	16056.8	17085.9	17215.4
52.5°	54.5	81.8	190.8	170.4	170.4	286.2	4300.4	16043.2	17154.1	16874.6
55°	40.9	61.3	109.0	122.7	149.9	252.2	4177.8	16554.3	17174.5	17372.2
57.5°	27.3	47.7	75.0	95.4	129.5	218.1	3925.6	17167.7	17808.3	17910.6
60°	13.6	34.1	54.5	75.0	109.0	190.8	3571.2	17617.5	18578.5	18687.5
62.5°	6.8	20.4	40.9	61.3	88.6	149.9	3203.2	16901.9	18244.5	18435.3
65°	0.0	13.6	27.3	40.9	54.5	109.0	2603.4	15259.4	16922.3	17624.3
67.5°	0.0	0.0	13.6	27.3	34.1	81.8	1962.8	13882.7	15702.4	16656.5
70°	0.0	0.0	6.8	6.8	20.4	61.3	1254.0	11497.4	14019.0	14543.8
72.5°	0.0	0.0	0.0	0.0	6.8	40.9	729.2	8539.5	10986.2	11960.8
75°	0.0	0.0	0.0	0.0	0.0	34.1	368.0	5493.1	7646.7	8955.3
77.5°	0.0	0.0	0.0	0.0	0.0	27.3	197.6	3543.9	5636.2	6733.5
80°	0.0	0.0	0.0	0.0	0.0	6.8	115.9	2058.2	3605.3	4368.6
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	47.7	1008.7	2153.6	2521.7
85°	0.0	0.0	0.0	0.0	0.0	0.0	13.6	538.4	1076.8	1417.6
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	20.4	75.0	143.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)