

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599571

Luminaire Tested: **IFLD-L-SA8C-760-U-SLL-HSS**

Issue Date: 05/04/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

**Test Information**

Test Method: LM-79-08  
 Report Number: P599571  
 Test Lab: INNOVATION CENTER(G1)  
 Issue Date: 05/04/2022  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: IFLD-L-SA8C-760-U-SLL-HSS  
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens with House Side Shield  
 Light Source: (128) 5700K CCT, 70 CRI LEDS  
 Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
 Luminaire Lumens: 37745.6 lumens  
 Efficiency: N/A  
 Efficacy: 89.8 lumens/watt  
 Spacing Criteria (0/90/45): 0.53 / 0.46 / 0.63  
 Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')  
 CIE Type: Direct

Input Watts (W): 420.3  
 Input Voltage (V): 120  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599571  
CATALOG NUMBER: IFLD-L-SA8C-760-U-SLL-HSS

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    ··· 90°-270°    - · 135°-315°



TEST NUMBER: P599571  
 CATALOG NUMBER: IFLD-L-SA8C-760-U-SLL-HSS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	106	100	95	90	103	98	93	89	94	90	86	90	86	83	86	83	81	79	79	79	79
2	94	84	76	69	91	82	75	68	78	72	66	75	70	65	72	67	63	61	61	61	61
3	84	72	62	54	81	70	61	53	67	59	52	64	57	51	61	55	50	48	48	48	48
4	76	62	51	44	73	60	51	43	58	49	43	55	48	42	53	46	41	39	39	39	39
5	69	54	44	36	67	53	43	36	51	42	35	48	41	35	46	40	34	32	32	32	32
6	63	48	38	30	61	47	37	30	45	36	30	43	35	30	41	35	29	27	27	27	27
7	58	43	33	26	56	42	33	26	40	32	26	39	31	26	37	31	25	23	23	23	23
8	54	39	29	23	52	38	29	23	37	28	23	35	28	22	34	27	22	20	20	20	20
9	50	35	26	20	49	35	26	20	34	26	20	32	25	20	31	25	20	18	18	18	18
10	47	33	24	18	46	32	24	18	31	23	18	30	23	18	29	23	18	16	16	16	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	76381	76381	76381	76381
5°	80267	76401	55817	56143
10°	69021	66377	30517	29801
15°	67113	63799	19825	14939
20°	77358	74125	10622	5311
25°	97266	90981	6884	4130
30°	116824	108868	5575	3383
35°	138343	129800	4570	2715
40°	166913	157140	4036	2054
45°	190031	181746	3759	1381
50°	213182	204911	3713	844
55°	241081	240229	3689	378
60°	297496	304548	3364	109
65°	331944	366087	3081	0
70°	338475	413181	2854	0
75°	275412	304755	2724	0
80°	200249	127461	2811	0
85°	129467	53526	3736	0

TEST NUMBER: P599571  
 CATALOG NUMBER: IFLD-L-SA8C-760-U-SLL-HSS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1078.1	2.9
10°-20°	2114.2	5.6
20°-30°	2925.8	7.8
30°-40°	4134.8	11.0
40°-50°	5629.7	14.9
50°-60°	7456.1	19.8
60°-70°	8657.1	22.9
70°-80°	4902.6	13.0
80°-90°	847.1	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6118.1	16.2
0°-40°	10253.0	27.2
0°-60°	23338.8	61.8
0°-90°	37745.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	37745.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	14192	14192	14192	14192	14192	
5°	14857	14142	10332	10392	14857	1334
15°	12045	11450	3558	2681	12045	3533
25°	16379	15321	1159	696	16379	7639
35°	21056	19756	696	413	21056	13274
45°	24967	23879	494	181	24967	19357
55°	25693	25602	393	40	25693	23278
65°	26066	28747	242	0	26066	25410
75°	13245	14656	131	0	13245	14455
85°	2097	867	60	0	2097	2519
90°	0	0	0	0	0	

TEST NUMBER: P599571  
 CATALOG NUMBER: IFLD-L-SA8C-760-U-SLL-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	2°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1
2.5°	14746.5	15058.9	15069.0	15210.1	15351.2	15351.2	15683.9	15603.2	15310.9	15260.5	15048.8
5°	14857.3	14968.2	15048.8	15764.5	16369.3	16308.8	16490.2	16369.3	15804.8	15079.1	14585.2
7.5°	13899.8	14020.7	14343.3	15562.9	16379.4	16651.5	16994.2	16238.2	15643.5	14333.2	13385.7
10°	12629.7	12861.6	13456.3	14847.3	15855.2	16722.1	16722.1	16117.3	14968.2	13688.1	12528.9
12.5°	11924.2	12387.8	12710.4	14121.5	15431.9	16026.6	16006.4	15683.9	14938.0	13325.2	12014.9
15°	12045.1	12176.2	12861.6	13960.2	14827.1	14796.9	15159.7	15058.9	14534.8	13647.8	12206.4
17.5°	12599.5	12801.1	13395.8	13960.2	14373.5	14252.6	14242.5	14726.3	14756.5	14192.1	12922.1
20°	13506.7	14101.4	14383.6	14554.9	14051.0	13536.9	13476.4	14151.8	14675.9	14887.6	13778.8
22.5°	14958.1	15351.2	15925.8	15048.8	13738.5	13093.4	12972.4	13718.3	14776.7	15714.1	14887.6
25°	16379.4	16681.7	17236.1	16107.2	14091.3	13002.7	12791.0	13436.1	15159.7	16863.2	16228.2
27.5°	17881.2	18143.3	18203.8	16883.3	14282.8	12821.3	12569.3	13436.1	15482.3	17468.0	17830.8
30°	18798.5	19110.9	19171.4	17568.7	14595.3	12972.4	12851.5	13496.6	15704.0	17982.0	18979.9
32.5°	19826.6	19907.2	19856.8	17689.7	14938.0	13416.0	12912.0	13899.8	15956.0	18596.9	20028.2
35°	21056.3	21197.4	20683.3	18244.1	15704.0	13698.2	13516.7	14393.7	16389.4	18879.1	21298.2
37.5°	21993.7	22437.2	21278.0	18455.8	15855.2	14292.9	14323.1	15421.8	16691.8	19221.8	22699.3
40°	23757.6	23011.7	22286.0	19181.5	16429.8	15300.8	15139.6	16480.2	17709.9	19443.6	23616.5
42.5°	24725.3	24332.2	22679.1	19252.0	17316.8	16691.8	16732.1	17679.6	18244.1	20068.5	23868.5
45°	24967.2	24553.9	23213.3	19302.4	18193.7	18334.8	19030.3	19211.7	19030.3	20481.8	24342.2
47.5°	25582.0	24684.9	23152.8	19977.8	19614.9	20159.2	21046.2	21439.3	20098.7	20330.6	24564.0
50°	25461.1	24947.0	23021.8	20260.0	21348.6	22790.0	23384.7	23223.4	21288.1	20018.1	24322.1
52.5°	24957.1	24402.7	23425.0	21026.1	22971.4	24715.2	25541.7	25138.5	22346.5	20723.7	24160.8
55°	25692.9	25269.6	23949.1	22064.3	24191.0	26408.6	26993.2	26690.8	23646.7	21378.8	25078.1
57.5°	26489.2	26398.5	25370.4	23283.9	25632.4	28152.3	28152.3	27779.4	24775.7	22326.3	26438.8
60°	27638.3	27839.9	26418.6	24090.3	26126.3	28051.5	29513.1	29079.7	25914.7	23989.5	27981.0
62.5°	27265.3	27910.4	27769.3	25823.9	26690.8	28545.4	29341.7	29664.3	27325.8	26015.5	30037.2
65°	26065.9	26751.3	27759.2	26962.9	26267.4	27346.0	27749.1	28726.9	28031.4	27920.5	30883.9
67.5°	24634.5	25380.4	26005.4	27729.0	25410.7	26126.3	25773.5	26086.0	27265.3	30007.0	31367.7
70°	21509.9	22225.5	23213.3	26025.5	23142.8	22497.7	22407.0	22255.8	24090.3	29261.1	29170.4
72.5°	17689.7	18022.3	19655.2	21157.1	17125.2	17004.3	17145.4	16974.1	19100.8	26489.2	24987.3
75°	13244.6	13577.2	14504.5	16248.3	11662.1	10966.6	11773.0	12569.3	14585.2	20562.4	17951.8
77.5°	9958.6	10382.0	10966.6	12156.0	8557.6	7469.0	7579.9	8335.8	10543.3	16470.1	10059.4
80°	6461.0	6410.6	7539.5	8366.1	6440.9	6642.5	6360.2	6914.6	7640.3	8809.6	5140.6
82.5°	3729.5	3779.9	4253.6	4797.9	4485.4	5130.5	3699.2	6178.8	5453.1	3588.3	1915.1
85°	2096.6	2187.3	2620.7	3326.3	2812.2	1884.9	1542.2	3064.2	3427.1	1471.6	927.3
87.5°	211.7	181.4	352.8	1260.0	766.0	312.5	463.7	735.8	826.5	554.4	272.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599571  
 CATALOG NUMBER: IFLD-L-SA8C-760-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1
2.5°	14746.5	14746.5	14494.5	14071.1	13899.8	13597.4	13184.1	13315.2	13174.0	12660.0	12528.9
5°	14141.7	13657.9	13133.7	12488.6	12115.7	11349.6	11107.7	10674.3	10744.9	10311.4	10331.6
7.5°	12881.7	12498.7	11611.7	10765.0	10029.2	9364.0	8426.5	8073.8	7731.1	7559.7	7761.3
10°	12145.9	11430.3	10220.7	9112.0	8134.2	7539.5	6914.6	6430.8	5987.3	5654.7	5584.1
12.5°	11611.7	10976.7	9515.1	8164.5	7398.4	6914.6	6340.1	5674.8	5241.4	4666.9	4495.5
15°	11450.4	10674.3	9132.1	7791.5	7045.6	6249.4	5594.2	4939.0	4374.5	3769.8	3558.1
17.5°	12004.8	11107.7	9122.0	7489.1	6440.9	5584.1	4676.9	3941.1	3366.6	2812.2	2681.2
20°	12942.2	11571.4	9414.3	7307.7	5866.3	4717.3	3689.1	2953.3	2308.2	1945.4	1854.6
22.5°	14010.6	12357.6	9444.6	6823.9	5291.8	3850.4	2691.3	1945.4	1582.5	1411.1	1360.7
25°	15321.0	13617.5	9807.5	6430.8	4616.5	2923.1	1915.1	1491.8	1280.1	1179.3	1159.2
27.5°	16399.5	14494.5	10200.6	6017.5	3951.2	2167.1	1501.9	1219.6	1108.8	1008.0	997.9
30°	17518.3	15502.4	10311.4	5765.5	3376.7	1784.1	1290.2	1078.5	957.6	907.2	897.1
32.5°	18496.1	16601.1	10664.2	5352.3	2832.4	1572.4	1169.2	967.6	887.0	806.4	796.3
35°	19756.0	17236.1	10835.6	5130.5	2630.8	1421.2	1068.4	887.0	766.0	715.7	695.5
37.5°	21106.7	17851.0	10946.4	4959.2	2459.4	1330.5	1008.0	836.6	725.7	655.2	635.0
40°	22366.6	18717.8	10785.2	4747.5	2328.4	1219.6	967.6	776.1	675.3	604.8	574.5
42.5°	23334.3	19564.5	10734.8	4545.9	2187.3	1179.3	917.2	745.9	635.0	554.4	544.3
45°	23878.6	20139.0	10382.0	4384.6	2076.4	1199.5	897.1	705.6	604.8	534.2	493.9
47.5°	23747.5	20582.5	10472.7	4334.2	1925.2	1118.8	887.0	675.3	554.4	493.9	463.7
50°	24473.3	21479.6	10321.5	4173.0	1814.3	1008.0	967.6	675.3	544.3	473.7	443.5
52.5°	24594.2	22296.1	10644.1	3880.6	1643.0	927.3	957.6	665.3	524.1	453.6	413.3
55°	25602.2	23243.6	11269.0	3719.4	1501.9	806.4	876.9	645.1	473.7	413.3	393.1
57.5°	26973.0	25209.1	11672.2	3568.2	1310.3	705.6	735.8	635.0	433.4	383.0	352.8
60°	28293.4	25995.3	11702.4	3296.0	1128.9	635.0	574.5	635.0	403.2	342.7	312.5
62.5°	29281.2	25995.3	11500.8	3064.2	987.8	564.5	504.0	604.8	362.9	302.4	282.2
65°	28747.0	25299.8	10976.7	2872.7	897.1	493.9	433.4	463.7	322.5	262.1	241.9
67.5°	27789.5	23132.7	9817.5	2640.9	887.0	433.4	372.9	342.7	282.2	231.8	211.7
70°	26257.4	20209.6	8174.6	2378.8	866.8	393.1	332.6	292.3	252.0	201.6	181.4
72.5°	21157.1	16691.8	6713.0	2227.6	846.7	342.7	282.2	252.0	211.7	171.4	151.2
75°	14655.7	10664.2	5170.8	1905.0	826.5	312.5	262.1	221.8	181.4	141.1	131.0
77.5°	8789.4	7126.3	3336.3	1431.3	544.3	252.0	221.8	171.4	151.2	121.0	110.9
80°	4112.5	3366.6	1350.7	554.4	262.1	181.4	151.2	131.0	121.0	100.8	90.7
82.5°	1612.7	1421.2	655.2	322.5	211.7	141.1	121.0	110.9	100.8	80.6	70.6
85°	866.8	766.0	312.5	221.8	151.2	100.8	100.8	90.7	80.6	70.6	60.5
87.5°	191.5	141.1	131.0	131.0	110.9	80.6	80.6	70.6	60.5	50.4	40.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599571  
 CATALOG NUMBER: IFLD-L-SA8C-760-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1
2.5°	12458.4	12609.6	12367.7	12518.9	12307.2	12468.5	12488.6	12337.4	12377.8	12579.3	12670.1
5°	10613.8	10513.0	10291.3	10220.7	10230.8	10099.8	10150.2	10220.7	10331.6	10392.1	10573.5
7.5°	7650.4	7882.2	7872.2	8043.5	8053.6	8033.4	7892.3	7589.9	7690.7	7610.1	7710.9
10°	5473.2	5574.0	5765.5	5876.4	6078.0	5967.1	5644.6	5523.6	5463.1	5453.1	5553.9
12.5°	4374.5	4132.6	4112.5	4152.8	4253.6	4122.6	3961.3	3820.2	3890.7	4031.8	4142.7
15°	3386.7	3185.2	2923.1	2882.8	2902.9	2842.4	2671.1	2489.7	2540.1	2681.2	2761.8
17.5°	2600.5	2368.7	2187.3	2066.3	2026.0	1814.3	1562.3	1411.1	1370.8	1360.7	1431.3
20°	1753.9	1713.5	1683.3	1532.1	1532.1	1229.7	1018.0	907.2	907.2	927.3	937.4
22.5°	1310.3	1260.0	1270.0	1239.8	1159.2	917.2	806.4	776.1	776.1	796.3	796.3
25°	1139.0	1068.4	1048.3	1038.2	957.6	786.2	705.6	675.3	675.3	695.5	695.5
27.5°	967.6	947.5	917.2	876.9	806.4	675.3	624.9	594.7	604.8	614.9	604.8
30°	887.0	836.6	796.3	796.3	715.7	604.8	564.5	544.3	524.1	544.3	554.4
32.5°	786.2	756.0	735.8	705.6	614.9	534.2	493.9	473.7	463.7	463.7	473.7
35°	675.3	675.3	655.2	614.9	534.2	483.8	433.4	413.3	403.2	413.3	413.3
37.5°	604.8	574.5	584.6	544.3	473.7	423.3	372.9	352.8	352.8	342.7	352.8
40°	564.5	514.1	483.8	463.7	423.3	362.9	322.5	302.4	292.3	292.3	292.3
42.5°	504.0	463.7	403.2	393.1	383.0	312.5	262.1	252.0	241.9	231.8	231.8
45°	473.7	413.3	362.9	312.5	312.5	262.1	221.8	201.6	191.5	181.4	191.5
47.5°	433.4	372.9	312.5	262.1	252.0	211.7	171.4	151.2	141.1	141.1	141.1
50°	413.3	332.6	272.1	221.8	191.5	171.4	131.0	110.9	100.8	100.8	100.8
52.5°	383.0	312.5	241.9	191.5	151.2	131.0	100.8	80.6	70.6	70.6	70.6
55°	342.7	282.2	211.7	161.3	131.0	100.8	70.6	50.4	40.3	40.3	40.3
57.5°	322.5	252.0	181.4	141.1	100.8	70.6	40.3	30.2	30.2	20.2	30.2
60°	292.3	221.8	151.2	110.9	80.6	50.4	30.2	10.1	10.1	10.1	10.1
62.5°	252.0	191.5	131.0	90.7	60.5	30.2	10.1	0.0	0.0	0.0	0.0
65°	211.7	151.2	100.8	70.6	40.3	10.1	0.0	0.0	0.0	0.0	0.0
67.5°	181.4	131.0	80.6	50.4	30.2	0.0	0.0	0.0	0.0	0.0	0.0
70°	161.3	110.9	60.5	40.3	10.1	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	131.0	90.7	50.4	20.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	110.9	70.6	30.2	10.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	90.7	50.4	20.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	70.6	40.3	10.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	60.5	30.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	40.3	10.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	30.2	10.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





TEST NUMBER: P599571  
 CATALOG NUMBER: IFLD-L-SA8C-760-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

	285°	295°	305°	315°	325°	335°	345°	355°	358°	360°
0°	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1	14192.1
2.5°	12801.1	12740.6	13043.0	13536.9	13788.9	14282.8	14403.8	14716.2	14635.6	14746.5
5°	10593.7	10714.6	11158.1	11883.9	12145.9	12861.6	13536.9	14212.2	14645.7	14857.3
7.5°	7862.1	8265.3	8809.6	9474.8	10150.2	11087.6	12236.6	13022.8	13446.2	13899.8
10°	5856.2	6289.7	6914.6	7569.8	8668.5	9716.7	10865.8	11843.5	12206.4	12629.7
12.5°	4606.4	5281.7	6007.4	6713.0	7368.2	8366.1	9787.3	11208.5	11601.6	11924.2
15°	3205.3	4031.8	5070.0	5987.3	6904.5	7771.4	9243.0	10966.6	11500.8	12045.1
17.5°	1774.0	2429.2	3618.6	4908.8	6259.4	7589.9	9424.4	11410.1	12216.5	12599.5
20°	1028.1	1290.2	2136.9	3669.0	5453.1	7196.8	9515.1	12246.7	13315.2	13506.7
22.5°	846.7	937.4	1209.6	2298.1	4465.3	6944.8	9978.8	13416.0	14504.5	14958.1
25°	725.7	796.3	937.4	1380.9	3376.7	6410.6	10271.1	14877.5	15885.5	16379.4
27.5°	645.1	715.7	826.5	1018.0	2298.1	5674.8	10754.9	16197.9	17205.9	17881.2
30°	564.5	624.9	735.8	866.8	1592.6	4848.3	11168.2	17165.6	18586.8	18798.5
32.5°	504.0	554.4	635.0	745.9	1179.3	3679.1	11500.8	18163.4	19362.9	19826.6
35°	433.4	493.9	544.3	635.0	897.1	2771.9	11299.2	18939.6	20501.9	21056.3
37.5°	383.0	423.3	473.7	534.2	756.0	2167.1	10886.0	19866.9	21479.6	21993.7
40°	322.5	352.8	413.3	473.7	685.4	1673.2	10412.2	20985.7	22850.5	23757.6
42.5°	272.1	302.4	342.7	443.5	564.5	1239.8	9454.7	21852.6	23959.2	24725.3
45°	211.7	252.0	312.5	443.5	453.6	917.2	8466.9	22497.7	24584.2	24967.2
47.5°	161.3	201.6	302.4	383.0	362.9	635.0	7297.6	23233.5	25229.2	25582.0
50°	121.0	161.3	342.7	332.6	302.4	483.8	6561.8	23747.5	25269.6	25461.1
52.5°	80.6	121.0	282.2	252.0	252.0	423.3	6360.2	23727.4	25370.4	24957.1
55°	60.5	90.7	161.3	181.4	221.8	372.9	6178.8	24483.4	25400.6	25692.9
57.5°	40.3	70.6	110.9	141.1	191.5	322.5	5805.9	25390.5	26338.0	26489.2
60°	20.2	50.4	80.6	110.9	161.3	282.2	5281.7	26055.8	27477.0	27638.3
62.5°	10.1	30.2	60.5	90.7	131.0	221.8	4737.4	24997.4	26983.1	27265.3
65°	0.0	20.2	40.3	60.5	80.6	161.3	3850.4	22568.2	25027.7	26065.9
67.5°	0.0	0.0	20.2	40.3	50.4	121.0	2902.9	20532.2	23223.4	24634.5
70°	0.0	0.0	10.1	10.1	30.2	90.7	1854.6	17004.3	20733.7	21509.9
72.5°	0.0	0.0	0.0	0.0	10.1	60.5	1078.5	12629.7	16248.3	17689.7
75°	0.0	0.0	0.0	0.0	0.0	50.4	544.3	8124.2	11309.3	13244.6
77.5°	0.0	0.0	0.0	0.0	0.0	40.3	292.3	5241.4	8335.8	9958.6
80°	0.0	0.0	0.0	0.0	0.0	10.1	171.4	3044.0	5332.1	6461.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	70.6	1491.8	3185.2	3729.5
85°	0.0	0.0	0.0	0.0	0.0	0.0	20.2	796.3	1592.6	2096.6
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	30.2	110.9	211.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)