

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599572

Luminaire Tested: **IFLD-L-SA8D-760-U-SLL-HSS**

Issue Date: 05/04/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P599572
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/04/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-L-SA8D-760-U-SLL-HSS
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens with House Side Shield
 Light Source: (128) 5700K CCT, 70 CRI LEDS
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 41533.0 lumens
 Efficiency: N/A
 Efficacy: 85.1 lumens/watt
 Spacing Criteria (0/90/45): 0.53 / 0.46 / 0.63
 Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
 CIE Type: Direct

Input Watts (W): 488.3
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599572
CATALOG NUMBER: IFLD-L-SA8D-760-U-SLL-HSS

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°

TEST NUMBER: P599572
 CATALOG NUMBER: IFLD-L-SA8D-760-U-SLL-HSS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	106	100	95	90	103	98	93	89	94	90	86	90	86	83	86	83	81	79	79	79	79
2	94	84	76	69	91	82	75	68	78	72	66	75	70	65	72	67	63	61	61	61	61
3	84	72	62	54	81	70	61	53	67	59	52	64	57	51	61	55	50	48	48	48	48
4	76	62	51	44	73	60	51	43	58	49	43	55	48	42	53	46	41	39	39	39	39
5	69	54	44	36	67	53	43	36	51	42	35	48	41	35	46	40	34	32	32	32	32
6	63	48	38	30	61	47	37	30	45	36	30	43	35	30	41	35	29	27	27	27	27
7	58	43	33	26	56	42	33	26	40	32	26	39	31	26	37	31	25	23	23	23	23
8	54	39	29	23	52	38	29	23	37	28	23	35	28	22	34	27	22	20	20	20	20
9	50	35	26	20	49	35	26	20	34	26	20	32	25	20	31	25	20	18	18	18	18
10	47	33	24	18	46	32	24	18	31	23	18	30	23	18	29	23	18	16	16	16	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	84045	84045	84045	84045
5°	88321	84067	61417	61777
10°	75947	73038	33579	32791
15°	73847	70201	21814	16438
20°	85119	81562	11688	5844
25°	107026	100110	7574	4545
30°	128546	119793	6134	3722
35°	152225	142825	5028	2987
40°	183661	172907	4442	2259
45°	209099	199982	4137	1519
50°	234573	225471	4086	929
55°	265271	264334	4058	417
60°	327347	335107	3701	119
65°	365251	402821	3390	0
70°	372438	454640	3141	0
75°	303048	335335	2999	0
80°	220342	140248	3093	0
85°	142453	58898	4106	0

TEST NUMBER: P599572
 CATALOG NUMBER: IFLD-L-SA8D-760-U-SLL-HSS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1186.3	2.9
10°-20°	2326.4	5.6
20°-30°	3219.3	7.8
30°-40°	4549.7	11.0
40°-50°	6194.5	14.9
50°-60°	8204.3	19.8
60°-70°	9525.8	22.9
70°-80°	5394.5	13.0
80°-90°	932.1	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6732.1	16.2
0°-40°	11281.8	27.2
0°-60°	25680.6	61.8
0°-90°	41533.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	41533.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	15616	15616	15616	15616	15616	
5°	16348	15561	11368	11435	16348	1468
15°	13254	12599	3915	2950	13254	3887
25°	18023	16858	1276	765	18023	8406
35°	23169	21738	765	455	23169	14606
45°	27472	26275	544	200	27472	21299
55°	28271	28171	432	44	28271	25614
65°	28681	31632	266	0	28681	27959
75°	14574	16126	144	0	14574	15906
85°	2307	954	66	0	2307	2772
90°	0	0	0	0	0	

TEST NUMBER: P599572
 CATALOG NUMBER: IFLD-L-SA8D-760-U-SLL-HSS

CANDELA DISTRIBUTION (FULL):

	0°	2°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1
2.5°	16226.1	16570.0	16581.0	16736.3	16891.6	16891.6	17257.6	17168.9	16847.2	16791.8	16558.9
5°	16348.1	16470.1	16558.9	17346.3	18011.8	17945.2	18144.9	18011.8	17390.7	16592.1	16048.7
7.5°	15294.5	15427.6	15782.5	17124.5	18022.9	18322.3	18699.4	17867.6	17213.2	15771.4	14728.8
10°	13897.0	14152.1	14806.5	16337.0	17446.1	18400.0	18400.0	17734.5	16470.1	15061.6	13786.1
12.5°	13120.7	13630.8	13985.8	15538.5	16980.3	17634.7	17612.5	17257.6	16436.9	14662.3	13220.5
15°	13253.7	13397.9	14152.1	15361.0	16314.9	16281.6	16680.9	16570.0	15993.2	15017.2	13431.2
17.5°	13863.8	14085.6	14739.9	15361.0	15815.8	15682.7	15671.6	16204.0	16237.2	15616.1	14218.7
20°	14861.9	15516.3	15826.9	16015.4	15460.9	14895.2	14828.7	15571.8	16148.5	16381.4	15161.4
22.5°	16459.0	16891.6	17523.8	16558.9	15117.0	14407.2	14274.1	15094.9	16259.4	17290.9	16381.4
25°	18022.9	18355.6	18965.6	17723.4	15505.2	14307.4	14074.5	14784.3	16680.9	18555.2	17856.5
27.5°	19675.4	19963.8	20030.3	18577.4	15715.9	14107.8	13830.5	14784.3	17035.8	19220.7	19620.0
30°	20684.7	21028.5	21095.1	19331.6	16059.8	14274.1	14141.0	14850.8	17279.8	19786.3	20884.4
32.5°	21816.0	21904.7	21849.3	19464.7	16436.9	14762.1	14207.6	15294.5	17557.1	20462.9	22037.8
35°	23169.1	23324.4	22758.7	20074.7	17279.8	15072.7	14873.0	15837.9	18034.0	20773.4	23435.3
37.5°	24200.6	24688.6	23413.1	20307.6	17446.1	15727.0	15760.3	16969.2	18366.7	21150.5	24976.9
40°	26141.5	25320.8	24522.2	21106.2	18078.3	16836.1	16658.7	18133.8	19486.9	21394.5	25986.2
42.5°	27206.2	26773.7	24954.8	21183.8	19054.3	18366.7	18411.1	19453.6	20074.7	22082.2	26263.5
45°	27472.4	27017.7	25542.6	21239.3	20019.3	20174.5	20939.8	21139.4	20939.8	22536.9	26784.8
47.5°	28149.0	27161.9	25476.0	21982.4	21583.1	22182.0	23158.0	23590.6	22115.5	22370.5	27028.8
50°	28015.9	27450.2	25331.8	22292.9	23490.7	25076.8	25731.1	25553.7	23424.2	22026.7	26762.6
52.5°	27461.3	26851.3	25775.5	23135.8	25276.4	27195.1	28104.6	27661.0	24588.7	22803.1	26585.1
55°	28271.0	27805.1	26352.2	24278.2	26618.4	29058.4	29701.7	29369.0	26019.5	23524.0	27594.4
57.5°	29147.1	29047.3	27916.0	25620.2	28204.4	30977.2	30977.2	30566.8	27261.7	24566.6	29091.7
60°	30411.5	30633.3	29069.5	26507.5	28747.9	30866.3	32474.4	31997.5	28515.0	26396.6	30788.6
62.5°	30001.2	30711.0	30555.7	28415.1	29369.0	31409.7	32285.9	32640.8	30067.7	28625.9	33051.2
65°	28681.3	29435.5	30544.6	29668.4	28903.1	30089.9	30533.5	31609.4	30844.1	30722.1	33982.8
67.5°	27106.4	27927.1	28614.8	30511.3	27960.4	28747.9	28359.7	28703.5	30001.2	33017.9	34515.2
70°	23668.2	24455.7	25542.6	28637.0	25464.9	24755.1	24655.3	24488.9	26507.5	32197.2	32097.4
72.5°	19464.7	19830.7	21627.5	23280.0	18843.6	18710.5	18865.8	18677.2	21017.4	29147.1	27494.6
75°	14573.6	14939.6	15959.9	17878.7	12832.3	12067.0	12954.3	13830.5	16048.7	22625.6	19753.1
77.5°	10957.9	11423.7	12067.0	13375.7	9416.3	8218.4	8340.4	9172.3	11601.2	18122.7	11068.8
80°	7109.3	7053.9	8296.1	9205.5	7087.1	7309.0	6998.4	7608.4	8407.0	9693.5	5656.4
82.5°	4103.7	4159.1	4680.4	5279.3	4935.5	5645.3	4070.4	6798.8	6000.2	3948.4	2107.3
85°	2306.9	2406.7	2883.7	3660.0	3094.4	2074.0	1696.9	3371.7	3770.9	1619.3	1020.4
87.5°	232.9	199.6	388.2	1386.4	842.9	343.8	510.2	809.6	909.5	610.0	299.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599572
 CATALOG NUMBER: IFLD-L-SA8D-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1
2.5°	16226.1	16226.1	15948.9	15483.0	15294.5	14961.8	14507.0	14651.2	14495.9	13930.3	13786.1
5°	15560.7	15028.3	14451.6	13741.7	13331.4	12488.5	12222.3	11745.4	11823.0	11346.1	11368.3
7.5°	14174.3	13752.8	12776.8	11845.2	11035.5	10303.5	9272.1	8883.9	8506.8	8318.3	8540.1
10°	13364.7	12577.2	11246.3	10026.3	8950.4	8296.1	7608.4	7076.1	6588.1	6222.1	6144.4
12.5°	12776.8	12078.1	10469.9	8983.7	8140.8	7608.4	6976.2	6244.2	5767.3	5135.1	4946.6
15°	12599.4	11745.4	10048.4	8573.3	7752.6	6876.4	6155.5	5434.6	4813.5	4148.0	3915.1
17.5°	13209.4	12222.3	10037.4	8240.6	7087.1	6144.4	5146.2	4336.6	3704.4	3094.4	2950.2
20°	14240.8	12732.5	10359.0	8041.0	6455.0	5190.6	4059.3	3249.7	2539.8	2140.6	2040.7
22.5°	15416.5	13597.6	10392.3	7508.6	5822.8	4236.8	2961.3	2140.6	1741.3	1552.7	1497.3
25°	16858.3	14983.9	10791.5	7076.1	5079.7	3216.4	2107.3	1641.5	1408.6	1297.6	1275.5
27.5°	18045.1	15948.9	11224.1	6621.3	4347.7	2384.6	1652.6	1342.0	1220.0	1109.1	1098.0
30°	19276.2	17058.0	11346.1	6344.1	3715.5	1963.1	1419.6	1186.7	1053.6	998.2	987.1
32.5°	20352.0	18266.9	11734.3	5889.3	3116.6	1730.2	1286.6	1064.7	976.0	887.3	876.2
35°	21738.4	18965.6	11922.8	5645.3	2894.8	1563.8	1175.6	976.0	842.9	787.5	765.3
37.5°	23224.6	19642.2	12044.8	5456.8	2706.2	1464.0	1109.1	920.6	798.6	720.9	698.7
40°	24610.9	20596.0	11867.4	5223.9	2562.0	1342.0	1064.7	854.0	743.1	665.5	632.2
42.5°	25675.7	21527.6	11811.9	5002.0	2406.7	1297.6	1009.3	820.7	698.7	610.0	598.9
45°	26274.6	22159.8	11423.7	4824.6	2284.7	1319.8	987.1	776.4	665.5	587.8	543.5
47.5°	26130.4	22647.8	11523.5	4769.1	2118.4	1231.1	976.0	743.1	610.0	543.5	510.2
50°	26928.9	23634.9	11357.2	4591.7	1996.4	1109.1	1064.7	743.1	598.9	521.3	488.0
52.5°	27062.0	24533.3	11712.1	4270.0	1807.8	1020.4	1053.6	732.0	576.7	499.1	454.7
55°	28171.1	25575.8	12399.7	4092.6	1652.6	887.3	964.9	709.8	521.3	454.7	432.5
57.5°	29679.5	27738.6	12843.4	3926.2	1441.8	776.4	809.6	698.7	476.9	421.5	388.2
60°	31132.4	28603.7	12876.7	3626.8	1242.2	698.7	632.2	698.7	443.6	377.1	343.8
62.5°	32219.4	28603.7	12654.8	3371.7	1086.9	621.1	554.6	665.5	399.3	332.7	310.5
65°	31631.5	27838.4	12078.1	3160.9	987.1	543.5	476.9	510.2	354.9	288.4	266.2
67.5°	30577.9	25453.8	10802.6	2905.8	976.0	476.9	410.4	377.1	310.5	255.1	232.9
70°	28892.1	22237.5	8994.8	2617.5	953.8	432.5	366.0	321.6	277.3	221.8	199.6
72.5°	23280.0	18366.7	7386.6	2451.1	931.6	377.1	310.5	277.3	232.9	188.5	166.4
75°	16126.3	11734.3	5689.7	2096.2	909.5	343.8	288.4	244.0	199.6	155.3	144.2
77.5°	9671.4	7841.3	3671.1	1574.9	598.9	277.3	244.0	188.5	166.4	133.1	122.0
80°	4525.1	3704.4	1486.2	610.0	288.4	199.6	166.4	144.2	133.1	110.9	99.8
82.5°	1774.6	1563.8	720.9	354.9	232.9	155.3	133.1	122.0	110.9	88.7	77.6
85°	953.8	842.9	343.8	244.0	166.4	110.9	110.9	99.8	88.7	77.6	66.5
87.5°	210.7	155.3	144.2	144.2	122.0	88.7	88.7	77.6	66.5	55.5	44.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599572
 CATALOG NUMBER: IFLD-L-SA8D-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1
2.5°	13708.5	13874.8	13608.7	13775.0	13542.1	13719.6	13741.7	13575.4	13619.7	13841.6	13941.4
5°	11678.8	11567.9	11323.9	11246.3	11257.4	11113.2	11168.6	11246.3	11368.3	11434.8	11634.5
7.5°	8418.1	8673.2	8662.1	8850.6	8861.7	8839.5	8684.3	8351.5	8462.4	8373.7	8484.6
10°	6022.4	6133.3	6344.1	6466.1	6687.9	6565.9	6211.0	6077.9	6011.3	6000.2	6111.1
12.5°	4813.5	4547.3	4525.1	4569.5	4680.4	4536.2	4358.8	4203.5	4281.1	4436.4	4558.4
15°	3726.6	3504.8	3216.4	3172.0	3194.2	3127.7	2939.1	2739.5	2794.9	2950.2	3038.9
17.5°	2861.5	2606.4	2406.7	2273.7	2229.3	1996.4	1719.1	1552.7	1508.4	1497.3	1574.9
20°	1929.8	1885.5	1852.2	1685.8	1685.8	1353.1	1120.2	998.2	998.2	1020.4	1031.5
22.5°	1441.8	1386.4	1397.5	1364.2	1275.5	1009.3	887.3	854.0	854.0	876.2	876.2
25°	1253.3	1175.6	1153.5	1142.4	1053.6	865.1	776.4	743.1	743.1	765.3	765.3
27.5°	1064.7	1042.6	1009.3	964.9	887.3	743.1	687.6	654.4	665.5	676.6	665.5
30°	976.0	920.6	876.2	876.2	787.5	665.5	621.1	598.9	576.7	598.9	610.0
32.5°	865.1	831.8	809.6	776.4	676.6	587.8	543.5	521.3	510.2	510.2	521.3
35°	743.1	743.1	720.9	676.6	587.8	532.4	476.9	454.7	443.6	454.7	454.7
37.5°	665.5	632.2	643.3	598.9	521.3	465.8	410.4	388.2	388.2	377.1	388.2
40°	621.1	565.6	532.4	510.2	465.8	399.3	354.9	332.7	321.6	321.6	321.6
42.5°	554.6	510.2	443.6	432.5	421.5	343.8	288.4	277.3	266.2	255.1	255.1
45°	521.3	454.7	399.3	343.8	343.8	288.4	244.0	221.8	210.7	199.6	210.7
47.5°	476.9	410.4	343.8	288.4	277.3	232.9	188.5	166.4	155.3	155.3	155.3
50°	454.7	366.0	299.5	244.0	210.7	188.5	144.2	122.0	110.9	110.9	110.9
52.5°	421.5	343.8	266.2	210.7	166.4	144.2	110.9	88.7	77.6	77.6	77.6
55°	377.1	310.5	232.9	177.5	144.2	110.9	77.6	55.5	44.4	44.4	44.4
57.5°	354.9	277.3	199.6	155.3	110.9	77.6	44.4	33.3	33.3	22.2	33.3
60°	321.6	244.0	166.4	122.0	88.7	55.5	33.3	11.1	11.1	11.1	11.1
62.5°	277.3	210.7	144.2	99.8	66.5	33.3	11.1	0.0	0.0	0.0	0.0
65°	232.9	166.4	110.9	77.6	44.4	11.1	0.0	0.0	0.0	0.0	0.0
67.5°	199.6	144.2	88.7	55.5	33.3	0.0	0.0	0.0	0.0	0.0	0.0
70°	177.5	122.0	66.5	44.4	11.1	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	144.2	99.8	55.5	22.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	122.0	77.6	33.3	11.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	99.8	55.5	22.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	77.6	44.4	11.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	66.5	33.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	44.4	11.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	33.3	11.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599572
 CATALOG NUMBER: IFLD-L-SA8D-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	358°	360°
0°	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1	15616.1
2.5°	14085.6	14019.0	14351.8	14895.2	15172.5	15715.9	15849.0	16192.9	16104.1	16226.1
5°	11656.6	11789.7	12277.7	13076.3	13364.7	14152.1	14895.2	15638.3	16115.2	16348.1
7.5°	8651.0	9094.6	9693.5	10425.5	11168.6	12200.1	13464.5	14329.6	14795.4	15294.5
10°	6443.9	6920.8	7608.4	8329.3	9538.3	10691.7	11956.1	13031.9	13431.2	13897.0
12.5°	5068.6	5811.7	6610.2	7386.6	8107.5	9205.5	10769.4	12333.2	12765.7	13120.7
15°	3526.9	4436.4	5578.8	6588.1	7597.3	8551.2	10170.4	12067.0	12654.8	13253.7
17.5°	1952.0	2672.9	3981.7	5401.3	6887.5	8351.5	10370.1	12555.0	13442.3	13863.8
20°	1131.3	1419.6	2351.3	4037.1	6000.2	7919.0	10469.9	13475.6	14651.2	14861.9
22.5°	931.6	1031.5	1330.9	2528.7	4913.3	7641.7	10980.1	14762.1	15959.9	16459.0
25°	798.6	876.2	1031.5	1519.5	3715.5	7053.9	11301.7	16370.3	17479.4	18022.9
27.5°	709.8	787.5	909.5	1120.2	2528.7	6244.2	11834.1	17823.2	18932.3	19675.4
30°	621.1	687.6	809.6	953.8	1752.4	5334.8	12288.8	18888.0	20451.8	20684.7
32.5°	554.6	610.0	698.7	820.7	1297.6	4048.2	12654.8	19986.0	21305.8	21816.0
35°	476.9	543.5	598.9	698.7	987.1	3050.0	12433.0	20840.0	22559.1	23169.1
37.5°	421.5	465.8	521.3	587.8	831.8	2384.6	11978.3	21860.4	23634.9	24200.6
40°	354.9	388.2	454.7	521.3	754.2	1841.1	11457.0	23091.5	25143.3	26141.5
42.5°	299.5	332.7	377.1	488.0	621.1	1364.2	10403.4	24045.3	26363.3	27206.2
45°	232.9	277.3	343.8	488.0	499.1	1009.3	9316.4	24755.1	27051.0	27472.4
47.5°	177.5	221.8	332.7	421.5	399.3	698.7	8029.9	25564.8	27760.8	28149.0
50°	133.1	177.5	377.1	366.0	332.7	532.4	7220.2	26130.4	27805.1	28015.9
52.5°	88.7	133.1	310.5	277.3	277.3	465.8	6998.4	26108.2	27916.0	27461.3
55°	66.5	99.8	177.5	199.6	244.0	410.4	6798.8	26940.0	27949.3	28271.0
57.5°	44.4	77.6	122.0	155.3	210.7	354.9	6388.4	27938.2	28980.8	29147.1
60°	22.2	55.5	88.7	122.0	177.5	310.5	5811.7	28670.2	30234.1	30411.5
62.5°	11.1	33.3	66.5	99.8	144.2	244.0	5212.8	27505.7	29690.6	30001.2
65°	0.0	22.2	44.4	66.5	88.7	177.5	4236.8	24832.7	27539.0	28681.3
67.5°	0.0	0.0	22.2	44.4	55.5	133.1	3194.2	22592.4	25553.7	27106.4
70°	0.0	0.0	11.1	11.1	33.3	99.8	2040.7	18710.5	22814.2	23668.2
72.5°	0.0	0.0	0.0	0.0	11.1	66.5	1186.7	13897.0	17878.7	19464.7
75°	0.0	0.0	0.0	0.0	0.0	55.5	598.9	8939.3	12444.1	14573.6
77.5°	0.0	0.0	0.0	0.0	0.0	44.4	321.6	5767.3	9172.3	10957.9
80°	0.0	0.0	0.0	0.0	0.0	11.1	188.5	3349.5	5867.1	7109.3
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	77.6	1641.5	3504.8	4103.7
85°	0.0	0.0	0.0	0.0	0.0	0.0	22.2	876.2	1752.4	2306.9
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	33.3	122.0	232.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)