

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599546

Luminaire Tested: **IFLD-S-SA2C-760-U-SLL-HSS**

Issue Date: 05/04/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P599546
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/04/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-S-SA2C-760-U-SLL-HSS
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens with House Side Shield
 Light Source: (32) 5700K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 10589.2 lumens
 Efficiency: N/A
 Efficacy: 97.9 lumens/watt
 Spacing Criteria (0/90/45): 0.53 / 0.46 / 0.63
 Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
 CIE Type: Direct

Input Watts (W): 108.2
 Input Voltage (V): 120
 Input Current (A_{in}): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599546
CATALOG NUMBER: IFLD-S-SA2C-760-U-SLL-HSS

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ··· 90°-270° - · 135°-315°

TEST NUMBER: P599546
 CATALOG NUMBER: IFLD-S-SA2C-760-U-SLL-HSS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	106	100	95	90	103	98	93	89	94	90	86	90	86	83	86	83	81	79			79	
2	94	84	76	69	91	82	75	68	78	72	66	75	70	65	72	67	63	61			61	
3	84	72	62	54	81	70	61	53	67	59	52	64	57	51	61	55	50	48			48	
4	76	62	51	44	73	60	51	43	58	49	43	55	48	42	53	46	41	39			39	
5	69	54	44	36	67	53	43	36	51	42	35	48	41	35	46	40	34	32			32	
6	63	48	38	30	61	47	37	30	45	36	30	43	35	30	41	35	29	27			27	
7	58	43	33	26	56	42	33	26	40	32	26	39	31	26	37	31	25	23			23	
8	54	39	29	23	52	38	29	23	37	28	23	35	28	22	34	27	22	20			20	
9	50	35	26	20	49	35	26	20	34	26	20	32	25	20	31	25	20	18			18	
10	47	33	24	18	46	32	24	18	31	23	18	30	23	18	29	23	18	16			16	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	85713	85713	85713	85713
5°	90073	85734	62637	63002
10°	77454	74486	34246	33441
15°	75313	71593	22247	16764
20°	86808	83180	11920	5961
25°	109149	102097	7725	4634
30°	131097	122168	6257	3796
35°	155245	145658	5127	3046
40°	187304	176338	4530	2304
45°	213249	203951	4220	1550
50°	239225	229945	4166	948
55°	270535	269578	4140	424
60°	333841	341754	3776	121
65°	372498	410814	3459	0
70°	379824	463658	3204	0
75°	309061	341991	3061	0
80°	224715	143029	3149	0
85°	145288	60071	4199	0

TEST NUMBER: P599546
 CATALOG NUMBER: IFLD-S-SA2C-760-U-SLL-HSS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	302.5	2.9
10°-20°	593.1	5.6
20°-30°	820.8	7.8
30°-40°	1160.0	11.0
40°-50°	1579.4	14.9
50°-60°	2091.8	19.8
60°-70°	2428.7	22.9
70°-80°	1375.4	13.0
80°-90°	237.6	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1716.4	16.2
0°-40°	2876.4	27.2
0°-60°	6547.5	61.8
0°-90°	10589.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10589.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	3982	3982	3982	3982	3982	
5°	4168	3967	2898	2915	4168	374
15°	3379	3212	998	752	3379	991
25°	4595	4298	325	195	4595	2143
35°	5907	5542	195	116	5907	3724
45°	7004	6699	139	51	7004	5430
55°	7208	7182	110	11	7208	6530
65°	7313	8065	68	0	7313	7128
75°	3716	4112	37	0	3716	4055
85°	588	243	17	0	588	707
90°	0	0	0	0	0	

TEST NUMBER: P599546
 CATALOG NUMBER: IFLD-S-SA2C-760-U-SLL-HSS

CANDELA DISTRIBUTION (FULL):

	0°	2°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5
2.5°	4137.0	4224.7	4227.5	4267.1	4306.7	4306.7	4400.0	4377.4	4295.4	4281.2	4221.8
5°	4168.1	4199.2	4221.8	4422.6	4592.3	4575.3	4626.2	4592.3	4433.9	4230.3	4091.8
7.5°	3899.5	3933.4	4023.9	4366.1	4595.1	4671.5	4767.6	4555.5	4388.7	4021.1	3755.3
10°	3543.2	3608.2	3775.1	4165.3	4448.1	4691.2	4691.2	4521.6	4199.2	3840.1	3514.9
12.5°	3345.2	3475.3	3565.8	3961.7	4329.3	4496.1	4490.5	4400.0	4190.7	3738.3	3370.7
15°	3379.2	3415.9	3608.2	3916.4	4159.6	4151.1	4252.9	4224.7	4077.6	3828.8	3424.4
17.5°	3534.7	3591.3	3758.1	3916.4	4032.4	3998.4	3995.6	4131.4	4139.8	3981.5	3625.2
20°	3789.2	3956.0	4035.2	4083.3	3941.9	3797.7	3780.7	3970.2	4117.2	4176.6	3865.5
22.5°	4196.4	4306.7	4467.9	4221.8	3854.2	3673.3	3639.3	3848.6	4145.5	4408.5	4176.6
25°	4595.1	4679.9	4835.5	4518.8	3953.2	3647.8	3588.4	3769.4	4252.9	4730.8	4552.7
27.5°	5016.4	5090.0	5106.9	4736.5	4006.9	3596.9	3526.2	3769.4	4343.4	4900.5	5002.3
30°	5273.8	5361.4	5378.4	4928.8	4094.6	3639.3	3605.4	3786.4	4405.6	5044.7	5324.7
32.5°	5562.2	5584.8	5570.7	4962.7	4190.7	3763.7	3622.4	3899.5	4476.3	5217.2	5618.8
35°	5907.2	5946.8	5802.6	5118.2	4405.6	3842.9	3792.0	4038.0	4597.9	5296.4	5975.1
37.5°	6170.2	6294.6	5969.4	5177.6	4448.1	4009.8	4018.2	4326.5	4682.8	5392.5	6368.1
40°	6665.0	6455.8	6252.2	5381.2	4609.2	4292.5	4247.3	4623.4	4968.4	5454.7	6625.4
42.5°	6936.5	6826.2	6362.5	5401.0	4858.1	4682.8	4694.1	4959.9	5118.2	5630.1	6696.1
45°	7004.4	6888.4	6512.3	5415.2	5104.1	5143.7	5338.8	5389.7	5338.8	5746.0	6829.0
47.5°	7176.8	6925.2	6495.4	5604.6	5502.8	5655.5	5904.4	6014.6	5638.5	5703.6	6891.2
50°	7142.9	6998.7	6458.6	5683.8	5989.2	6393.6	6560.4	6515.2	5972.2	5615.9	6823.4
52.5°	7001.5	6846.0	6571.7	5898.7	6444.5	6933.7	7165.5	7052.4	6269.1	5813.9	6778.1
55°	7208.0	7089.2	6718.8	6190.0	6786.6	7408.7	7572.7	7487.9	6633.9	5997.7	7035.5
57.5°	7431.3	7405.9	7117.5	6532.1	7191.0	7897.9	7897.9	7793.3	6950.6	6263.5	7417.2
60°	7753.7	7810.3	7411.6	6758.3	7329.5	7869.6	8279.7	8158.1	7270.2	6730.1	7849.9
62.5°	7649.1	7830.1	7790.5	7244.7	7487.9	8008.2	8231.6	8322.1	7666.1	7298.4	8426.7
65°	7312.6	7504.9	7787.6	7564.3	7369.1	7671.7	7784.8	8059.1	7864.0	7832.9	8664.2
67.5°	6911.0	7120.3	7295.6	7779.2	7128.8	7329.5	7230.6	7318.2	7649.1	8418.2	8800.0
70°	6034.4	6235.2	6512.3	7301.3	6492.5	6311.6	6286.1	6243.7	6758.3	8209.0	8183.5
72.5°	4962.7	5056.0	5514.1	5935.5	4804.4	4770.4	4810.0	4761.9	5358.6	7431.3	7010.0
75°	3715.7	3809.0	4069.1	4558.3	3271.7	3076.6	3302.8	3526.2	4091.8	5768.6	5036.2
77.5°	2793.8	2912.6	3076.6	3410.3	2400.8	2095.4	2126.5	2338.6	2957.8	4620.6	2822.1
80°	1812.6	1798.5	2115.2	2347.0	1806.9	1863.5	1784.3	1939.8	2143.4	2471.5	1442.2
82.5°	1046.3	1060.4	1193.3	1346.0	1258.4	1439.3	1037.8	1733.4	1529.8	1006.7	537.3
85°	588.2	613.6	735.2	933.2	788.9	528.8	432.6	859.6	961.4	412.9	260.2
87.5°	59.4	50.9	99.0	353.5	214.9	87.7	130.1	206.4	231.9	155.5	76.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599546
 CATALOG NUMBER: IFLD-S-SA2C-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5
2.5°	4137.0	4137.0	4066.3	3947.5	3899.5	3814.6	3698.7	3735.5	3695.9	3551.7	3514.9
5°	3967.3	3831.6	3684.6	3503.6	3399.0	3184.1	3116.2	2994.6	3014.4	2892.8	2898.5
7.5°	3613.9	3506.4	3257.6	3020.0	2813.6	2627.0	2364.0	2265.0	2168.9	2120.8	2177.4
10°	3407.4	3206.7	2867.3	2556.3	2282.0	2115.2	1939.8	1804.1	1679.7	1586.4	1566.6
12.5°	3257.6	3079.4	2669.4	2290.5	2075.6	1939.8	1778.7	1592.0	1470.4	1309.3	1261.2
15°	3212.3	2994.6	2561.9	2185.9	1976.6	1753.2	1569.4	1385.6	1227.2	1057.6	998.2
17.5°	3367.9	3116.2	2559.1	2101.0	1806.9	1566.6	1312.1	1105.7	944.5	788.9	752.2
20°	3630.8	3246.3	2641.1	2050.1	1645.8	1323.4	1035.0	828.5	647.6	545.8	520.3
22.5°	3930.6	3466.8	2649.6	1914.4	1484.6	1080.2	755.0	545.8	444.0	395.9	381.7
25°	4298.2	3820.3	2751.4	1804.1	1295.1	820.0	537.3	418.5	359.1	330.8	325.2
27.5°	4600.8	4066.3	2861.7	1688.2	1108.5	608.0	421.3	342.2	311.1	282.8	279.9
30°	4914.6	4349.1	2892.8	1617.5	947.3	500.5	362.0	302.6	268.6	254.5	251.7
32.5°	5188.9	4657.3	2991.8	1501.5	794.6	441.1	328.0	271.5	248.8	226.2	223.4
35°	5542.4	4835.5	3039.8	1439.3	738.0	398.7	299.7	248.8	214.9	200.8	195.1
37.5°	5921.3	5008.0	3070.9	1391.3	690.0	373.3	282.8	234.7	203.6	183.8	178.1
40°	6274.8	5251.1	3025.7	1331.9	653.2	342.2	271.5	217.7	189.5	169.7	161.2
42.5°	6546.3	5488.7	3011.6	1275.3	613.6	330.8	257.3	209.3	178.1	155.5	152.7
45°	6699.0	5649.9	2912.6	1230.1	582.5	336.5	251.7	197.9	169.7	149.9	138.6
47.5°	6662.2	5774.3	2938.0	1215.9	540.1	313.9	248.8	189.5	155.5	138.6	130.1
50°	6865.8	6026.0	2895.6	1170.7	509.0	282.8	271.5	189.5	152.7	132.9	124.4
52.5°	6899.7	6255.0	2986.1	1088.7	460.9	260.2	268.6	186.6	147.0	127.2	115.9
55°	7182.5	6520.8	3161.4	1043.4	421.3	226.2	246.0	181.0	132.9	115.9	110.3
57.5°	7567.1	7072.2	3274.5	1001.0	367.6	197.9	206.4	178.1	121.6	107.5	99.0
60°	7937.5	7292.8	3283.0	924.7	316.7	178.1	161.2	178.1	113.1	96.1	87.7
62.5°	8214.6	7292.8	3226.5	859.6	277.1	158.4	141.4	169.7	101.8	84.8	79.2
65°	8064.8	7097.7	3079.4	805.9	251.7	138.6	121.6	130.1	90.5	73.5	67.9
67.5°	7796.1	6489.7	2754.2	740.9	248.8	121.6	104.6	96.1	79.2	65.0	59.4
70°	7366.3	5669.7	2293.3	667.4	243.2	110.3	93.3	82.0	70.7	56.6	50.9
72.5°	5935.5	4682.8	1883.3	624.9	237.5	96.1	79.2	70.7	59.4	48.1	42.4
75°	4111.6	2991.8	1450.6	534.4	231.9	87.7	73.5	62.2	50.9	39.6	36.8
77.5°	2465.8	1999.2	936.0	401.5	152.7	70.7	62.2	48.1	42.4	33.9	31.1
80°	1153.7	944.5	378.9	155.5	73.5	50.9	42.4	36.8	33.9	28.3	25.4
82.5°	452.4	398.7	183.8	90.5	59.4	39.6	33.9	31.1	28.3	22.6	19.8
85°	243.2	214.9	87.7	62.2	42.4	28.3	28.3	25.4	22.6	19.8	17.0
87.5°	53.7	39.6	36.8	36.8	31.1	22.6	22.6	19.8	17.0	14.1	11.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599546
 CATALOG NUMBER: IFLD-S-SA2C-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5
2.5°	3495.1	3537.5	3469.7	3512.1	3452.7	3497.9	3503.6	3461.2	3472.5	3529.0	3554.5
5°	2977.6	2949.4	2887.1	2867.3	2870.2	2833.4	2847.6	2867.3	2898.5	2915.4	2966.3
7.5°	2146.3	2211.3	2208.5	2256.6	2259.4	2253.7	2214.1	2129.3	2157.6	2135.0	2163.2
10°	1535.5	1563.7	1617.5	1648.6	1705.1	1674.0	1583.5	1549.6	1532.6	1529.8	1558.1
12.5°	1227.2	1159.4	1153.7	1165.0	1193.3	1156.6	1111.3	1071.7	1091.5	1131.1	1162.2
15°	950.1	893.6	820.0	808.7	814.4	797.4	749.4	698.5	712.6	752.2	774.8
17.5°	729.6	664.5	613.6	579.7	568.4	509.0	438.3	395.9	384.6	381.7	401.5
20°	492.0	480.7	472.2	429.8	429.8	345.0	285.6	254.5	254.5	260.2	263.0
22.5°	367.6	353.5	356.3	347.8	325.2	257.3	226.2	217.7	217.7	223.4	223.4
25°	319.5	299.7	294.1	291.3	268.6	220.6	197.9	189.5	189.5	195.1	195.1
27.5°	271.5	265.8	257.3	246.0	226.2	189.5	175.3	166.8	169.7	172.5	169.7
30°	248.8	234.7	223.4	223.4	200.8	169.7	158.4	152.7	147.0	152.7	155.5
32.5°	220.6	212.1	206.4	197.9	172.5	149.9	138.6	132.9	130.1	130.1	132.9
35°	189.5	189.5	183.8	172.5	149.9	135.7	121.6	115.9	113.1	115.9	115.9
37.5°	169.7	161.2	164.0	152.7	132.9	118.8	104.6	99.0	99.0	96.1	99.0
40°	158.4	144.2	135.7	130.1	118.8	101.8	90.5	84.8	82.0	82.0	82.0
42.5°	141.4	130.1	113.1	110.3	107.5	87.7	73.5	70.7	67.9	65.0	65.0
45°	132.9	115.9	101.8	87.7	87.7	73.5	62.2	56.6	53.7	50.9	53.7
47.5°	121.6	104.6	87.7	73.5	70.7	59.4	48.1	42.4	39.6	39.6	39.6
50°	115.9	93.3	76.3	62.2	53.7	48.1	36.8	31.1	28.3	28.3	28.3
52.5°	107.5	87.7	67.9	53.7	42.4	36.8	28.3	22.6	19.8	19.8	19.8
55°	96.1	79.2	59.4	45.2	36.8	28.3	19.8	14.1	11.3	11.3	11.3
57.5°	90.5	70.7	50.9	39.6	28.3	19.8	11.3	8.5	8.5	5.7	8.5
60°	82.0	62.2	42.4	31.1	22.6	14.1	8.5	2.8	2.8	2.8	2.8
62.5°	70.7	53.7	36.8	25.4	17.0	8.5	2.8	0.0	0.0	0.0	0.0
65°	59.4	42.4	28.3	19.8	11.3	2.8	0.0	0.0	0.0	0.0	0.0
67.5°	50.9	36.8	22.6	14.1	8.5	0.0	0.0	0.0	0.0	0.0	0.0
70°	45.2	31.1	17.0	11.3	2.8	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	36.8	25.4	14.1	5.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	31.1	19.8	8.5	2.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	25.4	14.1	5.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	19.8	11.3	2.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	17.0	8.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	11.3	2.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	8.5	2.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599546
 CATALOG NUMBER: IFLD-S-SA2C-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	358°	360°
0°	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5	3981.5
2.5°	3591.3	3574.3	3659.1	3797.7	3868.4	4006.9	4040.9	4128.5	4105.9	4137.0
5°	2972.0	3005.9	3130.3	3333.9	3407.4	3608.2	3797.7	3987.1	4108.7	4168.1
7.5°	2205.7	2318.8	2471.5	2658.1	2847.6	3110.5	3432.9	3653.5	3772.2	3899.5
10°	1642.9	1764.5	1939.8	2123.6	2431.9	2726.0	3048.3	3322.6	3424.4	3543.2
12.5°	1292.3	1481.7	1685.3	1883.3	2067.1	2347.0	2745.8	3144.5	3254.7	3345.2
15°	899.2	1131.1	1422.4	1679.7	1937.0	2180.2	2593.1	3076.6	3226.5	3379.2
17.5°	497.7	681.5	1015.2	1377.1	1756.0	2129.3	2644.0	3201.0	3427.2	3534.7
20°	288.4	362.0	599.5	1029.3	1529.8	2019.0	2669.4	3435.7	3735.5	3789.2
22.5°	237.5	263.0	339.3	644.7	1252.7	1948.3	2799.5	3763.7	4069.1	4196.4
25°	203.6	223.4	263.0	387.4	947.3	1798.5	2881.5	4173.8	4456.5	4595.1
27.5°	181.0	200.8	231.9	285.6	644.7	1592.0	3017.2	4544.2	4827.0	5016.4
30°	158.4	175.3	206.4	243.2	446.8	1360.2	3133.2	4815.7	5214.4	5273.8
32.5°	141.4	155.5	178.1	209.3	330.8	1032.1	3226.5	5095.6	5432.1	5562.2
35°	121.6	138.6	152.7	178.1	251.7	777.6	3169.9	5313.4	5751.7	5907.2
37.5°	107.5	118.8	132.9	149.9	212.1	608.0	3054.0	5573.5	6026.0	6170.2
40°	90.5	99.0	115.9	132.9	192.3	469.4	2921.1	5887.4	6410.5	6665.0
42.5°	76.3	84.8	96.1	124.4	158.4	347.8	2652.4	6130.6	6721.6	6936.5
45°	59.4	70.7	87.7	124.4	127.2	257.3	2375.3	6311.6	6896.9	7004.4
47.5°	45.2	56.6	84.8	107.5	101.8	178.1	2047.3	6518.0	7077.9	7176.8
50°	33.9	45.2	96.1	93.3	84.8	135.7	1840.9	6662.2	7089.2	7142.9
52.5°	22.6	33.9	79.2	70.7	70.7	118.8	1784.3	6656.5	7117.5	7001.5
55°	17.0	25.4	45.2	50.9	62.2	104.6	1733.4	6868.6	7125.9	7208.0
57.5°	11.3	19.8	31.1	39.6	53.7	90.5	1628.8	7123.1	7388.9	7431.3
60°	5.7	14.1	22.6	31.1	45.2	79.2	1481.7	7309.8	7708.5	7753.7
62.5°	2.8	8.5	17.0	25.4	36.8	62.2	1329.0	7012.8	7569.9	7649.1
65°	0.0	5.7	11.3	17.0	22.6	45.2	1080.2	6331.3	7021.3	7312.6
67.5°	0.0	0.0	5.7	11.3	14.1	33.9	814.4	5760.1	6515.2	6911.0
70°	0.0	0.0	2.8	2.8	8.5	25.4	520.3	4770.4	5816.7	6034.4
72.5°	0.0	0.0	0.0	0.0	2.8	17.0	302.6	3543.2	4558.3	4962.7
75°	0.0	0.0	0.0	0.0	0.0	14.1	152.7	2279.2	3172.7	3715.7
77.5°	0.0	0.0	0.0	0.0	0.0	11.3	82.0	1470.4	2338.6	2793.8
80°	0.0	0.0	0.0	0.0	0.0	2.8	48.1	854.0	1495.9	1812.6
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	19.8	418.5	893.6	1046.3
85°	0.0	0.0	0.0	0.0	0.0	0.0	5.7	223.4	446.8	588.2
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	8.5	31.1	59.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)