

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599547

Luminaire Tested: **IFLD-S-SA2D-760-U-SLL-HSS**

Issue Date: 05/04/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P599547
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/04/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-S-SA2D-760-U-SLL-HSS
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens with House Side Shield
 Light Source: (32) 5700K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 11651.7 lumens
 Efficiency: N/A
 Efficacy: 94.0 lumens/watt
 Spacing Criteria (0/90/45): 0.53 / 0.46 / 0.63
 Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
 CIE Type: Direct

Input Watts (W): 123.9
 Input Voltage (V): 120
 Input Current (A_{in}): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599547
CATALOG NUMBER: IFLD-S-SA2D-760-U-SLL-HSS

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ···· 90°-270° - · - · 135°-315°

TEST NUMBER: P599547

CATALOG NUMBER: IFLD-S-SA2D-760-U-SLL-HSS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	106	100	95	90	103	98	93	89	94	90	86	90	86	83	86	83	81	79	79	79	79
2	94	84	76	69	91	82	75	68	78	72	66	75	70	65	72	67	63	61	61	61	61
3	84	72	62	54	81	70	61	53	67	59	52	64	57	51	61	55	50	48	48	48	48
4	76	62	51	44	73	60	51	43	58	49	43	55	48	42	53	46	41	39	39	39	39
5	69	54	44	36	67	53	43	36	51	42	35	48	41	35	46	40	34	32	32	32	32
6	63	48	38	30	61	47	37	30	45	36	30	43	35	30	41	35	29	27	27	27	27
7	58	43	33	26	56	42	33	26	40	32	26	39	31	26	37	31	25	23	23	23	23
8	54	39	29	23	52	38	29	23	37	28	23	35	28	22	34	27	22	20	20	20	20
9	50	35	26	20	49	35	26	20	34	26	20	32	25	20	31	25	20	18	18	18	18
10	47	33	24	18	46	32	24	18	31	23	18	30	23	18	29	23	18	16	16	16	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	94313	94313	94313	94313
5°	99110	94337	68921	69323
10°	85225	81959	37682	36797
15°	82868	78777	24480	18447
20°	95519	91525	13116	6559
25°	120102	112341	8499	5100
30°	144250	134428	6883	4176
35°	170821	160272	5642	3353
40°	206099	194031	4985	2535
45°	234642	224413	4643	1705
50°	263229	253017	4585	1042
55°	297679	296628	4553	465
60°	367338	376044	4155	133
65°	409872	452034	3805	0
70°	417936	510180	3525	0
75°	340070	376302	3360	0
80°	247266	157385	3471	0
85°	159861	66098	4619	0

TEST NUMBER: P599547
 CATALOG NUMBER: IFLD-S-SA2D-760-U-SLL-HSS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	332.8	2.9
10°-20°	652.6	5.6
20°-30°	903.2	7.8
30°-40°	1276.4	11.0
40°-50°	1737.8	14.9
50°-60°	2301.6	19.8
60°-70°	2672.4	22.9
70°-80°	1513.4	13.0
80°-90°	261.5	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1888.6	16.2
0°-40°	3165.0	27.2
0°-60°	7204.5	61.8
0°-90°	11651.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11651.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	4381	4381	4381	4381	4381	
5°	4586	4365	3189	3208	4586	412
15°	3718	3535	1098	828	3718	1091
25°	5056	4730	358	215	5056	2358
35°	6500	6098	215	128	6500	4098
45°	7707	7371	152	56	7707	5975
55°	7931	7903	121	12	7931	7186
65°	8046	8874	75	0	8046	7844
75°	4088	4524	40	0	4088	4462
85°	647	268	19	0	647	778
90°	0	0	0	0	0	

TEST NUMBER: P599547
 CATALOG NUMBER: IFLD-S-SA2D-760-U-SLL-HSS

CANDELA DISTRIBUTION (FULL):

	0°	2°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0
2.5°	4552.1	4648.6	4651.7	4695.2	4738.8	4738.8	4841.5	4816.6	4726.3	4710.8	4645.4
5°	4586.3	4620.6	4645.4	4866.4	5053.1	5034.4	5090.4	5053.1	4878.8	4654.8	4502.3
7.5°	4290.7	4328.1	4427.6	4804.1	5056.2	5140.2	5246.0	5012.6	4829.0	4424.5	4132.1
10°	3898.7	3970.3	4153.8	4583.2	4894.4	5162.0	5162.0	4975.3	4620.6	4225.4	3867.6
12.5°	3680.9	3824.0	3923.6	4359.2	4763.7	4947.3	4941.0	4841.5	4611.2	4113.4	3708.9
15°	3718.2	3758.7	3970.3	4309.4	4577.0	4567.7	4679.7	4648.6	4486.8	4213.0	3768.0
17.5°	3889.4	3951.6	4135.2	4309.4	4437.0	4399.6	4396.5	4545.9	4555.2	4381.0	3988.9
20°	4169.4	4353.0	4440.1	4493.0	4337.4	4178.7	4160.1	4368.5	4530.3	4595.7	4253.4
22.5°	4617.4	4738.8	4916.1	4645.4	4241.0	4041.8	4004.5	4234.7	4561.4	4850.8	4595.7
25°	5056.2	5149.5	5320.6	4972.2	4349.9	4013.8	3948.5	4147.6	4679.7	5205.5	5009.5
27.5°	5519.8	5600.7	5619.3	5211.7	4409.0	3957.8	3880.0	4147.6	4779.2	5392.2	5504.2
30°	5802.9	5899.4	5918.0	5423.3	4505.4	4004.5	3967.1	4166.3	4847.7	5550.9	5858.9
32.5°	6120.3	6145.2	6129.6	5460.7	4611.2	4141.4	3985.8	4290.7	4925.5	5740.7	6182.5
35°	6499.9	6543.5	6384.8	5631.8	4847.7	4228.5	4172.5	4443.2	5059.3	5827.8	6574.6
37.5°	6789.3	6926.2	6568.3	5697.1	4894.4	4412.1	4421.4	4760.6	5152.6	5933.6	7007.1
40°	7333.8	7103.5	6879.5	5921.2	5071.7	4723.2	4673.5	5087.3	5466.9	6002.1	7290.2
42.5°	7632.5	7511.1	7000.8	5942.9	5345.5	5152.6	5165.1	5457.5	5631.8	6195.0	7368.0
45°	7707.1	7579.6	7165.7	5958.5	5616.2	5659.8	5874.5	5930.5	5874.5	6322.5	7514.2
47.5°	7896.9	7620.0	7147.1	6167.0	6054.9	6223.0	6496.8	6618.1	6204.3	6275.9	7582.7
50°	7859.6	7700.9	7106.6	6254.1	6590.1	7035.1	7218.6	7168.9	6571.5	6179.4	7508.0
52.5°	7704.0	7532.9	7231.1	6490.6	7091.1	7629.4	7884.5	7760.0	6898.2	6397.2	7458.2
55°	7931.2	7800.5	7392.9	6811.0	7467.6	8152.1	8332.6	8239.2	7299.5	6599.5	7741.4
57.5°	8177.0	8149.0	7831.6	7187.5	7912.5	8690.4	8690.4	8575.3	7648.0	6891.9	8161.4
60°	8531.7	8593.9	8155.2	7436.4	8065.0	8659.3	9110.4	8976.6	7999.6	7405.3	8637.5
62.5°	8416.6	8615.7	8572.1	7971.6	8239.2	8811.7	9057.5	9157.1	8435.2	8030.7	9272.2
65°	8046.3	8257.9	8569.0	8323.2	8108.5	8441.5	8565.9	8867.7	8653.0	8618.8	9533.6
67.5°	7604.5	7834.7	8027.6	8559.7	7844.1	8065.0	7956.1	8052.5	8416.6	9262.9	9682.9
70°	6639.9	6860.8	7165.7	8033.9	7144.0	6944.8	6916.8	6870.2	7436.4	9032.6	9004.6
72.5°	5460.7	5563.3	6067.4	6531.0	5286.4	5249.1	5292.6	5239.7	5896.3	8177.0	7713.4
75°	4088.5	4191.2	4477.4	5015.7	3600.0	3385.3	3634.2	3880.0	4502.3	6347.4	5541.6
77.5°	3074.1	3204.8	3385.3	3752.5	2641.7	2305.6	2339.8	2573.2	3254.6	5084.2	3105.3
80°	1994.5	1978.9	2327.4	2582.5	1988.2	2050.5	1963.3	2134.5	2358.5	2719.4	1586.9
82.5°	1151.2	1166.8	1313.0	1481.1	1384.6	1583.7	1141.9	1907.3	1683.3	1107.7	591.2
85°	647.2	675.2	809.0	1026.8	868.1	581.8	476.1	945.9	1057.9	454.3	286.3
87.5°	65.3	56.0	108.9	388.9	236.5	96.5	143.1	227.1	255.1	171.1	84.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599547
 CATALOG NUMBER: IFLD-S-SA2D-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0
2.5°	4552.1	4552.1	4474.3	4343.6	4290.7	4197.4	4069.8	4110.3	4066.7	3908.0	3867.6
5°	4365.4	4216.1	4054.3	3855.1	3740.0	3503.5	3428.9	3295.1	3316.8	3183.0	3189.3
7.5°	3976.5	3858.2	3584.4	3323.1	3095.9	2890.6	2601.2	2492.3	2386.5	2333.6	2395.8
10°	3749.3	3528.4	3155.0	2812.8	2511.0	2327.4	2134.5	1985.1	1848.2	1745.5	1723.8
12.5°	3584.4	3388.4	2937.2	2520.3	2283.8	2134.5	1957.1	1751.8	1618.0	1440.6	1387.7
15°	3534.6	3295.1	2819.0	2405.2	2174.9	1929.1	1726.9	1524.6	1350.4	1163.7	1098.4
17.5°	3705.8	3428.9	2815.9	2311.8	1988.2	1723.8	1443.7	1216.6	1039.2	868.1	827.7
20°	3995.1	3572.0	2906.1	2255.8	1810.9	1456.2	1138.8	911.7	712.5	600.5	572.5
22.5°	4325.0	3814.7	2915.5	2106.5	1633.5	1188.6	830.8	600.5	488.5	435.6	420.1
25°	4729.5	4203.6	3027.5	1985.1	1425.1	902.3	591.2	460.5	395.2	364.0	357.8
27.5°	5062.4	4474.3	3148.8	1857.6	1219.7	669.0	463.6	376.5	342.3	311.1	308.0
30°	5407.8	4785.5	3183.0	1779.8	1042.3	550.7	398.3	332.9	295.6	280.0	276.9
32.5°	5709.6	5124.6	3292.0	1652.2	874.3	485.4	360.9	298.7	273.8	248.9	245.8
35°	6098.5	5320.6	3344.8	1583.7	812.1	438.7	329.8	273.8	236.5	220.9	214.7
37.5°	6515.4	5510.4	3379.1	1530.9	759.2	410.7	311.1	258.3	224.0	202.2	196.0
40°	6904.4	5778.0	3329.3	1465.5	718.8	376.5	298.7	239.6	208.5	186.7	177.4
42.5°	7203.1	6039.4	3313.7	1403.3	675.2	364.0	283.1	230.2	196.0	171.1	168.0
45°	7371.1	6216.7	3204.8	1353.5	641.0	370.3	276.9	217.8	186.7	164.9	152.5
47.5°	7330.7	6353.7	3232.8	1337.9	594.3	345.4	273.8	208.5	171.1	152.5	143.1
50°	7554.7	6630.6	3186.2	1288.2	560.1	311.1	298.7	208.5	168.0	146.2	136.9
52.5°	7592.0	6882.6	3285.7	1197.9	507.2	286.3	295.6	205.4	161.8	140.0	127.6
55°	7903.2	7175.1	3478.6	1148.1	463.6	248.9	270.7	199.1	146.2	127.6	121.3
57.5°	8326.3	7781.8	3603.1	1101.5	404.5	217.8	227.1	196.0	133.8	118.2	108.9
60°	8733.9	8024.5	3612.4	1017.5	348.5	196.0	177.4	196.0	124.5	105.8	96.5
62.5°	9038.9	8024.5	3550.2	945.9	304.9	174.2	155.6	186.7	112.0	93.3	87.1
65°	8874.0	7809.8	3388.4	886.8	276.9	152.5	133.8	143.1	99.6	80.9	74.7
67.5°	8578.4	7140.9	3030.6	815.2	273.8	133.8	115.1	105.8	87.1	71.6	65.3
70°	8105.4	6238.5	2523.4	734.3	267.6	121.3	102.7	90.2	77.8	62.2	56.0
72.5°	6531.0	5152.6	2072.2	687.6	261.4	105.8	87.1	77.8	65.3	52.9	46.7
75°	4524.1	3292.0	1596.2	588.1	255.1	96.5	80.9	68.5	56.0	43.6	40.4
77.5°	2713.2	2199.8	1029.9	441.8	168.0	77.8	68.5	52.9	46.7	37.3	34.2
80°	1269.5	1039.2	416.9	171.1	80.9	56.0	46.7	40.4	37.3	31.1	28.0
82.5°	497.8	438.7	202.2	99.6	65.3	43.6	37.3	34.2	31.1	24.9	21.8
85°	267.6	236.5	96.5	68.5	46.7	31.1	31.1	28.0	24.9	21.8	18.7
87.5°	59.1	43.6	40.4	40.4	34.2	24.9	24.9	21.8	18.7	15.6	12.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599547
 CATALOG NUMBER: IFLD-S-SA2D-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0
2.5°	3845.8	3892.5	3817.8	3864.5	3799.1	3848.9	3855.1	3808.5	3820.9	3883.1	3911.1
5°	3276.4	3245.3	3176.8	3155.0	3158.2	3117.7	3133.3	3155.0	3189.3	3207.9	3263.9
7.5°	2361.6	2433.2	2430.1	2483.0	2486.1	2479.9	2436.3	2342.9	2374.1	2349.2	2380.3
10°	1689.5	1720.7	1779.8	1814.0	1876.2	1842.0	1742.4	1705.1	1686.4	1683.3	1714.4
12.5°	1350.4	1275.7	1269.5	1281.9	1313.0	1272.6	1222.8	1179.3	1201.0	1244.6	1278.8
15°	1045.5	983.2	902.3	889.9	896.1	877.4	824.5	768.5	784.1	827.7	852.5
17.5°	802.8	731.2	675.2	637.9	625.4	560.1	482.3	435.6	423.2	420.1	441.8
20°	541.4	529.0	519.6	472.9	472.9	379.6	314.3	280.0	280.0	286.3	289.4
22.5°	404.5	388.9	392.0	382.7	357.8	283.1	248.9	239.6	239.6	245.8	245.8
25°	351.6	329.8	323.6	320.5	295.6	242.7	217.8	208.5	208.5	214.7	214.7
27.5°	298.7	292.5	283.1	270.7	248.9	208.5	192.9	183.6	186.7	189.8	186.7
30°	273.8	258.3	245.8	245.8	220.9	186.7	174.2	168.0	161.8	168.0	171.1
32.5°	242.7	233.4	227.1	217.8	189.8	164.9	152.5	146.2	143.1	143.1	146.2
35°	208.5	208.5	202.2	189.8	164.9	149.4	133.8	127.6	124.5	127.6	127.6
37.5°	186.7	177.4	180.5	168.0	146.2	130.7	115.1	108.9	108.9	105.8	108.9
40°	174.2	158.7	149.4	143.1	130.7	112.0	99.6	93.3	90.2	90.2	90.2
42.5°	155.6	143.1	124.5	121.3	118.2	96.5	80.9	77.8	74.7	71.6	71.6
45°	146.2	127.6	112.0	96.5	96.5	80.9	68.5	62.2	59.1	56.0	59.1
47.5°	133.8	115.1	96.5	80.9	77.8	65.3	52.9	46.7	43.6	43.6	43.6
50°	127.6	102.7	84.0	68.5	59.1	52.9	40.4	34.2	31.1	31.1	31.1
52.5°	118.2	96.5	74.7	59.1	46.7	40.4	31.1	24.9	21.8	21.8	21.8
55°	105.8	87.1	65.3	49.8	40.4	31.1	21.8	15.6	12.4	12.4	12.4
57.5°	99.6	77.8	56.0	43.6	31.1	21.8	12.4	9.3	9.3	6.2	9.3
60°	90.2	68.5	46.7	34.2	24.9	15.6	9.3	3.1	3.1	3.1	3.1
62.5°	77.8	59.1	40.4	28.0	18.7	9.3	3.1	0.0	0.0	0.0	0.0
65°	65.3	46.7	31.1	21.8	12.4	3.1	0.0	0.0	0.0	0.0	0.0
67.5°	56.0	40.4	24.9	15.6	9.3	0.0	0.0	0.0	0.0	0.0	0.0
70°	49.8	34.2	18.7	12.4	3.1	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	40.4	28.0	15.6	6.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	34.2	21.8	9.3	3.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	28.0	15.6	6.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	21.8	12.4	3.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	18.7	9.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	12.4	3.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	9.3	3.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599547
 CATALOG NUMBER: IFLD-S-SA2D-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	358°	360°
0°	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0	4381.0
2.5°	3951.6	3932.9	4026.3	4178.7	4256.5	4409.0	4446.3	4542.8	4517.9	4552.1
5°	3270.2	3307.5	3444.4	3668.4	3749.3	3970.3	4178.7	4387.2	4521.0	4586.3
7.5°	2427.0	2551.4	2719.4	2924.8	3133.3	3422.6	3777.3	4020.0	4150.7	4290.7
10°	1807.8	1941.6	2134.5	2336.7	2675.9	2999.5	3354.2	3656.0	3768.0	3898.7
12.5°	1421.9	1630.4	1854.4	2072.2	2274.5	2582.5	3021.3	3460.0	3581.3	3680.9
15°	989.5	1244.6	1565.1	1848.2	2131.4	2399.0	2853.2	3385.3	3550.2	3718.2
17.5°	547.6	749.9	1117.0	1515.3	1932.2	2342.9	2909.2	3522.2	3771.1	3889.4
20°	317.4	398.3	659.6	1132.6	1683.3	2221.6	2937.2	3780.5	4110.3	4169.4
22.5°	261.4	289.4	373.4	709.4	1378.4	2143.8	3080.4	4141.4	4477.4	4617.4
25°	224.0	245.8	289.4	426.3	1042.3	1978.9	3170.6	4592.6	4903.7	5056.2
27.5°	199.1	220.9	255.1	314.3	709.4	1751.8	3320.0	5000.2	5311.3	5519.8
30°	174.2	192.9	227.1	267.6	491.6	1496.6	3447.5	5298.9	5737.6	5802.9
32.5°	155.6	171.1	196.0	230.2	364.0	1135.7	3550.2	5606.9	5977.2	6120.3
35°	133.8	152.5	168.0	196.0	276.9	855.7	3488.0	5846.5	6328.8	6499.9
37.5°	118.2	130.7	146.2	164.9	233.4	669.0	3360.4	6132.7	6630.6	6789.3
40°	99.6	108.9	127.6	146.2	211.6	516.5	3214.2	6478.1	7053.7	7333.8
42.5°	84.0	93.3	105.8	136.9	174.2	382.7	2918.6	6745.7	7396.0	7632.5
45°	65.3	77.8	96.5	136.9	140.0	283.1	2613.6	6944.8	7588.9	7707.1
47.5°	49.8	62.2	93.3	118.2	112.0	196.0	2252.7	7172.0	7788.0	7896.9
50°	37.3	49.8	105.8	102.7	93.3	149.4	2025.6	7330.7	7800.5	7859.6
52.5°	24.9	37.3	87.1	77.8	77.8	130.7	1963.3	7324.4	7831.6	7704.0
55°	18.7	28.0	49.8	56.0	68.5	115.1	1907.3	7557.8	7840.9	7931.2
57.5°	12.4	21.8	34.2	43.6	59.1	99.6	1792.2	7837.8	8130.3	8177.0
60°	6.2	15.6	24.9	34.2	49.8	87.1	1630.4	8043.2	8481.9	8531.7
62.5°	3.1	9.3	18.7	28.0	40.4	68.5	1462.4	7716.5	8329.4	8416.6
65°	0.0	6.2	12.4	18.7	24.9	49.8	1188.6	6966.6	7725.8	8046.3
67.5°	0.0	0.0	6.2	12.4	15.6	37.3	896.1	6338.1	7168.9	7604.5
70°	0.0	0.0	3.1	3.1	9.3	28.0	572.5	5249.1	6400.3	6639.9
72.5°	0.0	0.0	0.0	0.0	3.1	18.7	332.9	3898.7	5015.7	5460.7
75°	0.0	0.0	0.0	0.0	0.0	15.6	168.0	2507.9	3491.1	4088.5
77.5°	0.0	0.0	0.0	0.0	0.0	12.4	90.2	1618.0	2573.2	3074.1
80°	0.0	0.0	0.0	0.0	0.0	3.1	52.9	939.7	1646.0	1994.5
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	21.8	460.5	983.2	1151.2
85°	0.0	0.0	0.0	0.0	0.0	0.0	6.2	245.8	491.6	647.2
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	9.3	34.2	65.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)