

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599556

Luminaire Tested: **IFLD-S-SA6C-760-U-SLL-HSS**

Issue Date: 05/04/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P599556
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/04/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-S-SA6C-760-U-SLL-HSS
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens with House Side Shield
 Light Source: (96) 5700K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 30956.9 lumens
 Efficiency: N/A
 Efficacy: 96.3 lumens/watt
 Spacing Criteria (0/90/45): 0.53 / 0.46 / 0.63
 Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
 CIE Type: Direct

Input Watts (W): 321.5
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599556
CATALOG NUMBER: IFLD-S-SA6C-760-U-SLL-HSS

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ··· 90°-270° - · 135°-315°

TEST NUMBER: P599556
 CATALOG NUMBER: IFLD-S-SA6C-760-U-SLL-HSS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	106	100	95	90	103	98	93	89	94	90	86	90	86	83	86	83	81	79	79	79	79
2	94	84	76	69	91	82	75	68	78	72	66	75	70	65	72	67	63	61	61	61	61
3	84	72	62	54	81	70	61	53	67	59	52	64	57	51	61	55	50	48	48	48	48
4	76	62	51	44	73	60	51	43	58	49	43	55	48	42	53	46	41	39	39	39	39
5	69	54	44	36	67	53	43	36	51	42	35	48	41	35	46	40	34	32	32	32	32
6	63	48	38	30	61	47	37	30	45	36	30	43	35	30	41	35	29	27	27	27	27
7	58	43	33	26	56	42	33	26	40	32	26	39	31	26	37	31	25	23	23	23	23
8	54	39	29	23	52	38	29	23	37	28	23	35	28	22	34	27	22	20	20	20	20
9	50	35	26	20	49	35	26	20	34	26	20	32	25	20	31	25	20	18	18	18	18
10	47	33	24	18	46	32	24	18	31	23	18	30	23	18	29	23	18	16	16	16	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	83525	83525	83525	83525
5°	87774	83546	61037	61394
10°	75477	72585	33371	32588
15°	73390	69767	21680	16337
20°	84592	81057	11616	5808
25°	106363	99490	7527	4516
30°	127750	119051	6096	3699
35°	151282	141940	4997	2969
40°	182523	171837	4414	2245
45°	207804	198744	4111	1510
50°	233120	224075	4060	923
55°	263628	262697	4034	414
60°	325320	333031	3678	119
65°	362989	400326	3369	0
70°	370131	451825	3122	0
75°	301171	333258	2981	0
80°	218979	139380	3075	0
85°	141575	58532	4084	0

TEST NUMBER: P599556
 CATALOG NUMBER: IFLD-S-SA6C-760-U-SLL-HSS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	884.2	2.9
10°-20°	1734.0	5.6
20°-30°	2399.5	7.8
30°-40°	3391.2	11.0
40°-50°	4617.1	14.9
50°-60°	6115.1	19.8
60°-70°	7100.1	22.9
70°-80°	4020.8	13.0
80°-90°	694.7	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5017.8	16.2
0°-40°	8408.9	27.2
0°-60°	19141.2	61.8
0°-90°	30956.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	30956.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	11640	11640	11640	11640	11640	
5°	12185	11598	8473	8523	12185	1094
15°	9879	9391	2918	2199	9879	2898
25°	13434	12565	951	570	13434	6265
35°	17269	16203	570	339	17269	10887
45°	20477	19584	405	149	20477	15875
55°	21072	20998	322	33	21072	19091
65°	21378	23577	198	0	21378	20839
75°	10862	12020	108	0	10862	11855
85°	1720	711	50	0	1720	2066
90°	0	0	0	0	0	

TEST NUMBER: P599556
 CATALOG NUMBER: IFLD-S-SA6C-760-U-SLL-HSS

CANDELA DISTRIBUTION (FULL):

	0°	2°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6
2.5°	12094.2	12350.5	12358.8	12474.5	12590.2	12590.2	12863.0	12796.9	12557.2	12515.8	12342.2
5°	12185.2	12276.1	12342.2	12929.2	13425.2	13375.6	13524.4	13425.2	12962.2	12367.0	11962.0
7.5°	11399.8	11499.0	11763.6	12763.8	13433.5	13656.7	13937.7	13317.7	12830.0	11755.3	10978.2
10°	10358.2	10548.4	11036.1	12176.9	13003.6	13714.5	13714.5	13218.5	12276.1	11226.2	10275.6
12.5°	9779.6	10159.8	10424.4	11581.7	12656.4	13144.1	13127.6	12863.0	12251.3	10928.6	9854.0
15°	9878.8	9986.2	10548.4	11449.4	12160.4	12135.6	12433.2	12350.5	11920.6	11193.2	10011.0
17.5°	10333.4	10498.8	10986.5	11449.4	11788.4	11689.2	11680.9	12077.7	12102.5	11639.6	10598.0
20°	11077.4	11565.2	11796.6	11937.2	11523.8	11102.2	11052.6	11606.5	12036.4	12210.0	11300.6
22.5°	12267.8	12590.2	13061.4	12342.2	11267.6	10738.5	10639.3	11251.0	12119.0	12887.8	12210.0
25°	13433.5	13681.5	14136.1	13210.2	11556.9	10664.1	10490.5	11019.6	12433.2	13830.3	13309.4
27.5°	14665.2	14880.1	14929.7	13846.8	11714.0	10515.3	10308.6	11019.6	12697.7	14326.3	14623.9
30°	15417.5	15673.7	15723.3	14408.9	11970.2	10639.3	10540.1	11069.2	12879.6	14747.9	15566.3
32.5°	16260.7	16326.8	16285.5	14508.1	12251.3	11003.0	10589.7	11399.8	13086.2	15252.1	16426.0
35°	17269.2	17385.0	16963.3	14962.8	12879.6	11234.5	11085.7	11804.9	13441.7	15483.6	17467.6
37.5°	18038.0	18401.8	17451.1	15136.4	13003.6	11722.2	11747.0	12648.1	13689.7	15764.7	18616.7
40°	19484.7	18873.0	18277.8	15731.6	13474.8	12548.9	12416.6	13516.1	14524.7	15946.5	19369.0
42.5°	20278.3	19955.9	18600.2	15789.5	14202.3	13689.7	13722.8	14499.9	14962.8	16459.1	19575.6
45°	20476.7	20137.8	19038.3	15830.8	14921.5	15037.2	15607.6	15756.4	15607.6	16798.0	19964.2
47.5°	20981.0	20245.2	18988.7	16384.7	16087.1	16533.5	17261.0	17583.4	16483.9	16674.0	20146.0
50°	20881.8	20460.2	18881.2	16616.1	17509.0	18691.1	19178.8	19046.6	17459.4	16417.7	19947.6
52.5°	20468.4	20013.8	19211.9	17244.4	18839.9	20270.0	20947.9	20617.2	18327.4	16996.4	19815.4
55°	21071.9	20724.7	19641.8	18095.9	19840.2	21658.9	22138.3	21890.3	19393.8	17533.8	20567.6
57.5°	21725.0	21650.6	20807.4	19096.2	21022.3	23089.0	23089.0	22783.1	20319.6	18310.8	21683.7
60°	22667.4	22832.7	21667.1	19757.5	21427.4	23006.3	24205.0	23849.5	21253.8	19674.8	22948.5
62.5°	22361.5	22890.6	22774.9	21179.4	21890.3	23411.4	24064.5	24329.0	22411.1	21336.5	24634.9
65°	21377.8	21939.9	22766.6	22113.5	21543.1	22427.7	22758.3	23560.2	22989.8	22898.9	25329.3
67.5°	20203.9	20815.6	21328.2	22741.8	20840.4	21427.4	21138.1	21394.3	22361.5	24610.1	25726.1
70°	17641.2	18228.2	19038.3	21344.7	18980.4	18451.4	18377.0	18253.0	19757.5	23998.3	23923.9
72.5°	14508.1	14780.9	16120.1	17351.9	14045.2	13946.0	14061.7	13921.2	15665.5	21725.0	20493.2
75°	10862.5	11135.3	11895.8	13326.0	9564.6	8994.2	9655.6	10308.6	11962.0	16864.1	14723.1
77.5°	8167.5	8514.7	8994.2	9969.7	7018.5	6125.7	6216.6	6836.6	8647.0	13507.9	8250.2
80°	5299.0	5257.6	6183.5	6861.4	5282.4	5447.8	5216.3	5671.0	6266.2	7225.1	4216.0
82.5°	3058.7	3100.0	3488.6	3935.0	3678.7	4207.8	3033.9	5067.5	4472.3	2943.0	1570.7
85°	1719.5	1793.9	2149.4	2728.0	2306.4	1545.9	1264.8	2513.1	2810.7	1206.9	760.5
87.5°	173.6	148.8	289.3	1033.3	628.3	256.3	380.3	603.5	677.9	454.7	223.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599556
 CATALOG NUMBER: IFLD-S-SA6C-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6
2.5°	12094.2	12094.2	11887.6	11540.4	11399.8	11151.8	10812.9	10920.4	10804.6	10383.0	10275.6
5°	11598.2	11201.4	10771.6	10242.5	9936.6	9308.3	9109.9	8754.5	8812.3	8456.9	8473.4
7.5°	10564.9	10250.8	9523.3	8828.9	8225.4	7679.8	6911.0	6621.7	6340.6	6200.1	6365.4
10°	9961.4	9374.5	8382.5	7473.1	6671.3	6183.5	5671.0	5274.2	4910.4	4637.6	4579.8
12.5°	9523.3	9002.5	7803.8	6696.1	6067.8	5671.0	5199.8	4654.2	4298.7	3827.5	3687.0
15°	9391.0	8754.5	7489.7	6390.2	5778.5	5125.4	4588.0	4050.7	3587.8	3091.8	2918.2
17.5°	9845.7	9109.9	7481.4	6142.2	5282.4	4579.8	3835.8	3232.3	2761.1	2306.4	2199.0
20°	10614.5	9490.2	7721.1	5993.4	4811.2	3868.8	3025.6	2422.2	1893.1	1595.5	1521.1
22.5°	11490.8	10135.0	7745.9	5596.6	4340.0	3157.9	2207.2	1595.5	1297.9	1157.3	1116.0
25°	12565.4	11168.4	8043.5	5274.2	3786.2	2397.4	1570.7	1223.5	1049.9	967.2	950.7
27.5°	13450.0	11887.6	8365.9	4935.2	3240.6	1777.3	1231.7	1000.3	909.3	826.7	818.4
30°	14367.6	12714.2	8456.9	4728.6	2769.4	1463.2	1058.1	884.5	785.3	744.0	735.7
32.5°	15169.5	13615.3	8746.2	4389.6	2323.0	1289.6	958.9	793.6	727.5	661.3	653.1
35°	16202.8	14136.1	8886.7	4207.8	2157.6	1165.6	876.3	727.5	628.3	586.9	570.4
37.5°	17310.6	14640.4	8977.7	4067.2	2017.1	1091.2	826.7	686.1	595.2	537.3	520.8
40°	18343.9	15351.3	8845.4	3893.6	1909.6	1000.3	793.6	636.5	553.9	496.0	471.2
42.5°	19137.5	16045.7	8804.1	3728.3	1793.9	967.2	752.3	611.7	520.8	454.7	446.4
45°	19583.9	16516.9	8514.7	3596.0	1702.9	983.7	735.7	578.7	496.0	438.1	405.1
47.5°	19476.4	16880.7	8589.1	3554.7	1578.9	917.6	727.5	553.9	454.7	405.1	380.3
50°	20071.6	17616.4	8465.1	3422.4	1488.0	826.7	793.6	553.9	446.4	388.5	363.7
52.5°	20170.8	18286.0	8729.7	3182.7	1347.5	760.5	785.3	545.6	429.9	372.0	338.9
55°	20997.5	19063.1	9242.2	3050.4	1231.7	661.3	719.2	529.1	388.5	338.9	322.4
57.5°	22121.8	20675.1	9572.9	2926.4	1074.7	578.7	603.5	520.8	355.5	314.1	289.3
60°	23204.7	21319.9	9597.7	2703.2	925.9	520.8	471.2	520.8	330.7	281.1	256.3
62.5°	24014.9	21319.9	9432.3	2513.1	810.1	462.9	413.3	496.0	297.6	248.0	231.5
65°	23576.7	20749.5	9002.5	2356.0	735.7	405.1	355.5	380.3	264.5	214.9	198.4
67.5°	22791.4	18972.2	8051.8	2165.9	727.5	355.5	305.9	281.1	231.5	190.1	173.6
70°	21534.9	16574.8	6704.3	1951.0	710.9	322.4	272.8	239.7	206.7	165.3	148.8
72.5°	17351.9	13689.7	5505.6	1826.9	694.4	281.1	231.5	206.7	173.6	140.5	124.0
75°	12019.8	8746.2	4240.8	1562.4	677.9	256.3	214.9	181.9	148.8	115.7	107.5
77.5°	7208.6	5844.6	2736.3	1173.9	446.4	206.7	181.9	140.5	124.0	99.2	90.9
80°	3372.8	2761.1	1107.7	454.7	214.9	148.8	124.0	107.5	99.2	82.7	74.4
82.5°	1322.7	1165.6	537.3	264.5	173.6	115.7	99.2	90.9	82.7	66.1	57.9
85°	710.9	628.3	256.3	181.9	124.0	82.7	82.7	74.4	66.1	57.9	49.6
87.5°	157.1	115.7	107.5	107.5	90.9	66.1	66.1	57.9	49.6	41.3	33.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599556
 CATALOG NUMBER: IFLD-S-SA6C-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6
2.5°	10217.7	10341.7	10143.3	10267.3	10093.7	10226.0	10242.5	10118.5	10151.6	10316.9	10391.3
5°	8704.9	8622.2	8440.3	8382.5	8390.7	8283.3	8324.6	8382.5	8473.4	8523.0	8671.8
7.5°	6274.5	6464.6	6456.3	6596.9	6605.1	6588.6	6472.9	6224.9	6307.5	6241.4	6324.1
10°	4488.8	4571.5	4728.6	4819.5	4984.8	4893.9	4629.4	4530.2	4480.6	4472.3	4555.0
12.5°	3587.8	3389.4	3372.8	3405.9	3488.6	3381.1	3248.8	3133.1	3191.0	3306.7	3397.6
15°	2777.6	2612.3	2397.4	2364.3	2380.8	2331.2	2190.7	2041.9	2083.2	2199.0	2265.1
17.5°	2132.8	1942.7	1793.9	1694.7	1661.6	1488.0	1281.3	1157.3	1124.3	1116.0	1173.9
20°	1438.4	1405.3	1380.5	1256.5	1256.5	1008.5	834.9	744.0	744.0	760.5	768.8
22.5°	1074.7	1033.3	1041.6	1016.8	950.7	752.3	661.3	636.5	636.5	653.1	653.1
25°	934.1	876.3	859.7	851.5	785.3	644.8	578.7	553.9	553.9	570.4	570.4
27.5°	793.6	777.1	752.3	719.2	661.3	553.9	512.5	487.7	496.0	504.3	496.0
30°	727.5	686.1	653.1	653.1	586.9	496.0	462.9	446.4	429.9	446.4	454.7
32.5°	644.8	620.0	603.5	578.7	504.3	438.1	405.1	388.5	380.3	380.3	388.5
35°	553.9	553.9	537.3	504.3	438.1	396.8	355.5	338.9	330.7	338.9	338.9
37.5°	496.0	471.2	479.5	446.4	388.5	347.2	305.9	289.3	289.3	281.1	289.3
40°	462.9	421.6	396.8	380.3	347.2	297.6	264.5	248.0	239.7	239.7	239.7
42.5°	413.3	380.3	330.7	322.4	314.1	256.3	214.9	206.7	198.4	190.1	190.1
45°	388.5	338.9	297.6	256.3	256.3	214.9	181.9	165.3	157.1	148.8	157.1
47.5°	355.5	305.9	256.3	214.9	206.7	173.6	140.5	124.0	115.7	115.7	115.7
50°	338.9	272.8	223.2	181.9	157.1	140.5	107.5	90.9	82.7	82.7	82.7
52.5°	314.1	256.3	198.4	157.1	124.0	107.5	82.7	66.1	57.9	57.9	57.9
55°	281.1	231.5	173.6	132.3	107.5	82.7	57.9	41.3	33.1	33.1	33.1
57.5°	264.5	206.7	148.8	115.7	82.7	57.9	33.1	24.8	24.8	16.5	24.8
60°	239.7	181.9	124.0	90.9	66.1	41.3	24.8	8.3	8.3	8.3	8.3
62.5°	206.7	157.1	107.5	74.4	49.6	24.8	8.3	0.0	0.0	0.0	0.0
65°	173.6	124.0	82.7	57.9	33.1	8.3	0.0	0.0	0.0	0.0	0.0
67.5°	148.8	107.5	66.1	41.3	24.8	0.0	0.0	0.0	0.0	0.0	0.0
70°	132.3	90.9	49.6	33.1	8.3	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	107.5	74.4	41.3	16.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	90.9	57.9	24.8	8.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	74.4	41.3	16.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	57.9	33.1	8.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	49.6	24.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	33.1	8.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	24.8	8.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599556
 CATALOG NUMBER: IFLD-S-SA6C-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	358°	360°
0°	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6	11639.6
2.5°	10498.8	10449.2	10697.2	11102.2	11308.9	11714.0	11813.2	12069.4	12003.3	12094.2
5°	8688.3	8787.5	9151.3	9746.5	9961.4	10548.4	11102.2	11656.1	12011.6	12185.2
7.5°	6448.1	6778.7	7225.1	7770.7	8324.6	9093.4	10035.8	10680.6	11027.8	11399.8
10°	4803.0	5158.4	5671.0	6208.3	7109.4	7969.1	8911.5	9713.4	10011.0	10358.2
12.5°	3777.9	4331.8	4927.0	5505.6	6043.0	6861.4	8027.0	9192.6	9515.0	9779.6
15°	2628.8	3306.7	4158.2	4910.4	5662.7	6373.7	7580.6	8994.2	9432.3	9878.8
17.5°	1454.9	1992.3	2967.8	4025.9	5133.6	6224.9	7729.4	9357.9	10019.3	10333.4
20°	843.2	1058.1	1752.5	3009.1	4472.3	5902.5	7803.8	10044.1	10920.4	11077.4
22.5°	694.4	768.8	992.0	1884.8	3662.2	5695.8	8184.1	11003.0	11895.8	12267.8
25°	595.2	653.1	768.8	1132.5	2769.4	5257.6	8423.8	12201.7	13028.4	13433.5
27.5°	529.1	586.9	677.9	834.9	1884.8	4654.2	8820.6	13284.6	14111.3	14665.2
30°	462.9	512.5	603.5	710.9	1306.1	3976.3	9159.5	14078.3	15243.9	15417.5
32.5°	413.3	454.7	520.8	611.7	967.2	3017.4	9432.3	14896.7	15880.4	16260.7
35°	355.5	405.1	446.4	520.8	735.7	2273.4	9267.0	15533.2	16814.5	17269.2
37.5°	314.1	347.2	388.5	438.1	620.0	1777.3	8928.1	16293.7	17616.4	18038.0
40°	264.5	289.3	338.9	388.5	562.1	1372.3	8539.5	17211.3	18740.7	19484.7
42.5°	223.2	248.0	281.1	363.7	462.9	1016.8	7754.2	17922.3	19650.0	20278.3
45°	173.6	206.7	256.3	363.7	372.0	752.3	6944.1	18451.4	20162.6	20476.7
47.5°	132.3	165.3	248.0	314.1	297.6	520.8	5985.1	19054.8	20691.6	20981.0
50°	99.2	132.3	281.1	272.8	248.0	396.8	5381.6	19476.4	20724.7	20881.8
52.5°	66.1	99.2	231.5	206.7	206.7	347.2	5216.3	19459.9	20807.4	20468.4
55°	49.6	74.4	132.3	148.8	181.9	305.9	5067.5	20079.9	20832.2	21071.9
57.5°	33.1	57.9	90.9	115.7	157.1	264.5	4761.6	20823.9	21601.0	21725.0
60°	16.5	41.3	66.1	90.9	132.3	231.5	4331.8	21369.5	22535.1	22667.4
62.5°	8.3	24.8	49.6	74.4	107.5	181.9	3885.4	20501.5	22130.1	22361.5
65°	0.0	16.5	33.1	49.6	66.1	132.3	3157.9	18509.2	20526.3	21377.8
67.5°	0.0	0.0	16.5	33.1	41.3	99.2	2380.8	16839.3	19046.6	20203.9
70°	0.0	0.0	8.3	8.3	24.8	74.4	1521.1	13946.0	17004.7	17641.2
72.5°	0.0	0.0	0.0	0.0	8.3	49.6	884.5	10358.2	13326.0	14508.1
75°	0.0	0.0	0.0	0.0	0.0	41.3	446.4	6663.0	9275.3	10862.5
77.5°	0.0	0.0	0.0	0.0	0.0	33.1	239.7	4298.7	6836.6	8167.5
80°	0.0	0.0	0.0	0.0	0.0	8.3	140.5	2496.6	4373.1	5299.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	57.9	1223.5	2612.3	3058.7
85°	0.0	0.0	0.0	0.0	0.0	0.0	16.5	653.1	1306.1	1719.5
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	24.8	90.9	173.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)