

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599557

Luminaire Tested: **IFLD-S-SA6D-760-U-SLL-HSS**

Issue Date: 05/04/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P599557
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/04/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-S-SA6D-760-U-SLL-HSS
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens with House Side Shield
 Light Source: (96) 5700K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 34063.6 lumens
 Efficiency: N/A
 Efficacy: 92.5 lumens/watt
 Spacing Criteria (0/90/45): 0.53 / 0.46 / 0.63
 Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
 CIE Type: Direct

Input Watts (W): 368.2
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599557
CATALOG NUMBER: IFLD-S-SA6D-760-U-SLL-HSS

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - 90°-270° · · · 135°-315°

TEST NUMBER: P599557

CATALOG NUMBER: IFLD-S-SA6D-760-U-SLL-HSS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	106	100	95	90	103	98	93	89	94	90	86	90	86	83	86	83	81	79
2	94	84	76	69	91	82	75	68	78	72	66	75	70	65	72	67	63	61
3	84	72	62	54	81	70	61	53	67	59	52	64	57	51	61	55	50	48
4	76	62	51	44	73	60	51	43	58	49	43	55	48	42	53	46	41	39
5	69	54	44	36	67	53	43	36	51	42	35	48	41	35	46	40	34	32
6	63	48	38	30	61	47	37	30	45	36	30	43	35	30	41	35	29	27
7	58	43	33	26	56	42	33	26	40	32	26	39	31	26	37	31	25	23
8	54	39	29	23	52	38	29	23	37	28	23	35	28	22	34	27	22	20
9	50	35	26	20	49	35	26	20	34	26	20	32	25	20	31	25	20	18
10	47	33	24	18	46	32	24	18	31	23	18	30	23	18	29	23	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	91907	91907	91907	91907
5°	96583	91931	67163	67556
10°	83051	79870	36720	35858
15°	80756	76768	23855	17975
20°	93082	89192	12781	6391
25°	117037	109475	8283	4969
30°	140571	130999	6708	4070
35°	166464	156185	5498	3268
40°	200841	189082	4857	2471
45°	228659	218689	4523	1661
50°	256515	246563	4468	1016
55°	290085	289061	4439	455
60°	357968	366454	4047	131
65°	399418	440502	3707	0
70°	407276	497167	3435	0
75°	331394	366703	3280	0
80°	240956	153368	3384	0
85°	155777	64410	4495	0

TEST NUMBER: P599557
 CATALOG NUMBER: IFLD-S-SA6D-760-U-SLL-HSS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	973.0	2.9
10°-20°	1908.0	5.6
20°-30°	2640.4	7.8
30°-40°	3731.5	11.0
40°-50°	5080.5	14.9
50°-60°	6728.8	19.8
60°-70°	7812.7	22.9
70°-80°	4424.4	13.0
80°-90°	764.5	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5521.3	16.2
0°-40°	9252.8	27.2
0°-60°	21062.2	61.8
0°-90°	34063.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	34063.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	12808	12808	12808	12808	12808	
5°	13408	12762	9324	9378	13408	1204
15°	10870	10334	3211	2420	10870	3188
25°	14782	13826	1046	628	14782	6894
35°	19002	17829	628	373	19002	11979
45°	22532	21549	446	164	22532	17469
55°	23187	23105	355	36	23187	21007
65°	23523	25943	218	0	23523	22931
75°	11953	13226	118	0	11953	13045
85°	1892	782	55	0	1892	2273
90°	0	0	0	0	0	

TEST NUMBER: P599557
 CATALOG NUMBER: IFLD-S-SA6D-760-U-SLL-HSS

CANDELA DISTRIBUTION (FULL):

	0°	2°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7
2.5°	13308.0	13590.0	13599.1	13726.4	13853.8	13853.8	14153.9	14081.2	13817.4	13771.9	13580.9
5°	13408.0	13508.1	13580.9	14226.7	14772.5	14717.9	14881.7	14772.5	14263.1	13608.2	13162.4
7.5°	12543.9	12653.0	12944.1	14044.8	14781.6	15027.2	15336.5	14654.2	14117.6	12935.0	12080.0
10°	11397.7	11607.0	12143.6	13398.9	14308.6	15090.9	15090.9	14545.1	13508.1	12352.9	11306.8
12.5°	10761.0	11179.4	11470.5	12744.0	13926.5	14463.2	14445.0	14153.9	13480.8	12025.4	10842.9
15°	10870.2	10988.4	11607.0	12598.5	13380.8	13353.5	13680.9	13590.0	13117.0	12316.5	11015.7
17.5°	11370.5	11552.4	12089.1	12598.5	12971.4	12862.3	12853.2	13289.8	13317.1	12807.7	11661.5
20°	12189.1	12725.8	12980.5	13135.2	12680.3	12216.4	12161.8	12771.3	13244.3	13435.3	12434.7
22.5°	13499.0	13853.8	14372.3	13580.9	12398.3	11816.2	11707.0	12380.2	13335.3	14181.2	13435.3
25°	14781.6	15054.5	15554.8	14536.0	12716.7	11734.3	11543.3	12125.5	13680.9	15218.2	14645.1
27.5°	16137.0	16373.5	16428.0	15236.4	12889.5	11570.6	11343.2	12125.5	13972.0	15764.0	16091.5
30°	16964.7	17246.7	17301.3	15855.0	13171.5	11707.0	11597.9	12180.0	14172.1	16227.9	17128.5
32.5°	17892.5	17965.3	17919.8	15964.1	13480.8	12107.3	11652.4	12543.9	14399.5	16782.8	18074.5
35°	19002.3	19129.7	18665.7	16464.4	14172.1	12362.0	12198.2	12989.6	14790.7	17037.5	19220.6
37.5°	19848.3	20248.5	19202.4	16655.4	14308.6	12898.6	12925.9	13917.4	15063.6	17346.8	20485.0
40°	21440.1	20767.0	20112.1	17310.4	14827.1	13808.3	13662.7	14872.6	15982.3	17546.9	21312.8
42.5°	22313.4	21958.6	20466.8	17374.1	15627.6	15063.6	15100.0	15955.0	16464.4	18110.9	21540.2
45°	22531.7	22158.7	20948.9	17419.5	16418.9	16546.3	17173.9	17337.7	17173.9	18483.8	21967.7
47.5°	23086.6	22277.0	20894.3	18029.0	17701.5	18192.7	18993.2	19348.0	18138.2	18347.4	22167.8
50°	22977.4	22513.5	20776.1	18283.7	19266.1	20566.9	21103.6	20958.0	19211.5	18065.4	21949.5
52.5°	22522.6	22022.3	21140.0	18975.0	20730.6	22304.3	23050.2	22686.3	20166.6	18702.1	21804.0
55°	23186.6	22804.6	21613.0	19911.9	21831.3	23832.5	24360.1	24087.2	21340.1	19293.4	22631.8
57.5°	23905.2	23823.4	22895.5	21012.6	23132.1	25406.1	25406.1	25069.6	22358.9	20148.4	23859.8
60°	24942.2	25124.2	23841.6	21740.3	23577.8	25315.2	26634.2	26243.0	23386.8	21649.3	25251.5
62.5°	24605.7	25187.8	25060.5	23304.9	24087.2	25760.9	26479.5	26770.6	24660.2	23477.7	27107.2
65°	23523.2	24141.8	25051.4	24332.8	23705.1	24678.4	25042.3	25924.6	25297.0	25196.9	27871.3
67.5°	22231.5	22904.6	23468.6	25024.1	22931.9	23577.8	23259.4	23541.4	24605.7	27079.9	28307.9
70°	19411.6	20057.5	20948.9	23486.8	20885.3	20303.1	20221.2	20084.8	21740.3	26406.7	26324.9
72.5°	15964.1	16264.3	17737.9	19093.3	15454.7	15345.6	15472.9	15318.3	17237.6	23905.2	22549.9
75°	11952.6	12252.8	13089.7	14663.3	10524.5	9896.8	10624.6	11343.2	13162.4	18556.6	16200.6
77.5°	8987.2	9369.3	9896.8	10970.2	7722.8	6740.4	6840.5	7522.7	9514.8	14863.5	9078.2
80°	5830.8	5785.3	6804.1	7550.0	5812.6	5994.5	5739.8	6240.1	6895.0	7950.2	4639.1
82.5°	3365.7	3411.1	3838.7	4329.9	4047.9	4630.0	3338.4	5576.1	4921.1	3238.3	1728.3
85°	1892.0	1973.9	2365.1	3001.8	2537.9	1701.0	1391.7	2765.3	3092.8	1328.1	836.9
87.5°	191.0	163.7	318.4	1137.0	691.3	282.0	418.4	664.0	745.9	500.3	245.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599557
 CATALOG NUMBER: IFLD-S-SA6D-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7
2.5°	13308.0	13308.0	13080.6	12698.5	12543.9	12271.0	11898.0	12016.3	11888.9	11425.0	11306.8
5°	12762.2	12325.6	11852.6	11270.4	10933.8	10242.5	10024.2	9633.0	9696.7	9305.6	9323.8
7.5°	11625.2	11279.5	10479.0	9714.9	9050.9	8450.5	7604.6	7286.2	6976.9	6822.3	7004.2
10°	10961.1	10315.3	9223.7	8223.1	7340.8	6804.1	6240.1	5803.5	5403.2	5103.1	5039.4
12.5°	10479.0	9905.9	8587.0	7368.1	6676.7	6240.1	5721.6	5121.3	4730.1	4211.6	4057.0
15°	10333.5	9633.0	8241.3	7031.5	6358.4	5639.7	5048.5	4457.2	3947.8	3402.0	3211.0
17.5°	10833.8	10024.2	8232.2	6758.6	5812.6	5039.4	4220.7	3556.7	3038.2	2537.9	2419.6
20°	11679.7	10442.6	8496.0	6594.9	5294.1	4257.1	3329.3	2665.2	2083.1	1755.6	1673.7
22.5°	12643.9	11152.1	8523.3	6158.2	4775.6	3474.8	2428.7	1755.6	1428.1	1273.5	1228.0
25°	13826.5	12289.2	8850.8	5803.5	4166.1	2637.9	1728.3	1346.3	1155.2	1064.3	1046.1
27.5°	14799.8	13080.6	9205.5	5430.5	3565.8	1955.7	1355.4	1100.7	1000.6	909.6	900.5
30°	15809.5	13990.2	9305.6	5203.1	3047.3	1610.1	1164.3	973.3	864.2	818.7	809.6
32.5°	16691.8	14981.7	9624.0	4830.2	2556.1	1419.0	1055.2	873.3	800.5	727.7	718.6
35°	17828.9	15554.8	9778.6	4630.0	2374.2	1282.6	964.2	800.5	691.3	645.8	627.6
37.5°	19047.8	16109.7	9878.7	4475.4	2219.5	1200.7	909.6	755.0	654.9	591.3	573.1
40°	20184.8	16891.9	9733.1	4284.4	2101.3	1100.7	873.3	700.4	609.5	545.8	518.5
42.5°	21058.1	17656.0	9687.6	4102.5	1973.9	1064.3	827.8	673.1	573.1	500.3	491.2
45°	21549.3	18174.5	9369.3	3956.9	1873.9	1082.5	809.6	636.7	545.8	482.1	445.7
47.5°	21431.0	18574.8	9451.1	3911.4	1737.4	1009.7	800.5	609.5	500.3	445.7	418.4
50°	22086.0	19384.4	9314.7	3765.9	1637.3	909.6	873.3	609.5	491.2	427.5	400.2
52.5°	22195.1	20121.2	9605.8	3502.1	1482.7	836.9	864.2	600.4	473.0	409.3	373.0
55°	23104.8	20976.2	10169.7	3356.6	1355.4	727.7	791.4	582.2	427.5	373.0	354.8
57.5°	24341.9	22750.0	10533.6	3220.1	1182.5	636.7	664.0	573.1	391.1	345.7	318.4
60°	25533.5	23459.5	10560.9	2974.5	1018.8	573.1	518.5	573.1	363.9	309.3	282.0
62.5°	26424.9	23459.5	10379.0	2765.3	891.4	509.4	454.8	545.8	327.5	272.9	254.7
65°	25942.8	22831.9	9905.9	2592.5	809.6	445.7	391.1	418.4	291.1	236.5	218.3
67.5°	25078.7	20876.2	8859.9	2383.2	800.5	391.1	336.6	309.3	254.7	209.2	191.0
70°	23696.0	18238.2	7377.2	2146.7	782.3	354.8	300.2	263.8	227.4	181.9	163.7
72.5°	19093.3	15063.6	6058.2	2010.3	764.1	309.3	254.7	227.4	191.0	154.6	136.4
75°	13226.1	9624.0	4666.4	1719.2	745.9	282.0	236.5	200.1	163.7	127.3	118.3
77.5°	7932.0	6431.1	3010.9	1291.7	491.2	227.4	200.1	154.6	136.4	109.2	100.1
80°	3711.3	3038.2	1218.9	500.3	236.5	163.7	136.4	118.3	109.2	91.0	81.9
82.5°	1455.4	1282.6	591.3	291.1	191.0	127.3	109.2	100.1	91.0	72.8	63.7
85°	782.3	691.3	282.0	200.1	136.4	91.0	91.0	81.9	72.8	63.7	54.6
87.5°	172.8	127.3	118.3	118.3	100.1	72.8	72.8	63.7	54.6	45.5	36.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599557
 CATALOG NUMBER: IFLD-S-SA6D-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7
2.5°	11243.1	11379.6	11161.2	11297.7	11106.7	11252.2	11270.4	11133.9	11170.3	11352.3	11434.1
5°	9578.5	9487.5	9287.4	9223.7	9232.8	9114.6	9160.0	9223.7	9323.8	9378.4	9542.1
7.5°	6904.1	7113.4	7104.3	7258.9	7268.0	7249.8	7122.5	6849.6	6940.5	6867.8	6958.7
10°	4939.3	5030.3	5203.1	5303.2	5485.1	5385.0	5094.0	4984.8	4930.2	4921.1	5012.1
12.5°	3947.8	3729.5	3711.3	3747.7	3838.7	3720.4	3574.9	3447.5	3511.2	3638.5	3738.6
15°	3056.4	2874.5	2637.9	2601.6	2619.8	2565.2	2410.5	2246.8	2292.3	2419.6	2492.4
17.5°	2346.9	2137.6	1973.9	1864.8	1828.4	1637.3	1409.9	1273.5	1237.1	1228.0	1291.7
20°	1582.8	1546.4	1519.1	1382.6	1382.6	1109.8	918.7	818.7	818.7	836.9	846.0
22.5°	1182.5	1137.0	1146.1	1118.9	1046.1	827.8	727.7	700.4	700.4	718.6	718.6
25°	1027.9	964.2	946.0	936.9	864.2	709.5	636.7	609.5	609.5	627.6	627.6
27.5°	873.3	855.1	827.8	791.4	727.7	609.5	564.0	536.7	545.8	554.9	545.8
30°	800.5	755.0	718.6	718.6	645.8	545.8	509.4	491.2	473.0	491.2	500.3
32.5°	709.5	682.2	664.0	636.7	554.9	482.1	445.7	427.5	418.4	418.4	427.5
35°	609.5	609.5	591.3	554.9	482.1	436.6	391.1	373.0	363.9	373.0	373.0
37.5°	545.8	518.5	527.6	491.2	427.5	382.0	336.6	318.4	318.4	309.3	318.4
40°	509.4	463.9	436.6	418.4	382.0	327.5	291.1	272.9	263.8	263.8	263.8
42.5°	454.8	418.4	363.9	354.8	345.7	282.0	236.5	227.4	218.3	209.2	209.2
45°	427.5	373.0	327.5	282.0	282.0	236.5	200.1	181.9	172.8	163.7	172.8
47.5°	391.1	336.6	282.0	236.5	227.4	191.0	154.6	136.4	127.3	127.3	127.3
50°	373.0	300.2	245.6	200.1	172.8	154.6	118.3	100.1	91.0	91.0	91.0
52.5°	345.7	282.0	218.3	172.8	136.4	118.3	91.0	72.8	63.7	63.7	63.7
55°	309.3	254.7	191.0	145.5	118.3	91.0	63.7	45.5	36.4	36.4	36.4
57.5°	291.1	227.4	163.7	127.3	91.0	63.7	36.4	27.3	27.3	18.2	27.3
60°	263.8	200.1	136.4	100.1	72.8	45.5	27.3	9.1	9.1	9.1	9.1
62.5°	227.4	172.8	118.3	81.9	54.6	27.3	9.1	0.0	0.0	0.0	0.0
65°	191.0	136.4	91.0	63.7	36.4	9.1	0.0	0.0	0.0	0.0	0.0
67.5°	163.7	118.3	72.8	45.5	27.3	0.0	0.0	0.0	0.0	0.0	0.0
70°	145.5	100.1	54.6	36.4	9.1	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	118.3	81.9	45.5	18.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	100.1	63.7	27.3	9.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	81.9	45.5	18.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	63.7	36.4	9.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	54.6	27.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	36.4	9.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	27.3	9.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599557
 CATALOG NUMBER: IFLD-S-SA6D-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	358°	360°
0°	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7	12807.7
2.5°	11552.4	11497.8	11770.7	12216.4	12443.8	12889.5	12998.7	13280.7	13207.9	13308.0
5°	9560.3	9669.4	10069.7	10724.6	10961.1	11607.0	12216.4	12825.9	13217.0	13408.0
7.5°	7095.2	7459.0	7950.2	8550.6	9160.0	10006.0	11043.0	11752.5	12134.5	12543.9
10°	5285.0	5676.1	6240.1	6831.4	7822.9	8768.9	9805.9	10688.2	11015.7	11397.7
12.5°	4157.0	4766.5	5421.4	6058.2	6649.4	7550.0	8832.6	10115.2	10469.9	10761.0
15°	2892.6	3638.5	4575.5	5403.2	6231.0	7013.3	8341.4	9896.8	10379.0	10870.2
17.5°	1601.0	2192.2	3265.6	4429.9	5648.8	6849.6	8505.1	10297.1	11024.8	11370.5
20°	927.8	1164.3	1928.4	3311.1	4921.1	6494.8	8587.0	11052.1	12016.3	12189.1
22.5°	764.1	846.0	1091.6	2074.0	4029.7	6267.4	9005.4	12107.3	13089.7	13499.0
25°	654.9	718.6	846.0	1246.2	3047.3	5785.3	9269.2	13426.2	14335.9	14781.6
27.5°	582.2	645.8	745.9	918.7	2074.0	5121.3	9705.8	14617.9	15527.5	16137.0
30°	509.4	564.0	664.0	782.3	1437.2	4375.4	10078.8	15491.1	16773.7	16964.7
32.5°	454.8	500.3	573.1	673.1	1064.3	3320.2	10379.0	16391.6	17474.1	17892.5
35°	391.1	445.7	491.2	573.1	809.6	2501.5	10197.0	17092.1	18502.0	19002.3
37.5°	345.7	382.0	427.5	482.1	682.2	1955.7	9824.1	17928.9	19384.4	19848.3
40°	291.1	318.4	373.0	427.5	618.6	1510.0	9396.5	18938.6	20621.5	21440.1
42.5°	245.6	272.9	309.3	400.2	509.4	1118.9	8532.4	19720.9	21622.1	22313.4
45°	191.0	227.4	282.0	400.2	409.3	827.8	7640.9	20303.1	22186.0	22531.7
47.5°	145.5	181.9	272.9	345.7	327.5	573.1	6585.8	20967.1	22768.2	23086.6
50°	109.2	145.5	309.3	300.2	272.9	436.6	5921.7	21431.0	22804.6	22977.4
52.5°	72.8	109.2	254.7	227.4	227.4	382.0	5739.8	21412.8	22895.5	22522.6
55°	54.6	81.9	145.5	163.7	200.1	336.6	5576.1	22095.1	22922.8	23186.6
57.5°	36.4	63.7	100.1	127.3	172.8	291.1	5239.5	22913.7	23768.8	23905.2
60°	18.2	45.5	72.8	100.1	145.5	254.7	4766.5	23514.1	24796.7	24942.2
62.5°	9.1	27.3	54.6	81.9	118.3	200.1	4275.3	22559.0	24351.0	24605.7
65°	0.0	18.2	36.4	54.6	72.8	145.5	3474.8	20366.8	22586.3	23523.2
67.5°	0.0	0.0	18.2	36.4	45.5	109.2	2619.8	18529.3	20958.0	22231.5
70°	0.0	0.0	9.1	9.1	27.3	81.9	1673.7	15345.6	18711.2	19411.6
72.5°	0.0	0.0	0.0	0.0	9.1	54.6	973.3	11397.7	14663.3	15964.1
75°	0.0	0.0	0.0	0.0	0.0	45.5	491.2	7331.7	10206.1	11952.6
77.5°	0.0	0.0	0.0	0.0	0.0	36.4	263.8	4730.1	7522.7	8987.2
80°	0.0	0.0	0.0	0.0	0.0	9.1	154.6	2747.1	4812.0	5830.8
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	63.7	1346.3	2874.5	3365.7
85°	0.0	0.0	0.0	0.0	0.0	0.0	18.2	718.6	1437.2	1892.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	27.3	100.1	191.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)