

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P948705

Luminaire Tested: **GLAN-SB3C-935-U-SLR-HSS**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P948705
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB3C-935-U-SLR-HSS
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(3) 90 CRI, 3500K, 615mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11930 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G3

Input Watts (W): 149.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P948705
CATALOG NUMBER: GLAN-SB3C-935-U-SLR-HSS



REPORT NUMBER: P948705
CATALOG NUMBER: GLAN-SB3C-935-U-SLR-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P948705

CATALOG NUMBER: GLAN-SB3C-935-U-SLR-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1670.7	0.0	1670.7
	% Fixture	14.0	0.0	14.0
Street Side	Lumens	10259.3	0.0	10259.3
	% Fixture	86.0	0.0	86.0
Total	Lumens	11930.0	0.0	11930.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.6	1.4
10°-20°	487.5	4.1
20°-30°	718.2	6.0
30°-40°	922.7	7.7
40°-50°	1492.4	12.5
50°-60°	2617.0	21.9
60°-70°	3274.6	27.4
70°-80°	1913.5	16.0
80°-90°	341.4	2.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11930.0	100.0
0°-180°	11930.0	100.0

Coefficient of Utilization



REPORT NUMBER: P948705


CATALOG NUMBER: GLAN-SB3C-935-U-SLR-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	930.5	7.8			
FM	(30°-60°)	4181.3	35.0			
FH	(60°-80°)	4819.2	40.4			G2/5000
FVH	(80°-90°)	328.3	2.8			G3/500
BL	(0°-30°)	437.9	3.7	B1/500		
BM	(30°-60°)	850.8	7.1	B1/1000		
BH	(60°-80°)	368.9	3.1	B1/500		G1/500
BVH	(80°-90°)	13.1	0.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G3

Type IV Short



REPORT NUMBER: P948705

CATALOG NUMBER: GLAN-SB3C-935-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9
2.5°	1866.4	1834.4	1815.5	1768.6	1721.8	1684.0	1633.0	1599.3	1559.1	1520.4
5°	2080.1	2028.3	1965.9	1880.4	1802.3	1722.6	1645.3	1568.9	1488.4	1414.4
7.5°	2260.9	2186.1	2076.0	1962.6	1863.1	1767.0	1676.6	1575.5	1477.7	1361.8
10°	2399.0	2303.7	2159.0	2010.3	1896.0	1799.0	1711.1	1625.6	1527.0	1387.3
12.5°	2482.8	2380.9	2209.1	2034.9	1904.2	1795.7	1727.5	1689.7	1651.1	1512.2
15°	2544.5	2434.3	2244.5	2052.2	1885.3	1752.2	1702.1	1739.9	1784.2	1695.5
17.5°	2608.6	2492.7	2290.5	2059.6	1834.4	1667.5	1646.2	1744.0	1846.7	1842.6
20°	2669.4	2554.3	2330.8	2054.6	1752.2	1564.8	1583.7	1708.6	1827.8	1877.9
22.5°	2739.2	2617.6	2369.4	2035.7	1645.3	1468.7	1527.8	1652.7	1757.1	1816.3
25°	2824.7	2697.3	2423.6	2007.8	1530.3	1388.9	1471.1	1587.8	1672.5	1713.6
27.5°	2916.8	2792.7	2496.0	1993.0	1437.4	1332.2	1407.0	1510.6	1586.2	1614.9
30°	3031.0	2903.6	2581.4	1976.6	1376.6	1299.3	1340.4	1421.0	1494.9	1523.7
32.5°	3155.9	3026.9	2663.6	1937.1	1339.6	1274.7	1275.5	1326.5	1393.9	1428.4
35°	3312.1	3174.8	2751.6	1850.8	1310.0	1245.9	1212.2	1236.9	1292.8	1333.9
37.5°	3534.8	3368.8	2859.2	1727.5	1266.5	1201.5	1145.7	1151.4	1194.2	1239.4
40°	3842.2	3629.3	2985.8	1599.3	1204.0	1139.1	1072.5	1070.1	1101.3	1145.7
42.5°	4258.0	3973.7	3137.8	1476.9	1144.0	1063.5	995.3	991.2	1015.8	1054.4
45°	4807.0	4414.2	3324.4	1371.7	1097.2	989.5	922.1	920.5	941.0	974.7
47.5°	5509.7	5026.4	3511.0	1300.2	1072.5	931.2	862.1	865.4	883.5	913.9
50°	6419.5	5824.5	3567.7	1264.0	1072.5	899.9	808.7	825.1	839.9	862.9
52.5°	7510.1	6590.4	3380.3	1231.1	1079.1	904.0	763.5	798.8	809.5	829.2
55°	8521.0	6966.0	2906.1	1185.9	1080.7	929.5	724.9	777.5	797.2	804.6
57.5°	9107.8	6837.0	2349.7	1109.5	1074.2	946.8	700.2	751.2	789.0	793.9
60°	8996.0	6384.1	1730.0	1051.1	1025.7	940.2	692.8	710.9	770.9	778.3
62.5°	8134.7	5624.8	1200.7	1005.9	918.8	911.4	690.4	647.6	731.4	749.5
65°	6538.7	4428.1	848.2	866.2	805.4	849.0	677.2	581.9	683.8	708.4
67.5°	4743.7	2996.5	612.3	701.9	729.8	747.9	647.6	534.2	629.5	662.4
70°	3044.1	1618.2	429.8	463.5	614.7	635.3	596.7	491.5	574.5	612.3
72.5°	2163.9	955.8	309.0	324.6	493.9	529.3	525.2	443.8	510.4	556.4
75°	1493.3	526.8	208.8	231.8	358.3	429.8	405.2	381.3	432.3	479.1
77.5°	936.1	235.9	124.9	161.1	235.0	337.8	277.8	295.0	337.0	380.5
80°	521.1	91.2	69.9	106.8	128.2	245.7	153.7	189.8	248.2	279.4
82.5°	113.4	11.5	31.2	46.0	50.1	143.0	81.4	110.1	156.2	153.7
85°	0.0	0.0	5.8	6.6	3.3	61.6	29.6	36.2	51.0	47.7
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P948705

CATALOG NUMBER: GLAN-SB3C-935-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

90°		95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
1651.9	0°	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9
1485.9	2.5°	1479.3	1439.1	1409.5	1394.7	1382.4	1393.9	1400.4	1400.4	1428.4	1444.8
1369.2	5°	1340.4	1268.1	1213.1	1176.1	1153.9	1161.3	1169.5	1178.5	1213.9	1237.7
1300.2	7.5°	1244.3	1133.3	1049.5	997.7	970.6	974.7	980.5	987.9	1022.4	1046.2
1310.0	10°	1226.2	1066.8	948.4	880.2	847.3	841.6	838.3	835.8	856.4	874.5
1421.8	12.5°	1300.2	1070.1	904.9	821.9	781.6	764.3	744.6	729.0	732.3	743.8
1591.1	15°	1432.5	1112.0	890.9	791.4	741.3	712.5	689.5	670.6	666.5	670.6
1739.0	17.5°	1583.7	1168.7	889.2	765.1	702.7	673.1	654.2	636.9	631.2	632.0
1822.0	20°	1684.0	1213.9	884.3	735.6	665.7	639.4	623.0	605.7	600.0	601.6
1799.0	22.5°	1693.8	1237.7	876.9	702.7	628.7	606.5	590.1	574.5	573.7	573.7
1712.7	25°	1640.4	1237.7	861.3	673.1	593.4	573.7	558.9	540.0	543.2	544.9
1614.9	27.5°	1557.4	1208.1	831.7	649.3	563.0	542.4	527.6	510.4	514.5	516.9
1523.7	30°	1475.2	1170.3	796.4	622.1	534.2	510.4	499.7	484.9	486.5	489.8
1433.3	32.5°	1398.8	1130.0	754.5	600.0	505.4	481.6	473.4	456.9	459.4	462.7
1344.6	35°	1323.2	1085.7	705.1	573.7	479.1	455.3	448.7	429.8	431.5	436.4
1255.8	37.5°	1241.8	1038.8	664.9	547.4	453.7	429.0	422.4	402.7	404.4	410.1
1163.7	40°	1156.3	992.8	625.4	519.4	426.5	401.9	396.1	374.8	376.4	383.0
1073.3	42.5°	1070.1	942.7	595.0	483.2	398.6	372.3	366.5	346.8	349.3	356.7
994.4	45°	990.3	882.7	575.3	443.0	372.3	342.7	337.0	318.9	323.8	332.0
927.9	47.5°	922.1	821.0	567.1	409.3	344.4	312.3	307.4	292.6	300.8	309.8
871.2	50°	863.8	761.9	556.4	374.8	318.1	286.0	281.1	271.2	281.9	290.9
832.5	52.5°	821.9	694.5	533.4	343.5	295.0	263.8	262.2	257.2	267.1	275.3
803.8	55°	785.7	624.6	496.4	316.4	274.5	244.9	246.6	244.1	252.3	258.9
786.5	57.5°	752.8	563.8	449.6	295.0	252.3	228.5	233.4	230.1	234.2	238.3
768.4	60°	713.4	502.2	393.7	271.2	226.0	212.0	217.8	208.8	207.9	209.6
735.6	62.5°	655.0	419.1	335.3	241.6	203.0	194.0	196.4	179.2	166.0	166.0
687.1	65°	573.7	337.0	281.1	208.8	176.7	169.3	167.7	143.0	124.9	123.3
634.5	67.5°	479.1	277.0	233.4	175.9	147.1	142.2	143.8	125.7	107.7	106.0
581.9	70°	390.4	229.3	188.2	140.5	113.4	118.3	125.7	107.7	90.4	87.9
520.2	72.5°	317.2	182.5	147.1	107.7	83.8	97.8	106.8	87.9	71.5	69.9
443.8	75°	244.9	134.0	105.2	73.1	60.8	75.6	83.8	64.1	51.0	48.5
343.5	77.5°	163.5	83.0	59.2	46.0	36.2	51.8	55.9	33.7	29.6	28.8
249.8	80°	99.4	38.6	25.5	22.2	12.3	18.9	22.2	14.0	15.6	16.4
133.1	82.5°	50.1	10.7	4.1	0.8	0.0	0.0	6.6	3.3	6.6	8.2
36.2	85°	4.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.6	4.1
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P948705

CATALOG NUMBER: GLAN-SB3C-935-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

185°		195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
1651.9	0°	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9
1451.4	2.5°	1497.4	1531.9	1564.8	1617.4	1671.6	1725.1	1779.3	1831.9	1850.8	1864.8
1253.3	5°	1324.8	1389.8	1465.4	1569.7	1681.5	1796.6	1913.3	2020.1	2068.6	2101.5
1066.8	7.5°	1146.5	1231.1	1339.6	1496.6	1671.6	1854.9	2038.2	2206.7	2284.7	2348.0
890.9	10°	969.8	1061.8	1199.1	1378.2	1614.9	1877.9	2131.1	2362.8	2463.9	2543.6
764.3	12.5°	814.5	900.8	1044.6	1242.6	1526.2	1859.9	2184.5	2463.1	2582.3	2671.8
673.9	15°	705.1	766.0	893.4	1107.0	1421.0	1801.5	2187.8	2510.8	2641.4	2735.1
636.1	17.5°	644.3	664.9	747.9	969.0	1304.3	1725.1	2157.4	2527.2	2666.9	2754.0
602.4	20°	611.5	614.7	637.8	789.8	1154.7	1653.6	2128.6	2543.6	2690.7	2763.9
578.6	22.5°	585.2	585.2	590.9	646.0	961.6	1568.1	2119.6	2572.4	2723.6	2768.8
551.5	25°	561.3	561.3	563.0	577.8	761.9	1437.4	2113.8	2616.8	2768.8	2781.1
524.3	27.5°	536.7	537.5	537.5	545.7	613.9	1259.9	2089.1	2674.3	2823.1	2797.6
498.0	30°	512.0	513.7	513.7	519.4	543.2	1052.0	2040.7	2743.3	2893.7	2819.0
471.7	32.5°	487.4	489.0	489.0	493.9	511.2	839.9	1979.8	2806.6	2965.2	2828.0
446.3	35°	461.9	464.3	462.7	469.3	487.4	668.2	1902.6	2869.9	3042.5	2856.8
421.6	37.5°	436.4	438.0	437.2	443.8	464.3	576.9	1813.0	2917.6	3147.7	2920.9
395.3	40°	410.9	410.1	410.1	417.5	439.7	550.6	1700.4	2993.2	3298.9	3033.5
369.0	42.5°	384.6	384.6	383.0	391.2	418.3	530.9	1592.7	3128.8	3519.2	3212.6
344.4	45°	360.8	360.0	356.7	364.1	397.8	496.4	1554.9	3381.9	3844.6	3502.7
319.7	47.5°	337.8	337.0	328.7	335.3	373.1	465.2	1696.3	3796.1	4295.8	3929.3
300.0	50°	317.2	318.1	302.4	308.2	348.5	441.3	2002.9	4333.6	4895.0	4503.8
283.5	52.5°	298.3	298.3	277.8	281.1	318.1	420.0	2294.6	4916.3	5685.6	5305.1
266.3	55°	279.4	277.8	254.8	256.4	287.6	389.6	2338.2	5485.0	6763.8	6510.7
247.4	57.5°	258.1	254.8	233.4	233.4	259.7	367.4	2026.7	5922.3	8101.8	8282.6
212.0	60°	231.8	229.3	215.3	211.2	237.5	387.1	1430.0	5973.2	8964.8	10638.9
168.5	62.5°	198.1	201.4	194.0	188.2	216.1	401.9	847.3	5563.1	8756.0	11388.4
130.7	65°	156.2	169.3	167.7	163.5	237.5	338.6	500.5	4775.8	8115.8	10783.5
114.2	67.5°	133.1	142.2	139.7	139.7	249.0	257.2	314.8	3731.2	7234.8	10066.0
95.3	70°	113.4	122.5	113.4	113.4	188.2	156.2	217.8	2605.3	6283.9	9272.1
76.4	72.5°	93.7	102.7	92.9	86.3	150.4	116.7	159.4	1628.1	5381.5	8445.4
54.2	75°	71.5	82.2	74.8	66.6	99.4	87.1	120.8	946.0	4458.5	7225.7
32.9	77.5°	45.2	59.2	55.9	46.8	73.1	63.3	87.1	563.0	3440.3	5646.1
19.7	80°	27.9	30.4	31.2	29.6	41.9	42.7	59.2	320.5	2354.6	3935.0
12.3	82.5°	18.1	18.1	14.0	15.6	20.5	24.7	33.7	120.8	1384.0	2395.7
7.4	85°	13.1	11.5	7.4	7.4	9.9	12.3	13.1	37.0	561.3	946.0
3.3	87.5°	6.6	5.8	2.5	3.3	4.9	4.1	3.3	1.6	141.4	302.4
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P948705

CATALOG NUMBER: GLAN-SB3C-935-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

285°		295°	305°	315°	325°	335°	345°	355°	360°
1651.9	0°	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9
1896.0	2.5°	1912.5	1937.9	1939.6	1939.6	1917.4	1916.6	1871.4	1866.4
2175.4	5°	2251.9	2268.3	2272.4	2264.2	2219.8	2186.9	2099.0	2080.1
2460.6	7.5°	2562.5	2595.4	2595.4	2575.7	2503.4	2436.0	2308.6	2260.9
2696.5	10°	2810.7	2848.5	2840.3	2800.1	2708.8	2616.0	2461.4	2399.0
2839.5	12.5°	2931.5	2970.2	2948.8	2902.8	2814.0	2716.2	2553.5	2482.8
2880.6	15°	2929.1	2918.4	2896.2	2890.5	2847.7	2773.8	2621.7	2544.5
2855.1	17.5°	2824.7	2734.3	2717.0	2774.6	2828.8	2810.7	2680.9	2608.6
2794.3	20°	2659.5	2501.7	2486.1	2596.2	2750.7	2829.6	2735.9	2669.4
2706.4	22.5°	2485.3	2315.2	2279.0	2400.6	2633.2	2835.4	2805.8	2739.2
2609.4	25°	2320.1	2149.1	2113.0	2226.4	2502.5	2825.5	2881.4	2824.7
2516.5	27.5°	2182.0	2016.8	1983.1	2096.5	2376.8	2797.6	2957.0	2916.8
2424.5	30°	2075.2	1922.3	1897.7	2007.0	2268.3	2763.1	3053.2	3031.0
2339.0	32.5°	2012.7	1900.9	1910.0	1999.6	2210.0	2725.3	3145.2	3155.9
2297.1	35°	2074.4	2079.3	2158.2	2195.2	2264.2	2719.5	3270.2	3312.1
2347.2	37.5°	2380.9	2551.9	2715.4	2685.0	2529.7	2786.1	3456.7	3534.8
2565.8	40°	2902.8	3253.7	3519.2	3403.3	3012.1	2989.9	3725.5	3842.2
2953.7	42.5°	3540.5	4135.6	4572.8	4262.1	3634.2	3346.6	4109.3	4258.0
3423.0	45°	4213.6	5222.9	5911.6	5265.6	4297.5	3846.3	4690.3	4807.0
3862.7	47.5°	4922.9	6544.4	7435.3	6378.4	4912.2	4415.0	5482.6	5509.7
4279.4	50°	5698.7	7993.3	8988.6	7490.4	5505.6	5066.7	6450.7	6419.5
4765.1	52.5°	6437.6	9483.4	10509.0	8607.3	6026.6	5875.4	7574.2	7510.1
5429.2	55°	7142.7	10972.6	12038.5	9680.6	6518.1	6943.8	8908.9	8521.0
6386.6	57.5°	7960.5	12311.3	13614.8	10758.9	7205.2	8331.1	10401.4	9107.8
8220.2	60°	9169.4	13832.6	15397.4	12236.6	8511.9	9789.1	10936.4	8996.0
10416.2	62.5°	10712.8	15231.4	16693.5	13684.7	9824.4	10063.6	10148.2	8134.7
9968.2	65°	11012.8	15585.6	16766.6	14071.8	9655.1	8536.6	8285.1	6538.7
8903.9	67.5°	10217.3	14945.4	15744.2	13351.0	8540.7	6597.0	6217.3	4743.7
8205.4	70°	9324.7	13724.9	13962.4	12125.6	7511.7	4852.2	4198.8	3044.1
7727.1	72.5°	8410.0	12096.8	11605.4	10530.4	6601.9	3533.1	3028.5	2163.9
7045.7	75°	7323.5	9955.9	9141.5	8749.4	5466.1	2772.9	2191.1	1493.3
6060.3	77.5°	5864.7	7007.9	6790.1	6781.9	4107.6	2025.9	1462.1	936.1
4734.7	80°	4137.2	4548.1	4437.2	5107.8	2755.7	1469.5	880.2	521.1
3295.6	82.5°	2002.9	2514.9	2581.4	3041.7	1340.4	864.6	203.0	113.4
1288.7	85°	784.0	1213.1	1023.2	1154.7	376.4	240.8	4.9	0.0
212.0	87.5°	87.9	140.5	129.0	101.9	46.0	9.9	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)