

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599303

Luminaire Tested: **IFLD-L-SA7A-760-U-SLR-HSS**

Issue Date: 05/04/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

**Test Information**

Test Method: LM-79-08  
 Report Number: P599303  
 Test Lab: INNOVATION CENTER(G1)  
 Issue Date: 05/04/2022  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: IFLD-L-SA7A-760-U-SLR-HSS  
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLR distribution lens with House Side Shield  
 Light Source: (112) 5700K CCT, 70 CRI LEDS  
 Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
 Luminaire Lumens: 23321.9 lumens  
 Efficiency: N/A  
 Efficacy: 107.2 lumens/watt  
 Spacing Criteria (0/90/45): 0.44 / 0.52 / 0.65  
 Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')  
 CIE Type: Direct

Input Watts (W): 217.6  
 Input Voltage (V): 120  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599303  
CATALOG NUMBER: IFLD-L-SA7A-760-U-SLR-HSS

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - · - 135°-315°

TEST NUMBER: P599303  
 CATALOG NUMBER: IFLD-L-SA7A-760-U-SLR-HSS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	107	101	96	91	104	99	94	90	94	90	87	90	87	84	87	84	82	79
2	95	85	77	70	92	83	75	69	79	73	67	76	71	66	73	68	64	62
3	85	72	63	55	82	71	62	54	67	60	53	65	58	52	62	56	51	49
4	76	62	52	44	74	61	51	44	58	50	43	56	49	43	53	47	42	40
5	69	55	44	37	67	53	44	36	51	43	36	49	41	35	47	40	35	33
6	63	48	38	31	61	47	38	31	45	37	30	44	36	30	42	35	30	27
7	58	43	33	27	56	42	33	26	41	32	26	39	32	26	38	31	26	24
8	54	39	30	23	52	38	29	23	37	29	23	36	28	23	34	28	23	20
9	50	36	27	21	49	35	26	21	34	26	20	33	25	20	32	25	20	18
10	47	33	24	18	46	32	24	18	31	24	18	30	23	18	29	23	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	47985	47985	47985	47985
5°	46199	33766	36347	50920
10°	41132	18384	18624	43537
15°	41060	12262	7497	41830
20°	49300	6122	2989	49012
25°	60638	3846	2315	60339
30°	73266	3087	1758	72797
35°	85969	2479	1363	85101
40°	104077	2120	884	101205
45°	119069	1914	479	115766
50°	135089	1843	105	129561
55°	162954	1770	0	146906
60°	197287	1489	0	185579
65°	228447	1201	0	207628
70°	231326	990	0	209360
75°	149706	653	0	160559
80°	51059	195	0	113613
85°	25627	0	0	83481

TEST NUMBER: P599303  
 CATALOG NUMBER: IFLD-L-SA7A-760-U-SLR-HSS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	675.4	2.9
10°-20°	1307.8	5.6
20°-30°	1821.5	7.8
30°-40°	2588.1	11.1
40°-50°	3588.9	15.4
50°-60°	4890.1	21.0
60°-70°	5376.3	23.1
70°-80°	2642.4	11.3
80°-90°	431.5	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3804.6	16.3
0°-40°	6392.7	27.4
0°-60°	14871.7	63.8
0°-90°	23321.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	23321.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	8916	8916	8916	8916	8916	
5°	8551	6250	6728	9425	8551	783
15°	7369	2201	1346	7508	7369	2181
25°	10211	648	390	10161	10211	4747
35°	13085	377	208	12953	13085	8306
45°	15644	252	63	15210	15644	12127
55°	17367	189	0	15656	17367	15622
65°	17939	94	0	16304	17939	17336
75°	7199	31	0	7721	7199	7849
85°	415	0	0	1352	415	574
90°	0	0	0	0	0	

TEST NUMBER: P599303  
 CATALOG NUMBER: IFLD-L-SA7A-760-U-SLR-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9
2.5°	9098.3	9205.2	9104.6	8752.5	8689.6	8519.8	8262.0	8243.2	7972.8	8004.2	7859.6
5°	8551.3	8658.1	8444.4	7979.1	7545.2	7199.4	6991.9	6620.9	6539.2	6356.8	6356.8
7.5°	7991.6	7985.4	7620.7	7230.8	6583.2	5948.1	5658.9	5124.5	4810.1	4640.3	4476.8
10°	7526.4	7425.8	7199.4	6394.6	5690.4	5030.1	4671.7	4319.6	3992.7	3709.7	3426.8
12.5°	7199.4	7262.3	6903.9	6029.9	5118.2	4659.2	4275.6	3904.7	3514.8	3194.1	2879.8
15°	7369.2	7268.6	6847.3	5948.1	5023.9	4395.1	3885.8	3433.1	2999.2	2578.0	2339.0
17.5°	7897.3	7639.5	7142.8	5948.1	4828.9	3992.7	3376.5	2842.0	2376.7	1999.5	1704.0
20°	8607.8	8312.3	7777.9	6168.2	4684.3	3697.2	2854.6	2181.8	1697.7	1345.6	1119.2
22.5°	9337.2	9104.6	8299.7	6256.2	4514.6	3301.0	2251.0	1578.2	1131.8	905.4	792.2
25°	10211.2	9884.2	9004.0	6608.4	4263.1	2917.5	1773.1	1100.3	842.5	723.1	653.9
27.5°	10909.1	10852.5	9664.2	6822.1	4074.4	2603.1	1402.2	874.0	697.9	609.9	565.9
30°	11789.4	11481.3	10469.0	7249.7	3860.6	2244.7	1169.5	786.0	641.3	547.0	515.6
32.5°	12317.6	12173.0	10890.3	7488.6	3621.7	1949.2	1006.0	691.6	584.8	515.6	484.2
35°	13084.7	12795.4	11493.9	7639.5	3496.0	1779.4	905.4	628.8	490.4	421.3	383.5
37.5°	13939.8	13832.9	12217.0	7633.2	3313.6	1678.8	836.3	584.8	465.3	389.8	345.8
40°	14813.8	14379.9	12657.1	7809.3	3219.3	1603.4	786.0	559.6	440.1	371.0	314.4
42.5°	15467.7	14971.0	13166.4	7746.4	3106.1	1471.3	767.1	521.9	421.3	339.5	289.2
45°	15643.8	15467.7	13625.4	7727.6	3024.4	1364.4	735.7	515.6	408.7	320.7	270.4
47.5°	15983.3	15863.8	14191.3	7759.0	2961.5	1282.7	660.2	528.2	389.8	301.8	257.8
50°	16134.2	15920.4	14650.3	7834.5	2816.9	1182.1	591.0	553.3	383.5	295.5	245.2
52.5°	16756.7	16568.0	15279.1	8048.2	2697.4	1050.0	521.9	528.2	396.1	276.7	232.6
55°	17366.6	17152.8	16247.4	8538.7	2527.6	943.2	446.4	465.3	377.3	251.5	207.5
57.5°	18202.8	17850.7	16895.0	8739.9	2376.7	798.5	396.1	383.5	352.1	226.4	182.3
60°	18328.6	18473.2	16800.7	8614.1	2219.6	704.2	345.8	295.5	377.3	201.2	157.2
62.5°	18749.9	18146.3	16360.6	8324.9	2106.4	647.6	308.1	245.2	327.0	176.1	132.0
65°	17938.8	17492.3	15329.4	7394.3	1961.8	653.9	270.4	201.2	207.5	144.6	106.9
67.5°	16750.4	16398.3	13619.1	6382.0	1817.1	641.3	238.9	176.1	157.2	125.8	94.3
70°	14700.6	13939.8	11569.3	5181.1	1603.4	597.3	201.2	157.2	132.0	100.6	69.2
72.5°	10695.4	10387.3	8299.7	4005.3	1439.9	540.7	188.6	132.0	113.2	75.5	56.6
75°	7199.4	6690.1	5237.6	2628.3	1156.9	471.6	157.2	119.5	88.0	56.6	44.0
77.5°	3804.0	3596.6	2967.8	1251.2	641.3	220.1	88.0	69.2	50.3	44.0	25.2
80°	1647.4	1465.0	1282.7	509.3	226.4	100.6	56.6	37.7	31.4	25.2	12.6
82.5°	842.5	804.8	666.5	220.1	132.0	75.5	31.4	25.2	18.9	12.6	6.3
85°	415.0	427.6	352.1	69.2	75.5	44.0	6.3	6.3	0.0	0.0	0.0
87.5°	31.4	31.4	25.2	12.6	18.9	6.3	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599303  
 CATALOG NUMBER: IFLD-L-SA7A-760-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9
2.5°	7803.0	7891.0	7740.1	7834.5	7790.4	7809.3	7828.2	7777.9	7790.4	7966.5	7972.8
5°	6250.0	6419.7	6356.8	6444.9	6595.8	6520.3	6589.5	6576.9	6589.5	6614.6	6727.8
7.5°	4458.0	4407.7	4527.1	4759.8	5030.1	5193.6	5111.9	5067.9	5042.7	4979.8	5055.3
10°	3363.9	3338.8	3307.3	3376.5	3552.5	3734.9	3835.5	3665.7	3571.4	3451.9	3407.9
12.5°	2791.7	2634.5	2546.5	2439.6	2489.9	2653.4	2659.7	2496.2	2345.3	2282.4	2351.6
15°	2200.7	2093.8	1936.6	1785.7	1710.3	1836.0	1729.1	1571.9	1377.0	1351.9	1345.6
17.5°	1571.9	1509.0	1395.9	1333.0	1245.0	1213.5	1100.3	861.4	723.1	685.4	697.9
20°	1068.9	1018.6	1012.3	955.7	918.0	892.9	710.5	553.3	509.3	515.6	521.9
22.5°	792.2	767.1	735.7	729.4	697.9	666.5	521.9	465.3	433.9	433.9	452.7
25°	647.6	635.1	603.6	591.0	578.5	534.5	440.1	396.1	383.5	371.0	389.8
27.5°	553.3	547.0	528.2	509.3	496.7	452.7	383.5	345.8	333.2	333.2	333.2
30°	496.7	496.7	471.6	433.9	433.9	383.5	327.0	301.8	289.2	289.2	282.9
32.5°	465.3	452.7	421.3	396.1	377.3	327.0	289.2	264.1	245.2	245.2	251.5
35°	377.3	377.3	371.0	352.1	327.0	276.7	245.2	220.1	207.5	201.2	207.5
37.5°	333.2	314.4	289.2	295.5	282.9	238.9	207.5	188.6	169.8	169.8	169.8
40°	301.8	282.9	257.8	238.9	232.6	213.8	182.3	150.9	132.0	125.8	125.8
42.5°	270.4	257.8	220.1	188.6	182.3	182.3	138.3	113.2	94.3	94.3	94.3
45°	251.5	232.6	201.2	163.5	132.0	138.3	113.2	81.7	69.2	62.9	62.9
47.5°	238.9	220.1	176.1	138.3	100.6	100.6	81.7	56.6	44.0	37.7	37.7
50°	220.1	201.2	157.2	113.2	75.5	62.9	50.3	31.4	18.9	12.6	12.6
52.5°	207.5	188.6	138.3	94.3	62.9	44.0	31.4	6.3	0.0	0.0	0.0
55°	188.6	163.5	119.5	75.5	50.3	25.2	6.3	0.0	0.0	0.0	0.0
57.5°	163.5	144.6	94.3	56.6	31.4	6.3	0.0	0.0	0.0	0.0	0.0
60°	138.3	119.5	75.5	44.0	12.6	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	113.2	100.6	56.6	25.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	94.3	75.5	44.0	6.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	81.7	62.9	31.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	62.9	44.0	18.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	44.0	31.4	6.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	31.4	18.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	18.9	6.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	6.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599303  
 CATALOG NUMBER: IFLD-L-SA7A-760-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9
2.5°	7997.9	8186.6	8362.6	8412.9	8551.3	8934.8	8934.8	9117.1	9444.1	9563.6	9588.7
5°	6746.7	6947.9	6985.6	7375.5	7557.8	7947.6	8205.4	8821.6	9192.6	9425.2	9569.9
7.5°	5130.8	5199.9	5344.5	5709.2	6067.6	6539.2	7029.6	7815.6	8469.5	8733.6	9224.0
10°	3527.4	3734.9	4049.3	4376.2	4935.8	5457.7	6092.8	6834.7	7639.5	7966.5	8387.8
12.5°	2376.7	2666.0	3169.0	3634.3	4149.9	4678.0	5281.7	6275.1	7186.8	7639.5	8060.8
15°	1389.6	1741.7	2175.5	2930.1	3615.4	4206.5	4810.1	5816.1	6922.7	7507.5	8023.1
17.5°	704.2	811.1	1169.5	1823.4	2728.9	3697.2	4596.3	5879.0	7123.9	7840.7	8268.3
20°	528.2	559.6	660.2	968.3	1867.4	3055.8	4395.1	5973.3	7683.6	8557.5	8790.2
22.5°	459.0	484.2	528.2	628.8	1050.0	2339.0	4112.1	6205.9	8444.4	9268.0	9758.5
25°	389.8	415.0	452.7	515.6	672.8	1590.8	3766.3	6451.2	9123.4	10160.9	10619.9
27.5°	339.5	358.4	396.1	446.4	547.0	1012.3	3169.0	6778.1	10160.9	11242.4	11361.8
30°	289.2	308.1	339.5	396.1	465.3	716.8	2326.4	6822.1	10733.1	11714.0	12047.2
32.5°	251.5	257.8	295.5	345.8	389.8	565.9	1634.8	6866.2	11154.4	12323.9	12393.0
35°	207.5	220.1	257.8	289.2	339.5	446.4	1238.7	6646.1	11701.4	12952.6	12933.8
37.5°	169.8	188.6	213.8	238.9	276.7	377.3	987.2	6237.4	12386.7	13927.2	13336.2
40°	132.0	150.9	176.1	207.5	232.6	339.5	741.9	5621.2	13103.5	14405.1	13776.3
42.5°	94.3	106.9	132.0	163.5	207.5	282.9	534.5	4891.8	13386.5	14964.7	14304.5
45°	69.2	81.7	100.6	138.3	213.8	226.4	371.0	4225.3	13688.3	15209.9	14185.0
47.5°	37.7	50.3	75.5	119.5	188.6	169.8	264.1	3628.0	14034.1	15430.0	14279.3
50°	12.6	18.9	44.0	125.8	150.9	132.0	207.5	3307.3	14373.6	15474.0	14468.0
52.5°	0.0	0.0	25.2	132.0	113.2	100.6	182.3	3181.6	14285.6	15612.3	14348.5
55°	0.0	0.0	6.3	56.6	62.9	75.5	150.9	3175.3	14908.1	15656.3	15002.4
57.5°	0.0	0.0	0.0	18.9	37.7	62.9	132.0	2974.1	15304.2	16750.4	15882.7
60°	0.0	0.0	0.0	6.3	25.2	44.0	100.6	2798.0	15706.6	17240.8	16825.8
62.5°	0.0	0.0	0.0	0.0	6.3	18.9	69.2	2527.6	14895.5	17203.1	17737.6
65°	0.0	0.0	0.0	0.0	0.0	0.0	44.0	1999.5	13399.1	16304.0	17234.5
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	25.2	1383.3	11732.8	15172.2	16310.3
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	836.3	9469.3	13304.7	13832.9
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	358.4	6759.3	10563.3	11349.3
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	144.6	4181.3	7721.3	8689.6
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	56.6	2710.0	5847.5	6595.8
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	12.6	1446.2	3665.7	4263.1
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	628.8	2225.8	2565.4
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	201.2	1351.9	1540.5
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	207.5	276.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P599303  
 CATALOG NUMBER: IFLD-L-SA7A-760-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9	8915.9
2.5°	9601.3	9783.6	9852.8	9745.9	9758.5	9538.4	9507.0	9198.9	9073.1	9098.3
5°	10041.4	10305.5	10450.1	10330.7	10060.3	9639.0	9255.5	8890.8	8664.4	8551.3
7.5°	9940.8	10236.4	10418.7	10531.9	10223.8	9544.7	8960.0	8274.6	7985.4	7991.6
10°	9387.5	10003.7	10374.7	10230.1	10085.4	9406.4	8500.9	7759.0	7501.2	7526.4
12.5°	8941.1	9626.4	9846.5	9959.7	9664.2	9123.4	8513.5	7664.7	7375.5	7199.4
15°	8664.4	9173.7	9186.3	9362.4	9242.9	9242.9	8645.6	7815.6	7564.1	7369.2
17.5°	8664.4	8777.6	8765.0	8827.9	9029.1	9268.0	8978.8	8425.5	7928.8	7897.3
20°	8859.3	8507.2	8425.5	8450.6	8620.4	9330.9	9714.5	9022.8	8708.4	8607.8
22.5°	9312.1	8538.7	8041.9	7953.9	8475.8	9324.6	10186.0	9966.0	9419.0	9337.2
25°	9934.5	8482.1	7941.3	7828.2	8224.3	9551.0	10833.7	10877.7	10381.0	10211.2
27.5°	10525.6	8733.6	7928.8	7903.6	8425.5	9500.7	11280.1	11607.1	11047.5	10909.1
30°	10726.8	8985.1	8161.4	7828.2	8500.9	9683.0	11267.5	12122.7	11758.0	11789.4
32.5°	10965.7	9236.6	8186.6	8054.5	8821.6	9978.6	11625.9	12952.6	12688.5	12317.6
35°	11317.8	9576.1	8425.5	8306.0	9048.0	10242.6	11701.4	13562.5	13518.5	13084.7
37.5°	11619.6	9909.4	8922.2	8941.1	9739.6	10670.2	12034.6	14310.8	14235.3	13939.8
40°	11833.4	10374.7	9695.6	9745.9	10343.2	11148.1	12625.7	14688.0	15247.6	14813.8
42.5°	11864.9	10789.7	10582.2	10984.6	11544.2	11890.0	12864.6	14945.8	15750.6	15467.7
45°	11984.3	11449.9	12028.3	12323.9	12782.9	12543.9	12852.0	15386.0	15788.4	15643.8
47.5°	12449.6	12650.8	13380.2	14279.3	14442.8	13656.9	13153.8	15455.1	16002.2	15983.3
50°	12933.8	13939.8	14964.7	15562.0	15769.5	14423.9	13436.8	15398.5	16285.1	16134.2
52.5°	13474.5	15059.0	16536.6	17272.3	17159.1	15272.8	13757.5	15857.5	16807.0	16756.7
55°	13814.0	15562.0	17548.9	18573.8	18485.8	16222.2	14776.1	16517.7	17492.3	17366.6
57.5°	14713.2	16379.4	18555.0	19032.8	19265.5	17467.2	15486.6	17599.2	18064.5	18202.8
60°	15455.1	16913.9	18819.0	19510.7	19592.4	18209.1	16731.5	18712.1	18793.9	18328.6
62.5°	16542.9	17121.4	18259.4	18881.9	19303.2	18630.4	17850.7	19309.5	18781.3	18749.9
65°	17341.4	16442.3	17215.7	17561.5	17831.9	17989.1	18976.2	19718.2	18548.7	17938.8
67.5°	16895.0	15159.6	15015.0	15033.9	15115.6	16065.0	18599.0	18718.4	17253.4	16750.4
70°	14870.4	12437.0	12242.1	12393.0	11984.3	13128.7	17071.1	17014.5	15222.5	14700.6
72.5°	12028.3	9066.8	8733.6	8941.1	9035.4	10248.9	14361.1	12902.3	11104.1	10695.4
75°	9557.3	6646.1	5608.6	6111.6	6432.3	7463.5	11217.2	8765.0	7752.7	7199.4
77.5°	7507.5	5030.1	4363.7	4162.4	4458.0	5426.3	8161.4	4602.6	4061.8	3804.0
80°	4759.8	3697.2	4011.5	3722.3	3848.1	3873.2	4250.5	2093.8	1666.2	1647.4
82.5°	2867.2	2527.6	3005.5	1653.7	3011.8	2691.1	1766.8	949.4	842.5	842.5
85°	2030.9	1565.6	1037.5	672.8	1339.3	1477.6	685.4	490.4	427.6	415.0
87.5°	1018.6	484.2	232.6	150.9	169.8	276.7	81.7	37.7	37.7	31.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)