

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599306

Luminaire Tested: **IFLD-L-SA7D-760-U-SLR-HSS**

Issue Date: 05/04/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

**Test Information**

Test Method: LM-79-08  
 Report Number: P599306  
 Test Lab: INNOVATION CENTER(G1)  
 Issue Date: 05/04/2022  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: IFLD-L-SA7D-760-U-SLR-HSS  
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLR distribution lens with House Side Shield  
 Light Source: (112) 5700K CCT, 70 CRI LEDS  
 Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
 Luminaire Lumens: 36345.1 lumens  
 Efficiency: N/A  
 Efficacy: 86.0 lumens/watt  
 Spacing Criteria (0/90/45): 0.44 / 0.52 / 0.65  
 Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')  
 CIE Type: Direct

Input Watts (W): 422.6  
 Input Voltage (V): 120  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599306  
CATALOG NUMBER: IFLD-L-SA7D-760-U-SLR-HSS

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - · - · 90°-270°    - · - · 135°-315°

TEST NUMBER: P599306  
 CATALOG NUMBER: IFLD-L-SA7D-760-U-SLR-HSS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	107	101	96	91	104	99	94	90	94	90	87	90	87	84	87	84	82	79
2	95	85	77	70	92	83	75	69	79	73	67	76	71	66	73	68	64	62
3	85	72	63	55	82	71	62	54	67	60	53	65	58	52	62	56	51	49
4	76	62	52	44	74	61	51	44	58	50	43	56	49	43	53	47	42	40
5	69	55	44	37	67	53	44	36	51	43	36	49	41	35	47	40	35	33
6	63	48	38	31	61	47	38	31	45	37	30	44	36	30	42	35	30	27
7	58	43	33	27	56	42	33	26	41	32	26	39	32	26	38	31	26	24
8	54	39	30	23	52	38	29	23	37	29	23	36	28	23	34	28	23	20
9	50	36	27	21	49	35	26	21	34	26	20	33	25	20	32	25	20	18
10	47	33	24	18	46	32	24	18	31	24	18	30	23	18	29	23	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	74781	74781	74781	74781
5°	71996	52621	56644	79354
10°	64100	28650	29024	67848
15°	63988	19109	11684	65189
20°	76830	9541	4658	76381
25°	94498	5994	3608	94033
30°	114178	4811	2740	113448
35°	133974	3863	2125	132622
40°	162194	3304	1377	157719
45°	185557	2984	746	180411
50°	210524	2872	164	201909
55°	253949	2759	0	228940
60°	307455	2321	0	289208
65°	356014	1872	0	323570
70°	360501	1542	0	326271
75°	233304	1019	0	250216
80°	79570	304	0	177056
85°	39934	0	0	130091

TEST NUMBER: P599306  
 CATALOG NUMBER: IFLD-L-SA7D-760-U-SLR-HSS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1052.5	2.9
10°-20°	2038.1	5.6
20°-30°	2838.6	7.8
30°-40°	4033.3	11.1
40°-50°	5593.0	15.4
50°-60°	7620.8	21.0
60°-70°	8378.5	23.1
70°-80°	4117.9	11.3
80°-90°	672.5	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5929.2	16.3
0°-40°	9962.5	27.4
0°-60°	23176.3	63.8
0°-90°	36345.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	36345.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	13895	13895	13895	13895	13895	
5°	13326	9740	10485	14688	13326	1219
15°	11484	3430	2097	11700	11484	3399
25°	15913	1009	608	15835	15913	7398
35°	20391	588	323	20186	20391	12944
45°	24379	392	98	23703	24379	18898
55°	27064	294	0	24399	27064	24346
65°	27956	147	0	25408	27956	27016
75°	11220	49	0	12033	11220	12232
85°	647	0	0	2107	647	895
90°	0	0	0	0	0	

TEST NUMBER: P599306  
 CATALOG NUMBER: IFLD-L-SA7D-760-U-SLR-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7
2.5°	14178.9	14345.4	14188.7	13639.9	13541.9	13277.4	12875.6	12846.2	12424.9	12473.9	12248.5
5°	13326.4	13492.9	13159.8	12434.7	11758.6	11219.6	10896.3	10318.1	10190.7	9906.6	9906.6
7.5°	12454.3	12444.5	11876.1	11268.6	10259.3	9269.7	8818.9	7986.0	7496.1	7231.5	6976.7
10°	11729.2	11572.4	11219.6	9965.4	8867.9	7839.0	7280.5	6731.8	6222.2	5781.3	5340.3
12.5°	11219.6	11317.6	10759.1	9397.0	7976.2	7260.9	6663.2	6085.1	5477.5	4977.8	4487.8
15°	11484.2	11327.4	10670.9	9269.7	7829.2	6849.4	6055.7	5350.1	4674.0	4017.5	3645.2
17.5°	12307.3	11905.5	11131.4	9269.7	7525.5	6222.2	5262.0	4429.1	3703.9	3116.0	2655.5
20°	13414.6	12954.0	12121.1	9612.6	7300.1	5761.7	4448.7	3400.2	2645.7	2096.9	1744.2
22.5°	14551.2	14188.7	12934.4	9749.8	7035.5	5144.4	3508.0	2459.5	1763.8	1411.0	1234.6
25°	15913.2	15403.7	14031.9	10298.5	6643.6	4546.6	2763.3	1714.8	1313.0	1126.9	1019.1
27.5°	17000.9	16912.7	15060.7	10631.7	6349.6	4056.7	2185.1	1362.0	1087.7	950.5	881.9
30°	18372.7	17892.6	16315.0	11298.0	6016.5	3498.2	1822.6	1224.8	999.5	852.5	803.5
32.5°	19195.8	18970.5	16971.5	11670.4	5644.1	3037.6	1567.8	1077.9	911.3	803.5	754.5
35°	20391.3	19940.5	17912.2	11905.5	5448.1	2773.1	1411.0	979.9	764.3	656.5	597.7
37.5°	21723.9	21557.3	19039.1	11895.7	5164.0	2616.3	1303.2	911.3	725.1	607.5	538.9
40°	23086.0	22409.8	19725.0	12170.1	5017.0	2498.7	1224.8	872.1	685.9	578.1	489.9
42.5°	24105.0	23330.9	20518.7	12072.1	4840.6	2292.9	1195.5	813.3	656.5	529.1	450.7
45°	24379.4	24105.0	21234.0	12042.7	4713.2	2126.3	1146.5	803.5	636.9	499.7	421.3
47.5°	24908.5	24722.4	22115.9	12091.7	4615.2	1999.0	1028.9	823.1	607.5	470.3	401.8
50°	25143.7	24810.5	22831.2	12209.3	4389.9	1842.2	921.1	862.3	597.7	460.5	382.2
52.5°	26113.8	25819.8	23811.1	12542.5	4203.7	1636.4	813.3	823.1	617.3	431.1	362.6
55°	27064.3	26731.1	25320.1	13306.8	3939.1	1469.8	695.7	725.1	587.9	392.0	323.4
57.5°	28367.5	27818.8	26329.4	13620.3	3703.9	1244.4	617.3	597.7	548.7	352.8	284.2
60°	28563.5	28788.9	26182.4	13424.3	3459.0	1097.5	538.9	460.5	587.9	313.6	245.0
62.5°	29220.0	28279.3	25496.5	12973.6	3282.6	1009.3	480.1	382.2	509.5	274.4	205.8
65°	27956.0	27260.2	23889.5	11523.4	3057.2	1019.1	421.3	313.6	323.4	225.4	166.6
67.5°	26104.0	25555.3	21224.2	9945.8	2831.9	999.5	372.4	274.4	245.0	196.0	147.0
70°	22909.6	21723.9	18029.8	8074.2	2498.7	930.9	313.6	245.0	205.8	156.8	107.8
72.5°	16667.8	16187.6	12934.4	6241.8	2243.9	842.7	294.0	205.8	176.4	117.6	88.2
75°	11219.6	10425.9	8162.4	4095.9	1803.0	734.9	245.0	186.2	137.2	88.2	68.6
77.5°	5928.3	5604.9	4625.0	1950.0	999.5	343.0	137.2	107.8	78.4	68.6	39.2
80°	2567.3	2283.1	1999.0	793.7	352.8	156.8	88.2	58.8	49.0	39.2	19.6
82.5°	1313.0	1254.2	1038.7	343.0	205.8	117.6	49.0	39.2	29.4	19.6	9.8
85°	646.7	666.3	548.7	107.8	117.6	68.6	9.8	9.8	0.0	0.0	0.0
87.5°	49.0	49.0	39.2	19.6	29.4	9.8	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599306  
 CATALOG NUMBER: IFLD-L-SA7D-760-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7
2.5°	12160.3	12297.5	12062.3	12209.3	12140.7	12170.1	12199.5	12121.1	12140.7	12415.1	12424.9
5°	9740.0	10004.6	9906.6	10043.8	10278.9	10161.4	10269.1	10249.5	10269.1	10308.3	10484.7
7.5°	6947.3	6869.0	7055.1	7417.7	7839.0	8093.8	7966.4	7897.8	7858.6	7760.6	7878.2
10°	5242.4	5203.2	5154.2	5262.0	5536.3	5820.5	5977.3	5712.7	5565.7	5379.5	5310.9
12.5°	4350.7	4105.7	3968.5	3801.9	3880.3	4135.1	4144.9	3890.1	3655.0	3557.0	3664.7
15°	3429.6	3263.0	3018.0	2782.9	2665.3	2861.2	2694.7	2449.7	2145.9	2106.7	2096.9
17.5°	2449.7	2351.7	2175.3	2077.3	1940.2	1891.2	1714.8	1342.4	1126.9	1068.1	1087.7
20°	1665.8	1587.4	1577.6	1489.4	1430.6	1391.4	1107.3	862.3	793.7	803.5	813.3
22.5°	1234.6	1195.5	1146.5	1136.7	1087.7	1038.7	813.3	725.1	676.1	676.1	705.5
25°	1009.3	989.7	940.7	921.1	901.5	832.9	685.9	617.3	597.7	578.1	607.5
27.5°	862.3	852.5	823.1	793.7	774.1	705.5	597.7	538.9	519.3	519.3	519.3
30°	774.1	774.1	734.9	676.1	676.1	597.7	509.5	470.3	450.7	450.7	440.9
32.5°	725.1	705.5	656.5	617.3	587.9	509.5	450.7	411.5	382.2	382.2	392.0
35°	587.9	587.9	578.1	548.7	509.5	431.1	382.2	343.0	323.4	313.6	323.4
37.5°	519.3	489.9	450.7	460.5	440.9	372.4	323.4	294.0	264.6	264.6	264.6
40°	470.3	440.9	401.8	372.4	362.6	333.2	284.2	235.2	205.8	196.0	196.0
42.5°	421.3	401.8	343.0	294.0	284.2	284.2	215.6	176.4	147.0	147.0	147.0
45°	392.0	362.6	313.6	254.8	205.8	215.6	176.4	127.4	107.8	98.0	98.0
47.5°	372.4	343.0	274.4	215.6	156.8	156.8	127.4	88.2	68.6	58.8	58.8
50°	343.0	313.6	245.0	176.4	117.6	98.0	78.4	49.0	29.4	19.6	19.6
52.5°	323.4	294.0	215.6	147.0	98.0	68.6	49.0	9.8	0.0	0.0	0.0
55°	294.0	254.8	186.2	117.6	78.4	39.2	9.8	0.0	0.0	0.0	0.0
57.5°	254.8	225.4	147.0	88.2	49.0	9.8	0.0	0.0	0.0	0.0	0.0
60°	215.6	186.2	117.6	68.6	19.6	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	176.4	156.8	88.2	39.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	147.0	117.6	68.6	9.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	127.4	98.0	49.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	98.0	68.6	29.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	68.6	49.0	9.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	49.0	29.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	29.4	9.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	9.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599306  
 CATALOG NUMBER: IFLD-L-SA7D-760-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7
2.5°	12464.1	12758.0	13032.4	13110.8	13326.4	13924.1	13924.1	14208.3	14717.8	14904.0	14943.2
5°	10514.1	10827.7	10886.5	11494.0	11778.2	12385.7	12787.4	13747.7	14325.8	14688.4	14913.8
7.5°	7995.8	8103.6	8329.0	8897.3	9455.8	10190.7	10955.1	12179.9	13199.0	13610.5	14374.8
10°	5497.1	5820.5	6310.4	6820.0	7692.1	8505.4	9495.0	10651.3	11905.5	12415.1	13071.6
12.5°	3703.9	4154.7	4938.6	5663.7	6467.2	7290.3	8231.0	9779.2	11200.0	11905.5	12562.1
15°	2165.5	2714.3	3390.4	4566.2	5634.3	6555.4	7496.1	9063.9	10788.5	11699.8	12503.3
17.5°	1097.5	1264.0	1822.6	2841.7	4252.7	5761.7	7162.9	9161.9	11102.0	12219.1	12885.4
20°	823.1	872.1	1028.9	1509.0	2910.2	4762.2	6849.4	9308.9	11974.1	13336.2	13698.7
22.5°	715.3	754.5	823.1	979.9	1636.4	3645.2	6408.4	9671.4	13159.8	14443.4	15207.7
25°	607.5	646.7	705.5	803.5	1048.5	2479.1	5869.5	10053.6	14218.1	15834.9	16550.2
27.5°	529.1	558.5	617.3	695.7	852.5	1577.6	4938.6	10563.1	15834.9	17520.2	17706.4
30°	450.7	480.1	529.1	617.3	725.1	1117.1	3625.6	10631.7	16726.5	18255.2	18774.5
32.5°	392.0	401.8	460.5	538.9	607.5	881.9	2547.7	10700.3	17383.1	19205.6	19313.4
35°	323.4	343.0	401.8	450.7	529.1	695.7	1930.4	10357.3	18235.6	20185.5	20156.1
37.5°	264.6	294.0	333.2	372.4	431.1	587.9	1538.4	9720.4	19303.6	21704.3	20783.2
40°	205.8	235.2	274.4	323.4	362.6	529.1	1156.3	8760.1	20420.7	22449.0	21469.2
42.5°	147.0	166.6	205.8	254.8	323.4	440.9	832.9	7623.5	20861.6	23321.1	22292.3
45°	107.8	127.4	156.8	215.6	333.2	352.8	578.1	6584.8	21332.0	23703.3	22106.1
47.5°	58.8	78.4	117.6	186.2	294.0	264.6	411.5	5653.9	21870.9	24046.2	22253.1
50°	19.6	29.4	68.6	196.0	235.2	205.8	323.4	5154.2	22400.0	24114.8	22547.0
52.5°	0.0	0.0	39.2	205.8	176.4	156.8	284.2	4958.2	22262.9	24330.4	22360.9
55°	0.0	0.0	9.8	88.2	98.0	117.6	235.2	4948.4	23232.9	24399.0	23379.9
57.5°	0.0	0.0	0.0	29.4	58.8	98.0	205.8	4634.8	23850.3	26104.0	24751.8
60°	0.0	0.0	0.0	9.8	39.2	68.6	156.8	4360.5	24477.4	26868.3	26221.6
62.5°	0.0	0.0	0.0	0.0	9.8	29.4	107.8	3939.1	23213.3	26809.5	27642.4
65°	0.0	0.0	0.0	0.0	0.0	0.0	68.6	3116.0	20881.2	25408.3	26858.5
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	39.2	2155.7	18284.6	23644.5	25418.1
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1303.2	14757.0	20734.3	21557.3
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	558.5	10533.7	16462.0	17686.8
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	225.4	6516.2	12032.9	13541.9
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	88.2	4223.3	9112.9	10278.9
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	19.6	2253.7	5712.7	6643.6
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	979.9	3468.8	3997.9
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	313.6	2106.7	2400.7
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	323.4	431.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P599306  
 CATALOG NUMBER: IFLD-L-SA7D-760-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7	13894.7
2.5°	14962.8	15246.9	15354.7	15188.1	15207.7	14864.8	14815.8	14335.6	14139.7	14178.9
5°	15648.7	16060.2	16285.6	16099.4	15678.1	15021.6	14423.8	13855.5	13502.7	13326.4
7.5°	15491.9	15952.4	16236.6	16413.0	15932.8	14874.6	13963.3	12895.2	12444.5	12454.3
10°	14629.6	15589.9	16168.0	15942.6	15717.3	14659.0	13248.0	12091.7	11690.0	11729.2
12.5°	13933.9	15002.0	15344.9	15521.3	15060.7	14218.1	13267.6	11944.7	11494.0	11219.6
15°	13502.7	14296.4	14316.0	14590.4	14404.2	14404.2	13473.3	12179.9	11788.0	11484.2
17.5°	13502.7	13679.1	13659.5	13757.5	14071.1	14443.4	13992.7	13130.4	12356.3	12307.3
20°	13806.5	13257.8	13130.4	13169.6	13434.1	14541.4	15139.1	14061.3	13571.3	13414.6
22.5°	14512.0	13306.8	12532.7	12395.5	13208.8	14531.6	15874.0	15531.1	14678.6	14551.2
25°	15482.1	13218.6	12375.9	12199.5	12816.8	14884.4	16883.3	16951.9	16177.8	15913.2
27.5°	16403.2	13610.5	12356.3	12317.1	13130.4	14806.0	17579.0	18088.6	17216.5	17000.9
30°	16716.7	14002.5	12718.8	12199.5	13248.0	15090.1	17559.4	18892.1	18323.7	18372.7
32.5°	17089.1	14394.4	12758.0	12552.3	13747.7	15550.7	18118.0	20185.5	19774.0	19195.8
35°	17637.8	14923.6	13130.4	12944.2	14100.5	15962.2	18235.6	21136.0	21067.4	20391.3
37.5°	18108.2	15442.9	13904.5	13933.9	15178.3	16628.6	18754.9	22302.1	22184.5	21723.9
40°	18441.3	16168.0	15109.7	15188.1	16119.0	17373.3	19676.0	22890.0	23762.1	23086.0
42.5°	18490.3	16814.7	16491.4	17118.5	17990.6	18529.5	20048.3	23291.7	24546.0	24105.0
45°	18676.5	17843.6	18745.1	19205.6	19921.0	19548.6	20028.7	23977.7	24604.8	24379.4
47.5°	19401.6	19715.2	20851.8	22253.1	22507.8	21283.0	20499.1	24085.4	24937.9	24908.5
50°	20156.1	21723.9	23321.1	24252.0	24575.4	22478.4	20940.0	23997.2	25378.9	25143.7
52.5°	20998.8	23468.1	25770.8	26917.3	26740.9	23801.3	21439.8	24712.6	26192.2	26113.8
55°	21528.0	24252.0	27348.4	28945.6	28808.5	25280.9	23027.2	25741.4	27260.2	27064.3
57.5°	22929.2	25525.9	28916.2	29661.0	30023.5	27221.1	24134.4	27426.8	28151.9	28367.5
60°	24085.4	26358.8	29327.8	30405.7	30533.0	28377.3	26074.6	29161.2	29288.6	28563.5
62.5°	25780.6	26682.1	28455.7	29425.8	30082.3	29033.8	27818.8	30092.1	29269.0	29220.0
65°	27025.1	25623.8	26829.1	27368.0	27789.4	28034.4	29572.8	30729.0	28906.4	27956.0
67.5°	26329.4	23624.9	23399.5	23428.9	23556.3	25035.9	28984.8	29171.0	26887.9	26104.0
70°	23174.2	19382.0	19078.3	19313.4	18676.5	20459.9	26603.7	26515.5	23722.9	22909.6
72.5°	18745.1	14129.9	13610.5	13933.9	14080.9	15972.0	22380.4	20107.1	17304.7	16667.8
75°	14894.2	10357.3	8740.5	9524.4	10024.2	11631.2	17481.1	13659.5	12081.9	11219.6
77.5°	11699.8	7839.0	6800.4	6486.8	6947.3	8456.4	12718.8	7172.7	6330.0	5928.3
80°	7417.7	5761.7	6251.6	5800.9	5996.9	6036.1	6624.0	3263.0	2596.7	2567.3
82.5°	4468.3	3939.1	4683.8	2577.1	4693.6	4193.9	2753.5	1479.6	1313.0	1313.0
85°	3165.0	2439.9	1616.8	1048.5	2087.1	2302.7	1068.1	764.3	666.3	646.7
87.5°	1587.4	754.5	362.6	235.2	264.6	431.1	127.4	58.8	58.8	49.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)