

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P951562

Luminaire Tested: **GLAN-SB5C-935-U-SLR**

Issue Date: 1/21/2025

### Test Information

Test Method: LM-79-08  
Report Number: P951562  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SB5C-935-U-SLR  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(5) 90 CRI, 3500K, 615mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT  
ELIMINATOR RIGHT OPTICS  
Light Source: -  
Ballast/Driver: -

### Summary

Lumens per Lamp: N/A  
Luminaire Lumens: 26223 lumens  
Efficiency: N/A  
Efficacy: 105.1 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B3 - U0 - G5

Input Watts (W): 249.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P951562

CATALOG NUMBER: GLAN-SB5C-935-U-SLR


## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
- - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 7.1 fc  
Type IV - Short - N/A

REPORT NUMBER: P951562  
CATALOG NUMBER: GLAN-SB5C-935-U-SLR



REPORT NUMBER: P951562

CATALOG NUMBER: GLAN-SB5C-935-U-SLR

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 6664.6   | 0.0    | 6664.6  |
|                    | % Fixture | 25.4     | 0.0    | 25.4    |
| <b>Street Side</b> | Lumens    | 19558.4  | 0.0    | 19558.4 |
|                    | % Fixture | 74.6     | 0.0    | 74.6    |
| <b>Total</b>       | Lumens    | 26223.0  | 0.0    | 26223.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 357.7   | 1.4       |
| 10°-20°   | 1122.9  | 4.3       |
| 20°-30°   | 1734.5  | 6.6       |
| 30°-40°   | 2198.0  | 8.4       |
| 40°-50°   | 3315.2  | 12.6      |
| 50°-60°   | 5356.2  | 20.4      |
| 60°-70°   | 6677.3  | 25.5      |
| 70°-80°   | 4378.7  | 16.7      |
| 80°-90°   | 1082.5  | 4.1       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 26223.0 | 100.0     |
| 0°-180°   | 26223.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P951562


CATALOG NUMBER: GLAN-SB5C-935-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |          |
|------|-------------|--------|-----------|-------------------------|------|----------|
|      |             |        |           | B                       | U    | G        |
| FL   | (0°-30°)    | 1763.8 | 6.7       |                         |      |          |
| FM   | (30°-60°)   | 7648.7 | 29.2      |                         |      |          |
| FH   | (60°-80°)   | 9254.2 | 35.3      |                         |      | G4/12000 |
| FVH  | (80°-90°)   | 891.8  | 3.4       |                         |      | G5       |
| BL   | (0°-30°)    | 1451.3 | 5.5       | B3/2500                 |      |          |
| BM   | (30°-60°)   | 3220.7 | 12.3      | B3/5000                 |      |          |
| BH   | (60°-80°)   | 1801.8 | 6.9       | B3/2500                 |      | G3/2500  |
| BVH  | (80°-90°)   | 190.8  | 0.7       |                         |      | G2/225   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |          |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |          |

**BUG Rating: B3-U0-G5**

Type IV Short



REPORT NUMBER: P951562

CATALOG NUMBER: GLAN-SB5C-935-U-SLR

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 10°    | 15°    | 20°    | 25°    | 30°    | 35°    | 40°    | 45°    |
|-------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 3605.9  | 3605.9  | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 |
| 2.5°  | 3877.8  | 3848.0  | 3818.3 | 3786.6 | 3755.0 | 3723.2 | 3691.4 | 3661.0 | 3630.5 | 3601.0 |
| 5°    | 4169.7  | 4104.0  | 4038.3 | 3972.7 | 3907.3 | 3841.3 | 3775.4 | 3713.8 | 3652.2 | 3594.1 |
| 7.5°  | 4463.1  | 4354.6  | 4246.3 | 4146.1 | 4045.9 | 3948.4 | 3850.8 | 3764.9 | 3678.9 | 3599.7 |
| 10°   | 4687.9  | 4550.8  | 4413.7 | 4281.3 | 4149.0 | 4030.5 | 3912.0 | 3810.4 | 3708.6 | 3610.7 |
| 12.5° | 4825.6  | 4674.9  | 4524.4 | 4374.4 | 4224.4 | 4084.6 | 3944.9 | 3829.9 | 3714.9 | 3612.1 |
| 15°   | 4909.3  | 4752.3  | 4595.2 | 4432.5 | 4269.8 | 4108.9 | 3947.9 | 3814.8 | 3681.7 | 3567.8 |
| 17.5° | 4956.4  | 4797.1  | 4637.8 | 4460.3 | 4282.8 | 4096.0 | 3909.2 | 3749.1 | 3589.0 | 3455.1 |
| 20°   | 5008.3  | 4842.8  | 4677.1 | 4482.0 | 4286.9 | 4060.6 | 3834.2 | 3635.8 | 3437.4 | 3281.4 |
| 22.5° | 5068.4  | 4899.4  | 4730.1 | 4511.4 | 4292.5 | 4017.1 | 3741.8 | 3502.8 | 3263.8 | 3086.3 |
| 25°   | 5145.9  | 4980.2  | 4814.5 | 4564.5 | 4314.3 | 3974.2 | 3634.3 | 3354.3 | 3074.6 | 2892.6 |
| 27.5° | 5251.1  | 5093.1  | 4934.9 | 4647.5 | 4360.0 | 3945.6 | 3531.2 | 3218.6 | 2906.0 | 2740.4 |
| 30°   | 5392.9  | 5240.2  | 5087.5 | 4755.0 | 4422.5 | 3932.2 | 3441.5 | 3105.1 | 2768.8 | 2629.7 |
| 32.5° | 5560.3  | 5409.1  | 5258.0 | 4867.3 | 4476.5 | 3915.6 | 3354.3 | 3007.3 | 2660.1 | 2548.1 |
| 35°   | 5763.7  | 5619.0  | 5474.1 | 4995.1 | 4516.1 | 3884.3 | 3252.8 | 2911.1 | 2569.5 | 2476.1 |
| 37.5° | 6106.2  | 5921.6  | 5737.0 | 5138.3 | 4539.6 | 3830.7 | 3121.9 | 2798.0 | 2474.0 | 2392.4 |
| 40°   | 6623.7  | 6354.7  | 6085.7 | 5320.1 | 4554.4 | 3757.0 | 2959.7 | 2662.9 | 2366.1 | 2292.1 |
| 42.5° | 7310.0  | 6921.8  | 6533.5 | 5558.0 | 4582.5 | 3680.9 | 2779.6 | 2513.9 | 2248.2 | 2180.0 |
| 45°   | 8157.5  | 7633.8  | 7110.1 | 5871.0 | 4631.9 | 3610.2 | 2588.6 | 2355.6 | 2122.6 | 2053.4 |
| 47.5° | 9217.4  | 8480.3  | 7743.1 | 6204.5 | 4665.8 | 3551.8 | 2437.8 | 2230.4 | 2023.0 | 1933.7 |
| 50°   | 10606.7 | 9495.4  | 8384.0 | 6513.8 | 4643.7 | 3488.1 | 2332.6 | 2147.2 | 1961.8 | 1844.5 |
| 52.5° | 12201.4 | 10561.7 | 8922.0 | 6714.8 | 4507.4 | 3380.6 | 2254.0 | 2092.4 | 1930.9 | 1796.0 |
| 55°   | 13899.1 | 11507.0 | 9115.0 | 6670.5 | 4225.8 | 3202.4 | 2179.0 | 2052.7 | 1926.4 | 1800.9 |
| 57.5° | 15443.3 | 12177.0 | 8910.7 | 6358.9 | 3807.2 | 2951.1 | 2094.9 | 2005.7 | 1916.4 | 1805.7 |
| 60°   | 16376.6 | 12344.4 | 8312.1 | 5779.0 | 3245.9 | 2624.9 | 2003.9 | 1933.7 | 1863.5 | 1790.5 |
| 62.5° | 15902.7 | 11639.4 | 7376.2 | 4994.8 | 2613.5 | 2234.4 | 1855.2 | 1808.6 | 1762.1 | 1753.1 |
| 65°   | 14954.2 | 10641.9 | 6329.7 | 4194.8 | 2060.0 | 1883.1 | 1706.1 | 1684.1 | 1662.1 | 1663.2 |
| 67.5° | 13683.3 | 9454.9  | 5226.5 | 3411.1 | 1595.7 | 1545.4 | 1495.1 | 1507.4 | 1519.6 | 1516.5 |
| 70°   | 12156.4 | 8159.6  | 4162.8 | 2685.7 | 1208.7 | 1223.0 | 1237.3 | 1294.3 | 1351.2 | 1351.2 |
| 72.5° | 10336.8 | 6755.4  | 3174.2 | 2053.3 | 932.3  | 975.6  | 1019.1 | 1099.9 | 1180.6 | 1194.1 |
| 75°   | 8035.1  | 5145.8  | 2256.5 | 1490.2 | 723.9  | 763.2  | 802.5  | 893.0  | 983.5  | 1046.1 |
| 77.5° | 5740.9  | 3601.6  | 1462.3 | 1009.8 | 557.3  | 584.1  | 610.9  | 698.8  | 786.6  | 889.7  |
| 80°   | 3757.4  | 2320.4  | 883.5  | 650.6  | 417.9  | 428.9  | 440.0  | 514.5  | 588.8  | 711.9  |
| 82.5° | 2184.1  | 1343.0  | 502.0  | 400.2  | 298.6  | 300.5  | 302.8  | 357.5  | 412.3  | 517.5  |
| 85°   | 961.0   | 604.1   | 247.4  | 213.9  | 180.6  | 179.6  | 178.5  | 218.6  | 258.7  | 336.9  |
| 87.5° | 297.5   | 197.9   | 98.2   | 88.7   | 79.1   | 78.2   | 77.2   | 93.5   | 110.0  | 142.5  |
| 90°   | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P951562

CATALOG NUMBER: GLAN-SB5C-935-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 50°    |       | 55°    | 60°    | 65°    | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    | 100°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 3605.9 | 0°    | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 |
| 3568.3 | 2.5°  | 3541.7 | 3515.3 | 3491.3 | 3467.5 | 3446.6 | 3425.7 | 3404.7 | 3383.8 | 3367.6 | 3351.3 |
| 3536.7 | 5°    | 3486.6 | 3436.4 | 3394.3 | 3352.4 | 3315.3 | 3278.2 | 3244.6 | 3210.8 | 3185.0 | 3159.0 |
| 3525.4 | 7.5°  | 3458.7 | 3392.1 | 3336.8 | 3281.4 | 3234.8 | 3188.0 | 3146.8 | 3105.7 | 3074.8 | 3044.1 |
| 3530.9 | 10°   | 3460.6 | 3390.3 | 3335.0 | 3279.6 | 3229.4 | 3179.0 | 3132.7 | 3086.3 | 3049.5 | 3012.6 |
| 3537.8 | 12.5° | 3480.2 | 3423.0 | 3386.2 | 3349.6 | 3310.1 | 3270.8 | 3222.7 | 3174.9 | 3127.8 | 3080.8 |
| 3508.3 | 15°   | 3480.8 | 3453.4 | 3458.4 | 3463.4 | 3453.1 | 3442.9 | 3401.2 | 3359.6 | 3292.6 | 3225.7 |
| 3418.4 | 17.5° | 3428.5 | 3438.5 | 3498.8 | 3559.1 | 3591.2 | 3623.2 | 3589.6 | 3556.1 | 3467.4 | 3378.7 |
| 3271.7 | 20°   | 3318.8 | 3365.8 | 3470.6 | 3575.4 | 3642.6 | 3709.7 | 3694.2 | 3678.5 | 3577.1 | 3475.8 |
| 3105.3 | 22.5° | 3174.9 | 3244.5 | 3364.0 | 3483.8 | 3571.2 | 3658.5 | 3667.9 | 3677.1 | 3580.3 | 3483.4 |
| 2943.8 | 25°   | 3024.0 | 3104.3 | 3211.8 | 3319.5 | 3405.4 | 3491.3 | 3523.4 | 3555.4 | 3476.0 | 3396.7 |
| 2802.7 | 27.5° | 2880.1 | 2957.6 | 3046.0 | 3134.3 | 3203.2 | 3272.1 | 3307.8 | 3343.7 | 3287.1 | 3230.6 |
| 2678.5 | 30°   | 2740.0 | 2801.7 | 2875.0 | 2948.4 | 3005.5 | 3062.8 | 3091.8 | 3120.9 | 3077.9 | 3034.7 |
| 2569.8 | 32.5° | 2606.2 | 2642.6 | 2701.1 | 2759.8 | 2814.6 | 2869.5 | 2901.7 | 2934.1 | 2894.5 | 2854.8 |
| 2467.1 | 35°   | 2477.1 | 2487.2 | 2531.9 | 2576.4 | 2630.7 | 2685.0 | 2723.8 | 2762.5 | 2734.3 | 2706.2 |
| 2359.5 | 37.5° | 2348.4 | 2337.3 | 2369.4 | 2401.4 | 2455.5 | 2509.7 | 2557.6 | 2605.5 | 2592.5 | 2579.5 |
| 2241.6 | 40°   | 2216.5 | 2191.5 | 2214.6 | 2237.7 | 2290.0 | 2342.3 | 2397.4 | 2452.6 | 2455.8 | 2458.8 |
| 2116.3 | 42.5° | 2083.1 | 2049.9 | 2068.8 | 2087.7 | 2137.2 | 2186.9 | 2246.4 | 2305.9 | 2321.8 | 2337.7 |
| 1991.8 | 45°   | 1959.4 | 1927.2 | 1943.0 | 1959.0 | 2006.1 | 2053.1 | 2114.8 | 2176.5 | 2199.4 | 2222.2 |
| 1880.7 | 47.5° | 1853.6 | 1826.5 | 1841.4 | 1856.2 | 1902.3 | 1948.2 | 2009.1 | 2070.0 | 2096.3 | 2122.6 |
| 1782.9 | 50°   | 1758.8 | 1734.9 | 1758.1 | 1781.5 | 1824.9 | 1868.3 | 1922.8 | 1977.3 | 2011.1 | 2044.8 |
| 1710.0 | 52.5° | 1686.2 | 1662.5 | 1697.5 | 1732.4 | 1772.2 | 1811.9 | 1862.7 | 1913.6 | 1953.6 | 1993.6 |
| 1671.2 | 55°   | 1633.6 | 1596.1 | 1645.8 | 1695.3 | 1738.2 | 1781.1 | 1825.6 | 1870.1 | 1912.4 | 1954.9 |
| 1648.0 | 57.5° | 1593.2 | 1538.4 | 1591.8 | 1645.2 | 1695.6 | 1745.9 | 1789.9 | 1834.1 | 1876.8 | 1919.5 |
| 1626.1 | 60°   | 1555.1 | 1484.0 | 1530.9 | 1577.7 | 1635.5 | 1693.4 | 1738.0 | 1782.9 | 1825.8 | 1868.7 |
| 1600.6 | 62.5° | 1511.8 | 1423.1 | 1452.9 | 1482.6 | 1550.0 | 1617.5 | 1665.3 | 1713.0 | 1752.3 | 1791.6 |
| 1547.0 | 65°   | 1452.6 | 1358.1 | 1369.6 | 1380.9 | 1453.1 | 1525.5 | 1571.2 | 1616.8 | 1651.4 | 1686.0 |
| 1451.2 | 67.5° | 1372.6 | 1294.0 | 1290.4 | 1286.8 | 1353.5 | 1420.4 | 1463.7 | 1506.8 | 1536.7 | 1566.6 |
| 1329.7 | 70°   | 1273.8 | 1217.9 | 1205.5 | 1193.0 | 1251.7 | 1310.4 | 1347.7 | 1385.1 | 1412.1 | 1439.0 |
| 1194.4 | 72.5° | 1156.1 | 1117.7 | 1099.5 | 1081.4 | 1127.6 | 1173.6 | 1207.4 | 1241.2 | 1267.6 | 1294.0 |
| 1040.8 | 75°   | 1011.3 | 981.7  | 964.3  | 946.7  | 981.0  | 1015.3 | 1045.9 | 1076.5 | 1100.6 | 1124.7 |
| 886.9  | 77.5° | 863.3  | 839.6  | 821.9  | 804.2  | 832.1  | 860.0  | 886.3  | 912.5  | 937.9  | 963.0  |
| 711.5  | 80°   | 691.7  | 671.8  | 657.0  | 642.0  | 665.3  | 688.4  | 710.5  | 732.7  | 751.9  | 771.0  |
| 523.3  | 82.5° | 513.6  | 503.9  | 493.4  | 482.9  | 481.0  | 479.0  | 471.3  | 463.5  | 504.5  | 545.4  |
| 344.5  | 85°   | 334.2  | 323.8  | 312.0  | 300.3  | 290.3  | 280.2  | 258.7  | 237.3  | 275.6  | 314.1  |
| 152.2  | 87.5° | 148.1  | 143.9  | 141.7  | 139.5  | 139.1  | 138.6  | 122.3  | 105.9  | 121.9  | 138.1  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P951562

CATALOG NUMBER: GLAN-SB5C-935-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 105°   |       | 110°   | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   | 150°   | 155°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 3605.9 | 0°    | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 |
| 3338.1 | 2.5°  | 3325.0 | 3314.8 | 3304.5 | 3295.1 | 3285.6 | 3273.8 | 3285.6 | 3295.1 | 3304.5 | 3314.8 |
| 3140.8 | 5°    | 3122.7 | 3109.8 | 3097.0 | 3087.1 | 3077.3 | 3067.6 | 3077.3 | 3087.1 | 3097.0 | 3109.8 |
| 3022.5 | 7.5°  | 3000.9 | 2986.1 | 2971.5 | 2962.6 | 2953.9 | 2947.3 | 2953.9 | 2962.6 | 2971.5 | 2986.1 |
| 2988.5 | 10°   | 2964.1 | 2950.2 | 2936.2 | 2928.7 | 2921.2 | 2918.2 | 2921.2 | 2928.7 | 2936.2 | 2950.2 |
| 3049.6 | 12.5° | 3018.5 | 3002.9 | 2987.4 | 2981.0 | 2974.7 | 2973.5 | 2974.7 | 2981.0 | 2987.4 | 3002.9 |
| 3178.3 | 15°   | 3131.0 | 3109.3 | 3087.7 | 3079.4 | 3071.1 | 3070.4 | 3071.1 | 3079.4 | 3087.7 | 3109.3 |
| 3308.9 | 17.5° | 3239.2 | 3207.1 | 3174.9 | 3164.4 | 3153.7 | 3152.0 | 3153.7 | 3164.4 | 3174.9 | 3207.1 |
| 3390.3 | 20°   | 3304.9 | 3263.8 | 3222.6 | 3209.5 | 3196.3 | 3192.2 | 3196.3 | 3209.5 | 3222.6 | 3263.8 |
| 3395.4 | 22.5° | 3307.3 | 3264.0 | 3220.5 | 3206.0 | 3191.5 | 3185.2 | 3191.5 | 3206.0 | 3220.5 | 3264.0 |
| 3318.4 | 25°   | 3240.3 | 3202.7 | 3165.2 | 3151.5 | 3137.9 | 3129.9 | 3137.9 | 3151.5 | 3165.2 | 3202.7 |
| 3169.9 | 27.5° | 3109.1 | 3084.0 | 3058.6 | 3052.4 | 3046.2 | 3044.1 | 3046.2 | 3052.4 | 3058.6 | 3084.0 |
| 2991.3 | 30°   | 2947.5 | 2934.7 | 2921.7 | 2921.7 | 2921.7 | 2923.7 | 2921.7 | 2921.7 | 2921.7 | 2934.7 |
| 2820.1 | 32.5° | 2785.4 | 2776.9 | 2768.5 | 2769.6 | 2770.8 | 2772.9 | 2770.8 | 2769.6 | 2768.5 | 2776.9 |
| 2674.1 | 35°   | 2642.2 | 2629.3 | 2616.6 | 2613.8 | 2611.0 | 2609.6 | 2611.0 | 2613.8 | 2616.6 | 2629.3 |
| 2550.0 | 37.5° | 2520.4 | 2497.0 | 2473.8 | 2461.4 | 2449.1 | 2442.2 | 2449.1 | 2461.4 | 2473.8 | 2497.0 |
| 2433.8 | 40°   | 2408.7 | 2374.7 | 2340.9 | 2318.0 | 2295.3 | 2281.7 | 2295.3 | 2318.0 | 2340.9 | 2374.7 |
| 2316.6 | 42.5° | 2295.5 | 2253.3 | 2211.1 | 2177.8 | 2144.4 | 2122.6 | 2144.4 | 2177.8 | 2211.1 | 2253.3 |
| 2203.1 | 45°   | 2184.1 | 2135.9 | 2087.7 | 2048.5 | 2009.4 | 1984.2 | 2009.4 | 2048.5 | 2087.7 | 2135.9 |
| 2109.3 | 47.5° | 2096.0 | 2053.1 | 2010.2 | 1974.0 | 1937.9 | 1913.6 | 1937.9 | 1974.0 | 2010.2 | 2053.1 |
| 2044.0 | 50°   | 2043.4 | 2009.1 | 1974.8 | 1941.3 | 1907.8 | 1884.6 | 1907.8 | 1941.3 | 1974.8 | 2009.1 |
| 2000.8 | 52.5° | 2008.0 | 1980.1 | 1952.1 | 1922.1 | 1892.2 | 1870.7 | 1892.2 | 1922.1 | 1952.1 | 1980.1 |
| 1964.8 | 55°   | 1974.8 | 1950.4 | 1926.1 | 1899.8 | 1873.5 | 1854.1 | 1873.5 | 1899.8 | 1926.1 | 1950.4 |
| 1929.6 | 57.5° | 1939.7 | 1915.0 | 1890.4 | 1864.4 | 1838.2 | 1818.2 | 1838.2 | 1864.4 | 1890.4 | 1915.0 |
| 1879.7 | 60°   | 1890.8 | 1866.7 | 1842.8 | 1816.0 | 1789.1 | 1768.4 | 1789.1 | 1816.0 | 1842.8 | 1866.7 |
| 1802.3 | 62.5° | 1812.9 | 1791.2 | 1769.5 | 1741.2 | 1713.0 | 1688.1 | 1713.0 | 1741.2 | 1769.5 | 1791.2 |
| 1697.0 | 65°   | 1707.7 | 1686.9 | 1666.0 | 1638.6 | 1611.3 | 1589.9 | 1611.3 | 1638.6 | 1666.0 | 1686.9 |
| 1577.3 | 67.5° | 1587.8 | 1568.5 | 1549.5 | 1524.0 | 1498.5 | 1479.2 | 1498.5 | 1524.0 | 1549.5 | 1568.5 |
| 1449.3 | 70°   | 1459.5 | 1443.9 | 1428.2 | 1403.9 | 1379.5 | 1357.4 | 1379.5 | 1403.9 | 1428.2 | 1443.9 |
| 1306.2 | 72.5° | 1318.4 | 1305.4 | 1292.4 | 1269.1 | 1246.0 | 1224.6 | 1246.0 | 1269.1 | 1292.4 | 1305.4 |
| 1137.4 | 75°   | 1150.1 | 1143.8 | 1137.4 | 1117.9 | 1098.4 | 1077.9 | 1098.4 | 1117.9 | 1137.4 | 1143.8 |
| 974.9  | 77.5° | 986.8  | 978.0  | 968.9  | 949.2  | 929.6  | 913.2  | 929.6  | 949.2  | 968.9  | 978.0  |
| 786.8  | 80°   | 802.5  | 798.7  | 794.9  | 768.5  | 741.9  | 711.2  | 741.9  | 768.5  | 794.9  | 798.7  |
| 572.3  | 82.5° | 599.1  | 597.5  | 595.7  | 573.4  | 551.0  | 531.3  | 551.0  | 573.4  | 595.7  | 597.5  |
| 347.3  | 85°   | 380.5  | 377.7  | 375.0  | 357.5  | 340.1  | 322.4  | 340.1  | 357.5  | 375.0  | 377.7  |
| 151.5  | 87.5° | 164.9  | 161.6  | 158.0  | 149.2  | 140.0  | 131.5  | 140.0  | 149.2  | 158.0  | 161.6  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P951562

CATALOG NUMBER: GLAN-SB5C-935-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 160°   |       | 165°   | 170°   | 175°   | 180°   | 185°   | 190°   | 195°   | 200°   | 205°   | 210°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 3605.9 | 0°    | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 |
| 3325.0 | 2.5°  | 3338.1 | 3351.3 | 3367.6 | 3383.8 | 3404.7 | 3425.7 | 3446.6 | 3467.5 | 3491.3 | 3515.3 |
| 3122.7 | 5°    | 3140.8 | 3159.0 | 3185.0 | 3210.8 | 3244.6 | 3278.2 | 3315.3 | 3352.4 | 3394.3 | 3436.4 |
| 3000.9 | 7.5°  | 3022.5 | 3044.1 | 3074.8 | 3105.7 | 3146.8 | 3188.0 | 3234.8 | 3281.4 | 3336.8 | 3392.1 |
| 2964.1 | 10°   | 2988.5 | 3012.6 | 3049.5 | 3086.3 | 3132.7 | 3179.0 | 3229.4 | 3279.6 | 3335.0 | 3390.3 |
| 3018.5 | 12.5° | 3049.6 | 3080.8 | 3127.8 | 3174.9 | 3222.7 | 3270.8 | 3310.1 | 3349.6 | 3386.2 | 3423.0 |
| 3131.0 | 15°   | 3178.3 | 3225.7 | 3292.6 | 3359.6 | 3401.2 | 3442.9 | 3453.1 | 3463.4 | 3458.4 | 3453.4 |
| 3239.2 | 17.5° | 3308.9 | 3378.7 | 3467.4 | 3556.1 | 3589.6 | 3623.2 | 3591.2 | 3559.1 | 3498.8 | 3438.5 |
| 3304.9 | 20°   | 3390.3 | 3475.8 | 3577.1 | 3678.5 | 3694.2 | 3709.7 | 3642.6 | 3575.4 | 3470.6 | 3365.8 |
| 3307.3 | 22.5° | 3395.4 | 3483.4 | 3580.3 | 3677.1 | 3667.9 | 3658.5 | 3571.2 | 3483.8 | 3364.0 | 3244.5 |
| 3240.3 | 25°   | 3318.4 | 3396.7 | 3476.0 | 3555.4 | 3523.4 | 3491.3 | 3405.4 | 3319.5 | 3211.8 | 3104.3 |
| 3109.1 | 27.5° | 3169.9 | 3230.6 | 3287.1 | 3343.7 | 3307.8 | 3272.1 | 3203.2 | 3134.3 | 3046.0 | 2957.6 |
| 2947.5 | 30°   | 2991.3 | 3034.7 | 3077.9 | 3120.9 | 3091.8 | 3062.8 | 3005.5 | 2948.4 | 2875.0 | 2801.7 |
| 2785.4 | 32.5° | 2820.1 | 2854.8 | 2894.5 | 2934.1 | 2901.7 | 2869.5 | 2814.6 | 2759.8 | 2701.1 | 2642.6 |
| 2642.2 | 35°   | 2674.1 | 2706.2 | 2734.3 | 2762.5 | 2723.8 | 2685.0 | 2630.7 | 2576.4 | 2531.9 | 2487.2 |
| 2520.4 | 37.5° | 2550.0 | 2579.5 | 2592.5 | 2605.5 | 2557.6 | 2509.7 | 2455.5 | 2401.4 | 2369.4 | 2337.3 |
| 2408.7 | 40°   | 2433.8 | 2458.8 | 2455.8 | 2452.6 | 2397.4 | 2342.3 | 2290.0 | 2237.7 | 2214.6 | 2191.5 |
| 2295.5 | 42.5° | 2316.6 | 2337.7 | 2321.8 | 2305.9 | 2246.4 | 2186.9 | 2137.2 | 2087.7 | 2068.8 | 2049.9 |
| 2184.1 | 45°   | 2203.1 | 2222.2 | 2199.4 | 2176.5 | 2114.8 | 2053.1 | 2006.1 | 1959.0 | 1943.0 | 1927.2 |
| 2096.0 | 47.5° | 2109.3 | 2122.6 | 2096.3 | 2070.0 | 2009.1 | 1948.2 | 1902.3 | 1856.2 | 1841.4 | 1826.5 |
| 2043.4 | 50°   | 2044.0 | 2044.8 | 2011.1 | 1977.3 | 1922.8 | 1868.3 | 1824.9 | 1781.5 | 1758.1 | 1734.9 |
| 2008.0 | 52.5° | 2000.8 | 1993.6 | 1953.6 | 1913.6 | 1862.7 | 1811.9 | 1772.2 | 1732.4 | 1697.5 | 1662.5 |
| 1974.8 | 55°   | 1964.8 | 1954.9 | 1912.4 | 1870.1 | 1825.6 | 1781.1 | 1738.2 | 1695.3 | 1645.8 | 1596.1 |
| 1939.7 | 57.5° | 1929.6 | 1919.5 | 1876.8 | 1834.1 | 1789.9 | 1745.9 | 1695.6 | 1645.2 | 1591.8 | 1538.4 |
| 1890.8 | 60°   | 1879.7 | 1868.7 | 1825.8 | 1782.9 | 1738.0 | 1693.4 | 1635.5 | 1577.7 | 1530.9 | 1484.0 |
| 1812.9 | 62.5° | 1802.3 | 1791.6 | 1752.3 | 1713.0 | 1665.3 | 1617.5 | 1550.0 | 1482.6 | 1452.9 | 1423.1 |
| 1707.7 | 65°   | 1697.0 | 1686.0 | 1651.4 | 1616.8 | 1571.2 | 1525.5 | 1453.1 | 1380.9 | 1369.6 | 1358.1 |
| 1587.8 | 67.5° | 1577.3 | 1566.6 | 1536.7 | 1506.8 | 1463.7 | 1420.4 | 1353.5 | 1286.8 | 1290.4 | 1294.0 |
| 1459.5 | 70°   | 1449.3 | 1439.0 | 1412.1 | 1385.1 | 1347.7 | 1310.4 | 1251.7 | 1193.0 | 1205.5 | 1217.9 |
| 1318.4 | 72.5° | 1306.2 | 1294.0 | 1267.6 | 1241.2 | 1207.4 | 1173.6 | 1127.6 | 1081.4 | 1099.5 | 1117.7 |
| 1150.1 | 75°   | 1137.4 | 1124.7 | 1100.6 | 1076.5 | 1045.9 | 1015.3 | 981.0  | 946.7  | 964.3  | 981.7  |
| 986.8  | 77.5° | 974.9  | 963.0  | 937.9  | 912.5  | 886.3  | 860.0  | 832.1  | 804.2  | 821.9  | 839.6  |
| 802.5  | 80°   | 786.8  | 771.0  | 751.9  | 732.7  | 710.5  | 688.4  | 665.3  | 642.0  | 657.0  | 671.8  |
| 599.1  | 82.5° | 572.3  | 545.4  | 504.5  | 463.5  | 471.3  | 479.0  | 481.0  | 482.9  | 493.4  | 503.9  |
| 380.5  | 85°   | 347.3  | 314.1  | 275.6  | 237.3  | 258.7  | 280.2  | 290.3  | 300.3  | 312.0  | 323.8  |
| 164.9  | 87.5° | 151.5  | 138.1  | 121.9  | 105.9  | 122.3  | 138.6  | 139.1  | 139.5  | 141.7  | 143.9  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P951562

CATALOG NUMBER: GLAN-SB5C-935-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 215°   |       | 220°   | 225°   | 230°   | 235°   | 240°   | 245°   | 250°   | 255°   | 260°   | 265°    |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|---------|
| 3605.9 | 0°    | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9 | 3605.9  |
| 3541.7 | 2.5°  | 3568.3 | 3601.0 | 3630.5 | 3661.0 | 3691.4 | 3723.2 | 3755.0 | 3786.6 | 3818.3 | 3848.0  |
| 3486.6 | 5°    | 3536.7 | 3594.1 | 3652.2 | 3713.8 | 3775.4 | 3841.3 | 3907.3 | 3972.7 | 4038.3 | 4104.0  |
| 3458.7 | 7.5°  | 3525.4 | 3599.7 | 3678.9 | 3764.9 | 3850.8 | 3948.4 | 4045.9 | 4146.1 | 4246.3 | 4354.6  |
| 3460.6 | 10°   | 3530.9 | 3610.7 | 3708.6 | 3810.4 | 3912.0 | 4030.5 | 4149.0 | 4281.3 | 4413.7 | 4550.8  |
| 3480.2 | 12.5° | 3537.8 | 3612.1 | 3714.9 | 3829.9 | 3944.9 | 4084.6 | 4224.4 | 4374.4 | 4524.4 | 4674.9  |
| 3480.8 | 15°   | 3508.3 | 3567.8 | 3681.7 | 3814.8 | 3947.9 | 4108.9 | 4269.8 | 4432.5 | 4595.2 | 4752.3  |
| 3428.5 | 17.5° | 3418.4 | 3455.1 | 3589.0 | 3749.1 | 3909.2 | 4096.0 | 4282.8 | 4460.3 | 4637.8 | 4797.1  |
| 3318.8 | 20°   | 3271.7 | 3281.4 | 3437.4 | 3635.8 | 3834.2 | 4060.6 | 4286.9 | 4482.0 | 4677.1 | 4842.8  |
| 3174.9 | 22.5° | 3105.3 | 3086.3 | 3263.8 | 3502.8 | 3741.8 | 4017.1 | 4292.5 | 4511.4 | 4730.1 | 4899.4  |
| 3024.0 | 25°   | 2943.8 | 2892.6 | 3074.6 | 3354.3 | 3634.3 | 3974.2 | 4314.3 | 4564.5 | 4814.5 | 4980.2  |
| 2880.1 | 27.5° | 2802.7 | 2740.4 | 2906.0 | 3218.6 | 3531.2 | 3945.6 | 4360.0 | 4647.5 | 4934.9 | 5093.1  |
| 2740.0 | 30°   | 2678.5 | 2629.7 | 2768.8 | 3105.1 | 3441.5 | 3932.2 | 4422.5 | 4755.0 | 5087.5 | 5240.2  |
| 2606.2 | 32.5° | 2569.8 | 2548.1 | 2660.1 | 3007.3 | 3354.3 | 3915.6 | 4476.5 | 4867.3 | 5258.0 | 5409.1  |
| 2477.1 | 35°   | 2467.1 | 2476.1 | 2569.5 | 2911.1 | 3252.8 | 3884.3 | 4516.1 | 4995.1 | 5474.1 | 5619.0  |
| 2348.4 | 37.5° | 2359.5 | 2392.4 | 2474.0 | 2798.0 | 3121.9 | 3830.7 | 4539.6 | 5138.3 | 5737.0 | 5921.6  |
| 2216.5 | 40°   | 2241.6 | 2292.1 | 2366.1 | 2662.9 | 2959.7 | 3757.0 | 4554.4 | 5320.1 | 6085.7 | 6354.7  |
| 2083.1 | 42.5° | 2116.3 | 2180.0 | 2248.2 | 2513.9 | 2779.6 | 3680.9 | 4582.5 | 5558.0 | 6533.5 | 6921.8  |
| 1959.4 | 45°   | 1991.8 | 2053.4 | 2122.6 | 2355.6 | 2588.6 | 3610.2 | 4631.9 | 5871.0 | 7110.1 | 7633.8  |
| 1853.6 | 47.5° | 1880.7 | 1933.7 | 2023.0 | 2230.4 | 2437.8 | 3551.8 | 4665.8 | 6204.5 | 7743.1 | 8480.3  |
| 1758.8 | 50°   | 1782.9 | 1844.5 | 1961.8 | 2147.2 | 2332.6 | 3488.1 | 4643.7 | 6513.8 | 8384.0 | 9495.4  |
| 1686.2 | 52.5° | 1710.0 | 1796.0 | 1930.9 | 2092.4 | 2254.0 | 3380.6 | 4507.4 | 6714.8 | 8922.0 | 10561.7 |
| 1633.6 | 55°   | 1671.2 | 1800.9 | 1926.4 | 2052.7 | 2179.0 | 3202.4 | 4225.8 | 6670.5 | 9115.0 | 11507.0 |
| 1593.2 | 57.5° | 1648.0 | 1805.7 | 1916.4 | 2005.7 | 2094.9 | 2951.1 | 3807.2 | 6358.9 | 8910.7 | 12177.0 |
| 1555.1 | 60°   | 1626.1 | 1790.5 | 1863.5 | 1933.7 | 2003.9 | 2624.9 | 3245.9 | 5779.0 | 8312.1 | 12344.4 |
| 1511.8 | 62.5° | 1600.6 | 1753.1 | 1762.1 | 1808.6 | 1855.2 | 2234.4 | 2613.5 | 4994.8 | 7376.2 | 11639.4 |
| 1452.6 | 65°   | 1547.0 | 1663.2 | 1662.1 | 1684.1 | 1706.1 | 1883.1 | 2060.0 | 4194.8 | 6329.7 | 10641.9 |
| 1372.6 | 67.5° | 1451.2 | 1516.5 | 1519.6 | 1507.4 | 1495.1 | 1545.4 | 1595.7 | 3411.1 | 5226.5 | 9454.9  |
| 1273.8 | 70°   | 1329.7 | 1351.2 | 1351.2 | 1294.3 | 1237.3 | 1223.0 | 1208.7 | 2685.7 | 4162.8 | 8159.6  |
| 1156.1 | 72.5° | 1194.4 | 1194.1 | 1180.6 | 1099.9 | 1019.1 | 975.6  | 932.3  | 2053.3 | 3174.2 | 6755.4  |
| 1011.3 | 75°   | 1040.8 | 1046.1 | 983.5  | 893.0  | 802.5  | 763.2  | 723.9  | 1490.2 | 2256.5 | 5145.8  |
| 863.3  | 77.5° | 886.9  | 889.7  | 786.6  | 698.8  | 610.9  | 584.1  | 557.3  | 1009.8 | 1462.3 | 3601.6  |
| 691.7  | 80°   | 711.5  | 711.9  | 588.8  | 514.5  | 440.0  | 428.9  | 417.9  | 650.6  | 883.5  | 2320.4  |
| 513.6  | 82.5° | 523.3  | 517.5  | 412.3  | 357.5  | 302.8  | 300.5  | 298.6  | 400.2  | 502.0  | 1343.0  |
| 334.2  | 85°   | 344.5  | 336.9  | 258.7  | 218.6  | 178.5  | 179.6  | 180.6  | 213.9  | 247.4  | 604.1   |
| 148.1  | 87.5° | 152.2  | 142.5  | 110.0  | 93.5   | 77.2   | 78.2   | 79.1   | 88.7   | 98.2   | 197.9   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     |

REPORT NUMBER: P951562

CATALOG NUMBER: GLAN-SB5C-935-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 270°    |       | 275°    | 280°    | 285°    | 290°    | 295°    | 300°    | 305°    | 310°    | 315°    | 320°    |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 3605.9  | 0°    | 3605.9  | 3605.9  | 3605.9  | 3605.9  | 3605.9  | 3605.9  | 3605.9  | 3605.9  | 3605.9  | 3605.9  |
| 3877.8  | 2.5°  | 3892.4  | 3907.3  | 3928.1  | 3949.0  | 3961.5  | 3973.9  | 3980.2  | 3986.4  | 3983.6  | 3986.4  |
| 4169.7  | 5°    | 4221.1  | 4272.5  | 4323.5  | 4374.5  | 4402.2  | 4429.9  | 4446.6  | 4463.5  | 4476.2  | 4463.5  |
| 4463.1  | 7.5°  | 4546.7  | 4630.1  | 4705.2  | 4780.4  | 4825.6  | 4870.9  | 4895.3  | 4919.7  | 4931.5  | 4919.7  |
| 4687.9  | 10°   | 4786.7  | 4885.5  | 4973.7  | 5061.8  | 5115.2  | 5168.3  | 5192.1  | 5215.8  | 5224.8  | 5215.8  |
| 4825.6  | 12.5° | 4932.7  | 5039.7  | 5119.4  | 5198.8  | 5237.5  | 5276.3  | 5289.3  | 5302.3  | 5303.7  | 5302.3  |
| 4909.3  | 15°   | 5001.8  | 5094.0  | 5144.0  | 5194.1  | 5195.5  | 5196.9  | 5183.0  | 5169.2  | 5152.9  | 5169.2  |
| 4956.4  | 17.5° | 5018.8  | 5081.2  | 5082.1  | 5083.0  | 5026.9  | 4970.9  | 4919.6  | 4868.1  | 4831.8  | 4868.1  |
| 5008.3  | 20°   | 5030.0  | 5051.8  | 4986.1  | 4920.4  | 4796.7  | 4673.0  | 4582.9  | 4492.8  | 4437.5  | 4492.8  |
| 5068.4  | 22.5° | 5039.9  | 5011.4  | 4875.3  | 4739.1  | 4557.2  | 4375.2  | 4262.6  | 4150.0  | 4088.8  | 4150.0  |
| 5145.9  | 25°   | 5056.0  | 4966.1  | 4759.3  | 4552.6  | 4331.6  | 4110.7  | 3992.2  | 3874.0  | 3816.2  | 3874.0  |
| 5251.1  | 27.5° | 5090.3  | 4929.4  | 4655.6  | 4381.9  | 4136.9  | 3892.0  | 3775.5  | 3659.2  | 3604.5  | 3659.2  |
| 5392.9  | 30°   | 5153.1  | 4913.5  | 4576.4  | 4239.3  | 3984.2  | 3729.0  | 3621.0  | 3512.9  | 3462.0  | 3512.9  |
| 5560.3  | 32.5° | 5232.0  | 4903.8  | 4522.4  | 4141.1  | 3901.3  | 3661.5  | 3576.7  | 3491.7  | 3455.1  | 3491.7  |
| 5763.7  | 35°   | 5361.9  | 4960.2  | 4562.8  | 4165.6  | 3999.0  | 3832.5  | 3812.7  | 3793.0  | 3789.9  | 3793.0  |
| 6106.2  | 37.5° | 5633.5  | 5160.9  | 4799.7  | 4438.6  | 4427.8  | 4417.0  | 4507.5  | 4598.0  | 4645.0  | 4598.0  |
| 6623.7  | 40°   | 6109.7  | 5595.6  | 5327.1  | 5058.5  | 5248.0  | 5437.6  | 5657.6  | 5877.6  | 5987.2  | 5877.6  |
| 7310.0  | 42.5° | 6800.0  | 6290.0  | 6135.3  | 5980.6  | 6394.0  | 6807.5  | 7207.6  | 7607.8  | 7842.7  | 7607.8  |
| 8157.5  | 45°   | 7699.4  | 7241.1  | 7172.9  | 7104.5  | 7766.9  | 8429.4  | 9086.9  | 9744.6  | 10143.8 | 9744.6  |
| 9217.4  | 47.5° | 8771.7  | 8325.9  | 8312.1  | 8298.2  | 9253.8  | 10209.1 | 11171.8 | 12134.2 | 12699.5 | 12134.2 |
| 10606.7 | 50°   | 10056.1 | 9505.7  | 9508.0  | 9510.4  | 10741.8 | 11973.3 | 13244.0 | 14514.6 | 15282.8 | 14514.6 |
| 12201.4 | 52.5° | 11534.7 | 10868.2 | 10800.8 | 10733.3 | 12204.3 | 13675.3 | 15247.4 | 16819.4 | 17740.3 | 16819.4 |
| 13899.1 | 55°   | 13240.5 | 12581.9 | 12319.1 | 12056.3 | 13693.5 | 15330.6 | 17204.8 | 19079.0 | 20174.2 | 19079.0 |
| 15443.3 | 57.5° | 15084.7 | 14725.9 | 14198.8 | 13671.9 | 15325.0 | 16978.1 | 19101.0 | 21223.7 | 22581.8 | 21223.7 |
| 16376.6 | 60°   | 16933.7 | 17490.9 | 16836.4 | 16181.9 | 17746.3 | 19310.7 | 21583.6 | 23856.4 | 25324.2 | 23856.4 |
| 15902.7 | 62.5° | 17424.9 | 18947.1 | 18873.4 | 18799.5 | 20232.5 | 21665.8 | 23828.2 | 25990.5 | 27347.2 | 25990.5 |
| 14954.2 | 65°   | 16382.9 | 17811.5 | 18094.2 | 18376.7 | 20198.0 | 22019.3 | 24116.1 | 26212.8 | 27367.9 | 26212.8 |
| 13683.3 | 67.5° | 15042.1 | 16400.8 | 16533.4 | 16665.8 | 18563.4 | 20460.9 | 22566.7 | 24672.5 | 25577.5 | 24672.5 |
| 12156.4 | 70°   | 13634.3 | 15112.4 | 15171.6 | 15230.9 | 16927.9 | 18624.7 | 20436.9 | 22249.0 | 22752.0 | 22249.0 |
| 10336.8 | 72.5° | 12032.8 | 13728.9 | 13771.6 | 13814.0 | 15141.7 | 16469.3 | 17826.6 | 19183.7 | 19234.6 | 19183.7 |
| 8035.1  | 75°   | 9790.4  | 11545.8 | 11703.4 | 11861.0 | 12893.9 | 13926.8 | 14882.2 | 15837.7 | 15581.7 | 15837.7 |
| 5740.9  | 77.5° | 7379.5  | 9018.2  | 9243.7  | 9469.3  | 10254.5 | 11039.7 | 11717.3 | 12395.1 | 11955.1 | 12395.1 |
| 3757.4  | 80°   | 5136.0  | 6514.4  | 6794.7  | 7075.1  | 7668.1  | 8260.9  | 8616.8  | 8972.5  | 8264.8  | 8972.5  |
| 2184.1  | 82.5° | 3126.6  | 4069.1  | 4382.3  | 4695.5  | 5103.7  | 5511.9  | 5660.4  | 5808.7  | 5252.5  | 5808.7  |
| 961.0   | 85°   | 1461.2  | 1961.4  | 2227.7  | 2494.1  | 2829.5  | 3164.8  | 3249.0  | 3333.3  | 2887.8  | 3333.3  |
| 297.5   | 87.5° | 465.6   | 633.7   | 782.3   | 930.9   | 1098.6  | 1266.4  | 1273.5  | 1280.6  | 1075.1  | 1280.6  |
| 0.0     | 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P951562

CATALOG NUMBER: GLAN-SB5C-935-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 325°    |       | 330°    | 335°    | 340°    | 345°    | 350°    | 355°    | 360°    |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|
| 3605.9  | 0°    | 3605.9  | 3605.9  | 3605.9  | 3605.9  | 3605.9  | 3605.9  | 3605.9  |
| 3980.2  | 2.5°  | 3973.9  | 3961.5  | 3949.0  | 3928.1  | 3907.3  | 3892.4  | 3877.8  |
| 4446.6  | 5°    | 4429.9  | 4402.2  | 4374.5  | 4323.5  | 4272.5  | 4221.1  | 4169.7  |
| 4895.3  | 7.5°  | 4870.9  | 4825.6  | 4780.4  | 4705.2  | 4630.1  | 4546.7  | 4463.1  |
| 5192.1  | 10°   | 5168.3  | 5115.2  | 5061.8  | 4973.7  | 4885.5  | 4786.7  | 4687.9  |
| 5289.3  | 12.5° | 5276.3  | 5237.5  | 5198.8  | 5119.4  | 5039.7  | 4932.7  | 4825.6  |
| 5183.0  | 15°   | 5196.9  | 5195.5  | 5194.1  | 5144.0  | 5094.0  | 5001.8  | 4909.3  |
| 4919.6  | 17.5° | 4970.9  | 5026.9  | 5083.0  | 5082.1  | 5081.2  | 5018.8  | 4956.4  |
| 4582.9  | 20°   | 4673.0  | 4796.7  | 4920.4  | 4986.1  | 5051.8  | 5030.0  | 5008.3  |
| 4262.6  | 22.5° | 4375.2  | 4557.2  | 4739.1  | 4875.3  | 5011.4  | 5039.9  | 5068.4  |
| 3992.2  | 25°   | 4110.7  | 4331.6  | 4552.6  | 4759.3  | 4966.1  | 5056.0  | 5145.9  |
| 3775.5  | 27.5° | 3892.0  | 4136.9  | 4381.9  | 4655.6  | 4929.4  | 5090.3  | 5251.1  |
| 3621.0  | 30°   | 3729.0  | 3984.2  | 4239.3  | 4576.4  | 4913.5  | 5153.1  | 5392.9  |
| 3576.7  | 32.5° | 3661.5  | 3901.3  | 4141.1  | 4522.4  | 4903.8  | 5232.0  | 5560.3  |
| 3812.7  | 35°   | 3832.5  | 3999.0  | 4165.6  | 4562.8  | 4960.2  | 5361.9  | 5763.7  |
| 4507.5  | 37.5° | 4417.0  | 4427.8  | 4438.6  | 4799.7  | 5160.9  | 5633.5  | 6106.2  |
| 5657.6  | 40°   | 5437.6  | 5248.0  | 5058.5  | 5327.1  | 5595.6  | 6109.7  | 6623.7  |
| 7207.6  | 42.5° | 6807.5  | 6394.0  | 5980.6  | 6135.3  | 6290.0  | 6800.0  | 7310.0  |
| 9086.9  | 45°   | 8429.4  | 7766.9  | 7104.5  | 7172.9  | 7241.1  | 7699.4  | 8157.5  |
| 11171.8 | 47.5° | 10209.1 | 9253.8  | 8298.2  | 8312.1  | 8325.9  | 8771.7  | 9217.4  |
| 13244.0 | 50°   | 11973.3 | 10741.8 | 9510.4  | 9508.0  | 9505.7  | 10056.1 | 10606.7 |
| 15247.4 | 52.5° | 13675.3 | 12204.3 | 10733.3 | 10800.8 | 10868.2 | 11534.7 | 12201.4 |
| 17204.8 | 55°   | 15330.6 | 13693.5 | 12056.3 | 12319.1 | 12581.9 | 13240.5 | 13899.1 |
| 19101.0 | 57.5° | 16978.1 | 15325.0 | 13671.9 | 14198.8 | 14725.9 | 15084.7 | 15443.3 |
| 21583.6 | 60°   | 19310.7 | 17746.3 | 16181.9 | 16836.4 | 17490.9 | 16933.7 | 16376.6 |
| 23828.2 | 62.5° | 21665.8 | 20232.5 | 18799.5 | 18873.4 | 18947.1 | 17424.9 | 15902.7 |
| 24116.1 | 65°   | 22019.3 | 20198.0 | 18376.7 | 18094.2 | 17811.5 | 16382.9 | 14954.2 |
| 22566.7 | 67.5° | 20460.9 | 18563.4 | 16665.8 | 16533.4 | 16400.8 | 15042.1 | 13683.3 |
| 20436.9 | 70°   | 18624.7 | 16927.9 | 15230.9 | 15171.6 | 15112.4 | 13634.3 | 12156.4 |
| 17826.6 | 72.5° | 16469.3 | 15141.7 | 13814.0 | 13771.6 | 13728.9 | 12032.8 | 10336.8 |
| 14882.2 | 75°   | 13926.8 | 12893.9 | 11861.0 | 11703.4 | 11545.8 | 9790.4  | 8035.1  |
| 11717.3 | 77.5° | 11039.7 | 10254.5 | 9469.3  | 9243.7  | 9018.2  | 7379.5  | 5740.9  |
| 8616.8  | 80°   | 8260.9  | 7668.1  | 7075.1  | 6794.7  | 6514.4  | 5136.0  | 3757.4  |
| 5660.4  | 82.5° | 5511.9  | 5103.7  | 4695.5  | 4382.3  | 4069.1  | 3126.6  | 2184.1  |
| 3249.0  | 85°   | 3164.8  | 2829.5  | 2494.1  | 2227.7  | 1961.4  | 1461.2  | 961.0   |
| 1273.5  | 87.5° | 1266.4  | 1098.6  | 930.9   | 782.3   | 633.7   | 465.6   | 297.5   |
| 0.0     | 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

(END OF REPORT)