

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS  
Report Number: P599264

Luminaire Tested: **IFLD-S-SA6A-750-U-SLR-HSS**

Issue Date: 05/04/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

**Test Information**

Test Method: LM-79-08  
 Report Number: P599264  
 Test Lab: INNOVATION CENTER(G1)  
 Issue Date: 05/04/2022  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: IFLD-S-SA6A-750-U-SLR-HSS  
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLR distribution lens with House Side Shield  
 Light Source: (96) 5000K CCT, 70 CRI LEDs  
 Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
 Luminaire Lumens: 20110.1 lumens  
 Efficiency: N/A  
 Efficacy: 106.1 lumens/watt  
 Spacing Criteria (0/90/45): 0.44 / 0.52 / 0.65  
 Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
 CIE Type: Direct

Input Watts (W): 189.6  
 Input Voltage (V): 120  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599264  
CATALOG NUMBER: IFLD-S-SA6A-750-U-SLR-HSS

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - · - 90°-270°    - - - 135°-315°

TEST NUMBER: P599264  
 CATALOG NUMBER: IFLD-S-SA6A-750-U-SLR-HSS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	107	101	96	91	104	99	94	90	94	90	87	90	87	84	87	84	82	87	84	82	79
2	95	85	77	70	92	83	75	69	79	73	67	76	71	66	73	68	64	73	68	64	62
3	85	72	63	55	82	71	62	54	67	60	53	65	58	52	62	56	51	62	56	51	49
4	76	62	52	44	74	61	51	44	58	50	43	56	49	43	53	47	42	53	47	42	40
5	69	55	44	37	67	53	44	36	51	43	36	49	41	35	47	40	35	47	40	35	33
6	63	48	38	31	61	47	38	31	45	37	30	44	36	30	42	35	30	42	35	30	27
7	58	43	33	27	56	42	33	26	41	32	26	39	32	26	38	31	26	38	31	26	24
8	54	39	30	23	52	38	29	23	37	29	23	36	28	23	34	28	23	34	28	23	20
9	50	36	27	21	49	35	26	21	34	26	20	33	25	20	32	25	20	32	25	20	18
10	47	33	24	18	46	32	24	18	31	24	18	30	23	18	29	23	18	29	23	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	55169	55169	55169	55169
5°	53115	38820	41789	58543
10°	47290	21136	21413	50055
15°	47207	14097	8620	48093
20°	56681	7039	3436	56350
25°	69716	4421	2661	69372
30°	84234	3549	2022	83696
35°	98839	2850	1567	97841
40°	119658	2437	1015	116357
45°	136895	2201	550	133098
50°	155314	2119	121	148958
55°	187349	2036	0	168899
60°	226824	1712	0	213362
65°	262648	1380	0	238711
70°	265958	1137	0	240705
75°	172118	751	0	184595
80°	58702	223	0	130623
85°	29459	0	0	95978

TEST NUMBER: P599264  
 CATALOG NUMBER: IFLD-S-SA6A-750-U-SLR-HSS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	582.4	2.9
10°-20°	1127.7	5.6
20°-30°	1570.6	7.8
30°-40°	2231.7	11.1
40°-50°	3094.7	15.4
50°-60°	4216.6	21.0
60°-70°	4635.9	23.1
70°-80°	2278.5	11.3
80°-90°	372.1	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3280.7	16.3
0°-40°	5512.3	27.4
0°-60°	12823.6	63.8
0°-90°	20110.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	20110.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	7688	7688	7688	7688	7688	
5°	7374	5389	5801	8127	7374	675
15°	6354	1898	1160	6474	6354	1881
25°	8805	558	336	8762	8805	4094
35°	11283	325	179	11169	11283	7162
45°	13489	217	54	13115	13489	10457
55°	14975	163	0	13500	14975	13471
65°	15468	81	0	14059	15468	14948
75°	6208	27	0	6658	6208	6768
85°	358	0	0	1166	358	495
90°	0	0	0	0	0	

TEST NUMBER: P599264  
 CATALOG NUMBER: IFLD-S-SA6A-750-U-SLR-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1
2.5°	7845.3	7937.5	7850.7	7547.1	7492.9	7346.5	7124.2	7107.9	6874.8	6901.9	6777.2
5°	7373.6	7465.8	7281.4	6880.2	6506.1	6207.9	6029.0	5709.1	5638.6	5481.4	5481.4
7.5°	6891.1	6885.6	6571.2	6235.0	5676.6	5129.0	4879.6	4418.7	4147.7	4001.3	3860.3
10°	6489.9	6403.1	6207.9	5513.9	4906.7	4337.4	4028.4	3724.8	3442.8	3198.8	2954.9
12.5°	6207.9	6262.1	5953.1	5199.5	4413.3	4017.5	3686.8	3366.9	3030.8	2754.3	2483.2
15°	6354.3	6267.6	5904.3	5129.0	4332.0	3789.8	3350.7	2960.3	2586.2	2222.9	2016.9
17.5°	6809.7	6587.5	6159.1	5129.0	4163.9	3442.8	2911.5	2450.6	2049.4	1724.1	1469.3
20°	7422.4	7167.6	6706.7	5318.8	4039.2	3188.0	2461.5	1881.4	1463.9	1160.3	965.1
22.5°	8051.3	7850.7	7156.7	5394.7	3892.8	2846.4	1941.0	1360.9	975.9	780.7	683.1
25°	8805.0	8523.0	7764.0	5698.3	3676.0	2515.7	1528.9	948.8	726.5	623.5	563.9
27.5°	9406.8	9358.0	8333.3	5882.6	3513.3	2244.6	1209.1	753.6	601.8	525.9	488.0
30°	10165.8	9900.2	9027.2	6251.3	3329.0	1935.6	1008.4	677.7	553.0	471.7	444.6
32.5°	10621.2	10496.5	9390.5	6457.3	3122.9	1680.7	867.5	596.4	504.2	444.6	417.5
35°	11282.7	11033.3	9911.0	6587.5	3014.5	1534.4	780.7	542.2	422.9	363.3	330.7
37.5°	12020.1	11927.9	10534.5	6582.0	2857.3	1447.6	721.1	504.2	401.2	336.1	298.2
40°	12773.7	12399.6	10914.0	6733.8	2775.9	1382.6	677.7	482.5	379.5	319.9	271.1
42.5°	13337.6	12909.2	11353.2	6679.6	2678.4	1268.7	661.5	450.0	363.3	292.8	249.4
45°	13489.4	13337.6	11749.0	6663.4	2607.9	1176.5	634.3	444.6	352.4	276.5	233.1
47.5°	13782.1	13679.1	12236.9	6690.5	2553.7	1106.0	569.3	455.4	336.1	260.2	222.3
50°	13912.3	13727.9	12632.7	6755.5	2429.0	1019.3	509.6	477.1	330.7	254.8	211.4
52.5°	14449.0	14286.4	13174.9	6939.9	2325.9	905.4	450.0	455.4	341.6	238.6	200.6
55°	14974.9	14790.6	14009.9	7362.8	2179.6	813.3	384.9	401.2	325.3	216.9	178.9
57.5°	15696.0	15392.4	14568.3	7536.3	2049.4	688.6	341.6	330.7	303.6	195.2	157.2
60°	15804.5	15929.2	14487.0	7427.8	1913.9	607.2	298.2	254.8	325.3	173.5	135.5
62.5°	16167.7	15647.2	14107.4	7178.4	1816.3	558.4	265.7	211.4	281.9	151.8	113.9
65°	15468.3	15083.4	13218.3	6376.0	1691.6	563.9	233.1	173.5	178.9	124.7	92.2
67.5°	14443.6	14140.0	11743.6	5503.1	1566.9	553.0	206.0	151.8	135.5	108.4	81.3
70°	12676.1	12020.1	9976.1	4467.5	1382.6	515.1	173.5	135.5	113.9	86.7	59.6
72.5°	9222.4	8956.8	7156.7	3453.7	1241.6	466.3	162.7	113.9	97.6	65.1	48.8
75°	6207.9	5768.8	4516.3	2266.3	997.6	406.6	135.5	103.0	75.9	48.8	38.0
77.5°	3280.2	3101.3	2559.1	1078.9	553.0	189.8	75.9	59.6	43.4	38.0	21.7
80°	1420.5	1263.3	1106.0	439.2	195.2	86.7	48.8	32.5	27.1	21.7	10.8
82.5°	726.5	694.0	574.7	189.8	113.9	65.1	27.1	21.7	16.3	10.8	5.4
85°	357.8	368.7	303.6	59.6	65.1	38.0	5.4	5.4	0.0	0.0	0.0
87.5°	27.1	27.1	21.7	10.8	16.3	5.4	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599264  
 CATALOG NUMBER: IFLD-S-SA6A-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1
2.5°	6728.4	6804.3	6674.2	6755.5	6717.6	6733.8	6750.1	6706.7	6717.6	6869.4	6874.8
5°	5389.2	5535.6	5481.4	5557.3	5687.4	5622.4	5682.0	5671.2	5682.0	5703.7	5801.3
7.5°	3844.0	3800.7	3903.7	4104.3	4337.4	4478.4	4407.9	4369.9	4348.3	4294.0	4359.1
10°	2900.6	2879.0	2851.9	2911.5	3063.3	3220.5	3307.3	3160.9	3079.6	2976.6	2938.6
12.5°	2407.3	2271.7	2195.8	2103.6	2147.0	2288.0	2293.4	2152.4	2022.3	1968.1	2027.7
15°	1897.6	1805.4	1669.9	1539.8	1474.7	1583.2	1491.0	1355.4	1187.4	1165.7	1160.3
17.5°	1355.4	1301.2	1203.6	1149.4	1073.5	1046.4	948.8	742.8	623.5	591.0	601.8
20°	921.7	878.3	872.9	824.1	791.6	769.9	612.7	477.1	439.2	444.6	450.0
22.5°	683.1	661.5	634.3	628.9	601.8	574.7	450.0	401.2	374.1	374.1	390.4
25°	558.4	547.6	520.5	509.6	498.8	460.9	379.5	341.6	330.7	319.9	336.1
27.5°	477.1	471.7	455.4	439.2	428.3	390.4	330.7	298.2	287.4	287.4	287.4
30°	428.3	428.3	406.6	374.1	374.1	330.7	281.9	260.2	249.4	249.4	244.0
32.5°	401.2	390.4	363.3	341.6	325.3	281.9	249.4	227.7	211.4	211.4	216.9
35°	325.3	325.3	319.9	303.6	281.9	238.6	211.4	189.8	178.9	173.5	178.9
37.5°	287.4	271.1	249.4	254.8	244.0	206.0	178.9	162.7	146.4	146.4	146.4
40°	260.2	244.0	222.3	206.0	200.6	184.3	157.2	130.1	113.9	108.4	108.4
42.5°	233.1	222.3	189.8	162.7	157.2	157.2	119.3	97.6	81.3	81.3	81.3
45°	216.9	200.6	173.5	141.0	113.9	119.3	97.6	70.5	59.6	54.2	54.2
47.5°	206.0	189.8	151.8	119.3	86.7	86.7	70.5	48.8	38.0	32.5	32.5
50°	189.8	173.5	135.5	97.6	65.1	54.2	43.4	27.1	16.3	10.8	10.8
52.5°	178.9	162.7	119.3	81.3	54.2	38.0	27.1	5.4	0.0	0.0	0.0
55°	162.7	141.0	103.0	65.1	43.4	21.7	5.4	0.0	0.0	0.0	0.0
57.5°	141.0	124.7	81.3	48.8	27.1	5.4	0.0	0.0	0.0	0.0	0.0
60°	119.3	103.0	65.1	38.0	10.8	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	97.6	86.7	48.8	21.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	81.3	65.1	38.0	5.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	70.5	54.2	27.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	54.2	38.0	16.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	38.0	27.1	5.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	27.1	16.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	16.3	5.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	5.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599264  
 CATALOG NUMBER: IFLD-S-SA6A-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1
2.5°	6896.5	7059.1	7211.0	7254.3	7373.6	7704.3	7704.3	7861.6	8143.5	8246.5	8268.2
5°	5817.6	5991.1	6023.6	6359.7	6517.0	6853.1	7075.4	7606.7	7926.6	8127.2	8251.9
7.5°	4424.2	4483.8	4608.5	4923.0	5232.0	5638.6	6061.5	6739.3	7303.1	7530.8	7953.7
10°	3041.6	3220.5	3491.6	3773.6	4256.1	4706.1	5253.7	5893.5	6587.5	6869.4	7232.6
12.5°	2049.4	2298.8	2732.6	3133.8	3578.4	4033.8	4554.3	5410.9	6197.1	6587.5	6950.7
15°	1198.2	1501.8	1875.9	2526.5	3117.5	3627.2	4147.7	5015.1	5969.4	6473.6	6918.2
17.5°	607.2	699.4	1008.4	1572.3	2353.0	3188.0	3963.3	5069.4	6142.9	6760.9	7129.6
20°	455.4	482.5	569.3	835.0	1610.3	2635.0	3789.8	5150.7	6625.4	7379.0	7579.6
22.5°	395.8	417.5	455.4	542.2	905.4	2016.9	3545.8	5351.3	7281.4	7991.7	8414.6
25°	336.1	357.8	390.4	444.6	580.1	1371.7	3247.6	5562.7	7867.0	8761.6	9157.4
27.5°	292.8	309.0	341.6	384.9	471.7	872.9	2732.6	5844.7	8761.6	9694.1	9797.1
30°	249.4	265.7	292.8	341.6	401.2	618.1	2006.1	5882.6	9255.0	10100.8	10388.1
32.5°	216.9	222.3	254.8	298.2	336.1	488.0	1409.7	5920.6	9618.2	10626.7	10686.3
35°	178.9	189.8	222.3	249.4	292.8	384.9	1068.1	5730.8	10089.9	11168.8	11152.6
37.5°	146.4	162.7	184.3	206.0	238.6	325.3	851.2	5378.4	10680.9	12009.2	11499.6
40°	113.9	130.1	151.8	178.9	200.6	292.8	639.8	4847.1	11299.0	12421.3	11879.1
42.5°	81.3	92.2	113.9	141.0	178.9	244.0	460.9	4218.1	11542.9	12903.8	12334.5
45°	59.6	70.5	86.7	119.3	184.3	195.2	319.9	3643.4	11803.2	13115.3	12231.5
47.5°	32.5	43.4	65.1	103.0	162.7	146.4	227.7	3128.4	12101.4	13305.0	12312.8
50°	10.8	16.3	38.0	108.4	130.1	113.9	178.9	2851.9	12394.2	13343.0	12475.5
52.5°	0.0	0.0	21.7	113.9	97.6	86.7	157.2	2743.4	12318.3	13462.3	12372.5
55°	0.0	0.0	5.4	48.8	54.2	65.1	130.1	2738.0	12855.0	13500.2	12936.3
57.5°	0.0	0.0	0.0	16.3	32.5	54.2	113.9	2564.5	13196.6	14443.6	13695.4
60°	0.0	0.0	0.0	5.4	21.7	38.0	86.7	2412.7	13543.6	14866.5	14508.7
62.5°	0.0	0.0	0.0	0.0	5.4	16.3	59.6	2179.6	12844.2	14834.0	15294.8
65°	0.0	0.0	0.0	0.0	0.0	0.0	38.0	1724.1	11553.8	14058.6	14861.1
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	21.7	1192.8	10117.0	13082.7	14064.1
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	721.1	8165.2	11472.5	11927.9
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	309.0	5828.4	9108.6	9786.3
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	124.7	3605.5	6657.9	7492.9
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	48.8	2336.8	5042.2	5687.4
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	10.8	1247.0	3160.9	3676.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	542.2	1919.3	2212.1
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	173.5	1165.7	1328.3
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	178.9	238.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P599264  
 CATALOG NUMBER: IFLD-S-SA6A-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1	7688.1
2.5°	8279.0	8436.3	8495.9	8403.7	8414.6	8224.8	8197.7	7932.0	7823.6	7845.3
5°	8658.6	8886.3	9011.0	8908.0	8674.8	8311.6	7980.8	7666.4	7471.2	7373.6
7.5°	8571.8	8826.6	8983.9	9081.5	8815.8	8230.2	7726.0	7135.0	6885.6	6891.1
10°	8094.7	8626.0	8945.9	8821.2	8696.5	8111.0	7330.2	6690.5	6468.2	6489.9
12.5°	7709.8	8300.7	8490.5	8588.1	8333.3	7867.0	7341.1	6609.1	6359.7	6207.9
15°	7471.2	7910.4	7921.2	8073.0	7970.0	7970.0	7454.9	6739.3	6522.4	6354.3
17.5°	7471.2	7568.8	7557.9	7612.2	7785.7	7991.7	7742.3	7265.2	6836.9	6809.7
20°	7639.3	7335.7	7265.2	7286.9	7433.2	8045.9	8376.6	7780.2	7509.2	7422.4
22.5°	8029.6	7362.8	6934.4	6858.5	7308.5	8040.5	8783.3	8593.5	8121.8	8051.3
25°	8566.4	7314.0	6847.7	6750.1	7091.7	8235.7	9341.7	9379.7	8951.3	8805.0
27.5°	9076.0	7530.8	6836.9	6815.2	7265.2	8192.3	9726.7	10008.6	9526.0	9406.8
30°	9249.5	7747.7	7037.5	6750.1	7330.2	8349.5	9715.8	10453.2	10138.7	10165.8
32.5°	9455.6	7964.6	7059.1	6945.3	7606.7	8604.3	10024.9	11168.8	10941.1	10621.2
35°	9759.2	8257.4	7265.2	7162.2	7801.9	8832.1	10089.9	11694.8	11656.8	11282.7
37.5°	10019.4	8544.7	7693.5	7709.8	8398.3	9200.7	10377.3	12339.9	12274.9	12020.1
40°	10203.8	8945.9	8360.4	8403.7	8918.8	9612.8	10886.9	12665.3	13147.8	12773.7
42.5°	10230.9	9303.8	9124.8	9471.8	9954.4	10252.6	11092.9	12887.5	13581.5	13337.6
45°	10333.9	9873.0	10371.8	10626.7	11022.5	10816.4	11082.1	13267.1	13614.1	13489.4
47.5°	10735.1	10908.6	11537.5	12312.8	12453.8	11776.1	11342.3	13326.7	13798.4	13782.1
50°	11152.6	12020.1	12903.8	13418.9	13597.8	12437.5	11586.3	13277.9	14042.4	13912.3
52.5°	11618.9	12985.1	14259.3	14893.6	14796.0	13169.5	11862.8	13673.7	14492.4	14449.0
55°	11911.6	13418.9	15132.2	16015.9	15940.0	13988.2	12741.2	14243.0	15083.4	14974.9
57.5°	12686.9	14123.7	15999.6	16411.7	16612.3	15061.7	13353.8	15175.5	15576.7	15696.0
60°	13326.7	14584.6	16227.4	16823.8	16894.2	15701.4	14427.3	16135.2	16205.7	15804.5
62.5°	14264.7	14763.5	15744.8	16281.6	16644.8	16064.7	15392.4	16650.3	16194.8	16167.7
65°	14953.2	14177.9	14844.8	15143.0	15376.1	15511.7	16362.9	17002.7	15994.2	15468.3
67.5°	14568.3	13071.9	12947.2	12963.5	13033.9	13852.6	16037.6	16140.6	14877.3	14443.6
70°	12822.5	10724.3	10556.2	10686.3	10333.9	11320.7	14720.1	14671.3	13126.1	12676.1
72.5°	10371.8	7818.2	7530.8	7709.8	7791.1	8837.5	12383.3	11125.5	9574.8	9222.4
75°	8241.1	5730.8	4836.2	5270.0	5546.5	6435.6	9672.4	7557.9	6685.0	6207.9
77.5°	6473.6	4337.4	3762.7	3589.2	3844.0	4679.0	7037.5	3968.7	3502.5	3280.2
80°	4104.3	3188.0	3459.1	3209.7	3318.1	3339.8	3665.1	1805.4	1436.8	1420.5
82.5°	2472.3	2179.6	2591.6	1425.9	2597.0	2320.5	1523.5	818.7	726.5	726.5
85°	1751.2	1350.0	894.6	580.1	1154.8	1274.1	591.0	422.9	368.7	357.8
87.5°	878.3	417.5	200.6	130.1	146.4	238.6	70.5	32.5	32.5	27.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)