

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P949462

Luminaire Tested: **GLAN-SB4A-950-U-SLR**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P949462
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB4A-950-U-SLR
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(4) 90 CRI, 5000K, 350mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12462 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B2 - U0 - G3


Input Watts (W): 114
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P949462
CATALOG NUMBER: GLAN-SB4A-950-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
- - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 3.4 fc
Type IV - Short - N/A

REPORT NUMBER: P949462
CATALOG NUMBER: GLAN-SB4A-950-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P949462

CATALOG NUMBER: GLAN-SB4A-950-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3167.2	0.0	3167.2
	% Fixture	25.4	0.0	25.4
Street Side	Lumens	9294.8	0.0	9294.8
	% Fixture	74.6	0.0	74.6
Total	Lumens	12462.0	0.0	12462.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.0	1.4
10°-20°	533.6	4.3
20°-30°	824.3	6.6
30°-40°	1044.6	8.4
40°-50°	1575.5	12.6
50°-60°	2545.4	20.4
60°-70°	3173.3	25.5
70°-80°	2080.9	16.7
80°-90°	514.4	4.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	12462.0	100.0
0°-180°	12462.0	100.0

Coefficient of Utilization



REPORT NUMBER: P949462


CATALOG NUMBER: GLAN-SB4A-950-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	838.2	6.7			
FM	(30°-60°)	3634.9	29.2			
FH	(60°-80°)	4397.9	35.3			G2/5000
FVH	(80°-90°)	423.8	3.4			G3/500
BL	(0°-30°)	689.7	5.5	B2/1000		
BM	(30°-60°)	1530.6	12.3	B2/2500		
BH	(60°-80°)	856.3	6.9	B2/1000		G2/1000
BVH	(80°-90°)	90.7	0.7			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type IV Short



REPORT NUMBER: P949462

CATALOG NUMBER: GLAN-SB4A-950-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°
0°	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6
2.5°	1842.8	1828.7	1814.6	1799.5	1784.5	1769.4	1754.3	1739.8	1725.3	1711.3
5°	1981.6	1950.4	1919.1	1888.0	1856.9	1825.5	1794.2	1764.9	1735.7	1708.0
7.5°	2121.0	2069.4	2018.0	1970.3	1922.7	1876.4	1830.0	1789.2	1748.4	1710.7
10°	2227.9	2162.7	2097.5	2034.6	1971.7	1915.4	1859.1	1810.8	1762.4	1715.9
12.5°	2293.3	2221.7	2150.1	2078.8	2007.6	1941.2	1874.7	1820.1	1765.4	1716.6
15°	2333.1	2258.4	2183.8	2106.5	2029.1	1952.7	1876.2	1812.9	1749.7	1695.5
17.5°	2355.4	2279.7	2204.0	2119.7	2035.3	1946.5	1857.8	1781.7	1705.6	1642.0
20°	2380.1	2301.4	2222.7	2130.0	2037.3	1929.7	1822.1	1727.8	1633.5	1559.4
22.5°	2408.7	2328.3	2247.9	2143.9	2039.9	1909.1	1778.2	1664.6	1551.1	1466.7
25°	2445.5	2366.7	2288.0	2169.2	2050.3	1888.7	1727.1	1594.1	1461.1	1374.7
27.5°	2495.5	2420.4	2345.2	2208.7	2072.0	1875.1	1678.1	1529.6	1381.0	1302.3
30°	2562.9	2490.3	2417.8	2259.7	2101.7	1868.7	1635.5	1475.7	1315.8	1249.7
32.5°	2642.5	2570.6	2498.8	2313.1	2127.4	1860.8	1594.1	1429.2	1264.2	1210.9
35°	2739.1	2670.3	2601.5	2373.8	2146.2	1845.9	1545.8	1383.5	1221.1	1176.7
37.5°	2901.9	2814.1	2726.4	2441.9	2157.4	1820.5	1483.6	1329.7	1175.7	1136.9
40°	3147.8	3020.0	2892.1	2528.3	2164.4	1785.4	1406.5	1265.5	1124.4	1089.3
42.5°	3474.0	3289.4	3104.9	2641.3	2177.7	1749.3	1320.9	1194.7	1068.4	1036.0
45°	3876.7	3627.8	3378.9	2790.1	2201.2	1715.7	1230.2	1119.5	1008.7	975.8
47.5°	4380.4	4030.1	3679.8	2948.6	2217.3	1687.9	1158.5	1059.9	961.4	919.0
50°	5040.6	4512.5	3984.4	3095.6	2206.8	1657.7	1108.5	1020.4	932.3	876.5
52.5°	5798.5	5019.2	4240.0	3191.1	2142.0	1606.6	1071.2	994.4	917.6	853.5
55°	6605.3	5468.5	4331.8	3170.0	2008.2	1521.9	1035.5	975.5	915.5	855.8
57.5°	7339.2	5786.9	4234.6	3021.9	1809.3	1402.5	995.6	953.2	910.7	858.1
60°	7782.7	5866.5	3950.2	2746.3	1542.5	1247.4	952.3	919.0	885.6	850.9
62.5°	7557.5	5531.4	3505.4	2373.7	1242.0	1061.8	881.7	859.5	837.4	833.1
65°	7106.7	5057.4	3008.1	1993.5	979.0	894.9	810.8	800.3	789.9	790.4
67.5°	6502.7	4493.3	2483.8	1621.0	758.3	734.4	710.5	716.4	722.1	720.7
70°	5777.1	3877.7	1978.3	1276.3	574.4	581.2	588.0	615.1	642.1	642.1
72.5°	4912.4	3210.4	1508.5	975.8	443.1	463.7	484.3	522.7	561.0	567.5
75°	3818.5	2445.4	1072.4	708.2	344.0	362.7	381.4	424.4	467.4	497.1
77.5°	2728.3	1711.6	694.9	479.9	264.9	277.6	290.3	332.1	373.8	422.8
80°	1785.6	1102.7	419.9	309.2	198.6	203.8	209.1	244.5	279.8	338.3
82.5°	1038.0	638.2	238.6	190.2	141.9	142.8	143.9	169.9	196.0	245.9
85°	456.7	287.1	117.6	101.7	85.8	85.4	84.8	103.9	123.0	160.1
87.5°	141.4	94.0	46.7	42.2	37.6	37.2	36.7	44.5	52.3	67.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949462

CATALOG NUMBER: GLAN-SB4A-950-U-SLR

CANDELA DISTRIBUTION (continued):

50°		55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
1713.6	0°	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6
1695.7	2.5°	1683.1	1670.6	1659.2	1647.9	1637.9	1628.0	1618.0	1608.1	1600.4	1592.6
1680.8	5°	1656.9	1633.1	1613.1	1593.2	1575.5	1557.9	1541.9	1525.9	1513.6	1501.2
1675.4	7.5°	1643.7	1612.0	1585.7	1559.4	1537.3	1515.0	1495.4	1475.9	1461.3	1446.7
1678.0	10°	1644.6	1611.2	1584.9	1558.6	1534.7	1510.8	1488.7	1466.7	1449.2	1431.7
1681.3	12.5°	1653.9	1626.7	1609.2	1591.9	1573.0	1554.4	1531.6	1508.8	1486.4	1464.1
1667.3	15°	1654.2	1641.2	1643.5	1645.9	1641.0	1636.2	1616.4	1596.6	1564.8	1532.9
1624.5	17.5°	1629.3	1634.1	1662.7	1691.4	1706.7	1721.9	1705.9	1690.0	1647.8	1605.7
1554.8	20°	1577.2	1599.5	1649.3	1699.2	1731.1	1763.0	1755.6	1748.2	1700.0	1651.8
1475.7	22.5°	1508.8	1541.9	1598.7	1655.6	1697.1	1738.6	1743.1	1747.5	1701.5	1655.4
1399.0	25°	1437.1	1475.3	1526.4	1577.5	1618.4	1659.2	1674.4	1689.6	1651.9	1614.2
1331.9	27.5°	1368.7	1405.6	1447.6	1489.5	1522.3	1555.0	1572.0	1589.0	1562.1	1535.3
1272.9	30°	1302.1	1331.5	1366.3	1401.2	1428.3	1455.5	1469.3	1483.2	1462.7	1442.2
1221.2	32.5°	1238.5	1255.8	1283.6	1311.5	1337.6	1363.7	1379.0	1394.4	1375.6	1356.7
1172.5	35°	1177.2	1182.0	1203.2	1224.4	1250.2	1276.0	1294.4	1312.8	1299.4	1286.1
1121.3	37.5°	1116.0	1110.8	1126.0	1141.2	1166.9	1192.7	1215.5	1238.2	1232.0	1225.8
1065.3	40°	1053.4	1041.5	1052.4	1063.4	1088.3	1113.1	1139.3	1165.5	1167.1	1168.5
1005.8	42.5°	990.0	974.2	983.1	992.1	1015.7	1039.3	1067.6	1095.8	1103.4	1111.0
946.6	45°	931.2	915.9	923.4	931.0	953.3	975.7	1005.0	1034.4	1045.2	1056.1
893.8	47.5°	880.9	868.0	875.1	882.1	904.0	925.9	954.8	983.7	996.2	1008.7
847.3	50°	835.8	824.5	835.5	846.6	867.3	887.9	913.8	939.7	955.7	971.8
812.6	52.5°	801.3	790.1	806.7	823.3	842.2	861.1	885.2	909.4	928.4	947.4
794.2	55°	776.3	758.5	782.1	805.7	826.0	846.4	867.6	888.7	908.8	929.0
783.2	57.5°	757.1	731.1	756.5	781.9	805.8	829.7	850.6	871.6	891.9	912.2
772.8	60°	739.0	705.2	727.5	749.8	777.2	804.7	826.0	847.3	867.7	888.1
760.7	62.5°	718.5	676.3	690.5	704.6	736.6	768.7	791.4	814.1	832.7	851.4
735.2	65°	690.3	645.4	650.9	656.3	690.6	725.0	746.7	768.4	784.8	801.3
689.7	67.5°	652.3	615.0	613.3	611.5	643.2	675.0	695.6	716.1	730.3	744.5
631.9	70°	605.4	578.8	572.9	567.0	594.8	622.7	640.5	658.2	671.1	683.9
567.6	72.5°	549.4	531.2	522.5	513.9	535.9	557.8	573.8	589.8	602.4	615.0
494.6	75°	480.6	466.5	458.3	449.9	466.2	482.5	497.1	511.6	523.0	534.5
421.5	77.5°	410.3	399.0	390.6	382.2	395.5	408.7	421.2	433.7	445.7	457.7
338.1	80°	328.7	319.3	312.2	305.1	316.2	327.1	337.7	348.2	357.3	366.4
248.7	82.5°	244.1	239.5	234.5	229.5	228.6	227.7	224.0	220.3	239.8	259.2
163.7	85°	158.8	153.9	148.3	142.7	138.0	133.2	123.0	112.8	131.0	149.3
72.3	87.5°	70.4	68.4	67.3	66.3	66.1	65.9	58.1	50.3	57.9	65.6
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949462

CATALOG NUMBER: GLAN-SB4A-950-U-SLR

CANDELA DISTRIBUTION (continued):

105°		110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
1713.6	0°	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6
1586.4	2.5°	1580.1	1575.3	1570.4	1565.9	1561.4	1555.8	1561.4	1565.9	1570.4	1575.3
1492.6	5°	1484.0	1477.9	1471.8	1467.1	1462.4	1457.8	1462.4	1467.1	1471.8	1477.9
1436.4	7.5°	1426.1	1419.1	1412.1	1407.9	1403.8	1400.6	1403.8	1407.9	1412.1	1419.1
1420.2	10°	1408.7	1402.0	1395.4	1391.8	1388.3	1386.8	1388.3	1391.8	1395.4	1402.0
1449.3	12.5°	1434.5	1427.1	1419.7	1416.7	1413.6	1413.1	1413.6	1416.7	1419.7	1427.1
1510.4	15°	1488.0	1477.6	1467.4	1463.4	1459.5	1459.2	1459.5	1463.4	1467.4	1477.6
1572.5	17.5°	1539.4	1524.1	1508.8	1503.8	1498.7	1497.9	1498.7	1503.8	1508.8	1524.1
1611.2	20°	1570.6	1551.1	1531.5	1525.2	1519.0	1517.0	1519.0	1525.2	1531.5	1551.1
1613.6	22.5°	1571.7	1551.1	1530.5	1523.6	1516.7	1513.7	1516.7	1523.6	1530.5	1551.1
1577.0	25°	1539.9	1522.0	1504.2	1497.7	1491.2	1487.4	1491.2	1497.7	1504.2	1522.0
1506.4	27.5°	1477.6	1465.6	1453.6	1450.6	1447.6	1446.7	1447.6	1450.6	1453.6	1465.6
1421.5	30°	1400.8	1394.6	1388.5	1388.5	1388.5	1389.4	1388.5	1388.5	1388.5	1394.6
1340.2	32.5°	1323.7	1319.7	1315.7	1316.2	1316.8	1317.8	1316.8	1316.2	1315.7	1319.7
1270.8	35°	1255.6	1249.5	1243.5	1242.2	1240.8	1240.2	1240.8	1242.2	1243.5	1249.5
1211.8	37.5°	1197.8	1186.7	1175.6	1169.8	1163.9	1160.6	1163.9	1169.8	1175.6	1186.7
1156.6	40°	1144.7	1128.5	1112.5	1101.6	1090.8	1084.3	1090.8	1101.6	1112.5	1128.5
1100.9	42.5°	1090.9	1070.9	1050.8	1035.0	1019.1	1008.7	1019.1	1035.0	1050.8	1070.9
1047.0	45°	1038.0	1015.0	992.1	973.5	954.9	943.0	954.9	973.5	992.1	1015.0
1002.4	47.5°	996.1	975.7	955.3	938.1	920.9	909.4	920.9	938.1	955.3	975.7
971.4	50°	971.1	954.8	938.5	922.6	906.7	895.6	906.7	922.6	938.5	954.8
950.8	52.5°	954.3	941.0	927.7	913.4	899.2	889.0	899.2	913.4	927.7	941.0
933.8	55°	938.5	926.9	915.3	902.8	890.4	881.1	890.4	902.8	915.3	926.9
917.0	57.5°	921.8	910.1	898.4	886.0	873.6	864.0	873.6	886.0	898.4	910.1
893.3	60°	898.6	887.1	875.8	863.0	850.2	840.4	850.2	863.0	875.8	887.1
856.5	62.5°	861.6	851.2	840.9	827.5	814.1	802.2	814.1	827.5	840.9	851.2
806.4	65°	811.6	801.6	791.7	778.7	765.7	755.6	765.7	778.7	791.7	801.6
749.6	67.5°	754.6	745.4	736.3	724.2	712.2	702.9	712.2	724.2	736.3	745.4
688.7	70°	693.6	686.2	678.7	667.2	655.6	645.1	655.6	667.2	678.7	686.2
620.7	72.5°	626.5	620.4	614.2	603.1	592.1	582.0	592.1	603.1	614.2	620.4
540.5	75°	546.6	543.5	540.5	531.3	522.0	512.2	522.0	531.3	540.5	543.5
463.3	77.5°	469.0	464.8	460.4	451.1	441.8	434.0	441.8	451.1	460.4	464.8
373.9	80°	381.4	379.6	377.8	365.2	352.6	338.0	352.6	365.2	377.8	379.6
272.0	82.5°	284.7	283.9	283.1	272.5	261.8	252.5	261.8	272.5	283.1	283.9
165.1	85°	180.8	179.5	178.2	169.9	161.6	153.2	161.6	169.9	178.2	179.5
72.0	87.5°	78.4	76.8	75.1	70.9	66.5	62.5	66.5	70.9	75.1	76.8
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949462

CATALOG NUMBER: GLAN-SB4A-950-U-SLR

CANDELA DISTRIBUTION (continued):

160°		165°	170°	175°	180°	185°	190°	195°	200°	205°	210°
1713.6	0°	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6
1580.1	2.5°	1586.4	1592.6	1600.4	1608.1	1618.0	1628.0	1637.9	1647.9	1659.2	1670.6
1484.0	5°	1492.6	1501.2	1513.6	1525.9	1541.9	1557.9	1575.5	1593.2	1613.1	1633.1
1426.1	7.5°	1436.4	1446.7	1461.3	1475.9	1495.4	1515.0	1537.3	1559.4	1585.7	1612.0
1408.7	10°	1420.2	1431.7	1449.2	1466.7	1488.7	1510.8	1534.7	1558.6	1584.9	1611.2
1434.5	12.5°	1449.3	1464.1	1486.4	1508.8	1531.6	1554.4	1573.0	1591.9	1609.2	1626.7
1488.0	15°	1510.4	1532.9	1564.8	1596.6	1616.4	1636.2	1641.0	1645.9	1643.5	1641.2
1539.4	17.5°	1572.5	1605.7	1647.8	1690.0	1705.9	1721.9	1706.7	1691.4	1662.7	1634.1
1570.6	20°	1611.2	1651.8	1700.0	1748.2	1755.6	1763.0	1731.1	1699.2	1649.3	1599.5
1571.7	22.5°	1613.6	1655.4	1701.5	1747.5	1743.1	1738.6	1697.1	1655.6	1598.7	1541.9
1539.9	25°	1577.0	1614.2	1651.9	1689.6	1674.4	1659.2	1618.4	1577.5	1526.4	1475.3
1477.6	27.5°	1506.4	1535.3	1562.1	1589.0	1572.0	1555.0	1522.3	1489.5	1447.6	1405.6
1400.8	30°	1421.5	1442.2	1462.7	1483.2	1469.3	1455.5	1428.3	1401.2	1366.3	1331.5
1323.7	32.5°	1340.2	1356.7	1375.6	1394.4	1379.0	1363.7	1337.6	1311.5	1283.6	1255.8
1255.6	35°	1270.8	1286.1	1299.4	1312.8	1294.4	1276.0	1250.2	1224.4	1203.2	1182.0
1197.8	37.5°	1211.8	1225.8	1232.0	1238.2	1215.5	1192.7	1166.9	1141.2	1126.0	1110.8
1144.7	40°	1156.6	1168.5	1167.1	1165.5	1139.3	1113.1	1088.3	1063.4	1052.4	1041.5
1090.9	42.5°	1100.9	1111.0	1103.4	1095.8	1067.6	1039.3	1015.7	992.1	983.1	974.2
1038.0	45°	1047.0	1056.1	1045.2	1034.4	1005.0	975.7	953.3	931.0	923.4	915.9
996.1	47.5°	1002.4	1008.7	996.2	983.7	954.8	925.9	904.0	882.1	875.1	868.0
971.1	50°	971.4	971.8	955.7	939.7	913.8	887.9	867.3	846.6	835.5	824.5
954.3	52.5°	950.8	947.4	928.4	909.4	885.2	861.1	842.2	823.3	806.7	790.1
938.5	55°	933.8	929.0	908.8	888.7	867.6	846.4	826.0	805.7	782.1	758.5
921.8	57.5°	917.0	912.2	891.9	871.6	850.6	829.7	805.8	781.9	756.5	731.1
898.6	60°	893.3	888.1	867.7	847.3	826.0	804.7	777.2	749.8	727.5	705.2
861.6	62.5°	856.5	851.4	832.7	814.1	791.4	768.7	736.6	704.6	690.5	676.3
811.6	65°	806.4	801.3	784.8	768.4	746.7	725.0	690.6	656.3	650.9	645.4
754.6	67.5°	749.6	744.5	730.3	716.1	695.6	675.0	643.2	611.5	613.3	615.0
693.6	70°	688.7	683.9	671.1	658.2	640.5	622.7	594.8	567.0	572.9	578.8
626.5	72.5°	620.7	615.0	602.4	589.8	573.8	557.8	535.9	513.9	522.5	531.2
546.6	75°	540.5	534.5	523.0	511.6	497.1	482.5	466.2	449.9	458.3	466.5
469.0	77.5°	463.3	457.7	445.7	433.7	421.2	408.7	395.5	382.2	390.6	399.0
381.4	80°	373.9	366.4	357.3	348.2	337.7	327.1	316.2	305.1	312.2	319.3
284.7	82.5°	272.0	259.2	239.8	220.3	224.0	227.7	228.6	229.5	234.5	239.5
180.8	85°	165.1	149.3	131.0	112.8	123.0	133.2	138.0	142.7	148.3	153.9
78.4	87.5°	72.0	65.6	57.9	50.3	58.1	65.9	66.1	66.3	67.3	68.4
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949462

CATALOG NUMBER: GLAN-SB4A-950-U-SLR

CANDELA DISTRIBUTION (continued):

215°		220°	225°	230°	235°	240°	245°	250°	255°	260°	265°
1713.6	0°	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6
1683.1	2.5°	1695.7	1711.3	1725.3	1739.8	1754.3	1769.4	1784.5	1799.5	1814.6	1828.7
1656.9	5°	1680.8	1708.0	1735.7	1764.9	1794.2	1825.5	1856.9	1888.0	1919.1	1950.4
1643.7	7.5°	1675.4	1710.7	1748.4	1789.2	1830.0	1876.4	1922.7	1970.3	2018.0	2069.4
1644.6	10°	1678.0	1715.9	1762.4	1810.8	1859.1	1915.4	1971.7	2034.6	2097.5	2162.7
1653.9	12.5°	1681.3	1716.6	1765.4	1820.1	1874.7	1941.2	2007.6	2078.8	2150.1	2221.7
1654.2	15°	1667.3	1695.5	1749.7	1812.9	1876.2	1952.7	2029.1	2106.5	2183.8	2258.4
1629.3	17.5°	1624.5	1642.0	1705.6	1781.7	1857.8	1946.5	2035.3	2119.7	2204.0	2279.7
1577.2	20°	1554.8	1559.4	1633.5	1727.8	1822.1	1929.7	2037.3	2130.0	2222.7	2301.4
1508.8	22.5°	1475.7	1466.7	1551.1	1664.6	1778.2	1909.1	2039.9	2143.9	2247.9	2328.3
1437.1	25°	1399.0	1374.7	1461.1	1594.1	1727.1	1888.7	2050.3	2169.2	2288.0	2366.7
1368.7	27.5°	1331.9	1302.3	1381.0	1529.6	1678.1	1875.1	2072.0	2208.7	2345.2	2420.4
1302.1	30°	1272.9	1249.7	1315.8	1475.7	1635.5	1868.7	2101.7	2259.7	2417.8	2490.3
1238.5	32.5°	1221.2	1210.9	1264.2	1429.2	1594.1	1860.8	2127.4	2313.1	2498.8	2570.6
1177.2	35°	1172.5	1176.7	1221.1	1383.5	1545.8	1845.9	2146.2	2373.8	2601.5	2670.3
1116.0	37.5°	1121.3	1136.9	1175.7	1329.7	1483.6	1820.5	2157.4	2441.9	2726.4	2814.1
1053.4	40°	1065.3	1089.3	1124.4	1265.5	1406.5	1785.4	2164.4	2528.3	2892.1	3020.0
990.0	42.5°	1005.8	1036.0	1068.4	1194.7	1320.9	1749.3	2177.7	2641.3	3104.9	3289.4
931.2	45°	946.6	975.8	1008.7	1119.5	1230.2	1715.7	2201.2	2790.1	3378.9	3627.8
880.9	47.5°	893.8	919.0	961.4	1059.9	1158.5	1687.9	2217.3	2948.6	3679.8	4030.1
835.8	50°	847.3	876.5	932.3	1020.4	1108.5	1657.7	2206.8	3095.6	3984.4	4512.5
801.3	52.5°	812.6	853.5	917.6	994.4	1071.2	1606.6	2142.0	3191.1	4240.0	5019.2
776.3	55°	794.2	855.8	915.5	975.5	1035.5	1521.9	2008.2	3170.0	4331.8	5468.5
757.1	57.5°	783.2	858.1	910.7	953.2	995.6	1402.5	1809.3	3021.9	4234.6	5786.9
739.0	60°	772.8	850.9	885.6	919.0	952.3	1247.4	1542.5	2746.3	3950.2	5866.5
718.5	62.5°	760.7	833.1	837.4	859.5	881.7	1061.8	1242.0	2373.7	3505.4	5531.4
690.3	65°	735.2	790.4	789.9	800.3	810.8	894.9	979.0	1993.5	3008.1	5057.4
652.3	67.5°	689.7	720.7	722.1	716.4	710.5	734.4	758.3	1621.0	2483.8	4493.3
605.4	70°	631.9	642.1	642.1	615.1	588.0	581.2	574.4	1276.3	1978.3	3877.7
549.4	72.5°	567.6	567.5	561.0	522.7	484.3	463.7	443.1	975.8	1508.5	3210.4
480.6	75°	494.6	497.1	467.4	424.4	381.4	362.7	344.0	708.2	1072.4	2445.4
410.3	77.5°	421.5	422.8	373.8	332.1	290.3	277.6	264.9	479.9	694.9	1711.6
328.7	80°	338.1	338.3	279.8	244.5	209.1	203.8	198.6	309.2	419.9	1102.7
244.1	82.5°	248.7	245.9	196.0	169.9	143.9	142.8	141.9	190.2	238.6	638.2
158.8	85°	163.7	160.1	123.0	103.9	84.8	85.4	85.8	101.7	117.6	287.1
70.4	87.5°	72.3	67.7	52.3	44.5	36.7	37.2	37.6	42.2	46.7	94.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949462

CATALOG NUMBER: GLAN-SB4A-950-U-SLR

CANDELA DISTRIBUTION (continued):

270°		275°	280°	285°	290°	295°	300°	305°	310°	315°	320°
1713.6	0°	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6
1842.8	2.5°	1849.8	1856.9	1866.8	1876.7	1882.6	1888.5	1891.5	1894.5	1893.1	1894.5
1981.6	5°	2006.0	2030.5	2054.6	2078.9	2092.1	2105.2	2113.2	2121.2	2127.2	2121.2
2121.0	7.5°	2160.7	2200.4	2236.1	2271.8	2293.3	2314.8	2326.4	2338.0	2343.6	2338.0
2227.9	10°	2274.8	2321.8	2363.6	2405.5	2430.9	2456.2	2467.5	2478.7	2483.0	2478.7
2293.3	12.5°	2344.2	2395.0	2432.9	2470.6	2489.0	2507.5	2513.6	2519.8	2520.5	2519.8
2333.1	15°	2377.0	2420.9	2444.6	2468.4	2469.1	2469.7	2463.1	2456.6	2448.8	2456.6
2355.4	17.5°	2385.1	2414.7	2415.2	2415.6	2389.0	2362.3	2337.9	2313.5	2296.2	2313.5
2380.1	20°	2390.4	2400.8	2369.6	2338.3	2279.5	2220.8	2177.9	2135.1	2108.8	2135.1
2408.7	22.5°	2395.1	2381.6	2316.9	2252.2	2165.7	2079.2	2025.7	1972.2	1943.1	1972.2
2445.5	25°	2402.8	2360.0	2261.8	2163.5	2058.5	1953.5	1897.2	1841.1	1813.6	1841.1
2495.5	27.5°	2419.1	2342.6	2212.5	2082.4	1966.0	1849.6	1794.3	1738.9	1713.0	1738.9
2562.9	30°	2448.9	2335.0	2174.9	2014.7	1893.4	1772.2	1720.8	1669.4	1645.2	1669.4
2642.5	32.5°	2486.4	2330.4	2149.2	1968.0	1854.0	1740.1	1699.8	1659.4	1642.0	1659.4
2739.1	35°	2548.2	2357.3	2168.4	1979.6	1900.4	1821.3	1811.9	1802.5	1801.1	1802.5
2901.9	37.5°	2677.2	2452.6	2281.0	2109.4	2104.2	2099.1	2142.1	2185.1	2207.5	2185.1
3147.8	40°	2903.5	2659.2	2531.6	2404.0	2494.0	2584.1	2688.7	2793.2	2845.3	2793.2
3474.0	42.5°	3231.6	2989.2	2915.7	2842.2	3038.6	3235.1	3425.3	3615.5	3727.1	3615.5
3876.7	45°	3659.0	3441.2	3408.8	3376.3	3691.1	4005.9	4318.4	4630.9	4820.7	4630.9
4380.4	47.5°	4168.6	3956.7	3950.2	3943.6	4397.7	4851.7	5309.2	5766.6	6035.2	5766.6
5040.6	50°	4779.0	4517.4	4518.5	4519.6	5104.9	5690.1	6293.9	6897.8	7262.9	6897.8
5798.5	52.5°	5481.7	5164.9	5132.9	5100.8	5799.8	6498.9	7246.0	7993.1	8430.7	7993.1
6605.3	55°	6292.3	5979.3	5854.4	5729.6	6507.6	7285.6	8176.2	9066.9	9587.4	9066.9
7339.2	57.5°	7168.7	6998.2	6747.7	6497.3	7282.9	8068.5	9077.4	10086.2	10731.6	10086.2
7782.7	60°	8047.4	8312.2	8001.2	7690.2	8433.6	9177.1	10257.2	11337.3	12034.9	11337.3
7557.5	62.5°	8280.9	9004.3	8969.2	8934.1	9615.1	10296.3	11323.9	12351.5	12996.3	12351.5
7106.7	65°	7785.7	8464.6	8598.9	8733.2	9598.7	10464.3	11460.8	12457.2	13006.1	12457.2
6502.7	67.5°	7148.5	7794.2	7857.2	7920.1	8821.9	9723.6	10724.4	11725.2	12155.2	11725.2
5777.1	70°	6479.5	7181.9	7210.0	7238.2	8044.7	8851.0	9712.3	10573.4	10812.5	10573.4
4912.4	72.5°	5718.4	6524.4	6544.7	6564.9	7195.8	7826.7	8471.8	9116.7	9140.9	9116.7
3818.5	75°	4652.7	5486.9	5561.8	5636.7	6127.6	6618.5	7072.5	7526.6	7404.9	7526.6
2728.3	77.5°	3507.0	4285.7	4392.9	4500.1	4873.3	5246.4	5568.5	5890.5	5681.4	5890.5
1785.6	80°	2440.8	3095.8	3229.1	3362.3	3644.1	3925.8	4095.0	4264.0	3927.7	4264.0
1038.0	82.5°	1485.8	1933.8	2082.6	2231.5	2425.5	2619.4	2690.0	2760.5	2496.1	2760.5
456.7	85°	694.4	932.1	1058.7	1185.3	1344.7	1504.0	1544.0	1584.1	1372.4	1584.1
141.4	87.5°	221.3	301.2	371.8	442.4	522.1	601.8	605.2	608.6	510.9	608.6
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949462

CATALOG NUMBER: GLAN-SB4A-950-U-SLR

CANDELA DISTRIBUTION (continued):

325°		330°	335°	340°	345°	350°	355°	360°
1713.6	0°	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6	1713.6
1891.5	2.5°	1888.5	1882.6	1876.7	1866.8	1856.9	1849.8	1842.8
2113.2	5°	2105.2	2092.1	2078.9	2054.6	2030.5	2006.0	1981.6
2326.4	7.5°	2314.8	2293.3	2271.8	2236.1	2200.4	2160.7	2121.0
2467.5	10°	2456.2	2430.9	2405.5	2363.6	2321.8	2274.8	2227.9
2513.6	12.5°	2507.5	2489.0	2470.6	2432.9	2395.0	2344.2	2293.3
2463.1	15°	2469.7	2469.1	2468.4	2444.6	2420.9	2377.0	2333.1
2337.9	17.5°	2362.3	2389.0	2415.6	2415.2	2414.7	2385.1	2355.4
2177.9	20°	2220.8	2279.5	2338.3	2369.6	2400.8	2390.4	2380.1
2025.7	22.5°	2079.2	2165.7	2252.2	2316.9	2381.6	2395.1	2408.7
1897.2	25°	1953.5	2058.5	2163.5	2261.8	2360.0	2402.8	2445.5
1794.3	27.5°	1849.6	1966.0	2082.4	2212.5	2342.6	2419.1	2495.5
1720.8	30°	1772.2	1893.4	2014.7	2174.9	2335.0	2448.9	2562.9
1699.8	32.5°	1740.1	1854.0	1968.0	2149.2	2330.4	2486.4	2642.5
1811.9	35°	1821.3	1900.4	1979.6	2168.4	2357.3	2548.2	2739.1
2142.1	37.5°	2099.1	2104.2	2109.4	2281.0	2452.6	2677.2	2901.9
2688.7	40°	2584.1	2494.0	2404.0	2531.6	2659.2	2903.5	3147.8
3425.3	42.5°	3235.1	3038.6	2842.2	2915.7	2989.2	3231.6	3474.0
4318.4	45°	4005.9	3691.1	3376.3	3408.8	3441.2	3659.0	3876.7
5309.2	47.5°	4851.7	4397.7	3943.6	3950.2	3956.7	4168.6	4380.4
6293.9	50°	5690.1	5104.9	4519.6	4518.5	4517.4	4779.0	5040.6
7246.0	52.5°	6498.9	5799.8	5100.8	5132.9	5164.9	5481.7	5798.5
8176.2	55°	7285.6	6507.6	5729.6	5854.4	5979.3	6292.3	6605.3
9077.4	57.5°	8068.5	7282.9	6497.3	6747.7	6998.2	7168.7	7339.2
10257.2	60°	9177.1	8433.6	7690.2	8001.2	8312.2	8047.4	7782.7
11323.9	62.5°	10296.3	9615.1	8934.1	8969.2	9004.3	8280.9	7557.5
11460.8	65°	10464.3	9598.7	8733.2	8598.9	8464.6	7785.7	7106.7
10724.4	67.5°	9723.6	8821.9	7920.1	7857.2	7794.2	7148.5	6502.7
9712.3	70°	8851.0	8044.7	7238.2	7210.0	7181.9	6479.5	5777.1
8471.8	72.5°	7826.7	7195.8	6564.9	6544.7	6524.4	5718.4	4912.4
7072.5	75°	6618.5	6127.6	5636.7	5561.8	5486.9	4652.7	3818.5
5568.5	77.5°	5246.4	4873.3	4500.1	4392.9	4285.7	3507.0	2728.3
4095.0	80°	3925.8	3644.1	3362.3	3229.1	3095.8	2440.8	1785.6
2690.0	82.5°	2619.4	2425.5	2231.5	2082.6	1933.8	1485.8	1038.0
1544.0	85°	1504.0	1344.7	1185.3	1058.7	932.1	694.4	456.7
605.2	87.5°	601.8	522.1	442.4	371.8	301.2	221.3	141.4
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)