

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599559

Luminaire Tested: **IFLD-M-SA4A-760-U-SLL-HSS**

Issue Date: 05/04/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P599559
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/04/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-M-SA4A-760-U-SLL-HSS
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens with House Side Shield
 Light Source: (64) 5700K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 13758.5 lumens
 Efficiency: N/A
 Efficacy: 107.0 lumens/watt
 Spacing Criteria (0/90/45): 0.53 / 0.46 / 0.63
 Luminous Opening: Rectangular (W 2' x L: 0.5' x H: 0')
 CIE Type: Direct

Input Watts (W): 128.6
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599559
CATALOG NUMBER: IFLD-M-SA4A-760-U-SLL-HSS

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ··· 90°-270° - · 135°-315°

TEST NUMBER: P599559
 CATALOG NUMBER: IFLD-M-SA4A-760-U-SLL-HSS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	106	100	95	90	103	98	93	89	94	90	86	90	86	83	86	83	81	79				
2	94	84	76	69	91	82	75	68	78	72	66	75	70	65	72	67	63	61				
3	84	72	62	54	81	70	61	53	67	59	52	64	57	51	61	55	50	48				
4	76	62	51	44	73	60	51	43	58	49	43	55	48	42	53	46	41	39				
5	69	54	44	36	67	53	43	36	51	42	35	48	41	35	46	40	34	32				
6	63	48	38	30	61	47	37	30	45	36	30	43	35	30	41	35	29	27				
7	58	43	33	26	56	42	33	26	40	32	26	39	31	26	37	31	25	23				
8	54	39	29	23	52	38	29	23	37	28	23	35	28	22	34	27	22	20				
9	50	35	26	20	49	35	26	20	34	26	20	32	25	20	31	25	20	18				
10	47	33	24	18	46	32	24	18	31	23	18	30	23	18	29	23	18	16				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	55683	55683	55683	55683
5°	58516	55697	40691	40929
10°	50317	48390	22247	21725
15°	48926	46511	14453	10891
20°	56395	54038	7743	3872
25°	70908	66326	5018	3011
30°	85167	79367	4064	2466
35°	100855	94626	3331	1979
40°	121681	114557	2942	1496
45°	138535	132495	2740	1006
50°	155412	149383	2708	615
55°	175750	175131	2689	276
60°	216878	222021	2452	80
65°	241992	266883	2246	0
70°	246753	301215	2080	0
75°	200777	222170	1988	0
80°	145985	92918	2052	0
85°	94380	39027	2717	0

TEST NUMBER: P599559
 CATALOG NUMBER: IFLD-M-SA4A-760-U-SLL-HSS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	393.0	2.9
10°-20°	770.7	5.6
20°-30°	1066.5	7.8
30°-40°	1507.2	11.0
40°-50°	2052.0	14.9
50°-60°	2717.8	19.8
60°-70°	3155.6	22.9
70°-80°	1787.0	13.0
80°-90°	308.8	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2230.1	16.2
0°-40°	3737.3	27.2
0°-60°	8507.1	61.8
0°-90°	13758.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13758.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	5173	5173	5173	5173	5173	
5°	5416	5155	3766	3788	5416	486
15°	4390	4174	1297	977	4390	1288
25°	5970	5585	422	254	5970	2785
35°	7675	7201	254	151	7675	4838
45°	9101	8704	180	66	9101	7056
55°	9365	9332	143	15	9365	8485
65°	9501	10478	88	0	9501	9262
75°	4828	5342	48	0	4828	5269
85°	764	316	22	0	764	918
90°	0	0	0	0	0	

TEST NUMBER: P599559
 CATALOG NUMBER: IFLD-M-SA4A-760-U-SLL-HSS

CANDELA DISTRIBUTION (FULL):

	0°	2°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1
2.5°	5375.2	5489.1	5492.8	5544.2	5595.6	5595.6	5716.9	5687.5	5580.9	5562.6	5485.4
5°	5415.6	5456.0	5485.4	5746.3	5966.7	5944.7	6010.8	5966.7	5761.0	5496.4	5316.4
7.5°	5066.6	5110.7	5228.2	5672.8	5970.4	6069.6	6194.5	5919.0	5702.2	5224.5	4879.2
10°	4603.6	4688.1	4904.9	5411.9	5779.3	6095.3	6095.3	5874.9	5456.0	4989.4	4566.9
12.5°	4346.4	4515.4	4633.0	5147.4	5625.0	5841.8	5834.4	5716.9	5445.0	4857.1	4379.5
15°	4390.5	4438.3	4688.1	5088.6	5404.6	5393.6	5525.8	5489.1	5298.0	4974.7	4449.3
17.5°	4592.6	4666.1	4882.9	5088.6	5239.2	5195.2	5191.5	5367.8	5378.9	5173.1	4710.2
20°	4923.3	5140.0	5242.9	5305.4	5121.7	4934.3	4912.3	5158.4	5349.5	5426.6	5022.5
22.5°	5452.3	5595.6	5805.1	5485.4	5007.8	4772.6	4728.5	5000.4	5386.2	5727.9	5426.6
25°	5970.4	6080.6	6282.7	5871.2	5136.4	4739.6	4662.4	4897.6	5525.8	6146.7	5915.3
27.5°	6517.8	6613.4	6635.4	6154.1	5206.2	4673.4	4581.6	4897.6	5643.4	6367.2	6499.5
30°	6852.2	6966.1	6988.1	6403.9	5320.1	4728.5	4684.5	4919.6	5724.2	6554.6	6918.3
32.5°	7226.9	7256.3	7237.9	6448.0	5445.0	4890.2	4706.5	5066.6	5816.1	6778.7	7300.4
35°	7675.2	7726.6	7539.2	6650.1	5724.2	4993.1	4926.9	5246.6	5974.1	6881.6	7763.3
37.5°	8016.9	8178.5	7756.0	6727.2	5779.3	5209.9	5220.9	5621.3	6084.3	7006.5	8274.0
40°	8659.8	8387.9	8123.4	6991.8	5988.8	5577.3	5518.5	6007.1	6455.4	7087.3	8608.4
42.5°	9012.5	8869.2	8266.7	7017.5	6312.1	6084.3	6099.0	6444.3	6650.1	7315.1	8700.2
45°	9100.7	8950.1	8461.4	7035.9	6631.7	6683.2	6936.7	7002.8	6936.7	7465.7	8872.9
47.5°	9324.8	8997.8	8439.4	7282.0	7149.8	7348.2	7671.5	7814.8	7326.1	7410.6	8953.7
50°	9280.7	9093.4	8391.6	7384.9	7781.7	8307.1	8523.9	8465.1	7759.7	7296.7	8865.6
52.5°	9097.0	8895.0	8538.6	7664.1	8373.2	9008.9	9310.1	9163.2	8145.4	7553.9	8806.8
55°	9365.2	9210.9	8729.6	8042.6	8817.8	9626.1	9839.2	9729.0	8619.4	7792.7	9141.1
57.5°	9655.5	9622.4	9247.7	8487.1	9343.2	10261.7	10261.7	10125.8	9030.9	8138.1	9637.1
60°	10074.3	10147.8	9629.8	8781.1	9523.2	10225.0	10757.7	10599.7	9446.1	8744.3	10199.3
62.5°	9938.4	10173.5	10122.1	9413.0	9729.0	10405.0	10695.3	10812.8	9960.4	9482.8	10948.8
65°	9501.2	9751.0	10118.4	9828.2	9574.7	9967.8	10114.8	10471.1	10217.6	10177.2	11257.4
67.5°	8979.5	9251.3	9479.1	10107.4	9262.4	9523.2	9394.6	9508.5	9938.4	10937.7	11433.8
70°	7840.5	8101.4	8461.4	9486.5	8435.7	8200.6	8167.5	8112.4	8781.1	10665.9	10632.8
72.5°	6448.0	6569.3	7164.5	7711.9	6242.3	6198.2	6249.6	6187.2	6962.4	9655.5	9108.1
75°	4827.7	4949.0	5287.0	5922.6	4250.9	3997.4	4291.3	4581.6	5316.4	7495.1	6543.5
77.5°	3630.0	3784.3	3997.4	4430.9	3119.3	2722.5	2762.9	3038.5	3843.1	6003.5	3666.7
80°	2355.1	2336.7	2748.2	3049.5	2347.7	2421.2	2318.3	2520.4	2785.0	3211.1	1873.8
82.5°	1359.4	1377.8	1550.5	1748.9	1635.0	1870.1	1348.4	2252.2	1987.7	1308.0	698.1
85°	764.2	797.3	955.3	1212.4	1025.1	687.1	562.1	1116.9	1249.2	536.4	338.0
87.5°	77.2	66.1	128.6	459.3	279.2	113.9	169.0	268.2	301.3	202.1	99.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599559
 CATALOG NUMBER: IFLD-M-SA4A-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1
2.5°	5375.2	5375.2	5283.3	5129.0	5066.6	4956.3	4805.7	4853.5	4802.0	4614.7	4566.9
5°	5154.7	4978.4	4787.3	4552.2	4416.2	4137.0	4048.8	3890.9	3916.6	3758.6	3765.9
7.5°	4695.5	4555.9	4232.5	3923.9	3655.7	3413.2	3071.5	2942.9	2818.0	2755.6	2829.0
10°	4427.3	4166.4	3725.5	3321.4	2965.0	2748.2	2520.4	2344.1	2182.4	2061.2	2035.4
12.5°	4232.5	4001.1	3468.3	2976.0	2696.8	2520.4	2311.0	2068.5	1910.5	1701.1	1638.6
15°	4173.8	3890.9	3328.7	2840.1	2568.2	2277.9	2039.1	1800.3	1594.6	1374.1	1297.0
17.5°	4375.8	4048.8	3325.0	2729.8	2347.7	2035.4	1704.8	1436.6	1227.1	1025.1	977.3
20°	4717.5	4217.8	3431.6	2663.7	2138.3	1719.5	1344.7	1076.5	841.4	709.1	676.0
22.5°	5107.0	4504.4	3442.6	2487.4	1928.9	1403.5	981.0	709.1	576.8	514.4	496.0
25°	5584.6	4963.7	3574.9	2344.1	1682.7	1065.5	698.1	543.8	466.6	429.9	422.5
27.5°	5977.7	5283.3	3718.2	2193.4	1440.2	789.9	547.4	444.6	404.1	367.4	363.7
30°	6385.6	5650.7	3758.6	2101.6	1230.8	650.3	470.3	393.1	349.0	330.7	327.0
32.5°	6741.9	6051.2	3887.2	1950.9	1032.4	573.2	426.2	352.7	323.3	293.9	290.3
35°	7201.2	6282.7	3949.6	1870.1	958.9	518.0	389.5	323.3	279.2	260.9	253.5
37.5°	7693.5	6506.8	3990.1	1807.6	896.5	485.0	367.4	304.9	264.5	238.8	231.5
40°	8152.8	6822.8	3931.3	1730.5	848.7	444.6	352.7	282.9	246.2	220.4	209.4
42.5°	8505.5	7131.4	3912.9	1657.0	797.3	429.9	334.3	271.9	231.5	202.1	198.4
45°	8703.9	7340.8	3784.3	1598.2	756.9	437.2	327.0	257.2	220.4	194.7	180.0
47.5°	8656.1	7502.5	3817.4	1579.9	701.8	407.8	323.3	246.2	202.1	180.0	169.0
50°	8920.7	7829.5	3762.3	1521.1	661.3	367.4	352.7	246.2	198.4	172.7	161.7
52.5°	8964.8	8127.1	3879.8	1414.5	598.9	338.0	349.0	242.5	191.1	165.3	150.6
55°	9332.2	8472.4	4107.6	1355.7	547.4	293.9	319.6	235.1	172.7	150.6	143.3
57.5°	9831.8	9188.9	4254.6	1300.6	477.6	257.2	268.2	231.5	158.0	139.6	128.6
60°	10313.2	9475.5	4265.6	1201.4	411.5	231.5	209.4	231.5	147.0	124.9	113.9
62.5°	10673.2	9475.5	4192.1	1116.9	360.1	205.7	183.7	220.4	132.3	110.2	102.9
65°	10478.5	9222.0	4001.1	1047.1	327.0	180.0	158.0	169.0	117.6	95.5	88.2
67.5°	10129.5	8432.0	3578.6	962.6	323.3	158.0	135.9	124.9	102.9	84.5	77.2
70°	9571.0	7366.5	2979.7	867.1	316.0	143.3	121.2	106.5	91.9	73.5	66.1
72.5°	7711.9	6084.3	2446.9	812.0	308.6	124.9	102.9	91.9	77.2	62.5	55.1
75°	5342.1	3887.2	1884.8	694.4	301.3	113.9	95.5	80.8	66.1	51.4	47.8
77.5°	3203.8	2597.6	1216.1	521.7	198.4	91.9	80.8	62.5	55.1	44.1	40.4
80°	1499.0	1227.1	492.3	202.1	95.5	66.1	55.1	47.8	44.1	36.7	33.1
82.5°	587.9	518.0	238.8	117.6	77.2	51.4	44.1	40.4	36.7	29.4	25.7
85°	316.0	279.2	113.9	80.8	55.1	36.7	36.7	33.1	29.4	25.7	22.0
87.5°	69.8	51.4	47.8	47.8	40.4	29.4	29.4	25.7	22.0	18.4	14.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599559
 CATALOG NUMBER: IFLD-M-SA4A-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1
2.5°	4541.2	4596.3	4508.1	4563.2	4486.1	4544.8	4552.2	4497.1	4511.8	4585.3	4618.3
5°	3868.8	3832.1	3751.2	3725.5	3729.2	3681.4	3699.8	3725.5	3765.9	3788.0	3854.1
7.5°	2788.6	2873.1	2869.5	2931.9	2935.6	2928.2	2876.8	2766.6	2803.3	2773.9	2810.7
10°	1995.0	2031.8	2101.6	2142.0	2215.5	2175.1	2057.5	2013.4	1991.4	1987.7	2024.4
12.5°	1594.6	1506.4	1499.0	1513.7	1550.5	1502.7	1443.9	1392.5	1418.2	1469.6	1510.0
15°	1234.5	1161.0	1065.5	1050.8	1058.1	1036.1	973.6	907.5	925.9	977.3	1006.7
17.5°	947.9	863.4	797.3	753.2	738.5	661.3	569.5	514.4	499.7	496.0	521.7
20°	639.3	624.6	613.6	558.5	558.5	448.2	371.1	330.7	330.7	338.0	341.7
22.5°	477.6	459.3	462.9	451.9	422.5	334.3	293.9	282.9	282.9	290.3	290.3
25°	415.2	389.5	382.1	378.4	349.0	286.6	257.2	246.2	246.2	253.5	253.5
27.5°	352.7	345.4	334.3	319.6	293.9	246.2	227.8	216.8	220.4	224.1	220.4
30°	323.3	304.9	290.3	290.3	260.9	220.4	205.7	198.4	191.1	198.4	202.1
32.5°	286.6	275.6	268.2	257.2	224.1	194.7	180.0	172.7	169.0	169.0	172.7
35°	246.2	246.2	238.8	224.1	194.7	176.4	158.0	150.6	147.0	150.6	150.6
37.5°	220.4	209.4	213.1	198.4	172.7	154.3	135.9	128.6	128.6	124.9	128.6
40°	205.7	187.4	176.4	169.0	154.3	132.3	117.6	110.2	106.5	106.5	106.5
42.5°	183.7	169.0	147.0	143.3	139.6	113.9	95.5	91.9	88.2	84.5	84.5
45°	172.7	150.6	132.3	113.9	113.9	95.5	80.8	73.5	69.8	66.1	69.8
47.5°	158.0	135.9	113.9	95.5	91.9	77.2	62.5	55.1	51.4	51.4	51.4
50°	150.6	121.2	99.2	80.8	69.8	62.5	47.8	40.4	36.7	36.7	36.7
52.5°	139.6	113.9	88.2	69.8	55.1	47.8	36.7	29.4	25.7	25.7	25.7
55°	124.9	102.9	77.2	58.8	47.8	36.7	25.7	18.4	14.7	14.7	14.7
57.5°	117.6	91.9	66.1	51.4	36.7	25.7	14.7	11.0	11.0	7.3	11.0
60°	106.5	80.8	55.1	40.4	29.4	18.4	11.0	3.7	3.7	3.7	3.7
62.5°	91.9	69.8	47.8	33.1	22.0	11.0	3.7	0.0	0.0	0.0	0.0
65°	77.2	55.1	36.7	25.7	14.7	3.7	0.0	0.0	0.0	0.0	0.0
67.5°	66.1	47.8	29.4	18.4	11.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	58.8	40.4	22.0	14.7	3.7	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	47.8	33.1	18.4	7.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	40.4	25.7	11.0	3.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	33.1	18.4	7.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	25.7	14.7	3.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	22.0	11.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	14.7	3.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	11.0	3.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599559
 CATALOG NUMBER: IFLD-M-SA4A-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	358°	360°
0°	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1	5173.1
2.5°	4666.1	4644.0	4754.3	4934.3	5026.1	5206.2	5250.3	5364.2	5334.8	5375.2
5°	3861.5	3905.6	4067.2	4331.7	4427.3	4688.1	4934.3	5180.5	5338.4	5415.6
7.5°	2865.8	3012.7	3211.1	3453.6	3699.8	4041.5	4460.3	4746.9	4901.2	5066.6
10°	2134.6	2292.6	2520.4	2759.2	3159.7	3541.8	3960.7	4317.0	4449.3	4603.6
12.5°	1679.1	1925.2	2189.8	2446.9	2685.8	3049.5	3567.5	4085.6	4228.9	4346.4
15°	1168.4	1469.6	1848.1	2182.4	2516.7	2832.7	3369.1	3997.4	4192.1	4390.5
17.5°	646.6	885.5	1319.0	1789.3	2281.6	2766.6	3435.3	4159.1	4453.0	4592.6
20°	374.8	470.3	778.9	1337.4	1987.7	2623.3	3468.3	4464.0	4853.5	4923.3
22.5°	308.6	341.7	440.9	837.7	1627.6	2531.4	3637.3	4890.2	5287.0	5452.3
25°	264.5	290.3	341.7	503.3	1230.8	2336.7	3743.9	5422.9	5790.4	5970.4
27.5°	235.1	260.9	301.3	371.1	837.7	2068.5	3920.2	5904.3	6271.7	6517.8
30°	205.7	227.8	268.2	316.0	580.5	1767.2	4070.9	6257.0	6775.0	6852.2
32.5°	183.7	202.1	231.5	271.9	429.9	1341.0	4192.1	6620.7	7057.9	7226.9
35°	158.0	180.0	198.4	231.5	327.0	1010.4	4118.6	6903.6	7473.1	7675.2
37.5°	139.6	154.3	172.7	194.7	275.6	789.9	3968.0	7241.6	7829.5	8016.9
40°	117.6	128.6	150.6	172.7	249.8	609.9	3795.3	7649.4	8329.1	8659.8
42.5°	99.2	110.2	124.9	161.7	205.7	451.9	3446.3	7965.4	8733.3	9012.5
45°	77.2	91.9	113.9	161.7	165.3	334.3	3086.2	8200.6	8961.1	9100.7
47.5°	58.8	73.5	110.2	139.6	132.3	231.5	2660.0	8468.8	9196.2	9324.8
50°	44.1	58.8	124.9	121.2	110.2	176.4	2391.8	8656.1	9210.9	9280.7
52.5°	29.4	44.1	102.9	91.9	91.9	154.3	2318.3	8648.8	9247.7	9097.0
55°	22.0	33.1	58.8	66.1	80.8	135.9	2252.2	8924.4	9258.7	9365.2
57.5°	14.7	25.7	40.4	51.4	69.8	117.6	2116.3	9255.0	9600.4	9655.5
60°	7.3	18.4	29.4	40.4	58.8	102.9	1925.2	9497.5	10015.6	10074.3
62.5°	3.7	11.0	22.0	33.1	47.8	80.8	1726.8	9111.7	9835.5	9938.4
65°	0.0	7.3	14.7	22.0	29.4	58.8	1403.5	8226.3	9122.8	9501.2
67.5°	0.0	0.0	7.3	14.7	18.4	44.1	1058.1	7484.1	8465.1	8979.5
70°	0.0	0.0	3.7	3.7	11.0	33.1	676.0	6198.2	7557.6	7840.5
72.5°	0.0	0.0	0.0	0.0	3.7	22.0	393.1	4603.6	5922.6	6448.0
75°	0.0	0.0	0.0	0.0	0.0	18.4	198.4	2961.3	4122.3	4827.7
77.5°	0.0	0.0	0.0	0.0	0.0	14.7	106.5	1910.5	3038.5	3630.0
80°	0.0	0.0	0.0	0.0	0.0	3.7	62.5	1109.6	1943.6	2355.1
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	25.7	543.8	1161.0	1359.4
85°	0.0	0.0	0.0	0.0	0.0	0.0	7.3	290.3	580.5	764.2
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	11.0	40.4	77.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)