

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599550

Luminaire Tested: **IFLD-S-SA3B-760-U-SLL-HSS**

Issue Date: 05/04/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P599550
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/04/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-S-SA3B-760-U-SLL-HSS
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens with House Side Shield
 Light Source: (48) 5700K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 12677.1 lumens
 Efficiency: N/A
 Efficacy: 103.6 lumens/watt
 Spacing Criteria (0/90/45): 0.53 / 0.46 / 0.63
 Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
 CIE Type: Direct

Input Watts (W): 122.4
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599550
CATALOG NUMBER: IFLD-S-SA3B-760-U-SLL-HSS

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ··· 90°-270° - · 135°-315°

TEST NUMBER: P599550
 CATALOG NUMBER: IFLD-S-SA3B-760-U-SLL-HSS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	106	100	95	90	103	98	93	89	94	90	86	90	86	83	86	83	81	79				
2	94	84	76	69	91	82	75	68	78	72	66	75	70	65	72	67	63	61				
3	84	72	62	54	81	70	61	53	67	59	52	64	57	51	61	55	50	48				
4	76	62	51	44	73	60	51	43	58	49	43	55	48	42	53	46	41	39				
5	69	54	44	36	67	53	43	36	51	42	35	48	41	35	46	40	34	32				
6	63	48	38	30	61	47	37	30	45	36	30	43	35	30	41	35	29	27				
7	58	43	33	26	56	42	33	26	40	32	26	39	31	26	37	31	25	23				
8	54	39	29	23	52	38	29	23	37	28	23	35	28	22	34	27	22	20				
9	50	35	26	20	49	35	26	20	34	26	20	32	25	20	31	25	20	18				
10	47	33	24	18	46	32	24	18	31	23	18	30	23	18	29	23	18	16				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	68408	68408	68408	68408
5°	71888	68426	49990	50284
10°	61817	59449	27332	26691
15°	60107	57140	17756	13380
20°	69283	66387	9514	4756
25°	87113	81485	6165	3699
30°	104630	97505	4993	3029
35°	123903	116251	4093	2432
40°	149491	140738	3616	1840
45°	170195	162775	3367	1236
50°	190930	183521	3327	757
55°	215915	215155	3303	338
60°	266443	272760	3011	98
65°	297295	327875	2758	0
70°	303143	370051	2555	0
75°	246665	272943	2440	0
80°	179349	114155	2521	0
85°	115944	47935	3343	0

TEST NUMBER: P599550
 CATALOG NUMBER: IFLD-S-SA3B-760-U-SLL-HSS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	362.1	2.9
10°-20°	710.1	5.6
20°-30°	982.6	7.8
30°-40°	1388.7	11.0
40°-50°	1890.8	14.9
50°-60°	2504.2	19.8
60°-70°	2907.6	22.9
70°-80°	1646.6	13.0
80°-90°	284.5	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2054.8	16.2
0°-40°	3443.5	27.2
0°-60°	7838.5	61.8
0°-90°	12677.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12677.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	4766	4766	4766	4766	4766	
5°	4990	4750	3470	3490	4990	448
15°	4045	3846	1195	900	4045	1187
25°	5501	5146	389	234	5501	2566
35°	7072	6635	234	139	7072	4458
45°	8385	8020	166	61	8385	6501
55°	8629	8599	132	14	8629	7818
65°	8754	9655	81	0	8754	8534
75°	4448	4922	44	0	4448	4855
85°	704	291	20	0	704	846
90°	0	0	0	0	0	

TEST NUMBER: P599550
 CATALOG NUMBER: IFLD-S-SA3B-760-U-SLL-HSS

CANDELA DISTRIBUTION (FULL):

	0°	2°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5
2.5°	4952.7	5057.7	5061.0	5108.4	5155.8	5155.8	5267.5	5240.5	5142.3	5125.4	5054.3
5°	4989.9	5027.2	5054.3	5294.6	5497.7	5477.4	5538.4	5497.7	5308.2	5064.4	4898.5
7.5°	4668.3	4709.0	4817.3	5226.9	5501.1	5592.5	5707.6	5453.7	5254.0	4813.9	4495.7
10°	4241.8	4319.7	4519.4	4986.6	5325.1	5616.2	5616.2	5413.1	5027.2	4597.2	4207.9
12.5°	4004.8	4160.5	4268.9	4742.8	5182.9	5382.6	5375.9	5267.5	5017.0	4475.4	4035.3
15°	4045.4	4089.5	4319.7	4688.7	4979.8	4969.6	5091.5	5057.7	4881.6	4583.7	4099.6
17.5°	4231.6	4299.3	4499.1	4688.7	4827.4	4786.8	4783.4	4945.9	4956.1	4766.5	4340.0
20°	4536.3	4736.0	4830.8	4888.4	4719.1	4546.5	4526.2	4753.0	4929.0	5000.1	4627.7
22.5°	5023.8	5155.8	5348.8	5054.3	4614.2	4397.5	4356.9	4607.4	4962.9	5277.7	5000.1
25°	5501.1	5602.7	5788.9	5409.7	4732.7	4367.0	4296.0	4512.6	5091.5	5663.6	5450.3
27.5°	6005.5	6093.6	6113.9	5670.4	4797.0	4306.1	4221.5	4512.6	5199.8	5866.7	5988.6
30°	6313.6	6418.5	6438.9	5900.6	4901.9	4356.9	4316.3	4532.9	5274.3	6039.4	6374.5
32.5°	6658.9	6686.0	6669.1	5941.2	5017.0	4505.8	4336.6	4668.3	5358.9	6245.9	6726.6
35°	7071.9	7119.3	6946.7	6127.4	5274.3	4600.6	4539.7	4834.2	5504.5	6340.7	7153.2
37.5°	7386.7	7535.7	7146.4	6198.5	5325.1	4800.4	4810.5	5179.5	5606.1	6455.8	7623.7
40°	7979.2	7728.7	7484.9	6442.2	5518.1	5138.9	5084.7	5535.0	5948.0	6530.3	7931.8
42.5°	8304.2	8172.1	7616.9	6465.9	5816.0	5606.1	5619.6	5937.8	6127.4	6740.1	8016.4
45°	8385.4	8246.6	7796.4	6482.9	6110.5	6157.9	6391.5	6452.4	6391.5	6878.9	8175.5
47.5°	8591.9	8290.6	7776.1	6709.7	6587.8	6770.6	7068.5	7200.5	6750.3	6828.2	8250.0
50°	8551.3	8378.6	7732.0	6804.5	7170.1	7654.2	7853.9	7799.7	7149.8	6723.2	8168.7
52.5°	8382.0	8195.8	7867.5	7061.8	7715.1	8300.8	8578.4	8443.0	7505.2	6960.2	8114.6
55°	8629.1	8487.0	8043.5	7410.4	8124.7	8869.5	9065.9	8964.3	7941.9	7180.2	8422.6
57.5°	8896.6	8866.1	8520.8	7820.1	8608.8	9455.2	9455.2	9329.9	8321.1	7498.5	8879.7
60°	9282.5	9350.2	8872.9	8090.9	8774.7	9421.3	9912.2	9766.6	8703.6	8057.0	9397.6
62.5°	9157.3	9373.9	9326.5	8673.2	8964.3	9587.2	9854.6	9963.0	9177.6	8737.5	10088.2
65°	8754.4	8984.6	9323.1	9055.7	8822.1	9184.3	9319.8	9648.1	9414.5	9377.3	10372.6
67.5°	8273.7	8524.2	8734.1	9313.0	8534.4	8774.7	8656.2	8761.2	9157.3	10078.1	10535.1
70°	7224.2	7464.6	7796.4	8740.9	7772.7	7556.0	7525.5	7474.8	8090.9	9827.5	9797.1
72.5°	5941.2	6052.9	6601.4	7105.8	5751.6	5711.0	5758.4	5700.9	6415.2	8896.6	8392.2
75°	4448.3	4560.0	4871.5	5457.1	3916.8	3683.2	3954.0	4221.5	4898.5	6906.0	6029.2
77.5°	3344.7	3486.9	3683.2	4082.7	2874.1	2508.5	2545.8	2799.6	3541.0	5531.6	3378.5
80°	2170.0	2153.1	2532.2	2809.8	2163.2	2230.9	2136.1	2322.3	2566.1	2958.8	1726.5
82.5°	1252.6	1269.5	1428.6	1611.4	1506.5	1723.1	1242.4	2075.2	1831.5	1205.2	643.2
85°	704.1	734.6	880.2	1117.2	944.5	633.1	518.0	1029.1	1151.0	494.3	311.4
87.5°	71.1	60.9	118.5	423.2	257.3	104.9	155.7	247.1	277.6	186.2	91.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599550
 CATALOG NUMBER: IFLD-S-SA3B-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5
2.5°	4952.7	4952.7	4868.1	4725.9	4668.3	4566.8	4428.0	4472.0	4424.6	4251.9	4207.9
5°	4749.6	4587.1	4411.1	4194.4	4069.1	3811.9	3730.6	3585.0	3608.7	3463.2	3469.9
7.5°	4326.4	4197.8	3899.9	3615.5	3368.4	3145.0	2830.1	2711.6	2596.5	2539.0	2606.7
10°	4079.3	3838.9	3432.7	3060.3	2731.9	2532.2	2322.3	2159.8	2010.9	1899.2	1875.5
12.5°	3899.9	3686.6	3195.7	2742.1	2484.8	2322.3	2129.4	1905.9	1760.4	1567.4	1509.8
15°	3845.7	3585.0	3067.1	2616.8	2366.3	2098.9	1878.8	1658.8	1469.2	1266.1	1195.0
17.5°	4031.9	3730.6	3063.7	2515.3	2163.2	1875.5	1570.8	1323.7	1130.7	944.5	900.5
20°	4346.7	3886.3	3161.9	2454.3	1970.2	1584.3	1239.0	991.9	775.2	653.4	622.9
22.5°	4705.6	4150.4	3172.0	2291.9	1777.3	1293.2	903.9	653.4	531.5	473.9	457.0
25°	5145.7	4573.6	3293.9	2159.8	1550.5	981.7	643.2	501.0	429.9	396.1	389.3
27.5°	5507.9	4868.1	3425.9	2021.0	1327.0	727.8	504.4	409.6	372.4	338.5	335.1
30°	5883.7	5206.6	3463.2	1936.4	1134.1	599.2	433.3	362.2	321.6	304.7	301.3
32.5°	6212.0	5575.6	3581.7	1797.6	951.3	528.1	392.7	325.0	297.9	270.8	267.4
35°	6635.2	5788.9	3639.2	1723.1	883.6	477.3	358.8	297.9	257.3	240.4	233.6
37.5°	7088.8	5995.4	3676.4	1665.6	826.0	446.9	338.5	281.0	243.7	220.0	213.3
40°	7512.0	6286.5	3622.3	1594.5	782.0	409.6	325.0	260.7	226.8	203.1	193.0
42.5°	7837.0	6570.9	3605.4	1526.8	734.6	396.1	308.1	250.5	213.3	186.2	182.8
45°	8019.8	6763.8	3486.9	1472.6	697.4	402.9	301.3	237.0	203.1	179.4	165.9
47.5°	7975.8	6912.8	3517.3	1455.7	646.6	375.8	297.9	226.8	186.2	165.9	155.7
50°	8219.5	7214.1	3466.6	1401.5	609.4	338.5	325.0	226.8	182.8	159.1	149.0
52.5°	8260.2	7488.3	3574.9	1303.3	551.8	311.4	321.6	223.4	176.0	152.3	138.8
55°	8598.7	7806.5	3784.8	1249.2	504.4	270.8	294.5	216.7	159.1	138.8	132.0
57.5°	9059.1	8466.7	3920.2	1198.4	440.1	237.0	247.1	213.3	145.6	128.6	118.5
60°	9502.6	8730.7	3930.3	1107.0	379.2	213.3	193.0	213.3	135.4	115.1	104.9
62.5°	9834.3	8730.7	3862.6	1029.1	331.8	189.6	169.3	203.1	121.9	101.6	94.8
65°	9654.9	8497.1	3686.6	964.8	301.3	165.9	145.6	155.7	108.3	88.0	81.2
67.5°	9333.3	7769.3	3297.3	887.0	297.9	145.6	125.3	115.1	94.8	77.9	71.1
70°	8818.7	6787.5	2745.5	798.9	291.1	132.0	111.7	98.2	84.6	67.7	60.9
72.5°	7105.8	5606.1	2254.6	748.2	284.4	115.1	94.8	84.6	71.1	57.6	50.8
75°	4922.2	3581.7	1736.7	639.8	277.6	104.9	88.0	74.5	60.9	47.4	44.0
77.5°	2952.0	2393.4	1120.5	480.7	182.8	84.6	74.5	57.6	50.8	40.6	37.2
80°	1381.2	1130.7	453.6	186.2	88.0	60.9	50.8	44.0	40.6	33.9	30.5
82.5°	541.6	477.3	220.0	108.3	71.1	47.4	40.6	37.2	33.9	27.1	23.7
85°	291.1	257.3	104.9	74.5	50.8	33.9	33.9	30.5	27.1	23.7	20.3
87.5°	64.3	47.4	44.0	44.0	37.2	27.1	27.1	23.7	20.3	16.9	13.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599550
 CATALOG NUMBER: IFLD-S-SA3B-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5
2.5°	4184.2	4235.0	4153.8	4204.6	4133.5	4187.6	4194.4	4143.6	4157.2	4224.9	4255.3
5°	3564.7	3530.9	3456.4	3432.7	3436.1	3392.1	3409.0	3432.7	3469.9	3490.3	3551.2
7.5°	2569.4	2647.3	2643.9	2701.5	2704.9	2698.1	2650.7	2549.1	2583.0	2555.9	2589.8
10°	1838.2	1872.1	1936.4	1973.6	2041.3	2004.1	1895.8	1855.1	1834.8	1831.5	1865.3
12.5°	1469.2	1388.0	1381.2	1394.7	1428.6	1384.6	1330.4	1283.0	1306.7	1354.1	1391.4
15°	1137.5	1069.8	981.7	968.2	975.0	954.7	897.1	836.2	853.1	900.5	927.6
17.5°	873.4	795.5	734.6	694.0	680.4	609.4	524.7	473.9	460.4	457.0	480.7
20°	589.0	575.5	565.3	514.6	514.6	413.0	341.9	304.7	304.7	311.4	314.8
22.5°	440.1	423.2	426.5	416.4	389.3	308.1	270.8	260.7	260.7	267.4	267.4
25°	382.5	358.8	352.1	348.7	321.6	264.1	237.0	226.8	226.8	233.6	233.6
27.5°	325.0	318.2	308.1	294.5	270.8	226.8	209.9	199.7	203.1	206.5	203.1
30°	297.9	281.0	267.4	267.4	240.4	203.1	189.6	182.8	176.0	182.8	186.2
32.5°	264.1	253.9	247.1	237.0	206.5	179.4	165.9	159.1	155.7	155.7	159.1
35°	226.8	226.8	220.0	206.5	179.4	162.5	145.6	138.8	135.4	138.8	138.8
37.5°	203.1	193.0	196.3	182.8	159.1	142.2	125.3	118.5	118.5	115.1	118.5
40°	189.6	172.7	162.5	155.7	142.2	121.9	108.3	101.6	98.2	98.2	98.2
42.5°	169.3	155.7	135.4	132.0	128.6	104.9	88.0	84.6	81.2	77.9	77.9
45°	159.1	138.8	121.9	104.9	104.9	88.0	74.5	67.7	64.3	60.9	64.3
47.5°	145.6	125.3	104.9	88.0	84.6	71.1	57.6	50.8	47.4	47.4	47.4
50°	138.8	111.7	91.4	74.5	64.3	57.6	44.0	37.2	33.9	33.9	33.9
52.5°	128.6	104.9	81.2	64.3	50.8	44.0	33.9	27.1	23.7	23.7	23.7
55°	115.1	94.8	71.1	54.2	44.0	33.9	23.7	16.9	13.5	13.5	13.5
57.5°	108.3	84.6	60.9	47.4	33.9	23.7	13.5	10.2	10.2	6.8	10.2
60°	98.2	74.5	50.8	37.2	27.1	16.9	10.2	3.4	3.4	3.4	3.4
62.5°	84.6	64.3	44.0	30.5	20.3	10.2	3.4	0.0	0.0	0.0	0.0
65°	71.1	50.8	33.9	23.7	13.5	3.4	0.0	0.0	0.0	0.0	0.0
67.5°	60.9	44.0	27.1	16.9	10.2	0.0	0.0	0.0	0.0	0.0	0.0
70°	54.2	37.2	20.3	13.5	3.4	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	44.0	30.5	16.9	6.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	37.2	23.7	10.2	3.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	30.5	16.9	6.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	23.7	13.5	3.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	20.3	10.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	13.5	3.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	10.2	3.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599550
 CATALOG NUMBER: IFLD-S-SA3B-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	358°	360°
0°	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5	4766.5
2.5°	4299.3	4279.0	4380.6	4546.5	4631.1	4797.0	4837.6	4942.5	4915.5	4952.7
5°	3558.0	3598.6	3747.5	3991.3	4079.3	4319.7	4546.5	4773.3	4918.9	4989.9
7.5°	2640.5	2776.0	2958.8	3182.2	3409.0	3723.8	4109.8	4373.8	4516.0	4668.3
10°	1966.9	2112.4	2322.3	2542.4	2911.4	3263.4	3649.4	3977.7	4099.6	4241.8
12.5°	1547.1	1773.9	2017.6	2254.6	2474.7	2809.8	3287.1	3764.5	3896.5	4004.8
15°	1076.5	1354.1	1702.8	2010.9	2318.9	2610.1	3104.3	3683.2	3862.6	4045.4
17.5°	595.8	815.9	1215.3	1648.6	2102.3	2549.1	3165.3	3832.2	4103.0	4231.6
20°	345.3	433.3	717.7	1232.3	1831.5	2417.1	3195.7	4113.1	4472.0	4536.3
22.5°	284.4	314.8	406.2	771.9	1499.7	2332.5	3351.5	4505.8	4871.5	5023.8
25°	243.7	267.4	314.8	463.8	1134.1	2153.1	3449.6	4996.7	5335.2	5501.1
27.5°	216.7	240.4	277.6	341.9	771.9	1905.9	3612.1	5440.2	5778.7	6005.5
30°	189.6	209.9	247.1	291.1	534.9	1628.3	3750.9	5765.2	6242.5	6313.6
32.5°	169.3	186.2	213.3	250.5	396.1	1235.6	3862.6	6100.3	6503.2	6658.9
35°	145.6	165.9	182.8	213.3	301.3	931.0	3794.9	6361.0	6885.7	7071.9
37.5°	128.6	142.2	159.1	179.4	253.9	727.8	3656.1	6672.4	7214.1	7386.7
40°	108.3	118.5	138.8	159.1	230.2	562.0	3497.0	7048.2	7674.5	7979.2
42.5°	91.4	101.6	115.1	149.0	189.6	416.4	3175.4	7339.3	8046.9	8304.2
45°	71.1	84.6	104.9	149.0	152.3	308.1	2843.7	7556.0	8256.8	8385.4
47.5°	54.2	67.7	101.6	128.6	121.9	213.3	2451.0	7803.1	8473.4	8591.9
50°	40.6	54.2	115.1	111.7	101.6	162.5	2203.8	7975.8	8487.0	8551.3
52.5°	27.1	40.6	94.8	84.6	84.6	142.2	2136.1	7969.0	8520.8	8382.0
55°	20.3	30.5	54.2	60.9	74.5	125.3	2075.2	8222.9	8531.0	8629.1
57.5°	13.5	23.7	37.2	47.4	64.3	108.3	1949.9	8527.6	8845.8	8896.6
60°	6.8	16.9	27.1	37.2	54.2	94.8	1773.9	8751.0	9228.3	9282.5
62.5°	3.4	10.2	20.3	30.5	44.0	74.5	1591.1	8395.6	9062.5	9157.3
65°	0.0	6.8	13.5	20.3	27.1	54.2	1293.2	7579.7	8405.7	8754.4
67.5°	0.0	0.0	6.8	13.5	16.9	40.6	975.0	6895.9	7799.7	8273.7
70°	0.0	0.0	3.4	3.4	10.2	30.5	622.9	5711.0	6963.6	7224.2
72.5°	0.0	0.0	0.0	0.0	3.4	20.3	362.2	4241.8	5457.1	5941.2
75°	0.0	0.0	0.0	0.0	0.0	16.9	182.8	2728.6	3798.3	4448.3
77.5°	0.0	0.0	0.0	0.0	0.0	13.5	98.2	1760.4	2799.6	3344.7
80°	0.0	0.0	0.0	0.0	0.0	3.4	57.6	1022.4	1790.8	2170.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	23.7	501.0	1069.8	1252.6
85°	0.0	0.0	0.0	0.0	0.0	0.0	6.8	267.4	534.9	704.1
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	10.2	37.2	71.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)