

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599555

Luminaire Tested: **IFLD-S-SA6B-760-U-SLL-HSS**

Issue Date: 05/04/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P599555
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/04/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-S-SA6B-760-U-SLL-HSS
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens with House Side Shield
 Light Source: (96) 5700K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 24868.5 lumens
 Efficiency: N/A
 Efficacy: 101.5 lumens/watt
 Spacing Criteria (0/90/45): 0.53 / 0.46 / 0.63
 Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
 CIE Type: Direct

Input Watts (W): 244.9
 Input Voltage (V): 120
 Input Current (A_{in}): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599555
CATALOG NUMBER: IFLD-S-SA6B-760-U-SLL-HSS

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ··· 90°-270° - · 135°-315°

TEST NUMBER: P599555

CATALOG NUMBER: IFLD-S-SA6B-760-U-SLL-HSS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	106	100	95	90	103	98	93	89	94	90	86	90	86	83	86	83	81	81	81	81	79
2	94	84	76	69	91	82	75	68	78	72	66	75	70	65	72	67	63	63	63	63	61
3	84	72	62	54	81	70	61	53	67	59	52	64	57	51	61	55	50	50	50	50	48
4	76	62	51	44	73	60	51	43	58	49	43	55	48	42	53	46	41	41	41	41	39
5	69	54	44	36	67	53	43	36	51	42	35	48	41	35	46	40	34	34	34	34	32
6	63	48	38	30	61	47	37	30	45	36	30	43	35	30	41	35	29	29	29	29	27
7	58	43	33	26	56	42	33	26	40	32	26	39	31	26	37	31	25	25	25	25	23
8	54	39	29	23	52	38	29	23	37	28	23	35	28	22	34	27	22	22	22	22	20
9	50	35	26	20	49	35	26	20	34	26	20	32	25	20	31	25	20	20	20	20	18
10	47	33	24	18	46	32	24	18	31	23	18	30	23	18	29	23	18	18	18	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	67098	67098	67098	67098
5°	70511	67115	49033	49320
10°	60632	58310	26808	26179
15°	58956	56046	17415	13123
20°	67956	65115	9331	4666
25°	85444	79924	6047	3628
30°	102625	95637	4897	2971
35°	121529	114024	4014	2385
40°	146626	138041	3546	1804
45°	166935	159656	3302	1213
50°	187271	180006	3262	741
55°	211779	211032	3240	333
60°	261338	267534	2955	95
65°	291598	321593	2707	0
70°	297337	362962	2507	0
75°	241937	267717	2393	0
80°	175911	111969	2471	0
85°	113729	47021	3277	0

TEST NUMBER: P599555
 CATALOG NUMBER: IFLD-S-SA6B-760-U-SLL-HSS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	710.3	2.9
10°-20°	1393.0	5.6
20°-30°	1927.6	7.8
30°-40°	2724.2	11.0
40°-50°	3709.1	14.9
50°-60°	4912.4	19.8
60°-70°	5703.7	22.9
70°-80°	3230.0	13.0
80°-90°	558.1	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4030.9	16.2
0°-40°	6755.1	27.2
0°-60°	15376.6	61.8
0°-90°	24868.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	24868.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	9350	9350	9350	9350	9350	
5°	9789	9317	6807	6847	9789	879
15°	7936	7544	2344	1766	7936	2328
25°	10791	10094	764	458	10791	5033
35°	13873	13016	458	272	13873	8746
45°	16450	15732	325	120	16450	12753
55°	16928	16868	259	27	16928	15337
65°	17173	18940	159	0	17173	16741
75°	8726	9656	86	0	8726	9524
85°	1381	571	40	0	1381	1660
90°	0	0	0	0	0	

TEST NUMBER: P599555
 CATALOG NUMBER: IFLD-S-SA6B-760-U-SLL-HSS

CANDELA DISTRIBUTION (FULL):

	0°	2°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4
2.5°	9715.6	9921.5	9928.1	10021.1	10114.1	10114.1	10333.2	10280.1	10087.5	10054.3	9914.8
5°	9788.7	9861.7	9914.8	10386.4	10784.8	10745.0	10864.5	10784.8	10412.9	9934.8	9609.4
7.5°	9157.8	9237.5	9450.0	10253.5	10791.4	10970.7	11196.5	10698.5	10306.7	9443.3	8819.1
10°	8321.0	8473.8	8865.6	9782.0	10446.1	11017.2	11017.2	10618.8	9861.7	9018.3	8254.6
12.5°	7856.2	8161.7	8374.2	9303.9	10167.2	10559.0	10545.7	10333.2	9841.8	8779.3	7915.9
15°	7935.9	8022.2	8473.8	9197.6	9768.7	9748.8	9987.9	9921.5	9576.2	8991.8	8042.1
17.5°	8301.1	8433.9	8825.7	9197.6	9469.9	9390.2	9383.6	9702.3	9722.3	9350.4	8513.6
20°	8898.8	9290.6	9476.5	9589.4	9257.4	8918.7	8878.9	9323.8	9669.1	9808.6	9078.1
22.5°	9855.1	10114.1	10492.6	9914.8	9051.5	8626.5	8546.8	9038.3	9735.5	10353.1	9808.6
25°	10791.4	10990.7	11355.9	10612.1	9284.0	8566.7	8427.3	8852.3	9987.9	11110.2	10691.8
27.5°	11780.9	11953.6	11993.4	11123.5	9410.1	8447.2	8281.2	8852.3	10200.4	11508.7	11747.7
30°	12385.3	12591.1	12631.0	11575.1	9616.0	8546.8	8467.1	8892.2	10346.5	11847.3	12504.8
32.5°	13062.6	13115.8	13082.6	11654.8	9841.8	8839.0	8507.0	9157.8	10512.5	12252.4	13195.4
35°	13872.8	13965.8	13627.1	12020.0	10346.5	9025.0	8905.4	9483.2	10798.1	12438.4	14032.2
37.5°	14490.4	14782.6	14018.9	12159.5	10446.1	9416.8	9436.7	10160.6	10997.3	12664.2	14955.3
40°	15652.6	15161.2	14683.0	12637.6	10824.7	10080.9	9974.6	10857.9	11668.0	12810.3	15559.6
42.5°	16290.1	16031.1	14942.0	12684.1	11409.0	10997.3	11023.9	11648.1	12020.0	13222.0	15725.6
45°	16449.5	16177.2	15294.0	12717.3	11986.8	12079.8	12538.0	12657.5	12538.0	13494.3	16037.7
47.5°	16854.6	16263.5	15254.1	13162.2	12923.2	13281.8	13866.2	14125.2	13241.9	13394.7	16183.8
50°	16774.9	16436.2	15167.8	13348.2	14065.4	15015.1	15406.9	15300.6	14025.6	13188.8	16024.5
52.5°	16442.8	16077.6	15433.4	13852.9	15134.6	16283.5	16828.0	16562.4	14722.9	13653.7	15918.2
55°	16927.6	16648.7	15778.8	14536.9	15938.1	17399.1	17784.3	17585.1	15579.5	14085.3	16522.5
57.5°	17452.3	17392.5	16715.1	15340.5	16887.8	18548.0	18548.0	18302.3	16323.3	14709.6	17419.1
60°	18209.3	18342.1	17405.8	15871.7	17213.2	18481.6	19444.5	19159.0	17073.7	15805.3	18435.1
62.5°	17963.6	18388.6	18295.7	17014.0	17585.1	18807.0	19331.6	19544.1	18003.5	17140.1	19789.9
65°	17173.3	17624.9	18289.0	17764.4	17306.2	18016.7	18282.4	18926.5	18468.3	18395.3	20347.7
67.5°	16230.3	16721.8	17133.5	18269.1	16741.7	17213.2	16980.8	17186.6	17963.6	19769.9	20666.4
70°	14171.7	14643.2	15294.0	17146.8	15247.5	14822.5	14762.7	14663.1	15871.7	19278.5	19218.7
72.5°	11654.8	11873.9	12949.7	13939.2	11282.9	11203.2	11296.2	11183.3	12584.5	17452.3	16462.8
75°	8726.1	8945.3	9556.2	10705.1	7683.5	7225.3	7756.6	8281.2	9609.4	13547.4	11827.4
77.5°	6561.2	6840.1	7225.3	8008.9	5638.1	4920.9	4993.9	5492.0	6946.4	10851.2	6627.6
80°	4256.8	4223.6	4967.4	5511.9	4243.5	4376.3	4190.4	4555.7	5033.8	5804.1	3386.9
82.5°	2457.1	2490.3	2802.5	3161.1	2955.2	3380.2	2437.2	4070.9	3592.7	2364.2	1261.8
85°	1381.3	1441.1	1726.6	2191.5	1852.8	1241.8	1016.1	2018.8	2257.9	969.6	611.0
87.5°	139.5	119.5	232.4	830.1	504.7	205.9	305.5	484.8	544.6	365.2	179.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599555
 CATALOG NUMBER: IFLD-S-SA6B-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4
2.5°	9715.6	9715.6	9549.6	9270.7	9157.8	8958.6	8686.3	8772.6	8679.6	8341.0	8254.6
5°	9317.2	8998.4	8653.1	8228.1	7982.3	7477.6	7318.3	7032.7	7079.2	6793.6	6806.9
7.5°	8487.1	8234.7	7650.3	7092.5	6607.7	6169.4	5551.8	5319.4	5093.6	4980.7	5113.5
10°	8002.3	7530.8	6733.9	6003.4	5359.2	4967.4	4555.7	4236.9	3944.7	3725.5	3679.1
12.5°	7650.3	7231.9	6269.0	5379.1	4874.4	4555.7	4177.1	3738.8	3453.3	3074.7	2961.8
15°	7544.1	7032.7	6016.6	5133.4	4642.0	4117.4	3685.7	3254.0	2882.1	2483.7	2344.2
17.5°	7909.3	7318.3	6010.0	4934.2	4243.5	3679.1	3081.4	2596.6	2218.1	1852.8	1766.5
20°	8526.9	7623.7	6202.6	4814.6	3865.0	3107.9	2430.6	1945.8	1520.8	1281.7	1221.9
22.5°	9230.8	8141.7	6222.5	4495.9	3486.5	2536.8	1773.1	1281.7	1042.6	929.7	896.5
25°	10094.2	8971.8	6461.6	4236.9	3041.5	1925.9	1261.8	982.9	843.4	777.0	763.7
27.5°	10804.7	9549.6	6720.6	3964.6	2603.2	1427.8	989.5	803.5	730.5	664.1	657.4
30°	11541.9	10213.7	6793.6	3798.6	2224.7	1175.4	850.0	710.6	630.9	597.7	591.0
32.5°	12186.0	10937.5	7026.1	3526.3	1866.1	1036.0	770.3	637.5	584.4	531.3	524.6
35°	13016.1	11355.9	7139.0	3380.2	1733.3	936.4	703.9	584.4	504.7	471.5	458.2
37.5°	13906.0	11761.0	7212.0	3267.3	1620.4	876.6	664.1	551.2	478.1	431.7	418.4
40°	14736.1	12332.1	7105.8	3127.9	1534.0	803.5	637.5	511.3	444.9	398.5	378.5
42.5°	15373.7	12890.0	7072.5	2995.0	1441.1	777.0	604.3	491.4	418.4	365.2	358.6
45°	15732.3	13268.5	6840.1	2888.8	1368.0	790.3	591.0	464.9	398.5	352.0	325.4
47.5°	15645.9	13560.7	6899.9	2855.6	1268.4	737.1	584.4	444.9	365.2	325.4	305.5
50°	16124.1	14151.7	6800.3	2749.3	1195.4	664.1	637.5	444.9	358.6	312.1	292.2
52.5°	16203.8	14689.6	7012.8	2556.7	1082.5	611.0	630.9	438.3	345.3	298.8	272.3
55°	16867.9	15313.9	7424.5	2450.5	989.5	531.3	577.8	425.0	312.1	272.3	259.0
57.5°	17771.0	16608.9	7690.2	2350.9	863.3	464.9	484.8	418.4	285.6	252.4	232.4
60°	18641.0	17126.9	7710.1	2171.6	743.8	418.4	378.5	418.4	265.6	225.8	205.9
62.5°	19291.8	17126.9	7577.3	2018.8	650.8	371.9	332.0	398.5	239.1	199.2	185.9
65°	18939.8	16668.6	7231.9	1892.7	591.0	325.4	285.6	305.5	212.5	172.7	159.4
67.5°	18308.9	15240.8	6468.2	1739.9	584.4	285.6	245.7	225.8	185.9	152.7	139.5
70°	17299.5	13315.0	5385.8	1567.2	571.1	259.0	219.1	192.6	166.0	132.8	119.5
72.5°	13939.2	10997.3	4422.8	1467.6	557.8	225.8	185.9	166.0	139.5	112.9	99.6
75°	9655.9	7026.1	3406.8	1255.1	544.6	205.9	172.7	146.1	119.5	93.0	86.3
77.5°	5790.9	4695.1	2198.1	943.0	358.6	166.0	146.1	112.9	99.6	79.7	73.0
80°	2709.5	2218.1	889.9	365.2	172.7	119.5	99.6	86.3	79.7	66.4	59.8
82.5°	1062.5	936.4	431.7	212.5	139.5	93.0	79.7	73.0	66.4	53.1	46.5
85°	571.1	504.7	205.9	146.1	99.6	66.4	66.4	59.8	53.1	46.5	39.8
87.5°	126.2	93.0	86.3	86.3	73.0	53.1	53.1	46.5	39.8	33.2	26.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599555
 CATALOG NUMBER: IFLD-S-SA6B-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4
2.5°	8208.1	8307.8	8148.4	8248.0	8108.5	8214.8	8228.1	8128.4	8155.0	8287.8	8347.6
5°	6992.9	6926.4	6780.3	6733.9	6740.5	6654.2	6687.4	6733.9	6806.9	6846.8	6966.3
7.5°	5040.4	5193.2	5186.5	5299.4	5306.1	5292.8	5199.8	5000.6	5067.0	5013.9	5080.3
10°	3606.0	3672.4	3798.6	3871.6	4004.5	3931.4	3718.9	3639.2	3599.4	3592.7	3659.1
12.5°	2882.1	2722.8	2709.5	2736.0	2802.5	2716.1	2609.9	2516.9	2563.4	2656.4	2729.4
15°	2231.3	2098.5	1925.9	1899.3	1912.6	1872.7	1759.8	1640.3	1673.5	1766.5	1819.6
17.5°	1713.3	1560.6	1441.1	1361.4	1334.8	1195.4	1029.3	929.7	903.2	896.5	943.0
20°	1155.5	1129.0	1109.0	1009.4	1009.4	810.2	670.7	597.7	597.7	611.0	617.6
22.5°	863.3	830.1	836.8	816.8	763.7	604.3	531.3	511.3	511.3	524.6	524.6
25°	750.4	703.9	690.7	684.0	630.9	518.0	464.9	444.9	444.9	458.2	458.2
27.5°	637.5	624.2	604.3	577.8	531.3	444.9	411.7	391.8	398.5	405.1	398.5
30°	584.4	551.2	524.6	524.6	471.5	398.5	371.9	358.6	345.3	358.6	365.2
32.5°	518.0	498.1	484.8	464.9	405.1	352.0	325.4	312.1	305.5	305.5	312.1
35°	444.9	444.9	431.7	405.1	352.0	318.8	285.6	272.3	265.6	272.3	272.3
37.5°	398.5	378.5	385.2	358.6	312.1	278.9	245.7	232.4	232.4	225.8	232.4
40°	371.9	338.7	318.8	305.5	278.9	239.1	212.5	199.2	192.6	192.6	192.6
42.5°	332.0	305.5	265.6	259.0	252.4	205.9	172.7	166.0	159.4	152.7	152.7
45°	312.1	272.3	239.1	205.9	205.9	172.7	146.1	132.8	126.2	119.5	126.2
47.5°	285.6	245.7	205.9	172.7	166.0	139.5	112.9	99.6	93.0	93.0	93.0
50°	272.3	219.1	179.3	146.1	126.2	112.9	86.3	73.0	66.4	66.4	66.4
52.5°	252.4	205.9	159.4	126.2	99.6	86.3	66.4	53.1	46.5	46.5	46.5
55°	225.8	185.9	139.5	106.3	86.3	66.4	46.5	33.2	26.6	26.6	26.6
57.5°	212.5	166.0	119.5	93.0	66.4	46.5	26.6	19.9	19.9	13.3	19.9
60°	192.6	146.1	99.6	73.0	53.1	33.2	19.9	6.6	6.6	6.6	6.6
62.5°	166.0	126.2	86.3	59.8	39.8	19.9	6.6	0.0	0.0	0.0	0.0
65°	139.5	99.6	66.4	46.5	26.6	6.6	0.0	0.0	0.0	0.0	0.0
67.5°	119.5	86.3	53.1	33.2	19.9	0.0	0.0	0.0	0.0	0.0	0.0
70°	106.3	73.0	39.8	26.6	6.6	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	86.3	59.8	33.2	13.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	73.0	46.5	19.9	6.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	59.8	33.2	13.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	46.5	26.6	6.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	39.8	19.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	26.6	6.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	19.9	6.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599555
 CATALOG NUMBER: IFLD-S-SA6B-760-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	358°	360°
0°	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4	9350.4
2.5°	8433.9	8394.1	8593.3	8918.7	9084.7	9410.1	9489.8	9695.7	9642.6	9715.6
5°	6979.6	7059.3	7351.5	7829.6	8002.3	8473.8	8918.7	9363.7	9649.2	9788.7
7.5°	5179.9	5445.5	5804.1	6242.4	6687.4	7305.0	8062.0	8580.0	8858.9	9157.8
10°	3858.4	4143.9	4555.7	4987.3	5711.2	6401.8	7158.9	7803.0	8042.1	8321.0
12.5°	3034.9	3479.8	3958.0	4422.8	4854.5	5511.9	6448.3	7384.7	7643.7	7856.2
15°	2111.8	2656.4	3340.4	3944.7	4549.0	5120.1	6089.7	7225.3	7577.3	7935.9
17.5°	1168.8	1600.5	2384.1	3234.1	4124.0	5000.6	6209.2	7517.5	8048.8	8301.1
20°	677.4	850.0	1407.9	2417.3	3592.7	4741.6	6269.0	8068.7	8772.6	8898.8
22.5°	557.8	617.6	796.9	1514.1	2941.9	4575.6	6574.5	8839.0	9556.2	9855.1
25°	478.1	524.6	617.6	909.8	2224.7	4223.6	6767.1	9802.0	10466.0	10791.4
27.5°	425.0	471.5	544.6	670.7	1514.1	3738.8	7085.8	10671.9	11336.0	11780.9
30°	371.9	411.7	484.8	571.1	1049.3	3194.3	7358.1	11309.4	12245.8	12385.3
32.5°	332.0	365.2	418.4	491.4	777.0	2423.9	7577.3	11966.9	12757.1	13062.6
35°	285.6	325.4	358.6	418.4	591.0	1826.2	7444.4	12478.2	13507.6	13872.8
37.5°	252.4	278.9	312.1	352.0	498.1	1427.8	7172.2	13089.2	14151.7	14490.4
40°	212.5	232.4	272.3	312.1	451.6	1102.4	6860.0	13826.3	15054.9	15652.6
42.5°	179.3	199.2	225.8	292.2	371.9	816.8	6229.2	14397.4	15785.4	16290.1
45°	139.5	166.0	205.9	292.2	298.8	604.3	5578.3	14822.5	16197.1	16449.5
47.5°	106.3	132.8	199.2	252.4	239.1	418.4	4808.0	15307.3	16622.1	16854.6
50°	79.7	106.3	225.8	219.1	199.2	318.8	4323.2	15645.9	16648.7	16774.9
52.5°	53.1	79.7	185.9	166.0	166.0	278.9	4190.4	15632.7	16715.1	16442.8
55°	39.8	59.8	106.3	119.5	146.1	245.7	4070.9	16130.7	16735.0	16927.6
57.5°	26.6	46.5	73.0	93.0	126.2	212.5	3825.2	16728.4	17352.6	17452.3
60°	13.3	33.2	53.1	73.0	106.3	185.9	3479.8	17166.7	18103.1	18209.3
62.5°	6.6	19.9	39.8	59.8	86.3	146.1	3121.2	16469.4	17777.7	17963.6
65°	0.0	13.3	26.6	39.8	53.1	106.3	2536.8	14869.0	16489.3	17173.3
67.5°	0.0	0.0	13.3	26.6	33.2	79.7	1912.6	13527.5	15300.6	16230.3
70°	0.0	0.0	6.6	6.6	19.9	59.8	1221.9	11203.2	13660.3	14171.7
72.5°	0.0	0.0	0.0	0.0	6.6	39.8	710.6	8321.0	10705.1	11654.8
75°	0.0	0.0	0.0	0.0	0.0	33.2	358.6	5352.6	7451.1	8726.1
77.5°	0.0	0.0	0.0	0.0	0.0	26.6	192.6	3453.3	5492.0	6561.2
80°	0.0	0.0	0.0	0.0	0.0	6.6	112.9	2005.5	3513.0	4256.8
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	46.5	982.9	2098.5	2457.1
85°	0.0	0.0	0.0	0.0	0.0	0.0	13.3	524.6	1049.3	1381.3
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	19.9	73.0	139.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)