

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599283

Luminaire Tested: **IFLD-S-SA2A-760-U-SLR-HSS**

Issue Date: 05/04/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

**Test Information**

Test Method: LM-79-08  
 Report Number: P599283  
 Test Lab: INNOVATION CENTER(G1)  
 Issue Date: 05/04/2022  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: IFLD-S-SA2A-760-U-SLR-HSS  
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLR distribution lens with House Side Shield  
 Light Source: (32) 5700K CCT, 70 CRI LEDs  
 Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
 Luminaire Lumens: 6878.9 lumens  
 Efficiency: N/A  
 Efficacy: 107.8 lumens/watt  
 Spacing Criteria (0/90/45): 0.44 / 0.52 / 0.65  
 Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')  
 CIE Type: Direct

Input Watts (W): 63.8  
 Input Voltage (V): 120  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599283  
CATALOG NUMBER: IFLD-S-SA2A-760-U-SLR-HSS

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    ··· 90°-270°    - · - 135°-315°

TEST NUMBER: P599283  
 CATALOG NUMBER: IFLD-S-SA2A-760-U-SLR-HSS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	107	101	96	91	104	99	94	90	94	90	87	90	87	84	87	84	82	79			79	
2	95	85	77	70	92	83	75	69	79	73	67	76	71	66	73	68	64	62			62	
3	85	72	63	55	82	71	62	54	67	60	53	65	58	52	62	56	51	49			49	
4	76	62	52	44	74	61	51	44	58	50	43	56	49	43	53	47	42	40			40	
5	69	55	44	37	67	53	44	36	51	43	36	49	41	35	47	40	35	33			33	
6	63	48	38	31	61	47	38	31	45	37	30	44	36	30	42	35	30	27			27	
7	58	43	33	27	56	42	33	26	41	32	26	39	32	26	38	31	26	24			24	
8	54	39	30	23	52	38	29	23	37	29	23	36	28	23	34	28	23	20			20	
9	50	36	27	21	49	35	26	21	34	26	20	33	25	20	32	25	20	18			18	
10	47	33	24	18	46	32	24	18	31	24	18	30	23	18	29	23	18	16			16	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	56614	56614	56614	56614
5°	54505	39838	42883	60076
10°	48527	21689	21974	51366
15°	48444	14467	8846	49353
20°	58165	7223	3526	57826
25°	71540	4537	2732	71189
30°	86439	3642	2076	85888
35°	101427	2925	1608	100403
40°	122791	2501	1043	119402
45°	140479	2259	563	136582
50°	159379	2174	124	152858
55°	192253	2087	0	173322
60°	232763	1757	0	218951
65°	269524	1416	0	244961
70°	272922	1164	0	247008
75°	176627	774	0	189428
80°	60239	236	0	134041
85°	30233	0	0	98481

TEST NUMBER: P599283  
 CATALOG NUMBER: IFLD-S-SA2A-760-U-SLR-HSS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	199.2	2.9
10°-20°	385.7	5.6
20°-30°	537.2	7.8
30°-40°	763.4	11.1
40°-50°	1058.6	15.4
50°-60°	1442.4	21.0
60°-70°	1585.8	23.1
70°-80°	779.4	11.3
80°-90°	127.3	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1122.2	16.3
0°-40°	1885.6	27.4
0°-60°	4386.5	63.8
0°-90°	6878.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6878.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2630	2630	2630	2630	2630	
5°	2522	1844	1984	2780	2522	231
15°	2174	649	397	2214	2174	643
25°	3012	191	115	2997	3012	1400
35°	3859	111	61	3820	3859	2450
45°	4614	74	18	4486	4614	3577
55°	5122	56	0	4618	5122	4608
65°	5291	28	0	4809	5291	5113
75°	2124	9	0	2277	2124	2315
85°	122	0	0	399	122	169
90°	0	0	0	0	0	

TEST NUMBER: P599283  
 CATALOG NUMBER: IFLD-S-SA2A-760-U-SLR-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8
2.5°	2683.6	2715.1	2685.4	2581.6	2563.0	2513.0	2436.9	2431.4	2351.6	2360.9	2318.2
5°	2522.2	2553.8	2490.7	2353.5	2225.5	2123.5	2062.3	1952.9	1928.8	1875.0	1875.0
7.5°	2357.2	2355.3	2247.7	2132.8	1941.7	1754.4	1669.1	1511.5	1418.8	1368.7	1320.5
10°	2219.9	2190.3	2123.5	1886.1	1678.4	1483.7	1378.0	1274.1	1177.7	1094.2	1010.7
12.5°	2123.5	2142.0	2036.3	1778.5	1509.6	1374.2	1261.1	1151.7	1036.7	942.1	849.4
15°	2173.6	2143.9	2019.6	1754.4	1481.8	1296.4	1146.1	1012.6	884.6	760.4	689.9
17.5°	2329.4	2253.3	2106.8	1754.4	1424.3	1177.7	995.9	838.3	701.0	589.8	502.6
20°	2538.9	2451.8	2294.1	1819.3	1381.7	1090.5	842.0	643.5	500.7	396.9	330.1
22.5°	2754.0	2685.4	2448.0	1845.3	1331.6	973.7	663.9	465.5	333.8	267.1	233.7
25°	3011.8	2915.4	2655.8	1949.2	1257.4	860.5	523.0	324.6	248.5	213.3	192.9
27.5°	3217.7	3201.0	2850.5	2012.2	1201.8	767.8	413.6	257.8	205.9	179.9	166.9
30°	3477.3	3386.5	3087.9	2138.3	1138.7	662.1	345.0	231.8	189.2	161.3	152.1
32.5°	3633.1	3590.5	3212.1	2208.8	1068.2	574.9	296.7	204.0	172.5	152.1	142.8
35°	3859.4	3774.1	3390.2	2253.3	1031.1	524.8	267.1	185.5	144.7	124.3	113.1
37.5°	4111.6	4080.1	3603.4	2251.5	977.4	495.2	246.7	172.5	137.2	115.0	102.0
40°	4369.4	4241.4	3733.3	2303.4	949.5	472.9	231.8	165.1	129.8	109.4	92.7
42.5°	4562.3	4415.8	3883.5	2284.8	916.2	434.0	226.3	153.9	124.3	100.1	85.3
45°	4614.2	4562.3	4018.9	2279.3	892.1	402.4	217.0	152.1	120.5	94.6	79.7
47.5°	4714.3	4679.1	4185.8	2288.6	873.5	378.3	194.7	155.8	115.0	89.0	76.0
50°	4758.8	4695.8	4321.2	2310.8	830.9	348.7	174.3	163.2	113.1	87.2	72.3
52.5°	4942.5	4886.8	4506.6	2373.9	795.6	309.7	153.9	155.8	116.8	81.6	68.6
55°	5122.3	5059.3	4792.2	2518.5	745.5	278.2	131.7	137.2	111.3	74.2	61.2
57.5°	5369.0	5265.1	4983.3	2577.9	701.0	235.5	116.8	113.1	103.9	66.8	53.8
60°	5406.1	5448.8	4955.4	2540.8	654.7	207.7	102.0	87.2	111.3	59.3	46.4
62.5°	5530.4	5352.3	4825.6	2455.5	621.3	191.0	90.9	72.3	96.4	51.9	38.9
65°	5291.1	5159.4	4521.5	2181.0	578.6	192.9	79.7	59.3	61.2	42.7	31.5
67.5°	4940.6	4836.7	4017.0	1882.4	536.0	189.2	70.5	51.9	46.4	37.1	27.8
70°	4336.0	4111.6	3412.4	1528.2	472.9	176.2	59.3	46.4	38.9	29.7	20.4
72.5°	3154.6	3063.8	2448.0	1181.4	424.7	159.5	55.6	38.9	33.4	22.3	16.7
75°	2123.5	1973.3	1544.9	775.2	341.2	139.1	46.4	35.2	26.0	16.7	13.0
77.5°	1122.0	1060.8	875.4	369.1	189.2	64.9	26.0	20.4	14.8	13.0	7.4
80°	485.9	432.1	378.3	150.2	66.8	29.7	16.7	11.1	9.3	7.4	3.7
82.5°	248.5	237.4	196.6	64.9	38.9	22.3	9.3	7.4	5.6	3.7	1.9
85°	122.4	126.1	103.9	20.4	22.3	13.0	1.9	1.9	0.0	0.0	0.0
87.5°	9.3	9.3	7.4	3.7	5.6	1.9	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599283  
 CATALOG NUMBER: IFLD-S-SA2A-760-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8
2.5°	2301.5	2327.5	2283.0	2310.8	2297.8	2303.4	2309.0	2294.1	2297.8	2349.8	2351.6
5°	1843.5	1893.5	1875.0	1900.9	1945.5	1923.2	1943.6	1939.9	1943.6	1951.0	1984.4
7.5°	1314.9	1300.1	1335.3	1403.9	1483.7	1531.9	1507.8	1494.8	1487.4	1468.8	1491.1
10°	992.2	984.8	975.5	995.9	1047.8	1101.6	1131.3	1081.2	1053.4	1018.2	1005.2
12.5°	823.4	777.1	751.1	719.6	734.4	782.6	784.5	736.3	691.8	673.2	693.6
15°	649.1	617.6	571.2	526.7	504.4	541.5	510.0	463.6	406.2	398.7	396.9
17.5°	463.6	445.1	411.7	393.2	367.2	357.9	324.6	254.1	213.3	202.1	205.9
20°	315.3	300.4	298.6	281.9	270.8	263.4	209.6	163.2	150.2	152.1	153.9
22.5°	233.7	226.3	217.0	215.1	205.9	196.6	153.9	137.2	128.0	128.0	133.5
25°	191.0	187.3	178.0	174.3	170.6	157.6	129.8	116.8	113.1	109.4	115.0
27.5°	163.2	161.3	155.8	150.2	146.5	133.5	113.1	102.0	98.3	98.3	98.3
30°	146.5	146.5	139.1	128.0	128.0	113.1	96.4	89.0	85.3	85.3	83.5
32.5°	137.2	133.5	124.3	116.8	111.3	96.4	85.3	77.9	72.3	72.3	74.2
35°	111.3	111.3	109.4	103.9	96.4	81.6	72.3	64.9	61.2	59.3	61.2
37.5°	98.3	92.7	85.3	87.2	83.5	70.5	61.2	55.6	50.1	50.1	50.1
40°	89.0	83.5	76.0	70.5	68.6	63.1	53.8	44.5	38.9	37.1	37.1
42.5°	79.7	76.0	64.9	55.6	53.8	53.8	40.8	33.4	27.8	27.8	27.8
45°	74.2	68.6	59.3	48.2	38.9	40.8	33.4	24.1	20.4	18.5	18.5
47.5°	70.5	64.9	51.9	40.8	29.7	29.7	24.1	16.7	13.0	11.1	11.1
50°	64.9	59.3	46.4	33.4	22.3	18.5	14.8	9.3	5.6	3.7	3.7
52.5°	61.2	55.6	40.8	27.8	18.5	13.0	9.3	1.9	0.0	0.0	0.0
55°	55.6	48.2	35.2	22.3	14.8	7.4	1.9	0.0	0.0	0.0	0.0
57.5°	48.2	42.7	27.8	16.7	9.3	1.9	0.0	0.0	0.0	0.0	0.0
60°	40.8	35.2	22.3	13.0	3.7	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	33.4	29.7	16.7	7.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	27.8	22.3	13.0	1.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	24.1	18.5	9.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	18.5	13.0	5.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	13.0	9.3	1.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	9.3	5.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	5.6	1.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	1.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599283  
 CATALOG NUMBER: IFLD-S-SA2A-760-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8
2.5°	2359.0	2414.7	2466.6	2481.4	2522.2	2635.4	2635.4	2689.1	2785.6	2820.8	2828.2
5°	1990.0	2049.3	2060.4	2175.4	2229.2	2344.2	2420.2	2602.0	2711.4	2780.0	2822.7
7.5°	1513.3	1533.7	1576.4	1684.0	1789.7	1928.8	2073.4	2305.2	2498.1	2576.0	2720.7
10°	1040.4	1101.6	1194.3	1290.8	1455.8	1609.8	1797.1	2015.9	2253.3	2349.8	2474.0
12.5°	701.0	786.3	934.7	1071.9	1224.0	1379.8	1557.8	1850.9	2119.8	2253.3	2377.6
15°	409.9	513.7	641.7	864.2	1066.4	1240.7	1418.8	1715.5	2041.9	2214.4	2366.4
17.5°	207.7	239.2	345.0	537.8	804.9	1090.5	1355.7	1734.0	2101.2	2312.7	2438.8
20°	155.8	165.1	194.7	285.6	550.8	901.3	1296.4	1761.8	2266.3	2524.1	2592.7
22.5°	135.4	142.8	155.8	185.5	309.7	689.9	1212.9	1830.5	2490.7	2733.6	2878.3
25°	115.0	122.4	133.5	152.1	198.4	469.2	1110.9	1902.8	2691.0	2997.0	3132.4
27.5°	100.1	105.7	116.8	131.7	161.3	298.6	934.7	1999.2	2997.0	3316.0	3351.2
30°	85.3	90.9	100.1	116.8	137.2	211.4	686.2	2012.2	3165.8	3455.1	3553.4
32.5°	74.2	76.0	87.2	102.0	115.0	166.9	482.2	2025.2	3290.0	3635.0	3655.4
35°	61.2	64.9	76.0	85.3	100.1	131.7	365.4	1960.3	3451.4	3820.4	3814.9
37.5°	50.1	55.6	63.1	70.5	81.6	111.3	291.2	1839.7	3653.5	4107.9	3933.6
40°	38.9	44.5	51.9	61.2	68.6	100.1	218.8	1658.0	3864.9	4248.8	4063.4
42.5°	27.8	31.5	38.9	48.2	61.2	83.5	157.6	1442.9	3948.4	4413.9	4219.2
45°	20.4	24.1	29.7	40.8	63.1	66.8	109.4	1246.3	4037.4	4486.2	4183.9
47.5°	11.1	14.8	22.3	35.2	55.6	50.1	77.9	1070.1	4139.4	4551.1	4211.7
50°	3.7	5.6	13.0	37.1	44.5	38.9	61.2	975.5	4239.6	4564.1	4267.4
52.5°	0.0	0.0	7.4	38.9	33.4	29.7	53.8	938.4	4213.6	4604.9	4232.1
55°	0.0	0.0	1.9	16.7	18.5	22.3	44.5	936.6	4397.2	4617.9	4425.0
57.5°	0.0	0.0	0.0	5.6	11.1	18.5	38.9	877.2	4514.0	4940.6	4684.7
60°	0.0	0.0	0.0	1.9	7.4	13.0	29.7	825.3	4632.7	5085.3	4962.9
62.5°	0.0	0.0	0.0	0.0	1.9	5.6	20.4	745.5	4393.5	5074.1	5231.8
65°	0.0	0.0	0.0	0.0	0.0	0.0	13.0	589.8	3952.1	4808.9	5083.4
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	7.4	408.0	3460.6	4475.1	4810.8
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	246.7	2793.0	3924.3	4080.1
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	105.7	1993.7	3115.7	3347.5
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	42.7	1233.3	2277.4	2563.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	16.7	799.3	1724.8	1945.5
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	3.7	426.6	1081.2	1257.4
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	185.5	656.5	756.7
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	59.3	398.7	454.4
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	61.2	81.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P599283  
 CATALOG NUMBER: IFLD-S-SA2A-760-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8	2629.8
2.5°	2831.9	2885.7	2906.1	2874.6	2878.3	2813.4	2804.1	2713.2	2676.2	2683.6
5°	2961.8	3039.7	3082.3	3047.1	2967.3	2843.1	2729.9	2622.4	2555.6	2522.2
7.5°	2932.1	3019.3	3073.0	3106.4	3015.5	2815.3	2642.8	2440.6	2355.3	2357.2
10°	2768.9	2950.6	3060.1	3017.4	2974.7	2774.4	2507.4	2288.6	2212.5	2219.9
12.5°	2637.2	2839.4	2904.3	2937.7	2850.5	2691.0	2511.1	2260.7	2175.4	2123.5
15°	2555.6	2705.8	2709.5	2761.5	2726.2	2726.2	2550.0	2305.2	2231.1	2173.6
17.5°	2555.6	2589.0	2585.3	2603.8	2663.2	2733.6	2648.3	2485.1	2338.6	2329.4
20°	2613.1	2509.2	2485.1	2492.6	2542.6	2752.2	2865.3	2661.3	2568.6	2538.9
22.5°	2746.6	2518.5	2372.0	2346.0	2500.0	2750.3	3004.4	2939.5	2778.2	2754.0
25°	2930.2	2501.8	2342.3	2309.0	2425.8	2817.1	3195.4	3208.4	3061.9	3011.8
27.5°	3104.6	2576.0	2338.6	2331.2	2485.1	2802.3	3327.1	3423.6	3258.5	3217.7
30°	3163.9	2650.2	2407.2	2309.0	2507.4	2856.1	3323.4	3575.6	3468.1	3477.3
32.5°	3234.4	2724.4	2414.7	2375.7	2602.0	2943.2	3429.1	3820.4	3742.5	3633.1
35°	3338.2	2824.5	2485.1	2449.9	2668.7	3021.1	3451.4	4000.3	3987.3	3859.4
37.5°	3427.3	2922.8	2631.6	2637.2	2872.7	3147.2	3549.7	4221.0	4198.8	4111.6
40°	3490.3	3060.1	2859.8	2874.6	3050.8	3288.2	3724.0	4332.3	4497.4	4369.4
42.5°	3499.6	3182.5	3121.3	3239.9	3405.0	3507.0	3794.5	4408.3	4645.7	4562.3
45°	3534.8	3377.2	3547.8	3635.0	3770.4	3699.9	3790.8	4538.2	4656.8	4614.2
47.5°	3672.1	3731.4	3946.5	4211.7	4260.0	4028.1	3879.8	4558.6	4719.9	4714.3
50°	3814.9	4111.6	4413.9	4590.1	4651.3	4254.4	3963.2	4541.9	4803.4	4758.8
52.5°	3974.4	4441.7	4877.5	5094.5	5061.1	4504.8	4057.8	4677.2	4957.3	4942.5
55°	4074.5	4590.1	5176.1	5478.4	5452.5	4784.8	4358.3	4872.0	5159.4	5122.3
57.5°	4339.7	4831.2	5472.9	5613.8	5682.4	5152.0	4567.8	5191.0	5328.2	5369.0
60°	4558.6	4988.8	5550.8	5754.8	5778.9	5370.9	4935.0	5519.2	5543.3	5406.1
62.5°	4879.4	5050.0	5385.7	5569.3	5693.6	5495.1	5265.1	5695.4	5539.6	5530.4
65°	5114.9	4849.7	5077.8	5179.8	5259.6	5305.9	5597.1	5816.0	5471.0	5291.1
67.5°	4983.3	4471.4	4428.7	4434.3	4458.4	4738.4	5485.8	5521.1	5089.0	4940.6
70°	4386.1	3668.4	3610.9	3655.4	3534.8	3872.4	5035.2	5018.5	4489.9	4336.0
72.5°	3547.8	2674.3	2576.0	2637.2	2665.0	3023.0	4235.9	3805.6	3275.2	3154.6
75°	2819.0	1960.3	1654.3	1802.7	1897.2	2201.4	3308.6	2585.3	2286.7	2123.5
77.5°	2214.4	1483.7	1287.1	1227.7	1314.9	1600.5	2407.2	1357.6	1198.1	1122.0
80°	1403.9	1090.5	1183.2	1097.9	1135.0	1142.4	1253.7	617.6	491.5	485.9
82.5°	845.7	745.5	886.5	487.8	888.3	793.8	521.1	280.0	248.5	248.5
85°	599.0	461.8	306.0	198.4	395.0	435.8	202.1	144.7	126.1	122.4
87.5°	300.4	142.8	68.6	44.5	50.1	81.6	24.1	11.1	11.1	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)