

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599255

Luminaire Tested: **IFLD-S-SA2B-750-U-SLR-HSS**

Issue Date: 05/04/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P599255
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/04/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-S-SA2B-750-U-SLR-HSS
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLR distribution lens with House Side Shield
 Light Source: (32) 5000K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 8507.3 lumens
 Efficiency: N/A
 Efficacy: 103.2 lumens/watt
 Spacing Criteria (0/90/45): 0.44 / 0.52 / 0.65
 Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
 CIE Type: Direct

Input Watts (W): 82.4
 Input Voltage (V): 120
 Input Current (A_{in}): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599255
CATALOG NUMBER: IFLD-S-SA2B-750-U-SLR-HSS

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ··· 90°-270° - · 135°-315°

TEST NUMBER: P599255
 CATALOG NUMBER: IFLD-S-SA2B-750-U-SLR-HSS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	107	101	96	91	104	99	94	90	94	90	87	90	87	84	87	84	82	79
2	95	85	77	70	92	83	75	69	79	73	67	76	71	66	73	68	64	62
3	85	72	63	55	82	71	62	54	67	60	53	65	58	52	62	56	51	49
4	76	62	52	44	74	61	51	44	58	50	43	56	49	43	53	47	42	40
5	69	55	44	37	67	53	44	36	51	43	36	49	41	35	47	40	35	33
6	63	48	38	31	61	47	38	31	45	37	30	44	36	30	42	35	30	27
7	58	43	33	27	56	42	33	26	41	32	26	39	32	26	38	31	26	24
8	54	39	30	23	52	38	29	23	37	29	23	36	28	23	34	28	23	20
9	50	36	27	21	49	35	26	21	34	26	20	33	25	20	32	25	20	18
10	47	33	24	18	46	32	24	18	31	24	18	30	23	18	29	23	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	70015	70015	70015	70015
5°	67408	49269	53035	74298
10°	60016	26824	27174	63525
15°	59910	17892	10939	61036
20°	71936	8932	4362	71514
25°	88476	5611	3378	88042
30°	106903	4504	2565	106219
35°	125437	3616	1989	124171
40°	151861	3094	1290	147671
45°	173734	2792	697	168918
50°	197110	2689	154	189045
55°	237769	2582	0	214353
60°	287866	2174	0	270781
65°	333331	1752	0	302951
70°	337533	1441	0	305482
75°	218440	957	0	234277
80°	74496	285	0	165778
85°	37396	0	0	121798

TEST NUMBER: P599255
 CATALOG NUMBER: IFLD-S-SA2B-750-U-SLR-HSS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	246.4	2.9
10°-20°	477.1	5.6
20°-30°	664.4	7.8
30°-40°	944.1	11.1
40°-50°	1309.2	15.4
50°-60°	1783.8	21.0
60°-70°	1961.2	23.1
70°-80°	963.9	11.3
80°-90°	157.4	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1387.9	16.3
0°-40°	2331.9	27.4
0°-60°	5424.9	63.8
0°-90°	8507.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8507.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	3252	3252	3252	3252	3252	
5°	3119	2280	2454	3438	3119	285
15°	2688	803	491	2739	2688	796
25°	3725	236	142	3706	3725	1732
35°	4773	138	76	4725	4773	3030
45°	5706	92	23	5548	5706	4424
55°	6335	69	0	5711	6335	5699
65°	6544	34	0	5947	6544	6324
75°	2626	12	0	2817	2626	2863
85°	151	0	0	493	151	209
90°	0	0	0	0	0	

TEST NUMBER: P599255
 CATALOG NUMBER: IFLD-S-SA2B-750-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3
2.5°	3318.9	3357.9	3321.2	3192.7	3169.8	3107.8	3013.8	3006.9	2908.3	2919.8	2867.0
5°	3119.3	3158.3	3080.3	2910.6	2752.3	2626.2	2550.5	2415.2	2385.4	2318.8	2318.8
7.5°	2915.2	2912.9	2779.9	2637.7	2401.4	2169.8	2064.3	1869.3	1754.6	1692.7	1633.1
10°	2745.5	2708.8	2626.2	2332.6	2075.7	1834.9	1704.2	1575.7	1456.4	1353.2	1250.0
12.5°	2626.2	2649.1	2518.4	2199.6	1867.0	1699.6	1559.7	1424.3	1282.1	1165.2	1050.5
15°	2688.1	2651.4	2497.7	2169.8	1832.6	1603.2	1417.5	1252.3	1094.1	940.4	853.2
17.5°	2880.8	2786.7	2605.5	2169.8	1761.5	1456.4	1231.7	1036.7	867.0	729.4	621.6
20°	3140.0	3032.2	2837.2	2250.0	1708.7	1348.6	1041.3	795.9	619.3	490.8	408.3
22.5°	3406.0	3321.2	3027.6	2282.1	1646.8	1204.1	821.1	575.7	412.9	330.3	289.0
25°	3724.8	3605.6	3284.5	2410.6	1555.1	1064.2	646.8	401.4	307.3	263.8	238.5
27.5°	3979.4	3958.8	3525.3	2488.6	1486.3	949.6	511.5	318.8	254.6	222.5	206.4
30°	4300.5	4188.1	3818.9	2644.5	1408.3	818.8	426.6	286.7	233.9	199.5	188.1
32.5°	4493.2	4440.4	3972.5	2731.7	1321.1	711.0	367.0	252.3	213.3	188.1	176.6
35°	4773.0	4667.5	4192.7	2786.7	1275.2	649.1	330.3	229.4	178.9	153.7	139.9
37.5°	5084.9	5046.0	4456.5	2784.4	1208.7	612.4	305.1	213.3	169.7	142.2	126.1
40°	5403.8	5245.5	4617.0	2848.7	1174.3	584.9	286.7	204.1	160.6	135.3	114.7
42.5°	5642.3	5461.1	4802.8	2825.7	1133.0	536.7	279.8	190.4	153.7	123.9	105.5
45°	5706.5	5642.3	4970.3	2818.9	1103.2	497.7	268.4	188.1	149.1	117.0	98.6
47.5°	5830.4	5786.8	5176.7	2830.3	1080.3	467.9	240.8	192.7	142.2	110.1	94.0
50°	5885.4	5807.4	5344.1	2857.8	1027.5	431.2	215.6	201.8	139.9	107.8	89.5
52.5°	6112.5	6043.7	5573.5	2935.8	984.0	383.0	190.4	192.7	144.5	100.9	84.9
55°	6335.0	6257.0	5926.7	3114.7	922.0	344.0	162.8	169.7	137.6	91.7	75.7
57.5°	6640.0	6511.6	6162.9	3188.1	867.0	291.3	144.5	139.9	128.4	82.6	66.5
60°	6685.9	6738.6	6128.5	3142.3	809.6	256.9	126.1	107.8	137.6	73.4	57.3
62.5°	6839.6	6619.4	5968.0	3036.7	768.4	236.2	112.4	89.5	119.3	64.2	48.2
65°	6543.7	6380.8	5591.8	2697.3	715.6	238.5	98.6	73.4	75.7	52.8	39.0
67.5°	6110.2	5981.7	4968.0	2328.0	662.9	233.9	87.2	64.2	57.3	45.9	34.4
70°	5362.5	5084.9	4220.3	1889.9	584.9	217.9	73.4	57.3	48.2	36.7	25.2
72.5°	3901.4	3789.1	3027.6	1461.0	525.2	197.3	68.8	48.2	41.3	27.5	20.6
75°	2626.2	2440.4	1910.6	958.7	422.0	172.0	57.3	43.6	32.1	20.6	16.1
77.5°	1387.6	1311.9	1082.6	456.4	233.9	80.3	32.1	25.2	18.3	16.1	9.2
80°	600.9	534.4	467.9	185.8	82.6	36.7	20.6	13.8	11.5	9.2	4.6
82.5°	307.3	293.6	243.1	80.3	48.2	27.5	11.5	9.2	6.9	4.6	2.3
85°	151.4	156.0	128.4	25.2	27.5	16.1	2.3	2.3	0.0	0.0	0.0
87.5°	11.5	11.5	9.2	4.6	6.9	2.3	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599255
 CATALOG NUMBER: IFLD-S-SA2B-750-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3
2.5°	2846.4	2878.5	2823.4	2857.8	2841.8	2848.7	2855.6	2837.2	2841.8	2906.0	2908.3
5°	2279.9	2341.8	2318.8	2351.0	2406.0	2378.5	2403.7	2399.1	2403.7	2412.9	2454.2
7.5°	1626.2	1607.8	1651.4	1736.3	1834.9	1894.5	1864.7	1848.7	1839.5	1816.5	1844.1
10°	1227.1	1217.9	1206.4	1231.7	1295.9	1362.4	1399.1	1337.2	1302.8	1259.2	1243.1
12.5°	1018.4	961.0	928.9	889.9	908.3	967.9	970.2	910.6	855.5	832.6	857.8
15°	802.8	763.8	706.4	651.4	623.9	669.7	630.7	573.4	502.3	493.1	490.8
17.5°	573.4	550.5	509.2	486.2	454.1	442.7	401.4	314.2	263.8	250.0	254.6
20°	389.9	371.6	369.3	348.6	334.9	325.7	259.2	201.8	185.8	188.1	190.4
22.5°	289.0	279.8	268.4	266.1	254.6	243.1	190.4	169.7	158.3	158.3	165.1
25°	236.2	231.7	220.2	215.6	211.0	195.0	160.6	144.5	139.9	135.3	142.2
27.5°	201.8	199.5	192.7	185.8	181.2	165.1	139.9	126.1	121.6	121.6	121.6
30°	181.2	181.2	172.0	158.3	158.3	139.9	119.3	110.1	105.5	105.5	103.2
32.5°	169.7	165.1	153.7	144.5	137.6	119.3	105.5	96.3	89.5	89.5	91.7
35°	137.6	137.6	135.3	128.4	119.3	100.9	89.5	80.3	75.7	73.4	75.7
37.5°	121.6	114.7	105.5	107.8	103.2	87.2	75.7	68.8	61.9	61.9	61.9
40°	110.1	103.2	94.0	87.2	84.9	78.0	66.5	55.0	48.2	45.9	45.9
42.5°	98.6	94.0	80.3	68.8	66.5	66.5	50.5	41.3	34.4	34.4	34.4
45°	91.7	84.9	73.4	59.6	48.2	50.5	41.3	29.8	25.2	22.9	22.9
47.5°	87.2	80.3	64.2	50.5	36.7	36.7	29.8	20.6	16.1	13.8	13.8
50°	80.3	73.4	57.3	41.3	27.5	22.9	18.3	11.5	6.9	4.6	4.6
52.5°	75.7	68.8	50.5	34.4	22.9	16.1	11.5	2.3	0.0	0.0	0.0
55°	68.8	59.6	43.6	27.5	18.3	9.2	2.3	0.0	0.0	0.0	0.0
57.5°	59.6	52.8	34.4	20.6	11.5	2.3	0.0	0.0	0.0	0.0	0.0
60°	50.5	43.6	27.5	16.1	4.6	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	41.3	36.7	20.6	9.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	34.4	27.5	16.1	2.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	29.8	22.9	11.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	22.9	16.1	6.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	16.1	11.5	2.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	11.5	6.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	6.9	2.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	2.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599255
 CATALOG NUMBER: IFLD-S-SA2B-750-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3
2.5°	2917.5	2986.3	3050.5	3068.9	3119.3	3259.2	3259.2	3325.7	3445.0	3488.6	3497.8
5°	2461.0	2534.4	2548.2	2690.4	2756.9	2899.1	2993.2	3217.9	3353.3	3438.1	3490.9
7.5°	1871.6	1896.8	1949.6	2082.6	2213.3	2385.4	2564.3	2851.0	3089.5	3185.8	3364.7
10°	1286.7	1362.4	1477.1	1596.4	1800.5	1990.9	2222.5	2493.2	2786.7	2906.0	3059.7
12.5°	867.0	972.5	1156.0	1325.7	1513.8	1706.4	1926.6	2289.0	2621.6	2786.7	2940.4
15°	506.9	635.3	793.6	1068.8	1318.8	1534.4	1754.6	2121.6	2525.3	2738.6	2926.7
17.5°	256.9	295.9	426.6	665.1	995.4	1348.6	1676.6	2144.5	2598.7	2860.1	3016.1
20°	192.7	204.1	240.8	353.2	681.2	1114.7	1603.2	2178.9	2802.8	3121.6	3206.5
22.5°	167.4	176.6	192.7	229.4	383.0	853.2	1500.0	2263.8	3080.3	3380.8	3559.7
25°	142.2	151.4	165.1	188.1	245.4	580.3	1373.9	2353.2	3328.0	3706.5	3873.9
27.5°	123.9	130.7	144.5	162.8	199.5	369.3	1156.0	2472.5	3706.5	4101.0	4144.6
30°	105.5	112.4	123.9	144.5	169.7	261.5	848.6	2488.6	3915.2	4273.0	4394.6
32.5°	91.7	94.0	107.8	126.1	142.2	206.4	596.3	2504.6	4068.9	4495.5	4520.7
35°	75.7	80.3	94.0	105.5	123.9	162.8	451.8	2424.4	4268.4	4724.8	4718.0
37.5°	61.9	68.8	78.0	87.2	100.9	137.6	360.1	2275.3	4518.4	5080.4	4864.8
40°	48.2	55.0	64.2	75.7	84.9	123.9	270.6	2050.5	4779.9	5254.7	5025.3
42.5°	34.4	39.0	48.2	59.6	75.7	103.2	195.0	1784.4	4883.1	5458.8	5218.0
45°	25.2	29.8	36.7	50.5	78.0	82.6	135.3	1541.3	4993.2	5548.3	5174.4
47.5°	13.8	18.3	27.5	43.6	68.8	61.9	96.3	1323.4	5119.3	5628.5	5208.8
50°	4.6	6.9	16.1	45.9	55.0	48.2	75.7	1206.4	5243.2	5644.6	5277.6
52.5°	0.0	0.0	9.2	48.2	41.3	36.7	66.5	1160.6	5211.1	5695.0	5234.0
55°	0.0	0.0	2.3	20.6	22.9	27.5	55.0	1158.3	5438.2	5711.1	5472.6
57.5°	0.0	0.0	0.0	6.9	13.8	22.9	48.2	1084.9	5582.7	6110.2	5793.7
60°	0.0	0.0	0.0	2.3	9.2	16.1	36.7	1020.7	5729.4	6289.1	6137.7
62.5°	0.0	0.0	0.0	0.0	2.3	6.9	25.2	922.0	5433.6	6275.3	6470.3
65°	0.0	0.0	0.0	0.0	0.0	0.0	16.1	729.4	4887.7	5947.3	6286.8
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	9.2	504.6	4279.9	5534.5	5949.6
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	305.1	3454.2	4853.3	5046.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	130.7	2465.6	3853.3	4140.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	52.8	1525.3	2816.6	3169.8
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	20.6	988.5	2133.1	2406.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.6	527.5	1337.2	1555.1
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	229.4	811.9	935.8
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	73.4	493.1	561.9
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	75.7	100.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599255
 CATALOG NUMBER: IFLD-S-SA2B-750-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3	3252.3
2.5°	3502.3	3568.9	3594.1	3555.1	3559.7	3479.4	3467.9	3355.6	3309.7	3318.9
5°	3662.9	3759.2	3812.0	3768.4	3669.8	3516.1	3376.2	3243.2	3160.6	3119.3
7.5°	3626.2	3734.0	3800.5	3841.8	3729.4	3481.7	3268.4	3018.4	2912.9	2915.2
10°	3424.4	3649.1	3784.5	3731.7	3679.0	3431.2	3101.0	2830.3	2736.3	2745.5
12.5°	3261.5	3511.5	3591.8	3633.1	3525.3	3328.0	3105.6	2795.9	2690.4	2626.2
15°	3160.6	3346.4	3351.0	3415.2	3371.6	3371.6	3153.7	2851.0	2759.2	2688.1
17.5°	3160.6	3201.9	3197.3	3220.2	3293.6	3380.8	3275.3	3073.4	2892.2	2880.8
20°	3231.7	3103.3	3073.4	3082.6	3144.5	3403.7	3543.6	3291.3	3176.7	3140.0
22.5°	3396.8	3114.7	2933.5	2901.4	3091.8	3401.4	3715.7	3635.4	3435.8	3406.0
25°	3623.9	3094.1	2896.8	2855.6	3000.0	3484.0	3951.9	3968.0	3786.8	3724.8
27.5°	3839.5	3185.8	2892.2	2883.1	3073.4	3465.7	4114.7	4234.0	4029.9	3979.4
30°	3912.9	3277.6	2977.1	2855.6	3101.0	3532.2	4110.2	4422.1	4289.1	4300.5
32.5°	4000.1	3369.3	2986.3	2938.1	3217.9	3640.0	4240.9	4724.8	4628.5	4493.2
35°	4128.5	3493.2	3073.4	3029.9	3300.5	3736.3	4268.4	4947.3	4931.3	4773.0
37.5°	4238.6	3614.7	3254.6	3261.5	3552.8	3892.3	4390.0	5220.3	5192.7	5084.9
40°	4316.6	3784.5	3536.8	3555.1	3773.0	4066.6	4605.6	5357.9	5562.0	5403.8
42.5°	4328.1	3935.8	3860.2	4006.9	4211.1	4337.2	4692.7	5451.9	5745.5	5642.3
45°	4371.6	4176.7	4387.7	4495.5	4662.9	4575.8	4688.1	5612.5	5759.3	5706.5
47.5°	4541.4	4614.8	4880.8	5208.8	5268.4	4981.7	4798.2	5637.7	5837.2	5830.4
50°	4718.0	5084.9	5458.8	5676.7	5752.4	5261.6	4901.5	5617.1	5940.5	5885.4
52.5°	4915.2	5493.2	6032.2	6300.6	6259.3	5571.2	5018.4	5784.5	6130.8	6112.5
55°	5039.1	5676.7	6401.5	6775.3	6743.2	5917.5	5390.0	6025.3	6380.8	6335.0
57.5°	5367.1	5974.9	6768.5	6942.8	7027.6	6371.7	5649.2	6419.8	6589.6	6640.0
60°	5637.7	6169.8	6864.8	7117.1	7146.9	6642.3	6103.3	6825.8	6855.6	6685.9
62.5°	6034.5	6245.5	6660.7	6887.7	7041.4	6796.0	6511.6	7043.7	6851.0	6839.6
65°	6325.8	5997.8	6279.9	6406.1	6504.7	6562.0	6922.1	7192.8	6766.2	6543.7
67.5°	6162.9	5529.9	5477.2	5484.0	5513.8	5860.2	6784.5	6828.1	6293.7	6110.2
70°	5424.4	4536.8	4465.7	4520.7	4371.6	4789.1	6227.2	6206.5	5552.8	5362.5
72.5°	4387.7	3307.4	3185.8	3261.5	3295.9	3738.6	5238.6	4706.5	4050.5	3901.4
75°	3486.3	2424.4	2045.9	2229.4	2346.4	2722.5	4091.8	3197.3	2828.0	2626.2
77.5°	2738.6	1834.9	1591.8	1518.4	1626.2	1979.4	2977.1	1678.9	1481.7	1387.6
80°	1736.3	1348.6	1463.3	1357.8	1403.7	1412.9	1550.5	763.8	607.8	600.9
82.5°	1045.9	922.0	1096.3	603.2	1098.6	981.7	644.5	346.3	307.3	307.3
85°	740.8	571.1	378.4	245.4	488.5	539.0	250.0	178.9	156.0	151.4
87.5°	371.6	176.6	84.9	55.0	61.9	100.9	29.8	13.8	13.8	11.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)