

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599288

Luminaire Tested: **IFLD-S-SA3A-760-U-SLR-HSS**

Issue Date: 05/04/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P599288
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/04/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-S-SA3A-760-U-SLR-HSS
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLR distribution lens with House Side Shield
 Light Source: (48) 5700K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 10251.4 lumens
 Efficiency: N/A
 Efficacy: 108.1 lumens/watt
 Spacing Criteria (0/90/45): 0.44 / 0.52 / 0.65
 Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
 CIE Type: Direct

Input Watts (W): 94.8
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599288
CATALOG NUMBER: IFLD-S-SA3A-760-U-SLR-HSS

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ··· 90°-270° - · 135°-315°

TEST NUMBER: P599288
 CATALOG NUMBER: IFLD-S-SA3A-760-U-SLR-HSS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	107	101	96	91	104	99	94	90	94	90	87	90	87	84	87	84	82	79
2	95	85	77	70	92	83	75	69	79	73	67	76	71	66	73	68	64	62
3	85	72	63	55	82	71	62	54	67	60	53	65	58	52	62	56	51	49
4	76	62	52	44	74	61	51	44	58	50	43	56	49	43	53	47	42	40
5	69	55	44	37	67	53	44	36	51	43	36	49	41	35	47	40	35	33
6	63	48	38	31	61	47	38	31	45	37	30	44	36	30	42	35	30	27
7	58	43	33	27	56	42	33	26	41	32	26	39	32	26	38	31	26	24
8	54	39	30	23	52	38	29	23	37	29	23	36	28	23	34	28	23	20
9	50	36	27	21	49	35	26	21	34	26	20	33	25	20	32	25	20	18
10	47	33	24	18	46	32	24	18	31	24	18	30	23	18	29	23	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	56246	56246	56246	56246
5°	54152	39578	42605	59687
10°	48213	21548	21831	51033
15°	48129	14372	8789	49032
20°	57788	7177	3504	57451
25°	71078	4508	2714	70726
30°	85880	3618	2062	85330
35°	100769	2905	1598	99753
40°	121995	2486	1036	118629
45°	139568	2245	560	135697
50°	158347	2159	123	151868
55°	191009	2074	0	172197
60°	231255	1745	0	217529
65°	267777	1409	0	243374
70°	271151	1158	0	245407
75°	175482	765	0	188202
80°	59846	231	0	133173
85°	30036	0	0	97847

TEST NUMBER: P599288
 CATALOG NUMBER: IFLD-S-SA3A-760-U-SLR-HSS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	296.9	2.9
10°-20°	574.9	5.6
20°-30°	800.6	7.8
30°-40°	1137.6	11.1
40°-50°	1577.6	15.4
50°-60°	2149.5	21.0
60°-70°	2363.2	23.1
70°-80°	1161.5	11.3
80°-90°	189.7	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1672.4	16.3
0°-40°	2810.0	27.4
0°-60°	6537.0	63.8
0°-90°	10251.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10251.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	3919	3919	3919	3919	3919	
5°	3759	2747	2957	4143	3759	344
15°	3239	967	592	3300	3239	959
25°	4488	285	171	4466	4488	2087
35°	5752	166	91	5694	5752	3651
45°	6876	111	28	6686	6876	5330
55°	7634	83	0	6882	7634	6867
65°	7885	42	0	7167	7885	7620
75°	3165	14	0	3394	3165	3450
85°	182	0	0	594	182	252
90°	0	0	0	0	0	

TEST NUMBER: P599288
 CATALOG NUMBER: IFLD-S-SA3A-760-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1
2.5°	3999.3	4046.2	4002.0	3847.2	3819.6	3745.0	3631.7	3623.4	3504.5	3518.4	3454.8
5°	3758.8	3805.8	3711.8	3507.3	3316.6	3164.6	3073.4	2910.3	2874.4	2794.2	2794.2
7.5°	3512.8	3510.1	3349.8	3178.4	2893.7	2614.6	2487.4	2252.5	2114.3	2039.7	1967.8
10°	3308.3	3264.1	3164.6	2810.8	2501.3	2211.1	2053.5	1898.7	1755.0	1630.7	1506.3
12.5°	3164.6	3192.2	3034.7	2650.5	2249.8	2048.0	1879.4	1716.3	1545.0	1404.0	1265.8
15°	3239.2	3195.0	3009.8	2614.6	2208.3	1931.9	1708.0	1509.1	1318.3	1133.2	1028.1
17.5°	3471.4	3358.1	3139.7	2614.6	2122.6	1755.0	1484.2	1249.3	1044.7	878.9	749.0
20°	3783.7	3653.8	3418.9	2711.3	2059.1	1625.1	1254.8	959.0	746.2	591.5	492.0
22.5°	4104.3	4002.0	3648.3	2750.0	1984.4	1451.0	989.5	693.7	497.5	398.0	348.2
25°	4488.5	4344.7	3957.8	2904.8	1873.9	1282.4	779.4	483.7	370.4	317.8	287.4
27.5°	4795.2	4770.4	4248.0	2998.8	1791.0	1144.2	616.3	384.2	306.8	268.1	248.7
30°	5182.2	5046.8	4601.8	3186.7	1697.0	986.7	514.1	345.5	281.9	240.5	226.6
32.5°	5414.3	5350.8	4787.0	3291.7	1592.0	856.8	442.2	304.0	257.0	226.6	212.8
35°	5751.5	5624.4	5052.3	3358.1	1536.7	782.2	398.0	276.4	215.6	185.2	168.6
37.5°	6127.4	6080.4	5370.1	3355.3	1456.5	737.9	367.6	257.0	204.5	171.4	152.0
40°	6511.6	6320.9	5563.6	3432.7	1415.1	704.8	345.5	246.0	193.5	163.1	138.2
42.5°	6799.0	6580.7	5787.5	3405.0	1365.3	646.7	337.2	229.4	185.2	149.2	127.1
45°	6876.4	6799.0	5989.2	3396.7	1329.4	599.8	323.4	226.6	179.6	141.0	118.8
47.5°	7025.7	6973.1	6238.0	3410.6	1301.8	563.8	290.2	232.2	171.4	132.7	113.3
50°	7092.0	6998.0	6439.7	3443.7	1238.2	519.6	259.8	243.2	168.6	129.9	107.8
52.5°	7365.6	7282.7	6716.1	3537.7	1185.7	461.6	229.4	232.2	174.1	121.6	102.3
55°	7633.7	7539.7	7141.7	3753.3	1111.1	414.6	196.2	204.5	165.8	110.6	91.2
57.5°	8001.3	7846.5	7426.4	3841.7	1044.7	351.0	174.1	168.6	154.8	99.5	80.2
60°	8056.6	8120.1	7384.9	3786.4	975.6	309.5	152.0	129.9	165.8	88.4	69.1
62.5°	8241.7	7976.4	7191.5	3659.3	925.9	284.7	135.4	107.8	143.7	77.4	58.0
65°	7885.2	7689.0	6738.2	3250.3	862.3	287.4	118.8	88.4	91.2	63.6	47.0
67.5°	7362.8	7208.1	5986.5	2805.3	798.7	281.9	105.0	77.4	69.1	55.3	41.5
70°	6461.8	6127.4	5085.4	2277.4	704.8	262.6	88.4	69.1	58.0	44.2	30.4
72.5°	4701.3	4565.8	3648.3	1760.6	632.9	237.7	82.9	58.0	49.7	33.2	24.9
75°	3164.6	2940.7	2302.3	1155.3	508.5	207.3	69.1	52.5	38.7	24.9	19.3
77.5°	1672.1	1580.9	1304.5	550.0	281.9	96.7	38.7	30.4	22.1	19.3	11.1
80°	724.1	644.0	563.8	223.9	99.5	44.2	24.9	16.6	13.8	11.1	5.5
82.5°	370.4	353.8	293.0	96.7	58.0	33.2	13.8	11.1	8.3	5.5	2.8
85°	182.4	187.9	154.8	30.4	33.2	19.3	2.8	2.8	0.0	0.0	0.0
87.5°	13.8	13.8	11.1	5.5	8.3	2.8	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599288
 CATALOG NUMBER: IFLD-S-SA3A-760-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1
2.5°	3429.9	3468.6	3402.3	3443.7	3424.4	3432.7	3441.0	3418.9	3424.4	3501.8	3504.5
5°	2747.2	2821.9	2794.2	2832.9	2899.3	2866.1	2896.5	2891.0	2896.5	2907.5	2957.3
7.5°	1959.6	1937.4	1990.0	2092.2	2211.1	2282.9	2247.0	2227.6	2216.6	2189.0	2222.1
10°	1478.6	1467.6	1453.8	1484.2	1561.6	1641.7	1685.9	1611.3	1569.9	1517.3	1498.0
12.5°	1227.1	1158.0	1119.4	1072.4	1094.5	1166.3	1169.1	1097.2	1030.9	1003.3	1033.7
15°	967.3	920.4	851.3	784.9	751.8	807.0	760.1	691.0	605.3	594.2	591.5
17.5°	691.0	663.3	613.6	585.9	547.2	533.4	483.7	378.6	317.8	301.3	306.8
20°	469.9	447.7	445.0	420.1	403.5	392.5	312.3	243.2	223.9	226.6	229.4
22.5°	348.2	337.2	323.4	320.6	306.8	293.0	229.4	204.5	190.7	190.7	199.0
25°	284.7	279.1	265.3	259.8	254.3	234.9	193.5	174.1	168.6	163.1	171.4
27.5°	243.2	240.5	232.2	223.9	218.3	199.0	168.6	152.0	146.5	146.5	146.5
30°	218.3	218.3	207.3	190.7	190.7	168.6	143.7	132.7	127.1	127.1	124.4
32.5°	204.5	199.0	185.2	174.1	165.8	143.7	127.1	116.1	107.8	107.8	110.6
35°	165.8	165.8	163.1	154.8	143.7	121.6	107.8	96.7	91.2	88.4	91.2
37.5°	146.5	138.2	127.1	129.9	124.4	105.0	91.2	82.9	74.6	74.6	74.6
40°	132.7	124.4	113.3	105.0	102.3	94.0	80.2	66.3	58.0	55.3	55.3
42.5°	118.8	113.3	96.7	82.9	80.2	80.2	60.8	49.7	41.5	41.5	41.5
45°	110.6	102.3	88.4	71.9	58.0	60.8	49.7	35.9	30.4	27.6	27.6
47.5°	105.0	96.7	77.4	60.8	44.2	44.2	35.9	24.9	19.3	16.6	16.6
50°	96.7	88.4	69.1	49.7	33.2	27.6	22.1	13.8	8.3	5.5	5.5
52.5°	91.2	82.9	60.8	41.5	27.6	19.3	13.8	2.8	0.0	0.0	0.0
55°	82.9	71.9	52.5	33.2	22.1	11.1	2.8	0.0	0.0	0.0	0.0
57.5°	71.9	63.6	41.5	24.9	13.8	2.8	0.0	0.0	0.0	0.0	0.0
60°	60.8	52.5	33.2	19.3	5.5	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	49.7	44.2	24.9	11.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	41.5	33.2	19.3	2.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	35.9	27.6	13.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	27.6	19.3	8.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	19.3	13.8	2.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	13.8	8.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	8.3	2.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	2.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599288
 CATALOG NUMBER: IFLD-S-SA3A-760-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1
2.5°	3515.6	3598.5	3675.9	3698.0	3758.8	3927.4	3927.4	4007.6	4151.3	4203.8	4214.8
5°	2965.6	3054.0	3070.6	3242.0	3322.1	3493.5	3606.8	3877.7	4040.7	4143.0	4206.5
7.5°	2255.3	2285.7	2349.3	2509.6	2667.1	2874.4	3090.0	3435.4	3722.9	3839.0	4054.5
10°	1550.5	1641.7	1779.9	1923.6	2169.6	2399.0	2678.1	3004.3	3358.1	3501.8	3686.9
12.5°	1044.7	1171.9	1393.0	1597.5	1824.1	2056.3	2321.6	2758.3	3159.1	3358.1	3543.2
15°	610.8	765.6	956.3	1287.9	1589.2	1849.0	2114.3	2556.5	3043.0	3300.0	3526.6
17.5°	309.5	356.5	514.1	801.5	1199.5	1625.1	2020.4	2584.2	3131.4	3446.5	3634.4
20°	232.2	246.0	290.2	425.6	820.9	1343.2	1931.9	2625.6	3377.4	3761.6	3863.8
22.5°	201.8	212.8	232.2	276.4	461.6	1028.1	1807.5	2727.9	3711.8	4073.9	4289.5
25°	171.4	182.4	199.0	226.6	295.7	699.2	1655.5	2835.7	4010.3	4466.3	4668.1
27.5°	149.2	157.5	174.1	196.2	240.5	445.0	1393.0	2979.4	4466.3	4941.7	4994.2
30°	127.1	135.4	149.2	174.1	204.5	315.1	1022.6	2998.8	4717.9	5149.0	5295.5
32.5°	110.6	113.3	129.9	152.0	171.4	248.7	718.6	3018.1	4903.0	5417.1	5447.5
35°	91.2	96.7	113.3	127.1	149.2	196.2	544.5	2921.4	5143.5	5693.5	5685.2
37.5°	74.6	82.9	94.0	105.0	121.6	165.8	433.9	2741.7	5444.7	6121.9	5862.1
40°	58.0	66.3	77.4	91.2	102.3	149.2	326.1	2470.9	5759.8	6331.9	6055.5
42.5°	41.5	47.0	58.0	71.9	91.2	124.4	234.9	2150.3	5884.2	6577.9	6287.7
45°	30.4	35.9	44.2	60.8	94.0	99.5	163.1	1857.3	6016.9	6685.7	6235.2
47.5°	16.6	22.1	33.2	52.5	82.9	74.6	116.1	1594.7	6168.9	6782.4	6276.7
50°	5.5	8.3	19.3	55.3	66.3	58.0	91.2	1453.8	6318.1	6801.8	6359.6
52.5°	0.0	0.0	11.1	58.0	49.7	44.2	80.2	1398.5	6279.4	6862.6	6307.1
55°	0.0	0.0	2.8	24.9	27.6	33.2	66.3	1395.7	6553.0	6881.9	6594.5
57.5°	0.0	0.0	0.0	8.3	16.6	27.6	58.0	1307.3	6727.2	7362.8	6981.4
60°	0.0	0.0	0.0	2.8	11.1	19.3	44.2	1229.9	6904.0	7578.4	7396.0
62.5°	0.0	0.0	0.0	0.0	2.8	8.3	30.4	1111.1	6547.5	7561.8	7796.8
65°	0.0	0.0	0.0	0.0	0.0	0.0	19.3	878.9	5889.7	7166.6	7575.7
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	11.1	608.0	5157.3	6669.1	7169.4
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	367.6	4162.3	5848.3	6080.4
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	157.5	2971.1	4643.2	4988.7
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	63.6	1837.9	3394.0	3819.6
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	24.9	1191.2	2570.4	2899.3
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	5.5	635.7	1611.3	1873.9
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	276.4	978.4	1127.6
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	88.4	594.2	677.1
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	91.2	121.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599288
 CATALOG NUMBER: IFLD-S-SA3A-760-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1	3919.1
2.5°	4220.4	4300.5	4330.9	4283.9	4289.5	4192.7	4178.9	4043.5	3988.2	3999.3
5°	4413.8	4529.9	4593.5	4541.0	4422.1	4236.9	4068.4	3908.1	3808.6	3758.8
7.5°	4369.6	4499.5	4579.7	4629.4	4494.0	4195.5	3938.5	3637.2	3510.1	3512.8
10°	4126.4	4397.3	4560.3	4496.7	4433.2	4134.7	3736.7	3410.6	3297.2	3308.3
12.5°	3930.2	4231.4	4328.2	4377.9	4248.0	4010.3	3742.2	3369.1	3242.0	3164.6
15°	3808.6	4032.4	4038.0	4115.3	4062.8	4062.8	3800.3	3435.4	3324.9	3239.2
17.5°	3808.6	3858.3	3852.8	3880.4	3968.9	4073.9	3946.7	3703.5	3485.2	3471.4
20°	3894.2	3739.5	3703.5	3714.6	3789.2	4101.5	4270.1	3966.1	3827.9	3783.7
22.5°	4093.2	3753.3	3534.9	3496.2	3725.6	4098.8	4477.4	4380.7	4140.2	4104.3
25°	4366.8	3728.4	3490.7	3441.0	3615.1	4198.3	4762.1	4781.4	4563.1	4488.5
27.5°	4626.6	3839.0	3485.2	3474.1	3703.5	4176.1	4958.3	5102.0	4856.0	4795.2
30°	4715.1	3949.5	3587.4	3441.0	3736.7	4256.3	4952.8	5328.7	5168.4	5182.2
32.5°	4820.1	4060.1	3598.5	3540.5	3877.7	4386.2	5110.3	5693.5	5577.4	5414.3
35°	4974.9	4209.3	3703.5	3651.0	3977.1	4502.3	5143.5	5961.6	5942.2	5751.5
37.5°	5107.6	4355.8	3921.9	3930.2	4281.2	4690.2	5290.0	6290.5	6257.3	6127.4
40°	5201.5	4560.3	4261.8	4283.9	4546.5	4900.3	5549.8	6456.3	6702.3	6511.6
42.5°	5215.3	4742.7	4651.5	4828.4	5074.4	5226.4	5654.8	6569.6	6923.4	6799.0
45°	5267.9	5032.9	5287.2	5417.1	5618.9	5513.8	5649.3	6763.1	6940.0	6876.4
47.5°	5472.4	5560.8	5881.4	6276.7	6348.5	6003.0	5781.9	6793.5	7033.9	7025.7
50°	5685.2	6127.4	6577.9	6840.5	6931.7	6340.2	5906.3	6768.6	7158.3	7092.0
52.5°	5922.9	6619.4	7268.9	7592.2	7542.5	6713.3	6047.3	6970.4	7387.7	7365.6
55°	6072.1	6840.5	7713.8	8164.3	8125.7	7130.7	6495.0	7260.6	7689.0	7633.7
57.5°	6467.4	7199.8	8156.1	8366.1	8468.4	7677.9	6807.3	7736.0	7940.5	8001.3
60°	6793.5	7434.7	8272.1	8576.2	8612.1	8004.0	7354.5	8225.2	8261.1	8056.6
62.5°	7271.6	7525.9	8026.2	8299.8	8485.0	8189.2	7846.5	8487.7	8255.6	8241.7
65°	7622.6	7227.4	7567.4	7719.4	7838.2	7907.3	8341.2	8667.4	8153.3	7885.2
67.5°	7426.4	6663.6	6600.0	6608.3	6644.2	7061.6	8175.4	8227.9	7583.9	7362.8
70°	6536.5	5466.9	5381.2	5447.5	5267.9	5770.9	7503.8	7478.9	6691.2	6461.8
72.5°	5287.2	3985.4	3839.0	3930.2	3971.6	4505.0	6312.6	5671.4	4880.9	4701.3
75°	4201.0	2921.4	2465.3	2686.4	2827.4	3280.7	4930.7	3852.8	3407.8	3164.6
77.5°	3300.0	2211.1	1918.1	1829.7	1959.6	2385.2	3587.4	2023.1	1785.4	1672.1
80°	2092.2	1625.1	1763.3	1636.2	1691.5	1702.5	1868.3	920.4	732.4	724.1
82.5°	1260.3	1111.1	1321.1	726.9	1323.9	1182.9	776.6	417.3	370.4	370.4
85°	892.7	688.2	456.0	295.7	588.7	649.5	301.3	215.6	187.9	182.4
87.5°	447.7	212.8	102.3	66.3	74.6	121.6	35.9	16.6	16.6	13.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)