

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599019

Luminaire Tested: **IFLD-L-SA8B-750-U-SLL**

Issue Date: 05/03/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P599019
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/03/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-L-SA8B-750-U-SLL
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens
 Light Source: (128) 5000K CCT, 70 CRI LEDS
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 35411.2 lumens
 Efficiency: N/A
 Efficacy: 110.7 lumens/watt
 Spacing Criteria (0/90/45): 1.12 / 0.52 / 0.8
 Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
 CIE Type: Direct

Input Watts (W): 320
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599019
CATALOG NUMBER: IFLD-L-SA8B-750-U-SLL

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ··· 90°-270° - · 135°-315°

TEST NUMBER: P599019

CATALOG NUMBER: IFLD-L-SA8B-750-U-SLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	106	100	94	89	103	97	92	88	93	89	85	89	85	82	85	82	80	77
2	94	83	75	68	91	81	74	67	78	71	65	74	69	64	71	66	62	60
3	84	71	61	53	81	69	60	53	66	58	52	63	56	51	60	55	50	47
4	75	61	51	43	73	60	50	42	57	48	42	54	47	41	52	46	40	38
5	68	53	43	35	66	52	42	35	50	41	34	48	40	34	46	39	34	31
6	63	47	37	30	60	46	37	29	44	36	29	42	35	29	41	34	29	26
7	58	42	32	25	56	41	32	25	40	31	25	38	31	25	37	30	25	22
8	53	38	29	22	52	37	28	22	36	28	22	35	27	22	33	27	22	19
9	50	35	26	20	48	34	26	20	33	25	19	32	25	19	31	24	19	17
10	46	32	23	18	45	31	23	18	30	23	17	29	22	17	28	22	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	60870	60870	60870	60870
5°	66874	59406	42603	46506
10°	59234	52281	25840	27729
15°	57679	49626	18293	18993
20°	65767	57400	11966	13226
25°	80129	72761	10448	10821
30°	96547	88250	10836	10055
35°	112599	103621	8979	8463
40°	135305	125151	8387	7946
45°	157462	143833	8489	7891
50°	177953	163486	8681	8154
55°	207533	194857	8991	8549
60°	253121	246188	8962	8962
65°	284464	284863	9202	9602
70°	279567	289455	9640	9887
75°	230613	245965	10127	10780
80°	166506	174785	11198	11685
85°	92151	98944	12610	15518

TEST NUMBER: P599019
 CATALOG NUMBER: IFLD-L-SA8B-750-U-SLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	878.7	2.5
10°-20°	1855.1	5.2
20°-30°	2714.2	7.7
30°-40°	3824.2	10.8
40°-50°	5255.6	14.8
50°-60°	7162.8	20.2
60°-70°	7839.3	22.1
70°-80°	4525.9	12.8
80°-90°	1355.3	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5448.0	15.4
0°-40°	9272.2	26.2
0°-60°	21690.6	61.3
0°-90°	35411.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	35411.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	11310	11310	11310	11310	11310	
5°	12378	10996	7886	8608	12378	1124
15°	10352	8907	3283	3409	10352	3024
25°	13494	12253	1759	1822	13494	6319
35°	17138	15771	1367	1288	17138	10867
45°	20688	18897	1115	1037	20688	15900
55°	22118	20767	958	911	22118	19956
65°	22338	22369	723	754	22338	21379
75°	11090	11828	487	518	11090	11913
85°	1492	1602	204	251	1492	2071
90°	0	0	0	0	0	

TEST NUMBER: P599019
 CATALOG NUMBER: IFLD-L-SA8B-750-U-SLL

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1
2.5°	12111.3	12064.2	12111.3	12284.1	12331.2	12409.7	12409.7	12299.8	12095.6	12001.3	11844.2
5°	12378.3	12299.8	12692.5	13053.8	13336.5	13305.1	13038.1	12818.2	12409.7	11797.1	11215.9
7.5°	11844.2	11922.8	12205.5	13148.0	13807.8	13933.5	13509.3	13069.5	12189.8	11341.6	10556.1
10°	10838.9	10948.8	11561.5	12535.4	13572.2	13776.4	13509.3	12975.2	11922.8	10870.3	9959.2
12.5°	10351.9	10603.3	10964.6	12142.7	12881.0	13368.0	13242.3	12896.7	11718.6	10477.6	9597.9
15°	10351.9	10414.8	10948.8	11938.5	12362.6	12378.3	12425.4	12488.3	11781.4	10650.4	9472.2
17.5°	10681.8	10854.6	11310.1	11922.8	12001.3	11812.8	11812.8	12079.9	11907.1	11137.3	9927.8
20°	11482.9	11420.1	12017.0	12268.4	11844.2	11373.0	11325.9	11781.4	12048.4	11655.7	10760.3
22.5°	12284.1	12566.8	13053.8	12488.3	11702.9	11074.5	11011.7	11577.2	12472.6	12551.1	11718.6
25°	13493.6	13776.4	14027.7	13336.5	11687.1	10996.0	11043.1	11482.9	12991.0	13823.5	13320.8
27.5°	14797.4	14970.2	15331.5	14263.3	12064.2	10901.7	10948.8	11608.6	13477.9	14656.1	14577.5
30°	15535.7	15724.2	15645.7	14436.1	12315.5	10964.6	10838.9	11781.4	13210.9	14656.1	15394.4
32.5°	16258.3	16148.4	16101.2	14718.9	12629.7	11357.3	11043.1	12142.7	13368.0	14891.7	16446.8
35°	17138.0	16980.9	16855.3	15268.7	13148.0	11734.3	11592.9	12613.9	13713.5	15378.7	17295.1
37.5°	18111.9	18111.9	17499.3	15677.1	13760.7	12346.9	12189.8	13289.4	14263.3	15677.1	18457.5
40°	19258.7	19305.8	18221.9	16226.9	14451.8	13320.8	13273.7	14169.1	14797.4	16117.0	19572.8
42.5°	20106.9	20138.3	18850.2	16431.1	15253.0	14671.8	14876.0	15582.9	15410.1	16509.7	19651.4
45°	20688.1	20531.0	19290.1	17012.3	16132.7	16698.2	16761.0	16965.2	16211.2	16745.3	19965.5
47.5°	20970.9	20939.5	19478.6	17687.8	17986.3	18756.0	19117.3	18834.5	16949.5	16494.0	19965.5
50°	21253.6	20986.6	19651.4	18614.6	19792.7	21347.9	21269.4	20751.0	17970.6	16808.1	19667.1
52.5°	21442.1	21206.5	19997.0	19447.2	21520.7	23280.0	23594.2	22636.0	19164.4	17389.3	19808.5
55°	22117.6	21929.1	21033.7	20578.2	23515.7	25322.2	25369.3	24034.1	20421.1	18347.6	20735.3
57.5°	22934.5	23044.4	22463.2	22180.4	25039.4	26814.5	26641.7	25070.8	21489.3	19510.0	21803.4
60°	23515.7	23688.5	23547.1	23578.5	25793.4	27317.1	26924.4	25714.9	22274.7	20389.7	23107.2
62.5°	23201.5	23547.1	24128.3	24002.6	25824.8	26955.8	26406.0	24866.6	22368.9	21536.4	24096.9
65°	22337.5	22368.9	23500.0	24191.1	24411.1	25086.5	24363.9	23091.5	21395.0	22243.3	23955.5
67.5°	20122.6	20374.0	21395.0	22746.0	21819.1	21976.2	21913.4	20075.5	19918.4	21756.3	22871.6
70°	17766.3	17939.1	19054.4	20641.0	18426.1	17687.8	17829.2	16462.5	17106.6	20248.3	20688.1
72.5°	14687.5	14797.4	16069.8	17467.9	14781.7	13462.2	13792.1	12676.8	13587.9	17719.2	17452.2
75°	11090.2	11294.4	12284.1	13933.5	10886.0	10037.8	10367.6	9912.1	10760.3	14593.2	13540.8
77.5°	7885.7	7728.6	8953.9	10901.7	8184.1	7681.5	7712.9	7791.4	8702.5	12299.8	9723.6
80°	5372.3	5419.4	6519.0	7995.6	6424.8	6346.2	6267.7	6896.0	7304.5	9739.3	7068.8
82.5°	3188.8	3188.8	4398.4	5686.5	5073.9	5717.9	5356.6	5922.1	5717.9	7163.1	4634.0
85°	1492.3	1492.3	2262.0	4099.9	3927.1	4712.6	4005.7	4476.9	4225.6	4995.3	2089.2
87.5°	251.3	219.9	455.5	2010.7	1618.0	1837.9	722.6	2387.7	2654.7	3487.3	518.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599019
 CATALOG NUMBER: IFLD-L-SA8B-750-U-SLL

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1
2.5°	11671.4	11561.5	11341.6	11058.8	10823.2	10524.7	10430.5	10226.3	9943.5	9912.1	9786.4
5°	10996.0	10619.0	10147.7	9566.5	9173.8	8765.4	8419.8	8215.6	7979.9	7948.5	7885.7
7.5°	10257.7	9786.4	9001.0	8309.8	7634.3	6990.3	6676.1	6283.4	6016.4	5812.2	5717.9
10°	9566.5	9126.7	8152.7	7210.2	6613.3	6189.2	5812.2	5403.7	5073.9	4822.5	4728.3
12.5°	9110.9	8592.6	7540.1	6644.7	6204.9	5717.9	5293.8	4853.9	4429.8	4099.9	3927.1
15°	8906.7	8419.8	7351.6	6362.0	5717.9	5042.4	4555.5	4115.6	3597.3	3361.6	3283.1
17.5°	9393.7	8671.1	7288.8	6032.1	5121.0	4351.3	3754.3	3283.1	2906.1	2670.5	2576.2
20°	10022.0	9126.7	7398.7	5639.4	4555.5	3691.5	3031.7	2529.1	2277.7	2104.9	2089.2
22.5°	10823.2	9802.1	7571.5	5356.6	3927.1	2968.9	2372.0	2073.5	1900.7	1885.0	1853.6
25°	12252.7	11027.4	7854.3	4979.6	3424.5	2450.5	2026.4	1853.6	1775.1	1727.9	1759.4
27.5°	13477.9	11828.5	8058.5	4744.0	3220.2	2309.2	1963.6	1775.1	1696.5	1680.8	1696.5
30°	14200.5	12566.8	7995.6	4304.1	2811.8	2199.2	2089.2	2026.4	1869.3	1743.6	1743.6
32.5°	14860.3	13038.1	7979.9	3911.4	2403.4	1837.9	1743.6	1696.5	1790.8	1853.6	1806.5
35°	15771.4	13776.4	7932.8	3691.5	2230.6	1696.5	1539.4	1413.8	1350.9	1319.5	1366.6
37.5°	16745.3	14279.1	7807.1	3660.1	2136.4	1618.0	1492.3	1366.6	1303.8	1272.4	1256.7
40°	17813.5	14813.1	7665.8	3503.0	2089.2	1570.9	1445.2	1335.2	1256.7	1209.6	1193.8
42.5°	18504.6	15237.3	7524.4	3424.5	1995.0	1539.4	1398.1	1303.8	1225.3	1162.4	1162.4
45°	18897.4	15739.9	7383.0	3345.9	1885.0	1555.1	1398.1	1272.4	1178.1	1146.7	1115.3
47.5°	19070.2	16117.0	7335.9	3220.2	1790.8	1492.3	1366.6	1241.0	1146.7	1083.9	1068.2
50°	19525.7	16918.1	7508.7	3126.0	1680.8	1429.5	1445.2	1225.3	1131.0	1052.5	1036.8
52.5°	19792.7	17562.1	7885.7	2984.6	1602.3	1350.9	1413.8	1193.8	1083.9	1005.3	1005.3
55°	20766.7	18630.3	8294.1	2874.7	1508.0	1241.0	1303.8	1131.0	1005.3	958.2	958.2
57.5°	22007.7	19761.3	8639.7	2827.5	1445.2	1162.4	1162.4	1099.6	958.2	895.4	879.7
60°	22871.6	20688.1	8843.9	2796.1	1382.4	1083.9	1036.8	1099.6	911.1	848.3	832.6
62.5°	22965.9	20154.0	8639.7	2780.4	1366.6	1005.3	942.5	1052.5	864.0	801.1	769.7
65°	22368.9	19070.2	8074.2	2717.6	1350.9	926.8	879.7	911.1	801.1	754.0	722.6
67.5°	21175.1	17310.8	7257.3	2686.2	1335.2	864.0	801.1	785.4	738.3	691.2	659.8
70°	18394.7	15017.4	6299.1	2544.8	1303.8	816.8	722.6	706.9	659.8	628.3	612.6
72.5°	15441.5	12284.1	5199.5	2356.3	1241.0	738.3	659.8	628.3	612.6	565.5	549.8
75°	11828.5	9456.5	4162.8	2089.2	1083.9	659.8	581.2	549.8	534.1	502.7	487.0
77.5°	8309.8	7037.4	3078.9	1696.5	911.1	596.9	518.4	487.0	471.3	424.1	424.1
80°	5639.4	4932.5	2089.2	1178.1	706.9	487.0	455.5	424.1	392.7	361.3	361.3
82.5°	3503.0	3455.9	1508.0	769.7	518.4	392.7	361.3	361.3	314.2	282.8	282.8
85°	1602.3	2120.7	1052.5	534.1	392.7	298.5	298.5	282.8	251.3	204.2	204.2
87.5°	502.7	706.9	549.8	235.6	219.9	172.8	172.8	157.1	157.1	125.7	125.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599019
 CATALOG NUMBER: IFLD-L-SA8B-750-U-SLL

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1
2.5°	9912.1	9896.4	9896.4	9833.5	9990.6	9990.6	10084.9	10006.3	10053.5	10069.2	10194.8
5°	7870.0	7995.6	8089.9	8278.4	8388.4	8435.5	8435.5	8561.1	8514.0	8608.3	8796.8
7.5°	5765.0	5922.1	6204.9	6440.5	6629.0	6691.8	6676.1	6707.5	6754.7	6644.7	6676.1
10°	4665.4	4555.5	4649.7	4869.6	5042.4	5246.6	5089.6	5073.9	5121.0	5073.9	5168.1
12.5°	3895.7	3770.0	3691.5	3691.5	3817.2	3911.4	3864.3	3942.8	4115.6	4162.8	4272.7
15°	3157.4	3047.5	2984.6	2906.1	3031.7	3063.2	3110.3	3220.2	3345.9	3408.8	3534.4
17.5°	2529.1	2529.1	2529.1	2466.2	2513.4	2560.5	2576.2	2717.6	2733.3	2796.1	2843.2
20°	2073.5	2120.7	2199.2	2230.6	2277.7	2277.7	2246.3	2324.9	2262.0	2309.2	2340.6
22.5°	1869.3	1932.1	1963.6	1979.3	2042.1	2057.8	1979.3	1995.0	2010.7	1963.6	1979.3
25°	1759.4	1790.8	1759.4	1775.1	1790.8	1759.4	1775.1	1806.5	1790.8	1822.2	1806.5
27.5°	1712.2	1680.8	1665.1	1649.4	1649.4	1618.0	1633.7	1633.7	1665.1	1680.8	1680.8
30°	1712.2	1665.1	1602.3	1555.1	1555.1	1508.0	1539.4	1570.9	1586.6	1618.0	1618.0
32.5°	1759.4	1665.1	1555.1	1508.0	1460.9	1429.5	1460.9	1508.0	1570.9	1586.6	1602.3
35°	1398.1	1445.2	1429.5	1366.6	1350.9	1350.9	1335.2	1335.2	1288.1	1288.1	1272.4
37.5°	1256.7	1241.0	1272.4	1288.1	1303.8	1256.7	1256.7	1193.8	1178.1	1193.8	1193.8
40°	1178.1	1178.1	1178.1	1225.3	1241.0	1209.6	1162.4	1131.0	1131.0	1131.0	1146.7
42.5°	1146.7	1115.3	1099.6	1131.0	1178.1	1146.7	1099.6	1083.9	1083.9	1099.6	1099.6
45°	1099.6	1083.9	1068.2	1052.5	1115.3	1068.2	1052.5	1036.8	1036.8	1036.8	1052.5
47.5°	1052.5	1036.8	1005.3	1005.3	1021.1	1005.3	989.6	989.6	989.6	1021.1	1021.1
50°	1021.1	1005.3	973.9	973.9	973.9	973.9	958.2	958.2	958.2	973.9	989.6
52.5°	973.9	958.2	942.5	926.8	926.8	926.8	926.8	926.8	926.8	942.5	958.2
55°	926.8	911.1	895.4	895.4	911.1	911.1	895.4	911.1	895.4	911.1	926.8
57.5°	879.7	864.0	848.3	864.0	879.7	864.0	864.0	864.0	864.0	864.0	879.7
60°	816.8	816.8	816.8	816.8	848.3	848.3	848.3	848.3	816.8	832.6	848.3
62.5°	785.4	769.7	769.7	785.4	801.1	801.1	816.8	801.1	785.4	801.1	801.1
65°	722.6	722.6	722.6	738.3	738.3	754.0	754.0	754.0	738.3	754.0	754.0
67.5°	675.5	675.5	675.5	675.5	706.9	706.9	706.9	706.9	691.2	691.2	706.9
70°	596.9	612.6	596.9	628.3	659.8	644.0	659.8	659.8	644.0	628.3	659.8
72.5°	549.8	549.8	549.8	549.8	596.9	596.9	596.9	612.6	596.9	581.2	596.9
75°	487.0	487.0	487.0	502.7	534.1	534.1	534.1	534.1	534.1	518.4	518.4
77.5°	424.1	439.8	424.1	439.8	471.3	455.5	471.3	487.0	471.3	455.5	455.5
80°	361.3	361.3	361.3	377.0	392.7	392.7	392.7	408.4	392.7	377.0	377.0
82.5°	282.8	282.8	298.5	298.5	314.2	314.2	314.2	329.9	314.2	298.5	298.5
85°	219.9	219.9	219.9	235.6	235.6	251.3	251.3	267.0	267.0	251.3	251.3
87.5°	141.4	125.7	141.4	141.4	157.1	157.1	141.4	125.7	141.4	125.7	110.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599019
 CATALOG NUMBER: IFLD-L-SA8B-750-U-SLL

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1	11310.1
2.5°	10320.5	10603.3	10807.5	10948.8	11153.1	11545.8	11702.9	11985.6	12064.2	12111.3
5°	8875.3	9173.8	9613.6	9927.8	10289.1	11027.4	11592.9	12017.0	12205.5	12378.3
7.5°	6958.9	7351.6	7807.1	8215.6	8812.5	9723.6	10461.9	11341.6	11671.4	11844.2
10°	5435.2	5796.4	6299.1	6801.8	7634.3	8404.1	9456.5	10257.7	10713.2	10838.9
12.5°	4586.9	5011.0	5607.9	6220.6	6739.0	7618.6	8686.8	9849.2	10273.4	10351.9
15°	3895.7	4476.9	5089.6	5717.9	6314.8	7084.5	8231.3	9645.0	10273.4	10351.9
17.5°	3220.2	3738.6	4461.2	5136.7	5827.9	6880.3	8309.8	9817.8	10446.2	10681.8
20°	2560.5	3063.2	3628.7	4476.9	5419.4	6534.7	8482.6	10399.0	11231.6	11482.9
22.5°	2120.7	2340.6	2890.4	3707.2	4822.5	6299.1	8655.4	11310.1	12189.8	12284.1
25°	1853.6	2010.7	2356.3	3126.0	4351.3	6142.0	9063.8	12362.6	13493.6	13493.6
27.5°	1727.9	1790.8	2026.4	2717.6	4021.4	6000.7	9472.2	13525.0	14577.5	14797.4
30°	1696.5	1853.6	1979.3	2419.1	3660.1	5607.9	9849.2	14436.1	15520.0	15535.7
32.5°	1665.1	1633.7	1727.9	2104.9	3220.2	5199.5	10163.4	15362.9	16211.2	16258.3
35°	1303.8	1366.6	1523.7	1853.6	2890.4	4901.1	10320.5	15865.6	17090.9	17138.0
37.5°	1225.3	1303.8	1429.5	1712.2	2670.5	4649.7	10367.6	16839.5	18017.7	18111.9
40°	1193.8	1256.7	1350.9	1586.6	2497.7	4335.6	10461.9	17844.9	19384.3	19258.7
42.5°	1131.0	1209.6	1303.8	1523.7	2356.3	4099.9	10477.6	18394.7	20106.9	20106.9
45°	1115.3	1162.4	1272.4	1523.7	2199.2	3895.7	10226.3	18944.5	20939.5	20688.1
47.5°	1052.5	1146.7	1241.0	1476.6	2010.7	3691.5	9927.8	19227.2	21049.4	20970.9
50°	1036.8	1131.0	1288.1	1398.1	1900.7	3597.3	9865.0	19934.1	21269.4	21253.6
52.5°	1005.3	1099.6	1335.2	1335.2	1759.4	3471.6	10163.4	20248.3	21316.5	21442.1
55°	958.2	1099.6	1241.0	1225.3	1633.7	3314.5	10493.3	21065.1	22149.0	22117.6
57.5°	926.8	1068.2	1178.1	1115.3	1492.3	3204.5	10980.3	21850.6	23154.4	22934.5
60°	879.7	1068.2	1052.5	1036.8	1382.4	3110.3	11388.7	22007.7	23374.3	23515.7
62.5°	848.3	1115.3	926.8	958.2	1288.1	3063.2	11215.9	20829.5	23075.8	23201.5
65°	816.8	958.2	848.3	879.7	1256.7	2968.9	10540.4	19415.7	21787.7	22337.5
67.5°	754.0	785.4	785.4	816.8	1225.3	2749.0	9158.1	16871.0	19824.2	20122.6
70°	691.2	706.9	706.9	754.0	1193.8	2497.7	7555.8	14593.2	17200.8	17766.3
72.5°	628.3	628.3	628.3	691.2	1099.6	2293.4	6220.6	11215.9	14294.8	14687.5
75°	549.8	549.8	549.8	612.6	989.6	2089.2	4901.1	8341.2	10524.7	11090.2
77.5°	487.0	487.0	471.3	549.8	864.0	1696.5	3534.4	5890.7	7414.4	7885.7
80°	408.4	392.7	392.7	439.8	675.5	1225.3	2277.7	4162.8	5168.1	5372.3
82.5°	329.9	314.2	298.5	329.9	487.0	769.7	1413.8	2906.1	3314.5	3188.8
85°	314.2	329.9	267.0	251.3	345.6	502.7	895.4	1790.8	1492.3	1492.3
87.5°	125.7	110.0	110.0	94.3	172.8	188.5	392.7	329.9	251.3	251.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)