

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599039

Luminaire Tested: **IFLD-M-SA4C-760-U-SLL**

Issue Date: 05/03/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P599039
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/03/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-M-SA4C-760-U-SLL
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens
 Light Source: (64) 5700K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 24737.9 lumens
 Efficiency: N/A
 Efficacy: 113.4 lumens/watt
 Spacing Criteria (0/90/45): 1.12 / 0.52 / 0.8
 Luminous Opening: Rectangular (W 2' x L: 0.5' x H: 0')
 CIE Type: Direct

Input Watts (W): 218.1
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599039
CATALOG NUMBER: IFLD-M-SA4C-760-U-SLL

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ··· 90°-270° - · 135°-315°

TEST NUMBER: P599039
 CATALOG NUMBER: IFLD-M-SA4C-760-U-SLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	106	100	94	89	103	97	92	88	93	89	85	89	85	82	85	82	80	77	77	77
2	94	83	75	68	91	81	74	67	78	71	65	74	69	64	71	66	62	60	60	60
3	84	71	61	53	81	69	60	53	66	58	52	63	56	51	60	55	50	47	47	47
4	75	61	51	43	73	60	50	42	57	48	42	54	47	41	52	46	40	38	38	38
5	68	53	43	35	66	52	42	35	50	41	34	48	40	34	46	39	34	31	31	31
6	63	47	37	30	60	46	37	29	44	36	29	42	35	29	41	34	29	26	26	26
7	58	42	32	25	56	41	32	25	40	31	25	38	31	25	37	30	25	22	22	22
8	53	38	29	22	52	37	28	22	36	28	22	35	27	22	33	27	22	19	19	19
9	50	35	26	20	48	34	26	20	33	25	19	32	25	19	31	24	19	17	17	17
10	46	32	23	18	45	31	23	18	30	23	17	29	22	17	28	22	17	15	15	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	85047	85047	85047	85047
5°	93435	83001	59524	64978
10°	82761	73046	36103	38741
15°	80587	69338	25558	26536
20°	91889	80198	16718	18479
25°	111955	101660	14598	15119
30°	134894	123300	15140	14049
35°	157321	144776	12545	11825
40°	189045	174859	11719	11102
45°	220003	200959	11860	11026
50°	248633	228419	12129	11394
55°	289960	272250	12562	11945
60°	353655	343970	12521	12521
65°	397448	398006	12857	13415
70°	390606	404419	13470	13816
75°	322207	343659	14148	15059
80°	232637	244204	15645	16327
85°	128751	138236	17624	21687

TEST NUMBER: P599039
 CATALOG NUMBER: IFLD-M-SA4C-760-U-SLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	613.8	2.5
10°-20°	1296.0	5.2
20°-30°	1896.1	7.7
30°-40°	2671.6	10.8
40°-50°	3671.5	14.8
50°-60°	5003.8	20.2
60°-70°	5476.5	22.1
70°-80°	3161.8	12.8
80°-90°	946.8	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3805.9	15.4
0°-40°	6477.5	26.2
0°-60°	15152.8	61.3
0°-90°	24737.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	24737.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	7901	7901	7901	7901	7901	
5°	8647	7682	5509	6014	8647	785
15°	7232	6222	2294	2381	7232	2113
25°	9426	8560	1229	1273	9426	4414
35°	11972	11018	955	900	11972	7592
45°	14452	13202	779	724	14452	11108
55°	15451	14507	669	636	15451	13941
65°	15605	15627	505	527	15605	14935
75°	7748	8263	340	362	7748	8322
85°	1042	1119	143	176	1042	1446
90°	0	0	0	0	0	

TEST NUMBER: P599039
 CATALOG NUMBER: IFLD-M-SA4C-760-U-SLL

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1
2.5°	8460.8	8427.9	8460.8	8581.5	8614.4	8669.3	8669.3	8592.5	8449.8	8384.0	8274.3
5°	8647.4	8592.5	8866.8	9119.2	9316.8	9294.8	9108.3	8954.6	8669.3	8241.3	7835.3
7.5°	8274.3	8329.1	8526.7	9185.1	9646.0	9733.8	9437.5	9130.2	8515.7	7923.1	7374.4
10°	7571.9	7648.8	8076.7	8757.1	9481.4	9624.0	9437.5	9064.4	8329.1	7593.9	6957.4
12.5°	7231.7	7407.3	7659.7	8482.8	8998.5	9338.7	9250.9	9009.5	8186.5	7319.5	6705.0
15°	7231.7	7275.6	7648.8	8340.1	8636.4	8647.4	8680.3	8724.2	8230.4	7440.2	6617.2
17.5°	7462.2	7582.9	7901.1	8329.1	8384.0	8252.3	8252.3	8438.9	8318.2	7780.4	6935.5
20°	8021.9	7978.0	8395.0	8570.6	8274.3	7945.0	7912.1	8230.4	8416.9	8142.6	7517.1
22.5°	8581.5	8779.1	9119.2	8724.2	8175.5	7736.5	7692.6	8087.7	8713.2	8768.1	8186.5
25°	9426.5	9624.0	9799.6	9316.8	8164.5	7681.7	7714.6	8021.9	9075.3	9657.0	9305.8
27.5°	10337.3	10458.0	10710.4	9964.2	8427.9	7615.8	7648.8	8109.7	9415.5	10238.6	10183.7
30°	10853.1	10984.8	10929.9	10084.9	8603.5	7659.7	7571.9	8230.4	9229.0	10238.6	10754.3
32.5°	11357.9	11281.1	11248.2	10282.5	8822.9	7934.1	7714.6	8482.8	9338.7	10403.2	11489.6
35°	11972.4	11862.7	11774.9	10666.6	9185.1	8197.4	8098.7	8812.0	9580.1	10743.4	12082.2
37.5°	12652.8	12652.8	12224.8	10951.9	9613.1	8625.4	8515.7	9283.8	9964.2	10951.9	12894.2
40°	13453.9	13486.8	12729.6	11336.0	10095.9	9305.8	9272.9	9898.4	10337.3	11259.1	13673.4
42.5°	14046.5	14068.4	13168.6	11478.6	10655.6	10249.5	10392.2	10886.0	10765.3	11533.5	13728.2
45°	14452.5	14342.8	13475.8	11884.6	11270.1	11665.2	11709.1	11851.7	11325.0	11698.1	13947.7
47.5°	14650.0	14628.1	13607.5	12356.5	12565.0	13102.7	13355.1	13157.6	11840.7	11522.5	13947.7
50°	14847.6	14661.0	13728.2	13004.0	13827.0	14913.4	14858.5	14496.4	12554.0	11742.0	13739.2
52.5°	14979.3	14814.7	13969.7	13585.6	15034.1	16263.2	16482.7	15813.3	13388.1	12148.0	13838.0
55°	15451.1	15319.4	14693.9	14375.7	16427.8	17689.8	17722.7	16789.9	14266.0	12817.4	14485.4
57.5°	16021.8	16098.6	15692.6	15495.0	17492.3	18732.3	18611.6	17514.2	15012.2	13629.5	15231.7
60°	16427.8	16548.5	16449.8	16471.7	18019.0	19083.5	18809.1	17964.1	15560.9	14244.0	16142.5
62.5°	16208.3	16449.8	16855.8	16768.0	18041.0	18831.1	18447.0	17371.6	15626.7	15045.1	16833.8
65°	15604.8	15626.7	16416.8	16899.7	17053.3	17525.2	17020.4	16131.5	14946.3	15538.9	16735.1
67.5°	14057.5	14233.0	14946.3	15890.1	15242.6	15352.4	15308.5	14024.5	13914.8	15198.7	15977.9
70°	12411.4	12532.1	13311.2	14419.6	12872.3	12356.5	12455.3	11500.6	11950.5	14145.3	14452.5
72.5°	10260.5	10337.3	11226.2	12202.9	10326.4	9404.6	9635.0	8855.9	9492.4	12378.5	12191.9
75°	7747.5	7890.2	8581.5	9733.8	7604.9	7012.3	7242.7	6924.5	7517.1	10194.7	9459.4
77.5°	5508.9	5399.1	6255.1	7615.8	5717.4	5366.2	5388.1	5443.0	6079.5	8592.5	6792.8
80°	3753.0	3786.0	4554.1	5585.7	4488.3	4433.4	4378.6	4817.5	5102.8	6803.8	4938.2
82.5°	2227.7	2227.7	3072.7	3972.5	3544.5	3994.5	3742.1	4137.1	3994.5	5004.1	3237.3
85°	1042.5	1042.5	1580.2	2864.2	2743.5	3292.1	2798.3	3127.5	2952.0	3489.7	1459.5
87.5°	175.6	153.6	318.2	1404.6	1130.3	1283.9	504.8	1668.0	1854.6	2436.2	362.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599039
 CATALOG NUMBER: IFLD-M-SA4C-760-U-SLL

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1
2.5°	8153.5	8076.7	7923.1	7725.6	7561.0	7352.5	7286.6	7144.0	6946.4	6924.5	6836.7
5°	7681.7	7418.3	7089.1	6683.1	6408.7	6123.4	5882.0	5739.3	5574.7	5552.8	5508.9
7.5°	7165.9	6836.7	6288.0	5805.1	5333.3	4883.3	4663.9	4389.5	4203.0	4060.3	3994.5
10°	6683.1	6375.8	5695.4	5037.0	4620.0	4323.7	4060.3	3775.0	3544.5	3369.0	3303.1
12.5°	6364.8	6002.7	5267.4	4641.9	4334.7	3994.5	3698.2	3390.9	3094.6	2864.2	2743.5
15°	6222.2	5882.0	5135.7	4444.4	3994.5	3522.6	3182.4	2875.1	2513.0	2348.4	2293.5
17.5°	6562.3	6057.5	5091.9	4213.9	3577.5	3039.7	2622.7	2293.5	2030.2	1865.5	1799.7
20°	7001.3	6375.8	5168.7	3939.6	3182.4	2578.8	2117.9	1766.8	1591.2	1470.5	1459.5
22.5°	7561.0	6847.7	5289.4	3742.1	2743.5	2074.1	1657.0	1448.5	1327.8	1316.9	1294.9
25°	8559.6	7703.6	5486.9	3478.7	2392.3	1711.9	1415.6	1294.9	1240.0	1207.1	1229.1
27.5°	9415.5	8263.3	5629.6	3314.1	2249.6	1613.2	1371.7	1240.0	1185.2	1174.2	1185.2
30°	9920.3	8779.1	5585.7	3006.8	1964.3	1536.3	1459.5	1415.6	1305.9	1218.1	1218.1
32.5°	10381.2	9108.3	5574.7	2732.5	1679.0	1283.9	1218.1	1185.2	1251.0	1294.9	1262.0
35°	11017.7	9624.0	5541.8	2578.8	1558.3	1185.2	1075.4	987.6	943.7	921.8	954.7
37.5°	11698.1	9975.2	5454.0	2556.9	1492.4	1130.3	1042.5	954.7	910.8	888.9	877.9
40°	12444.3	10348.3	5355.2	2447.2	1459.5	1097.4	1009.6	932.8	877.9	845.0	834.0
42.5°	12927.2	10644.6	5256.5	2392.3	1393.7	1075.4	976.7	910.8	856.0	812.1	812.1
45°	13201.5	10995.8	5157.7	2337.4	1316.9	1086.4	976.7	888.9	823.0	801.1	779.1
47.5°	13322.2	11259.1	5124.8	2249.6	1251.0	1042.5	954.7	866.9	801.1	757.2	746.2
50°	13640.5	11818.8	5245.5	2183.8	1174.2	998.6	1009.6	856.0	790.1	735.2	724.3
52.5°	13827.0	12268.7	5508.9	2085.0	1119.3	943.7	987.6	834.0	757.2	702.3	702.3
55°	14507.4	13014.9	5794.2	2008.2	1053.5	866.9	910.8	790.1	702.3	669.4	669.4
57.5°	15374.3	13805.1	6035.6	1975.3	1009.6	812.1	812.1	768.2	669.4	625.5	614.5
60°	15977.9	14452.5	6178.3	1953.3	965.7	757.2	724.3	768.2	636.5	592.6	581.6
62.5°	16043.7	14079.4	6035.6	1942.4	954.7	702.3	658.4	735.2	603.6	559.7	537.7
65°	15626.7	13322.2	5640.5	1898.5	943.7	647.5	614.5	636.5	559.7	526.7	504.8
67.5°	14792.7	12093.1	5069.9	1876.5	932.8	603.6	559.7	548.7	515.8	482.8	460.9
70°	12850.3	10491.0	4400.5	1777.8	910.8	570.6	504.8	493.8	460.9	439.0	428.0
72.5°	10787.3	8581.5	3632.3	1646.1	866.9	515.8	460.9	439.0	428.0	395.1	384.1
75°	8263.3	6606.2	2908.1	1459.5	757.2	460.9	406.0	384.1	373.1	351.2	340.2
77.5°	5805.1	4916.3	2150.9	1185.2	636.5	417.0	362.1	340.2	329.2	296.3	296.3
80°	3939.6	3445.8	1459.5	823.0	493.8	340.2	318.2	296.3	274.3	252.4	252.4
82.5°	2447.2	2414.2	1053.5	537.7	362.1	274.3	252.4	252.4	219.5	197.5	197.5
85°	1119.3	1481.5	735.2	373.1	274.3	208.5	208.5	197.5	175.6	142.7	142.7
87.5°	351.2	493.8	384.1	164.6	153.6	120.7	120.7	109.7	109.7	87.8	87.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599039
 CATALOG NUMBER: IFLD-M-SA4C-760-U-SLL

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1
2.5°	6924.5	6913.5	6913.5	6869.6	6979.3	6979.3	7045.2	6990.3	7023.2	7034.2	7122.0
5°	5497.9	5585.7	5651.5	5783.2	5860.0	5892.9	5892.9	5980.7	5947.8	6013.7	6145.3
7.5°	4027.4	4137.1	4334.7	4499.3	4631.0	4674.8	4663.9	4685.8	4718.7	4641.9	4663.9
10°	3259.2	3182.4	3248.3	3401.9	3522.6	3665.3	3555.5	3544.5	3577.5	3544.5	3610.4
12.5°	2721.5	2633.7	2578.8	2578.8	2666.6	2732.5	2699.6	2754.4	2875.1	2908.1	2984.9
15°	2205.7	2128.9	2085.0	2030.2	2117.9	2139.9	2172.8	2249.6	2337.4	2381.3	2469.1
17.5°	1766.8	1766.8	1766.8	1722.9	1755.8	1788.7	1799.7	1898.5	1909.4	1953.3	1986.3
20°	1448.5	1481.5	1536.3	1558.3	1591.2	1591.2	1569.3	1624.1	1580.2	1613.2	1635.1
22.5°	1305.9	1349.8	1371.7	1382.7	1426.6	1437.6	1382.7	1393.7	1404.6	1371.7	1382.7
25°	1229.1	1251.0	1229.1	1240.0	1251.0	1229.1	1240.0	1262.0	1251.0	1273.0	1262.0
27.5°	1196.1	1174.2	1163.2	1152.3	1152.3	1130.3	1141.3	1141.3	1163.2	1174.2	1174.2
30°	1196.1	1163.2	1119.3	1086.4	1086.4	1053.5	1075.4	1097.4	1108.4	1130.3	1130.3
32.5°	1229.1	1163.2	1086.4	1053.5	1020.6	998.6	1020.6	1053.5	1097.4	1108.4	1119.3
35°	976.7	1009.6	998.6	954.7	943.7	943.7	932.8	932.8	899.9	899.9	888.9
37.5°	877.9	866.9	888.9	899.9	910.8	877.9	877.9	834.0	823.0	834.0	834.0
40°	823.0	823.0	823.0	856.0	866.9	845.0	812.1	790.1	790.1	790.1	801.1
42.5°	801.1	779.1	768.2	790.1	823.0	801.1	768.2	757.2	757.2	768.2	768.2
45°	768.2	757.2	746.2	735.2	779.1	746.2	735.2	724.3	724.3	724.3	735.2
47.5°	735.2	724.3	702.3	702.3	713.3	702.3	691.4	691.4	691.4	713.3	713.3
50°	713.3	702.3	680.4	680.4	680.4	680.4	669.4	669.4	669.4	680.4	691.4
52.5°	680.4	669.4	658.4	647.5	647.5	647.5	647.5	647.5	647.5	658.4	669.4
55°	647.5	636.5	625.5	625.5	636.5	636.5	625.5	636.5	625.5	636.5	647.5
57.5°	614.5	603.6	592.6	603.6	614.5	603.6	603.6	603.6	603.6	603.6	614.5
60°	570.6	570.6	570.6	570.6	592.6	592.6	592.6	592.6	570.6	581.6	592.6
62.5°	548.7	537.7	537.7	548.7	559.7	559.7	570.6	559.7	548.7	559.7	559.7
65°	504.8	504.8	504.8	515.8	515.8	526.7	526.7	526.7	515.8	526.7	526.7
67.5°	471.9	471.9	471.9	471.9	493.8	493.8	493.8	493.8	482.8	482.8	493.8
70°	417.0	428.0	417.0	439.0	460.9	449.9	460.9	460.9	449.9	439.0	460.9
72.5°	384.1	384.1	384.1	384.1	417.0	417.0	417.0	428.0	417.0	406.0	417.0
75°	340.2	340.2	340.2	351.2	373.1	373.1	373.1	373.1	373.1	362.1	362.1
77.5°	296.3	307.3	296.3	307.3	329.2	318.2	329.2	340.2	329.2	318.2	318.2
80°	252.4	252.4	252.4	263.4	274.3	274.3	274.3	285.3	274.3	263.4	263.4
82.5°	197.5	197.5	208.5	208.5	219.5	219.5	219.5	230.5	219.5	208.5	208.5
85°	153.6	153.6	153.6	164.6	164.6	175.6	175.6	186.6	186.6	175.6	175.6
87.5°	98.8	87.8	98.8	98.8	109.7	109.7	98.8	87.8	98.8	87.8	76.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P599039
 CATALOG NUMBER: IFLD-M-SA4C-760-U-SLL

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1	7901.1
2.5°	7209.8	7407.3	7550.0	7648.8	7791.4	8065.8	8175.5	8373.0	8427.9	8460.8
5°	6200.2	6408.7	6716.0	6935.5	7187.9	7703.6	8098.7	8395.0	8526.7	8647.4
7.5°	4861.4	5135.7	5454.0	5739.3	6156.3	6792.8	7308.6	7923.1	8153.5	8274.3
10°	3796.9	4049.3	4400.5	4751.7	5333.3	5871.0	6606.2	7165.9	7484.1	7571.9
12.5°	3204.4	3500.6	3917.7	4345.6	4707.8	5322.3	6068.5	6880.6	7176.9	7231.7
15°	2721.5	3127.5	3555.5	3994.5	4411.5	4949.2	5750.3	6737.9	7176.9	7231.7
17.5°	2249.6	2611.8	3116.6	3588.4	4071.3	4806.5	5805.1	6858.6	7297.6	7462.2
20°	1788.7	2139.9	2535.0	3127.5	3786.0	4565.1	5925.9	7264.7	7846.3	8021.9
22.5°	1481.5	1635.1	2019.2	2589.8	3369.0	4400.5	6046.6	7901.1	8515.7	8581.5
25°	1294.9	1404.6	1646.1	2183.8	3039.7	4290.8	6331.9	8636.4	9426.5	9426.5
27.5°	1207.1	1251.0	1415.6	1898.5	2809.3	4192.0	6617.2	9448.5	10183.7	10337.3
30°	1185.2	1294.9	1382.7	1690.0	2556.9	3917.7	6880.6	10084.9	10842.1	10853.1
32.5°	1163.2	1141.3	1207.1	1470.5	2249.6	3632.3	7100.1	10732.4	11325.0	11357.9
35°	910.8	954.7	1064.5	1294.9	2019.2	3423.8	7209.8	11083.6	11939.5	11972.4
37.5°	856.0	910.8	998.6	1196.1	1865.5	3248.3	7242.7	11763.9	12587.0	12652.8
40°	834.0	877.9	943.7	1108.4	1744.8	3028.8	7308.6	12466.3	13541.7	13453.9
42.5°	790.1	845.0	910.8	1064.5	1646.1	2864.2	7319.5	12850.3	14046.5	14046.5
45°	779.1	812.1	888.9	1064.5	1536.3	2721.5	7144.0	13234.4	14628.1	14452.5
47.5°	735.2	801.1	866.9	1031.5	1404.6	2578.8	6935.5	13432.0	14704.9	14650.0
50°	724.3	790.1	899.9	976.7	1327.8	2513.0	6891.6	13925.8	14858.5	14847.6
52.5°	702.3	768.2	932.8	932.8	1229.1	2425.2	7100.1	14145.3	14891.5	14979.3
55°	669.4	768.2	866.9	856.0	1141.3	2315.5	7330.5	14715.9	15473.1	15451.1
57.5°	647.5	746.2	823.0	779.1	1042.5	2238.7	7670.7	15264.6	16175.4	16021.8
60°	614.5	746.2	735.2	724.3	965.7	2172.8	7956.0	15374.3	16329.0	16427.8
62.5°	592.6	779.1	647.5	669.4	899.9	2139.9	7835.3	14551.3	16120.5	16208.3
65°	570.6	669.4	592.6	614.5	877.9	2074.1	7363.4	13563.6	15220.7	15604.8
67.5°	526.7	548.7	548.7	570.6	856.0	1920.4	6397.7	11785.9	13849.0	14057.5
70°	482.8	493.8	493.8	526.7	834.0	1744.8	5278.4	10194.7	12016.3	12411.4
72.5°	439.0	439.0	439.0	482.8	768.2	1602.2	4345.6	7835.3	9986.2	10260.5
75°	384.1	384.1	384.1	428.0	691.4	1459.5	3423.8	5827.1	7352.5	7747.5
77.5°	340.2	340.2	329.2	384.1	603.6	1185.2	2469.1	4115.2	5179.6	5508.9
80°	285.3	274.3	274.3	307.3	471.9	856.0	1591.2	2908.1	3610.4	3753.0
82.5°	230.5	219.5	208.5	230.5	340.2	537.7	987.6	2030.2	2315.5	2227.7
85°	219.5	230.5	186.6	175.6	241.4	351.2	625.5	1251.0	1042.5	1042.5
87.5°	87.8	76.8	76.8	65.8	120.7	131.7	274.3	230.5	175.6	175.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)