

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599023

Luminaire Tested: **IFLD-S-SA2B-760-U-SLL**

Issue Date: 05/03/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P599023
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/03/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-S-SA2B-760-U-SLL
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens
 Light Source: (32) 5700K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 9934.4 lumens
 Efficiency: N/A
 Efficacy: 120.6 lumens/watt
 Spacing Criteria (0/90/45): 1.12 / 0.52 / 0.8
 Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
 CIE Type: Direct

Input Watts (W): 82.4
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599023
CATALOG NUMBER: IFLD-S-SA2B-760-U-SLL

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ··· 90°-270° - · 135°-315°

TEST NUMBER: P599023

CATALOG NUMBER: IFLD-S-SA2B-760-U-SLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	106	100	94	89	103	97	92	88	93	89	85	89	85	82	85	82	80	77				
2	94	83	75	68	91	81	74	67	78	71	65	74	69	64	71	66	62	60				
3	84	71	61	53	81	69	60	53	66	58	52	63	56	51	60	55	50	47				
4	75	61	51	43	73	60	50	42	57	48	42	54	47	41	52	46	40	38				
5	68	53	43	35	66	52	42	35	50	41	34	48	40	34	46	39	34	31				
6	63	47	37	30	60	46	37	29	44	36	29	42	35	29	41	34	29	26				
7	58	42	32	25	56	41	32	25	40	31	25	38	31	25	37	30	25	22				
8	53	38	29	22	52	37	28	22	36	28	22	35	27	22	33	27	22	19				
9	50	35	26	20	48	34	26	20	33	25	19	32	25	19	31	24	19	17				
10	46	32	23	18	45	31	23	18	30	23	17	29	22	17	28	22	17	15				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	68308	68308	68308	68308
5°	75045	66665	47808	52188
10°	66472	58668	28997	31115
15°	64727	55689	20527	21313
20°	73803	64412	13427	14841
25°	89921	81650	11725	12143
30°	108344	99033	12161	11283
35°	126357	116281	10076	9498
40°	151835	140443	9412	8917
45°	176699	161404	9526	8856
50°	199696	183459	9743	9150
55°	232890	218665	10089	9593
60°	284047	276267	10058	10058
65°	319221	319669	10325	10774
70°	313721	324818	10820	11097
75°	258789	276015	11362	12094
80°	186853	196139	12571	13116
85°	103421	111028	14153	17414

TEST NUMBER: P599023
 CATALOG NUMBER: IFLD-S-SA2B-760-U-SLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	246.5	2.5
10°-20°	520.4	5.2
20°-30°	761.5	7.7
30°-40°	1072.9	10.8
40°-50°	1474.4	14.8
50°-60°	2009.5	20.2
60°-70°	2199.3	22.1
70°-80°	1269.7	12.8
80°-90°	380.2	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1528.4	15.4
0°-40°	2601.3	26.2
0°-60°	6085.2	61.3
0°-90°	9934.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9934.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	3173	3173	3173	3173	3173	
5°	3473	3085	2212	2415	3473	315
15°	2904	2499	921	956	2904	848
25°	3786	3437	494	511	3786	1773
35°	4808	4425	383	361	4808	3049
45°	5804	5302	313	291	5804	4461
55°	6205	5826	269	256	6205	5599
65°	6267	6276	203	212	6267	5998
75°	3111	3318	137	145	3111	3342
85°	419	450	57	70	419	581
90°	0	0	0	0	0	

TEST NUMBER: P599023
 CATALOG NUMBER: IFLD-S-SA2B-760-U-SLL

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0
2.5°	3397.7	3384.5	3397.7	3446.2	3459.4	3481.5	3481.5	3450.6	3393.3	3366.9	3322.8
5°	3472.7	3450.6	3560.8	3662.2	3741.5	3732.7	3657.8	3596.1	3481.5	3309.6	3146.6
7.5°	3322.8	3344.9	3424.2	3688.6	3873.7	3908.9	3790.0	3666.6	3419.8	3181.8	2961.5
10°	3040.8	3071.6	3243.5	3516.7	3807.6	3864.9	3790.0	3640.1	3344.9	3049.6	2794.0
12.5°	2904.2	2974.7	3076.0	3406.6	3613.7	3750.3	3715.0	3618.1	3287.6	2939.4	2692.6
15°	2904.2	2921.8	3071.6	3349.3	3468.3	3472.7	3485.9	3503.5	3305.2	2987.9	2657.4
17.5°	2996.7	3045.2	3173.0	3344.9	3366.9	3314.0	3314.0	3388.9	3340.5	3124.5	2785.2
20°	3221.5	3203.8	3371.3	3441.8	3322.8	3190.6	3177.4	3305.2	3380.1	3269.9	3018.7
22.5°	3446.2	3525.5	3662.2	3503.5	3283.2	3106.9	3089.3	3247.9	3499.1	3521.1	3287.6
25°	3785.6	3864.9	3935.4	3741.5	3278.8	3084.9	3098.1	3221.5	3644.5	3878.1	3737.1
27.5°	4151.3	4199.8	4301.2	4001.5	3384.5	3058.4	3071.6	3256.7	3781.1	4111.7	4089.6
30°	4358.5	4411.3	4389.3	4050.0	3455.0	3076.0	3040.8	3305.2	3706.2	4111.7	4318.8
32.5°	4561.2	4530.3	4517.1	4129.3	3543.2	3186.2	3098.1	3406.6	3750.3	4177.8	4614.1
35°	4808.0	4763.9	4728.6	4283.5	3688.6	3292.0	3252.3	3538.8	3847.3	4314.4	4852.0
37.5°	5081.2	5081.2	4909.3	4398.1	3860.5	3463.8	3419.8	3728.3	4001.5	4398.1	5178.1
40°	5402.9	5416.1	5112.0	4552.4	4054.4	3737.1	3723.9	3975.1	4151.3	4521.5	5491.0
42.5°	5640.9	5649.7	5288.3	4609.7	4279.1	4116.1	4173.4	4371.7	4323.2	4631.7	5513.1
45°	5803.9	5759.9	5411.7	4772.7	4525.9	4684.6	4702.2	4759.5	4548.0	4697.8	5601.2
47.5°	5883.3	5874.4	5464.6	4962.2	5045.9	5261.9	5363.2	5283.9	4755.1	4627.3	5601.2
50°	5962.6	5887.7	5513.1	5222.2	5552.7	5989.0	5967.0	5821.6	5041.5	4715.4	5517.5
52.5°	6015.5	5949.4	5610.0	5455.8	6037.5	6531.1	6619.2	6350.4	5376.5	4878.5	5557.1
55°	6205.0	6152.1	5900.9	5773.1	6597.2	7104.0	7117.2	6742.6	5729.0	5147.3	5817.2
57.5°	6434.1	6465.0	6301.9	6222.6	7024.7	7522.6	7474.2	7033.5	6028.7	5473.4	6116.8
60°	6597.2	6645.7	6606.0	6614.8	7236.2	7663.7	7553.5	7214.1	6249.0	5720.2	6482.6
62.5°	6509.0	6606.0	6769.0	6733.8	7245.0	7562.3	7408.1	6976.2	6275.5	6041.9	6760.2
65°	6266.7	6275.5	6592.8	6786.7	6848.4	7037.9	6835.2	6478.2	6002.2	6240.2	6720.6
67.5°	5645.3	5715.8	6002.2	6381.2	6121.2	6165.3	6147.7	5632.1	5588.0	6103.6	6416.5
70°	4984.2	5032.7	5345.6	5790.7	5169.3	4962.2	5001.9	4618.5	4799.2	5680.5	5803.9
72.5°	4120.5	4151.3	4508.3	4900.5	4146.9	3776.7	3869.3	3556.4	3812.0	4971.0	4896.1
75°	3111.3	3168.6	3446.2	3908.9	3054.0	2816.0	2908.6	2780.8	3018.7	4094.0	3798.8
77.5°	2212.3	2168.2	2512.0	3058.4	2296.0	2155.0	2163.8	2185.8	2441.4	3450.6	2727.9
80°	1507.2	1520.4	1828.9	2243.1	1802.4	1780.4	1758.4	1934.6	2049.2	2732.3	1983.1
82.5°	894.6	894.6	1233.9	1595.3	1423.4	1604.1	1502.8	1661.4	1604.1	2009.6	1300.0
85°	418.7	418.7	634.6	1150.2	1101.7	1322.1	1123.8	1256.0	1185.5	1401.4	586.1
87.5°	70.5	61.7	127.8	564.1	453.9	515.6	202.7	669.9	744.8	978.3	145.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599023
 CATALOG NUMBER: IFLD-S-SA2B-760-U-SLL

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0
2.5°	3274.4	3243.5	3181.8	3102.5	3036.4	2952.6	2926.2	2868.9	2789.6	2780.8	2745.5
5°	3084.9	2979.1	2846.9	2683.8	2573.6	2459.1	2362.1	2304.8	2238.7	2229.9	2212.3
7.5°	2877.7	2745.5	2525.2	2331.3	2141.8	1961.1	1872.9	1762.8	1687.9	1630.6	1604.1
10°	2683.8	2560.4	2287.2	2022.8	1855.3	1736.3	1630.6	1516.0	1423.4	1352.9	1326.5
12.5°	2556.0	2410.6	2115.3	1864.1	1740.7	1604.1	1485.1	1361.7	1242.8	1150.2	1101.7
15°	2498.7	2362.1	2062.4	1784.8	1604.1	1414.6	1278.0	1154.6	1009.2	943.1	921.0
17.5°	2635.3	2432.6	2044.8	1692.3	1436.7	1220.7	1053.3	921.0	815.3	749.2	722.7
20°	2811.6	2560.4	2075.7	1582.1	1278.0	1035.6	850.5	709.5	639.0	590.5	586.1
22.5°	3036.4	2749.9	2124.1	1502.8	1101.7	832.9	665.4	581.7	533.2	528.8	520.0
25°	3437.4	3093.7	2203.5	1397.0	960.7	687.5	568.5	520.0	498.0	484.8	493.6
27.5°	3781.1	3318.4	2260.8	1330.9	903.4	647.8	550.9	498.0	475.9	471.5	475.9
30°	3983.9	3525.5	2243.1	1207.5	788.8	617.0	586.1	568.5	524.4	489.2	489.2
32.5°	4169.0	3657.8	2238.7	1097.3	674.3	515.6	489.2	475.9	502.4	520.0	506.8
35°	4424.6	3864.9	2225.5	1035.6	625.8	475.9	431.9	396.6	379.0	370.2	383.4
37.5°	4697.8	4005.9	2190.2	1026.8	599.3	453.9	418.7	383.4	365.8	357.0	352.6
40°	4997.5	4155.7	2150.6	982.7	586.1	440.7	405.4	374.6	352.6	339.3	334.9
42.5°	5191.4	4274.7	2110.9	960.7	559.7	431.9	392.2	365.8	343.7	326.1	326.1
45°	5301.5	4415.7	2071.3	938.7	528.8	436.3	392.2	357.0	330.5	321.7	312.9
47.5°	5350.0	4521.5	2058.0	903.4	502.4	418.7	383.4	348.1	321.7	304.1	299.7
50°	5477.8	4746.3	2106.5	877.0	471.5	401.0	405.4	343.7	317.3	295.3	290.9
52.5°	5552.7	4927.0	2212.3	837.3	449.5	379.0	396.6	334.9	304.1	282.0	282.0
55°	5826.0	5226.6	2326.9	806.5	423.1	348.1	365.8	317.3	282.0	268.8	268.8
57.5°	6174.1	5543.9	2423.8	793.2	405.4	326.1	326.1	308.5	268.8	251.2	246.8
60°	6416.5	5803.9	2481.1	784.4	387.8	304.1	290.9	308.5	255.6	238.0	233.6
62.5°	6442.9	5654.1	2423.8	780.0	383.4	282.0	264.4	295.3	242.4	224.8	215.9
65°	6275.5	5350.0	2265.2	762.4	379.0	260.0	246.8	255.6	224.8	211.5	202.7
67.5°	5940.5	4856.4	2036.0	753.6	374.6	242.4	224.8	220.3	207.1	193.9	185.1
70°	5160.5	4213.0	1767.2	713.9	365.8	229.2	202.7	198.3	185.1	176.3	171.9
72.5°	4332.0	3446.2	1458.7	661.0	348.1	207.1	185.1	176.3	171.9	158.6	154.2
75°	3318.4	2653.0	1167.8	586.1	304.1	185.1	163.1	154.2	149.8	141.0	136.6
77.5°	2331.3	1974.3	863.8	475.9	255.6	167.5	145.4	136.6	132.2	119.0	119.0
80°	1582.1	1383.8	586.1	330.5	198.3	136.6	127.8	119.0	110.2	101.4	101.4
82.5°	982.7	969.5	423.1	215.9	145.4	110.2	101.4	101.4	88.1	79.3	79.3
85°	449.5	594.9	295.3	149.8	110.2	83.7	83.7	79.3	70.5	57.3	57.3
87.5°	141.0	198.3	154.2	66.1	61.7	48.5	48.5	44.1	44.1	35.3	35.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599023
 CATALOG NUMBER: IFLD-S-SA2B-760-U-SLL

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0
2.5°	2780.8	2776.4	2776.4	2758.7	2802.8	2802.8	2829.3	2807.2	2820.4	2824.8	2860.1
5°	2207.9	2243.1	2269.6	2322.5	2353.3	2366.5	2366.5	2401.8	2388.6	2415.0	2467.9
7.5°	1617.3	1661.4	1740.7	1806.8	1859.7	1877.4	1872.9	1881.8	1895.0	1864.1	1872.9
10°	1308.9	1278.0	1304.5	1366.1	1414.6	1471.9	1427.8	1423.4	1436.7	1423.4	1449.9
12.5°	1092.9	1057.7	1035.6	1035.6	1070.9	1097.3	1084.1	1106.1	1154.6	1167.8	1198.7
15°	885.8	854.9	837.3	815.3	850.5	859.4	872.6	903.4	938.7	956.3	991.6
17.5°	709.5	709.5	709.5	691.9	705.1	718.3	722.7	762.4	766.8	784.4	797.7
20°	581.7	594.9	617.0	625.8	639.0	639.0	630.2	652.2	634.6	647.8	656.6
22.5°	524.4	542.1	550.9	555.3	572.9	577.3	555.3	559.7	564.1	550.9	555.3
25°	493.6	502.4	493.6	498.0	502.4	493.6	498.0	506.8	502.4	511.2	506.8
27.5°	480.4	471.5	467.1	462.7	462.7	453.9	458.3	458.3	467.1	471.5	471.5
30°	480.4	467.1	449.5	436.3	436.3	423.1	431.9	440.7	445.1	453.9	453.9
32.5°	493.6	467.1	436.3	423.1	409.8	401.0	409.8	423.1	440.7	445.1	449.5
35°	392.2	405.4	401.0	383.4	379.0	379.0	374.6	374.6	361.4	361.4	357.0
37.5°	352.6	348.1	357.0	361.4	365.8	352.6	352.6	334.9	330.5	334.9	334.9
40°	330.5	330.5	330.5	343.7	348.1	339.3	326.1	317.3	317.3	317.3	321.7
42.5°	321.7	312.9	308.5	317.3	330.5	321.7	308.5	304.1	304.1	308.5	308.5
45°	308.5	304.1	299.7	295.3	312.9	299.7	295.3	290.9	290.9	290.9	295.3
47.5°	295.3	290.9	282.0	282.0	286.5	282.0	277.6	277.6	277.6	286.5	286.5
50°	286.5	282.0	273.2	273.2	273.2	273.2	268.8	268.8	268.8	273.2	277.6
52.5°	273.2	268.8	264.4	260.0	260.0	260.0	260.0	260.0	260.0	264.4	268.8
55°	260.0	255.6	251.2	251.2	255.6	255.6	251.2	255.6	251.2	255.6	260.0
57.5°	246.8	242.4	238.0	242.4	246.8	242.4	242.4	242.4	242.4	242.4	246.8
60°	229.2	229.2	229.2	229.2	238.0	238.0	238.0	238.0	229.2	233.6	238.0
62.5°	220.3	215.9	215.9	220.3	224.8	224.8	229.2	224.8	220.3	224.8	224.8
65°	202.7	202.7	202.7	207.1	207.1	211.5	211.5	211.5	207.1	211.5	211.5
67.5°	189.5	189.5	189.5	189.5	198.3	198.3	198.3	198.3	193.9	193.9	198.3
70°	167.5	171.9	167.5	176.3	185.1	180.7	185.1	185.1	180.7	176.3	185.1
72.5°	154.2	154.2	154.2	154.2	167.5	167.5	167.5	171.9	167.5	163.1	167.5
75°	136.6	136.6	136.6	141.0	149.8	149.8	149.8	149.8	149.8	145.4	145.4
77.5°	119.0	123.4	119.0	123.4	132.2	127.8	132.2	136.6	132.2	127.8	127.8
80°	101.4	101.4	101.4	105.8	110.2	110.2	110.2	114.6	110.2	105.8	105.8
82.5°	79.3	79.3	83.7	83.7	88.1	88.1	88.1	92.5	88.1	83.7	83.7
85°	61.7	61.7	61.7	66.1	66.1	70.5	70.5	74.9	74.9	70.5	70.5
87.5°	39.7	35.3	39.7	39.7	44.1	44.1	39.7	35.3	39.7	35.3	30.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599023
 CATALOG NUMBER: IFLD-S-SA2B-760-U-SLL

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0	3173.0
2.5°	2895.4	2974.7	3032.0	3071.6	3128.9	3239.1	3283.2	3362.5	3384.5	3397.7
5°	2489.9	2573.6	2697.0	2785.2	2886.5	3093.7	3252.3	3371.3	3424.2	3472.7
7.5°	1952.3	2062.4	2190.2	2304.8	2472.3	2727.9	2935.0	3181.8	3274.4	3322.8
10°	1524.8	1626.2	1767.2	1908.2	2141.8	2357.7	2653.0	2877.7	3005.5	3040.8
12.5°	1286.8	1405.8	1573.3	1745.1	1890.6	2137.4	2437.0	2763.1	2882.1	2904.2
15°	1092.9	1256.0	1427.8	1604.1	1771.6	1987.5	2309.2	2705.9	2882.1	2904.2
17.5°	903.4	1048.9	1251.6	1441.1	1635.0	1930.2	2331.3	2754.3	2930.6	2996.7
20°	718.3	859.4	1018.0	1256.0	1520.4	1833.3	2379.7	2917.4	3151.0	3221.5
22.5°	594.9	656.6	810.9	1040.0	1352.9	1767.2	2428.2	3173.0	3419.8	3446.2
25°	520.0	564.1	661.0	877.0	1220.7	1723.1	2542.8	3468.3	3785.6	3785.6
27.5°	484.8	502.4	568.5	762.4	1128.2	1683.4	2657.4	3794.4	4089.6	4151.3
30°	475.9	520.0	555.3	678.7	1026.8	1573.3	2763.1	4050.0	4354.1	4358.5
32.5°	467.1	458.3	484.8	590.5	903.4	1458.7	2851.3	4310.0	4548.0	4561.2
35°	365.8	383.4	427.5	520.0	810.9	1375.0	2895.4	4451.0	4794.7	4808.0
37.5°	343.7	365.8	401.0	480.4	749.2	1304.5	2908.6	4724.2	5054.8	5081.2
40°	334.9	352.6	379.0	445.1	700.7	1216.3	2935.0	5006.3	5438.2	5402.9
42.5°	317.3	339.3	365.8	427.5	661.0	1150.2	2939.4	5160.5	5640.9	5640.9
45°	312.9	326.1	357.0	427.5	617.0	1092.9	2868.9	5314.8	5874.4	5803.9
47.5°	295.3	321.7	348.1	414.3	564.1	1035.6	2785.2	5394.1	5905.3	5883.3
50°	290.9	317.3	361.4	392.2	533.2	1009.2	2767.6	5592.4	5967.0	5962.6
52.5°	282.0	308.5	374.6	374.6	493.6	973.9	2851.3	5680.5	5980.2	6015.5
55°	268.8	308.5	348.1	343.7	458.3	929.9	2943.8	5909.7	6213.8	6205.0
57.5°	260.0	299.7	330.5	312.9	418.7	899.0	3080.4	6130.0	6495.8	6434.1
60°	246.8	299.7	295.3	290.9	387.8	872.6	3195.0	6174.1	6557.5	6597.2
62.5°	238.0	312.9	260.0	268.8	361.4	859.4	3146.6	5843.6	6473.8	6509.0
65°	229.2	268.8	238.0	246.8	352.6	832.9	2957.1	5447.0	6112.4	6266.7
67.5°	211.5	220.3	220.3	229.2	343.7	771.2	2569.2	4733.0	5561.5	5645.3
70°	193.9	198.3	198.3	211.5	334.9	700.7	2119.7	4094.0	4825.6	4984.2
72.5°	176.3	176.3	176.3	193.9	308.5	643.4	1745.1	3146.6	4010.3	4120.5
75°	154.2	154.2	154.2	171.9	277.6	586.1	1375.0	2340.1	2952.6	3111.3
77.5°	136.6	136.6	132.2	154.2	242.4	475.9	991.6	1652.6	2080.1	2212.3
80°	114.6	110.2	110.2	123.4	189.5	343.7	639.0	1167.8	1449.9	1507.2
82.5°	92.5	88.1	83.7	92.5	136.6	215.9	396.6	815.3	929.9	894.6
85°	88.1	92.5	74.9	70.5	97.0	141.0	251.2	502.4	418.7	418.7
87.5°	35.3	30.8	30.8	26.4	48.5	52.9	110.2	92.5	70.5	70.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)