

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS
Report Number: P599029

Luminaire Tested: **IFLD-S-SA3C-760-U-SLL**

Issue Date: 05/03/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P599029
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/03/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-S-SA3C-760-U-SLL
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens
 Light Source: (48) 5700K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 18430.1 lumens
 Efficiency: N/A
 Efficacy: 114.6 lumens/watt
 Spacing Criteria (0/90/45): 1.12 / 0.52 / 0.8
 Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
 CIE Type: Direct

Input Watts (W): 160.8
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599029
CATALOG NUMBER: IFLD-S-SA3C-760-U-SLL

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ···· 90°-270° - · - · 135°-315°

TEST NUMBER: P599029

CATALOG NUMBER: IFLD-S-SA3C-760-U-SLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	106	100	94	89	103	97	92	88	93	89	85	89	85	82	85	82	80	77	77	77
2	94	83	75	68	91	81	74	67	78	71	65	74	69	64	71	66	62	60	60	60
3	84	71	61	53	81	69	60	53	66	58	52	63	56	51	60	55	50	47	47	47
4	75	61	51	43	73	60	50	42	57	48	42	54	47	41	52	46	40	38	38	38
5	68	53	43	35	66	52	42	35	50	41	34	48	40	34	46	39	34	31	31	31
6	63	47	37	30	60	46	37	29	44	36	29	42	35	29	41	34	29	26	26	26
7	58	42	32	25	56	41	32	25	40	31	25	38	31	25	37	30	25	22	22	22
8	53	38	29	22	52	37	28	22	36	28	22	35	27	22	33	27	22	19	19	19
9	50	35	26	20	48	34	26	20	33	25	19	32	25	19	31	24	19	17	17	17
10	46	32	23	18	45	31	23	18	30	23	17	29	22	17	28	22	17	15	15	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	84482	84482	84482	84482
5°	92814	82448	59128	64546
10°	82211	72560	35863	38484
15°	80051	68877	25388	26360
20°	91277	79665	16608	18355
25°	111212	100983	14501	15018
30°	133997	122481	15039	13955
35°	156275	143813	12462	11746
40°	187787	173696	11640	11027
45°	218540	199623	11782	10952
50°	246979	226899	12048	11318
55°	288033	270440	12478	11865
60°	351303	341681	12437	12437
65°	394806	395359	12772	13326
70°	388007	401733	13378	13722
75°	320066	341376	14051	14961
80°	231095	242584	15538	16216
85°	127899	137318	17504	21539

TEST NUMBER: P599029
 CATALOG NUMBER: IFLD-S-SA3C-760-U-SLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	457.3	2.5
10°-20°	965.5	5.2
20°-30°	1412.6	7.7
30°-40°	1990.3	10.8
40°-50°	2735.3	14.8
50°-60°	3727.9	20.2
60°-70°	4080.1	22.1
70°-80°	2355.6	12.8
80°-90°	705.4	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2835.5	15.4
0°-40°	4825.8	26.2
0°-60°	11289.1	61.3
0°-90°	18430.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	18430.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	5886	5886	5886	5886	5886	
5°	6442	5723	4104	4480	6442	585
15°	5388	4636	1709	1774	5388	1574
25°	7023	6377	916	948	7023	3289
35°	8920	8208	711	670	8920	5656
45°	10767	9835	580	540	10767	8276
55°	11511	10808	499	474	11511	10386
65°	11626	11642	376	392	11626	11127
75°	5772	6156	253	270	5772	6200
85°	777	834	106	131	777	1078
90°	0	0	0	0	0	

TEST NUMBER: P599029
 CATALOG NUMBER: IFLD-S-SA3C-760-U-SLL

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5
2.5°	6303.4	6278.9	6303.4	6393.4	6417.9	6458.8	6458.8	6401.5	6295.2	6246.2	6164.4
5°	6442.4	6401.5	6605.9	6794.0	6941.1	6924.8	6785.8	6671.3	6458.8	6139.9	5837.4
7.5°	6164.4	6205.3	6352.5	6843.0	7186.4	7251.8	7031.0	6802.1	6344.3	5902.8	5494.0
10°	5641.2	5698.4	6017.3	6524.2	7063.8	7170.0	7031.0	6753.1	6205.3	5657.5	5183.4
12.5°	5387.7	5518.6	5706.6	6319.8	6704.0	6957.5	6892.1	6712.2	6099.0	5453.2	4995.3
15°	5387.7	5420.4	5698.4	6213.5	6434.2	6442.4	6466.9	6499.6	6131.7	5543.1	4929.9
17.5°	5559.4	5649.4	5886.5	6205.3	6246.2	6148.1	6148.1	6287.1	6197.1	5796.5	5167.0
20°	5976.4	5943.7	6254.4	6385.2	6164.4	5919.2	5894.6	6131.7	6270.7	6066.3	5600.3
22.5°	6393.4	6540.5	6794.0	6499.6	6090.9	5763.8	5731.1	6025.4	6491.5	6532.3	6099.0
25°	7022.9	7170.0	7300.8	6941.1	6082.7	5722.9	5747.5	5976.4	6761.3	7194.6	6932.9
27.5°	7701.5	7791.4	7979.4	7423.5	6278.9	5673.9	5698.4	6041.8	7014.7	7627.9	7587.0
30°	8085.7	8183.8	8142.9	7513.4	6409.7	5706.6	5641.2	6131.7	6875.7	7627.9	8012.1
32.5°	8461.8	8404.6	8380.0	7660.6	6573.2	5911.0	5747.5	6319.8	6957.5	7750.5	8559.9
35°	8919.6	8837.9	8772.5	7946.7	6843.0	6107.2	6033.6	6565.0	7137.3	8004.0	9001.4
37.5°	9426.5	9426.5	9107.7	8159.3	7161.9	6426.1	6344.3	6916.6	7423.5	8159.3	9606.4
40°	10023.3	10047.9	9483.7	8445.4	7521.6	6932.9	6908.4	7374.4	7701.5	8388.2	10186.8
42.5°	10464.8	10481.2	9810.8	8551.7	7938.5	7636.0	7742.3	8110.2	8020.3	8592.6	10227.7
45°	10767.3	10685.6	10039.7	8854.2	8396.4	8690.7	8723.4	8829.7	8437.3	8715.2	10391.2
47.5°	10914.5	10898.1	10137.8	9205.8	9361.1	9761.7	9949.8	9802.6	8821.5	8584.4	10391.2
50°	11061.6	10922.7	10227.7	9688.1	10301.3	11110.7	11069.8	10800.0	9352.9	8747.9	10235.9
52.5°	11159.7	11037.1	10407.6	10121.4	11200.6	12116.3	12279.8	11781.1	9974.3	9050.4	10309.5
55°	11511.3	11413.2	10947.2	10710.1	12238.9	13179.1	13203.7	12508.7	10628.3	9549.1	10791.8
57.5°	11936.4	11993.7	11691.2	11544.0	13032.0	13955.8	13865.9	13048.3	11184.3	10154.1	11347.8
60°	12238.9	12328.9	12255.3	12271.6	13424.4	14217.4	14013.0	13383.5	11593.1	10612.0	12026.4
62.5°	12075.4	12255.3	12557.8	12492.4	13440.8	14029.4	13743.2	12942.0	11642.1	11208.8	12541.4
65°	11625.8	11642.1	12230.8	12590.5	12704.9	13056.5	12680.4	12018.2	11135.2	11576.7	12467.9
67.5°	10473.0	10603.8	11135.2	11838.3	11356.0	11437.7	11405.0	10448.5	10366.7	11323.3	11903.7
70°	9246.6	9336.6	9917.1	10742.8	9590.0	9205.8	9279.4	8568.1	8903.3	10538.4	10767.3
72.5°	7644.2	7701.5	8363.7	9091.3	7693.3	7006.5	7178.2	6597.7	7071.9	9222.1	9083.1
75°	5772.0	5878.3	6393.4	7251.8	5665.7	5224.2	5395.9	5158.8	5600.3	7595.2	7047.4
77.5°	4104.2	4022.4	4660.1	5673.9	4259.5	3997.9	4014.2	4055.1	4529.3	6401.5	5060.7
80°	2796.1	2820.6	3392.9	4161.4	3343.8	3303.0	3262.1	3589.1	3801.7	5068.9	3679.0
82.5°	1659.7	1659.7	2289.2	2959.6	2640.7	2975.9	2787.9	3082.2	2975.9	3728.1	2411.8
85°	776.7	776.7	1177.3	2133.8	2043.9	2452.7	2084.8	2330.1	2199.2	2599.9	1087.4
87.5°	130.8	114.5	237.1	1046.5	842.1	956.5	376.1	1242.7	1381.7	1815.0	269.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599029
 CATALOG NUMBER: IFLD-S-SA3C-760-U-SLL

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5
2.5°	6074.5	6017.3	5902.8	5755.7	5633.0	5477.7	5428.6	5322.3	5175.2	5158.8	5093.4
5°	5722.9	5526.7	5281.5	4979.0	4774.6	4562.0	4382.1	4275.9	4153.2	4136.9	4104.2
7.5°	5338.7	5093.4	4684.6	4324.9	3973.4	3638.2	3474.6	3270.3	3131.3	3025.0	2975.9
10°	4979.0	4750.0	4243.2	3752.6	3441.9	3221.2	3025.0	2812.4	2640.7	2509.9	2460.9
12.5°	4741.9	4472.1	3924.3	3458.3	3229.4	2975.9	2755.2	2526.3	2305.5	2133.8	2043.9
15°	4635.6	4382.1	3826.2	3311.1	2975.9	2624.4	2370.9	2142.0	1872.2	1749.6	1708.7
17.5°	4889.0	4513.0	3793.5	3139.4	2665.3	2264.7	1954.0	1708.7	1512.5	1389.9	1340.8
20°	5216.1	4750.0	3850.7	2935.1	2370.9	1921.3	1577.9	1316.3	1185.5	1095.5	1087.4
22.5°	5633.0	5101.6	3940.7	2787.9	2043.9	1545.2	1234.5	1079.2	989.3	981.1	964.7
25°	6377.0	5739.3	4087.8	2591.7	1782.3	1275.4	1054.7	964.7	923.8	899.3	915.7
27.5°	7014.7	6156.3	4194.1	2469.0	1676.0	1201.8	1022.0	923.8	883.0	874.8	883.0
30°	7390.8	6540.5	4161.4	2240.1	1463.4	1144.6	1087.4	1054.7	972.9	907.5	907.5
32.5°	7734.2	6785.8	4153.2	2035.7	1250.9	956.5	907.5	883.0	932.0	964.7	940.2
35°	8208.3	7170.0	4128.7	1921.3	1160.9	883.0	801.2	735.8	703.1	686.8	711.3
37.5°	8715.2	7431.7	4063.3	1904.9	1111.9	842.1	776.7	711.3	678.6	662.2	654.1
40°	9271.2	7709.6	3989.7	1823.2	1087.4	817.6	752.2	694.9	654.1	629.5	621.3
42.5°	9630.9	7930.4	3916.1	1782.3	1038.3	801.2	727.6	678.6	637.7	605.0	605.0
45°	9835.3	8192.0	3842.6	1741.4	981.1	809.4	727.6	662.2	613.2	596.8	580.5
47.5°	9925.2	8388.2	3818.0	1676.0	932.0	776.7	711.3	645.9	596.8	564.1	555.9
50°	10162.3	8805.2	3908.0	1627.0	874.8	744.0	752.2	637.7	588.6	547.8	539.6
52.5°	10301.3	9140.4	4104.2	1553.4	833.9	703.1	735.8	621.3	564.1	523.2	523.2
55°	10808.2	9696.3	4316.7	1496.1	784.9	645.9	678.6	588.6	523.2	498.7	498.7
57.5°	11454.1	10285.0	4496.6	1471.6	752.2	605.0	605.0	572.3	498.7	466.0	457.8
60°	11903.7	10767.3	4602.9	1455.3	719.5	564.1	539.6	572.3	474.2	441.5	433.3
62.5°	11952.8	10489.3	4496.6	1447.1	711.3	523.2	490.5	547.8	449.7	417.0	400.6
65°	11642.1	9925.2	4202.3	1414.4	703.1	482.4	457.8	474.2	417.0	392.4	376.1
67.5°	11020.8	9009.6	3777.1	1398.0	694.9	449.7	417.0	408.8	384.3	359.7	343.4
70°	9573.7	7815.9	3278.4	1324.5	678.6	425.1	376.1	367.9	343.4	327.0	318.8
72.5°	8036.7	6393.4	2706.1	1226.3	645.9	384.3	343.4	327.0	318.8	294.3	286.1
75°	6156.3	4921.7	2166.5	1087.4	564.1	343.4	302.5	286.1	278.0	261.6	253.4
77.5°	4324.9	3662.7	1602.4	883.0	474.2	310.7	269.8	253.4	245.3	220.7	220.7
80°	2935.1	2567.2	1087.4	613.2	367.9	253.4	237.1	220.7	204.4	188.0	188.0
82.5°	1823.2	1798.6	784.9	400.6	269.8	204.4	188.0	188.0	163.5	147.2	147.2
85°	833.9	1103.7	547.8	278.0	204.4	155.3	155.3	147.2	130.8	106.3	106.3
87.5°	261.6	367.9	286.1	122.6	114.5	89.9	89.9	81.8	81.8	65.4	65.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599029
 CATALOG NUMBER: IFLD-S-SA3C-760-U-SLL

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5
2.5°	5158.8	5150.7	5150.7	5118.0	5199.7	5199.7	5248.8	5207.9	5232.4	5240.6	5306.0
5°	4096.0	4161.4	4210.5	4308.6	4365.8	4390.3	4390.3	4455.7	4431.2	4480.3	4578.4
7.5°	3000.5	3082.2	3229.4	3352.0	3450.1	3482.8	3474.6	3491.0	3515.5	3458.3	3474.6
10°	2428.2	2370.9	2420.0	2534.4	2624.4	2730.7	2648.9	2640.7	2665.3	2640.7	2689.8
12.5°	2027.6	1962.2	1921.3	1921.3	1986.7	2035.7	2011.2	2052.1	2142.0	2166.5	2223.8
15°	1643.3	1586.1	1553.4	1512.5	1577.9	1594.2	1618.8	1676.0	1741.4	1774.1	1839.5
17.5°	1316.3	1316.3	1316.3	1283.6	1308.1	1332.6	1340.8	1414.4	1422.6	1455.3	1479.8
20°	1079.2	1103.7	1144.6	1160.9	1185.5	1185.5	1169.1	1210.0	1177.3	1201.8	1218.2
22.5°	972.9	1005.6	1022.0	1030.1	1062.8	1071.0	1030.1	1038.3	1046.5	1022.0	1030.1
25°	915.7	932.0	915.7	923.8	932.0	915.7	923.8	940.2	932.0	948.4	940.2
27.5°	891.1	874.8	866.6	858.4	858.4	842.1	850.3	850.3	866.6	874.8	874.8
30°	891.1	866.6	833.9	809.4	809.4	784.9	801.2	817.6	825.7	842.1	842.1
32.5°	915.7	866.6	809.4	784.9	760.3	744.0	760.3	784.9	817.6	825.7	833.9
35°	727.6	752.2	744.0	711.3	703.1	703.1	694.9	694.9	670.4	670.4	662.2
37.5°	654.1	645.9	662.2	670.4	678.6	654.1	654.1	621.3	613.2	621.3	621.3
40°	613.2	613.2	613.2	637.7	645.9	629.5	605.0	588.6	588.6	588.6	596.8
42.5°	596.8	580.5	572.3	588.6	613.2	596.8	572.3	564.1	564.1	572.3	572.3
45°	572.3	564.1	555.9	547.8	580.5	555.9	547.8	539.6	539.6	539.6	547.8
47.5°	547.8	539.6	523.2	523.2	531.4	523.2	515.1	515.1	515.1	531.4	531.4
50°	531.4	523.2	506.9	506.9	506.9	506.9	498.7	498.7	498.7	506.9	515.1
52.5°	506.9	498.7	490.5	482.4	482.4	482.4	482.4	482.4	482.4	490.5	498.7
55°	482.4	474.2	466.0	466.0	474.2	474.2	466.0	474.2	466.0	474.2	482.4
57.5°	457.8	449.7	441.5	449.7	457.8	449.7	449.7	449.7	449.7	449.7	457.8
60°	425.1	425.1	425.1	425.1	441.5	441.5	441.5	441.5	425.1	433.3	441.5
62.5°	408.8	400.6	400.6	408.8	417.0	417.0	425.1	417.0	408.8	417.0	417.0
65°	376.1	376.1	376.1	384.3	384.3	392.4	392.4	392.4	384.3	392.4	392.4
67.5°	351.6	351.6	351.6	351.6	367.9	367.9	367.9	367.9	359.7	359.7	367.9
70°	310.7	318.8	310.7	327.0	343.4	335.2	343.4	343.4	335.2	327.0	343.4
72.5°	286.1	286.1	286.1	286.1	310.7	310.7	310.7	318.8	310.7	302.5	310.7
75°	253.4	253.4	253.4	261.6	278.0	278.0	278.0	278.0	278.0	269.8	269.8
77.5°	220.7	228.9	220.7	228.9	245.3	237.1	245.3	253.4	245.3	237.1	237.1
80°	188.0	188.0	188.0	196.2	204.4	204.4	204.4	212.6	204.4	196.2	196.2
82.5°	147.2	147.2	155.3	155.3	163.5	163.5	163.5	171.7	163.5	155.3	155.3
85°	114.5	114.5	114.5	122.6	122.6	130.8	130.8	139.0	139.0	130.8	130.8
87.5°	73.6	65.4	73.6	73.6	81.8	81.8	73.6	65.4	73.6	65.4	57.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P599029
 CATALOG NUMBER: IFLD-S-SA3C-760-U-SLL

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5	5886.5
2.5°	5371.4	5518.6	5624.8	5698.4	5804.7	6009.1	6090.9	6238.0	6278.9	6303.4
5°	4619.2	4774.6	5003.5	5167.0	5355.0	5739.3	6033.6	6254.4	6352.5	6442.4
7.5°	3621.8	3826.2	4063.3	4275.9	4586.5	5060.7	5445.0	5902.8	6074.5	6164.4
10°	2828.8	3016.8	3278.4	3540.1	3973.4	4374.0	4921.7	5338.7	5575.8	5641.2
12.5°	2387.3	2608.0	2918.7	3237.6	3507.3	3965.2	4521.1	5126.1	5346.9	5387.7
15°	2027.6	2330.1	2648.9	2975.9	3286.6	3687.2	4284.0	5019.8	5346.9	5387.7
17.5°	1676.0	1945.8	2321.9	2673.4	3033.2	3580.9	4324.9	5109.8	5436.8	5559.4
20°	1332.6	1594.2	1888.6	2330.1	2820.6	3401.1	4414.8	5412.3	5845.6	5976.4
22.5°	1103.7	1218.2	1504.3	1929.5	2509.9	3278.4	4504.8	5886.5	6344.3	6393.4
25°	964.7	1046.5	1226.3	1627.0	2264.7	3196.7	4717.3	6434.2	7022.9	7022.9
27.5°	899.3	932.0	1054.7	1414.4	2093.0	3123.1	4929.9	7039.2	7587.0	7701.5
30°	883.0	964.7	1030.1	1259.0	1904.9	2918.7	5126.1	7513.4	8077.5	8085.7
32.5°	866.6	850.3	899.3	1095.5	1676.0	2706.1	5289.6	7995.8	8437.3	8461.8
35°	678.6	711.3	793.0	964.7	1504.3	2550.8	5371.4	8257.4	8895.1	8919.6
37.5°	637.7	678.6	744.0	891.1	1389.9	2420.0	5395.9	8764.3	9377.5	9426.5
40°	621.3	654.1	703.1	825.7	1299.9	2256.5	5445.0	9287.5	10088.7	10023.3
42.5°	588.6	629.5	678.6	793.0	1226.3	2133.8	5453.2	9573.7	10464.8	10464.8
45°	580.5	605.0	662.2	793.0	1144.6	2027.6	5322.3	9859.8	10898.1	10767.3
47.5°	547.8	596.8	645.9	768.5	1046.5	1921.3	5167.0	10007.0	10955.4	10914.5
50°	539.6	588.6	670.4	727.6	989.3	1872.2	5134.3	10374.9	11069.8	11061.6
52.5°	523.2	572.3	694.9	694.9	915.7	1806.8	5289.6	10538.4	11094.3	11159.7
55°	498.7	572.3	645.9	637.7	850.3	1725.1	5461.3	10963.5	11527.7	11511.3
57.5°	482.4	555.9	613.2	580.5	776.7	1667.8	5714.8	11372.3	12050.9	11936.4
60°	457.8	555.9	547.8	539.6	719.5	1618.8	5927.3	11454.1	12165.4	12238.9
62.5°	441.5	580.5	482.4	498.7	670.4	1594.2	5837.4	10840.9	12010.0	12075.4
65°	425.1	498.7	441.5	457.8	654.1	1545.2	5485.9	10105.1	11339.6	11625.8
67.5°	392.4	408.8	408.8	425.1	637.7	1430.7	4766.4	8780.6	10317.7	10473.0
70°	359.7	367.9	367.9	392.4	621.3	1299.9	3932.5	7595.2	8952.3	9246.6
72.5°	327.0	327.0	327.0	359.7	572.3	1193.6	3237.6	5837.4	7439.8	7644.2
75°	286.1	286.1	286.1	318.8	515.1	1087.4	2550.8	4341.3	5477.7	5772.0
77.5°	253.4	253.4	245.3	286.1	449.7	883.0	1839.5	3065.9	3858.9	4104.2
80°	212.6	204.4	204.4	228.9	351.6	637.7	1185.5	2166.5	2689.8	2796.1
82.5°	171.7	163.5	155.3	171.7	253.4	400.6	735.8	1512.5	1725.1	1659.7
85°	163.5	171.7	139.0	130.8	179.9	261.6	466.0	932.0	776.7	776.7
87.5°	65.4	57.2	57.2	49.1	89.9	98.1	204.4	171.7	130.8	130.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)