

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS
Report Number: P599003

Luminaire Tested: **IFLD-S-SA6A-750-U-SLL**

Issue Date: 05/03/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P599003
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/03/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-S-SA6A-750-U-SLL
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens
 Light Source: (96) 5000K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 23483.5 lumens
 Efficiency: N/A
 Efficacy: 123.9 lumens/watt
 Spacing Criteria (0/90/45): 1.12 / 0.52 / 0.8
 Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
 CIE Type: Direct

Input Watts (W): 189.6
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599003
CATALOG NUMBER: IFLD-S-SA6A-750-U-SLL

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ··· 90°-270° - · 135°-315°

TEST NUMBER: P599003
 CATALOG NUMBER: IFLD-S-SA6A-750-U-SLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	106	100	94	89	103	97	92	88	93	89	85	89	85	82	85	82	80	85	82	80	77
2	94	83	75	68	91	81	74	67	78	71	65	74	69	64	71	66	62	71	66	62	60
3	84	71	61	53	81	69	60	53	66	58	52	63	56	51	60	55	50	60	55	50	47
4	75	61	51	43	73	60	50	42	57	48	42	54	47	41	52	46	40	52	46	40	38
5	68	53	43	35	66	52	42	35	50	41	34	48	40	34	46	39	34	46	39	34	31
6	63	47	37	30	60	46	37	29	44	36	29	42	35	29	41	34	29	41	34	29	26
7	58	42	32	25	56	41	32	25	40	31	25	38	31	25	37	30	25	37	30	25	22
8	53	38	29	22	52	37	28	22	36	28	22	35	27	22	33	27	22	33	27	22	19
9	50	35	26	20	48	34	26	20	33	25	19	32	25	19	31	24	19	31	24	19	17
10	46	32	23	18	45	31	23	18	30	23	17	29	22	17	28	22	17	28	22	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	53823	53823	53823	53823
5°	59132	52528	37670	41122
10°	52376	46228	22848	24518
15°	51001	43881	16175	16794
20°	58153	50754	10580	11695
25°	70852	64336	9238	9568
30°	85370	78032	9581	8891
35°	99562	91623	7939	7483
40°	119639	110661	7416	7026
45°	139231	127180	7506	6977
50°	157350	144558	7675	7211
55°	183505	172296	7951	7559
60°	223815	217685	7924	7924
65°	251529	251882	8137	8490
70°	247199	255942	8525	8743
75°	203912	217489	8953	9532
80°	147227	154546	9901	10331
85°	81478	87489	11148	13725

TEST NUMBER: P599003
 CATALOG NUMBER: IFLD-S-SA6A-750-U-SLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	582.7	2.5
10°-20°	1230.2	5.2
20°-30°	1800.0	7.7
30°-40°	2536.1	10.8
40°-50°	3485.3	14.8
50°-60°	4750.1	20.2
60°-70°	5198.8	22.1
70°-80°	3001.4	12.8
80°-90°	898.8	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3612.9	15.4
0°-40°	6149.0	26.2
0°-60°	14384.4	61.3
0°-90°	23483.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	23483.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	7500	7500	7500	7500	7500	
5°	8209	7292	5230	5709	8209	745
15°	6865	5907	2177	2261	6865	2006
25°	8948	8126	1167	1208	8948	4190
35°	11365	10459	906	854	11365	7207
45°	13720	12532	740	688	13720	10545
55°	14668	13772	636	604	14668	13234
65°	14814	14834	479	500	14814	14178
75°	7355	7844	323	344	7355	7900
85°	990	1063	135	167	990	1373
90°	0	0	0	0	0	

TEST NUMBER: P599003
 CATALOG NUMBER: IFLD-S-SA6A-750-U-SLL

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5
2.5°	8031.8	8000.5	8031.8	8146.4	8177.6	8229.7	8229.7	8156.8	8021.4	7958.9	7854.7
5°	8208.9	8156.8	8417.2	8656.8	8844.3	8823.5	8646.4	8500.6	8229.7	7823.4	7438.0
7.5°	7854.7	7906.8	8094.3	8719.3	9156.8	9240.2	8958.9	8667.2	8083.9	7521.3	7000.5
10°	7188.0	7260.9	7667.2	8313.0	9000.6	9136.0	8958.9	8604.7	7906.8	7208.8	6604.6
12.5°	6865.0	7031.7	7271.3	8052.6	8542.2	8865.2	8781.8	8552.6	7771.3	6948.4	6365.0
15°	6865.0	6906.7	7260.9	7917.2	8198.5	8208.9	8240.1	8281.8	7813.0	7063.0	6281.7
17.5°	7083.8	7198.4	7500.5	7906.8	7958.9	7833.8	7833.8	8010.9	7896.3	7385.9	6583.8
20°	7615.1	7573.4	7969.3	8135.9	7854.7	7542.2	7510.9	7813.0	7990.1	7729.7	7135.9
22.5°	8146.4	8333.9	8656.8	8281.8	7760.9	7344.2	7302.6	7677.6	8271.4	8323.5	7771.3
25°	8948.5	9136.0	9302.7	8844.3	7750.5	7292.1	7323.4	7615.1	8615.1	9167.3	8833.9
27.5°	9813.1	9927.7	10167.3	9459.0	8000.5	7229.6	7260.9	7698.4	8938.1	9719.4	9667.3
30°	10302.8	10427.8	10375.7	9573.5	8167.2	7271.3	7188.0	7813.0	8761.0	9719.4	10209.0
32.5°	10782.0	10709.0	10677.8	9761.1	8375.5	7531.7	7323.4	8052.6	8865.2	9875.6	10907.0
35°	11365.3	11261.2	11177.8	10125.7	8719.3	7781.8	7688.0	8365.1	9094.3	10198.6	11469.5
37.5°	12011.2	12011.2	11604.9	10396.5	9125.6	8188.0	8083.9	8813.1	9459.0	10396.5	12240.4
40°	12771.7	12802.9	12084.1	10761.1	9584.0	8833.9	8802.7	9396.4	9813.1	10688.2	12980.0
42.5°	13334.2	13355.0	12500.8	10896.5	10115.2	9729.8	9865.2	10334.0	10219.4	10948.6	13032.1
45°	13719.6	13615.5	12792.5	11282.0	10698.6	11073.6	11115.3	11250.7	10750.7	11104.9	13240.4
47.5°	13907.2	13886.3	12917.5	11729.9	11927.9	12438.3	12677.9	12490.4	11240.3	10938.2	13240.4
50°	14094.7	13917.6	13032.1	12344.6	13125.9	14157.2	14105.1	13761.3	11917.4	11146.6	13042.5
52.5°	14219.7	14063.4	13261.3	12896.7	14271.8	15438.5	15646.9	15011.4	12709.2	11532.0	13136.3
55°	14667.6	14542.6	13948.8	13646.7	15594.8	16792.8	16824.0	15938.5	13542.6	12167.5	13750.9
57.5°	15209.3	15282.2	14896.8	14709.3	16605.3	17782.4	17667.8	16626.1	14250.9	12938.3	14459.3
60°	15594.8	15709.4	15615.6	15636.4	17105.3	18115.8	17855.3	17053.2	14771.8	13521.7	15323.9
62.5°	15386.4	15615.6	16001.0	15917.7	17126.1	17876.2	17511.6	16490.7	14834.3	14282.2	15980.2
65°	14813.5	14834.3	15584.4	16042.7	16188.6	16636.5	16157.3	15313.5	14188.4	14751.0	15886.5
67.5°	13344.6	13511.3	14188.4	15084.3	14469.7	14573.9	14532.2	13313.4	13209.2	14428.0	15167.7
70°	11782.0	11896.6	12636.2	13688.4	12219.5	11729.9	11823.7	10917.4	11344.5	13428.0	13719.6
72.5°	9740.2	9813.1	10656.9	11584.1	9802.7	8927.7	9146.4	8406.8	9011.0	11750.8	11573.7
75°	7354.6	7490.1	8146.4	9240.2	7219.2	6656.7	6875.4	6573.3	7135.9	9677.7	8979.8
77.5°	5229.5	5125.3	5937.9	7229.6	5427.4	5094.1	5114.9	5167.0	5771.2	8156.8	6448.3
80°	3562.7	3594.0	4323.2	5302.4	4260.7	4208.6	4156.5	4573.2	4844.1	6458.8	4687.8
82.5°	2114.7	2114.7	2916.9	3771.1	3364.8	3791.9	3552.3	3927.3	3791.9	4750.3	3073.1
85°	989.6	989.6	1500.1	2718.9	2604.3	3125.2	2656.4	2968.9	2802.3	3312.7	1385.5
87.5°	166.7	145.8	302.1	1333.4	1073.0	1218.8	479.2	1583.4	1760.5	2312.7	343.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599003
 CATALOG NUMBER: IFLD-S-SA6A-750-U-SLL

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5
2.5°	7740.1	7667.2	7521.3	7333.8	7177.6	6979.6	6917.1	6781.7	6594.2	6573.3	6490.0
5°	7292.1	7042.1	6729.6	6344.2	6083.7	5812.9	5583.7	5448.3	5292.0	5271.2	5229.5
7.5°	6802.5	6490.0	5969.1	5510.8	5062.8	4635.7	4427.4	4166.9	3989.8	3854.4	3791.9
10°	6344.2	6052.5	5406.6	4781.6	4385.7	4104.4	3854.4	3583.6	3364.8	3198.1	3135.6
12.5°	6042.1	5698.3	5000.3	4406.5	4114.9	3791.9	3510.6	3219.0	2937.7	2718.9	2604.3
15°	5906.6	5583.7	4875.3	4219.0	3791.9	3344.0	3021.0	2729.3	2385.6	2229.3	2177.2
17.5°	6229.6	5750.4	4833.6	4000.3	3396.1	2885.6	2489.7	2177.2	1927.2	1770.9	1708.4
20°	6646.3	6052.5	4906.6	3739.8	3021.0	2448.1	2010.5	1677.2	1510.5	1395.9	1385.5
22.5°	7177.6	6500.4	5021.2	3552.3	2604.3	1968.9	1573.0	1375.1	1260.5	1250.1	1229.2
25°	8125.5	7313.0	5208.7	3302.3	2271.0	1625.1	1343.8	1229.2	1177.2	1145.9	1166.7
27.5°	8938.1	7844.3	5344.1	3146.0	2135.6	1531.4	1302.2	1177.2	1125.1	1114.7	1125.1
30°	9417.3	8333.9	5302.4	2854.4	1864.7	1458.4	1385.5	1343.8	1239.7	1156.3	1156.3
32.5°	9854.8	8646.4	5292.0	2593.9	1593.9	1218.8	1156.3	1125.1	1187.6	1229.2	1198.0
35°	10459.0	9136.0	5260.8	2448.1	1479.3	1125.1	1020.9	937.6	895.9	875.1	906.3
37.5°	11104.9	9469.4	5177.4	2427.2	1416.8	1073.0	989.6	906.3	864.6	843.8	833.4
40°	11813.3	9823.6	5083.7	2323.1	1385.5	1041.7	958.4	885.5	833.4	802.1	791.7
42.5°	12271.6	10104.8	4989.9	2271.0	1323.0	1020.9	927.1	864.6	812.6	770.9	770.9
45°	12532.1	10438.2	4896.2	2218.9	1250.1	1031.3	927.1	843.8	781.3	760.5	739.6
47.5°	12646.7	10688.2	4864.9	2135.6	1187.6	989.6	906.3	823.0	760.5	718.8	708.4
50°	12948.8	11219.5	4979.5	2073.1	1114.7	948.0	958.4	812.6	750.0	698.0	687.5
52.5°	13125.9	11646.6	5229.5	1979.3	1062.6	895.9	937.6	791.7	718.8	666.7	666.7
55°	13771.7	12355.0	5500.4	1906.4	1000.1	823.0	864.6	750.0	666.7	635.5	635.5
57.5°	14594.7	13105.0	5729.5	1875.1	958.4	770.9	770.9	729.2	635.5	593.8	583.4
60°	15167.7	13719.6	5865.0	1854.3	916.7	718.8	687.5	729.2	604.2	562.5	552.1
62.5°	15230.2	13365.5	5729.5	1843.9	906.3	666.7	625.0	698.0	573.0	531.3	510.5
65°	14834.3	12646.7	5354.5	1802.2	895.9	614.6	583.4	604.2	531.3	500.0	479.2
67.5°	14042.6	11479.9	4812.8	1781.4	885.5	573.0	531.3	520.9	489.6	458.4	437.5
70°	12198.7	9959.0	4177.4	1687.6	864.6	541.7	479.2	468.8	437.5	416.7	406.3
72.5°	10240.3	8146.4	3448.1	1562.6	823.0	489.6	437.5	416.7	406.3	375.0	364.6
75°	7844.3	6271.2	2760.6	1385.5	718.8	437.5	385.4	364.6	354.2	333.4	322.9
77.5°	5510.8	4667.0	2041.8	1125.1	604.2	395.9	343.8	322.9	312.5	281.3	281.3
80°	3739.8	3271.0	1385.5	781.3	468.8	322.9	302.1	281.3	260.4	239.6	239.6
82.5°	2323.1	2291.8	1000.1	510.5	343.8	260.4	239.6	239.6	208.3	187.5	187.5
85°	1062.6	1406.3	698.0	354.2	260.4	197.9	197.9	187.5	166.7	135.4	135.4
87.5°	333.4	468.8	364.6	156.3	145.8	114.6	114.6	104.2	104.2	83.3	83.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599003
 CATALOG NUMBER: IFLD-S-SA6A-750-U-SLL

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5
2.5°	6573.3	6562.9	6562.9	6521.3	6625.4	6625.4	6687.9	6635.9	6667.1	6677.5	6760.9
5°	5219.1	5302.4	5364.9	5489.9	5562.9	5594.1	5594.1	5677.5	5646.2	5708.7	5833.7
7.5°	3823.2	3927.3	4114.9	4271.1	4396.1	4437.8	4427.4	4448.2	4479.5	4406.5	4427.4
10°	3094.0	3021.0	3083.5	3229.4	3344.0	3479.4	3375.2	3364.8	3396.1	3364.8	3427.3
12.5°	2583.5	2500.2	2448.1	2448.1	2531.4	2593.9	2562.7	2614.8	2729.3	2760.6	2833.5
15°	2093.9	2021.0	1979.3	1927.2	2010.5	2031.4	2062.6	2135.6	2218.9	2260.6	2343.9
17.5°	1677.2	1677.2	1677.2	1635.5	1666.8	1698.0	1708.4	1802.2	1812.6	1854.3	1885.5
20°	1375.1	1406.3	1458.4	1479.3	1510.5	1510.5	1489.7	1541.8	1500.1	1531.4	1552.2
22.5°	1239.7	1281.3	1302.2	1312.6	1354.3	1364.7	1312.6	1323.0	1333.4	1302.2	1312.6
25°	1166.7	1187.6	1166.7	1177.2	1187.6	1166.7	1177.2	1198.0	1187.6	1208.4	1198.0
27.5°	1135.5	1114.7	1104.2	1093.8	1093.8	1073.0	1083.4	1083.4	1104.2	1114.7	1114.7
30°	1135.5	1104.2	1062.6	1031.3	1031.3	1000.1	1020.9	1041.7	1052.2	1073.0	1073.0
32.5°	1166.7	1104.2	1031.3	1000.1	968.8	948.0	968.8	1000.1	1041.7	1052.2	1062.6
35°	927.1	958.4	948.0	906.3	895.9	895.9	885.5	885.5	854.2	854.2	843.8
37.5°	833.4	823.0	843.8	854.2	864.6	833.4	833.4	791.7	781.3	791.7	791.7
40°	781.3	781.3	781.3	812.6	823.0	802.1	770.9	750.0	750.0	750.0	760.5
42.5°	760.5	739.6	729.2	750.0	781.3	760.5	729.2	718.8	718.8	729.2	729.2
45°	729.2	718.8	708.4	698.0	739.6	708.4	698.0	687.5	687.5	687.5	698.0
47.5°	698.0	687.5	666.7	666.7	677.1	666.7	656.3	656.3	656.3	677.1	677.1
50°	677.1	666.7	645.9	645.9	645.9	645.9	635.5	635.5	635.5	645.9	656.3
52.5°	645.9	635.5	625.0	614.6	614.6	614.6	614.6	614.6	614.6	625.0	635.5
55°	614.6	604.2	593.8	593.8	604.2	604.2	593.8	604.2	593.8	604.2	614.6
57.5°	583.4	573.0	562.5	573.0	583.4	573.0	573.0	573.0	573.0	573.0	583.4
60°	541.7	541.7	541.7	541.7	562.5	562.5	562.5	562.5	541.7	552.1	562.5
62.5°	520.9	510.5	510.5	520.9	531.3	531.3	541.7	531.3	520.9	531.3	531.3
65°	479.2	479.2	479.2	489.6	489.6	500.0	500.0	500.0	489.6	500.0	500.0
67.5°	447.9	447.9	447.9	447.9	468.8	468.8	468.8	468.8	458.4	458.4	468.8
70°	395.9	406.3	395.9	416.7	437.5	427.1	437.5	437.5	427.1	416.7	437.5
72.5°	364.6	364.6	364.6	364.6	395.9	395.9	395.9	406.3	395.9	385.4	395.9
75°	322.9	322.9	322.9	333.4	354.2	354.2	354.2	354.2	354.2	343.8	343.8
77.5°	281.3	291.7	281.3	291.7	312.5	302.1	312.5	322.9	312.5	302.1	302.1
80°	239.6	239.6	239.6	250.0	260.4	260.4	260.4	270.9	260.4	250.0	250.0
82.5°	187.5	187.5	197.9	197.9	208.3	208.3	208.3	218.8	208.3	197.9	197.9
85°	145.8	145.8	145.8	156.3	156.3	166.7	166.7	177.1	177.1	166.7	166.7
87.5°	93.8	83.3	93.8	93.8	104.2	104.2	93.8	83.3	93.8	83.3	72.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599003
 CATALOG NUMBER: IFLD-S-SA6A-750-U-SLL

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5	7500.5
2.5°	6844.2	7031.7	7167.1	7260.9	7396.3	7656.8	7760.9	7948.4	8000.5	8031.8
5°	5885.8	6083.7	6375.4	6583.8	6823.4	7313.0	7688.0	7969.3	8094.3	8208.9
7.5°	4614.9	4875.3	5177.4	5448.3	5844.1	6448.3	6938.0	7521.3	7740.1	7854.7
10°	3604.4	3844.0	4177.4	4510.7	5062.8	5573.3	6271.2	6802.5	7104.6	7188.0
12.5°	3041.9	3323.1	3719.0	4125.3	4469.0	5052.4	5760.8	6531.7	6812.9	6865.0
15°	2583.5	2968.9	3375.2	3791.9	4187.8	4698.2	5458.7	6396.3	6812.9	6865.0
17.5°	2135.6	2479.3	2958.5	3406.5	3864.8	4562.8	5510.8	6510.8	6927.5	7083.8
20°	1698.0	2031.4	2406.4	2968.9	3594.0	4333.6	5625.4	6896.3	7448.4	7615.1
22.5°	1406.3	1552.2	1916.8	2458.5	3198.1	4177.4	5740.0	7500.5	8083.9	8146.4
25°	1229.2	1333.4	1562.6	2073.1	2885.6	4073.2	6010.8	8198.5	8948.5	8948.5
27.5°	1145.9	1187.6	1343.8	1802.2	2666.8	3979.4	6281.7	8969.3	9667.3	9813.1
30°	1125.1	1229.2	1312.6	1604.3	2427.2	3719.0	6531.7	9573.5	10292.3	10302.8
32.5°	1104.2	1083.4	1145.9	1395.9	2135.6	3448.1	6740.0	10188.2	10750.7	10782.0
35°	864.6	906.3	1010.5	1229.2	1916.8	3250.2	6844.2	10521.5	11334.1	11365.3
37.5°	812.6	864.6	948.0	1135.5	1770.9	3083.5	6875.4	11167.4	11948.7	12011.2
40°	791.7	833.4	895.9	1052.2	1656.4	2875.2	6938.0	11834.1	12855.0	12771.7
42.5°	750.0	802.1	864.6	1010.5	1562.6	2718.9	6948.4	12198.7	13334.2	13334.2
45°	739.6	770.9	843.8	1010.5	1458.4	2583.5	6781.7	12563.3	13886.3	13719.6
47.5°	698.0	760.5	823.0	979.2	1333.4	2448.1	6583.8	12750.8	13959.2	13907.2
50°	687.5	750.0	854.2	927.1	1260.5	2385.6	6542.1	13219.6	14105.1	14094.7
52.5°	666.7	729.2	885.5	885.5	1166.7	2302.2	6740.0	13428.0	14136.3	14219.7
55°	635.5	729.2	823.0	812.6	1083.4	2198.1	6958.8	13969.7	14688.5	14667.6
57.5°	614.6	708.4	781.3	739.6	989.6	2125.1	7281.7	14490.5	15355.2	15209.3
60°	583.4	708.4	698.0	687.5	916.7	2062.6	7552.6	14594.7	15501.0	15594.8
62.5°	562.5	739.6	614.6	635.5	854.2	2031.4	7438.0	13813.4	15303.1	15386.4
65°	541.7	635.5	562.5	583.4	833.4	1968.9	6990.0	12875.8	14448.9	14813.5
67.5°	500.0	520.9	520.9	541.7	812.6	1823.0	6073.3	11188.2	13146.7	13344.6
70°	458.4	468.8	468.8	500.0	791.7	1656.4	5010.7	9677.7	11407.0	11782.0
72.5°	416.7	416.7	416.7	458.4	729.2	1520.9	4125.3	7438.0	9479.8	9740.2
75°	364.6	364.6	364.6	406.3	656.3	1385.5	3250.2	5531.6	6979.6	7354.6
77.5°	322.9	322.9	312.5	364.6	573.0	1125.1	2343.9	3906.5	4917.0	5229.5
80°	270.9	260.4	260.4	291.7	447.9	812.6	1510.5	2760.6	3427.3	3562.7
82.5°	218.8	208.3	197.9	218.8	322.9	510.5	937.6	1927.2	2198.1	2114.7
85°	208.3	218.8	177.1	166.7	229.2	333.4	593.8	1187.6	989.6	989.6
87.5°	83.3	72.9	72.9	62.5	114.6	125.0	260.4	218.8	166.7	166.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)