

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599005

Luminaire Tested: **IFLD-S-SA6C-750-U-SLL**

Issue Date: 05/03/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P599005
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/03/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-S-SA6C-750-U-SLL
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens
 Light Source: (96) 5000K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 36153.5 lumens
 Efficiency: N/A
 Efficacy: 112.5 lumens/watt
 Spacing Criteria (0/90/45): 1.12 / 0.52 / 0.8
 Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
 CIE Type: Direct

Input Watts (W): 321.5
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599005
CATALOG NUMBER: IFLD-S-SA6C-750-U-SLL

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°

TEST NUMBER: P599005
 CATALOG NUMBER: IFLD-S-SA6C-750-U-SLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	106	100	94	89	103	97	92	88	93	89	85	89	85	82	85	82	80	77				
2	94	83	75	68	91	81	74	67	78	71	65	74	69	64	71	66	62	60				
3	84	71	61	53	81	69	60	53	66	58	52	63	56	51	60	55	50	47				
4	75	61	51	43	73	60	50	42	57	48	42	54	47	41	52	46	40	38				
5	68	53	43	35	66	52	42	35	50	41	34	48	40	34	46	39	34	31				
6	63	47	37	30	60	46	37	29	44	36	29	42	35	29	41	34	29	26				
7	58	42	32	25	56	41	32	25	40	31	25	38	31	25	37	30	25	22				
8	53	38	29	22	52	37	28	22	36	28	22	35	27	22	33	27	22	19				
9	50	35	26	20	48	34	26	20	33	25	19	32	25	19	31	24	19	17				
10	46	32	23	18	45	31	23	18	30	23	17	29	22	17	28	22	17	15				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	82862	82862	82862	82862
5°	91035	80868	57994	63308
10°	80635	71169	35176	37746
15°	78517	67556	24902	25855
20°	89527	78137	16289	18004
25°	109079	99047	14222	14730
30°	131429	120133	14751	13688
35°	153280	141057	12223	11521
40°	184188	170366	11418	10817
45°	214351	195797	11556	10742
50°	242245	222550	11817	11100
55°	282511	265256	12239	11638
60°	344569	335132	12199	12199
65°	387236	387781	12526	13071
70°	380571	394031	13124	13459
75°	313930	334830	13785	14672
80°	226661	237931	15245	15906
85°	125445	134691	17167	21127

TEST NUMBER: P599005
 CATALOG NUMBER: IFLD-S-SA6C-750-U-SLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	897.1	2.5
10°-20°	1894.0	5.2
20°-30°	2771.1	7.7
30°-40°	3904.4	10.8
40°-50°	5365.8	14.8
50°-60°	7312.9	20.2
60°-70°	8003.7	22.1
70°-80°	4620.8	12.8
80°-90°	1383.7	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5562.2	15.4
0°-40°	9466.6	26.2
0°-60°	22145.3	61.3
0°-90°	36153.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	36153.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	11547	11547	11547	11547	11547	
5°	12638	11226	8051	8789	12638	1148
15°	10569	9093	3352	3480	10569	3088
25°	13776	12510	1796	1860	13776	6451
35°	17497	16102	1395	1315	17497	11095
45°	21122	19294	1139	1058	21122	16234
55°	22581	21202	978	930	22581	20375
65°	22806	22838	738	770	22806	21828
75°	11323	12076	497	529	11323	12163
85°	1524	1636	208	257	1524	2114
90°	0	0	0	0	0	

TEST NUMBER: P599005
 CATALOG NUMBER: IFLD-S-SA6C-750-U-SLL

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2
2.5°	12365.2	12317.0	12365.2	12541.6	12589.7	12669.9	12669.9	12557.6	12349.1	12252.9	12092.5
5°	12637.8	12557.6	12958.6	13327.4	13616.1	13584.0	13311.4	13086.9	12669.9	12044.4	11451.0
7.5°	12092.5	12172.7	12461.4	13423.7	14097.2	14225.5	13792.5	13343.5	12445.3	11579.3	10777.4
10°	11066.1	11178.4	11803.8	12798.2	13856.7	14065.2	13792.5	13247.2	12172.7	11098.2	10168.0
12.5°	10568.9	10825.5	11194.4	12397.2	13151.0	13648.2	13519.9	13167.0	11964.2	10697.2	9799.1
15°	10568.9	10633.1	11178.4	12188.7	12621.8	12637.8	12685.9	12750.1	12028.4	10873.6	9670.8
17.5°	10905.7	11082.1	11547.2	12172.7	12252.9	12060.4	12060.4	12333.1	12156.7	11370.8	10135.9
20°	11723.6	11659.5	12268.9	12525.5	12092.5	11611.4	11563.3	12028.4	12301.0	11900.1	10985.9
22.5°	12541.6	12830.3	13327.4	12750.1	11948.2	11306.7	11242.5	11819.9	12734.0	12814.2	11964.2
25°	13776.5	14065.2	14321.8	13616.1	11932.1	11226.5	11274.6	11723.6	13263.3	14113.3	13600.1
27.5°	15107.6	15284.0	15652.9	14562.3	12317.0	11130.2	11178.4	11851.9	13760.4	14963.3	14883.1
30°	15861.4	16053.9	15973.7	14738.8	12573.6	11194.4	11066.1	12028.4	13487.8	14963.3	15717.1
32.5°	16599.1	16486.9	16438.8	15027.4	12894.4	11595.3	11274.6	12397.2	13648.2	15203.9	16791.6
35°	17497.3	17336.9	17208.6	15588.8	13423.7	11980.2	11835.9	12878.4	14001.0	15701.0	17657.6
37.5°	18491.6	18491.6	17866.1	16005.7	14049.1	12605.7	12445.3	13568.0	14562.3	16005.7	18844.4
40°	19662.4	19710.5	18603.9	16567.1	14754.8	13600.1	13552.0	14466.1	15107.6	16454.8	19983.1
42.5°	20528.4	20560.5	19245.4	16775.6	15572.7	14979.3	15187.8	15909.5	15733.1	16855.7	20063.3
45°	21121.8	20961.4	19694.4	17369.0	16470.8	17048.2	17112.4	17320.8	16551.0	17096.3	20384.1
47.5°	21410.5	21378.4	19886.9	18058.6	18363.3	19149.2	19518.0	19229.3	17304.8	16839.7	20384.1
50°	21699.2	21426.5	20063.3	19004.8	20207.6	21795.4	21715.2	21186.0	18347.3	17160.5	20079.3
52.5°	21891.6	21651.1	20416.1	19854.8	21971.8	23768.0	24088.8	23110.5	19566.1	17753.9	20223.7
55°	22581.2	22388.8	21474.6	21009.5	24008.6	25853.0	25901.1	24537.9	20849.2	18732.2	21169.9
57.5°	23415.2	23527.5	22934.1	22645.4	25564.3	27376.6	27200.1	25596.4	21939.7	19919.0	22260.5
60°	24008.6	24185.0	24040.7	24072.8	26334.1	27889.8	27488.8	26253.9	22741.6	20817.1	23591.6
62.5°	23687.9	24040.7	24634.1	24505.8	26366.2	27520.9	26959.6	25387.9	22837.9	21987.8	24602.0
65°	22805.8	22837.9	23992.6	24698.2	24922.8	25612.4	24874.7	23575.6	21843.5	22709.5	24457.7
67.5°	20544.4	20801.0	21843.5	23222.8	22276.5	22436.9	22372.8	20496.3	20336.0	22212.4	23351.1
70°	18138.8	18315.2	19453.9	21073.7	18812.4	18058.6	18202.9	16807.6	17465.2	20672.7	21121.8
72.5°	14995.4	15107.6	16406.7	17834.1	15091.6	13744.4	14081.2	12942.5	13872.7	18090.7	17818.0
75°	11322.7	11531.2	12541.6	14225.5	11114.2	10248.2	10585.0	10119.9	10985.9	14899.1	13824.6
77.5°	8051.0	7890.6	9141.6	11130.2	8355.7	7842.5	7874.6	7954.8	8885.0	12557.6	9927.4
80°	5484.9	5533.0	6655.7	8163.2	6559.5	6479.3	6399.1	7040.6	7457.6	9943.4	7217.0
82.5°	3255.7	3255.7	4490.6	5805.7	5180.2	5837.8	5468.9	6046.3	5837.8	7313.2	4731.2
85°	1523.6	1523.6	2309.4	4185.9	4009.5	4811.3	4089.6	4570.8	4314.2	5100.0	2133.0
87.5°	256.6	224.5	465.1	2052.8	1651.9	1876.4	737.7	2437.7	2710.4	3560.4	529.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599005
 CATALOG NUMBER: IFLD-S-SA6C-750-U-SLL

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2
2.5°	11916.1	11803.8	11579.3	11290.6	11050.1	10745.3	10649.1	10440.6	10151.9	10119.9	9991.6
5°	11226.5	10841.6	10360.4	9767.0	9366.1	8949.1	8596.3	8387.8	8147.2	8115.1	8051.0
7.5°	10472.7	9991.6	9189.7	8484.0	7794.4	7136.8	6816.1	6415.1	6142.5	5934.0	5837.8
10°	9767.0	9318.0	8323.6	7361.4	6751.9	6318.9	5934.0	5517.0	5180.2	4923.6	4827.4
12.5°	9301.9	8772.7	7698.2	6784.0	6334.9	5837.8	5404.7	4955.7	4522.7	4185.9	4009.5
15°	9093.4	8596.3	7505.7	6495.3	5837.8	5148.1	4651.0	4201.9	3672.7	3432.1	3351.9
17.5°	9590.6	8852.9	7441.5	6158.5	5228.3	4442.5	3833.0	3351.9	2967.0	2726.4	2630.2
20°	10232.1	9318.0	7553.8	5757.6	4651.0	3768.9	3095.3	2582.1	2325.5	2149.1	2133.0
22.5°	11050.1	10007.6	7730.2	5468.9	4009.5	3031.1	2421.7	2117.0	1940.6	1924.5	1892.5
25°	12509.5	11258.5	8018.9	5084.0	3496.2	2501.9	2068.9	1892.5	1812.3	1764.2	1796.2
27.5°	13760.4	12076.5	8227.4	4843.4	3287.8	2357.6	2004.7	1812.3	1732.1	1716.0	1732.1
30°	14498.2	12830.3	8163.2	4394.4	2870.8	2245.3	2133.0	2068.9	1908.5	1780.2	1780.2
32.5°	15171.8	13311.4	8147.2	3993.4	2453.8	1876.4	1780.2	1732.1	1828.3	1892.5	1844.3
35°	16102.0	14065.2	8099.1	3768.9	2277.4	1732.1	1571.7	1443.4	1379.3	1347.2	1395.3
37.5°	17096.3	14578.4	7970.8	3736.8	2181.1	1651.9	1523.6	1395.3	1331.1	1299.1	1283.0
40°	18186.9	15123.7	7826.5	3576.4	2133.0	1603.8	1475.5	1363.2	1283.0	1234.9	1218.9
42.5°	18892.5	15556.7	7682.1	3496.2	2036.8	1571.7	1427.4	1331.1	1250.9	1186.8	1186.8
45°	19293.5	16069.9	7537.8	3416.1	1924.5	1587.7	1427.4	1299.1	1202.8	1170.8	1138.7
47.5°	19469.9	16454.8	7489.7	3287.8	1828.3	1523.6	1395.3	1267.0	1170.8	1106.6	1090.6
50°	19935.0	17272.7	7666.1	3191.5	1716.0	1459.4	1475.5	1250.9	1154.7	1074.5	1058.5
52.5°	20207.6	17930.3	8051.0	3047.2	1635.9	1379.3	1443.4	1218.9	1106.6	1026.4	1026.4
55°	21202.0	19020.9	8468.0	2934.9	1539.6	1267.0	1331.1	1154.7	1026.4	978.3	978.3
57.5°	22469.0	20175.6	8820.8	2886.8	1475.5	1186.8	1186.8	1122.6	978.3	914.2	898.1
60°	23351.1	21121.8	9029.3	2854.7	1411.3	1106.6	1058.5	1122.6	930.2	866.0	850.0
62.5°	23447.3	20576.5	8820.8	2838.7	1395.3	1026.4	962.3	1074.5	882.1	817.9	785.9
65°	22837.9	19469.9	8243.4	2774.5	1379.3	946.2	898.1	930.2	817.9	769.8	737.7
67.5°	21619.0	17673.7	7409.5	2742.5	1363.2	882.1	817.9	801.9	753.8	705.7	673.6
70°	18780.3	15332.2	6431.2	2598.1	1331.1	834.0	737.7	721.7	673.6	641.5	625.5
72.5°	15765.2	12541.6	5308.5	2405.7	1267.0	753.8	673.6	641.5	625.5	577.4	561.3
75°	12076.5	9654.8	4250.0	2133.0	1106.6	673.6	593.4	561.3	545.3	513.2	497.2
77.5°	8484.0	7184.9	3143.4	1732.1	930.2	609.4	529.2	497.2	481.1	433.0	433.0
80°	5757.6	5035.9	2133.0	1202.8	721.7	497.2	465.1	433.0	400.9	368.9	368.9
82.5°	3576.4	3528.3	1539.6	785.9	529.2	400.9	368.9	368.9	320.8	288.7	288.7
85°	1635.9	2165.1	1074.5	545.3	400.9	304.7	304.7	288.7	256.6	208.5	208.5
87.5°	513.2	721.7	561.3	240.6	224.5	176.4	176.4	160.4	160.4	128.3	128.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599005
 CATALOG NUMBER: IFLD-S-SA6C-750-U-SLL

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2
2.5°	10119.9	10103.8	10103.8	10039.7	10200.1	10200.1	10296.3	10216.1	10264.2	10280.2	10408.5
5°	8034.9	8163.2	8259.5	8451.9	8564.2	8612.3	8612.3	8740.6	8692.5	8788.7	8981.2
7.5°	5885.9	6046.3	6334.9	6575.5	6768.0	6832.1	6816.1	6848.1	6896.3	6784.0	6816.1
10°	4763.2	4651.0	4747.2	4971.7	5148.1	5356.6	5196.3	5180.2	5228.3	5180.2	5276.4
12.5°	3977.4	3849.1	3768.9	3768.9	3897.2	3993.4	3945.3	4025.5	4201.9	4250.0	4362.3
15°	3223.6	3111.3	3047.2	2967.0	3095.3	3127.4	3175.5	3287.8	3416.1	3480.2	3608.5
17.5°	2582.1	2582.1	2582.1	2517.9	2566.1	2614.2	2630.2	2774.5	2790.6	2854.7	2902.8
20°	2117.0	2165.1	2245.3	2277.4	2325.5	2325.5	2293.4	2373.6	2309.4	2357.6	2389.6
22.5°	1908.5	1972.7	2004.7	2020.8	2084.9	2101.0	2020.8	2036.8	2052.8	2004.7	2020.8
25°	1796.2	1828.3	1796.2	1812.3	1828.3	1796.2	1812.3	1844.3	1828.3	1860.4	1844.3
27.5°	1748.1	1716.0	1700.0	1684.0	1684.0	1651.9	1667.9	1667.9	1700.0	1716.0	1716.0
30°	1748.1	1700.0	1635.9	1587.7	1587.7	1539.6	1571.7	1603.8	1619.8	1651.9	1651.9
32.5°	1796.2	1700.0	1587.7	1539.6	1491.5	1459.4	1491.5	1539.6	1603.8	1619.8	1635.9
35°	1427.4	1475.5	1459.4	1395.3	1379.3	1379.3	1363.2	1363.2	1315.1	1315.1	1299.1
37.5°	1283.0	1267.0	1299.1	1315.1	1331.1	1283.0	1283.0	1218.9	1202.8	1218.9	1218.9
40°	1202.8	1202.8	1202.8	1250.9	1267.0	1234.9	1186.8	1154.7	1154.7	1154.7	1170.8
42.5°	1170.8	1138.7	1122.6	1154.7	1202.8	1170.8	1122.6	1106.6	1106.6	1122.6	1122.6
45°	1122.6	1106.6	1090.6	1074.5	1138.7	1090.6	1074.5	1058.5	1058.5	1058.5	1074.5
47.5°	1074.5	1058.5	1026.4	1026.4	1042.5	1026.4	1010.4	1010.4	1010.4	1042.5	1042.5
50°	1042.5	1026.4	994.3	994.3	994.3	994.3	978.3	978.3	978.3	994.3	1010.4
52.5°	994.3	978.3	962.3	946.2	946.2	946.2	946.2	946.2	946.2	962.3	978.3
55°	946.2	930.2	914.2	914.2	930.2	930.2	914.2	930.2	914.2	930.2	946.2
57.5°	898.1	882.1	866.0	882.1	898.1	882.1	882.1	882.1	882.1	882.1	898.1
60°	834.0	834.0	834.0	834.0	866.0	866.0	866.0	866.0	834.0	850.0	866.0
62.5°	801.9	785.9	785.9	801.9	817.9	817.9	834.0	817.9	801.9	817.9	817.9
65°	737.7	737.7	737.7	753.8	753.8	769.8	769.8	769.8	753.8	769.8	769.8
67.5°	689.6	689.6	689.6	689.6	721.7	721.7	721.7	721.7	705.7	705.7	721.7
70°	609.4	625.5	609.4	641.5	673.6	657.6	673.6	673.6	657.6	641.5	673.6
72.5°	561.3	561.3	561.3	561.3	609.4	609.4	609.4	625.5	609.4	593.4	609.4
75°	497.2	497.2	497.2	513.2	545.3	545.3	545.3	545.3	545.3	529.2	529.2
77.5°	433.0	449.1	433.0	449.1	481.1	465.1	481.1	497.2	481.1	465.1	465.1
80°	368.9	368.9	368.9	384.9	400.9	400.9	400.9	417.0	400.9	384.9	384.9
82.5°	288.7	288.7	304.7	304.7	320.8	320.8	320.8	336.8	320.8	304.7	304.7
85°	224.5	224.5	224.5	240.6	240.6	256.6	256.6	272.6	272.6	256.6	256.6
87.5°	144.3	128.3	144.3	144.3	160.4	160.4	144.3	128.3	144.3	128.3	112.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P599005
 CATALOG NUMBER: IFLD-S-SA6C-750-U-SLL

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2	11547.2
2.5°	10536.8	10825.5	11034.0	11178.4	11386.8	11787.8	11948.2	12236.9	12317.0	12365.2
5°	9061.4	9366.1	9815.1	10135.9	10504.8	11258.5	11835.9	12268.9	12461.4	12637.8
7.5°	7104.8	7505.7	7970.8	8387.8	8997.2	9927.4	10681.2	11579.3	11916.1	12092.5
10°	5549.1	5918.0	6431.2	6944.4	7794.4	8580.2	9654.8	10472.7	10937.8	11066.1
12.5°	4683.0	5116.1	5725.5	6351.0	6880.2	7778.3	8868.9	10055.7	10488.7	10568.9
15°	3977.4	4570.8	5196.3	5837.8	6447.2	7233.1	8403.8	9847.2	10488.7	10568.9
17.5°	3287.8	3817.0	4554.7	5244.4	5950.0	7024.6	8484.0	10023.6	10665.1	10905.7
20°	2614.2	3127.4	3704.7	4570.8	5533.0	6671.7	8660.4	10617.0	11467.0	11723.6
22.5°	2165.1	2389.6	2951.0	3784.9	4923.6	6431.2	8836.8	11547.2	12445.3	12541.6
25°	1892.5	2052.8	2405.7	3191.5	4442.5	6270.8	9253.8	12621.8	13776.5	13776.5
27.5°	1764.2	1828.3	2068.9	2774.5	4105.7	6126.4	9670.8	13808.6	14883.1	15107.6
30°	1732.1	1892.5	2020.8	2469.8	3736.8	5725.5	10055.7	14738.8	15845.4	15861.4
32.5°	1700.0	1667.9	1764.2	2149.1	3287.8	5308.5	10376.5	15685.0	16551.0	16599.1
35°	1331.1	1395.3	1555.7	1892.5	2951.0	5003.8	10536.8	16198.2	17449.1	17497.3
37.5°	1250.9	1331.1	1459.4	1748.1	2726.4	4747.2	10585.0	17192.5	18395.4	18491.6
40°	1218.9	1283.0	1379.3	1619.8	2550.0	4426.4	10681.2	18219.0	19790.7	19662.4
42.5°	1154.7	1234.9	1331.1	1555.7	2405.7	4185.9	10697.2	18780.3	20528.4	20528.4
45°	1138.7	1186.8	1299.1	1555.7	2245.3	3977.4	10440.6	19341.6	21378.4	21121.8
47.5°	1074.5	1170.8	1267.0	1507.6	2052.8	3768.9	10135.9	19630.3	21490.7	21410.5
50°	1058.5	1154.7	1315.1	1427.4	1940.6	3672.7	10071.7	20352.0	21715.2	21699.2
52.5°	1026.4	1122.6	1363.2	1363.2	1796.2	3544.4	10376.5	20672.7	21763.3	21891.6
55°	978.3	1122.6	1267.0	1250.9	1667.9	3384.0	10713.3	21506.7	22613.3	22581.2
57.5°	946.2	1090.6	1202.8	1138.7	1523.6	3271.7	11210.4	22308.6	23639.7	23415.2
60°	898.1	1090.6	1074.5	1058.5	1411.3	3175.5	11627.4	22469.0	23864.3	24008.6
62.5°	866.0	1138.7	946.2	978.3	1315.1	3127.4	11451.0	21266.1	23559.6	23687.9
65°	834.0	978.3	866.0	898.1	1283.0	3031.1	10761.4	19822.7	22244.5	22805.8
67.5°	769.8	801.9	801.9	834.0	1250.9	2806.6	9350.0	17224.6	20239.7	20544.4
70°	705.7	721.7	721.7	769.8	1218.9	2550.0	7714.2	14899.1	17561.4	18138.8
72.5°	641.5	641.5	641.5	705.7	1122.6	2341.5	6351.0	11451.0	14594.4	14995.4
75°	561.3	561.3	561.3	625.5	1010.4	2133.0	5003.8	8516.1	10745.3	11322.7
77.5°	497.2	497.2	481.1	561.3	882.1	1732.1	3608.5	6014.2	7569.8	8051.0
80°	417.0	400.9	400.9	449.1	689.6	1250.9	2325.5	4250.0	5276.4	5484.9
82.5°	336.8	320.8	304.7	336.8	497.2	785.9	1443.4	2967.0	3384.0	3255.7
85°	320.8	336.8	272.6	256.6	352.8	513.2	914.2	1828.3	1523.6	1523.6
87.5°	128.3	112.3	112.3	96.2	176.4	192.5	400.9	336.8	256.6	256.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)