

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P598784

Luminaire Tested: **IFLD-L-SA7D-760-U-SLR**

Issue Date: 05/03/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P598784
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/03/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-L-SA7D-760-U-SLR
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLR distribution lens
 Light Source: (112) 5700K CCT, 70 CRI LEDS
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 42440.6 lumens
 Efficiency: N/A
 Efficacy: 100.4 lumens/watt
 Spacing Criteria (0/90/45): 1.13 / 0.53 / 0.8
 Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
 CIE Type: Direct

Input Watts (W): 422.6
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P598784
CATALOG NUMBER: IFLD-L-SA7D-760-U-SLR

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - 90°-270° - · · - 135°-315°

TEST NUMBER: P598784
 CATALOG NUMBER: IFLD-L-SA7D-760-U-SLR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	105	99	94	89	102	97	92	87	92	88	84	88	85	82	85	82	79	77	77	77	77
2	93	83	74	67	90	81	73	66	77	70	64	73	68	63	70	65	61	59	59	59	59
3	83	70	60	52	80	68	59	51	65	57	50	62	55	49	59	53	48	46	46	46	46
4	74	60	49	41	72	59	49	41	56	47	40	53	46	40	51	44	39	36	36	36	36
5	68	52	42	34	65	51	41	34	49	40	33	47	39	33	45	38	32	30	30	30	30
6	62	46	36	28	60	45	35	28	43	34	28	41	34	28	40	33	27	25	25	25	25
7	57	41	31	24	55	40	31	24	39	30	24	37	29	24	36	29	23	21	21	21	21
8	53	37	28	21	51	36	27	21	35	27	21	34	26	21	32	26	20	18	18	18	18
9	49	34	25	19	47	33	24	18	32	24	18	31	23	18	30	23	18	16	16	16	16
10	46	31	22	17	44	31	22	17	29	22	16	28	21	16	28	21	16	14	14	14	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	68231	68231	68231	68231
5°	70219	45661	49882	73768
10°	62297	29014	29305	63753
15°	61141	20578	19490	57184
20°	71085	13017	13119	60915
25°	91417	11177	10861	72016
30°	110787	10593	9931	90152
35°	131125	9333	8983	106860
40°	157556	8857	8233	126245
45°	182310	8784	7974	147173
50°	211703	8920	8028	173793
55°	259075	9164	8163	221421
60°	335996	9174	8600	276938
65°	412441	9271	8819	296442
70°	436429	9780	9220	288624
75°	367377	10339	9231	235564
80°	266906	12106	9357	203618
85°	282882	17543	7676	211615

TEST NUMBER: P598784
 CATALOG NUMBER: IFLD-L-SA7D-760-U-SLR

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	981.2	2.3
10°-20°	2053.4	4.8
20°-30°	2959.2	7.0
30°-40°	4260.0	10.0
40°-50°	6051.1	14.3
50°-60°	8699.8	20.5
60°-70°	10051.1	23.7
70°-80°	5691.1	13.4
80°-90°	1693.7	4.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5993.8	14.1
0°-40°	10253.8	24.2
0°-60°	25004.7	58.9
0°-90°	42440.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	42440.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	12678	12678	12678	12678	12678	
5°	12997	8452	9233	13654	12997	1179
15°	10973	3693	3498	10263	10973	3227
25°	15394	1882	1829	12127	15394	7145
35°	19958	1420	1367	16264	19958	12666
45°	23953	1154	1048	19336	23953	18547
55°	27611	977	870	23598	27611	25006
65°	32387	728	692	23278	32387	31057
75°	17667	497	444	11328	17667	18746
85°	4581	284	124	3427	4581	4562
90°	0	0	0	0	0	

TEST NUMBER: P598784
 CATALOG NUMBER: IFLD-L-SA7D-760-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8
2.5°	13388.0	13370.3	13263.7	12926.4	12571.2	12233.9	11914.3	11576.9	11399.3	11186.3	11097.5
5°	12997.4	12961.9	12660.0	11914.3	11257.3	10547.1	9943.4	9463.9	9073.3	8682.7	8540.6
7.5°	12109.6	12056.3	11701.2	10671.3	9712.5	8789.2	8061.2	7439.8	6924.8	6694.0	6427.7
10°	11399.3	11310.6	10848.9	9712.5	8469.6	7546.3	7066.9	6640.7	6196.8	5824.0	5433.3
12.5°	10955.4	10848.9	10369.5	9037.8	7830.4	7137.9	6640.7	6161.3	5610.9	5149.2	4723.1
15°	10973.2	10848.9	10263.0	8860.2	7670.6	6782.8	6090.3	5433.3	4794.1	4279.2	3799.8
17.5°	11488.1	11328.3	10706.9	9108.8	7546.3	6321.1	5397.8	4545.5	3817.5	3267.1	2876.5
20°	12411.4	12304.9	11594.7	9481.7	7422.0	5824.0	4687.6	3657.7	2894.2	2468.1	2308.3
22.5°	13796.4	13672.1	12908.6	10049.9	7386.5	5380.1	3924.1	2876.5	2326.0	2148.5	2059.7
25°	15394.4	15163.6	14453.4	11008.7	7457.5	4971.7	3302.6	2379.3	2077.5	1953.2	1899.9
27.5°	16779.4	16637.4	15838.3	11914.3	7493.0	4652.1	2876.5	2166.2	1935.4	1828.9	1793.4
30°	17827.0	17773.7	16992.5	12908.6	7404.2	4261.4	2610.1	2077.5	1935.4	1828.9	1722.3
32.5°	18874.6	18892.4	18057.8	13672.1	7280.0	3924.1	2361.5	1846.6	1704.6	1633.6	1651.3
35°	19957.7	20046.5	19336.3	14417.9	7013.6	3799.8	2184.0	1722.3	1598.0	1491.5	1438.2
37.5°	21324.9	21555.8	20863.3	15252.4	6747.3	3693.2	2095.2	1633.6	1509.3	1420.5	1349.5
40°	22425.8	22852.0	22443.6	16033.7	6569.7	3569.0	2024.2	1544.8	1456.0	1349.5	1296.2
42.5°	23242.6	23739.8	23597.7	16637.4	6569.7	3444.7	1953.2	1491.5	1420.5	1296.2	1225.2
45°	23952.8	24467.7	24450.0	17258.8	6711.8	3373.6	1864.4	1491.5	1385.0	1260.7	1189.7
47.5°	24592.0	25107.0	25284.5	18040.1	6942.6	3338.1	1757.8	1456.0	1385.0	1242.9	1136.4
50°	25284.5	25852.7	26385.4	19283.0	7226.7	3249.3	1686.8	1402.7	1402.7	1225.2	1100.9
52.5°	26172.3	26811.5	27788.1	20827.8	7510.8	3089.5	1580.3	1367.2	1402.7	1207.4	1065.4
55°	27610.6	28143.2	29421.7	22674.4	7865.9	2894.2	1491.5	1278.4	1331.7	1154.1	1012.1
57.5°	29226.3	29688.0	30753.4	24094.9	7972.4	2645.6	1367.2	1189.7	1278.4	1100.9	941.1
60°	31215.0	31445.8	31445.8	24503.3	7617.3	2414.8	1278.4	1118.6	1154.1	1047.6	887.8
62.5°	32475.7	32475.7	31445.8	23757.5	6942.6	2219.5	1207.4	1047.6	1012.1	976.6	834.5
65°	32386.9	32244.9	30717.9	21591.3	6161.3	2095.2	1136.4	958.8	905.6	887.8	781.3
67.5°	30895.4	30646.8	28569.4	18537.2	5344.6	2041.9	1065.4	870.0	834.5	799.0	710.2
70°	27734.8	27095.6	24538.8	14915.0	4545.5	2006.4	1047.6	799.0	763.5	728.0	657.0
72.5°	23153.8	22337.0	19158.7	11470.4	3817.5	1882.1	994.3	710.2	692.5	657.0	585.9
75°	17667.2	16157.9	13370.3	8771.5	2965.2	1633.6	852.3	621.5	621.5	603.7	532.7
77.5°	12180.6	11399.3	9321.9	6480.9	2166.2	1260.7	692.5	550.4	550.4	568.2	497.2
80°	8611.7	7883.7	6640.7	4652.1	1367.2	852.3	532.7	461.7	514.9	550.4	461.7
82.5°	6587.5	6054.8	4936.2	3391.4	799.0	585.9	408.4	372.9	443.9	479.4	390.6
85°	4581.0	3941.8	2503.6	2272.8	461.7	355.1	301.9	301.9	390.6	479.4	355.1
87.5°	1296.2	550.4	159.8	674.7	195.3	142.0	106.5	71.0	106.5	106.5	71.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598784
 CATALOG NUMBER: IFLD-L-SA7D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8
2.5°	11008.7	10902.2	10902.2	10866.7	10884.4	10902.2	10884.4	11008.7	11062.0	11133.0	11275.0
5°	8451.8	8593.9	8487.4	8593.9	8735.9	8949.0	9002.3	9162.1	9179.8	9304.1	9233.1
7.5°	6267.9	6250.1	6161.3	6285.6	6676.2	6978.1	7120.1	7208.9	7226.7	7226.7	7137.9
10°	5309.0	5149.2	4989.4	4900.7	4936.2	5255.8	5362.3	5415.6	5380.1	5433.3	5362.3
12.5°	4545.5	4403.5	4172.7	4012.9	3906.3	3995.1	4101.6	4154.9	4190.4	4279.2	4350.2
15°	3693.2	3551.2	3409.1	3320.4	3231.6	3160.6	3249.3	3302.6	3391.4	3462.4	3497.9
17.5°	2805.4	2734.4	2663.4	2716.7	2716.7	2681.2	2716.7	2734.4	2769.9	2823.2	2805.4
20°	2272.8	2255.0	2237.3	2326.0	2397.1	2397.1	2432.6	2379.3	2361.5	2308.3	2290.5
22.5°	2024.2	2024.2	2041.9	2113.0	2184.0	2219.5	2219.5	2130.7	2041.9	2006.4	2024.2
25°	1882.1	1882.1	1935.4	1953.2	1988.7	1988.7	2006.4	1917.6	1864.4	1811.1	1828.9
27.5°	1775.6	1775.6	1793.4	1793.4	1811.1	1811.1	1828.9	1793.4	1722.3	1704.6	1704.6
30°	1704.6	1704.6	1686.8	1686.8	1686.8	1686.8	1704.6	1651.3	1615.8	1598.0	1598.0
32.5°	1633.6	1615.8	1598.0	1598.0	1580.3	1580.3	1598.0	1544.8	1527.0	1527.0	1527.0
35°	1420.5	1402.7	1420.5	1456.0	1456.0	1473.7	1473.7	1456.0	1420.5	1385.0	1367.2
37.5°	1331.7	1313.9	1313.9	1313.9	1349.5	1367.2	1385.0	1349.5	1296.2	1242.9	1242.9
40°	1260.7	1260.7	1242.9	1242.9	1242.9	1278.4	1313.9	1260.7	1189.7	1171.9	1171.9
42.5°	1207.4	1189.7	1171.9	1154.1	1136.4	1189.7	1225.2	1154.1	1118.6	1118.6	1118.6
45°	1154.1	1136.4	1118.6	1100.9	1083.1	1100.9	1136.4	1065.4	1047.6	1047.6	1047.6
47.5°	1100.9	1083.1	1047.6	1029.8	1012.1	1012.1	1047.6	994.3	976.6	994.3	994.3
50°	1065.4	1029.8	994.3	976.6	958.8	958.8	958.8	941.1	941.1	941.1	958.8
52.5°	1029.8	994.3	941.1	923.3	905.6	905.6	905.6	905.6	887.8	905.6	923.3
55°	976.6	941.1	905.6	887.8	870.0	852.3	870.0	852.3	852.3	870.0	870.0
57.5°	905.6	870.0	834.5	834.5	816.8	816.8	834.5	816.8	816.8	834.5	834.5
60°	852.3	816.8	781.3	781.3	763.5	781.3	799.0	781.3	781.3	781.3	799.0
62.5°	781.3	763.5	728.0	728.0	728.0	728.0	745.8	728.0	745.8	745.8	745.8
65°	728.0	692.5	674.7	674.7	674.7	674.7	710.2	674.7	692.5	692.5	692.5
67.5°	674.7	639.2	621.5	621.5	621.5	621.5	657.0	621.5	639.2	657.0	639.2
70°	621.5	585.9	568.2	568.2	568.2	568.2	585.9	568.2	568.2	585.9	585.9
72.5°	550.4	532.7	514.9	514.9	497.2	514.9	532.7	514.9	514.9	514.9	514.9
75°	497.2	479.4	479.4	461.7	461.7	461.7	479.4	443.9	443.9	443.9	443.9
77.5°	461.7	426.1	426.1	426.1	408.4	426.1	408.4	372.9	372.9	372.9	372.9
80°	390.6	355.1	372.9	372.9	355.1	355.1	337.4	301.9	301.9	301.9	301.9
82.5°	319.6	284.1	301.9	301.9	301.9	301.9	266.3	248.6	230.8	213.1	213.1
85°	284.1	230.8	266.3	266.3	248.6	248.6	177.6	177.6	142.0	142.0	124.3
87.5°	53.3	35.5	71.0	88.8	88.8	106.5	71.0	88.8	53.3	35.5	35.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598784
 CATALOG NUMBER: IFLD-L-SA7D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8
2.5°	11257.3	11452.6	11718.9	11914.3	12216.1	12446.9	12802.1	13103.9	13388.0	13512.3	13636.6
5°	9446.2	9570.5	9978.9	10298.5	10777.9	11292.8	11932.0	12624.5	13334.7	13654.4	14027.2
7.5°	7066.9	7297.7	7528.5	7990.2	8576.1	9410.7	10227.4	11257.3	12251.6	12731.0	13370.3
10°	5486.6	5664.2	5930.5	6409.9	6960.3	7652.8	8629.4	9854.6	11044.2	11665.7	12322.7
12.5°	4403.5	4652.1	5007.2	5504.4	6143.6	6853.8	7564.0	8700.4	10085.4	10795.6	11541.4
15°	3569.0	3764.3	4154.9	4776.4	5522.1	6250.1	6995.9	7936.9	9446.2	10263.0	11150.8
17.5°	2841.0	2983.0	3338.1	3959.6	4705.3	5522.1	6374.4	7564.0	9233.1	10227.4	11275.0
20°	2308.3	2414.8	2645.6	3107.3	3817.5	4705.3	5770.7	7208.9	9357.4	10635.8	11914.3
22.5°	2024.2	2059.7	2166.2	2414.8	3000.8	3941.8	5220.3	6907.1	9588.2	11239.5	12961.9
25°	1828.9	1864.4	1899.9	2059.7	2397.1	3284.9	4740.8	6729.5	10085.4	12127.3	14169.3
27.5°	1704.6	1740.1	1757.8	1828.9	2059.7	2805.4	4332.5	6623.0	10760.1	13423.5	15660.8
30°	1598.0	1598.0	1651.3	1757.8	1917.6	2468.1	3977.3	6374.4	11470.4	14506.6	16832.7
32.5°	1509.3	1527.0	1598.0	1651.3	1757.8	2184.0	3622.2	6054.8	12109.6	15394.4	17986.8
35°	1349.5	1349.5	1367.2	1456.0	1598.0	1953.2	3302.6	5735.2	12464.7	16264.5	19016.7
37.5°	1242.9	1260.7	1296.2	1367.2	1491.5	1793.4	3036.3	5380.1	12837.6	17081.3	20224.1
40°	1171.9	1189.7	1225.2	1296.2	1420.5	1651.3	2805.4	5096.0	13228.2	17969.1	21520.3
42.5°	1118.6	1136.4	1171.9	1242.9	1349.5	1615.8	2556.9	4865.1	13459.0	18785.8	22745.4
45°	1065.4	1083.1	1136.4	1207.4	1296.2	1580.3	2414.8	4705.3	13547.8	19336.3	23722.0
47.5°	1012.1	1029.8	1083.1	1189.7	1296.2	1527.0	2361.5	4616.6	13618.8	19957.7	24503.3
50°	958.8	994.3	1065.4	1171.9	1313.9	1456.0	2326.0	4598.8	14027.2	20756.7	25249.0
52.5°	923.3	976.6	1047.6	1171.9	1296.2	1349.5	2308.3	4652.1	14844.0	21946.4	26314.4
55°	887.8	941.1	1012.1	1171.9	1242.9	1260.7	2219.5	4740.8	16086.9	23597.7	27823.6
57.5°	852.3	887.8	976.6	1136.4	1171.9	1189.7	2041.9	4865.1	17329.8	25213.5	29368.4
60°	799.0	834.5	923.3	1136.4	1065.4	1118.6	1811.1	4900.7	18217.6	25728.4	29510.4
62.5°	745.8	781.3	870.0	1171.9	976.6	1047.6	1615.8	4776.4	18395.2	24982.7	28711.4
65°	692.5	728.0	799.0	976.6	905.6	976.6	1491.5	4439.0	17809.3	23278.1	27255.4
67.5°	639.2	674.7	728.0	799.0	816.8	887.8	1438.2	3906.3	16335.5	21165.1	25266.8
70°	568.2	603.7	657.0	710.2	728.0	834.5	1349.5	3391.4	13956.2	18341.9	22834.2
72.5°	514.9	532.7	585.9	621.5	657.0	763.5	1296.2	2965.2	10671.3	14844.0	18626.0
75°	443.9	443.9	497.2	532.7	568.2	674.7	1189.7	2468.1	7528.5	11328.3	13689.9
77.5°	372.9	372.9	408.4	443.9	479.4	585.9	1012.1	2006.4	5220.3	8984.5	9925.6
80°	284.1	284.1	319.6	355.1	390.6	497.2	816.8	1473.7	3231.6	6569.7	7226.7
82.5°	195.3	195.3	248.6	266.3	284.1	390.6	621.5	1012.1	1899.9	4740.8	5167.0
85°	106.5	106.5	142.0	159.8	195.3	284.1	461.7	710.2	1136.4	3426.9	3444.7
87.5°	17.8	17.8	53.3	53.3	88.8	142.0	266.3	390.6	639.2	1899.9	1207.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598784
 CATALOG NUMBER: IFLD-L-SA7D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8	12677.8
2.5°	13867.4	14062.7	14080.5	14080.5	13991.7	14009.5	13760.9	13494.5	13405.8	13388.0
5°	14595.4	15110.3	15252.4	15323.4	15092.6	14737.5	14098.3	13405.8	13050.6	12997.4
7.5°	14453.4	15483.2	16033.7	16104.7	15643.0	14808.5	13689.9	12624.5	12216.1	12109.6
10°	13618.8	15003.8	15998.1	16246.7	15749.6	14684.2	13228.2	11985.3	11488.1	11399.3
12.5°	13032.9	14364.6	15341.2	15678.5	15447.7	14524.4	12997.4	11576.9	11079.7	10955.4
15°	12713.3	13938.4	14577.7	14684.2	14666.4	14275.8	12997.4	11665.7	11115.2	10973.2
17.5°	12979.6	13814.2	13902.9	13654.4	13796.4	13991.7	13281.5	12145.1	11612.4	11488.1
20°	13512.3	13760.9	13334.7	12961.9	13032.9	13654.4	13725.4	13050.6	12624.5	12411.4
22.5°	14630.9	13956.2	12979.6	12464.7	12518.0	13388.0	14311.3	14275.8	13902.9	13796.4
25°	15767.3	14506.6	12873.1	12269.4	12340.4	13334.7	15003.8	15643.0	15447.7	15394.4
27.5°	17028.0	15429.9	12944.1	12180.6	12269.4	13405.8	15483.2	16797.2	16832.7	16779.4
30°	17880.3	15873.8	13157.2	12287.1	12411.4	13583.3	15589.8	17489.6	17809.3	17827.0
32.5°	18590.5	16317.7	13601.1	12464.7	12677.8	13902.9	15873.8	18146.6	18856.9	18874.6
35°	19158.7	16814.9	14151.5	12784.3	13103.9	14435.6	16246.7	18768.1	19833.4	19957.7
37.5°	19886.7	17365.4	14790.7	13476.8	13831.9	15199.1	16903.7	19496.1	20987.6	21324.9
40°	20668.0	17915.8	15714.0	14595.4	15110.3	16335.5	17649.4	20312.8	21964.2	22425.8
42.5°	21538.0	18501.7	16761.6	16104.7	16885.9	17773.7	18501.7	21058.6	22709.9	23242.6
45°	22390.3	19212.0	18288.7	18164.4	19034.4	19478.3	19336.3	21591.3	23420.1	23952.8
47.5°	22994.0	20241.8	20135.3	20881.0	21697.8	21467.0	20312.8	21981.9	24006.1	24592.0
50°	23544.4	21520.3	22461.3	23917.3	24414.5	23633.2	21360.4	22514.6	24627.5	25284.5
52.5°	24361.2	22887.5	24858.4	26669.5	27148.9	25906.0	22496.8	23384.6	25586.4	26172.3
55°	26030.3	24432.2	27362.0	29439.4	29528.2	27983.4	24023.8	24858.4	26935.8	27610.6
57.5°	27894.7	26332.1	29350.6	31729.9	31694.4	30060.9	25746.2	26847.0	28764.7	29226.3
60°	29581.5	28249.8	31516.9	33363.5	33274.7	31570.1	27752.6	29102.1	30859.9	31215.0
62.5°	30575.8	29989.9	32475.7	33878.4	33541.1	32067.3	29457.2	31108.5	32351.4	32475.7
65°	30416.0	30984.2	31357.1	32227.1	31747.7	30682.3	30291.7	32386.9	32511.2	32386.9
67.5°	29208.6	30416.0	28285.3	28374.1	28125.5	27219.9	28995.5	32049.6	31197.3	30895.4
70°	27379.7	27468.5	23651.0	22532.3	22923.0	21680.1	24876.1	29421.7	28107.7	27734.8
72.5°	24343.5	23242.6	17880.3	16743.9	17329.8	16442.0	19957.7	25639.6	24361.2	23153.8
75°	20419.4	18413.0	13618.8	12003.0	12304.9	12269.4	15465.5	21182.9	18874.6	17667.2
77.5°	15820.6	14346.8	10049.9	9428.4	9108.8	9179.8	10795.6	15749.6	13689.9	12180.6
80°	11559.1	10032.1	7777.1	8132.2	7954.7	7528.5	7564.0	10547.1	9517.2	8611.7
82.5°	7990.2	7137.9	6303.4	7120.1	6694.0	6037.0	5895.0	7599.6	7137.9	6587.5
85°	5362.3	5877.2	5007.2	5451.1	4723.1	4350.2	5539.9	6356.6	5131.5	4581.0
87.5°	3497.9	5380.1	3604.5	2734.4	1562.5	2095.2	3391.4	4172.7	2397.1	1296.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)