

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P598777

Luminaire Tested: **IFLD-M-SA4B-760-U-SLR**

Issue Date: 05/03/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P598777
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/03/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-M-SA4B-760-U-SLR
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLR distribution lens
 Light Source: (64) 5700K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 19871.6 lumens
 Efficiency: N/A
 Efficacy: 119.6 lumens/watt
 Spacing Criteria (0/90/45): 1.13 / 0.53 / 0.8
 Luminous Opening: Rectangular (W 2' x L: 0.5' x H: 0')
 CIE Type: Direct

Input Watts (W): 166.1
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P598777
CATALOG NUMBER: IFLD-M-SA4B-760-U-SLR

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°

TEST NUMBER: P598777

CATALOG NUMBER: IFLD-M-SA4B-760-U-SLR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	105	99	94	89	102	97	92	87	92	88	84	88	85	82	85	82	79	85	82	79	77
2	93	83	74	67	90	81	73	66	77	70	64	73	68	63	70	65	61	70	65	61	59
3	83	70	60	52	80	68	59	51	65	57	50	62	55	49	59	53	48	59	53	48	46
4	74	60	49	41	72	59	49	41	56	47	40	53	46	40	51	44	39	51	44	39	36
5	68	52	42	34	65	51	41	34	49	40	33	47	39	33	45	38	32	45	38	32	30
6	62	46	36	28	60	45	35	28	43	34	28	41	34	28	40	33	27	40	33	27	25
7	57	41	31	24	55	40	31	24	39	30	24	37	29	24	36	29	23	36	29	23	21
8	53	37	28	21	51	36	27	21	35	27	21	34	26	21	32	26	20	32	26	20	18
9	49	34	25	19	47	33	24	18	32	24	18	31	23	18	30	23	18	30	23	18	16
10	46	31	22	17	44	31	22	17	29	22	16	28	21	16	28	21	16	28	21	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	63895	63895	63895	63895
5°	65756	42759	46711	69080
10°	58338	27170	27443	59701
15°	57255	19271	18251	53548
20°	66567	12190	12285	57043
25°	85607	10467	10170	67439
30°	103746	9920	9299	84422
35°	122792	8740	8412	100069
40°	147543	8294	7710	118221
45°	170723	8226	7467	137820
50°	198249	8353	7517	162748
55°	242609	8582	7645	207349
60°	314642	8592	8054	259337
65°	386229	8683	8257	277601
70°	408693	9158	8636	270281
75°	344029	9682	8642	220594
80°	249944	11337	8759	190678
85°	264900	16426	7188	198171

TEST NUMBER: P598777
 CATALOG NUMBER: IFLD-M-SA4B-760-U-SLR

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	459.4	2.3
10°-20°	961.5	4.8
20°-30°	1385.6	7.0
30°-40°	1994.6	10.0
40°-50°	2833.3	14.3
50°-60°	4073.4	20.5
60°-70°	4706.1	23.7
70°-80°	2664.7	13.4
80°-90°	793.0	4.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2806.4	14.1
0°-40°	4801.1	24.2
0°-60°	11707.7	58.9
0°-90°	19871.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	19871.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	5936	5936	5936	5936	5936	
5°	6086	3957	4323	6393	6086	552
15°	5138	1729	1638	4805	5138	1511
25°	7208	881	856	5678	7208	3346
35°	9345	665	640	7615	9345	5931
45°	11215	540	490	9054	11215	8684
55°	12928	457	407	11049	12928	11708
65°	15164	341	324	10899	15164	14541
75°	8272	233	208	5304	8272	8777
85°	2145	133	58	1605	2145	2136
90°	0	0	0	0	0	

TEST NUMBER: P598777
 CATALOG NUMBER: IFLD-M-SA4B-760-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0
2.5°	6268.6	6260.3	6210.4	6052.4	5886.1	5728.2	5578.5	5420.6	5337.4	5237.7	5196.1
5°	6085.7	6069.0	5927.7	5578.5	5270.9	4938.4	4655.7	4431.2	4248.3	4065.4	3998.9
7.5°	5670.0	5645.0	5478.8	4996.6	4547.6	4115.3	3774.4	3483.5	3242.4	3134.3	3009.6
10°	5337.4	5295.9	5079.7	4547.6	3965.7	3533.3	3308.9	3109.3	2901.5	2726.9	2544.0
12.5°	5129.6	5079.7	4855.2	4231.7	3666.4	3342.1	3109.3	2884.9	2627.1	2411.0	2211.5
15°	5137.9	5079.7	4805.3	4148.6	3591.5	3175.9	2851.6	2544.0	2244.7	2003.6	1779.1
17.5°	5379.0	5304.2	5013.2	4265.0	3533.3	2959.7	2527.4	2128.3	1787.5	1529.7	1346.8
20°	5811.3	5761.4	5428.9	4439.5	3475.1	2726.9	2194.8	1712.6	1355.1	1155.6	1080.8
22.5°	6459.8	6401.6	6044.1	4705.6	3458.5	2519.1	1837.3	1346.8	1089.1	1006.0	964.4
25°	7208.0	7099.9	6767.4	5154.5	3491.8	2327.8	1546.4	1114.0	972.7	914.5	889.6
27.5°	7856.5	7790.0	7415.9	5578.5	3508.4	2178.2	1346.8	1014.3	906.2	856.3	839.7
30°	8347.0	8322.1	7956.3	6044.1	3466.8	1995.3	1222.1	972.7	906.2	856.3	806.4
32.5°	8837.5	8845.8	8455.1	6401.6	3408.6	1837.3	1105.7	864.6	798.1	764.9	773.2
35°	9344.7	9386.2	9053.7	6750.8	3283.9	1779.1	1022.6	806.4	748.2	698.4	673.4
37.5°	9984.8	10092.9	9768.7	7141.5	3159.2	1729.3	981.0	764.9	706.7	665.1	631.8
40°	10500.3	10699.8	10508.6	7507.3	3076.1	1671.1	947.8	723.3	681.7	631.8	606.9
42.5°	10882.7	11115.5	11049.0	7790.0	3076.1	1612.9	914.5	698.4	665.1	606.9	573.6
45°	11215.2	11456.3	11448.0	8081.0	3142.6	1579.6	872.9	698.4	648.5	590.3	557.0
47.5°	11514.5	11755.6	11838.8	8446.8	3250.7	1563.0	823.1	681.7	648.5	582.0	532.1
50°	11838.8	12104.8	12354.2	9028.7	3383.7	1521.4	789.8	656.8	656.8	573.6	515.5
52.5°	12254.5	12553.8	13011.0	9752.0	3516.7	1446.6	739.9	640.2	656.8	565.3	498.8
55°	12927.9	13177.3	13775.9	10616.7	3683.0	1355.1	698.4	598.6	623.5	540.4	473.9
57.5°	13684.4	13900.6	14399.4	11281.8	3732.9	1238.7	640.2	557.0	598.6	515.5	440.6
60°	14615.6	14723.6	14723.6	11473.0	3566.6	1130.7	598.6	523.8	540.4	490.5	415.7
62.5°	15205.8	15205.8	14723.6	11123.8	3250.7	1039.2	565.3	490.5	473.9	457.3	390.7
65°	15164.3	15097.8	14382.8	10109.5	2884.9	981.0	532.1	448.9	424.0	415.7	365.8
67.5°	14465.9	14349.5	13376.8	8679.6	2502.4	956.1	498.8	407.4	390.7	374.1	332.5
70°	12986.1	12686.8	11489.6	6983.5	2128.3	939.5	490.5	374.1	357.5	340.9	307.6
72.5°	10841.1	10458.7	8970.5	5370.7	1787.5	881.3	465.6	332.5	324.2	307.6	274.4
75°	8272.2	7565.5	6260.3	4107.0	1388.4	764.9	399.1	291.0	291.0	282.7	249.4
77.5°	5703.2	5337.4	4364.7	3034.5	1014.3	590.3	324.2	257.7	257.7	266.0	232.8
80°	4032.2	3691.3	3109.3	2178.2	640.2	399.1	249.4	216.2	241.1	257.7	216.2
82.5°	3084.4	2835.0	2311.2	1587.9	374.1	274.4	191.2	174.6	207.8	224.5	182.9
85°	2144.9	1845.7	1172.2	1064.2	216.2	166.3	141.3	141.3	182.9	224.5	166.3
87.5°	606.9	257.7	74.8	315.9	91.5	66.5	49.9	33.3	49.9	49.9	33.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598777

CATALOG NUMBER: IFLD-M-SA4B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0
2.5°	5154.5	5104.6	5104.6	5088.0	5096.3	5104.6	5096.3	5154.5	5179.5	5212.7	5279.2
5°	3957.3	4023.9	3974.0	4023.9	4090.4	4190.1	4215.1	4289.9	4298.2	4356.4	4323.1
7.5°	2934.8	2926.4	2884.9	2943.1	3126.0	3267.3	3333.8	3375.4	3383.7	3383.7	3342.1
10°	2485.8	2411.0	2336.2	2294.6	2311.2	2460.9	2510.8	2535.7	2519.1	2544.0	2510.8
12.5°	2128.3	2061.8	1953.7	1878.9	1829.0	1870.6	1920.5	1945.4	1962.0	2003.6	2036.9
15°	1729.3	1662.7	1596.2	1554.7	1513.1	1479.8	1521.4	1546.4	1587.9	1621.2	1637.8
17.5°	1313.6	1280.3	1247.1	1272.0	1272.0	1255.4	1272.0	1280.3	1296.9	1321.9	1313.6
20°	1064.2	1055.8	1047.5	1089.1	1122.4	1122.4	1139.0	1114.0	1105.7	1080.8	1072.5
22.5°	947.8	947.8	956.1	989.3	1022.6	1039.2	1039.2	997.6	956.1	939.5	947.8
25°	881.3	881.3	906.2	914.5	931.1	931.1	939.5	897.9	872.9	848.0	856.3
27.5°	831.4	831.4	839.7	839.7	848.0	848.0	856.3	839.7	806.4	798.1	798.1
30°	798.1	798.1	789.8	789.8	789.8	789.8	798.1	773.2	756.6	748.2	748.2
32.5°	764.9	756.6	748.2	748.2	739.9	739.9	748.2	723.3	715.0	715.0	715.0
35°	665.1	656.8	665.1	681.7	681.7	690.0	690.0	681.7	665.1	648.5	640.2
37.5°	623.5	615.2	615.2	615.2	631.8	640.2	648.5	631.8	606.9	582.0	582.0
40°	590.3	590.3	582.0	582.0	582.0	598.6	615.2	590.3	557.0	548.7	548.7
42.5°	565.3	557.0	548.7	540.4	532.1	557.0	573.6	540.4	523.8	523.8	523.8
45°	540.4	532.1	523.8	515.5	507.1	515.5	532.1	498.8	490.5	490.5	490.5
47.5°	515.5	507.1	490.5	482.2	473.9	473.9	490.5	465.6	457.3	465.6	465.6
50°	498.8	482.2	465.6	457.3	448.9	448.9	448.9	440.6	440.6	440.6	448.9
52.5°	482.2	465.6	440.6	432.3	424.0	424.0	424.0	424.0	415.7	424.0	432.3
55°	457.3	440.6	424.0	415.7	407.4	399.1	407.4	399.1	399.1	407.4	407.4
57.5°	424.0	407.4	390.7	390.7	382.4	382.4	390.7	382.4	382.4	390.7	390.7
60°	399.1	382.4	365.8	365.8	357.5	365.8	374.1	365.8	365.8	365.8	374.1
62.5°	365.8	357.5	340.9	340.9	340.9	340.9	349.2	340.9	349.2	349.2	349.2
65°	340.9	324.2	315.9	315.9	315.9	315.9	332.5	315.9	324.2	324.2	324.2
67.5°	315.9	299.3	291.0	291.0	291.0	291.0	307.6	291.0	299.3	307.6	299.3
70°	291.0	274.4	266.0	266.0	266.0	266.0	274.4	266.0	266.0	274.4	274.4
72.5°	257.7	249.4	241.1	241.1	232.8	241.1	249.4	241.1	241.1	241.1	241.1
75°	232.8	224.5	224.5	216.2	216.2	216.2	224.5	207.8	207.8	207.8	207.8
77.5°	216.2	199.5	199.5	199.5	191.2	199.5	191.2	174.6	174.6	174.6	174.6
80°	182.9	166.3	174.6	174.6	166.3	166.3	158.0	141.3	141.3	141.3	141.3
82.5°	149.6	133.0	141.3	141.3	141.3	141.3	124.7	116.4	108.1	99.8	99.8
85°	133.0	108.1	124.7	124.7	116.4	116.4	83.1	83.1	66.5	66.5	58.2
87.5°	24.9	16.6	33.3	41.6	41.6	49.9	33.3	41.6	24.9	16.6	16.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598777
 CATALOG NUMBER: IFLD-M-SA4B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0
2.5°	5270.9	5362.4	5487.1	5578.5	5719.9	5827.9	5994.2	6135.5	6268.6	6326.8	6385.0
5°	4422.9	4481.1	4672.3	4822.0	5046.4	5287.5	5586.8	5911.1	6243.6	6393.3	6567.9
7.5°	3308.9	3416.9	3525.0	3741.2	4015.5	4406.3	4788.7	5270.9	5736.5	5961.0	6260.3
10°	2568.9	2652.1	2776.8	3001.3	3259.0	3583.2	4040.5	4614.1	5171.1	5462.1	5769.7
12.5°	2061.8	2178.2	2344.5	2577.3	2876.6	3209.1	3541.7	4073.7	4722.2	5054.8	5403.9
15°	1671.1	1762.5	1945.4	2236.4	2585.6	2926.4	3275.6	3716.2	4422.9	4805.3	5221.0
17.5°	1330.2	1396.7	1563.0	1854.0	2203.1	2585.6	2984.6	3541.7	4323.1	4788.7	5279.2
20°	1080.8	1130.7	1238.7	1454.9	1787.5	2203.1	2702.0	3375.4	4381.3	4979.9	5578.5
22.5°	947.8	964.4	1014.3	1130.7	1405.0	1845.7	2444.2	3234.0	4489.4	5262.6	6069.0
25°	856.3	872.9	889.6	964.4	1122.4	1538.0	2219.8	3150.9	4722.2	5678.3	6634.4
27.5°	798.1	814.7	823.1	856.3	964.4	1313.6	2028.6	3101.0	5038.1	6285.2	7332.7
30°	748.2	748.2	773.2	823.1	897.9	1155.6	1862.3	2984.6	5370.7	6792.3	7881.4
32.5°	706.7	715.0	748.2	773.2	823.1	1022.6	1696.0	2835.0	5670.0	7208.0	8421.8
35°	631.8	631.8	640.2	681.7	748.2	914.5	1546.4	2685.3	5836.2	7615.4	8904.0
37.5°	582.0	590.3	606.9	640.2	698.4	839.7	1421.7	2519.1	6010.8	7997.8	9469.4
40°	548.7	557.0	573.6	606.9	665.1	773.2	1313.6	2386.0	6193.7	8413.5	10076.3
42.5°	523.8	532.1	548.7	582.0	631.8	756.6	1197.2	2278.0	6301.8	8795.9	10649.9
45°	498.8	507.1	532.1	565.3	606.9	739.9	1130.7	2203.1	6343.4	9053.7	11107.2
47.5°	473.9	482.2	507.1	557.0	606.9	715.0	1105.7	2161.6	6376.6	9344.7	11473.0
50°	448.9	465.6	498.8	548.7	615.2	681.7	1089.1	2153.3	6567.9	9718.8	11822.1
52.5°	432.3	457.3	490.5	548.7	606.9	631.8	1080.8	2178.2	6950.3	10275.8	12321.0
55°	415.7	440.6	473.9	548.7	582.0	590.3	1039.2	2219.8	7532.3	11049.0	13027.6
57.5°	399.1	415.7	457.3	532.1	548.7	557.0	956.1	2278.0	8114.2	11805.5	13750.9
60°	374.1	390.7	432.3	532.1	498.8	523.8	848.0	2294.6	8529.9	12046.6	13817.4
62.5°	349.2	365.8	407.4	548.7	457.3	490.5	756.6	2236.4	8613.0	11697.4	13443.3
65°	324.2	340.9	374.1	457.3	424.0	457.3	698.4	2078.4	8338.7	10899.3	12761.6
67.5°	299.3	315.9	340.9	374.1	382.4	415.7	673.4	1829.0	7648.6	9910.0	11830.5
70°	266.0	282.7	307.6	332.5	340.9	390.7	631.8	1587.9	6534.6	8588.1	10691.5
72.5°	241.1	249.4	274.4	291.0	307.6	357.5	606.9	1388.4	4996.6	6950.3	8721.1
75°	207.8	207.8	232.8	249.4	266.0	315.9	557.0	1155.6	3525.0	5304.2	6409.9
77.5°	174.6	174.6	191.2	207.8	224.5	274.4	473.9	939.5	2444.2	4206.8	4647.4
80°	133.0	133.0	149.6	166.3	182.9	232.8	382.4	690.0	1513.1	3076.1	3383.7
82.5°	91.5	91.5	116.4	124.7	133.0	182.9	291.0	473.9	889.6	2219.8	2419.3
85°	49.9	49.9	66.5	74.8	91.5	133.0	216.2	332.5	532.1	1604.6	1612.9
87.5°	8.3	8.3	24.9	24.9	41.6	66.5	124.7	182.9	299.3	889.6	565.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598777
 CATALOG NUMBER: IFLD-M-SA4B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0	5936.0
2.5°	6493.0	6584.5	6592.8	6592.8	6551.2	6559.5	6443.2	6318.4	6276.9	6268.6
5°	6833.9	7075.0	7141.5	7174.8	7066.7	6900.4	6601.1	6276.9	6110.6	6085.7
7.5°	6767.4	7249.6	7507.3	7540.6	7324.4	6933.7	6409.9	5911.1	5719.9	5670.0
10°	6376.6	7025.1	7490.7	7607.1	7374.3	6875.5	6193.7	5611.8	5379.0	5337.4
12.5°	6102.3	6725.8	7183.1	7341.0	7233.0	6800.6	6085.7	5420.6	5187.8	5129.6
15°	5952.6	6526.3	6825.6	6875.5	6867.2	6684.3	6085.7	5462.1	5204.4	5137.9
17.5°	6077.3	6468.1	6509.7	6393.3	6459.8	6551.2	6218.7	5686.6	5437.2	5379.0
20°	6326.8	6443.2	6243.6	6069.0	6102.3	6393.3	6426.5	6110.6	5911.1	5811.3
22.5°	6850.5	6534.6	6077.3	5836.2	5861.2	6268.6	6700.9	6684.3	6509.7	6459.8
25°	7382.6	6792.3	6027.5	5744.8	5778.1	6243.6	7025.1	7324.4	7233.0	7208.0
27.5°	7972.9	7224.6	6060.7	5703.2	5744.8	6276.9	7249.6	7864.8	7881.4	7856.5
30°	8371.9	7432.5	6160.5	5753.1	5811.3	6360.0	7299.5	8189.0	8338.7	8347.0
32.5°	8704.5	7640.3	6368.3	5836.2	5936.0	6509.7	7432.5	8496.6	8829.2	8837.5
35°	8970.5	7873.1	6626.1	5985.9	6135.5	6759.1	7607.1	8787.6	9286.5	9344.7
37.5°	9311.4	8130.8	6925.4	6310.1	6476.4	7116.6	7914.7	9128.5	9826.8	9984.8
40°	9677.2	8388.6	7357.7	6833.9	7075.0	7648.6	8263.9	9510.9	10284.1	10500.3
42.5°	10084.6	8662.9	7848.2	7540.6	7906.4	8322.1	8662.9	9860.1	10633.3	10882.7
45°	10483.6	8995.5	8563.2	8505.0	8912.3	9120.2	9053.7	10109.5	10965.8	11215.2
47.5°	10766.3	9477.7	9427.8	9777.0	10159.4	10051.3	9510.9	10292.4	11240.2	11514.5
50°	11024.0	10076.3	10516.9	11198.6	11431.4	11065.6	10001.4	10541.8	11531.2	11838.8
52.5°	11406.5	10716.4	11639.2	12487.2	12711.7	12129.8	10533.5	10949.2	11980.1	12254.5
55°	12188.0	11439.7	12811.5	13784.2	13825.8	13102.5	11248.5	11639.2	12612.0	12927.9
57.5°	13060.9	12329.3	13742.6	14856.7	14840.0	14075.2	12054.9	12570.4	13468.3	13684.4
60°	13850.7	13227.2	14756.9	15621.5	15580.0	14781.8	12994.4	13626.2	14449.3	14615.6
62.5°	14316.3	14041.9	15205.8	15862.6	15704.7	15014.6	13792.5	14565.7	15147.6	15205.8
65°	14241.4	14507.5	14682.1	15089.4	14865.0	14366.2	14183.3	15164.3	15222.5	15164.3
67.5°	13676.1	14241.4	13243.8	13285.4	13169.0	12745.0	13576.3	15006.3	14607.3	14465.9
70°	12819.8	12861.4	11073.9	10550.1	10733.0	10151.1	11647.6	13775.9	13160.7	12986.1
72.5°	11398.1	10882.7	8371.9	7839.9	8114.2	7698.5	9344.7	12005.0	11406.5	10841.1
75°	9560.8	8621.4	6376.6	5620.1	5761.4	5744.8	7241.3	9918.3	8837.5	8272.2
77.5°	7407.5	6717.5	4705.6	4414.6	4265.0	4298.2	5054.8	7374.3	6409.9	5703.2
80°	5412.2	4697.3	3641.4	3807.7	3724.6	3525.0	3541.7	4938.4	4456.2	4032.2
82.5°	3741.2	3342.1	2951.4	3333.8	3134.3	2826.7	2760.2	3558.3	3342.1	3084.4
85°	2510.8	2751.8	2344.5	2552.3	2211.5	2036.9	2593.9	2976.3	2402.7	2144.9
87.5°	1637.8	2519.1	1687.7	1280.3	731.6	981.0	1587.9	1953.7	1122.4	606.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)