

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P598762

Luminaire Tested: **IFLD-S-SA2B-760-U-SLR**

Issue Date: 05/03/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P598762
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/03/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-S-SA2B-760-U-SLR
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLR distribution lens
 Light Source: (32) 5700K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 9934.1 lumens
 Efficiency: N/A
 Efficacy: 120.6 lumens/watt
 Spacing Criteria (0/90/45): 1.13 / 0.53 / 0.8
 Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
 CIE Type: Direct

Input Watts (W): 82.4
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P598762
CATALOG NUMBER: IFLD-S-SA2B-760-U-SLR

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - 90°-270° - · · - 135°-315°

TEST NUMBER: P598762
 CATALOG NUMBER: IFLD-S-SA2B-760-U-SLR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	100	100	100	100	100		
	1	105	99	94	89	102	97	92	87	92	88	84	88	85	82	85	82	79	77	77	77	77	77	77		
	2	93	83	74	67	90	81	73	66	77	70	64	73	68	63	70	65	61	59	59	59	59	59	59		
	3	83	70	60	52	80	68	59	51	65	57	50	62	55	49	59	53	48	46	46	46	46	46	46		
	4	74	60	49	41	72	59	49	41	56	47	40	53	46	40	51	44	39	36	36	36	36	36	36		
	5	68	52	42	34	65	51	41	34	49	40	33	47	39	33	45	38	32	30	30	30	30	30	30		
	6	62	46	36	28	60	45	35	28	43	34	28	41	34	28	40	33	27	25	25	25	25	25	25		
	7	57	41	31	24	55	40	31	24	39	30	24	37	29	24	36	29	23	21	21	21	21	21	21		
	8	53	37	28	21	51	36	27	21	35	27	21	34	26	21	32	26	20	18	18	18	18	18	18		
	9	49	34	25	19	47	33	24	18	32	24	18	31	23	18	30	23	18	16	16	16	16	16	16		
	10	46	31	22	17	44	31	22	17	29	22	16	28	21	16	28	21	16	14	14	14	14	14	14		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	63884	63884	63884	63884
5°	65744	42751	46704	69068
10°	58329	27165	27439	59691
15°	57245	19267	18249	53541
20°	66557	12188	12282	57033
25°	85593	10466	10169	67429
30°	103728	9918	9299	84408
35°	122770	8738	8410	100050
40°	147516	8293	7709	118199
45°	170696	8226	7465	137797
50°	198215	8353	7515	162721
55°	242566	8580	7645	207311
60°	314586	8590	8051	259294
65°	386160	8680	8257	277552
70°	408621	9158	8636	270234
75°	343971	9682	8642	220553
80°	249894	11331	8765	190647
85°	264863	16426	7188	198122

TEST NUMBER: P598762
 CATALOG NUMBER: IFLD-S-SA2B-760-U-SLR

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	229.7	2.3
10°-20°	480.6	4.8
20°-30°	692.7	7.0
30°-40°	997.2	10.0
40°-50°	1416.4	14.3
50°-60°	2036.4	20.5
60°-70°	2352.7	23.7
70°-80°	1332.1	13.4
80°-90°	396.4	4.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1403.0	14.1
0°-40°	2400.1	24.2
0°-60°	5852.9	58.9
0°-90°	9934.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9934.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2968	2968	2968	2968	2968	
5°	3042	1978	2161	3196	3042	276
15°	2568	864	819	2402	2568	755
25°	3603	441	428	2839	3603	1673
35°	4672	332	320	3807	4672	2965
45°	5607	270	245	4526	5607	4341
55°	6463	229	204	5524	6463	5853
65°	7581	170	162	5449	7581	7269
75°	4135	116	104	2652	4135	4388
85°	1072	66	29	802	1072	1068
90°	0	0	0	0	0	

TEST NUMBER: P598762
 CATALOG NUMBER: IFLD-S-SA2B-760-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5
2.5°	3133.7	3129.6	3104.7	3025.7	2942.6	2863.6	2788.8	2709.8	2668.3	2618.4	2597.6
5°	3042.3	3034.0	2963.3	2788.8	2635.0	2468.8	2327.5	2215.2	2123.8	2032.4	1999.1
7.5°	2834.5	2822.0	2738.9	2497.9	2273.4	2057.3	1886.9	1741.4	1620.9	1566.9	1504.5
10°	2668.3	2647.5	2539.4	2273.4	1982.5	1766.4	1654.2	1554.4	1450.5	1363.2	1271.8
12.5°	2564.4	2539.4	2427.2	2115.5	1832.9	1670.8	1554.4	1442.2	1313.3	1205.3	1105.5
15°	2568.5	2539.4	2402.3	2073.9	1795.5	1587.7	1425.6	1271.8	1122.2	1001.6	889.4
17.5°	2689.0	2651.6	2506.2	2132.1	1766.4	1479.6	1263.5	1064.0	893.6	764.7	673.3
20°	2905.2	2880.2	2714.0	2219.4	1737.3	1363.2	1097.2	856.2	677.5	577.7	540.3
22.5°	3229.3	3200.2	3021.5	2352.4	1729.0	1259.3	918.5	673.3	544.5	502.9	482.1
25°	3603.4	3549.4	3383.1	2576.8	1745.6	1163.7	773.0	556.9	486.3	457.2	444.7
27.5°	3927.6	3894.3	3707.3	2788.8	1753.9	1088.9	673.3	507.1	453.0	428.1	419.8
30°	4172.8	4160.3	3977.4	3021.5	1733.1	997.5	611.0	486.3	453.0	428.1	403.1
32.5°	4418.0	4422.2	4226.8	3200.2	1704.0	918.5	552.8	432.2	399.0	382.4	386.5
35°	4671.5	4692.3	4526.1	3374.8	1641.7	889.4	511.2	403.1	374.1	349.1	336.6
37.5°	4991.6	5045.6	4883.5	3570.1	1579.3	864.5	490.4	382.4	353.3	332.5	315.9
40°	5249.2	5349.0	5253.4	3753.0	1537.8	835.4	473.8	361.6	340.8	315.9	303.4
42.5°	5440.4	5556.8	5523.5	3894.3	1537.8	806.3	457.2	349.1	332.5	303.4	286.8
45°	5606.7	5727.2	5723.0	4039.8	1571.0	789.7	436.4	349.1	324.2	295.1	278.5
47.5°	5756.3	5876.8	5918.4	4222.7	1625.1	781.4	411.5	340.8	324.2	290.9	266.0
50°	5918.4	6051.4	6176.1	4513.6	1691.6	760.6	394.8	328.3	328.3	286.8	257.7
52.5°	6126.2	6275.8	6504.4	4875.2	1758.1	723.2	369.9	320.0	328.3	282.6	249.4
55°	6462.8	6587.5	6886.8	5307.4	1841.2	677.5	349.1	299.2	311.7	270.2	236.9
57.5°	6841.0	6949.1	7198.5	5639.9	1866.1	619.3	320.0	278.5	299.2	257.7	220.3
60°	7306.5	7360.6	7360.6	5735.5	1783.0	565.2	299.2	261.8	270.2	245.2	207.8
62.5°	7601.6	7601.6	7360.6	5560.9	1625.1	519.5	282.6	245.2	236.9	228.6	195.3
65°	7580.8	7547.6	7190.2	5053.9	1442.2	490.4	266.0	224.4	212.0	207.8	182.9
67.5°	7231.7	7173.5	6687.3	4339.0	1251.0	478.0	249.4	203.7	195.3	187.0	166.2
70°	6491.9	6342.3	5743.8	3491.2	1064.0	469.6	245.2	187.0	178.7	170.4	153.8
72.5°	5419.6	5228.5	4484.5	2684.9	893.6	440.6	232.7	166.2	162.1	153.8	137.2
75°	4135.4	3782.1	3129.6	2053.1	694.1	382.4	199.5	145.5	145.5	141.3	124.7
77.5°	2851.1	2668.3	2182.0	1517.0	507.1	295.1	162.1	128.8	128.8	133.0	116.4
80°	2015.7	1845.3	1554.4	1088.9	320.0	199.5	124.7	108.1	120.5	128.8	108.1
82.5°	1541.9	1417.3	1155.4	793.8	187.0	137.2	95.6	87.3	103.9	112.2	91.4
85°	1072.3	922.7	586.0	532.0	108.1	83.1	70.7	70.7	91.4	112.2	83.1
87.5°	303.4	128.8	37.4	157.9	45.7	33.2	24.9	16.6	24.9	24.9	16.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598762
 CATALOG NUMBER: IFLD-S-SA2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5
2.5°	2576.8	2551.9	2551.9	2543.6	2547.7	2551.9	2547.7	2576.8	2589.3	2605.9	2639.2
5°	1978.3	2011.6	1986.6	2011.6	2044.8	2094.7	2107.2	2144.6	2148.7	2177.8	2161.2
7.5°	1467.1	1463.0	1442.2	1471.3	1562.7	1633.4	1666.6	1687.4	1691.6	1691.6	1670.8
10°	1242.7	1205.3	1167.9	1147.1	1155.4	1230.2	1255.2	1267.6	1259.3	1271.8	1255.2
12.5°	1064.0	1030.7	976.7	939.3	914.4	935.1	960.1	972.5	980.9	1001.6	1018.3
15°	864.5	831.2	798.0	777.2	756.4	739.8	760.6	773.0	793.8	810.5	818.8
17.5°	656.7	640.0	623.4	635.9	635.9	627.6	635.9	640.0	648.4	660.8	656.7
20°	532.0	527.8	523.7	544.5	561.1	561.1	569.4	556.9	552.8	540.3	536.1
22.5°	473.8	473.8	478.0	494.6	511.2	519.5	519.5	498.7	478.0	469.6	473.8
25°	440.6	440.6	453.0	457.2	465.5	465.5	469.6	448.9	436.4	423.9	428.1
27.5°	415.6	415.6	419.8	419.8	423.9	423.9	428.1	419.8	403.1	399.0	399.0
30°	399.0	399.0	394.8	394.8	394.8	394.8	399.0	386.5	378.2	374.1	374.1
32.5°	382.4	378.2	374.1	374.1	369.9	369.9	374.1	361.6	357.4	357.4	357.4
35°	332.5	328.3	332.5	340.8	340.8	345.0	345.0	340.8	332.5	324.2	320.0
37.5°	311.7	307.6	307.6	307.6	315.9	320.0	324.2	315.9	303.4	290.9	290.9
40°	295.1	295.1	290.9	290.9	290.9	299.2	307.6	295.1	278.5	274.3	274.3
42.5°	282.6	278.5	274.3	270.2	266.0	278.5	286.8	270.2	261.8	261.8	261.8
45°	270.2	266.0	261.8	257.7	253.5	257.7	266.0	249.4	245.2	245.2	245.2
47.5°	257.7	253.5	245.2	241.1	236.9	236.9	245.2	232.7	228.6	232.7	232.7
50°	249.4	241.1	232.7	228.6	224.4	224.4	224.4	220.3	220.3	220.3	224.4
52.5°	241.1	232.7	220.3	216.1	212.0	212.0	212.0	212.0	207.8	212.0	216.1
55°	228.6	220.3	212.0	207.8	203.7	199.5	203.7	199.5	199.5	203.7	203.7
57.5°	212.0	203.7	195.3	195.3	191.2	191.2	195.3	191.2	191.2	195.3	195.3
60°	199.5	191.2	182.9	182.9	178.7	182.9	187.0	182.9	182.9	182.9	187.0
62.5°	182.9	178.7	170.4	170.4	170.4	170.4	174.6	170.4	174.6	174.6	174.6
65°	170.4	162.1	157.9	157.9	157.9	157.9	166.2	157.9	162.1	162.1	162.1
67.5°	157.9	149.6	145.5	145.5	145.5	145.5	153.8	145.5	149.6	153.8	149.6
70°	145.5	137.2	133.0	133.0	133.0	133.0	137.2	133.0	133.0	137.2	137.2
72.5°	128.8	124.7	120.5	120.5	116.4	120.5	124.7	120.5	120.5	120.5	120.5
75°	116.4	112.2	112.2	108.1	108.1	108.1	112.2	103.9	103.9	103.9	103.9
77.5°	108.1	99.7	99.7	99.7	95.6	99.7	95.6	87.3	87.3	87.3	87.3
80°	91.4	83.1	87.3	87.3	83.1	83.1	79.0	70.7	70.7	70.7	70.7
82.5°	74.8	66.5	70.7	70.7	70.7	70.7	62.3	58.2	54.0	49.9	49.9
85°	66.5	54.0	62.3	62.3	58.2	58.2	41.6	41.6	33.2	33.2	29.1
87.5°	12.5	8.3	16.6	20.8	20.8	24.9	16.6	20.8	12.5	8.3	8.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598762
 CATALOG NUMBER: IFLD-S-SA2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5
2.5°	2635.0	2680.7	2743.1	2788.8	2859.4	2913.5	2996.6	3067.2	3133.7	3162.8	3191.9
5°	2211.1	2240.2	2335.8	2410.6	2522.8	2643.3	2792.9	2955.0	3121.3	3196.1	3283.4
7.5°	1654.2	1708.2	1762.2	1870.3	2007.4	2202.8	2393.9	2635.0	2867.8	2980.0	3129.6
10°	1284.3	1325.8	1388.2	1500.4	1629.2	1791.3	2019.9	2306.7	2585.1	2730.6	2884.4
12.5°	1030.7	1088.9	1172.0	1288.4	1438.0	1604.3	1770.5	2036.5	2360.7	2526.9	2701.5
15°	835.4	881.1	972.5	1118.0	1292.6	1463.0	1637.5	1857.8	2211.1	2402.3	2610.1
17.5°	665.0	698.2	781.4	926.8	1101.4	1292.6	1492.1	1770.5	2161.2	2393.9	2639.2
20°	540.3	565.2	619.3	727.3	893.6	1101.4	1350.8	1687.4	2190.3	2489.5	2788.8
22.5°	473.8	482.1	507.1	565.2	702.4	922.7	1221.9	1616.7	2244.3	2630.9	3034.0
25°	428.1	436.4	444.7	482.1	561.1	768.9	1109.7	1575.2	2360.7	2838.7	3316.6
27.5°	399.0	407.3	411.5	428.1	482.1	656.7	1014.1	1550.2	2518.6	3142.1	3665.7
30°	374.1	374.1	386.5	411.5	448.9	577.7	931.0	1492.1	2684.9	3395.6	3940.0
32.5°	353.3	357.4	374.1	386.5	411.5	511.2	847.9	1417.3	2834.5	3603.4	4210.2
35°	315.9	315.9	320.0	340.8	374.1	457.2	773.0	1342.4	2917.6	3807.0	4451.2
37.5°	290.9	295.1	303.4	320.0	349.1	419.8	710.7	1259.3	3004.9	3998.2	4733.9
40°	274.3	278.5	286.8	303.4	332.5	386.5	656.7	1192.8	3096.3	4206.0	5037.3
42.5°	261.8	266.0	274.3	290.9	315.9	378.2	598.5	1138.8	3150.4	4397.2	5324.0
45°	249.4	253.5	266.0	282.6	303.4	369.9	565.2	1101.4	3171.2	4526.1	5552.6
47.5°	236.9	241.1	253.5	278.5	303.4	357.4	552.8	1080.6	3187.8	4671.5	5735.5
50°	224.4	232.7	249.4	274.3	307.6	340.8	544.5	1076.4	3283.4	4858.6	5910.1
52.5°	216.1	228.6	245.2	274.3	303.4	315.9	540.3	1088.9	3474.6	5137.0	6159.4
55°	207.8	220.3	236.9	274.3	290.9	295.1	519.5	1109.7	3765.5	5523.5	6512.7
57.5°	199.5	207.8	228.6	266.0	274.3	278.5	478.0	1138.8	4056.4	5901.8	6874.3
60°	187.0	195.3	216.1	266.0	249.4	261.8	423.9	1147.1	4264.2	6022.3	6907.5
62.5°	174.6	182.9	203.7	274.3	228.6	245.2	378.2	1118.0	4305.8	5847.7	6720.5
65°	162.1	170.4	187.0	228.6	212.0	228.6	349.1	1039.0	4168.6	5448.7	6379.7
67.5°	149.6	157.9	170.4	187.0	191.2	207.8	336.6	914.4	3823.7	4954.1	5914.2
70°	133.0	141.3	153.8	166.2	170.4	195.3	315.9	793.8	3266.7	4293.3	5344.8
72.5°	120.5	124.7	137.2	145.5	153.8	178.7	303.4	694.1	2497.9	3474.6	4359.8
75°	103.9	103.9	116.4	124.7	133.0	157.9	278.5	577.7	1762.2	2651.6	3204.4
77.5°	87.3	87.3	95.6	103.9	112.2	137.2	236.9	469.6	1221.9	2103.0	2323.3
80°	66.5	66.5	74.8	83.1	91.4	116.4	191.2	345.0	756.4	1537.8	1691.6
82.5°	45.7	45.7	58.2	62.3	66.5	91.4	145.5	236.9	444.7	1109.7	1209.4
85°	24.9	24.9	33.2	37.4	45.7	66.5	108.1	166.2	266.0	802.1	806.3
87.5°	4.2	4.2	12.5	12.5	20.8	33.2	62.3	91.4	149.6	444.7	282.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598762
 CATALOG NUMBER: IFLD-S-SA2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5	2967.5
2.5°	3246.0	3291.7	3295.8	3295.8	3275.1	3279.2	3221.0	3158.7	3137.9	3133.7
5°	3416.4	3536.9	3570.1	3586.8	3532.7	3449.6	3300.0	3137.9	3054.8	3042.3
7.5°	3383.1	3624.2	3753.0	3769.6	3661.6	3466.2	3204.4	2955.0	2859.4	2834.5
10°	3187.8	3512.0	3744.7	3802.9	3686.5	3437.1	3096.3	2805.4	2689.0	2668.3
12.5°	3050.6	3362.3	3590.9	3669.9	3615.9	3399.7	3042.3	2709.8	2593.4	2564.4
15°	2975.8	3262.6	3412.2	3437.1	3433.0	3341.6	3042.3	2730.6	2601.8	2568.5
17.5°	3038.2	3233.5	3254.3	3196.1	3229.3	3275.1	3108.8	2842.8	2718.1	2689.0
20°	3162.8	3221.0	3121.3	3034.0	3050.6	3196.1	3212.7	3054.8	2955.0	2905.2
22.5°	3424.7	3266.7	3038.2	2917.6	2930.1	3133.7	3349.9	3341.6	3254.3	3229.3
25°	3690.7	3395.6	3013.2	2871.9	2888.5	3121.3	3512.0	3661.6	3615.9	3603.4
27.5°	3985.8	3611.7	3029.8	2851.1	2871.9	3137.9	3624.2	3931.7	3940.0	3927.6
30°	4185.3	3715.6	3079.7	2876.1	2905.2	3179.5	3649.1	4093.8	4168.6	4172.8
32.5°	4351.5	3819.5	3183.6	2917.6	2967.5	3254.3	3715.6	4247.6	4413.8	4418.0
35°	4484.5	3935.9	3312.5	2992.4	3067.2	3379.0	3802.9	4393.1	4642.4	4671.5
37.5°	4654.9	4064.7	3462.1	3154.5	3237.7	3557.7	3956.7	4563.5	4912.6	4991.6
40°	4837.8	4193.6	3678.2	3416.4	3536.9	3823.7	4131.2	4754.6	5141.2	5249.2
42.5°	5041.4	4330.7	3923.4	3769.6	3952.5	4160.3	4330.7	4929.2	5315.7	5440.4
45°	5240.9	4497.0	4280.8	4251.8	4455.4	4559.3	4526.1	5053.9	5482.0	5606.7
47.5°	5382.2	4738.0	4713.1	4887.6	5078.8	5024.8	4754.6	5145.3	5619.1	5756.3
50°	5511.1	5037.3	5257.5	5598.4	5714.7	5531.9	4999.9	5270.0	5764.6	5918.4
52.5°	5702.3	5357.3	5818.6	6242.6	6354.8	6063.8	5265.9	5473.7	5989.0	6126.2
55°	6092.9	5718.9	6404.6	6890.9	6911.7	6550.1	5623.3	5818.6	6304.9	6462.8
57.5°	6529.3	6163.6	6870.1	7427.1	7418.7	7036.4	6026.4	6284.1	6733.0	6841.0
60°	6924.2	6612.5	7377.2	7809.4	7788.6	7389.7	6496.1	6811.9	7223.4	7306.5
62.5°	7156.9	7019.8	7601.6	7930.0	7851.0	7506.0	6895.1	7281.6	7572.5	7601.6
65°	7119.5	7252.5	7339.8	7543.4	7431.2	7181.8	7090.4	7580.8	7609.9	7580.8
67.5°	6836.9	7119.5	6620.8	6641.5	6583.4	6371.4	6787.0	7501.9	7302.4	7231.7
70°	6408.8	6429.6	5536.0	5274.2	5365.6	5074.7	5822.8	6886.8	6579.2	6491.9
72.5°	5698.1	5440.4	4185.3	3919.3	4056.4	3848.6	4671.5	6001.5	5702.3	5419.6
75°	4779.6	4309.9	3187.8	2809.6	2880.2	2871.9	3620.0	4958.3	4418.0	4135.4
77.5°	3703.1	3358.2	2352.4	2206.9	2132.1	2148.7	2526.9	3686.5	3204.4	2851.1
80°	2705.7	2348.2	1820.4	1903.5	1862.0	1762.2	1770.5	2468.8	2227.7	2015.7
82.5°	1870.3	1670.8	1475.4	1666.6	1566.9	1413.1	1379.8	1778.8	1670.8	1541.9
85°	1255.2	1375.7	1172.0	1275.9	1105.5	1018.3	1296.7	1487.9	1201.1	1072.3
87.5°	818.8	1259.3	843.7	640.0	365.7	490.4	793.8	976.7	561.1	303.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)