

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P598767

Luminaire Tested: **IFLD-S-SA3B-760-U-SLR**

Issue Date: 05/03/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P598767
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/03/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-S-SA3B-760-U-SLR
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLR distribution lens
 Light Source: (48) 5700K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 14804.8 lumens
 Efficiency: N/A
 Efficacy: 121.0 lumens/watt
 Spacing Criteria (0/90/45): 1.13 / 0.53 / 0.8
 Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
 CIE Type: Direct

Input Watts (W): 122.4
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P598767
CATALOG NUMBER: IFLD-S-SA3B-760-U-SLR

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - 90°-270° - · · - 135°-315°

TEST NUMBER: P598767

CATALOG NUMBER: IFLD-S-SA3B-760-U-SLR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	105	99	94	89	102	97	92	87	92	88	84	88	85	82	85	82	79	77			77	
2	93	83	74	67	90	81	73	66	77	70	64	73	68	63	70	65	61	59			59	
3	83	70	60	52	80	68	59	51	65	57	50	62	55	49	59	53	48	46			46	
4	74	60	49	41	72	59	49	41	56	47	40	53	46	40	51	44	39	36			36	
5	68	52	42	34	65	51	41	34	49	40	33	47	39	33	45	38	32	30			30	
6	62	46	36	28	60	45	35	28	43	34	28	41	34	28	40	33	27	25			25	
7	57	41	31	24	55	40	31	24	39	30	24	37	29	24	36	29	23	21			21	
8	53	37	28	21	51	36	27	21	35	27	21	34	26	21	32	26	20	18			18	
9	49	34	25	19	47	33	24	18	32	24	18	31	23	18	30	23	18	16			16	
10	46	31	22	17	44	31	22	17	29	22	16	28	21	16	28	21	16	14			14	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	63471	63471	63471	63471
5°	65319	42475	46401	68621
10°	57951	26990	27261	59305
15°	56874	19142	18130	53194
20°	66124	12108	12203	56666
25°	85039	10398	10103	66991
30°	103057	9854	9239	83862
35°	121977	8681	8355	99404
40°	146562	8240	7659	117435
45°	169591	8171	7416	136905
50°	196931	8297	7469	161667
55°	240997	8525	7594	205972
60°	312553	8534	8000	257616
65°	383664	8626	8205	275758
70°	405979	9097	8577	268486
75°	341742	9615	8584	219127
80°	248278	11265	8703	189407
85°	263142	16319	7147	196846

TEST NUMBER: P598767
 CATALOG NUMBER: IFLD-S-SA3B-760-U-SLR

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	342.3	2.3
10°-20°	716.3	4.8
20°-30°	1032.3	7.0
30°-40°	1486.1	10.0
40°-50°	2110.8	14.3
50°-60°	3034.8	20.5
60°-70°	3506.2	23.7
70°-80°	1985.3	13.4
80°-90°	590.8	4.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2090.8	14.1
0°-40°	3576.9	24.2
0°-60°	8722.5	58.9
0°-90°	14804.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	14804.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	4422	4422	4422	4422	4422	
5°	4534	2948	3221	4763	4534	411
15°	3828	1288	1220	3580	3828	1126
25°	5370	657	638	4230	5370	2493
35°	6962	496	477	5674	6962	4418
45°	8356	403	365	6745	8356	6470
55°	9632	341	304	8232	9632	8723
65°	11298	254	242	8120	11298	10834
75°	6163	173	155	3952	6163	6539
85°	1598	99	43	1195	1598	1591
90°	0	0	0	0	0	

TEST NUMBER: P598767
 CATALOG NUMBER: IFLD-S-SA3B-760-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5
2.5°	4670.2	4664.0	4626.9	4509.2	4385.3	4267.6	4156.1	4038.4	3976.5	3902.2	3871.2
5°	4533.9	4521.6	4416.3	4156.1	3926.9	3679.2	3468.6	3301.4	3165.1	3028.8	2979.3
7.5°	4224.2	4205.7	4081.8	3722.5	3388.1	3066.0	2812.0	2595.3	2415.6	2335.1	2242.2
10°	3976.5	3945.5	3784.5	3388.1	2954.5	2632.4	2465.2	2316.5	2161.7	2031.6	1895.3
12.5°	3821.6	3784.5	3617.2	3152.7	2731.5	2490.0	2316.5	2149.3	1957.3	1796.2	1647.6
15°	3827.8	3784.5	3580.1	3090.8	2675.8	2366.1	2124.5	1895.3	1672.4	1492.7	1325.5
17.5°	4007.5	3951.7	3734.9	3177.5	2632.4	2205.0	1883.0	1585.6	1331.7	1139.7	1003.4
20°	4329.5	4292.4	4044.6	3307.6	2589.1	2031.6	1635.2	1275.9	1009.6	861.0	805.2
22.5°	4812.7	4769.3	4503.0	3505.8	2576.7	1876.8	1368.9	1003.4	811.4	749.5	718.5
25°	5370.1	5289.6	5041.8	3840.2	2601.4	1734.3	1152.1	830.0	724.7	681.3	662.7
27.5°	5853.2	5803.7	5525.0	4156.1	2613.8	1622.8	1003.4	755.7	675.1	638.0	625.6
30°	6218.7	6200.1	5927.6	4503.0	2582.9	1486.5	910.5	724.7	675.1	638.0	600.8
32.5°	6584.1	6590.3	6299.2	4769.3	2539.5	1368.9	823.8	644.2	594.6	569.8	576.0
35°	6962.0	6992.9	6745.2	5029.5	2446.6	1325.5	761.9	600.8	557.5	520.3	501.7
37.5°	7438.9	7519.4	7277.8	5320.6	2353.7	1288.3	730.9	569.8	526.5	495.5	470.7
40°	7822.9	7971.6	7829.1	5593.1	2291.7	1245.0	706.1	538.9	507.9	470.7	452.2
42.5°	8107.8	8281.3	8231.7	5803.7	2291.7	1201.6	681.3	520.3	495.5	452.2	427.4
45°	8355.6	8535.2	8529.0	6020.5	2341.3	1176.8	650.4	520.3	483.1	439.8	415.0
47.5°	8578.6	8758.2	8820.1	6293.0	2421.8	1164.5	613.2	507.9	483.1	433.6	396.4
50°	8820.1	9018.3	9204.2	6726.6	2520.9	1133.5	588.4	489.3	489.3	427.4	384.0
52.5°	9129.8	9352.8	9693.5	7265.5	2620.0	1077.7	551.3	476.9	489.3	421.2	371.6
55°	9631.5	9817.4	10263.3	7909.6	2743.9	1009.6	520.3	446.0	464.5	402.6	353.1
57.5°	10195.2	10356.2	10727.9	8405.1	2781.1	922.9	476.9	415.0	446.0	384.0	328.3
60°	10888.9	10969.4	10969.4	8547.6	2657.2	842.4	446.0	390.2	402.6	365.4	309.7
62.5°	11328.7	11328.7	10969.4	8287.5	2421.8	774.2	421.2	365.4	353.1	340.7	291.1
65°	11297.7	11248.1	10715.5	7531.8	2149.3	730.9	396.4	334.5	315.9	309.7	272.5
67.5°	10777.4	10690.7	9966.0	6466.4	1864.4	712.3	371.6	303.5	291.1	278.7	247.8
70°	9674.9	9451.9	8560.0	5202.9	1585.6	699.9	365.4	278.7	266.3	254.0	229.2
72.5°	8076.9	7791.9	6683.2	4001.3	1331.7	656.6	346.9	247.8	241.6	229.2	204.4
75°	6162.9	5636.5	4664.0	3059.8	1034.4	569.8	297.3	216.8	216.8	210.6	185.8
77.5°	4249.0	3976.5	3251.8	2260.8	755.7	439.8	241.6	192.0	192.0	198.2	173.4
80°	3004.0	2750.1	2316.5	1622.8	476.9	297.3	185.8	161.0	179.6	192.0	161.0
82.5°	2297.9	2112.1	1721.9	1183.0	278.7	204.4	142.5	130.1	154.8	167.2	136.3
85°	1598.0	1375.0	873.3	792.8	161.0	123.9	105.3	105.3	136.3	167.2	123.9
87.5°	452.2	192.0	55.7	235.4	68.1	49.6	37.2	24.8	37.2	37.2	24.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598767
 CATALOG NUMBER: IFLD-S-SA3B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5
2.5°	3840.2	3803.1	3803.1	3790.7	3796.9	3803.1	3796.9	3840.2	3858.8	3883.6	3933.1
5°	2948.3	2997.9	2960.7	2997.9	3047.4	3121.7	3140.3	3196.1	3202.3	3245.6	3220.8
7.5°	2186.5	2180.3	2149.3	2192.6	2328.9	2434.2	2483.8	2514.7	2520.9	2520.9	2490.0
10°	1852.0	1796.2	1740.5	1709.5	1721.9	1833.4	1870.6	1889.1	1876.8	1895.3	1870.6
12.5°	1585.6	1536.1	1455.6	1399.8	1362.7	1393.6	1430.8	1449.4	1461.8	1492.7	1517.5
15°	1288.3	1238.8	1189.2	1158.3	1127.3	1102.5	1133.5	1152.1	1183.0	1207.8	1220.2
17.5°	978.6	953.9	929.1	947.7	947.7	935.3	947.7	953.9	966.3	984.8	978.6
20°	792.8	786.6	780.4	811.4	836.2	836.2	848.6	830.0	823.8	805.2	799.0
22.5°	706.1	706.1	712.3	737.1	761.9	774.2	774.2	743.3	712.3	699.9	706.1
25°	656.6	656.6	675.1	681.3	693.7	693.7	699.9	668.9	650.4	631.8	638.0
27.5°	619.4	619.4	625.6	625.6	631.8	631.8	638.0	625.6	600.8	594.6	594.6
30°	594.6	594.6	588.4	588.4	588.4	588.4	594.6	576.0	563.6	557.5	557.5
32.5°	569.8	563.6	557.5	557.5	551.3	551.3	557.5	538.9	532.7	532.7	532.7
35°	495.5	489.3	495.5	507.9	507.9	514.1	514.1	507.9	495.5	483.1	476.9
37.5°	464.5	458.3	458.3	458.3	470.7	476.9	483.1	470.7	452.2	433.6	433.6
40°	439.8	439.8	433.6	433.6	433.6	446.0	458.3	439.8	415.0	408.8	408.8
42.5°	421.2	415.0	408.8	402.6	396.4	415.0	427.4	402.6	390.2	390.2	390.2
45°	402.6	396.4	390.2	384.0	377.8	384.0	396.4	371.6	365.4	365.4	365.4
47.5°	384.0	377.8	365.4	359.2	353.1	353.1	365.4	346.9	340.7	346.9	346.9
50°	371.6	359.2	346.9	340.7	334.5	334.5	334.5	328.3	328.3	328.3	334.5
52.5°	359.2	346.9	328.3	322.1	315.9	315.9	315.9	315.9	309.7	315.9	322.1
55°	340.7	328.3	315.9	309.7	303.5	297.3	303.5	297.3	297.3	303.5	303.5
57.5°	315.9	303.5	291.1	291.1	284.9	284.9	291.1	284.9	284.9	291.1	291.1
60°	297.3	284.9	272.5	272.5	266.3	272.5	278.7	272.5	272.5	272.5	278.7
62.5°	272.5	266.3	254.0	254.0	254.0	254.0	260.1	254.0	260.1	260.1	260.1
65°	254.0	241.6	235.4	235.4	235.4	235.4	247.8	235.4	241.6	241.6	241.6
67.5°	235.4	223.0	216.8	216.8	216.8	216.8	229.2	216.8	223.0	229.2	223.0
70°	216.8	204.4	198.2	198.2	198.2	198.2	204.4	198.2	198.2	204.4	204.4
72.5°	192.0	185.8	179.6	179.6	173.4	179.6	185.8	179.6	179.6	179.6	179.6
75°	173.4	167.2	167.2	161.0	161.0	161.0	167.2	154.8	154.8	154.8	154.8
77.5°	161.0	148.7	148.7	148.7	142.5	148.7	142.5	130.1	130.1	130.1	130.1
80°	136.3	123.9	130.1	130.1	123.9	123.9	117.7	105.3	105.3	105.3	105.3
82.5°	111.5	99.1	105.3	105.3	105.3	105.3	92.9	86.7	80.5	74.3	74.3
85°	99.1	80.5	92.9	92.9	86.7	86.7	61.9	61.9	49.6	49.6	43.4
87.5°	18.6	12.4	24.8	31.0	31.0	37.2	24.8	31.0	18.6	12.4	12.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598767
 CATALOG NUMBER: IFLD-S-SA3B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5
2.5°	3926.9	3995.1	4088.0	4156.1	4261.4	4341.9	4465.8	4571.1	4670.2	4713.6	4756.9
5°	3295.2	3338.5	3481.0	3592.5	3759.7	3939.3	4162.3	4403.9	4651.6	4763.1	4893.2
7.5°	2465.2	2545.7	2626.2	2787.3	2991.7	3282.8	3567.7	3926.9	4273.8	4441.0	4664.0
10°	1913.9	1975.9	2068.8	2236.0	2428.0	2669.6	3010.2	3437.6	3852.6	4069.4	4298.6
12.5°	1536.1	1622.8	1746.7	1920.1	2143.1	2390.9	2638.6	3035.0	3518.1	3765.9	4026.0
15°	1245.0	1313.1	1449.4	1666.2	1926.3	2180.3	2440.4	2768.7	3295.2	3580.1	3889.8
17.5°	991.0	1040.6	1164.5	1381.2	1641.4	1926.3	2223.6	2638.6	3220.8	3567.7	3933.1
20°	805.2	842.4	922.9	1083.9	1331.7	1641.4	2013.0	2514.7	3264.2	3710.2	4156.1
22.5°	706.1	718.5	755.7	842.4	1046.8	1375.0	1821.0	2409.4	3344.7	3920.7	4521.6
25°	638.0	650.4	662.7	718.5	836.2	1145.9	1653.8	2347.5	3518.1	4230.4	4942.7
27.5°	594.6	607.0	613.2	638.0	718.5	978.6	1511.3	2310.3	3753.5	4682.6	5463.0
30°	557.5	557.5	576.0	613.2	668.9	861.0	1387.4	2223.6	4001.3	5060.4	5871.8
32.5°	526.5	532.7	557.5	576.0	613.2	761.9	1263.6	2112.1	4224.2	5370.1	6274.4
35°	470.7	470.7	476.9	507.9	557.5	681.3	1152.1	2000.6	4348.1	5673.6	6633.7
37.5°	433.6	439.8	452.2	476.9	520.3	625.6	1059.2	1876.8	4478.2	5958.5	7054.9
40°	408.8	415.0	427.4	452.2	495.5	576.0	978.6	1777.7	4614.5	6268.2	7507.0
42.5°	390.2	396.4	408.8	433.6	470.7	563.6	891.9	1697.1	4695.0	6553.2	7934.4
45°	371.6	377.8	396.4	421.2	452.2	551.3	842.4	1641.4	4726.0	6745.2	8275.1
47.5°	353.1	359.2	377.8	415.0	452.2	532.7	823.8	1610.4	4750.7	6962.0	8547.6
50°	334.5	346.9	371.6	408.8	458.3	507.9	811.4	1604.2	4893.2	7240.7	8807.7
52.5°	322.1	340.7	365.4	408.8	452.2	470.7	805.2	1622.8	5178.1	7655.7	9179.4
55°	309.7	328.3	353.1	408.8	433.6	439.8	774.2	1653.8	5611.7	8231.7	9705.9
57.5°	297.3	309.7	340.7	396.4	408.8	415.0	712.3	1697.1	6045.3	8795.4	10244.7
60°	278.7	291.1	322.1	396.4	371.6	390.2	631.8	1709.5	6355.0	8975.0	10294.3
62.5°	260.1	272.5	303.5	408.8	340.7	365.4	563.6	1666.2	6416.9	8714.8	10015.6
65°	241.6	254.0	278.7	340.7	315.9	340.7	520.3	1548.5	6212.5	8120.2	9507.7
67.5°	223.0	235.4	254.0	278.7	284.9	309.7	501.7	1362.7	5698.4	7383.1	8813.9
70°	198.2	210.6	229.2	247.8	254.0	291.1	470.7	1183.0	4868.4	6398.3	7965.4
72.5°	179.6	185.8	204.4	216.8	229.2	266.3	452.2	1034.4	3722.5	5178.1	6497.4
75°	154.8	154.8	173.4	185.8	198.2	235.4	415.0	861.0	2626.2	3951.7	4775.5
77.5°	130.1	130.1	142.5	154.8	167.2	204.4	353.1	699.9	1821.0	3134.1	3462.4
80°	99.1	99.1	111.5	123.9	136.3	173.4	284.9	514.1	1127.3	2291.7	2520.9
82.5°	68.1	68.1	86.7	92.9	99.1	136.3	216.8	353.1	662.7	1653.8	1802.4
85°	37.2	37.2	49.6	55.7	68.1	99.1	161.0	247.8	396.4	1195.4	1201.6
87.5°	6.2	6.2	18.6	18.6	31.0	49.6	92.9	136.3	223.0	662.7	421.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598767
 CATALOG NUMBER: IFLD-S-SA3B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5	4422.5
2.5°	4837.4	4905.6	4911.8	4911.8	4880.8	4887.0	4800.3	4707.4	4676.4	4670.2
5°	5091.4	5271.0	5320.6	5345.3	5264.8	5140.9	4918.0	4676.4	4552.5	4533.9
7.5°	5041.8	5401.1	5593.1	5617.9	5456.8	5165.7	4775.5	4403.9	4261.4	4224.2
10°	4750.7	5233.9	5580.7	5667.4	5494.0	5122.4	4614.5	4180.9	4007.5	3976.5
12.5°	4546.3	5010.9	5351.5	5469.2	5388.7	5066.6	4533.9	4038.4	3865.0	3821.6
15°	4434.8	4862.2	5085.2	5122.4	5116.2	4979.9	4533.9	4069.4	3877.4	3827.8
17.5°	4527.8	4818.9	4849.8	4763.1	4812.7	4880.8	4633.0	4236.6	4050.8	4007.5
20°	4713.6	4800.3	4651.6	4521.6	4546.3	4763.1	4787.9	4552.5	4403.9	4329.5
22.5°	5103.8	4868.4	4527.8	4348.1	4366.7	4670.2	4992.3	4979.9	4849.8	4812.7
25°	5500.2	5060.4	4490.6	4280.0	4304.8	4651.6	5233.9	5456.8	5388.7	5370.1
27.5°	5940.0	5382.5	4515.4	4249.0	4280.0	4676.4	5401.1	5859.4	5871.8	5853.2
30°	6237.3	5537.4	4589.7	4286.2	4329.5	4738.3	5438.3	6101.0	6212.5	6218.7
32.5°	6485.0	5692.2	4744.5	4348.1	4422.5	4849.8	5537.4	6330.2	6577.9	6584.1
35°	6683.2	5865.6	4936.6	4459.6	4571.1	5035.7	5667.4	6547.0	6918.6	6962.0
37.5°	6937.2	6057.6	5159.5	4701.2	4825.1	5302.0	5896.6	6800.9	7321.2	7438.9
40°	7209.7	6249.7	5481.6	5091.4	5271.0	5698.4	6156.8	7085.8	7661.9	7822.9
42.5°	7513.2	6454.1	5847.1	5617.9	5890.4	6200.1	6454.1	7346.0	7922.0	8107.8
45°	7810.5	6701.8	6379.7	6336.4	6639.9	6794.7	6745.2	7531.8	8169.8	8355.6
47.5°	8021.1	7061.1	7023.9	7284.0	7569.0	7488.4	7085.8	7668.1	8374.2	8578.6
50°	8213.1	7507.0	7835.3	8343.2	8516.6	8244.1	7451.3	7853.9	8591.0	8820.1
52.5°	8498.1	7984.0	8671.5	9303.3	9470.5	9036.9	7847.7	8157.4	8925.4	9129.8
55°	9080.3	8522.8	9544.8	10269.5	10300.5	9761.6	8380.4	8671.5	9396.2	9631.5
57.5°	9730.6	9185.6	10238.5	11068.5	11056.1	10486.3	8981.2	9365.2	10034.1	10195.2
60°	10319.1	9854.5	10994.2	11638.4	11607.4	11012.8	9681.1	10151.8	10765.0	10888.9
62.5°	10665.9	10461.5	11328.7	11818.0	11700.3	11186.2	10275.7	10851.7	11285.3	11328.7
65°	10610.2	10808.4	10938.5	11242.0	11074.7	10703.1	10566.8	11297.7	11341.1	11297.7
67.5°	10189.0	10610.2	9866.9	9897.9	9811.2	9495.3	10114.7	11180.0	10882.7	10777.4
70°	9551.0	9582.0	8250.3	7860.1	7996.3	7562.8	8677.7	10263.3	9805.0	9674.9
72.5°	8491.9	8107.8	6237.3	5840.9	6045.3	5735.6	6962.0	8944.0	8498.1	8076.9
75°	7123.0	6423.1	4750.7	4187.1	4292.4	4280.0	5394.9	7389.3	6584.1	6162.9
77.5°	5518.8	5004.7	3505.8	3289.0	3177.5	3202.3	3765.9	5494.0	4775.5	4249.0
80°	4032.2	3499.6	2712.9	2836.8	2774.9	2626.2	2638.6	3679.2	3319.9	3004.0
82.5°	2787.3	2490.0	2198.8	2483.8	2335.1	2105.9	2056.4	2651.0	2490.0	2297.9
85°	1870.6	2050.2	1746.7	1901.5	1647.6	1517.5	1932.5	2217.4	1790.0	1598.0
87.5°	1220.2	1876.8	1257.4	953.9	545.1	730.9	1183.0	1455.6	836.2	452.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)