

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P147490

Luminaire Tested: **TMU-E06-LED-E-U-5MQ**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P147490
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33674)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: TMU-E06-LED-E-U-5MQ
Description: TALON MEDIUM LED AREA LUMINAIRE
(6) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE MEDIUM
Light Source: (126) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 19342.6 lumens
Efficiency: N/A
Efficacy: 128.5 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type V - Short - Full Cutoff
BUG Rating: B4 - U0 - G2

Input Watts (W): 150.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P147490

CATALOG NUMBER: TMU-E06-LED-E-U-5MQ

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 25 foot mounting height. Maximum calculated value = 2.3 fc
 Type V - Short - Full Cutoff

REPORT NUMBER: P147490

CATALOG NUMBER: TMU-E06-LED-E-U-5MQ

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 62.5-Deg Vertical



REPORT NUMBER: P147490

CATALOG NUMBER: TMU-E06-LED-E-U-5MQ

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	9671.3	0.0	9671.3
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	9671.3	0.0	9671.3
	% Fixture	50.0	0.0	50.0
Total	Lumens	19342.6	0.0	19342.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.7	0.7
10°-20°	435.0	2.2
20°-30°	841.0	4.3
30°-40°	1628.3	8.4
40°-50°	2940.1	15.2
50°-60°	5112.4	26.4
60°-70°	5803.9	30.0
70°-80°	2250.2	11.6
80°-90°	203.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	19342.6	100.0
0°-180°	19342.6	100.0

Coefficient of Utilization



REPORT NUMBER: P147490


CATALOG NUMBER: TMU-E06-LED-E-U-5MQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	702.3	3.6			
FM	(30°-60°)	4840.4	25.0			
FH	(60°-80°)	4027.0	20.8			G2/5000
FVH	(80°-90°)	101.5	0.5			G2/225
BL	(0°-30°)	702.3	3.6	B2/1000		
BM	(30°-60°)	4840.4	25.0	B3/5000		
BH	(60°-80°)	4027.0	20.8	B4/5000		G2/5000
BVH	(80°-90°)	101.5	0.5			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G2

Type V Short





REPORT NUMBER: P147490

CATALOG NUMBER: TMU-E06-LED-E-U-5MQ

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1284	1284	1284	1284	1284	1284	1284	1284	1284	1284	1284
2.5°	1292	1296	1295	1293	1293	1293	1292	1289	1288	1290	1292
5°	1322	1322	1322	1322	1320	1320	1318	1316	1317	1315	1314
7.5°	1368	1365	1365	1364	1364	1362	1359	1355	1356	1355	1354
10°	1422	1423	1420	1423	1418	1417	1413	1411	1410	1407	1407
12.5°	1487	1484	1484	1482	1480	1478	1472	1471	1467	1465	1462
15°	1548	1547	1543	1539	1538	1536	1529	1525	1524	1519	1515
17.5°	1609	1607	1602	1600	1596	1593	1587	1581	1578	1576	1571
20°	1674	1672	1667	1663	1658	1654	1645	1640	1637	1634	1630
22.5°	1755	1751	1743	1736	1725	1721	1709	1702	1697	1693	1691
25°	1843	1844	1833	1824	1811	1800	1785	1777	1772	1768	1767
27.5°	1953	1954	1944	1931	1911	1899	1879	1869	1866	1862	1861
30°	2127	2118	2101	2080	2062	2036	2007	1997	1987	1984	1984
32.5°	2447	2442	2428	2376	2352	2298	2247	2218	2185	2169	2159
35°	2671	2669	2658	2640	2625	2614	2584	2579	2573	2573	2581
37.5°	2836	2824	2822	2825	2821	2823	2847	2880	2908	2922	2920
40°	3080	3063	3073	3066	3057	3055	3063	3076	3089	3089	3086
42.5°	3399	3407	3411	3382	3363	3358	3377	3373	3386	3381	3368
45°	3873	3868	3861	3826	3796	3772	3777	3770	3771	3763	3753
47.5°	4351	4368	4339	4322	4288	4271	4285	4273	4296	4254	4234
50°	4815	4827	4817	4793	4793	4817	4834	4856	4888	4840	4768
52.5°	5195	5205	5220	5240	5289	5340	5412	5489	5550	5541	5459
55°	5427	5439	5464	5533	5621	5755	5918	6097	6237	6305	6245
57.5°	5505	5514	5582	5665	5802	6001	6274	6583	6852	7023	6996
60°	5487	5487	5556	5670	5862	6126	6512	6940	7352	7608	7570
62.5°	5298	5308	5407	5544	5776	6092	6552	7099	7592	7910	7879
65°	4884	4891	4998	5161	5420	5794	6297	6903	7468	7774	7716
67.5°	4215	4222	4309	4493	4767	5158	5701	6368	6921	7163	6989
70°	3353	3373	3429	3624	3832	4215	4715	5382	5904	6133	5941
72.5°	2285	2336	2404	2577	2776	3094	3492	4054	4473	4738	4567
75°	1287	1359	1380	1511	1675	1926	2217	2620	3043	3258	3052
77.5°	556	615	641	702	830	935	1112	1384	1711	1862	1615
80°	274	288	299	318	354	388	472	591	725	759	604
82.5°	212	222	241	256	265	274	282	298	311	318	300
85°	149	162	183	200	210	217	224	229	217	198	208
87.5°	39	51	71	77	87	92	90	93	84	61	68
90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P147490

CATALOG NUMBER: TMU-E06-LED-E-U-5MQ

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1284	1284	1284	1284	1284	1284	1284	1284
2.5°	1291	1290	1291	1291	1291	1290	1290	1290
5°	1314	1314	1315	1313	1313	1314	1313	1312
7.5°	1353	1352	1352	1351	1352	1351	1351	1350
10°	1405	1403	1404	1401	1401	1400	1400	1400
12.5°	1461	1458	1459	1456	1451	1452	1453	1452
15°	1515	1512	1509	1507	1504	1505	1505	1504
17.5°	1570	1564	1563	1560	1559	1559	1559	1560
20°	1627	1623	1622	1619	1618	1621	1622	1620
22.5°	1688	1686	1688	1686	1689	1691	1692	1690
25°	1765	1763	1766	1773	1777	1779	1784	1782
27.5°	1864	1862	1869	1879	1885	1895	1900	1902
30°	1992	2001	2005	2025	2029	2045	2045	2052
32.5°	2178	2195	2225	2256	2299	2330	2330	2346
35°	2586	2593	2616	2621	2630	2640	2630	2638
37.5°	2899	2868	2846	2815	2796	2796	2798	2796
40°	3059	3047	3037	3011	3007	3006	3006	3010
42.5°	3345	3316	3300	3278	3271	3269	3268	3270
45°	3717	3670	3627	3605	3586	3568	3574	3574
47.5°	4150	4077	4007	3969	3936	3921	3911	3908
50°	4677	4575	4485	4414	4366	4365	4370	4338
52.5°	5323	5162	5050	4954	4909	4904	4888	4870
55°	6039	5848	5663	5560	5501	5469	5450	5420
57.5°	6777	6520	6254	6089	5985	5913	5875	5858
60°	7346	6995	6644	6379	6206	6099	6033	6006
62.5°	7570	7094	6644	6296	6046	5898	5809	5770
65°	7303	6739	6227	5843	5564	5399	5302	5260
67.5°	6557	6059	5502	5120	4833	4670	4565	4534
70°	5497	4988	4456	4115	3859	3726	3617	3604
72.5°	4131	3692	3236	2954	2748	2528	2472	2500
75°	2648	2237	1831	1577	1389	1179	1098	1118
77.5°	1254	971	701	542	455	389	372	362
80°	465	377	333	316	304	293	285	276
82.5°	301	294	285	282	273	259	233	222
85°	225	225	213	214	207	189	165	152
87.5°	66	59	54	50	49	44	32	28
90°	0	0	0	0	0	0	0	0

(END OF REPORT)