

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P148498

Luminaire Tested: **TMU-E03-LED-E-U-5XQ-8030**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P148498  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33676)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: TMU-E03-LED-E-U-5XQ-8030  
Description: TALON MEDIUM LED AREA LUMINAIRE  
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE EXTRA WIDE  
Light Source: (63) 3000K CCT, 80 CRI LEDs  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8052.6 lumens  
Efficiency: N/A  
Efficacy: 107.1 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')  
IES Classification: Type V - Short - Non-Cutoff  
BUG Rating: B3 - U0 - G3


Input Watts (W): 75.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P148498  
 CATALOG NUMBER: TMU-E03-LED-E-U-5XQ-8030

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 7.6 fc  
 Type V - Short - Non-Cutoff

REPORT NUMBER: P148498  
CATALOG NUMBER: TMU-E03-LED-E-U-5XQ-8030

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 72.5-Deg Vertical

REPORT NUMBER: P148498

CATALOG NUMBER: TMU-E03-LED-E-U-5XQ-8030

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	4026.3	0.0	4026.3
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	4026.3	0.0	4026.3
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	8052.6	0.0	8052.6
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.7	0.9
10°-20°	215.1	2.7
20°-30°	360.2	4.5
30°-40°	549.1	6.8
40°-50°	876.8	10.9
50°-60°	1348.1	16.7
60°-70°	1962.9	24.4
70°-80°	2211.2	27.5
80°-90°	456.5	5.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8052.6	100.0
0°-180°	8052.6	100.0



REPORT NUMBER: P148498


CATALOG NUMBER: TMU-E03-LED-E-U-5XQ-8030

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	324.0	4.0			
FM	(30°-60°)	1387.0	17.2			
FH	(60°-80°)	2087.1	25.9			G2/5000
FVH	(80°-90°)	228.2	2.8			G3/500
BL	(0°-30°)	324.0	4.0	B1/500		
BM	(30°-60°)	1387.0	17.2	B2/2500		
BH	(60°-80°)	2087.1	25.9	B3/2500		G2/5000
BVH	(80°-90°)	228.2	2.8			G3/500
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G3**

Type V Short





REPORT NUMBER: P148498

CATALOG NUMBER: TMU-E03-LED-E-U-5XQ-8030

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	763.0	763.0	763.0	763.0	763.0	763.0	763.0	763.0	763.0	763.0	763.0
2.5°	764.2	764.6	764.4	764.0	764.2	764.0	763.6	763.4	761.9	762.8	764.0
5°	764.2	763.8	763.6	763.4	763.4	764.0	763.4	762.8	762.6	763.0	762.3
7.5°	763.8	763.0	762.6	762.4	762.5	762.8	762.1	761.3	761.9	761.3	760.4
10°	762.6	761.9	762.1	761.3	761.5	761.3	760.4	759.8	760.2	759.6	758.6
12.5°	763.0	761.9	761.7	761.2	761.1	760.8	759.8	758.8	759.0	758.6	757.5
15°	763.0	762.4	762.1	761.3	761.0	760.7	759.4	759.0	759.0	758.3	757.0
17.5°	763.4	763.0	763.0	761.9	761.5	761.3	759.8	759.2	759.8	758.6	757.7
20°	764.6	764.2	764.4	763.8	763.0	763.0	761.9	761.5	761.7	761.5	759.2
22.5°	767.2	767.2	767.6	767.4	767.2	767.4	766.6	766.5	766.8	766.8	764.8
25°	774.3	774.2	774.6	774.6	774.8	776.3	775.6	775.4	776.4	776.5	774.6
27.5°	787.8	787.4	787.9	788.3	789.3	791.2	790.8	791.4	793.2	792.7	791.0
30°	803.5	803.1	804.1	805.4	806.2	809.2	807.9	811.1	812.6	813.8	812.6
32.5°	826.2	826.3	828.1	829.0	830.9	833.9	834.3	836.8	838.7	840.8	839.4
35°	856.6	856.2	857.7	859.2	861.5	864.2	865.3	868.7	871.6	873.1	870.4
37.5°	903.1	900.8	903.5	904.3	906.2	906.9	909.8	914.1	917.2	916.8	914.9
40°	966.0	965.5	964.4	963.2	966.2	967.2	967.2	972.9	978.0	977.1	976.9
42.5°	1039.4	1037.5	1036.2	1036.2	1037.9	1038.3	1044.8	1049.1	1052.7	1053.5	1052.6
45°	1118.3	1116.4	1116.8	1116.0	1116.6	1119.4	1123.1	1131.0	1137.7	1137.9	1134.4
47.5°	1203.1	1197.2	1201.8	1195.3	1199.3	1201.4	1210.9	1222.3	1234.1	1236.2	1233.1
50°	1289.2	1288.6	1288.1	1286.9	1288.8	1293.4	1305.0	1323.0	1334.4	1341.9	1336.9
52.5°	1383.3	1380.2	1378.7	1376.6	1378.5	1387.5	1403.8	1419.4	1439.9	1448.5	1441.5
55°	1474.8	1473.8	1468.3	1468.1	1472.1	1486.3	1504.0	1523.2	1545.3	1555.0	1552.5
57.5°	1569.0	1562.9	1561.2	1558.6	1566.7	1580.0	1601.7	1636.3	1659.3	1670.2	1664.0
60°	1661.0	1656.3	1652.8	1651.9	1657.4	1676.0	1707.2	1748.8	1777.2	1791.6	1781.4
62.5°	1759.8	1756.8	1752.6	1747.7	1759.3	1783.2	1822.0	1868.0	1910.0	1927.7	1912.2
65°	1882.5	1876.4	1871.8	1865.6	1875.1	1905.1	1953.8	2018.6	2075.0	2095.6	2084.7
67.5°	2012.1	2006.4	2006.8	2003.0	2019.9	2061.5	2124.3	2212.3	2287.8	2323.1	2302.4
70°	2125.2	2128.3	2129.2	2144.6	2173.7	2237.0	2341.6	2479.4	2594.0	2647.8	2625.6
71°	2091.8	2098.8	2109.6	2125.6	2175.8	2250.7	2393.6	2560.4	2697.2	2788.3	2757.7
72.5°	1997.3	2001.6	2007.0	2031.5	2088.3	2187.4	2334.5	2525.2	2701.0	2818.9	2783.5
75°	1860.6	1864.6	1866.5	1883.6	1935.3	2021.8	2156.4	2325.6	2480.7	2581.2	2571.2
77.5°	1654.2	1654.9	1669.6	1696.0	1754.0	1853.0	1994.8	2170.3	2316.1	2394.2	2344.6
80°	1187.9	1179.9	1195.1	1229.0	1300.8	1414.3	1559.5	1759.9	1921.8	1994.8	1918.0
82.5°	452.0	476.4	515.0	571.2	595.4	721.6	857.1	974.8	1111.1	1263.4	1225.3
85°	48.5	54.7	68.6	85.0	107.4	148.5	205.3	280.2	345.4	406.0	360.4
87.5°	18.2	18.6	20.7	23.8	24.2	25.3	27.0	31.4	29.3	25.3	20.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P148498

CATALOG NUMBER: TMU-E03-LED-E-U-5XQ-8030

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	763.0	763.0	763.0	763.0	763.0	763.0	763.0	763.0
2.5°	763.0	763.2	763.0	763.2	763.2	762.3	762.5	762.1
5°	762.8	762.1	762.3	762.6	762.3	762.8	762.1	762.6
7.5°	761.7	760.4	760.9	760.9	760.4	761.0	760.7	760.4
10°	759.6	757.9	758.8	758.3	758.1	758.3	758.3	758.4
12.5°	757.7	756.6	756.8	756.6	756.4	757.0	756.8	757.0
15°	757.3	755.6	755.4	755.0	755.2	755.6	755.6	756.2
17.5°	756.8	754.7	754.6	754.1	754.3	755.2	755.4	754.9
20°	758.1	756.4	756.0	755.6	755.4	756.4	756.2	756.2
22.5°	764.0	761.9	761.7	760.0	759.4	760.0	759.6	759.6
25°	773.5	771.0	770.2	767.9	766.1	766.1	765.5	765.0
27.5°	790.6	786.8	786.0	784.0	781.8	782.2	780.9	780.7
30°	810.4	807.1	804.1	801.4	798.6	797.6	796.1	795.8
32.5°	836.4	832.6	829.0	825.6	821.8	820.4	817.8	816.6
35°	868.2	863.2	859.0	856.6	852.9	850.9	849.2	851.2
37.5°	912.8	906.6	904.6	901.8	899.3	896.3	897.0	896.3
40°	974.4	968.9	966.8	961.9	961.3	957.9	960.0	957.9
42.5°	1050.6	1040.4	1039.0	1035.2	1033.9	1032.0	1032.8	1031.4
45°	1133.5	1124.4	1122.7	1116.6	1116.8	1112.4	1114.1	1114.1
47.5°	1226.7	1217.2	1209.5	1205.0	1203.3	1200.6	1202.0	1201.8
50°	1323.0	1310.1	1301.4	1292.8	1289.0	1290.0	1287.1	1292.2
52.5°	1426.4	1407.1	1394.9	1386.6	1379.5	1381.0	1381.4	1382.8
55°	1533.3	1508.8	1491.1	1480.4	1473.8	1474.2	1476.1	1477.8
57.5°	1640.9	1610.4	1586.3	1570.3	1566.0	1568.0	1567.9	1567.7
60°	1752.6	1715.8	1684.8	1666.7	1662.8	1661.8	1670.0	1667.3
62.5°	1872.4	1828.3	1796.2	1773.0	1767.5	1771.3	1778.7	1777.0
65°	2031.3	1970.3	1929.0	1906.0	1896.6	1900.4	1910.4	1910.0
67.5°	2236.2	2150.9	2096.3	2066.7	2060.0	2064.6	2070.1	2075.4
70°	2542.6	2420.8	2342.7	2278.8	2251.4	2246.1	2251.6	2251.8
71°	2650.3	2510.5	2386.2	2308.1	2263.2	2244.2	2245.6	2236.2
72.5°	2645.9	2473.5	2328.1	2246.5	2184.0	2168.8	2161.4	2150.0
75°	2467.6	2312.3	2186.2	2097.1	2037.0	2019.0	2006.0	2005.3
77.5°	2237.8	2123.3	1984.2	1889.9	1816.7	1786.9	1773.6	1773.2
80°	1799.0	1627.4	1525.7	1469.0	1380.6	1355.0	1328.0	1317.9
82.5°	1087.9	850.1	691.2	614.2	571.6	470.7	422.4	399.6
85°	253.4	180.0	124.1	81.5	58.7	46.6	35.9	31.6
87.5°	17.1	13.5	12.0	9.7	7.4	7.2	4.4	3.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)