

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599043

Luminaire Tested: **IFLD-L-SA7B-760-U-SLL**

Issue Date: 05/03/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P599043
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/03/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-L-SA7B-760-U-SLL
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens
 Light Source: (112) 5700K CCT, 70 CRI LEDS
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 30985.5 lumens
 Efficiency: N/A
 Efficacy: 110.3 lumens/watt
 Spacing Criteria (0/90/45): 1.12 / 0.52 / 0.8
 Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
 CIE Type: Direct

Input Watts (W): 281
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599043
CATALOG NUMBER: IFLD-L-SA7B-760-U-SLL

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ··· 90°-270° - · 135°-315°

TEST NUMBER: P599043
 CATALOG NUMBER: IFLD-L-SA7B-760-U-SLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	106	100	94	89	103	97	92	88	93	89	85	89	85	82	85	82	80	77	77	77	77
2	94	83	75	68	91	81	74	67	78	71	65	74	69	64	71	66	62	60	60	60	60
3	84	71	61	53	81	69	60	53	66	58	52	63	56	51	60	55	50	47	47	47	47
4	75	61	51	43	73	60	50	42	57	48	42	54	47	41	52	46	40	38	38	38	38
5	68	53	43	35	66	52	42	35	50	41	34	48	40	34	46	39	34	31	31	31	31
6	63	47	37	30	60	46	37	29	44	36	29	42	35	29	41	34	29	26	26	26	26
7	58	42	32	25	56	41	32	25	40	31	25	38	31	25	37	30	25	22	22	22	22
8	53	38	29	22	52	37	28	22	36	28	22	35	27	22	33	27	22	19	19	19	19
9	50	35	26	20	48	34	26	20	33	25	19	32	25	19	31	24	19	17	17	17	17
10	46	32	23	18	45	31	23	18	30	23	17	29	22	17	28	22	17	15	15	15	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	53263	53263	53263	53263
5°	58516	51981	37278	40694
10°	51831	45747	22610	24263
15°	50470	43424	16007	16619
20°	57547	50226	10470	11573
25°	70115	63667	9142	9468
30°	84481	77220	9482	8799
35°	98527	90669	7857	7405
40°	118394	109509	7339	6953
45°	137782	125856	7428	6905
50°	155712	143052	7596	7135
55°	181595	170503	7868	7480
60°	221485	215419	7842	7842
65°	248911	249261	8052	8402
70°	244627	253279	8436	8652
75°	201790	215225	8860	9432
80°	145697	152937	9797	10225
85°	80635	86575	11035	13579

TEST NUMBER: P599043
 CATALOG NUMBER: IFLD-L-SA7B-760-U-SLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	768.8	2.5
10°-20°	1623.3	5.2
20°-30°	2375.0	7.7
30°-40°	3346.3	10.8
40°-50°	4598.7	14.8
50°-60°	6267.6	20.2
60°-70°	6859.6	22.1
70°-80°	3960.3	12.8
80°-90°	1185.9	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4767.1	15.4
0°-40°	8113.4	26.2
0°-60°	18979.7	61.3
0°-90°	30985.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	30985.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	9897	9897	9897	9897	9897	
5°	10831	9622	6900	7532	10831	984
15°	9058	7794	2873	2983	9058	2646
25°	11807	10721	1540	1594	11807	5529
35°	14996	13800	1196	1127	14996	9509
45°	18102	16536	976	907	18102	13913
55°	19353	18171	838	797	19353	17462
65°	19546	19573	632	660	19546	18707
75°	9704	10350	426	454	9704	10424
85°	1306	1402	179	220	1306	1812
90°	0	0	0	0	0	

TEST NUMBER: P599043
 CATALOG NUMBER: IFLD-L-SA7B-760-U-SLL

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6
2.5°	10597.6	10556.3	10597.6	10748.8	10790.0	10858.7	10858.7	10762.5	10583.8	10501.4	10363.9
5°	10831.3	10762.5	11106.2	11422.3	11669.7	11642.2	11408.6	11216.1	10858.7	10322.7	9814.1
7.5°	10363.9	10432.6	10680.1	11504.8	12082.1	12192.0	11820.9	11436.0	10666.3	9924.1	9236.8
10°	9484.2	9580.4	10116.5	10968.7	11875.9	12054.6	11820.9	11353.6	10432.6	9511.7	8714.5
12.5°	9058.1	9278.0	9594.2	10625.1	11271.1	11697.2	11587.2	11284.8	10254.0	9168.1	8398.3
15°	9058.1	9113.1	9580.4	10446.4	10817.5	10831.3	10872.5	10927.5	10308.9	9319.3	8288.4
17.5°	9346.8	9498.0	9896.6	10432.6	10501.4	10336.4	10336.4	10570.1	10418.9	9745.4	8687.0
20°	10047.8	9992.8	10515.1	10735.0	10363.9	9951.6	9910.3	10308.9	10542.6	10199.0	9415.5
22.5°	10748.8	10996.2	11422.3	10927.5	10240.2	9690.4	9635.4	10130.2	10913.7	10982.5	10254.0
25°	11807.2	12054.6	12274.5	11669.7	10226.5	9621.7	9662.9	10047.8	11367.3	12095.8	11656.0
27.5°	12948.0	13099.2	13415.4	12480.7	10556.3	9539.2	9580.4	10157.7	11793.4	12824.3	12755.6
30°	13594.0	13759.0	13690.3	12631.9	10776.3	9594.2	9484.2	10308.9	11559.8	12824.3	13470.3
32.5°	14226.3	14130.1	14088.9	12879.3	11051.2	9937.8	9662.9	10625.1	11697.2	13030.5	14391.3
35°	14996.1	14858.6	14748.6	13360.4	11504.8	10267.7	10144.0	11037.4	11999.6	13456.6	15133.5
37.5°	15848.3	15848.3	15312.2	13717.8	12040.8	10803.8	10666.3	11628.5	12480.7	13717.8	16150.7
40°	16851.7	16892.9	15944.5	14198.8	12645.6	11656.0	11614.7	12398.2	12948.0	14102.6	17126.6
42.5°	17593.9	17621.4	16494.3	14377.5	13346.6	12838.1	13016.7	13635.3	13484.1	14446.3	17195.3
45°	18102.5	17965.0	16879.2	14886.1	14116.4	14611.2	14666.2	14844.9	14185.1	14652.4	17470.2
47.5°	18349.9	18322.4	17044.1	15477.1	15738.3	16411.8	16728.0	16480.6	14831.1	14432.5	17470.2
50°	18597.3	18363.6	17195.3	16288.1	17319.0	18679.8	18611.1	18157.5	15724.6	14707.4	17209.0
52.5°	18762.3	18556.1	17497.7	17016.6	18831.0	20370.5	20645.4	19806.9	16769.2	15216.0	17332.8
55°	19353.3	19188.4	18404.9	18006.3	20576.6	22157.3	22198.6	21030.2	17868.8	16054.4	18143.7
57.5°	20068.1	20164.3	19655.7	19408.3	21909.9	23463.1	23311.9	21937.4	18803.5	17071.6	19078.4
60°	20576.6	20727.8	20604.1	20631.6	22569.7	23903.0	23559.4	22501.0	19490.8	17841.3	20219.3
62.5°	20301.7	20604.1	21112.7	21002.7	22597.2	23586.8	23105.8	21758.7	19573.2	18844.7	21085.2
65°	19545.7	19573.2	20562.9	21167.7	21360.1	21951.2	21318.9	20205.5	18721.0	19463.3	20961.5
67.5°	17607.7	17827.6	18721.0	19903.1	19092.1	19229.6	19174.6	17566.4	17429.0	19037.2	20013.1
70°	15545.9	15697.1	16673.0	18061.3	16123.2	15477.1	15600.9	14405.0	14968.6	17717.6	18102.5
72.5°	12851.8	12948.0	14061.4	15284.7	12934.3	11779.7	12068.3	11092.4	11889.6	15504.6	15271.0
75°	9704.1	9882.8	10748.8	12192.0	9525.5	8783.2	9071.9	8673.3	9415.5	12769.3	11848.4
77.5°	6900.1	6762.7	7834.8	9539.2	7161.3	6721.4	6748.9	6817.6	7614.9	10762.5	8508.3
80°	4700.9	4742.1	5704.3	6996.3	5621.8	5553.1	5484.4	6034.2	6391.5	8522.1	6185.4
82.5°	2790.3	2790.3	3848.7	4975.8	4439.7	5003.3	4687.1	5182.0	5003.3	6267.8	4054.8
85°	1305.8	1305.8	1979.3	3587.5	3436.3	4123.6	3505.0	3917.4	3697.5	4371.0	1828.1
87.5°	219.9	192.4	398.6	1759.4	1415.8	1608.2	632.3	2089.3	2322.9	3051.4	453.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599043
 CATALOG NUMBER: IFLD-L-SA7B-760-U-SLL

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6
2.5°	10212.7	10116.5	9924.1	9676.7	9470.5	9209.3	9126.8	8948.2	8700.7	8673.3	8563.3
5°	9621.7	9291.8	8879.4	8370.9	8027.2	7669.8	7367.5	7188.8	6982.6	6955.1	6900.1
7.5°	8975.6	8563.3	7876.0	7271.2	6680.2	6116.6	5841.7	5498.1	5264.4	5085.7	5003.3
10°	8370.9	7986.0	7133.8	6309.1	5786.7	5415.6	5085.7	4728.4	4439.7	4219.8	4137.3
12.5°	7972.2	7518.6	6597.7	5814.2	5429.4	5003.3	4632.1	4247.3	3876.2	3587.5	3436.3
15°	7793.6	7367.5	6432.8	5566.8	5003.3	4412.2	3986.1	3601.3	3147.7	2941.5	2872.8
17.5°	8219.7	7587.4	6377.8	5278.2	4481.0	3807.4	3285.1	2872.8	2542.9	2336.7	2254.2
20°	8769.5	7986.0	6474.0	4934.5	3986.1	3230.1	2652.8	2213.0	1993.1	1841.9	1828.1
22.5°	9470.5	8577.0	6625.2	4687.1	3436.3	2597.9	2075.5	1814.4	1663.2	1649.4	1621.9
25°	10721.3	9649.2	6872.6	4357.2	2996.5	2144.3	1773.1	1621.9	1553.2	1512.0	1539.5
27.5°	11793.4	10350.2	7051.3	4151.1	2817.8	2020.6	1718.2	1553.2	1484.5	1470.7	1484.5
30°	12425.7	10996.2	6996.3	3766.2	2460.4	1924.3	1828.1	1773.1	1635.7	1525.7	1525.7
32.5°	13003.0	11408.6	6982.6	3422.6	2103.0	1608.2	1525.7	1484.5	1567.0	1621.9	1580.7
35°	13800.2	12054.6	6941.3	3230.1	1951.8	1484.5	1347.0	1237.1	1182.1	1154.6	1195.8
37.5°	14652.4	12494.4	6831.4	3202.6	1869.4	1415.8	1305.8	1195.8	1140.9	1113.4	1099.6
40°	15587.1	12961.8	6707.7	3065.2	1828.1	1374.5	1264.6	1168.3	1099.6	1058.4	1044.6
42.5°	16191.9	13332.9	6584.0	2996.5	1745.6	1347.0	1223.3	1140.9	1072.1	1017.1	1017.1
45°	16535.5	13772.7	6460.3	2927.7	1649.4	1360.8	1223.3	1113.4	1030.9	1003.4	975.9
47.5°	16686.7	14102.6	6419.0	2817.8	1567.0	1305.8	1195.8	1085.9	1003.4	948.4	934.7
50°	17085.3	14803.6	6570.2	2735.3	1470.7	1250.8	1264.6	1072.1	989.7	920.9	907.2
52.5°	17319.0	15367.2	6900.1	2611.6	1402.0	1182.1	1237.1	1044.6	948.4	879.7	879.7
55°	18171.2	16301.9	7257.5	2515.4	1319.5	1085.9	1140.9	989.7	879.7	838.5	838.5
57.5°	19257.1	17291.5	7559.9	2474.1	1264.6	1017.1	1017.1	962.2	838.5	783.5	769.7
60°	20013.1	18102.5	7738.6	2446.7	1209.6	948.4	907.2	962.2	797.2	742.2	728.5
62.5°	20095.6	17635.2	7559.9	2432.9	1195.8	879.7	824.7	920.9	756.0	701.0	673.5
65°	19573.2	16686.7	7065.1	2377.9	1182.1	811.0	769.7	797.2	701.0	659.8	632.3
67.5°	18528.6	15147.3	6350.3	2350.4	1168.3	756.0	701.0	687.3	646.0	604.8	577.3
70°	16095.7	13140.5	5511.8	2226.7	1140.9	714.8	632.3	618.5	577.3	549.8	536.1
72.5°	13511.6	10748.8	4549.7	2061.8	1085.9	646.0	577.3	549.8	536.1	494.8	481.1
75°	10350.2	8274.6	3642.5	1828.1	948.4	577.3	508.6	481.1	467.3	439.8	426.1
77.5°	7271.2	6157.9	2694.1	1484.5	797.2	522.3	453.6	426.1	412.4	371.1	371.1
80°	4934.5	4316.0	1828.1	1030.9	618.5	426.1	398.6	371.1	343.6	316.1	316.1
82.5°	3065.2	3024.0	1319.5	673.5	453.6	343.6	316.1	316.1	274.9	247.4	247.4
85°	1402.0	1855.6	920.9	467.3	343.6	261.2	261.2	247.4	219.9	178.7	178.7
87.5°	439.8	618.5	481.1	206.2	192.4	151.2	151.2	137.5	137.5	110.0	110.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599043
 CATALOG NUMBER: IFLD-L-SA7B-760-U-SLL

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6
2.5°	8673.3	8659.5	8659.5	8604.5	8742.0	8742.0	8824.4	8755.7	8797.0	8810.7	8920.7
5°	6886.4	6996.3	7078.8	7243.7	7340.0	7381.2	7381.2	7491.2	7449.9	7532.4	7697.3
7.5°	5044.5	5182.0	5429.4	5635.6	5800.5	5855.5	5841.7	5869.2	5910.5	5814.2	5841.7
10°	4082.3	3986.1	4068.6	4261.0	4412.2	4590.9	4453.5	4439.7	4481.0	4439.7	4522.2
12.5°	3408.8	3298.9	3230.1	3230.1	3340.1	3422.6	3381.3	3450.1	3601.3	3642.5	3738.7
15°	2762.8	2666.6	2611.6	2542.9	2652.8	2680.3	2721.6	2817.8	2927.7	2982.7	3092.7
17.5°	2213.0	2213.0	2213.0	2158.0	2199.2	2240.5	2254.2	2377.9	2391.7	2446.7	2487.9
20°	1814.4	1855.6	1924.3	1951.8	1993.1	1993.1	1965.6	2034.3	1979.3	2020.6	2048.0
22.5°	1635.7	1690.7	1718.2	1731.9	1786.9	1800.6	1731.9	1745.6	1759.4	1718.2	1731.9
25°	1539.5	1567.0	1539.5	1553.2	1567.0	1539.5	1553.2	1580.7	1567.0	1594.4	1580.7
27.5°	1498.2	1470.7	1457.0	1443.3	1443.3	1415.8	1429.5	1429.5	1457.0	1470.7	1470.7
30°	1498.2	1457.0	1402.0	1360.8	1360.8	1319.5	1347.0	1374.5	1388.3	1415.8	1415.8
32.5°	1539.5	1457.0	1360.8	1319.5	1278.3	1250.8	1278.3	1319.5	1374.5	1388.3	1402.0
35°	1223.3	1264.6	1250.8	1195.8	1182.1	1182.1	1168.3	1168.3	1127.1	1127.1	1113.4
37.5°	1099.6	1085.9	1113.4	1127.1	1140.9	1099.6	1099.6	1044.6	1030.9	1044.6	1044.6
40°	1030.9	1030.9	1030.9	1072.1	1085.9	1058.4	1017.1	989.7	989.7	989.7	1003.4
42.5°	1003.4	975.9	962.2	989.7	1030.9	1003.4	962.2	948.4	948.4	962.2	962.2
45°	962.2	948.4	934.7	920.9	975.9	934.7	920.9	907.2	907.2	907.2	920.9
47.5°	920.9	907.2	879.7	879.7	893.4	879.7	866.0	866.0	866.0	893.4	893.4
50°	893.4	879.7	852.2	852.2	852.2	852.2	838.5	838.5	838.5	852.2	866.0
52.5°	852.2	838.5	824.7	811.0	811.0	811.0	811.0	811.0	811.0	824.7	838.5
55°	811.0	797.2	783.5	783.5	797.2	797.2	783.5	797.2	783.5	797.2	811.0
57.5°	769.7	756.0	742.2	756.0	769.7	756.0	756.0	756.0	756.0	756.0	769.7
60°	714.8	714.8	714.8	714.8	742.2	742.2	742.2	742.2	714.8	728.5	742.2
62.5°	687.3	673.5	673.5	687.3	701.0	701.0	714.8	701.0	687.3	701.0	701.0
65°	632.3	632.3	632.3	646.0	646.0	659.8	659.8	659.8	646.0	659.8	659.8
67.5°	591.0	591.0	591.0	591.0	618.5	618.5	618.5	618.5	604.8	604.8	618.5
70°	522.3	536.1	522.3	549.8	577.3	563.6	577.3	577.3	563.6	549.8	577.3
72.5°	481.1	481.1	481.1	481.1	522.3	522.3	522.3	536.1	522.3	508.6	522.3
75°	426.1	426.1	426.1	439.8	467.3	467.3	467.3	467.3	467.3	453.6	453.6
77.5°	371.1	384.9	371.1	384.9	412.4	398.6	412.4	426.1	412.4	398.6	398.6
80°	316.1	316.1	316.1	329.9	343.6	343.6	343.6	357.4	343.6	329.9	329.9
82.5°	247.4	247.4	261.2	261.2	274.9	274.9	274.9	288.7	274.9	261.2	261.2
85°	192.4	192.4	192.4	206.2	206.2	219.9	219.9	233.7	233.7	219.9	219.9
87.5°	123.7	110.0	123.7	123.7	137.5	137.5	123.7	110.0	123.7	110.0	96.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599043
 CATALOG NUMBER: IFLD-L-SA7B-760-U-SLL

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6	9896.6
2.5°	9030.6	9278.0	9456.7	9580.4	9759.1	10102.8	10240.2	10487.6	10556.3	10597.6
5°	7766.1	8027.2	8412.1	8687.0	9003.1	9649.2	10144.0	10515.1	10680.1	10831.3
7.5°	6089.1	6432.8	6831.4	7188.8	7711.1	8508.3	9154.3	9924.1	10212.7	10363.9
10°	4755.9	5072.0	5511.8	5951.7	6680.2	7353.7	8274.6	8975.6	9374.3	9484.2
12.5°	4013.6	4384.7	4907.1	5443.1	5896.7	6666.4	7601.1	8618.3	8989.4	9058.1
15°	3408.8	3917.4	4453.5	5003.3	5525.6	6199.1	7202.5	8439.6	8989.4	9058.1
17.5°	2817.8	3271.4	3903.7	4494.7	5099.5	6020.4	7271.2	8590.8	9140.6	9346.8
20°	2240.5	2680.3	3175.2	3917.4	4742.1	5718.0	7422.4	9099.4	9827.9	10047.8
22.5°	1855.6	2048.0	2529.1	3243.9	4219.8	5511.8	7573.6	9896.6	10666.3	10748.8
25°	1621.9	1759.4	2061.8	2735.3	3807.4	5374.4	7931.0	10817.5	11807.2	11807.2
27.5°	1512.0	1567.0	1773.1	2377.9	3518.8	5250.7	8288.4	11834.7	12755.6	12948.0
30°	1484.5	1621.9	1731.9	2116.8	3202.6	4907.1	8618.3	12631.9	13580.3	13594.0
32.5°	1457.0	1429.5	1512.0	1841.9	2817.8	4549.7	8893.2	13442.9	14185.1	14226.3
35°	1140.9	1195.8	1333.3	1621.9	2529.1	4288.5	9030.6	13882.7	14954.8	14996.1
37.5°	1072.1	1140.9	1250.8	1498.2	2336.7	4068.6	9071.9	14734.9	15765.8	15848.3
40°	1044.6	1099.6	1182.1	1388.3	2185.5	3793.7	9154.3	15614.6	16961.6	16851.7
42.5°	989.7	1058.4	1140.9	1333.3	2061.8	3587.5	9168.1	16095.7	17593.9	17593.9
45°	975.9	1017.1	1113.4	1333.3	1924.3	3408.8	8948.2	16576.8	18322.4	18102.5
47.5°	920.9	1003.4	1085.9	1292.1	1759.4	3230.1	8687.0	16824.2	18418.6	18349.9
50°	907.2	989.7	1127.1	1223.3	1663.2	3147.7	8632.0	17442.7	18611.1	18597.3
52.5°	879.7	962.2	1168.3	1168.3	1539.5	3037.7	8893.2	17717.6	18652.3	18762.3
55°	838.5	962.2	1085.9	1072.1	1429.5	2900.2	9181.8	18432.4	19380.8	19353.3
57.5°	811.0	934.7	1030.9	975.9	1305.8	2804.0	9607.9	19119.6	20260.5	20068.1
60°	769.7	934.7	920.9	907.2	1209.6	2721.6	9965.3	19257.1	20452.9	20576.6
62.5°	742.2	975.9	811.0	838.5	1127.1	2680.3	9814.1	18226.2	20191.8	20301.7
65°	714.8	838.5	742.2	769.7	1099.6	2597.9	9223.1	16989.1	19064.7	19545.7
67.5°	659.8	687.3	687.3	714.8	1072.1	2405.4	8013.5	14762.4	17346.5	17607.7
70°	604.8	618.5	618.5	659.8	1044.6	2185.5	6611.5	12769.3	15051.0	15545.9
72.5°	549.8	549.8	549.8	604.8	962.2	2006.8	5443.1	9814.1	12508.2	12851.8
75°	481.1	481.1	481.1	536.1	866.0	1828.1	4288.5	7298.7	9209.3	9704.1
77.5°	426.1	426.1	412.4	481.1	756.0	1484.5	3092.7	5154.5	6487.8	6900.1
80°	357.4	343.6	343.6	384.9	591.0	1072.1	1993.1	3642.5	4522.2	4700.9
82.5°	288.7	274.9	261.2	288.7	426.1	673.5	1237.1	2542.9	2900.2	2790.3
85°	274.9	288.7	233.7	219.9	302.4	439.8	783.5	1567.0	1305.8	1305.8
87.5°	110.0	96.2	96.2	82.5	151.2	164.9	343.6	288.7	219.9	219.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)