

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599038

Luminaire Tested: **IFLD-M-SA4B-760-U-SLL**

Issue Date: 05/03/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P599038
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/03/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-M-SA4B-760-U-SLL
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens
 Light Source: (64) 5700K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 19872.2 lumens
 Efficiency: N/A
 Efficacy: 119.6 lumens/watt
 Spacing Criteria (0/90/45): 1.12 / 0.52 / 0.8
 Luminous Opening: Rectangular (W 2' x L: 0.5' x H: 0')
 CIE Type: Direct

Input Watts (W): 166.1
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599038
CATALOG NUMBER: IFLD-M-SA4B-760-U-SLL

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°

TEST NUMBER: P599038

CATALOG NUMBER: IFLD-M-SA4B-760-U-SLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	106	100	94	89	103	97	92	88	93	89	85	89	85	82	85	82	80	77
2	94	83	75	68	91	81	74	67	78	71	65	74	69	64	71	66	62	60
3	84	71	61	53	81	69	60	53	66	58	52	63	56	51	60	55	50	47
4	75	61	51	43	73	60	50	42	57	48	42	54	47	41	52	46	40	38
5	68	53	43	35	66	52	42	35	50	41	34	48	40	34	46	39	34	31
6	63	47	37	30	60	46	37	29	44	36	29	42	35	29	41	34	29	26
7	58	42	32	25	56	41	32	25	40	31	25	38	31	25	37	30	25	22
8	53	38	29	22	52	37	28	22	36	28	22	35	27	22	33	27	22	19
9	50	35	26	20	48	34	26	20	33	25	19	32	25	19	31	24	19	17
10	46	32	23	18	45	31	23	18	30	23	17	29	22	17	28	22	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	68320	68320	68320	68320
5°	75057	66676	47816	52197
10°	66483	58679	29002	31122
15°	64737	55699	20531	21317
20°	73814	64424	13430	14844
25°	89935	81664	11726	12145
30°	108362	99049	12162	11286
35°	126378	116300	10077	9499
40°	151861	140465	9414	8918
45°	176730	161433	9528	8856
50°	199729	183491	9743	9153
55°	232927	218701	10091	9595
60°	284094	276314	10058	10058
65°	319274	319722	10328	10776
70°	313778	324875	10820	11097
75°	258835	276065	11366	12098
80°	186884	196170	12571	13116
85°	103433	111053	14153	17414

TEST NUMBER: P599038
 CATALOG NUMBER: IFLD-M-SA4B-760-U-SLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	493.1	2.5
10°-20°	1041.1	5.2
20°-30°	1523.2	7.7
30°-40°	2146.1	10.8
40°-50°	2949.4	14.8
50°-60°	4019.6	20.2
60°-70°	4399.3	22.1
70°-80°	2539.9	12.8
80°-90°	760.6	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3057.3	15.4
0°-40°	5203.4	26.2
0°-60°	12172.4	61.3
0°-90°	19872.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	19872.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	6347	6347	6347	6347	6347	
5°	6946	6171	4425	4831	6946	631
15°	5809	4998	1842	1913	5809	1697
25°	7572	6876	987	1023	7572	3546
35°	9618	8851	767	723	9618	6098
45°	11610	10605	626	582	11610	8923
55°	12412	11654	538	511	12412	11199
65°	12536	12553	406	423	12536	11998
75°	6224	6638	273	291	6224	6685
85°	838	899	115	141	838	1162
90°	0	0	0	0	0	

TEST NUMBER: P599038
 CATALOG NUMBER: IFLD-M-SA4B-760-U-SLL

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1
2.5°	6796.7	6770.2	6796.7	6893.6	6920.1	6964.1	6964.1	6902.4	6787.8	6734.9	6646.8
5°	6946.5	6902.4	7122.8	7325.6	7484.3	7466.6	7316.8	7193.3	6964.1	6620.3	6294.2
7.5°	6646.8	6690.9	6849.5	7378.5	7748.7	7819.2	7581.2	7334.4	6840.7	6364.7	5923.9
10°	6082.6	6144.3	6488.1	7034.7	7616.5	7731.1	7581.2	7281.5	6690.9	6100.2	5588.9
12.5°	5809.3	5950.4	6153.1	6814.3	7228.6	7501.9	7431.4	7237.4	6576.3	5879.9	5386.2
15°	5809.3	5844.6	6144.3	6699.7	6937.7	6946.5	6973.0	7008.2	6611.5	5976.8	5315.7
17.5°	5994.5	6091.4	6347.1	6690.9	6734.9	6629.2	6629.2	6779.0	6682.1	6250.1	5571.3
20°	6444.0	6408.8	6743.8	6884.8	6646.8	6382.3	6355.9	6611.5	6761.4	6541.0	6038.5
22.5°	6893.6	7052.3	7325.6	7008.2	6567.5	6214.8	6179.6	6496.9	6999.4	7043.5	6576.3
25°	7572.4	7731.1	7872.1	7484.3	6558.6	6170.8	6197.2	6444.0	7290.3	7757.5	7475.4
27.5°	8304.1	8401.1	8603.8	8004.4	6770.2	6117.9	6144.3	6514.6	7563.6	8224.7	8180.7
30°	8718.4	8824.2	8780.1	8101.3	6911.3	6153.1	6082.6	6611.5	7413.7	8224.7	8639.1
32.5°	9123.9	9062.2	9035.8	8260.0	7087.6	6373.5	6197.2	6814.3	7501.9	8357.0	9229.7
35°	9617.6	9529.4	9458.9	8568.5	7378.5	6585.1	6505.7	7078.7	7695.8	8630.3	9705.7
37.5°	10164.1	10164.1	9820.3	8797.7	7722.3	6928.9	6840.7	7457.8	8004.4	8797.7	10358.1
40°	10807.6	10834.1	10225.8	9106.3	8110.1	7475.4	7449.0	7951.5	8304.1	9044.6	10984.0
42.5°	11283.7	11301.3	10578.4	9220.9	8559.7	8233.6	8348.2	8744.9	8647.9	9265.0	11028.0
45°	11609.8	11521.7	10825.3	9547.0	9053.4	9370.7	9406.0	9520.6	9097.5	9397.2	11204.3
47.5°	11768.5	11750.9	10931.1	9926.1	10093.6	10525.6	10728.3	10569.6	9511.8	9256.1	11204.3
50°	11927.2	11777.3	11028.0	10446.2	11107.4	11980.1	11936.0	11645.1	10084.8	9432.4	11036.8
52.5°	12033.0	11900.8	11222.0	10913.4	12077.1	13064.4	13240.7	12703.0	10754.8	9758.6	11116.2
55°	12412.0	12306.3	11803.8	11548.1	13196.6	14210.4	14236.8	13487.5	11460.0	10296.4	11636.3
57.5°	12870.4	12932.2	12606.0	12447.3	14051.7	15047.8	14950.9	14069.3	12059.4	10948.7	12235.7
60°	13196.6	13293.6	13214.2	13231.9	14474.8	15329.9	15109.6	14430.8	12500.2	11442.4	12967.4
62.5°	13020.3	13214.2	13540.4	13469.9	14492.5	15127.2	14818.6	13954.7	12553.1	12085.9	13522.8
65°	12535.5	12553.1	13187.8	13575.7	13699.1	14078.2	13672.6	12958.6	12006.5	12482.6	13443.4
67.5°	11292.5	11433.5	12006.5	12764.7	12244.6	12332.7	12297.4	11266.0	11177.9	12209.3	12835.2
70°	9970.2	10067.2	10693.0	11583.4	10340.4	9926.1	10005.4	9238.5	9599.9	11363.0	11609.8
72.5°	8242.4	8304.1	9018.1	9802.7	8295.3	7554.8	7739.9	7114.0	7625.3	9943.7	9793.9
75°	6223.7	6338.3	6893.6	7819.2	6109.1	5633.0	5818.1	5562.5	6038.5	8189.5	7598.9
77.5°	4425.3	4337.2	5024.8	6117.9	4592.8	4310.7	4328.3	4372.4	4883.7	6902.4	5456.7
80°	3014.9	3041.3	3658.4	4487.0	3605.5	3561.4	3517.3	3869.9	4099.1	5465.5	3966.9
82.5°	1789.5	1789.5	2468.3	3191.2	2847.4	3208.8	3006.0	3323.4	3208.8	4019.8	2600.5
85°	837.5	837.5	1269.4	2300.8	2203.8	2644.6	2247.9	2512.4	2371.3	2803.3	1172.4
87.5°	141.0	123.4	255.6	1128.4	908.0	1031.4	405.5	1339.9	1489.8	1957.0	290.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599038
 CATALOG NUMBER: IFLD-M-SA4B-760-U-SLL

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1
2.5°	6549.8	6488.1	6364.7	6206.0	6073.8	5906.3	5853.4	5738.8	5580.1	5562.5	5492.0
5°	6170.8	5959.2	5694.7	5368.6	5148.2	4919.0	4725.0	4610.4	4478.2	4460.6	4425.3
7.5°	5756.4	5492.0	5051.2	4663.3	4284.3	3922.8	3746.5	3526.1	3376.3	3261.7	3208.8
10°	5368.6	5121.7	4575.2	4046.3	3711.3	3473.3	3261.7	3032.5	2847.4	2706.3	2653.4
12.5°	5112.9	4822.0	4231.4	3728.9	3482.1	3208.8	2970.8	2724.0	2485.9	2300.8	2203.8
15°	4998.3	4725.0	4125.6	3570.2	3208.8	2829.7	2556.5	2309.6	2018.7	1886.5	1842.4
17.5°	5271.6	4866.1	4090.3	3385.1	2873.8	2441.9	2106.9	1842.4	1630.8	1498.6	1445.7
20°	5624.2	5121.7	4152.0	3164.7	2556.5	2071.6	1701.4	1419.3	1278.2	1181.3	1172.4
22.5°	6073.8	5500.8	4249.0	3006.0	2203.8	1666.1	1331.1	1163.6	1066.7	1057.8	1040.2
25°	6876.0	6188.4	4407.7	2794.5	1921.8	1375.2	1137.2	1040.2	996.1	969.7	987.3
27.5°	7563.6	6638.0	4522.3	2662.2	1807.2	1295.9	1101.9	996.1	952.1	943.2	952.1
30°	7969.1	7052.3	4487.0	2415.4	1578.0	1234.2	1172.4	1137.2	1049.0	978.5	978.5
32.5°	8339.3	7316.8	4478.2	2195.0	1348.8	1031.4	978.5	952.1	1005.0	1040.2	1013.8
35°	8850.6	7731.1	4451.8	2071.6	1251.8	952.1	863.9	793.4	758.1	740.5	766.9
37.5°	9397.2	8013.2	4381.2	2054.0	1198.9	908.0	837.5	766.9	731.7	714.0	705.2
40°	9996.6	8312.9	4301.9	1965.8	1172.4	881.5	811.0	749.3	705.2	678.8	670.0
42.5°	10384.5	8550.9	4222.6	1921.8	1119.6	863.9	784.6	731.7	687.6	652.3	652.3
45°	10604.9	8833.0	4143.2	1877.7	1057.8	872.7	784.6	714.0	661.2	643.5	625.9
47.5°	10701.9	9044.6	4116.8	1807.2	1005.0	837.5	766.9	696.4	643.5	608.3	599.4
50°	10957.5	9494.2	4213.7	1754.3	943.2	802.2	811.0	687.6	634.7	590.6	581.8
52.5°	11107.4	9855.6	4425.3	1674.9	899.2	758.1	793.4	670.0	608.3	564.2	564.2
55°	11653.9	10455.0	4654.5	1613.2	846.3	696.4	731.7	634.7	564.2	537.7	537.7
57.5°	12350.3	11089.7	4848.5	1586.8	811.0	652.3	652.3	617.1	537.7	502.5	493.7
60°	12835.2	11609.8	4963.1	1569.1	775.8	608.3	581.8	617.1	511.3	476.0	467.2
62.5°	12888.1	11310.1	4848.5	1560.3	766.9	564.2	528.9	590.6	484.8	449.6	432.0
65°	12553.1	10701.9	4531.1	1525.1	758.1	520.1	493.7	511.3	449.6	423.1	405.5
67.5°	11883.1	9714.5	4072.7	1507.4	749.3	484.8	449.6	440.8	414.3	387.9	370.2
70°	10322.8	8427.5	3535.0	1428.1	731.7	458.4	405.5	396.7	370.2	352.6	343.8
72.5°	8665.5	6893.6	2917.9	1322.3	696.4	414.3	370.2	352.6	343.8	317.4	308.5
75°	6638.0	5306.9	2336.1	1172.4	608.3	370.2	326.2	308.5	299.7	282.1	273.3
77.5°	4663.3	3949.3	1727.8	952.1	511.3	335.0	290.9	273.3	264.5	238.0	238.0
80°	3164.7	2768.0	1172.4	661.2	396.7	273.3	255.6	238.0	220.4	202.8	202.8
82.5°	1965.8	1939.4	846.3	432.0	290.9	220.4	202.8	202.8	176.3	158.7	158.7
85°	899.2	1190.1	590.6	299.7	220.4	167.5	167.5	158.7	141.0	114.6	114.6
87.5°	282.1	396.7	308.5	132.2	123.4	97.0	97.0	88.2	88.2	70.5	70.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599038
 CATALOG NUMBER: IFLD-M-SA4B-760-U-SLL

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1
2.5°	5562.5	5553.7	5553.7	5518.4	5606.6	5606.6	5659.5	5615.4	5641.8	5650.7	5721.2
5°	4416.5	4487.0	4539.9	4645.7	4707.4	4733.9	4733.9	4804.4	4777.9	4830.8	4936.6
7.5°	3235.2	3323.4	3482.1	3614.3	3720.1	3755.3	3746.5	3764.2	3790.6	3728.9	3746.5
10°	2618.2	2556.5	2609.4	2732.8	2829.7	2944.3	2856.2	2847.4	2873.8	2847.4	2900.3
12.5°	2186.2	2115.7	2071.6	2071.6	2142.1	2195.0	2168.6	2212.7	2309.6	2336.1	2397.8
15°	1771.9	1710.2	1674.9	1630.8	1701.4	1719.0	1745.4	1807.2	1877.7	1912.9	1983.5
17.5°	1419.3	1419.3	1419.3	1384.0	1410.5	1436.9	1445.7	1525.1	1533.9	1569.1	1595.6
20°	1163.6	1190.1	1234.2	1251.8	1278.2	1278.2	1260.6	1304.7	1269.4	1295.9	1313.5
22.5°	1049.0	1084.3	1101.9	1110.7	1146.0	1154.8	1110.7	1119.6	1128.4	1101.9	1110.7
25°	987.3	1005.0	987.3	996.1	1005.0	987.3	996.1	1013.8	1005.0	1022.6	1013.8
27.5°	960.9	943.2	934.4	925.6	925.6	908.0	916.8	916.8	934.4	943.2	943.2
30°	960.9	934.4	899.2	872.7	872.7	846.3	863.9	881.5	890.4	908.0	908.0
32.5°	987.3	934.4	872.7	846.3	819.8	802.2	819.8	846.3	881.5	890.4	899.2
35°	784.6	811.0	802.2	766.9	758.1	758.1	749.3	749.3	722.9	722.9	714.0
37.5°	705.2	696.4	714.0	722.9	731.7	705.2	705.2	670.0	661.2	670.0	670.0
40°	661.2	661.2	661.2	687.6	696.4	678.8	652.3	634.7	634.7	634.7	643.5
42.5°	643.5	625.9	617.1	634.7	661.2	643.5	617.1	608.3	608.3	617.1	617.1
45°	617.1	608.3	599.4	590.6	625.9	599.4	590.6	581.8	581.8	581.8	590.6
47.5°	590.6	581.8	564.2	564.2	573.0	564.2	555.4	555.4	555.4	573.0	573.0
50°	573.0	564.2	546.6	546.6	546.6	546.6	537.7	537.7	537.7	546.6	555.4
52.5°	546.6	537.7	528.9	520.1	520.1	520.1	520.1	520.1	520.1	528.9	537.7
55°	520.1	511.3	502.5	502.5	511.3	511.3	502.5	511.3	502.5	511.3	520.1
57.5°	493.7	484.8	476.0	484.8	493.7	484.8	484.8	484.8	484.8	484.8	493.7
60°	458.4	458.4	458.4	458.4	476.0	476.0	476.0	476.0	458.4	467.2	476.0
62.5°	440.8	432.0	432.0	440.8	449.6	449.6	458.4	449.6	440.8	449.6	449.6
65°	405.5	405.5	405.5	414.3	414.3	423.1	423.1	423.1	414.3	423.1	423.1
67.5°	379.1	379.1	379.1	379.1	396.7	396.7	396.7	396.7	387.9	387.9	396.7
70°	335.0	343.8	335.0	352.6	370.2	361.4	370.2	370.2	361.4	352.6	370.2
72.5°	308.5	308.5	308.5	308.5	335.0	335.0	335.0	343.8	335.0	326.2	335.0
75°	273.3	273.3	273.3	282.1	299.7	299.7	299.7	299.7	299.7	290.9	290.9
77.5°	238.0	246.8	238.0	246.8	264.5	255.6	264.5	273.3	264.5	255.6	255.6
80°	202.8	202.8	202.8	211.6	220.4	220.4	220.4	229.2	220.4	211.6	211.6
82.5°	158.7	158.7	167.5	167.5	176.3	176.3	176.3	185.1	176.3	167.5	167.5
85°	123.4	123.4	123.4	132.2	132.2	141.0	141.0	149.9	149.9	141.0	141.0
87.5°	79.3	70.5	79.3	79.3	88.2	88.2	79.3	70.5	79.3	70.5	61.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599038
 CATALOG NUMBER: IFLD-M-SA4B-760-U-SLL

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1	6347.1
2.5°	5791.7	5950.4	6065.0	6144.3	6258.9	6479.3	6567.5	6726.1	6770.2	6796.7
5°	4980.7	5148.2	5395.0	5571.3	5774.1	6188.4	6505.7	6743.8	6849.5	6946.5
7.5°	3905.2	4125.6	4381.2	4610.4	4945.4	5456.7	5871.0	6364.7	6549.8	6646.8
10°	3050.1	3252.9	3535.0	3817.1	4284.3	4716.2	5306.9	5756.4	6012.1	6082.6
12.5°	2574.1	2812.1	3147.1	3490.9	3781.8	4275.5	4874.9	5527.2	5765.3	5809.3
15°	2186.2	2512.4	2856.2	3208.8	3543.8	3975.7	4619.3	5412.6	5765.3	5809.3
17.5°	1807.2	2098.1	2503.6	2882.6	3270.5	3861.1	4663.3	5509.6	5862.2	5994.5
20°	1436.9	1719.0	2036.4	2512.4	3041.3	3667.2	4760.3	5835.8	6303.0	6444.0
22.5°	1190.1	1313.5	1622.0	2080.4	2706.3	3535.0	4857.3	6347.1	6840.7	6893.6
25°	1040.2	1128.4	1322.3	1754.3	2441.9	3446.8	5086.5	6937.7	7572.4	7572.4
27.5°	969.7	1005.0	1137.2	1525.1	2256.7	3367.5	5315.7	7590.0	8180.7	8304.1
30°	952.1	1040.2	1110.7	1357.6	2054.0	3147.1	5527.2	8101.3	8709.6	8718.4
32.5°	934.4	916.8	969.7	1181.3	1807.2	2917.9	5703.5	8621.4	9097.5	9123.9
35°	731.7	766.9	855.1	1040.2	1622.0	2750.4	5791.7	8903.5	9591.1	9617.6
37.5°	687.6	731.7	802.2	960.9	1498.6	2609.4	5818.1	9450.1	10111.2	10164.1
40°	670.0	705.2	758.1	890.4	1401.6	2433.0	5871.0	10014.3	10878.2	10807.6
42.5°	634.7	678.8	731.7	855.1	1322.3	2300.8	5879.9	10322.8	11283.7	11283.7
45°	625.9	652.3	714.0	855.1	1234.2	2186.2	5738.8	10631.3	11750.9	11609.8
47.5°	590.6	643.5	696.4	828.6	1128.4	2071.6	5571.3	10790.0	11812.6	11768.5
50°	581.8	634.7	722.9	784.6	1066.7	2018.7	5536.1	11186.7	11936.0	11927.2
52.5°	564.2	617.1	749.3	749.3	987.3	1948.2	5703.5	11363.0	11962.5	12033.0
55°	537.7	617.1	696.4	687.6	916.8	1860.0	5888.7	11821.4	12429.7	12412.0
57.5°	520.1	599.4	661.2	625.9	837.5	1798.3	6161.9	12262.2	12993.9	12870.4
60°	493.7	599.4	590.6	581.8	775.8	1745.4	6391.1	12350.3	13117.3	13196.6
62.5°	476.0	625.9	520.1	537.7	722.9	1719.0	6294.2	11689.2	12949.8	13020.3
65°	458.4	537.7	476.0	493.7	705.2	1666.1	5915.1	10895.8	12226.9	12535.5
67.5°	423.1	440.8	440.8	458.4	687.6	1542.7	5139.4	9467.7	11125.0	11292.5
70°	387.9	396.7	396.7	423.1	670.0	1401.6	4240.2	8189.5	9652.8	9970.2
72.5°	352.6	352.6	352.6	387.9	617.1	1287.0	3490.9	6294.2	8022.0	8242.4
75°	308.5	308.5	308.5	343.8	555.4	1172.4	2750.4	4681.0	5906.3	6223.7
77.5°	273.3	273.3	264.5	308.5	484.8	952.1	1983.5	3305.8	4160.9	4425.3
80°	229.2	220.4	220.4	246.8	379.1	687.6	1278.2	2336.1	2900.3	3014.9
82.5°	185.1	176.3	167.5	185.1	273.3	432.0	793.4	1630.8	1860.0	1789.5
85°	176.3	185.1	149.9	141.0	193.9	282.1	502.5	1005.0	837.5	837.5
87.5°	70.5	61.7	61.7	52.9	97.0	105.8	220.4	185.1	141.0	141.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)