

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P598993

Luminaire Tested: **IFLD-S-SA2A-750-U-SLL**

Issue Date: 05/03/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P598993
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/03/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-S-SA2A-750-U-SLL
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens
 Light Source: (32) 5000K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 8032.8 lumens
 Efficiency: N/A
 Efficacy: 125.9 lumens/watt
 Spacing Criteria (0/90/45): 1.12 / 0.52 / 0.8
 Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
 CIE Type: Direct

Input Watts (W): 63.8
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P598993
CATALOG NUMBER: IFLD-S-SA2A-750-U-SLL

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°

TEST NUMBER: P598993

CATALOG NUMBER: IFLD-S-SA2A-750-U-SLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	106	100	94	89	103	97	92	88	93	89	85	89	85	82	85	82	80	80	80	80	77
2	94	83	75	68	91	81	74	67	78	71	65	74	69	64	71	66	62	62	62	62	60
3	84	71	61	53	81	69	60	53	66	58	52	63	56	51	60	55	50	50	50	50	47
4	75	61	51	43	73	60	50	42	57	48	42	54	47	41	52	46	40	40	40	40	38
5	68	53	43	35	66	52	42	35	50	41	34	48	40	34	46	39	34	34	34	34	31
6	63	47	37	30	60	46	37	29	44	36	29	42	35	29	41	34	29	29	29	29	26
7	58	42	32	25	56	41	32	25	40	31	25	38	31	25	37	30	25	25	25	25	22
8	53	38	29	22	52	37	28	22	36	28	22	35	27	22	33	27	22	22	22	22	19
9	50	35	26	20	48	34	26	20	33	25	19	32	25	19	31	24	19	19	19	19	17
10	46	32	23	18	45	31	23	18	30	23	17	29	22	17	28	22	17	17	17	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	55232	55232	55232	55232
5°	60679	53904	38656	42198
10°	53747	47438	23447	25161
15°	52337	45029	16597	17235
20°	59675	52082	10857	12000
25°	72707	66020	9480	9820
30°	87605	80076	9831	9123
35°	102169	94022	8147	7679
40°	122772	113560	7610	7211
45°	142878	130508	7703	7161
50°	161469	148343	7877	7398
55°	188309	176809	8160	7758
60°	229676	223386	8133	8133
65°	258114	258476	8349	8711
70°	253674	262643	8749	8969
75°	209249	223181	9191	9782
80°	151087	158600	10166	10600
85°	83611	89786	11436	14079

TEST NUMBER: P598993
 CATALOG NUMBER: IFLD-S-SA2A-750-U-SLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.3	2.5
10°-20°	420.8	5.2
20°-30°	615.7	7.7
30°-40°	867.5	10.8
40°-50°	1192.2	14.8
50°-60°	1624.8	20.2
60°-70°	1778.3	22.1
70°-80°	1026.7	12.8
80°-90°	307.4	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1235.8	15.4
0°-40°	2103.3	26.2
0°-60°	4920.4	61.3
0°-90°	8032.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8032.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2566	2566	2566	2566	2566	
5°	2808	2494	1789	1953	2808	255
15°	2348	2020	745	773	2348	686
25°	3061	2779	399	413	3061	1433
35°	3888	3578	310	292	3888	2465
45°	4693	4287	253	235	4693	3607
55°	5017	4711	217	207	5017	4527
65°	5067	5074	164	171	5067	4850
75°	2516	2683	110	118	2516	2702
85°	338	364	46	57	338	470
90°	0	0	0	0	0	

TEST NUMBER: P598993
 CATALOG NUMBER: IFLD-S-SA2A-750-U-SLL

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6
2.5°	2747.4	2736.7	2747.4	2786.6	2797.2	2815.1	2815.1	2790.1	2743.8	2722.4	2686.8
5°	2807.9	2790.1	2879.2	2961.2	3025.3	3018.2	2957.6	2907.7	2815.1	2676.1	2544.2
7.5°	2686.8	2704.6	2768.7	2982.5	3132.2	3160.7	3064.5	2964.7	2765.2	2572.8	2394.6
10°	2458.7	2483.7	2622.6	2843.6	3078.8	3125.1	3064.5	2943.3	2704.6	2465.9	2259.2
12.5°	2348.3	2405.3	2487.2	2754.5	2922.0	3032.4	3003.9	2925.5	2658.3	2376.8	2177.2
15°	2348.3	2362.5	2483.7	2708.2	2804.4	2807.9	2818.6	2832.9	2672.5	2416.0	2148.7
17.5°	2423.1	2462.3	2565.6	2704.6	2722.4	2679.7	2679.7	2740.2	2701.0	2526.4	2252.1
20°	2604.8	2590.6	2726.0	2783.0	2686.8	2579.9	2569.2	2672.5	2733.1	2644.0	2440.9
22.5°	2786.6	2850.7	2961.2	2832.9	2654.7	2512.2	2497.9	2626.2	2829.3	2847.1	2658.3
25°	3060.9	3125.1	3182.1	3025.3	2651.1	2494.4	2505.1	2604.8	2946.9	3135.8	3021.7
27.5°	3356.7	3395.9	3477.9	3235.5	2736.7	2473.0	2483.7	2633.3	3057.4	3324.6	3306.8
30°	3524.2	3566.9	3549.1	3274.7	2793.7	2487.2	2458.7	2672.5	2996.8	3324.6	3492.1
32.5°	3688.1	3663.1	3652.5	3338.9	2865.0	2576.3	2505.1	2754.5	3032.4	3378.1	3730.9
35°	3887.6	3852.0	3823.5	3463.6	2982.5	2661.8	2629.8	2861.4	3110.8	3488.5	3923.3
37.5°	4108.6	4108.6	3969.6	3556.2	3121.5	2800.8	2765.2	3014.6	3235.5	3556.2	4187.0
40°	4368.7	4379.4	4133.5	3681.0	3278.3	3021.7	3011.1	3214.2	3356.7	3656.0	4440.0
42.5°	4561.1	4568.2	4276.0	3727.3	3460.0	3328.2	3374.5	3534.9	3495.7	3745.1	4457.8
45°	4693.0	4657.3	4375.8	3859.1	3659.6	3787.9	3802.1	3848.4	3677.4	3798.6	4529.0
47.5°	4757.1	4750.0	4418.6	4012.4	4080.1	4254.7	4336.6	4272.5	3844.9	3741.5	4529.0
50°	4821.2	4760.7	4457.8	4222.6	4489.9	4842.6	4824.8	4707.2	4076.5	3812.8	4461.3
52.5°	4864.0	4810.6	4536.2	4411.5	4881.8	5280.9	5352.2	5134.8	4347.3	3944.7	4493.4
55°	5017.2	4974.5	4771.4	4668.0	5334.4	5744.2	5754.8	5452.0	4632.4	4162.0	4703.7
57.5°	5202.5	5227.5	5095.6	5031.5	5680.0	6082.7	6043.5	5687.1	4874.7	4425.7	4946.0
60°	5334.4	5373.6	5341.5	5348.6	5851.1	6196.7	6107.6	5833.2	5052.9	4625.3	5241.7
62.5°	5263.1	5341.5	5473.3	5444.8	5858.2	6114.7	5990.0	5640.8	5074.2	4885.4	5466.2
65°	5067.1	5074.2	5330.8	5487.6	5537.5	5690.7	5526.8	5238.2	4853.3	5045.7	5434.1
67.5°	4564.7	4621.7	4853.3	5159.8	4949.5	4985.2	4970.9	4554.0	4518.4	4935.3	5188.3
70°	4030.2	4069.4	4322.4	4682.3	4179.8	4012.4	4044.4	3734.4	3880.5	4593.2	4693.0
72.5°	3331.8	3356.7	3645.3	3962.5	3353.1	3053.8	3128.6	2875.6	3082.3	4019.5	3958.9
75°	2515.7	2562.1	2786.6	3160.7	2469.4	2277.0	2351.8	2248.5	2440.9	3310.4	3071.6
77.5°	1788.8	1753.2	2031.1	2473.0	1856.5	1742.5	1749.6	1767.4	1974.1	2790.1	2205.7
80°	1218.7	1229.4	1478.8	1813.8	1457.4	1439.6	1421.8	1564.3	1657.0	2209.3	1603.5
82.5°	723.4	723.4	997.7	1289.9	1151.0	1297.1	1215.1	1343.4	1297.1	1624.9	1051.2
85°	338.5	338.5	513.1	930.0	890.8	1069.0	908.7	1015.6	958.5	1133.2	473.9
87.5°	57.0	49.9	103.3	456.1	367.0	416.9	163.9	541.6	602.2	791.1	117.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598993
 CATALOG NUMBER: IFLD-S-SA2A-750-U-SLL

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6
2.5°	2647.6	2622.6	2572.8	2508.6	2455.2	2387.5	2366.1	2319.8	2255.6	2248.5	2220.0
5°	2494.4	2408.8	2301.9	2170.1	2081.0	1988.4	1910.0	1863.6	1810.2	1803.1	1788.8
7.5°	2326.9	2220.0	2041.8	1885.0	1731.8	1585.7	1514.4	1425.3	1364.8	1318.4	1297.1
10°	2170.1	2070.3	1849.4	1635.6	1500.2	1404.0	1318.4	1225.8	1151.0	1094.0	1072.6
12.5°	2066.8	1949.2	1710.4	1507.3	1407.5	1297.1	1200.9	1101.1	1004.9	930.0	890.8
15°	2020.4	1910.0	1667.7	1443.2	1297.1	1143.8	1033.4	933.6	816.0	762.6	744.7
17.5°	2130.9	1967.0	1653.4	1368.3	1161.7	987.1	851.6	744.7	659.2	605.8	584.4
20°	2273.4	2070.3	1678.3	1279.3	1033.4	837.4	687.7	573.7	516.7	477.5	473.9
22.5°	2455.2	2223.5	1717.5	1215.1	890.8	673.5	538.1	470.4	431.2	427.6	420.5
25°	2779.4	2501.5	1781.7	1129.6	776.8	555.9	459.7	420.5	402.7	392.0	399.1
27.5°	3057.4	2683.2	1828.0	1076.1	730.5	523.8	445.4	402.7	384.8	381.3	384.8
30°	3221.3	2850.7	1813.8	976.4	637.8	498.9	473.9	459.7	424.0	395.5	395.5
32.5°	3371.0	2957.6	1810.2	887.3	545.2	416.9	395.5	384.8	406.2	420.5	409.8
35°	3577.6	3125.1	1799.5	837.4	506.0	384.8	349.2	320.7	306.5	299.3	310.0
37.5°	3798.6	3239.1	1771.0	830.3	484.6	367.0	338.5	310.0	295.8	288.6	285.1
40°	4040.9	3360.3	1738.9	794.6	473.9	356.3	327.8	302.9	285.1	274.4	270.8
42.5°	4197.7	3456.5	1706.9	776.8	452.5	349.2	317.1	295.8	277.9	263.7	263.7
45°	4286.7	3570.5	1674.8	759.0	427.6	352.8	317.1	288.6	267.3	260.1	253.0
47.5°	4325.9	3656.0	1664.1	730.5	406.2	338.5	310.0	281.5	260.1	245.9	242.3
50°	4429.3	3837.8	1703.3	709.1	381.3	324.3	327.8	277.9	256.6	238.7	235.2
52.5°	4489.9	3983.9	1788.8	677.0	363.5	306.5	320.7	270.8	245.9	228.1	228.1
55°	4710.8	4226.2	1881.5	652.1	342.1	281.5	295.8	256.6	228.1	217.4	217.4
57.5°	4992.3	4482.7	1959.9	641.4	327.8	263.7	263.7	249.4	217.4	203.1	199.5
60°	5188.3	4693.0	2006.2	634.3	313.6	245.9	235.2	249.4	206.7	192.4	188.9
62.5°	5209.7	4571.8	1959.9	630.7	310.0	228.1	213.8	238.7	196.0	181.7	174.6
65°	5074.2	4325.9	1831.6	616.5	306.5	210.2	199.5	206.7	181.7	171.0	163.9
67.5°	4803.4	3926.8	1646.3	609.3	302.9	196.0	181.7	178.2	167.5	156.8	149.7
70°	4172.7	3406.6	1428.9	577.3	295.8	185.3	163.9	160.4	149.7	142.5	139.0
72.5°	3502.8	2786.6	1179.5	534.5	281.5	167.5	149.7	142.5	139.0	128.3	124.7
75°	2683.2	2145.2	944.3	473.9	245.9	149.7	131.8	124.7	121.2	114.0	110.5
77.5°	1885.0	1596.4	698.4	384.8	206.7	135.4	117.6	110.5	106.9	96.2	96.2
80°	1279.3	1118.9	473.9	267.3	160.4	110.5	103.3	96.2	89.1	82.0	82.0
82.5°	794.6	783.9	342.1	174.6	117.6	89.1	82.0	82.0	71.3	64.1	64.1
85°	363.5	481.1	238.7	121.2	89.1	67.7	67.7	64.1	57.0	46.3	46.3
87.5°	114.0	160.4	124.7	53.5	49.9	39.2	39.2	35.6	35.6	28.5	28.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598993
 CATALOG NUMBER: IFLD-S-SA2A-750-U-SLL

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6
2.5°	2248.5	2244.9	2244.9	2230.7	2266.3	2266.3	2287.7	2269.9	2280.6	2284.1	2312.6
5°	1785.2	1813.8	1835.1	1877.9	1902.8	1913.5	1913.5	1942.0	1931.3	1952.7	1995.5
7.5°	1307.8	1343.4	1407.5	1461.0	1503.7	1518.0	1514.4	1521.6	1532.3	1507.3	1514.4
10°	1058.3	1033.4	1054.8	1104.6	1143.8	1190.2	1154.5	1151.0	1161.7	1151.0	1172.3
12.5°	883.7	855.2	837.4	837.4	865.9	887.3	876.6	894.4	933.6	944.3	969.2
15°	716.2	691.3	677.0	659.2	687.7	694.9	705.5	730.5	759.0	773.3	801.8
17.5°	573.7	573.7	573.7	559.4	570.1	580.8	584.4	616.5	620.0	634.3	645.0
20°	470.4	481.1	498.9	506.0	516.7	516.7	509.6	527.4	513.1	523.8	530.9
22.5°	424.0	438.3	445.4	449.0	463.2	466.8	449.0	452.5	456.1	445.4	449.0
25°	399.1	406.2	399.1	402.7	406.2	399.1	402.7	409.8	406.2	413.4	409.8
27.5°	388.4	381.3	377.7	374.2	374.2	367.0	370.6	370.6	377.7	381.3	381.3
30°	388.4	377.7	363.5	352.8	352.8	342.1	349.2	356.3	359.9	367.0	367.0
32.5°	399.1	377.7	352.8	342.1	331.4	324.3	331.4	342.1	356.3	359.9	363.5
35°	317.1	327.8	324.3	310.0	306.5	306.5	302.9	302.9	292.2	292.2	288.6
37.5°	285.1	281.5	288.6	292.2	295.8	285.1	285.1	270.8	267.3	270.8	270.8
40°	267.3	267.3	267.3	277.9	281.5	274.4	263.7	256.6	256.6	256.6	260.1
42.5°	260.1	253.0	249.4	256.6	267.3	260.1	249.4	245.9	245.9	249.4	249.4
45°	249.4	245.9	242.3	238.7	253.0	242.3	238.7	235.2	235.2	235.2	238.7
47.5°	238.7	235.2	228.1	228.1	231.6	228.1	224.5	224.5	224.5	231.6	231.6
50°	231.6	228.1	220.9	220.9	220.9	220.9	217.4	217.4	217.4	220.9	224.5
52.5°	220.9	217.4	213.8	210.2	210.2	210.2	210.2	210.2	210.2	213.8	217.4
55°	210.2	206.7	203.1	203.1	206.7	206.7	203.1	206.7	203.1	206.7	210.2
57.5°	199.5	196.0	192.4	196.0	199.5	196.0	196.0	196.0	196.0	196.0	199.5
60°	185.3	185.3	185.3	185.3	192.4	192.4	192.4	192.4	185.3	188.9	192.4
62.5°	178.2	174.6	174.6	178.2	181.7	181.7	185.3	181.7	178.2	181.7	181.7
65°	163.9	163.9	163.9	167.5	167.5	171.0	171.0	171.0	167.5	171.0	171.0
67.5°	153.2	153.2	153.2	153.2	160.4	160.4	160.4	160.4	156.8	156.8	160.4
70°	135.4	139.0	135.4	142.5	149.7	146.1	149.7	149.7	146.1	142.5	149.7
72.5°	124.7	124.7	124.7	124.7	135.4	135.4	135.4	139.0	135.4	131.8	135.4
75°	110.5	110.5	110.5	114.0	121.2	121.2	121.2	121.2	121.2	117.6	117.6
77.5°	96.2	99.8	96.2	99.8	106.9	103.3	106.9	110.5	106.9	103.3	103.3
80°	82.0	82.0	82.0	85.5	89.1	89.1	89.1	92.6	89.1	85.5	85.5
82.5°	64.1	64.1	67.7	67.7	71.3	71.3	71.3	74.8	71.3	67.7	67.7
85°	49.9	49.9	49.9	53.5	53.5	57.0	57.0	60.6	60.6	57.0	57.0
87.5°	32.1	28.5	32.1	32.1	35.6	35.6	32.1	28.5	32.1	28.5	24.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598993
 CATALOG NUMBER: IFLD-S-SA2A-750-U-SLL

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6	2565.6
2.5°	2341.1	2405.3	2451.6	2483.7	2530.0	2619.1	2654.7	2718.9	2736.7	2747.4
5°	2013.3	2081.0	2180.8	2252.1	2334.0	2501.5	2629.8	2726.0	2768.7	2807.9
7.5°	1578.6	1667.7	1771.0	1863.6	1999.1	2205.7	2373.2	2572.8	2647.6	2686.8
10°	1232.9	1314.9	1428.9	1542.9	1731.8	1906.4	2145.2	2326.9	2430.2	2458.7
12.5°	1040.5	1136.7	1272.1	1411.1	1528.7	1728.2	1970.5	2234.2	2330.4	2348.3
15°	883.7	1015.6	1154.5	1297.1	1432.5	1607.1	1867.2	2187.9	2330.4	2348.3
17.5°	730.5	848.1	1012.0	1165.2	1322.0	1560.8	1885.0	2227.1	2369.6	2423.1
20°	580.8	694.9	823.1	1015.6	1229.4	1482.4	1924.2	2359.0	2547.8	2604.8
22.5°	481.1	530.9	655.7	841.0	1094.0	1428.9	1963.4	2565.6	2765.2	2786.6
25°	420.5	456.1	534.5	709.1	987.1	1393.3	2056.1	2804.4	3060.9	3060.9
27.5°	392.0	406.2	459.7	616.5	912.2	1361.2	2148.7	3068.1	3306.8	3356.7
30°	384.8	420.5	449.0	548.8	830.3	1272.1	2234.2	3274.7	3520.6	3524.2
32.5°	377.7	370.6	392.0	477.5	730.5	1179.5	2305.5	3485.0	3677.4	3688.1
35°	295.8	310.0	345.6	420.5	655.7	1111.8	2341.1	3599.0	3877.0	3887.6
37.5°	277.9	295.8	324.3	388.4	605.8	1054.8	2351.8	3819.9	4087.2	4108.6
40°	270.8	285.1	306.5	359.9	566.6	983.5	2373.2	4048.0	4397.2	4368.7
42.5°	256.6	274.4	295.8	345.6	534.5	930.0	2376.8	4172.7	4561.1	4561.1
45°	253.0	263.7	288.6	345.6	498.9	883.7	2319.8	4297.4	4750.0	4693.0
47.5°	238.7	260.1	281.5	335.0	456.1	837.4	2252.1	4361.6	4774.9	4757.1
50°	235.2	256.6	292.2	317.1	431.2	816.0	2237.8	4521.9	4824.8	4821.2
52.5°	228.1	249.4	302.9	302.9	399.1	787.5	2305.5	4593.2	4835.5	4864.0
55°	217.4	249.4	281.5	277.9	370.6	751.9	2380.3	4778.5	5024.4	5017.2
57.5°	210.2	242.3	267.3	253.0	338.5	726.9	2490.8	4956.7	5252.4	5202.5
60°	199.5	242.3	238.7	235.2	313.6	705.5	2583.4	4992.3	5302.3	5334.4
62.5°	192.4	253.0	210.2	217.4	292.2	694.9	2544.2	4725.0	5234.6	5263.1
65°	185.3	217.4	192.4	199.5	285.1	673.5	2391.0	4404.3	4942.4	5067.1
67.5°	171.0	178.2	178.2	185.3	277.9	623.6	2077.4	3827.1	4497.0	4564.7
70°	156.8	160.4	160.4	171.0	270.8	566.6	1714.0	3310.4	3901.9	4030.2
72.5°	142.5	142.5	142.5	156.8	249.4	520.3	1411.1	2544.2	3242.7	3331.8
75°	124.7	124.7	124.7	139.0	224.5	473.9	1111.8	1892.2	2387.5	2515.7
77.5°	110.5	110.5	106.9	124.7	196.0	384.8	801.8	1336.3	1681.9	1788.8
80°	92.6	89.1	89.1	99.8	153.2	277.9	516.7	944.3	1172.3	1218.7
82.5°	74.8	71.3	67.7	74.8	110.5	174.6	320.7	659.2	751.9	723.4
85°	71.3	74.8	60.6	57.0	78.4	114.0	203.1	406.2	338.5	338.5
87.5°	28.5	24.9	24.9	21.4	39.2	42.8	89.1	74.8	57.0	57.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)