

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS
Report Number: P598995

Luminaire Tested: **IFLD-S-SA2C-750-U-SLL**

Issue Date: 05/03/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P598995
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/03/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-S-SA2C-750-U-SLL
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens
 Light Source: (32) 5000K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 12366.8 lumens
 Efficiency: N/A
 Efficacy: 114.3 lumens/watt
 Spacing Criteria (0/90/45): 1.12 / 0.52 / 0.8
 Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
 CIE Type: Direct

Input Watts (W): 108.2
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P598995
CATALOG NUMBER: IFLD-S-SA2C-750-U-SLL

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ··· 90°-270° - · 135°-315°

TEST NUMBER: P598995
 CATALOG NUMBER: IFLD-S-SA2C-750-U-SLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	106	100	94	89	103	97	92	88	93	89	85	89	85	82	85	82	80	77	77	77
2	94	83	75	68	91	81	74	67	78	71	65	74	69	64	71	66	62	60	60	60
3	84	71	61	53	81	69	60	53	66	58	52	63	56	51	60	55	50	47	47	47
4	75	61	51	43	73	60	50	42	57	48	42	54	47	41	52	46	40	38	38	38
5	68	53	43	35	66	52	42	35	50	41	34	48	40	34	46	39	34	31	31	31
6	63	47	37	30	60	46	37	29	44	36	29	42	35	29	41	34	29	26	26	26
7	58	42	32	25	56	41	32	25	40	31	25	38	31	25	37	30	25	22	22	22
8	53	38	29	22	52	37	28	22	36	28	22	35	27	22	33	27	22	19	19	19
9	50	35	26	20	48	34	26	20	33	25	19	32	25	19	31	24	19	17	17	17
10	46	32	23	18	45	31	23	18	30	23	17	29	22	17	28	22	17	15	15	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	85033	85033	85033	85033
5°	93418	82987	59514	64966
10°	82746	73034	36097	38736
15°	80575	69324	25555	26533
20°	91871	80183	16715	18474
25°	111935	101643	14594	15117
30°	134871	123279	15136	14047
35°	157295	144751	12544	11821
40°	189012	174829	11716	11101
45°	219965	200924	11858	11024
50°	248590	228381	12127	11390
55°	289910	272202	12558	11943
60°	353595	343911	12521	12521
65°	397377	397937	12857	13412
70°	390537	404353	13470	13810
75°	322153	343596	14148	15055
80°	232600	244166	15645	16327
85°	128739	138224	17611	21687

TEST NUMBER: P598995
 CATALOG NUMBER: IFLD-S-SA2C-750-U-SLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	306.9	2.5
10°-20°	647.9	5.2
20°-30°	947.9	7.7
30°-40°	1335.5	10.8
40°-50°	1835.4	14.8
50°-60°	2501.5	20.2
60°-70°	2737.8	22.1
70°-80°	1580.6	12.8
80°-90°	473.3	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1902.6	15.4
0°-40°	3238.2	26.2
0°-60°	7575.1	61.3
0°-90°	12366.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12366.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	3950	3950	3950	3950	3950	
5°	4323	3840	2754	3006	4323	393
15°	3615	3110	1147	1190	3615	1056
25°	4712	4279	614	636	4712	2207
35°	5985	5508	477	450	5985	3795
45°	7225	6600	390	362	7225	5553
55°	7724	7252	335	318	7724	6969
65°	7801	7812	252	263	7801	7466
75°	3873	4131	170	181	3873	4160
85°	521	560	71	88	521	723
90°	0	0	0	0	0	

TEST NUMBER: P598995
 CATALOG NUMBER: IFLD-S-SA2C-750-U-SLL

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9
2.5°	4229.7	4213.2	4229.7	4290.0	4306.5	4333.9	4333.9	4295.5	4224.2	4191.3	4136.4
5°	4322.9	4295.5	4432.7	4558.8	4657.6	4646.6	4553.4	4476.5	4333.9	4120.0	3917.0
7.5°	4136.4	4163.8	4262.6	4591.8	4822.2	4866.1	4717.9	4564.3	4257.1	3960.9	3686.6
10°	3785.3	3823.7	4037.7	4377.8	4739.9	4811.2	4717.9	4531.4	4163.8	3796.3	3478.1
12.5°	3615.3	3703.0	3829.2	4240.7	4498.5	4668.6	4624.7	4504.0	4092.5	3659.1	3351.9
15°	3615.3	3637.2	3823.7	4169.3	4317.5	4322.9	4339.4	4361.3	4114.5	3719.5	3308.0
17.5°	3730.5	3790.8	3949.9	4163.8	4191.3	4125.4	4125.4	4218.7	4158.4	3889.6	3467.1
20°	4010.2	3988.3	4196.8	4284.5	4136.4	3971.8	3955.4	4114.5	4207.7	4070.6	3757.9
22.5°	4290.0	4388.8	4558.8	4361.3	4087.0	3867.6	3845.7	4043.2	4355.9	4383.3	4092.5
25°	4712.4	4811.2	4899.0	4657.6	4081.6	3840.2	3856.6	4010.2	4536.9	4827.7	4652.1
27.5°	5167.8	5228.1	5354.3	4981.3	4213.2	3807.3	3823.7	4054.1	4707.0	5118.4	5091.0
30°	5425.6	5491.5	5464.0	5041.6	4301.0	3829.2	3785.3	4114.5	4613.7	5118.4	5376.2
32.5°	5678.0	5639.6	5623.1	5140.4	4410.7	3966.4	3856.6	4240.7	4668.6	5200.7	5743.8
35°	5985.2	5930.3	5886.4	5332.4	4591.8	4098.0	4048.6	4405.2	4789.2	5370.8	6040.0
37.5°	6325.3	6325.3	6111.4	5475.0	4805.7	4312.0	4257.1	4641.1	4981.3	5475.0	6446.0
40°	6725.8	6742.3	6363.7	5667.0	5047.1	4652.1	4635.6	4948.3	5167.8	5628.6	6835.5
42.5°	7022.0	7033.0	6583.2	5738.3	5326.9	5123.9	5195.2	5442.1	5381.7	5765.8	6862.9
45°	7225.0	7170.2	6736.8	5941.3	5634.1	5831.6	5853.5	5924.8	5661.5	5848.0	6972.7
47.5°	7323.8	7312.8	6802.6	6177.2	6281.4	6550.2	6676.4	6577.7	5919.4	5760.3	6972.7
50°	7422.5	7329.3	6862.9	6500.9	6912.3	7455.4	7428.0	7247.0	6275.9	5870.0	6868.4
52.5°	7488.3	7406.1	6983.6	6791.6	7515.8	8130.2	8239.9	7905.3	6692.9	6073.0	6917.8
55°	7724.2	7658.4	7345.7	7186.6	8212.5	8843.4	8859.8	8393.5	7131.8	6407.6	7241.5
57.5°	8009.5	8047.9	7844.9	7746.2	8744.6	9364.5	9304.2	8755.6	7504.8	6813.6	7614.5
60°	8212.5	8272.8	8223.5	8234.4	9008.0	9540.1	9402.9	8980.5	7779.1	7120.8	8069.9
62.5°	8102.8	8223.5	8426.4	8382.6	9018.9	9413.9	9221.9	8684.3	7812.0	7521.3	8415.5
65°	7801.0	7812.0	8207.0	8448.4	8525.2	8761.1	8508.7	8064.4	7471.9	7768.1	8366.1
67.5°	7027.5	7115.3	7471.9	7943.7	7620.0	7674.9	7652.9	7011.1	6956.2	7598.1	7987.6
70°	6204.6	6265.0	6654.5	7208.6	6435.0	6177.2	6226.6	5749.3	5974.2	7071.4	7225.0
72.5°	5129.4	5167.8	5612.1	6100.4	5162.3	4701.5	4816.7	4427.2	4745.4	6188.2	6094.9
75°	3873.1	3944.4	4290.0	4866.1	3801.8	3505.5	3620.7	3461.6	3757.9	5096.5	4728.9
77.5°	2754.0	2699.1	3127.0	3807.3	2858.2	2682.6	2693.6	2721.0	3039.2	4295.5	3395.8
80°	1876.2	1892.7	2276.7	2792.4	2243.8	2216.3	2188.9	2408.3	2551.0	3401.3	2468.7
82.5°	1113.7	1113.7	1536.1	1985.9	1772.0	1996.9	1870.7	2068.2	1996.9	2501.6	1618.4
85°	521.2	521.2	790.0	1431.8	1371.5	1645.8	1398.9	1563.5	1475.7	1744.5	729.6
87.5°	87.8	76.8	159.1	702.2	565.1	641.9	252.4	833.9	927.1	1217.9	181.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598995
 CATALOG NUMBER: IFLD-S-SA2C-750-U-SLL

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9
2.5°	4076.1	4037.7	3960.9	3862.1	3779.8	3675.6	3642.7	3571.4	3472.6	3461.6	3417.8
5°	3840.2	3708.5	3543.9	3341.0	3203.8	3061.2	2940.5	2869.2	2786.9	2775.9	2754.0
7.5°	3582.3	3417.8	3143.5	2902.1	2666.2	2441.3	2331.5	2194.4	2101.1	2029.8	1996.9
10°	3341.0	3187.3	2847.2	2518.1	2309.6	2161.5	2029.8	1887.2	1772.0	1684.2	1651.3
12.5°	3181.9	3000.8	2633.3	2320.6	2167.0	1996.9	1848.8	1695.2	1547.0	1431.8	1371.5
15°	3110.5	2940.5	2567.4	2221.8	1996.9	1761.0	1590.9	1437.3	1256.3	1174.0	1146.6
17.5°	3280.6	3028.3	2545.5	2106.6	1788.4	1519.6	1311.1	1146.6	1014.9	932.6	899.7
20°	3500.0	3187.3	2583.9	1969.5	1590.9	1289.2	1058.8	883.2	795.5	735.1	729.6
22.5°	3779.8	3423.2	2644.2	1870.7	1371.5	1036.8	828.4	724.1	663.8	658.3	647.3
25°	4279.1	3851.1	2743.0	1739.1	1195.9	855.8	707.7	647.3	619.9	603.5	614.4
27.5°	4707.0	4130.9	2814.3	1656.8	1124.6	806.4	685.7	619.9	592.5	587.0	592.5
30°	4959.3	4388.8	2792.4	1503.2	982.0	768.0	729.6	707.7	652.8	608.9	608.9
32.5°	5189.7	4553.4	2786.9	1366.0	839.4	641.9	608.9	592.5	625.4	647.3	630.9
35°	5507.9	4811.2	2770.4	1289.2	779.0	592.5	537.6	493.7	471.8	460.8	477.3
37.5°	5848.0	4986.7	2726.5	1278.2	746.1	565.1	521.2	477.3	455.3	444.4	438.9
40°	6221.1	5173.3	2677.2	1223.4	729.6	548.6	504.7	466.3	438.9	422.4	416.9
42.5°	6462.5	5321.4	2627.8	1195.9	696.7	537.6	488.3	455.3	427.9	406.0	406.0
45°	6599.6	5496.9	2578.4	1168.5	658.3	543.1	488.3	444.4	411.4	400.5	389.5
47.5°	6660.0	5628.6	2561.9	1124.6	625.4	521.2	477.3	433.4	400.5	378.5	373.0
50°	6819.1	5908.4	2622.3	1091.7	587.0	499.2	504.7	427.9	395.0	367.6	362.1
52.5°	6912.3	6133.3	2754.0	1042.3	559.6	471.8	493.7	416.9	378.5	351.1	351.1
55°	7252.4	6506.4	2896.6	1003.9	526.7	433.4	455.3	395.0	351.1	334.6	334.6
57.5°	7685.8	6901.3	3017.3	987.5	504.7	406.0	406.0	384.0	334.6	312.7	307.2
60°	7987.6	7225.0	3088.6	976.5	482.8	378.5	362.1	384.0	318.2	296.2	290.8
62.5°	8020.5	7038.5	3017.3	971.0	477.3	351.1	329.2	367.6	301.7	279.8	268.8
65°	7812.0	6660.0	2819.8	949.1	471.8	323.7	307.2	318.2	279.8	263.3	252.4
67.5°	7395.1	6045.5	2534.5	938.1	466.3	301.7	279.8	274.3	257.8	241.4	230.4
70°	6424.1	5244.6	2199.9	888.7	455.3	285.3	252.4	246.9	230.4	219.4	214.0
72.5°	5392.7	4290.0	1815.9	822.9	433.4	257.8	230.4	219.4	214.0	197.5	192.0
75°	4130.9	3302.6	1453.8	729.6	378.5	230.4	203.0	192.0	186.5	175.6	170.1
77.5°	2902.1	2457.7	1075.2	592.5	318.2	208.5	181.0	170.1	164.6	148.1	148.1
80°	1969.5	1722.6	729.6	411.4	246.9	170.1	159.1	148.1	137.1	126.2	126.2
82.5°	1223.4	1206.9	526.7	268.8	181.0	137.1	126.2	126.2	109.7	98.7	98.7
85°	559.6	740.6	367.6	186.5	137.1	104.2	104.2	98.7	87.8	71.3	71.3
87.5°	175.6	246.9	192.0	82.3	76.8	60.3	60.3	54.9	54.9	43.9	43.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598995
 CATALOG NUMBER: IFLD-S-SA2C-750-U-SLL

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9
2.5°	3461.6	3456.2	3456.2	3434.2	3489.1	3489.1	3522.0	3494.6	3511.0	3516.5	3560.4
5°	2748.5	2792.4	2825.3	2891.1	2929.5	2946.0	2946.0	2989.9	2973.4	3006.3	3072.1
7.5°	2013.3	2068.2	2167.0	2249.2	2315.1	2337.0	2331.5	2342.5	2359.0	2320.6	2331.5
10°	1629.3	1590.9	1623.8	1700.6	1761.0	1832.3	1777.5	1772.0	1788.4	1772.0	1804.9
12.5°	1360.5	1316.6	1289.2	1289.2	1333.1	1366.0	1349.5	1377.0	1437.3	1453.8	1492.2
15°	1102.7	1064.3	1042.3	1014.9	1058.8	1069.8	1086.2	1124.6	1168.5	1190.5	1234.3
17.5°	883.2	883.2	883.2	861.3	877.8	894.2	899.7	949.1	954.6	976.5	993.0
20°	724.1	740.6	768.0	779.0	795.5	795.5	784.5	811.9	790.0	806.4	817.4
22.5°	652.8	674.8	685.7	691.2	713.2	718.7	691.2	696.7	702.2	685.7	691.2
25°	614.4	625.4	614.4	619.9	625.4	614.4	619.9	630.9	625.4	636.4	630.9
27.5°	598.0	587.0	581.5	576.0	576.0	565.1	570.5	570.5	581.5	587.0	587.0
30°	598.0	581.5	559.6	543.1	543.1	526.7	537.6	548.6	554.1	565.1	565.1
32.5°	614.4	581.5	543.1	526.7	510.2	499.2	510.2	526.7	548.6	554.1	559.6
35°	488.3	504.7	499.2	477.3	471.8	471.8	466.3	466.3	449.8	449.8	444.4
37.5°	438.9	433.4	444.4	449.8	455.3	438.9	438.9	416.9	411.4	416.9	416.9
40°	411.4	411.4	411.4	427.9	433.4	422.4	406.0	395.0	395.0	395.0	400.5
42.5°	400.5	389.5	384.0	395.0	411.4	400.5	384.0	378.5	378.5	384.0	384.0
45°	384.0	378.5	373.0	367.6	389.5	373.0	367.6	362.1	362.1	362.1	367.6
47.5°	367.6	362.1	351.1	351.1	356.6	351.1	345.6	345.6	345.6	356.6	356.6
50°	356.6	351.1	340.1	340.1	340.1	340.1	334.6	334.6	334.6	340.1	345.6
52.5°	340.1	334.6	329.2	323.7	323.7	323.7	323.7	323.7	323.7	329.2	334.6
55°	323.7	318.2	312.7	312.7	318.2	318.2	312.7	318.2	312.7	318.2	323.7
57.5°	307.2	301.7	296.2	301.7	307.2	301.7	301.7	301.7	301.7	301.7	307.2
60°	285.3	285.3	285.3	285.3	296.2	296.2	296.2	296.2	285.3	290.8	296.2
62.5°	274.3	268.8	268.8	274.3	279.8	279.8	285.3	279.8	274.3	279.8	279.8
65°	252.4	252.4	252.4	257.8	257.8	263.3	263.3	263.3	257.8	263.3	263.3
67.5°	235.9	235.9	235.9	235.9	246.9	246.9	246.9	246.9	241.4	241.4	246.9
70°	208.5	214.0	208.5	219.4	230.4	224.9	230.4	230.4	224.9	219.4	230.4
72.5°	192.0	192.0	192.0	192.0	208.5	208.5	208.5	214.0	208.5	203.0	208.5
75°	170.1	170.1	170.1	175.6	186.5	186.5	186.5	186.5	186.5	181.0	181.0
77.5°	148.1	153.6	148.1	153.6	164.6	159.1	164.6	170.1	164.6	159.1	159.1
80°	126.2	126.2	126.2	131.7	137.1	137.1	137.1	142.6	137.1	131.7	131.7
82.5°	98.7	98.7	104.2	104.2	109.7	109.7	109.7	115.2	109.7	104.2	104.2
85°	76.8	76.8	76.8	82.3	82.3	87.8	87.8	93.3	93.3	87.8	87.8
87.5°	49.4	43.9	49.4	49.4	54.9	54.9	49.4	43.9	49.4	43.9	38.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P598995
 CATALOG NUMBER: IFLD-S-SA2C-750-U-SLL

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9	3949.9
2.5°	3604.3	3703.0	3774.3	3823.7	3895.0	4032.2	4087.0	4185.8	4213.2	4229.7
5°	3099.6	3203.8	3357.4	3467.1	3593.3	3851.1	4048.6	4196.8	4262.6	4322.9
7.5°	2430.3	2567.4	2726.5	2869.2	3077.6	3395.8	3653.7	3960.9	4076.1	4136.4
10°	1898.1	2024.3	2199.9	2375.4	2666.2	2935.0	3302.6	3582.3	3741.4	3785.3
12.5°	1601.9	1750.0	1958.5	2172.4	2353.5	2660.7	3033.7	3439.7	3587.8	3615.3
15°	1360.5	1563.5	1777.5	1996.9	2205.4	2474.2	2874.6	3368.4	3587.8	3615.3
17.5°	1124.6	1305.7	1558.0	1793.9	2035.3	2402.9	2902.1	3428.7	3648.2	3730.5
20°	894.2	1069.8	1267.3	1563.5	1892.7	2282.2	2962.4	3631.7	3922.5	4010.2
22.5°	740.6	817.4	1009.4	1294.7	1684.2	2199.9	3022.8	3949.9	4257.1	4290.0
25°	647.3	702.2	822.9	1091.7	1519.6	2145.0	3165.4	4317.5	4712.4	4712.4
27.5°	603.5	625.4	707.7	949.1	1404.4	2095.6	3308.0	4723.4	5091.0	5167.8
30°	592.5	647.3	691.2	844.8	1278.2	1958.5	3439.7	5041.6	5420.1	5425.6
32.5°	581.5	570.5	603.5	735.1	1124.6	1815.9	3549.4	5365.3	5661.5	5678.0
35°	455.3	477.3	532.1	647.3	1009.4	1711.6	3604.3	5540.8	5968.7	5985.2
37.5°	427.9	455.3	499.2	598.0	932.6	1623.8	3620.7	5881.0	6292.4	6325.3
40°	416.9	438.9	471.8	554.1	872.3	1514.1	3653.7	6232.1	6769.7	6725.8
42.5°	395.0	422.4	455.3	532.1	822.9	1431.8	3659.1	6424.1	7022.0	7022.0
45°	389.5	406.0	444.4	532.1	768.0	1360.5	3571.4	6616.1	7312.8	7225.0
47.5°	367.6	400.5	433.4	515.7	702.2	1289.2	3467.1	6714.8	7351.2	7323.8
50°	362.1	395.0	449.8	488.3	663.8	1256.3	3445.2	6961.7	7428.0	7422.5
52.5°	351.1	384.0	466.3	466.3	614.4	1212.4	3549.4	7071.4	7444.5	7488.3
55°	334.6	384.0	433.4	427.9	570.5	1157.5	3664.6	7356.7	7735.2	7724.2
57.5°	323.7	373.0	411.4	389.5	521.2	1119.1	3834.7	7631.0	8086.3	8009.5
60°	307.2	373.0	367.6	362.1	482.8	1086.2	3977.3	7685.8	8163.1	8212.5
62.5°	296.2	389.5	323.7	334.6	449.8	1069.8	3917.0	7274.4	8058.9	8102.8
65°	285.3	334.6	296.2	307.2	438.9	1036.8	3681.1	6780.7	7609.0	7801.0
67.5°	263.3	274.3	274.3	285.3	427.9	960.0	3198.3	5891.9	6923.3	7027.5
70°	241.4	246.9	246.9	263.3	416.9	872.3	2638.8	5096.5	6007.1	6204.6
72.5°	219.4	219.4	219.4	241.4	384.0	801.0	2172.4	3917.0	4992.2	5129.4
75°	192.0	192.0	192.0	214.0	345.6	729.6	1711.6	2913.0	3675.6	3873.1
77.5°	170.1	170.1	164.6	192.0	301.7	592.5	1234.3	2057.2	2589.4	2754.0
80°	142.6	137.1	137.1	153.6	235.9	427.9	795.5	1453.8	1804.9	1876.2
82.5°	115.2	109.7	104.2	115.2	170.1	268.8	493.7	1014.9	1157.5	1113.7
85°	109.7	115.2	93.3	87.8	120.7	175.6	312.7	625.4	521.2	521.2
87.5°	43.9	38.4	38.4	32.9	60.3	65.8	137.1	115.2	87.8	87.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)