

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P598998

Luminaire Tested: **IFLD-S-SA3A-750-U-SLL**

Issue Date: 05/03/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P598998
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/03/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-S-SA3A-750-U-SLL
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens
 Light Source: (48) 5000K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 11971.1 lumens
 Efficiency: N/A
 Efficacy: 126.3 lumens/watt
 Spacing Criteria (0/90/45): 1.12 / 0.52 / 0.8
 Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
 CIE Type: Direct

Input Watts (W): 94.8
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P598998
CATALOG NUMBER: IFLD-S-SA3A-750-U-SLL

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ··· 90°-270° - · 135°-315°

TEST NUMBER: P598998
 CATALOG NUMBER: IFLD-S-SA3A-750-U-SLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	106	100	94	89	103	97	92	88	93	89	85	89	85	82	85	82	80	77				
2	94	83	75	68	91	81	74	67	78	71	65	74	69	64	71	66	62	60				
3	84	71	61	53	81	69	60	53	66	58	52	63	56	51	60	55	50	47				
4	75	61	51	43	73	60	50	42	57	48	42	54	47	41	52	46	40	38				
5	68	53	43	35	66	52	42	35	50	41	34	48	40	34	46	39	34	31				
6	63	47	37	30	60	46	37	29	44	36	29	42	35	29	41	34	29	26				
7	58	42	32	25	56	41	32	25	40	31	25	38	31	25	37	30	25	22				
8	53	38	29	22	52	37	28	22	36	28	22	35	27	22	33	27	22	19				
9	50	35	26	20	48	34	26	20	33	25	19	32	25	19	31	24	19	17				
10	46	32	23	18	45	31	23	18	30	23	17	29	22	17	28	22	17	15				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	54874	54874	54874	54874
5°	60286	53554	38405	41925
10°	53399	47130	23294	24998
15°	51998	44738	16491	17123
20°	59288	51745	10787	11922
25°	72235	65592	9419	9755
30°	87037	79556	9769	9065
35°	101506	93412	8094	7630
40°	121975	112823	7561	7162
45°	141951	129663	7652	7114
50°	160424	147380	7826	7350
55°	187088	175660	8105	7707
60°	228186	221935	8080	8080
65°	256441	256801	8296	8656
70°	252029	260941	8690	8913
75°	207893	221734	9127	9715
80°	150108	157562	10091	10530
85°	83076	89201	11362	13997

TEST NUMBER: P598998
 CATALOG NUMBER: IFLD-S-SA3A-750-U-SLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	297.0	2.5
10°-20°	627.1	5.2
20°-30°	917.6	7.7
30°-40°	1292.8	10.8
40°-50°	1776.7	14.8
50°-60°	2421.4	20.2
60°-70°	2650.2	22.1
70°-80°	1530.0	12.8
80°-90°	458.2	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1841.7	15.4
0°-40°	3134.5	26.2
0°-60°	7332.7	61.3
0°-90°	11971.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11971.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	3824	3824	3824	3824	3824	
5°	4185	3717	2666	2910	4185	380
15°	3500	3011	1110	1152	3500	1022
25°	4562	4142	595	616	4562	2136
35°	5794	5332	462	436	5794	3674
45°	6994	6388	377	350	6994	5375
55°	7477	7020	324	308	7477	6746
65°	7551	7562	244	255	7551	7228
75°	3749	3999	165	175	3749	4027
85°	504	542	69	85	504	700
90°	0	0	0	0	0	

TEST NUMBER: P598998
 CATALOG NUMBER: IFLD-S-SA3A-750-U-SLL

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5
2.5°	4094.3	4078.4	4094.3	4152.7	4168.7	4195.2	4195.2	4158.0	4089.0	4057.1	4004.0
5°	4184.6	4158.0	4290.8	4412.9	4508.5	4497.9	4407.6	4333.3	4195.2	3988.1	3791.6
7.5°	4004.0	4030.6	4126.2	4444.8	4667.8	4710.3	4566.9	4418.3	4120.9	3834.1	3568.6
10°	3664.2	3701.3	3908.5	4237.7	4588.2	4657.2	4566.9	4386.4	4030.6	3674.8	3366.8
12.5°	3499.6	3584.5	3706.7	4104.9	4354.5	4519.1	4476.7	4359.8	3961.6	3542.0	3244.7
15°	3499.6	3520.8	3701.3	4035.9	4179.3	4184.6	4200.5	4221.8	3982.8	3600.4	3202.2
17.5°	3611.1	3669.5	3823.5	4030.6	4057.1	3993.4	3993.4	4083.7	4025.3	3765.1	3356.2
20°	3881.9	3860.7	4062.5	4147.4	4004.0	3844.7	3828.8	3982.8	4073.1	3940.3	3637.6
22.5°	4152.7	4248.3	4412.9	4221.8	3956.2	3743.8	3722.6	3913.8	4216.5	4243.0	3961.6
25°	4561.6	4657.2	4742.2	4508.5	3950.9	3717.3	3733.2	3881.9	4391.7	4673.2	4503.2
27.5°	5002.4	5060.8	5182.9	4821.8	4078.4	3685.4	3701.3	3924.4	4556.3	4954.6	4928.0
30°	5252.0	5315.7	5289.2	4880.3	4163.4	3706.7	3664.2	3982.8	4466.0	4954.6	5204.2
32.5°	5496.3	5459.1	5443.2	4975.8	4269.6	3839.4	3733.2	4104.9	4519.1	5034.3	5560.0
35°	5793.6	5740.5	5698.1	5161.7	4444.8	3966.9	3919.1	4264.2	4636.0	5198.9	5846.7
37.5°	6122.9	6122.9	5915.8	5299.8	4651.9	4174.0	4120.9	4492.6	4821.8	5299.8	6239.7
40°	6510.5	6526.5	6160.1	5485.6	4885.6	4503.2	4487.3	4790.0	5002.4	5448.5	6616.8
42.5°	6797.3	6807.9	6372.5	5554.7	5156.4	4959.9	5028.9	5267.9	5209.5	5581.2	6643.3
45°	6993.8	6940.7	6521.2	5751.2	5453.8	5645.0	5666.2	5735.2	5480.3	5660.9	6749.5
47.5°	7089.4	7078.8	6584.9	5979.5	6080.4	6340.6	6462.8	6367.2	5729.9	5575.9	6749.5
50°	7185.0	7094.7	6643.3	6292.8	6691.1	7216.8	7190.3	7015.0	6075.1	5682.1	6648.6
52.5°	7248.7	7169.0	6760.1	6574.3	7275.2	7870.0	7976.2	7652.3	6478.7	5878.6	6696.4
55°	7477.0	7413.3	7110.6	6956.6	7949.7	8560.4	8576.3	8124.9	6903.5	6202.5	7009.7
57.5°	7753.2	7790.4	7593.9	7498.3	8464.8	9064.8	9006.4	8475.4	7264.6	6595.5	7370.8
60°	7949.7	8008.1	7960.3	7970.9	8719.7	9234.8	9102.0	8693.1	7530.1	6892.9	7811.6
62.5°	7843.5	7960.3	8156.8	8114.3	8730.3	9112.6	8926.8	8406.4	7562.0	7280.6	8146.2
65°	7551.4	7562.0	7944.4	8178.0	8252.4	8480.7	8236.4	7806.3	7232.8	7519.5	8098.4
67.5°	6802.6	6887.6	7232.8	7689.5	7376.1	7429.2	7408.0	6786.7	6733.6	7354.9	7731.9
70°	6006.1	6064.5	6441.5	6977.9	6229.1	5979.5	6027.3	5565.3	5783.0	6845.1	6993.8
72.5°	4965.2	5002.4	5432.5	5905.2	4997.1	4551.0	4662.5	4285.5	4593.5	5990.1	5899.9
75°	3749.1	3818.2	4152.7	4710.3	3680.1	3393.3	3504.9	3350.9	3637.6	4933.4	4577.6
77.5°	2665.8	2612.7	3026.9	3685.4	2766.7	2596.8	2607.4	2634.0	2942.0	4158.0	3287.1
80°	1816.2	1832.1	2203.8	2703.0	2172.0	2145.4	2118.8	2331.3	2469.3	3292.4	2389.7
82.5°	1078.0	1078.0	1486.9	1922.4	1715.3	1933.0	1810.8	2002.0	1933.0	2421.5	1566.6
85°	504.5	504.5	764.7	1386.0	1327.6	1593.1	1354.2	1513.5	1428.5	1688.7	706.3
87.5°	85.0	74.3	154.0	679.7	547.0	621.3	244.3	807.2	897.5	1178.9	175.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598998
 CATALOG NUMBER: IFLD-S-SA3A-750-U-SLL

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5
2.5°	3945.6	3908.5	3834.1	3738.5	3658.9	3558.0	3526.1	3457.1	3361.5	3350.9	3308.4
5°	3717.3	3589.8	3430.5	3234.0	3101.3	2963.2	2846.4	2777.3	2697.7	2687.1	2665.8
7.5°	3467.7	3308.4	3042.9	2809.2	2580.9	2363.1	2256.9	2124.2	2033.9	1964.8	1933.0
10°	3234.0	3085.3	2756.1	2437.5	2235.7	2092.3	1964.8	1826.8	1715.3	1630.3	1598.4
12.5°	3080.0	2904.8	2549.0	2246.3	2097.6	1933.0	1789.6	1640.9	1497.5	1386.0	1327.6
15°	3011.0	2846.4	2485.3	2150.7	1933.0	1704.6	1540.0	1391.3	1216.1	1136.4	1109.9
17.5°	3175.6	2931.3	2464.0	2039.2	1731.2	1471.0	1269.2	1109.9	982.4	902.8	870.9
20°	3388.0	3085.3	2501.2	1906.4	1540.0	1247.9	1024.9	855.0	770.0	711.6	706.3
22.5°	3658.9	3313.7	2559.6	1810.8	1327.6	1003.7	801.9	701.0	642.6	637.2	626.6
25°	4142.1	3727.9	2655.2	1683.4	1157.7	828.4	685.0	626.6	600.1	584.1	594.8
27.5°	4556.3	3998.7	2724.2	1603.7	1088.6	780.6	663.8	600.1	573.5	568.2	573.5
30°	4800.6	4248.3	2703.0	1455.0	950.6	743.5	706.3	685.0	631.9	589.5	589.5
32.5°	5023.6	4407.6	2697.7	1322.3	812.5	621.3	589.5	573.5	605.4	626.6	610.7
35°	5331.6	4657.2	2681.8	1247.9	754.1	573.5	520.4	477.9	456.7	446.1	462.0
37.5°	5660.9	4827.2	2639.3	1237.3	722.2	547.0	504.5	462.0	440.8	430.1	424.8
40°	6022.0	5007.7	2591.5	1184.2	706.3	531.0	488.6	451.4	424.8	408.9	403.6
42.5°	6255.6	5151.1	2543.7	1157.7	674.4	520.4	472.6	440.8	414.2	393.0	393.0
45°	6388.4	5321.0	2495.9	1131.1	637.2	525.7	472.6	430.1	398.3	387.7	377.0
47.5°	6446.8	5448.5	2480.0	1088.6	605.4	504.5	462.0	419.5	387.7	366.4	361.1
50°	6600.8	5719.3	2538.4	1056.8	568.2	483.2	488.6	414.2	382.3	355.8	350.5
52.5°	6691.1	5937.0	2665.8	1009.0	541.7	456.7	477.9	403.6	366.4	339.9	339.9
55°	7020.3	6298.1	2803.9	971.8	509.8	419.5	440.8	382.3	339.9	323.9	323.9
57.5°	7439.9	6680.5	2920.7	955.9	488.6	393.0	393.0	371.7	323.9	302.7	297.4
60°	7731.9	6993.8	2989.8	945.3	467.3	366.4	350.5	371.7	308.0	286.8	281.5
62.5°	7763.8	6813.2	2920.7	939.9	462.0	339.9	318.6	355.8	292.1	270.8	260.2
65°	7562.0	6446.8	2729.5	918.7	456.7	313.3	297.4	308.0	270.8	254.9	244.3
67.5°	7158.4	5852.1	2453.4	908.1	451.4	292.1	270.8	265.5	249.6	233.7	223.0
70°	6218.5	5076.7	2129.5	860.3	440.8	276.1	244.3	239.0	223.0	212.4	207.1
72.5°	5220.1	4152.7	1757.7	796.6	419.5	249.6	223.0	212.4	207.1	191.2	185.9
75°	3998.7	3196.9	1407.3	706.3	366.4	223.0	196.5	185.9	180.6	169.9	164.6
77.5°	2809.2	2379.1	1040.8	573.5	308.0	201.8	175.2	164.6	159.3	143.4	143.4
80°	1906.4	1667.5	706.3	398.3	239.0	164.6	154.0	143.4	132.8	122.1	122.1
82.5°	1184.2	1168.3	509.8	260.2	175.2	132.8	122.1	122.1	106.2	95.6	95.6
85°	541.7	716.9	355.8	180.6	132.8	100.9	100.9	95.6	85.0	69.0	69.0
87.5°	169.9	239.0	185.9	79.7	74.3	58.4	58.4	53.1	53.1	42.5	42.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598998
 CATALOG NUMBER: IFLD-S-SA3A-750-U-SLL

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5
2.5°	3350.9	3345.6	3345.6	3324.3	3377.4	3377.4	3409.3	3382.7	3398.7	3404.0	3446.4
5°	2660.5	2703.0	2734.9	2798.6	2835.8	2851.7	2851.7	2894.2	2878.2	2910.1	2973.8
7.5°	1948.9	2002.0	2097.6	2177.3	2241.0	2262.2	2256.9	2267.5	2283.5	2246.3	2256.9
10°	1577.2	1540.0	1571.9	1646.2	1704.6	1773.7	1720.6	1715.3	1731.2	1715.3	1747.1
12.5°	1317.0	1274.5	1247.9	1247.9	1290.4	1322.3	1306.4	1332.9	1391.3	1407.3	1444.4
15°	1067.4	1030.2	1009.0	982.4	1024.9	1035.5	1051.5	1088.6	1131.1	1152.4	1194.8
17.5°	855.0	855.0	855.0	833.7	849.7	865.6	870.9	918.7	924.0	945.3	961.2
20°	701.0	716.9	743.5	754.1	770.0	770.0	759.4	785.9	764.7	780.6	791.2
22.5°	631.9	653.2	663.8	669.1	690.4	695.7	669.1	674.4	679.7	663.8	669.1
25°	594.8	605.4	594.8	600.1	605.4	594.8	600.1	610.7	605.4	616.0	610.7
27.5°	578.8	568.2	562.9	557.6	557.6	547.0	552.3	552.3	562.9	568.2	568.2
30°	578.8	562.9	541.7	525.7	525.7	509.8	520.4	531.0	536.4	547.0	547.0
32.5°	594.8	562.9	525.7	509.8	493.9	483.2	493.9	509.8	531.0	536.4	541.7
35°	472.6	488.6	483.2	462.0	456.7	456.7	451.4	451.4	435.5	435.5	430.1
37.5°	424.8	419.5	430.1	435.5	440.8	424.8	424.8	403.6	398.3	403.6	403.6
40°	398.3	398.3	398.3	414.2	419.5	408.9	393.0	382.3	382.3	382.3	387.7
42.5°	387.7	377.0	371.7	382.3	398.3	387.7	371.7	366.4	366.4	371.7	371.7
45°	371.7	366.4	361.1	355.8	377.0	361.1	355.8	350.5	350.5	350.5	355.8
47.5°	355.8	350.5	339.9	339.9	345.2	339.9	334.6	334.6	334.6	345.2	345.2
50°	345.2	339.9	329.2	329.2	329.2	329.2	323.9	323.9	323.9	329.2	334.6
52.5°	329.2	323.9	318.6	313.3	313.3	313.3	313.3	313.3	313.3	318.6	323.9
55°	313.3	308.0	302.7	302.7	308.0	308.0	302.7	308.0	302.7	308.0	313.3
57.5°	297.4	292.1	286.8	292.1	297.4	292.1	292.1	292.1	292.1	292.1	297.4
60°	276.1	276.1	276.1	276.1	286.8	286.8	286.8	286.8	276.1	281.5	286.8
62.5°	265.5	260.2	260.2	265.5	270.8	270.8	276.1	270.8	265.5	270.8	270.8
65°	244.3	244.3	244.3	249.6	249.6	254.9	254.9	254.9	249.6	254.9	254.9
67.5°	228.3	228.3	228.3	228.3	239.0	239.0	239.0	239.0	233.7	233.7	239.0
70°	201.8	207.1	201.8	212.4	223.0	217.7	223.0	223.0	217.7	212.4	223.0
72.5°	185.9	185.9	185.9	185.9	201.8	201.8	201.8	207.1	201.8	196.5	201.8
75°	164.6	164.6	164.6	169.9	180.6	180.6	180.6	180.6	180.6	175.2	175.2
77.5°	143.4	148.7	143.4	148.7	159.3	154.0	159.3	164.6	159.3	154.0	154.0
80°	122.1	122.1	122.1	127.4	132.8	132.8	132.8	138.1	132.8	127.4	127.4
82.5°	95.6	95.6	100.9	100.9	106.2	106.2	106.2	111.5	106.2	100.9	100.9
85°	74.3	74.3	74.3	79.7	79.7	85.0	85.0	90.3	90.3	85.0	85.0
87.5°	47.8	42.5	47.8	47.8	53.1	53.1	47.8	42.5	47.8	42.5	37.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598998
 CATALOG NUMBER: IFLD-S-SA3A-750-U-SLL

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5	3823.5
2.5°	3488.9	3584.5	3653.6	3701.3	3770.4	3903.1	3956.2	4051.8	4078.4	4094.3
5°	3000.4	3101.3	3250.0	3356.2	3478.3	3727.9	3919.1	4062.5	4126.2	4184.6
7.5°	2352.5	2485.3	2639.3	2777.3	2979.1	3287.1	3536.7	3834.1	3945.6	4004.0
10°	1837.4	1959.5	2129.5	2299.4	2580.9	2841.1	3196.9	3467.7	3621.7	3664.2
12.5°	1550.6	1694.0	1895.8	2102.9	2278.2	2575.5	2936.7	3329.6	3473.0	3499.6
15°	1317.0	1513.5	1720.6	1933.0	2134.8	2395.0	2782.6	3260.6	3473.0	3499.6
17.5°	1088.6	1263.9	1508.2	1736.5	1970.2	2326.0	2809.2	3319.0	3531.4	3611.1
20°	865.6	1035.5	1226.7	1513.5	1832.1	2209.1	2867.6	3515.5	3796.9	3881.9
22.5°	716.9	791.2	977.1	1253.3	1630.3	2129.5	2926.0	3823.5	4120.9	4152.7
25°	626.6	679.7	796.6	1056.8	1471.0	2076.4	3064.1	4179.3	4561.6	4561.6
27.5°	584.1	605.4	685.0	918.7	1359.5	2028.6	3202.2	4572.3	4928.0	5002.4
30°	573.5	626.6	669.1	817.8	1237.3	1895.8	3329.6	4880.3	5246.7	5252.0
32.5°	562.9	552.3	584.1	711.6	1088.6	1757.7	3435.8	5193.6	5480.3	5496.3
35°	440.8	462.0	515.1	626.6	977.1	1656.8	3488.9	5363.5	5777.7	5793.6
37.5°	414.2	440.8	483.2	578.8	902.8	1571.9	3504.9	5692.7	6091.0	6122.9
40°	403.6	424.8	456.7	536.4	844.4	1465.7	3536.7	6032.6	6553.0	6510.5
42.5°	382.3	408.9	440.8	515.1	796.6	1386.0	3542.0	6218.5	6797.3	6797.3
45°	377.0	393.0	430.1	515.1	743.5	1317.0	3457.1	6404.3	7078.8	6993.8
47.5°	355.8	387.7	419.5	499.2	679.7	1247.9	3356.2	6499.9	7115.9	7089.4
50°	350.5	382.3	435.5	472.6	642.6	1216.1	3334.9	6738.9	7190.3	7185.0
52.5°	339.9	371.7	451.4	451.4	594.8	1173.6	3435.8	6845.1	7206.2	7248.7
55°	323.9	371.7	419.5	414.2	552.3	1120.5	3547.3	7121.2	7487.7	7477.0
57.5°	313.3	361.1	398.3	377.0	504.5	1083.3	3712.0	7386.8	7827.5	7753.2
60°	297.4	361.1	355.8	350.5	467.3	1051.5	3850.0	7439.9	7901.9	7949.7
62.5°	286.8	377.0	313.3	323.9	435.5	1035.5	3791.6	7041.6	7801.0	7843.5
65°	276.1	323.9	286.8	297.4	424.8	1003.7	3563.3	6563.7	7365.5	7551.4
67.5°	254.9	265.5	265.5	276.1	414.2	929.3	3096.0	5703.4	6701.7	6802.6
70°	233.7	239.0	239.0	254.9	403.6	844.4	2554.3	4933.4	5814.9	6006.1
72.5°	212.4	212.4	212.4	233.7	371.7	775.3	2102.9	3791.6	4832.5	4965.2
75°	185.9	185.9	185.9	207.1	334.6	706.3	1656.8	2819.8	3558.0	3749.1
77.5°	164.6	164.6	159.3	185.9	292.1	573.5	1194.8	1991.4	2506.5	2665.8
80°	138.1	132.8	132.8	148.7	228.3	414.2	770.0	1407.3	1747.1	1816.2
82.5°	111.5	106.2	100.9	111.5	164.6	260.2	477.9	982.4	1120.5	1078.0
85°	106.2	111.5	90.3	85.0	116.8	169.9	302.7	605.4	504.5	504.5
87.5°	42.5	37.2	37.2	31.9	58.4	63.7	132.8	111.5	85.0	85.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)