

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P598999

Luminaire Tested: **IFLD-S-SA3B-750-U-SLL**

Issue Date: 05/03/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P598999
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/03/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-S-SA3B-750-U-SLL
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens
 Light Source: (48) 5000K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 14805.2 lumens
 Efficiency: N/A
 Efficacy: 121.0 lumens/watt
 Spacing Criteria (0/90/45): 1.12 / 0.52 / 0.8
 Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
 CIE Type: Direct

Input Watts (W): 122.4
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P598999
CATALOG NUMBER: IFLD-S-SA3B-750-U-SLL

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ··· 90°-270° - · 135°-315°

TEST NUMBER: P598999

CATALOG NUMBER: IFLD-S-SA3B-750-U-SLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	106	100	94	89	103	97	92	88	93	89	85	89	85	82	85	82	80	77
2	94	83	75	68	91	81	74	67	78	71	65	74	69	64	71	66	62	60
3	84	71	61	53	81	69	60	53	66	58	52	63	56	51	60	55	50	47
4	75	61	51	43	73	60	50	42	57	48	42	54	47	41	52	46	40	38
5	68	53	43	35	66	52	42	35	50	41	34	48	40	34	46	39	34	31
6	63	47	37	30	60	46	37	29	44	36	29	42	35	29	41	34	29	26
7	58	42	32	25	56	41	32	25	40	31	25	38	31	25	37	30	25	22
8	53	38	29	22	52	37	28	22	36	28	22	35	27	22	33	27	22	19
9	50	35	26	20	48	34	26	20	33	25	19	32	25	19	31	24	19	17
10	46	32	23	18	45	31	23	18	30	23	17	29	22	17	28	22	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	67866	67866	67866	67866
5°	74559	66232	47499	51851
10°	66042	58289	28810	30914
15°	64308	55330	20394	21176
20°	73324	63997	13341	14745
25°	89338	81122	11649	12064
30°	107643	98390	12081	11211
35°	125539	115528	10011	9435
40°	150853	139533	9351	8860
45°	175558	160362	9464	8799
50°	198403	182273	9679	9092
55°	231381	217249	10024	9531
60°	282210	274480	9992	9992
65°	317154	317599	10259	10704
70°	311695	322718	10746	11023
75°	257117	274230	11290	12016
80°	185638	194870	12488	13026
85°	102737	110312	14063	17307

TEST NUMBER: P598999
 CATALOG NUMBER: IFLD-S-SA3B-750-U-SLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	367.4	2.5
10°-20°	775.6	5.2
20°-30°	1134.8	7.7
30°-40°	1598.9	10.8
40°-50°	2197.3	14.8
50°-60°	2994.7	20.2
60°-70°	3277.6	22.1
70°-80°	1892.3	12.8
80°-90°	566.7	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2277.8	15.4
0°-40°	3876.6	26.2
0°-60°	9068.7	61.3
0°-90°	14805.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	14805.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	4729	4729	4729	4729	4729	
5°	5175	4597	3297	3599	5175	470
15°	4328	3724	1373	1425	4328	1265
25°	5642	5123	736	762	5642	2642
35°	7165	6594	571	538	7165	4543
45°	8650	7901	466	434	8650	6648
55°	9247	8682	401	381	9247	8344
65°	9339	9352	302	315	9339	8939
75°	4637	4945	204	217	4637	4981
85°	624	670	85	105	624	866
90°	0	0	0	0	0	

TEST NUMBER: P598999
 CATALOG NUMBER: IFLD-S-SA3B-750-U-SLL

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7
2.5°	5063.6	5043.9	5063.6	5135.9	5155.6	5188.4	5188.4	5142.5	5057.1	5017.7	4952.0
5°	5175.3	5142.5	5306.7	5457.7	5575.9	5562.8	5451.1	5359.2	5188.4	4932.3	4689.3
7.5°	4952.0	4984.8	5103.1	5497.1	5773.0	5825.5	5648.2	5464.3	5096.5	4741.8	4413.5
10°	4531.7	4577.6	4833.8	5241.0	5674.4	5759.8	5648.2	5424.9	4984.8	4544.8	4163.9
12.5°	4328.1	4433.2	4584.2	5076.8	5385.5	5589.1	5536.5	5392.0	4899.5	4380.6	4012.8
15°	4328.1	4354.3	4577.6	4991.4	5168.7	5175.3	5195.0	5221.3	4925.7	4452.9	3960.3
17.5°	4466.0	4538.2	4728.7	4984.8	5017.7	4938.9	4938.9	5050.5	4978.3	4656.5	4150.7
20°	4800.9	4774.7	5024.2	5129.3	4952.0	4755.0	4735.3	4925.7	5037.4	4873.2	4498.8
22.5°	5135.9	5254.1	5457.7	5221.3	4892.9	4630.2	4603.9	4840.3	5214.7	5247.5	4899.5
25°	5641.6	5759.8	5864.9	5575.9	4886.3	4597.3	4617.0	4800.9	5431.4	5779.5	5569.4
27.5°	6186.7	6259.0	6410.0	5963.4	5043.9	4557.9	4577.6	4853.5	5635.0	6127.6	6094.8
30°	6495.4	6574.2	6541.4	6035.7	5149.0	4584.2	4531.7	4925.7	5523.4	6127.6	6436.3
32.5°	6797.5	6751.5	6731.8	6153.9	5280.4	4748.4	4617.0	5076.8	5589.1	6226.1	6876.3
35°	7165.3	7099.6	7047.1	6383.7	5497.1	4906.0	4846.9	5273.8	5733.5	6429.7	7231.0
37.5°	7572.5	7572.5	7316.3	6554.5	5753.3	5162.2	5096.5	5556.2	5963.4	6554.5	7717.0
40°	8051.9	8071.6	7618.5	6784.4	6042.2	5569.4	5549.7	5924.0	6186.7	6738.4	8183.3
42.5°	8406.6	8419.7	7881.2	6869.7	6377.2	6134.2	6219.6	6515.1	6442.9	6902.6	8216.1
45°	8649.6	8583.9	8065.1	7112.8	6745.0	6981.4	7007.7	7093.0	6777.8	7001.1	8347.5
47.5°	8767.8	8754.7	8143.9	7395.2	7519.9	7841.8	7992.8	7874.6	7086.5	6896.0	8347.5
50°	8886.0	8774.4	8216.1	7782.7	8275.2	8925.4	8892.6	8675.8	7513.4	7027.4	8222.7
52.5°	8964.8	8866.3	8360.6	8130.7	8997.7	9733.2	9864.6	9464.0	8012.5	7270.4	8281.8
55°	9247.2	9168.4	8794.1	8603.6	9831.8	10587.0	10606.7	10048.5	8537.9	7671.0	8669.3
57.5°	9588.8	9634.7	9391.7	9273.5	10468.8	11211.0	11138.7	10482.0	8984.5	8157.0	9115.9
60°	9831.8	9904.0	9844.9	9858.0	10784.1	11421.1	11256.9	10751.2	9312.9	8524.8	9661.0
62.5°	9700.4	9844.9	10087.9	10035.4	10797.2	11270.1	11040.2	10396.6	9352.3	9004.2	10074.8
65°	9339.2	9352.3	9825.2	10114.2	10206.1	10488.5	10186.4	9654.4	8945.1	9299.8	10015.6
67.5°	8413.1	8518.2	8945.1	9509.9	9122.4	9188.1	9161.9	8393.4	8327.8	9096.2	9562.5
70°	7428.0	7500.2	7966.5	8629.9	7703.8	7395.2	7454.3	6882.9	7152.2	8465.7	8649.6
72.5°	6140.7	6186.7	6718.7	7303.2	6180.1	5628.5	5766.4	5300.1	5681.0	7408.3	7296.6
75°	4636.8	4722.1	5135.9	5825.5	4551.4	4196.7	4334.6	4144.2	4498.8	6101.3	5661.3
77.5°	3297.0	3231.3	3743.6	4557.9	3421.7	3211.6	3224.7	3257.5	3638.5	5142.5	4065.4
80°	2246.1	2265.8	2725.6	3342.9	2686.2	2653.3	2620.5	2883.2	3054.0	4071.9	2955.4
82.5°	1333.2	1333.2	1838.9	2377.5	2121.3	2390.6	2239.6	2476.0	2390.6	2994.8	1937.5
85°	623.9	623.9	945.7	1714.2	1641.9	1970.3	1674.7	1871.8	1766.7	2088.5	873.5
87.5°	105.1	91.9	190.5	840.7	676.5	768.4	302.1	998.3	1109.9	1458.0	216.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598999
 CATALOG NUMBER: IFLD-S-SA3B-750-U-SLL

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7
2.5°	4879.8	4833.8	4741.8	4623.6	4525.1	4400.3	4360.9	4275.5	4157.3	4144.2	4091.6
5°	4597.3	4439.7	4242.7	3999.7	3835.5	3664.7	3520.3	3434.9	3336.4	3323.2	3297.0
7.5°	4288.7	4091.6	3763.3	3474.3	3191.9	2922.6	2791.2	2627.1	2515.4	2430.0	2390.6
10°	3999.7	3815.8	3408.6	3014.5	2765.0	2587.6	2430.0	2259.3	2121.3	2016.3	1976.9
12.5°	3809.2	3592.5	3152.5	2778.1	2594.2	2390.6	2213.3	2029.4	1852.1	1714.2	1641.9
15°	3723.9	3520.3	3073.7	2659.9	2390.6	2108.2	1904.6	1720.7	1504.0	1405.5	1372.6
17.5°	3927.4	3625.3	3047.4	2522.0	2141.1	1819.2	1569.7	1372.6	1215.0	1116.5	1077.1
20°	4190.2	3815.8	3093.4	2357.8	1904.6	1543.4	1267.6	1057.4	952.3	880.1	873.5
22.5°	4525.1	4098.2	3165.6	2239.6	1641.9	1241.3	991.7	866.9	794.7	788.1	775.0
25°	5122.8	4610.5	3283.8	2081.9	1431.7	1024.6	847.2	775.0	742.1	722.4	735.6
27.5°	5635.0	4945.4	3369.2	1983.4	1346.4	965.4	821.0	742.1	709.3	702.7	709.3
30°	5937.1	5254.1	3342.9	1799.5	1175.6	919.5	873.5	847.2	781.5	729.0	729.0
32.5°	6213.0	5451.1	3336.4	1635.3	1004.8	768.4	729.0	709.3	748.7	775.0	755.3
35°	6593.9	5759.8	3316.7	1543.4	932.6	709.3	643.6	591.1	564.8	551.7	571.4
37.5°	7001.1	5970.0	3264.1	1530.3	893.2	676.5	623.9	571.4	545.1	532.0	525.4
40°	7447.7	6193.3	3205.0	1464.6	873.5	656.8	604.2	558.2	525.4	505.7	499.1
42.5°	7736.7	6370.6	3145.9	1431.7	834.1	643.6	584.5	545.1	512.3	486.0	486.0
45°	7900.9	6580.8	3086.8	1398.9	788.1	650.2	584.5	532.0	492.6	479.4	466.3
47.5°	7973.1	6738.4	3067.1	1346.4	748.7	623.9	571.4	518.8	479.4	453.2	446.6
50°	8163.6	7073.3	3139.3	1307.0	702.7	597.7	604.2	512.3	472.9	440.0	433.5
52.5°	8275.2	7342.6	3297.0	1247.9	669.9	564.8	591.1	499.1	453.2	420.3	420.3
55°	8682.4	7789.2	3467.7	1201.9	630.5	518.8	545.1	472.9	420.3	400.6	400.6
57.5°	9201.3	8262.1	3612.2	1182.2	604.2	486.0	486.0	459.7	400.6	374.4	367.8
60°	9562.5	8649.6	3697.6	1169.0	578.0	453.2	433.5	459.7	380.9	354.7	348.1
62.5°	9601.9	8426.3	3612.2	1162.5	571.4	420.3	394.1	440.0	361.2	334.9	321.8
65°	9352.3	7973.1	3375.8	1136.2	564.8	387.5	367.8	380.9	334.9	315.2	302.1
67.5°	8853.2	7237.5	3034.2	1123.1	558.2	361.2	334.9	328.4	308.7	289.0	275.8
70°	7690.7	6278.7	2633.6	1064.0	545.1	341.5	302.1	295.5	275.8	262.7	256.1
72.5°	6456.0	5135.9	2173.9	985.1	518.8	308.7	275.8	262.7	256.1	236.4	229.9
75°	4945.4	3953.7	1740.4	873.5	453.2	275.8	243.0	229.9	223.3	210.2	203.6
77.5°	3474.3	2942.3	1287.3	709.3	380.9	249.6	216.7	203.6	197.0	177.3	177.3
80°	2357.8	2062.2	873.5	492.6	295.5	203.6	190.5	177.3	164.2	151.1	151.1
82.5°	1464.6	1444.9	630.5	321.8	216.7	164.2	151.1	151.1	131.4	118.2	118.2
85°	669.9	886.6	440.0	223.3	164.2	124.8	124.8	118.2	105.1	85.4	85.4
87.5°	210.2	295.5	229.9	98.5	91.9	72.2	72.2	65.7	65.7	52.5	52.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598999
 CATALOG NUMBER: IFLD-S-SA3B-750-U-SLL

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7
2.5°	4144.2	4137.6	4137.6	4111.3	4177.0	4177.0	4216.4	4183.6	4203.3	4209.9	4262.4
5°	3290.4	3342.9	3382.3	3461.1	3507.1	3526.8	3526.8	3579.4	3559.7	3599.1	3677.9
7.5°	2410.3	2476.0	2594.2	2692.7	2771.5	2797.8	2791.2	2804.4	2824.1	2778.1	2791.2
10°	1950.6	1904.6	1944.0	2036.0	2108.2	2193.6	2127.9	2121.3	2141.1	2121.3	2160.8
12.5°	1628.8	1576.2	1543.4	1543.4	1595.9	1635.3	1615.6	1648.5	1720.7	1740.4	1786.4
15°	1320.1	1274.1	1247.9	1215.0	1267.6	1280.7	1300.4	1346.4	1398.9	1425.2	1477.7
17.5°	1057.4	1057.4	1057.4	1031.1	1050.8	1070.5	1077.1	1136.2	1142.8	1169.0	1188.7
20°	866.9	886.6	919.5	932.6	952.3	952.3	939.2	972.0	945.7	965.4	978.6
22.5°	781.5	807.8	821.0	827.5	853.8	860.4	827.5	834.1	840.7	821.0	827.5
25°	735.6	748.7	735.6	742.1	748.7	735.6	742.1	755.3	748.7	761.8	755.3
27.5°	715.9	702.7	696.2	689.6	689.6	676.5	683.0	683.0	696.2	702.7	702.7
30°	715.9	696.2	669.9	650.2	650.2	630.5	643.6	656.8	663.3	676.5	676.5
32.5°	735.6	696.2	650.2	630.5	610.8	597.7	610.8	630.5	656.8	663.3	669.9
35°	584.5	604.2	597.7	571.4	564.8	564.8	558.2	558.2	538.5	538.5	532.0
37.5°	525.4	518.8	532.0	538.5	545.1	525.4	525.4	499.1	492.6	499.1	499.1
40°	492.6	492.6	492.6	512.3	518.8	505.7	486.0	472.9	472.9	472.9	479.4
42.5°	479.4	466.3	459.7	472.9	492.6	479.4	459.7	453.2	453.2	459.7	459.7
45°	459.7	453.2	446.6	440.0	466.3	446.6	440.0	433.5	433.5	433.5	440.0
47.5°	440.0	433.5	420.3	420.3	426.9	420.3	413.8	413.8	413.8	426.9	426.9
50°	426.9	420.3	407.2	407.2	407.2	407.2	400.6	400.6	400.6	407.2	413.8
52.5°	407.2	400.6	394.1	387.5	387.5	387.5	387.5	387.5	387.5	394.1	400.6
55°	387.5	380.9	374.4	374.4	380.9	380.9	374.4	380.9	374.4	380.9	387.5
57.5°	367.8	361.2	354.7	361.2	367.8	361.2	361.2	361.2	361.2	361.2	367.8
60°	341.5	341.5	341.5	341.5	354.7	354.7	354.7	354.7	341.5	348.1	354.7
62.5°	328.4	321.8	321.8	328.4	334.9	334.9	341.5	334.9	328.4	334.9	334.9
65°	302.1	302.1	302.1	308.7	308.7	315.2	315.2	315.2	308.7	315.2	315.2
67.5°	282.4	282.4	282.4	282.4	295.5	295.5	295.5	295.5	289.0	289.0	295.5
70°	249.6	256.1	249.6	262.7	275.8	269.3	275.8	275.8	269.3	262.7	275.8
72.5°	229.9	229.9	229.9	229.9	249.6	249.6	249.6	256.1	249.6	243.0	249.6
75°	203.6	203.6	203.6	210.2	223.3	223.3	223.3	223.3	223.3	216.7	216.7
77.5°	177.3	183.9	177.3	183.9	197.0	190.5	197.0	203.6	197.0	190.5	190.5
80°	151.1	151.1	151.1	157.6	164.2	164.2	164.2	170.8	164.2	157.6	157.6
82.5°	118.2	118.2	124.8	124.8	131.4	131.4	131.4	137.9	131.4	124.8	124.8
85°	91.9	91.9	91.9	98.5	98.5	105.1	105.1	111.6	111.6	105.1	105.1
87.5°	59.1	52.5	59.1	59.1	65.7	65.7	59.1	52.5	59.1	52.5	46.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598999
 CATALOG NUMBER: IFLD-S-SA3B-750-U-SLL

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7	4728.7
2.5°	4314.9	4433.2	4518.5	4577.6	4663.0	4827.2	4892.9	5011.1	5043.9	5063.6
5°	3710.7	3835.5	4019.4	4150.7	4301.8	4610.5	4846.9	5024.2	5103.1	5175.3
7.5°	2909.5	3073.7	3264.1	3434.9	3684.4	4065.4	4374.0	4741.8	4879.8	4952.0
10°	2272.4	2423.5	2633.6	2843.8	3191.9	3513.7	3953.7	4288.7	4479.1	4531.7
12.5°	1917.8	2095.1	2344.6	2600.8	2817.5	3185.3	3631.9	4117.9	4295.2	4328.1
15°	1628.8	1871.8	2127.9	2390.6	2640.2	2962.0	3441.4	4032.5	4295.2	4328.1
17.5°	1346.4	1563.1	1865.2	2147.6	2436.6	2876.6	3474.3	4104.8	4367.5	4466.0
20°	1070.5	1280.7	1517.1	1871.8	2265.8	2732.1	3546.5	4347.8	4695.9	4800.9
22.5°	886.6	978.6	1208.4	1550.0	2016.3	2633.6	3618.8	4728.7	5096.5	5135.9
25°	775.0	840.7	985.1	1307.0	1819.2	2567.9	3789.5	5168.7	5641.6	5641.6
27.5°	722.4	748.7	847.2	1136.2	1681.3	2508.8	3960.3	5654.7	6094.8	6186.7
30°	709.3	775.0	827.5	1011.4	1530.3	2344.6	4117.9	6035.7	6488.8	6495.4
32.5°	696.2	683.0	722.4	880.1	1346.4	2173.9	4249.3	6423.2	6777.8	6797.5
35°	545.1	571.4	637.1	775.0	1208.4	2049.1	4314.9	6633.3	7145.6	7165.3
37.5°	512.3	545.1	597.7	715.9	1116.5	1944.0	4334.6	7040.5	7533.1	7572.5
40°	499.1	525.4	564.8	663.3	1044.3	1812.7	4374.0	7460.8	8104.5	8051.9
42.5°	472.9	505.7	545.1	637.1	985.1	1714.2	4380.6	7690.7	8406.6	8406.6
45°	466.3	486.0	532.0	637.1	919.5	1628.8	4275.5	7920.6	8754.7	8649.6
47.5°	440.0	479.4	518.8	617.4	840.7	1543.4	4150.7	8038.8	8800.6	8767.8
50°	433.5	472.9	538.5	584.5	794.7	1504.0	4124.5	8334.3	8892.6	8886.0
52.5°	420.3	459.7	558.2	558.2	735.6	1451.4	4249.3	8465.7	8912.3	8964.8
55°	400.6	459.7	518.8	512.3	683.0	1385.8	4387.2	8807.2	9260.4	9247.2
57.5°	387.5	446.6	492.6	466.3	623.9	1339.8	4590.8	9135.6	9680.7	9588.8
60°	367.8	446.6	440.0	433.5	578.0	1300.4	4761.5	9201.3	9772.6	9831.8
62.5°	354.7	466.3	387.5	400.6	538.5	1280.7	4689.3	8708.7	9647.9	9700.4
65°	341.5	400.6	354.7	367.8	525.4	1241.3	4406.9	8117.6	9109.3	9339.2
67.5°	315.2	328.4	328.4	341.5	512.3	1149.3	3828.9	7053.6	8288.4	8413.1
70°	289.0	295.5	295.5	315.2	499.1	1044.3	3159.0	6101.3	7191.6	7428.0
72.5°	262.7	262.7	262.7	289.0	459.7	958.9	2600.8	4689.3	5976.6	6140.7
75°	229.9	229.9	229.9	256.1	413.8	873.5	2049.1	3487.4	4400.3	4636.8
77.5°	203.6	203.6	197.0	229.9	361.2	709.3	1477.7	2462.9	3099.9	3297.0
80°	170.8	164.2	164.2	183.9	282.4	512.3	952.3	1740.4	2160.8	2246.1
82.5°	137.9	131.4	124.8	137.9	203.6	321.8	591.1	1215.0	1385.8	1333.2
85°	131.4	137.9	111.6	105.1	144.5	210.2	374.4	748.7	623.9	623.9
87.5°	52.5	46.0	46.0	39.4	72.2	78.8	164.2	137.9	105.1	105.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)