

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599004

Luminaire Tested: **IFLD-S-SA6B-750-U-SLL**

Issue Date: 05/03/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

**Test Information**

Test Method: LM-79-08  
 Report Number: P599004  
 Test Lab: INNOVATION CENTER(G1)  
 Issue Date: 05/03/2022  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: IFLD-S-SA6B-750-U-SLL  
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens  
 Light Source: (96) 5000K CCT, 70 CRI LEDs  
 Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
 Luminaire Lumens: 29043.1 lumens  
 Efficiency: N/A  
 Efficacy: 118.6 lumens/watt  
 Spacing Criteria (0/90/45): 1.12 / 0.52 / 0.8  
 Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
 CIE Type: Direct

Input Watts (W): 244.9  
 Input Voltage (V): 120  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599004  
CATALOG NUMBER: IFLD-S-SA6B-750-U-SLL

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    ···· 90°-270°    - · - · 135°-315°

TEST NUMBER: P599004  
 CATALOG NUMBER: IFLD-S-SA6B-750-U-SLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	106	100	94	89	103	97	92	88	93	89	85	89	85	82	85	82	80	77				77
2	94	83	75	68	91	81	74	67	78	71	65	74	69	64	71	66	62	60				60
3	84	71	61	53	81	69	60	53	66	58	52	63	56	51	60	55	50	47				47
4	75	61	51	43	73	60	50	42	57	48	42	54	47	41	52	46	40	38				38
5	68	53	43	35	66	52	42	35	50	41	34	48	40	34	46	39	34	31				31
6	63	47	37	30	60	46	37	29	44	36	29	42	35	29	41	34	29	26				26
7	58	42	32	25	56	41	32	25	40	31	25	38	31	25	37	30	25	22				22
8	53	38	29	22	52	37	28	22	36	28	22	35	27	22	33	27	22	19				19
9	50	35	26	20	48	34	26	20	33	25	19	32	25	19	31	24	19	17				17
10	46	32	23	18	45	31	23	18	30	23	17	29	22	17	28	22	17	15				15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	66565	66565	66565	66565
5°	73131	64963	46588	50857
10°	64776	57172	28258	30323
15°	63075	54269	20004	20769
20°	71920	62770	13085	14463
25°	87626	79567	11425	11833
30°	105580	96506	11850	10996
35°	123134	113314	9819	9255
40°	147963	136860	9173	8689
45°	172194	157289	9283	8629
50°	194602	178780	9493	8918
55°	226949	213086	9832	9348
60°	276802	269220	9799	9799
65°	311077	311513	10062	10500
70°	305723	316535	10543	10812
75°	252188	268978	11074	11789
80°	182085	191135	12244	12778
85°	100769	108196	13791	16969

TEST NUMBER: P599004  
 CATALOG NUMBER: IFLD-S-SA6B-750-U-SLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	720.6	2.5
10°-20°	1521.5	5.2
20°-30°	2226.1	7.7
30°-40°	3136.5	10.8
40°-50°	4310.5	14.8
50°-60°	5874.7	20.2
60°-70°	6429.6	22.1
70°-80°	3712.0	12.8
80°-90°	1111.6	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4468.3	15.4
0°-40°	7604.8	26.2
0°-60°	17789.9	61.3
0°-90°	29043.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	29043.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	9276	9276	9276	9276	9276	
5°	10152	9018	6468	7060	10152	922
15°	8490	7305	2693	2796	8490	2481
25°	11067	10049	1443	1494	11067	5182
35°	14056	12935	1121	1056	14056	8913
45°	16968	15499	915	850	16968	13041
55°	18140	17032	786	747	18140	16368
65°	18320	18346	593	618	18320	17535
75°	9096	9701	399	425	9096	9771
85°	1224	1314	168	206	1224	1698
90°	0	0	0	0	0	

TEST NUMBER: P599004  
 CATALOG NUMBER: IFLD-S-SA6B-750-U-SLL

**CANDELA DISTRIBUTION (FULL):**

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2
2.5°	9933.3	9894.6	9933.3	10075.0	10113.6	10178.0	10178.0	10087.9	9920.4	9843.1	9714.2
5°	10152.3	10087.9	10410.0	10706.3	10938.2	10912.4	10693.4	10513.0	10178.0	9675.6	9198.9
7.5°	9714.2	9778.7	10010.6	10783.6	11324.7	11427.8	11079.9	10719.2	9997.7	9302.0	8657.8
10°	8889.7	8979.9	9482.3	10281.1	11131.4	11298.9	11079.9	10641.9	9778.7	8915.5	8168.2
12.5°	8490.3	8696.4	8992.8	9959.0	10564.6	10963.9	10860.9	10577.4	9611.2	8593.4	7871.9
15°	8490.3	8541.8	8979.9	9791.5	10139.4	10152.3	10190.9	10242.5	9662.7	8735.1	7768.8
17.5°	8760.8	8902.6	9276.2	9778.7	9843.1	9688.5	9688.5	9907.5	9765.8	9134.5	8142.4
20°	9417.9	9366.4	9856.0	10062.1	9714.2	9327.7	9289.1	9662.7	9881.7	9559.6	8825.3
22.5°	10075.0	10306.9	10706.3	10242.5	9598.3	9082.9	9031.4	9495.2	10229.6	10294.0	9611.2
25°	11067.0	11298.9	11505.1	10938.2	9585.4	9018.5	9057.2	9417.9	10654.7	11337.6	10925.3
27.5°	12136.4	12278.1	12574.4	11698.3	9894.6	8941.2	8979.9	9521.0	11054.1	12020.4	11956.0
30°	12741.9	12896.5	12832.1	11840.0	10100.7	8992.8	8889.7	9662.7	10835.1	12020.4	12625.9
32.5°	13334.5	13244.3	13205.7	12071.9	10358.4	9314.8	9057.2	9959.0	10963.9	12213.7	13489.1
35°	14056.0	13927.2	13824.1	12522.9	10783.6	9624.1	9508.1	10345.5	11247.4	12613.0	14184.8
37.5°	14854.8	14854.8	14352.3	12857.8	11286.0	10126.5	9997.7	10899.5	11698.3	12857.8	15138.2
40°	15795.3	15833.9	14945.0	13308.8	11852.9	10925.3	10886.6	11621.0	12136.4	13218.6	16053.0
42.5°	16491.0	16516.8	15460.3	13476.2	12510.0	12033.3	12200.8	12780.5	12638.8	13540.7	16117.4
45°	16967.7	16838.9	15821.1	13952.9	13231.5	13695.3	13746.8	13914.3	13295.9	13733.9	16375.1
47.5°	17199.6	17173.8	15975.7	14506.9	14751.7	15383.0	15679.3	15447.4	13901.4	13527.8	16375.1
50°	17431.5	17212.5	16117.4	15267.1	16233.3	17508.8	17444.4	17019.2	14738.8	13785.5	16130.3
52.5°	17586.1	17392.9	16400.8	15949.9	17650.5	19093.5	19351.2	18565.3	15718.0	14262.1	16246.2
55°	18140.1	17985.5	17251.1	16877.5	19286.8	20768.4	20807.0	19711.9	16748.7	15048.0	17006.4
57.5°	18810.1	18900.2	18423.6	18191.6	20536.5	21992.3	21850.6	20562.2	17624.8	16001.4	17882.4
60°	19286.8	19428.5	19312.5	19338.3	21154.9	22404.6	22082.5	21090.5	18268.9	16722.9	18951.8
62.5°	19029.1	19312.5	19789.2	19686.1	21180.6	22108.3	21657.3	20394.7	18346.2	17663.4	19763.4
65°	18320.5	18346.2	19273.9	19840.7	20021.1	20575.1	19982.5	18938.9	17547.5	18243.2	19647.5
67.5°	16503.9	16710.0	17547.5	18655.5	17895.3	18024.2	17972.6	16465.2	16336.4	17843.8	18758.5
70°	14571.4	14713.1	15627.8	16929.1	15112.5	14506.9	14622.9	13502.0	14030.2	16607.0	16967.7
72.5°	12046.2	12136.4	13179.9	14326.6	12123.5	11041.2	11311.8	10397.1	11144.3	14532.7	14313.7
75°	9095.8	9263.3	10075.0	11427.8	8928.3	8232.6	8503.2	8129.6	8825.3	11968.9	11105.7
77.5°	6467.6	6338.7	7343.7	8941.2	6712.4	6300.1	6325.8	6390.3	7137.5	10087.9	7974.9
80°	4406.2	4444.8	5346.7	6557.8	5269.4	5205.0	5140.6	5655.9	5990.9	7987.8	5797.6
82.5°	2615.4	2615.4	3607.4	4663.9	4161.4	4689.6	4393.3	4857.1	4689.6	5874.9	3800.7
85°	1223.9	1223.9	1855.2	3362.6	3220.9	3865.1	3285.3	3671.8	3465.7	4097.0	1713.5
87.5°	206.1	180.4	373.6	1649.1	1327.0	1507.4	592.6	1958.3	2177.3	2860.2	425.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599004  
 CATALOG NUMBER: IFLD-S-SA6B-750-U-SLL

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2
2.5°	9572.5	9482.3	9302.0	9070.1	8876.8	8632.0	8554.7	8387.2	8155.3	8129.6	8026.5
5°	9018.5	8709.3	8322.8	7846.1	7524.0	7189.0	6905.6	6738.1	6544.9	6519.1	6467.6
7.5°	8413.0	8026.5	7382.3	6815.4	6261.4	5733.2	5475.5	5153.4	4934.4	4766.9	4689.6
10°	7846.1	7485.4	6686.6	5913.6	5424.0	5076.1	4766.9	4432.0	4161.4	3955.3	3878.0
12.5°	7472.5	7047.3	6184.1	5449.8	5089.0	4689.6	4341.8	3981.0	3633.2	3362.6	3220.9
15°	7305.0	6905.6	6029.5	5217.9	4689.6	4135.6	3736.2	3375.5	2950.3	2757.1	2692.7
17.5°	7704.4	7111.7	5978.0	4947.3	4200.1	3568.8	3079.2	2692.7	2383.5	2190.2	2112.9
20°	8219.7	7485.4	6068.2	4625.2	3736.2	3027.6	2486.5	2074.3	1868.1	1726.4	1713.5
22.5°	8876.8	8039.4	6209.9	4393.3	3220.9	2435.0	1945.4	1700.6	1558.9	1546.0	1520.3
25°	10049.2	9044.3	6441.8	4084.1	2808.6	2009.8	1662.0	1520.3	1455.8	1417.2	1443.0
27.5°	11054.1	9701.4	6609.3	3890.8	2641.1	1893.9	1610.5	1455.8	1391.4	1378.5	1391.4
30°	11646.8	10306.9	6557.8	3530.1	2306.2	1803.7	1713.5	1662.0	1533.1	1430.1	1430.1
32.5°	12187.9	10693.4	6544.9	3208.0	1971.2	1507.4	1430.1	1391.4	1468.7	1520.3	1481.6
35°	12935.1	11298.9	6506.2	3027.6	1829.5	1391.4	1262.6	1159.5	1108.0	1082.2	1120.9
37.5°	13733.9	11711.2	6403.2	3001.9	1752.2	1327.0	1223.9	1120.9	1069.3	1043.6	1030.7
40°	14610.0	12149.2	6287.2	2873.0	1713.5	1288.4	1185.3	1095.1	1030.7	992.0	979.2
42.5°	15176.9	12497.1	6171.2	2808.6	1636.2	1262.6	1146.6	1069.3	1004.9	953.4	953.4
45°	15499.0	12909.4	6055.3	2744.2	1546.0	1275.5	1146.6	1043.6	966.3	940.5	914.7
47.5°	15640.7	13218.6	6016.6	2641.1	1468.7	1223.9	1120.9	1017.8	940.5	889.0	876.1
50°	16014.3	13875.6	6158.4	2563.8	1378.5	1172.4	1185.3	1004.9	927.6	863.2	850.3
52.5°	16233.3	14403.9	6467.6	2447.9	1314.1	1108.0	1159.5	979.2	889.0	824.6	824.6
55°	17032.1	15280.0	6802.5	2357.7	1236.8	1017.8	1069.3	927.6	824.6	785.9	785.9
57.5°	18049.9	16207.6	7086.0	2319.0	1185.3	953.4	953.4	901.9	785.9	734.4	721.5
60°	18758.5	16967.7	7253.5	2293.3	1133.8	889.0	850.3	901.9	747.2	695.7	682.8
62.5°	18835.8	16529.7	7086.0	2280.4	1120.9	824.6	773.0	863.2	708.6	657.1	631.3
65°	18346.2	15640.7	6622.2	2228.9	1108.0	760.1	721.5	747.2	657.1	618.4	592.6
67.5°	17367.1	14197.7	5952.2	2203.1	1095.1	708.6	657.1	644.2	605.5	566.9	541.1
70°	15086.7	12316.7	5166.3	2087.1	1069.3	669.9	592.6	579.8	541.1	515.3	502.5
72.5°	12664.6	10075.0	4264.5	1932.5	1017.8	605.5	541.1	515.3	502.5	463.8	450.9
75°	9701.4	7755.9	3414.2	1713.5	889.0	541.1	476.7	450.9	438.0	412.3	399.4
77.5°	6815.4	5771.9	2525.2	1391.4	747.2	489.6	425.2	399.4	386.5	347.9	347.9
80°	4625.2	4045.5	1713.5	966.3	579.8	399.4	373.6	347.9	322.1	296.3	296.3
82.5°	2873.0	2834.4	1236.8	631.3	425.2	322.1	296.3	296.3	257.7	231.9	231.9
85°	1314.1	1739.3	863.2	438.0	322.1	244.8	244.8	231.9	206.1	167.5	167.5
87.5°	412.3	579.8	450.9	193.3	180.4	141.7	141.7	128.8	128.8	103.1	103.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599004  
 CATALOG NUMBER: IFLD-S-SA6B-750-U-SLL

**CANDELA DISTRIBUTION (continued):**

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2
2.5°	8129.6	8116.7	8116.7	8065.1	8194.0	8194.0	8271.3	8206.9	8245.5	8258.4	8361.5
5°	6454.7	6557.8	6635.1	6789.7	6879.8	6918.5	6918.5	7021.6	6982.9	7060.2	7214.8
7.5°	4728.3	4857.1	5089.0	5282.3	5436.9	5488.4	5475.5	5501.3	5539.9	5449.8	5475.5
10°	3826.4	3736.2	3813.5	3993.9	4135.6	4303.1	4174.3	4161.4	4200.1	4161.4	4238.7
12.5°	3195.1	3092.1	3027.6	3027.6	3130.7	3208.0	3169.4	3233.8	3375.5	3414.2	3504.3
15°	2589.6	2499.4	2447.9	2383.5	2486.5	2512.3	2551.0	2641.1	2744.2	2795.7	2898.8
17.5°	2074.3	2074.3	2074.3	2022.7	2061.4	2100.0	2112.9	2228.9	2241.7	2293.3	2331.9
20°	1700.6	1739.3	1803.7	1829.5	1868.1	1868.1	1842.4	1906.8	1855.2	1893.9	1919.7
22.5°	1533.1	1584.7	1610.5	1623.3	1674.9	1687.8	1623.3	1636.2	1649.1	1610.5	1623.3
25°	1443.0	1468.7	1443.0	1455.8	1468.7	1443.0	1455.8	1481.6	1468.7	1494.5	1481.6
27.5°	1404.3	1378.5	1365.7	1352.8	1352.8	1327.0	1339.9	1339.9	1365.7	1378.5	1378.5
30°	1404.3	1365.7	1314.1	1275.5	1275.5	1236.8	1262.6	1288.4	1301.2	1327.0	1327.0
32.5°	1443.0	1365.7	1275.5	1236.8	1198.2	1172.4	1198.2	1236.8	1288.4	1301.2	1314.1
35°	1146.6	1185.3	1172.4	1120.9	1108.0	1108.0	1095.1	1095.1	1056.5	1056.5	1043.6
37.5°	1030.7	1017.8	1043.6	1056.5	1069.3	1030.7	1030.7	979.2	966.3	979.2	979.2
40°	966.3	966.3	966.3	1004.9	1017.8	992.0	953.4	927.6	927.6	927.6	940.5
42.5°	940.5	914.7	901.9	927.6	966.3	940.5	901.9	889.0	889.0	901.9	901.9
45°	901.9	889.0	876.1	863.2	914.7	876.1	863.2	850.3	850.3	850.3	863.2
47.5°	863.2	850.3	824.6	824.6	837.4	824.6	811.7	811.7	811.7	837.4	837.4
50°	837.4	824.6	798.8	798.8	798.8	798.8	785.9	785.9	785.9	798.8	811.7
52.5°	798.8	785.9	773.0	760.1	760.1	760.1	760.1	760.1	760.1	773.0	785.9
55°	760.1	747.2	734.4	734.4	747.2	747.2	734.4	747.2	734.4	747.2	760.1
57.5°	721.5	708.6	695.7	708.6	721.5	708.6	708.6	708.6	708.6	708.6	721.5
60°	669.9	669.9	669.9	669.9	695.7	695.7	695.7	695.7	669.9	682.8	695.7
62.5°	644.2	631.3	631.3	644.2	657.1	657.1	669.9	657.1	644.2	657.1	657.1
65°	592.6	592.6	592.6	605.5	605.5	618.4	618.4	618.4	605.5	618.4	618.4
67.5°	554.0	554.0	554.0	554.0	579.8	579.8	579.8	579.8	566.9	566.9	579.8
70°	489.6	502.5	489.6	515.3	541.1	528.2	541.1	541.1	528.2	515.3	541.1
72.5°	450.9	450.9	450.9	450.9	489.6	489.6	489.6	502.5	489.6	476.7	489.6
75°	399.4	399.4	399.4	412.3	438.0	438.0	438.0	438.0	438.0	425.2	425.2
77.5°	347.9	360.7	347.9	360.7	386.5	373.6	386.5	399.4	386.5	373.6	373.6
80°	296.3	296.3	296.3	309.2	322.1	322.1	322.1	335.0	322.1	309.2	309.2
82.5°	231.9	231.9	244.8	244.8	257.7	257.7	257.7	270.6	257.7	244.8	244.8
85°	180.4	180.4	180.4	193.3	193.3	206.1	206.1	219.0	219.0	206.1	206.1
87.5°	116.0	103.1	116.0	116.0	128.8	128.8	116.0	103.1	116.0	103.1	90.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P599004  
 CATALOG NUMBER: IFLD-S-SA6B-750-U-SLL

**CANDELA DISTRIBUTION (continued):**

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2	9276.2
2.5°	8464.5	8696.4	8863.9	8979.9	9147.4	9469.4	9598.3	9830.2	9894.6	9933.3
5°	7279.2	7524.0	7884.8	8142.4	8438.8	9044.3	9508.1	9856.0	10010.6	10152.3
7.5°	5707.4	6029.5	6403.2	6738.1	7227.7	7974.9	8580.5	9302.0	9572.5	9714.2
10°	4457.7	4754.0	5166.3	5578.6	6261.4	6892.7	7755.9	8413.0	8786.6	8889.7
12.5°	3762.0	4109.9	4599.4	5101.9	5527.1	6248.5	7124.6	8078.0	8425.9	8490.3
15°	3195.1	3671.8	4174.3	4689.6	5179.2	5810.5	6751.0	7910.5	8425.9	8490.3
17.5°	2641.1	3066.3	3658.9	4212.9	4779.8	5643.0	6815.4	8052.3	8567.6	8760.8
20°	2100.0	2512.3	2976.1	3671.8	4444.8	5359.6	6957.1	8528.9	9211.8	9417.9
22.5°	1739.3	1919.7	2370.6	3040.5	3955.3	5166.3	7098.9	9276.2	9997.7	10075.0
25°	1520.3	1649.1	1932.5	2563.8	3568.8	5037.5	7433.8	10139.4	11067.0	11067.0
27.5°	1417.2	1468.7	1662.0	2228.9	3298.2	4921.5	7768.8	11092.8	11956.0	12136.4
30°	1391.4	1520.3	1623.3	1984.1	3001.9	4599.4	8078.0	11840.0	12729.0	12741.9
32.5°	1365.7	1339.9	1417.2	1726.4	2641.1	4264.5	8335.7	12600.2	13295.9	13334.5
35°	1069.3	1120.9	1249.7	1520.3	2370.6	4019.7	8464.5	13012.4	14017.4	14056.0
37.5°	1004.9	1069.3	1172.4	1404.3	2190.2	3813.5	8503.2	13811.2	14777.5	14854.8
40°	979.2	1030.7	1108.0	1301.2	2048.5	3555.9	8580.5	14635.8	15898.4	15795.3
42.5°	927.6	992.0	1069.3	1249.7	1932.5	3362.6	8593.4	15086.7	16491.0	16491.0
45°	914.7	953.4	1043.6	1249.7	1803.7	3195.1	8387.2	15537.6	17173.8	16967.7
47.5°	863.2	940.5	1017.8	1211.1	1649.1	3027.6	8142.4	15769.5	17264.0	17199.6
50°	850.3	927.6	1056.5	1146.6	1558.9	2950.3	8090.9	16349.3	17444.4	17431.5
52.5°	824.6	901.9	1095.1	1095.1	1443.0	2847.3	8335.7	16607.0	17483.0	17586.1
55°	785.9	901.9	1017.8	1004.9	1339.9	2718.4	8606.2	17276.9	18165.9	18140.1
57.5°	760.1	876.1	966.3	914.7	1223.9	2628.3	9005.6	17921.1	18990.4	18810.1
60°	721.5	876.1	863.2	850.3	1133.8	2551.0	9340.6	18049.9	19170.8	19286.8
62.5°	695.7	914.7	760.1	785.9	1056.5	2512.3	9198.9	17083.7	18926.0	19029.1
65°	669.9	785.9	695.7	721.5	1030.7	2435.0	8644.9	15924.1	17869.6	18320.5
67.5°	618.4	644.2	644.2	669.9	1004.9	2254.6	7511.1	13837.0	16259.1	16503.9
70°	566.9	579.8	579.8	618.4	979.2	2048.5	6197.0	11968.9	14107.5	14571.4
72.5°	515.3	515.3	515.3	566.9	901.9	1881.0	5101.9	9198.9	11724.1	12046.2
75°	450.9	450.9	450.9	502.5	811.7	1713.5	4019.7	6841.2	8632.0	9095.8
77.5°	399.4	399.4	386.5	450.9	708.6	1391.4	2898.8	4831.4	6081.1	6467.6
80°	335.0	322.1	322.1	360.7	554.0	1004.9	1868.1	3414.2	4238.7	4406.2
82.5°	270.6	257.7	244.8	270.6	399.4	631.3	1159.5	2383.5	2718.4	2615.4
85°	257.7	270.6	219.0	206.1	283.4	412.3	734.4	1468.7	1223.9	1223.9
87.5°	103.1	90.2	90.2	77.3	141.7	154.6	322.1	270.6	206.1	206.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)