

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599006

Luminaire Tested: **IFLD-S-SA6D-750-U-SLL**

Issue Date: 05/03/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P599006
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/03/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-S-SA6D-750-U-SLL
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens
 Light Source: (96) 5000K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 39781.8 lumens
 Efficiency: N/A
 Efficacy: 108.0 lumens/watt
 Spacing Criteria (0/90/45): 1.12 / 0.52 / 0.8
 Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
 CIE Type: Direct

Input Watts (W): 368.2
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599006
CATALOG NUMBER: IFLD-S-SA6D-750-U-SLL

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ··· 90°-270° - · 135°-315°

TEST NUMBER: P599006
 CATALOG NUMBER: IFLD-S-SA6D-750-U-SLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	106	100	94	89	103	97	92	88	93	89	85	89	85	82	85	82	80	77		
2	94	83	75	68	91	81	74	67	78	71	65	74	69	64	71	66	62	60		
3	84	71	61	53	81	69	60	53	66	58	52	63	56	51	60	55	50	47		
4	75	61	51	43	73	60	50	42	57	48	42	54	47	41	52	46	40	38		
5	68	53	43	35	66	52	42	35	50	41	34	48	40	34	46	39	34	31		
6	63	47	37	30	60	46	37	29	44	36	29	42	35	29	41	34	29	26		
7	58	42	32	25	56	41	32	25	40	31	25	38	31	25	37	30	25	22		
8	53	38	29	22	52	37	28	22	36	28	22	35	27	22	33	27	22	19		
9	50	35	26	20	48	34	26	20	33	25	19	32	25	19	31	24	19	17		
10	46	32	23	18	45	31	23	18	30	23	17	29	22	17	28	22	17	15		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	91178	91178	91178	91178
5°	100171	88984	63815	69661
10°	88727	78311	38705	41535
15°	86397	74335	27401	28450
20°	98512	85979	17924	19811
25°	120026	108987	15649	16208
30°	144618	132189	16232	15062
35°	168662	155213	13450	12677
40°	202672	187464	12564	11902
45°	235862	215446	12716	11820
50°	266555	244884	13002	12214
55°	310863	291876	13468	12805
60°	379148	368765	13423	13423
65°	426098	426697	13784	14384
70°	418763	433573	14439	14811
75°	345435	368430	15169	16147
80°	249411	261808	16774	17501
85°	138034	148202	18888	23251

TEST NUMBER: P599006
 CATALOG NUMBER: IFLD-S-SA6D-750-U-SLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	987.1	2.5
10°-20°	2084.1	5.2
20°-30°	3049.2	7.7
30°-40°	4296.2	10.8
40°-50°	5904.3	14.8
50°-60°	8046.8	20.2
60°-70°	8806.9	22.1
70°-80°	5084.6	12.8
80°-90°	1522.6	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6120.4	15.4
0°-40°	10416.6	26.2
0°-60°	24367.7	61.3
0°-90°	39781.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	39781.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	12706	12706	12706	12706	12706	
5°	13906	12353	8859	9671	13906	1263
15°	11630	10006	3688	3830	11630	3398
25°	15159	13765	1976	2047	15159	7098
35°	19253	17718	1535	1447	19253	12208
45°	23242	21230	1253	1165	23242	17863
55°	24847	23330	1076	1024	24847	22420
65°	25094	25130	812	847	25094	24018
75°	12459	13288	547	582	12459	13383
85°	1676	1800	229	282	1676	2326
90°	0	0	0	0	0	

TEST NUMBER: P599006
 CATALOG NUMBER: IFLD-S-SA6D-750-U-SLL

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1
2.5°	13606.1	13553.1	13606.1	13800.2	13853.2	13941.4	13941.4	13817.9	13588.4	13482.6	13306.1
5°	13906.1	13817.9	14259.0	14664.9	14982.6	14947.3	14647.3	14400.2	13941.4	13253.1	12600.2
7.5°	13306.1	13394.3	13712.0	14770.8	15512.0	15653.2	15176.7	14682.6	13694.3	12741.4	11859.0
10°	12176.7	12300.2	12988.4	14082.6	15247.3	15476.7	15176.7	14576.7	13394.3	12211.9	11188.4
12.5°	11629.6	11911.9	12317.8	13641.4	14470.8	15017.9	14876.7	14488.5	13164.9	11770.8	10782.5
15°	11629.6	11700.2	12300.2	13412.0	13888.4	13906.1	13959.0	14029.6	13235.5	11964.9	10641.3
17.5°	12000.2	12194.3	12706.1	13394.3	13482.6	13270.8	13270.8	13570.8	13376.7	12512.0	11153.1
20°	12900.2	12829.6	13500.2	13782.6	13306.1	12776.7	12723.7	13235.5	13535.5	13094.3	12088.4
22.5°	13800.2	14117.9	14664.9	14029.6	13147.3	12441.4	12370.8	13006.1	14012.0	14100.2	13164.9
25°	15159.1	15476.7	15759.1	14982.6	13129.6	12353.1	12406.1	12900.2	14594.3	15529.6	14964.9
27.5°	16623.8	16817.9	17223.8	16023.8	13553.1	12247.2	12300.2	13041.4	15141.4	16465.0	16376.7
30°	17453.2	17665.0	17576.7	16217.9	13835.5	12317.8	12176.7	13235.5	14841.4	16465.0	17294.4
32.5°	18265.0	18141.5	18088.5	16535.5	14188.4	12759.0	12406.1	13641.4	15017.9	16729.7	18476.7
35°	19253.2	19076.8	18935.6	17153.2	14770.8	13182.6	13023.7	14170.8	15406.1	17276.7	19429.7
37.5°	20347.4	20347.4	19659.1	17612.0	15459.1	13870.8	13694.3	14929.6	16023.8	17612.0	20735.6
40°	21635.6	21688.6	20470.9	18229.7	16235.5	14964.9	14912.0	15917.9	16623.8	18106.2	21988.6
42.5°	22588.6	22623.9	21176.8	18459.1	17135.6	16482.6	16712.0	17506.1	17312.0	18547.3	22076.8
45°	23241.5	23065.1	21670.9	19112.1	18123.8	18759.1	18829.7	19059.1	18212.0	18812.0	22429.7
47.5°	23559.2	23523.9	21882.7	19870.9	20206.2	21070.9	21476.8	21159.1	19041.5	18529.7	22429.7
50°	23876.8	23576.8	22076.8	20912.1	22235.6	23982.7	23894.5	23312.1	20188.5	18882.6	22094.5
52.5°	24088.6	23823.9	22465.0	21847.4	24176.8	26153.3	26506.3	25429.8	21529.7	19535.6	22253.3
55°	24847.4	24635.7	23629.8	23118.0	26418.0	28447.5	28500.4	27000.4	22941.5	20612.1	23294.5
57.5°	25765.1	25888.6	25235.7	24918.0	28129.8	30124.0	29929.9	28165.1	24141.5	21918.0	24494.5
60°	26418.0	26612.2	26453.3	26488.6	28976.9	30688.7	30247.5	28888.7	25023.9	22906.2	25959.2
62.5°	26065.1	26453.3	27106.3	26965.1	29012.2	30282.8	29665.2	27935.7	25129.8	24194.5	27071.0
65°	25094.5	25129.8	26400.4	27176.9	27423.9	28182.8	27371.0	25941.6	24035.7	24988.6	26912.2
67.5°	22606.2	22888.6	24035.7	25553.3	24512.1	24688.6	24618.0	22553.3	22376.8	24441.5	25694.5
70°	19959.1	20153.2	21406.2	23188.6	20700.3	19870.9	20029.7	18494.4	19217.9	22747.4	23241.5
72.5°	16500.2	16623.8	18053.2	19623.8	16606.1	15123.8	15494.4	14241.4	15264.9	19906.2	19606.2
75°	12459.0	12688.4	13800.2	15653.2	12229.6	11276.6	11647.2	11135.5	12088.4	16394.4	15212.0
77.5°	8859.0	8682.5	10059.0	12247.2	9194.3	8629.5	8664.8	8753.1	9776.6	13817.9	10923.7
80°	6035.4	6088.3	7323.6	8982.5	7217.8	7129.5	7041.3	7747.2	8206.0	10941.3	7941.3
82.5°	3582.4	3582.4	4941.3	6388.3	5700.1	6423.6	6017.7	6653.0	6423.6	8047.2	5206.0
85°	1676.5	1676.5	2541.2	4606.0	4411.8	5294.2	4500.1	5029.5	4747.1	5611.8	2347.1
87.5°	282.4	247.1	511.8	2258.9	1817.7	2064.7	811.8	2682.4	2982.4	3917.7	582.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599006
 CATALOG NUMBER: IFLD-S-SA6D-750-U-SLL

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1
2.5°	13112.0	12988.4	12741.4	12423.7	12159.0	11823.7	11717.8	11488.4	11170.8	11135.5	10994.3
5°	12353.1	11929.6	11400.2	10747.2	10306.0	9847.2	9459.0	9229.6	8964.8	8929.5	8859.0
7.5°	11523.7	10994.3	10111.9	9335.4	8576.6	7853.1	7500.1	7058.9	6758.9	6529.5	6423.6
10°	10747.2	10253.1	9159.0	8100.1	7429.5	6953.0	6529.5	6070.7	5700.1	5417.7	5311.8
12.5°	10235.4	9653.1	8470.7	7464.8	6970.7	6423.6	5947.1	5453.0	4976.5	4606.0	4411.8
15°	10006.0	9459.0	8258.9	7147.2	6423.6	5664.8	5117.7	4623.6	4041.2	3776.5	3688.3
17.5°	10553.1	9741.3	8188.4	6776.6	5753.0	4888.3	4217.7	3688.3	3264.8	3000.0	2894.2
20°	11259.0	10253.1	8311.9	6335.4	5117.7	4147.1	3405.9	2841.2	2558.9	2364.7	2347.1
22.5°	12159.0	11011.9	8506.0	6017.7	4411.8	3335.3	2664.7	2329.4	2135.3	2117.7	2082.4
25°	13764.9	12388.4	8823.7	5594.2	3847.1	2753.0	2276.5	2082.4	1994.1	1941.2	1976.5
27.5°	15141.4	13288.4	9053.1	5329.5	3617.7	2594.2	2205.9	1994.1	1905.9	1888.3	1905.9
30°	15953.2	14117.9	8982.5	4835.4	3158.9	2470.6	2347.1	2276.5	2100.0	1958.9	1958.9
32.5°	16694.4	14647.3	8964.8	4394.2	2700.0	2064.7	1958.9	1905.9	2011.8	2082.4	2029.4
35°	17717.9	15476.7	8911.9	4147.1	2505.9	1905.9	1729.4	1588.3	1517.7	1482.4	1535.3
37.5°	18812.0	16041.4	8770.7	4111.8	2400.0	1817.7	1676.5	1535.3	1464.7	1429.4	1411.8
40°	20012.1	16641.4	8611.9	3935.4	2347.1	1764.7	1623.6	1500.0	1411.8	1358.8	1341.2
42.5°	20788.5	17117.9	8453.1	3847.1	2241.2	1729.4	1570.6	1464.7	1376.5	1305.9	1305.9
45°	21229.7	17682.6	8294.2	3758.9	2117.7	1747.1	1570.6	1429.4	1323.5	1288.3	1253.0
47.5°	21423.9	18106.2	8241.3	3617.7	2011.8	1676.5	1535.3	1394.1	1288.3	1217.7	1200.0
50°	21935.6	19006.2	8435.4	3511.8	1888.3	1605.9	1623.6	1376.5	1270.6	1182.4	1164.7
52.5°	22235.6	19729.7	8859.0	3353.0	1800.0	1517.7	1588.3	1341.2	1217.7	1129.4	1129.4
55°	23329.8	20929.7	9317.8	3229.5	1694.1	1394.1	1464.7	1270.6	1129.4	1076.5	1076.5
57.5°	24723.9	22200.3	9706.0	3176.5	1623.6	1305.9	1305.9	1235.3	1076.5	1005.9	988.3
60°	25694.5	23241.5	9935.4	3141.2	1553.0	1217.7	1164.7	1235.3	1023.5	953.0	935.3
62.5°	25800.4	22641.5	9706.0	3123.6	1535.3	1129.4	1058.8	1182.4	970.6	900.0	864.7
65°	25129.8	21423.9	9070.7	3053.0	1517.7	1041.2	988.3	1023.5	900.0	847.1	811.8
67.5°	23788.6	19447.4	8153.1	3017.7	1500.0	970.6	900.0	882.4	829.4	776.5	741.2
70°	20665.0	16870.8	7076.6	2858.9	1464.7	917.7	811.8	794.1	741.2	705.9	688.2
72.5°	17347.3	13800.2	5841.3	2647.1	1394.1	829.4	741.2	705.9	688.2	635.3	617.7
75°	13288.4	10623.7	4676.5	2347.1	1217.7	741.2	653.0	617.7	600.0	564.7	547.1
77.5°	9335.4	7906.0	3458.9	1905.9	1023.5	670.6	582.4	547.1	529.4	476.5	476.5
80°	6335.4	5541.3	2347.1	1323.5	794.1	547.1	511.8	476.5	441.2	405.9	405.9
82.5°	3935.4	3882.4	1694.1	864.7	582.4	441.2	405.9	405.9	352.9	317.7	317.7
85°	1800.0	2382.4	1182.4	600.0	441.2	335.3	335.3	317.7	282.4	229.4	229.4
87.5°	564.7	794.1	617.7	264.7	247.1	194.1	194.1	176.5	176.5	141.2	141.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599006
 CATALOG NUMBER: IFLD-S-SA6D-750-U-SLL

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1
2.5°	11135.5	11117.8	11117.8	11047.2	11223.7	11223.7	11329.6	11241.3	11294.3	11311.9	11453.1
5°	8841.3	8982.5	9088.4	9300.1	9423.7	9476.6	9476.6	9617.8	9564.9	9670.7	9882.5
7.5°	6476.6	6653.0	6970.7	7235.4	7447.2	7517.8	7500.1	7535.4	7588.3	7464.8	7500.1
10°	5241.3	5117.7	5223.6	5470.7	5664.8	5894.2	5717.7	5700.1	5753.0	5700.1	5806.0
12.5°	4376.5	4235.4	4147.1	4147.1	4288.3	4394.2	4341.2	4429.5	4623.6	4676.5	4800.1
15°	3547.1	3423.6	3353.0	3264.8	3405.9	3441.2	3494.2	3617.7	3758.9	3829.5	3970.6
17.5°	2841.2	2841.2	2841.2	2770.6	2823.6	2876.5	2894.2	3053.0	3070.6	3141.2	3194.2
20°	2329.4	2382.4	2470.6	2505.9	2558.9	2558.9	2523.6	2611.8	2541.2	2594.2	2629.5
22.5°	2100.0	2170.6	2205.9	2223.6	2294.2	2311.8	2223.6	2241.2	2258.9	2205.9	2223.6
25°	1976.5	2011.8	1976.5	1994.1	2011.8	1976.5	1994.1	2029.4	2011.8	2047.1	2029.4
27.5°	1923.6	1888.3	1870.6	1853.0	1853.0	1817.7	1835.3	1835.3	1870.6	1888.3	1888.3
30°	1923.6	1870.6	1800.0	1747.1	1747.1	1694.1	1729.4	1764.7	1782.4	1817.7	1817.7
32.5°	1976.5	1870.6	1747.1	1694.1	1641.2	1605.9	1641.2	1694.1	1764.7	1782.4	1800.0
35°	1570.6	1623.6	1605.9	1535.3	1517.7	1517.7	1500.0	1500.0	1447.1	1447.1	1429.4
37.5°	1411.8	1394.1	1429.4	1447.1	1464.7	1411.8	1411.8	1341.2	1323.5	1341.2	1341.2
40°	1323.5	1323.5	1323.5	1376.5	1394.1	1358.8	1305.9	1270.6	1270.6	1270.6	1288.3
42.5°	1288.3	1253.0	1235.3	1270.6	1323.5	1288.3	1235.3	1217.7	1217.7	1235.3	1235.3
45°	1235.3	1217.7	1200.0	1182.4	1253.0	1200.0	1182.4	1164.7	1164.7	1164.7	1182.4
47.5°	1182.4	1164.7	1129.4	1129.4	1147.1	1129.4	1111.8	1111.8	1111.8	1147.1	1147.1
50°	1147.1	1129.4	1094.1	1094.1	1094.1	1094.1	1076.5	1076.5	1076.5	1094.1	1111.8
52.5°	1094.1	1076.5	1058.8	1041.2	1041.2	1041.2	1041.2	1041.2	1041.2	1058.8	1076.5
55°	1041.2	1023.5	1005.9	1005.9	1023.5	1023.5	1005.9	1023.5	1005.9	1023.5	1041.2
57.5°	988.3	970.6	953.0	970.6	988.3	970.6	970.6	970.6	970.6	970.6	988.3
60°	917.7	917.7	917.7	917.7	953.0	953.0	953.0	953.0	917.7	935.3	953.0
62.5°	882.4	864.7	864.7	882.4	900.0	900.0	917.7	900.0	882.4	900.0	900.0
65°	811.8	811.8	811.8	829.4	829.4	847.1	847.1	847.1	829.4	847.1	847.1
67.5°	758.8	758.8	758.8	758.8	794.1	794.1	794.1	794.1	776.5	776.5	794.1
70°	670.6	688.2	670.6	705.9	741.2	723.5	741.2	741.2	723.5	705.9	741.2
72.5°	617.7	617.7	617.7	617.7	670.6	670.6	670.6	688.2	670.6	653.0	670.6
75°	547.1	547.1	547.1	564.7	600.0	600.0	600.0	600.0	600.0	582.4	582.4
77.5°	476.5	494.1	476.5	494.1	529.4	511.8	529.4	547.1	529.4	511.8	511.8
80°	405.9	405.9	405.9	423.5	441.2	441.2	441.2	458.8	441.2	423.5	423.5
82.5°	317.7	317.7	335.3	335.3	352.9	352.9	352.9	370.6	352.9	335.3	335.3
85°	247.1	247.1	247.1	264.7	264.7	282.4	282.4	300.0	300.0	282.4	282.4
87.5°	158.8	141.2	158.8	158.8	176.5	176.5	158.8	141.2	158.8	141.2	123.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P599006
 CATALOG NUMBER: IFLD-S-SA6D-750-U-SLL

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1	12706.1
2.5°	11594.3	11911.9	12141.4	12300.2	12529.6	12970.8	13147.3	13464.9	13553.1	13606.1
5°	9970.7	10306.0	10800.2	11153.1	11559.0	12388.4	13023.7	13500.2	13712.0	13906.1
7.5°	7817.8	8258.9	8770.7	9229.6	9900.1	10923.7	11753.1	12741.4	13112.0	13306.1
10°	6106.0	6511.9	7076.6	7641.3	8576.6	9441.3	10623.7	11523.7	12035.5	12176.7
12.5°	5153.0	5629.5	6300.1	6988.3	7570.7	8559.0	9759.0	11064.9	11541.4	11629.6
15°	4376.5	5029.5	5717.7	6423.6	7094.2	7958.9	9247.2	10835.5	11541.4	11629.6
17.5°	3617.7	4200.1	5011.8	5770.7	6547.2	7729.5	9335.4	11029.6	11735.5	12000.2
20°	2876.5	3441.2	4076.5	5029.5	6088.3	7341.3	9529.6	11682.5	12617.8	12900.2
22.5°	2382.4	2629.5	3247.1	4164.8	5417.7	7076.6	9723.7	12706.1	13694.3	13800.2
25°	2082.4	2258.9	2647.1	3511.8	4888.3	6900.1	10182.5	13888.4	15159.1	15159.1
27.5°	1941.2	2011.8	2276.5	3053.0	4517.7	6741.3	10641.3	15194.3	16376.7	16623.8
30°	1905.9	2082.4	2223.6	2717.7	4111.8	6300.1	11064.9	16217.9	17435.6	17453.2
32.5°	1870.6	1835.3	1941.2	2364.7	3617.7	5841.3	11417.8	17259.1	18212.0	18265.0
35°	1464.7	1535.3	1711.8	2082.4	3247.1	5506.0	11594.3	17823.8	19200.3	19253.2
37.5°	1376.5	1464.7	1605.9	1923.6	3000.0	5223.6	11647.2	18917.9	20241.5	20347.4
40°	1341.2	1411.8	1517.7	1782.4	2805.9	4870.7	11753.1	20047.4	21776.8	21635.6
42.5°	1270.6	1358.8	1464.7	1711.8	2647.1	4606.0	11770.8	20665.0	22588.6	22588.6
45°	1253.0	1305.9	1429.4	1711.8	2470.6	4376.5	11488.4	21282.7	23523.9	23241.5
47.5°	1182.4	1288.3	1394.1	1658.8	2258.9	4147.1	11153.1	21600.3	23647.4	23559.2
50°	1164.7	1270.6	1447.1	1570.6	2135.3	4041.2	11082.5	22394.5	23894.5	23876.8
52.5°	1129.4	1235.3	1500.0	1500.0	1976.5	3900.1	11417.8	22747.4	23947.4	24088.6
55°	1076.5	1235.3	1394.1	1376.5	1835.3	3723.6	11788.4	23665.1	24882.7	24847.4
57.5°	1041.2	1200.0	1323.5	1253.0	1676.5	3600.1	12335.5	24547.4	26012.2	25765.1
60°	988.3	1200.0	1182.4	1164.7	1553.0	3494.2	12794.3	24723.9	26259.2	26418.0
62.5°	953.0	1253.0	1041.2	1076.5	1447.1	3441.2	12600.2	23400.4	25923.9	26065.1
65°	917.7	1076.5	953.0	988.3	1411.8	3335.3	11841.4	21812.1	24476.8	25094.5
67.5°	847.1	882.4	882.4	917.7	1376.5	3088.3	10288.4	18953.2	22270.9	22606.2
70°	776.5	794.1	794.1	847.1	1341.2	2805.9	8488.4	16394.4	19323.8	19959.1
72.5°	705.9	705.9	705.9	776.5	1235.3	2576.5	6988.3	12600.2	16059.1	16500.2
75°	617.7	617.7	617.7	688.2	1111.8	2347.1	5506.0	9370.7	11823.7	12459.0
77.5°	547.1	547.1	529.4	617.7	970.6	1905.9	3970.6	6617.7	8329.5	8859.0
80°	458.8	441.2	441.2	494.1	758.8	1376.5	2558.9	4676.5	5806.0	6035.4
82.5°	370.6	352.9	335.3	370.6	547.1	864.7	1588.3	3264.8	3723.6	3582.4
85°	352.9	370.6	300.0	282.4	388.2	564.7	1005.9	2011.8	1676.5	1676.5
87.5°	141.2	123.5	123.5	105.9	194.1	211.8	441.2	370.6	282.4	282.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)