

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P598781

Luminaire Tested: **IFLD-L-SA7A-760-U-SLR**

Issue Date: 05/03/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P598781
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/03/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-L-SA7A-760-U-SLR
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLR distribution lens
 Light Source: (112) 5700K CCT, 70 CRI LEDS
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 27233.2 lumens
 Efficiency: N/A
 Efficacy: 125.2 lumens/watt
 Spacing Criteria (0/90/45): 1.13 / 0.53 / 0.8
 Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
 CIE Type: Direct

Input Watts (W): 217.6
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P598781
CATALOG NUMBER: IFLD-L-SA7A-760-U-SLR

Luminous Intensity Polar Plot



TEST NUMBER: P598781
 CATALOG NUMBER: IFLD-L-SA7A-760-U-SLR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20										
RC	80					70					50					30					10					0					
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0				
RCR																															
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100													
1	105	99	94	89	102	97	92	87	92	88	84	88	85	82	85	82	79	77													
2	93	83	74	67	90	81	73	66	77	70	64	73	68	63	70	65	61	59													
3	83	70	60	52	80	68	59	51	65	57	50	62	55	49	59	53	48	46													
4	74	60	49	41	72	59	49	41	56	47	40	53	46	40	51	44	39	36													
5	68	52	42	34	65	51	41	34	49	40	33	47	39	33	45	38	32	30													
6	62	46	36	28	60	45	35	28	43	34	28	41	34	28	40	33	27	25													
7	57	41	31	24	55	40	31	24	39	30	24	37	29	24	36	29	23	21													
8	53	37	28	21	51	36	27	21	35	27	21	34	26	21	32	26	20	18													
9	49	34	25	19	47	33	24	18	32	24	18	31	23	18	30	23	18	16													
10	46	31	22	17	44	31	22	17	29	22	16	28	21	16	28	21	16	14													

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	43783	43783	43783	43783
5°	45058	29300	32008	47335
10°	39975	18618	18804	40909
15°	39233	13205	12506	36693
20°	45614	8353	8418	39088
25°	58661	7172	6969	46212
30°	71089	6797	6372	57849
35°	84141	5989	5764	68570
40°	101100	5683	5283	81009
45°	116985	5637	5116	94438
50°	135846	5724	5152	111520
55°	166242	5880	5239	142082
60°	215601	5887	5519	177706
65°	264655	5948	5659	190221
70°	280048	6275	5917	185204
75°	235739	6633	5922	151156
80°	171267	7770	6003	130656
85°	181523	11257	4928	135791

TEST NUMBER: P598781
 CATALOG NUMBER: IFLD-L-SA7A-760-U-SLR

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	629.6	2.3
10°-20°	1317.6	4.8
20°-30°	1898.9	7.0
30°-40°	2733.6	10.0
40°-50°	3882.9	14.3
50°-60°	5582.5	20.5
60°-70°	6449.6	23.7
70°-80°	3651.9	13.4
80°-90°	1086.8	4.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3846.1	14.1
0°-40°	6579.7	24.2
0°-60°	16045.0	58.9
0°-90°	27233.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	27233.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	8135	8135	8135	8135	8135	
5°	8340	5423	5925	8762	8340	757
15°	7041	2370	2244	6586	7041	2071
25°	9878	1208	1174	7782	9878	4585
35°	12806	912	877	10437	12806	8128
45°	15370	741	672	12408	15370	11901
55°	17717	627	558	15142	17717	16046
65°	20782	467	444	14937	20782	19928
75°	11337	319	285	7269	11337	12029
85°	2940	182	80	2199	2940	2927
90°	0	0	0	0	0	

TEST NUMBER: P598781
 CATALOG NUMBER: IFLD-L-SA7A-760-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1
2.5°	8590.8	8579.4	8511.1	8294.6	8066.7	7850.2	7645.1	7428.7	7314.7	7178.0	7121.0
5°	8340.2	8317.4	8123.7	7645.1	7223.6	6767.8	6380.4	6072.8	5822.2	5571.5	5480.3
7.5°	7770.5	7736.3	7508.4	6847.6	6232.3	5639.9	5172.7	4773.9	4443.5	4295.4	4124.5
10°	7314.7	7257.8	6961.5	6232.3	5434.8	4842.3	4534.7	4261.2	3976.4	3737.1	3486.5
12.5°	7029.9	6961.5	6653.9	5799.4	5024.6	4580.2	4261.2	3953.6	3600.4	3304.2	3030.7
15°	7041.3	6961.5	6585.5	5685.4	4922.1	4352.4	3908.0	3486.5	3076.3	2745.9	2438.2
17.5°	7371.7	7269.1	6870.4	5844.9	4842.3	4056.1	3463.7	2916.8	2449.6	2096.4	1845.8
20°	7964.2	7895.8	7440.1	6084.2	4762.5	3737.1	3007.9	2347.1	1857.2	1583.7	1481.2
22.5°	8852.9	8773.1	8283.2	6448.8	4739.8	3452.3	2518.0	1845.8	1492.6	1378.6	1321.7
25°	9878.3	9730.2	9274.4	7064.1	4785.3	3190.2	2119.2	1526.7	1333.1	1253.3	1219.1
27.5°	10767.0	10675.8	10163.1	7645.1	4808.1	2985.1	1845.8	1390.0	1241.9	1173.5	1150.8
30°	11439.2	11405.0	10903.7	8283.2	4751.2	2734.5	1674.9	1333.1	1241.9	1173.5	1105.2
32.5°	12111.4	12122.8	11587.3	8773.1	4671.4	2518.0	1515.4	1184.9	1093.8	1048.2	1059.6
35°	12806.5	12863.4	12407.7	9251.6	4500.5	2438.2	1401.4	1105.2	1025.4	957.1	922.9
37.5°	13683.8	13831.9	13387.5	9787.1	4329.6	2369.9	1344.5	1048.2	968.5	911.5	865.9
40°	14390.2	14663.6	14401.6	10288.5	4215.6	2290.1	1298.9	991.2	934.3	865.9	831.7
42.5°	14914.3	15233.3	15142.2	10675.8	4215.6	2210.4	1253.3	957.1	911.5	831.7	786.2
45°	15370.0	15700.4	15689.1	11074.6	4306.8	2164.8	1196.3	957.1	888.7	808.9	763.4
47.5°	15780.2	16110.6	16224.6	11575.9	4454.9	2142.0	1128.0	934.3	888.7	797.6	729.2
50°	16224.6	16589.2	16931.0	12373.5	4637.2	2085.0	1082.4	900.1	900.1	786.2	706.4
52.5°	16794.2	17204.4	17831.1	13364.7	4819.5	1982.5	1014.0	877.3	900.1	774.8	683.6
55°	17717.1	18058.9	18879.3	14549.7	5047.4	1857.2	957.1	820.3	854.5	740.6	649.4
57.5°	18753.9	19050.2	19733.8	15461.2	5115.7	1697.7	877.3	763.4	820.3	706.4	603.9
60°	20030.0	20178.2	20178.2	15723.2	4887.9	1549.5	820.3	717.8	740.6	672.2	569.7
62.5°	20839.0	20839.0	20178.2	15244.7	4454.9	1424.2	774.8	672.2	649.4	626.7	535.5
65°	20782.0	20690.9	19711.0	13854.7	3953.6	1344.5	729.2	615.3	581.1	569.7	501.3
67.5°	19824.9	19665.4	18332.4	11895.0	3429.5	1310.3	683.6	558.3	535.5	512.7	455.7
70°	17796.9	17386.7	15746.0	9570.7	2916.8	1287.5	672.2	512.7	489.9	467.1	421.6
72.5°	14857.3	14333.2	12293.7	7360.3	2449.6	1207.7	638.0	455.7	444.4	421.6	376.0
75°	11336.7	10368.2	8579.4	5628.5	1902.7	1048.2	546.9	398.8	398.8	387.4	341.8
77.5°	7816.0	7314.7	5981.7	4158.7	1390.0	808.9	444.4	353.2	353.2	364.6	319.0
80°	5525.9	5058.8	4261.2	2985.1	877.3	546.9	341.8	296.2	330.4	353.2	296.2
82.5°	4227.0	3885.2	3167.4	2176.2	512.7	376.0	262.1	239.3	284.8	307.6	250.7
85°	2939.6	2529.4	1606.5	1458.4	296.2	227.9	193.7	193.7	250.7	307.6	227.9
87.5°	831.7	353.2	102.5	433.0	125.3	91.1	68.4	45.6	68.4	68.4	45.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598781
 CATALOG NUMBER: IFLD-L-SA7A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1
2.5°	7064.1	6995.7	6995.7	6972.9	6984.3	6995.7	6984.3	7064.1	7098.2	7143.8	7235.0
5°	5423.4	5514.5	5446.2	5514.5	5605.7	5742.4	5776.6	5879.1	5890.5	5970.3	5924.7
7.5°	4022.0	4010.6	3953.6	4033.4	4284.0	4477.7	4568.9	4625.8	4637.2	4637.2	4580.2
10°	3406.7	3304.2	3201.6	3144.6	3167.4	3372.5	3440.9	3475.1	3452.3	3486.5	3440.9
12.5°	2916.8	2825.6	2677.5	2575.0	2506.6	2563.6	2631.9	2666.1	2688.9	2745.9	2791.4
15°	2369.9	2278.7	2187.6	2130.6	2073.6	2028.1	2085.0	2119.2	2176.2	2221.8	2244.5
17.5°	1800.2	1754.6	1709.0	1743.2	1743.2	1720.4	1743.2	1754.6	1777.4	1811.6	1800.2
20°	1458.4	1447.0	1435.6	1492.6	1538.1	1538.1	1560.9	1526.7	1515.4	1481.2	1469.8
22.5°	1298.9	1298.9	1310.3	1355.8	1401.4	1424.2	1424.2	1367.2	1310.3	1287.5	1298.9
25°	1207.7	1207.7	1241.9	1253.3	1276.1	1276.1	1287.5	1230.5	1196.3	1162.2	1173.5
27.5°	1139.4	1139.4	1150.8	1150.8	1162.2	1162.2	1173.5	1150.8	1105.2	1093.8	1093.8
30°	1093.8	1093.8	1082.4	1082.4	1082.4	1082.4	1093.8	1059.6	1036.8	1025.4	1025.4
32.5°	1048.2	1036.8	1025.4	1025.4	1014.0	1014.0	1025.4	991.2	979.9	979.9	979.9
35°	911.5	900.1	911.5	934.3	934.3	945.7	945.7	934.3	911.5	888.7	877.3
37.5°	854.5	843.1	843.1	843.1	865.9	877.3	888.7	865.9	831.7	797.6	797.6
40°	808.9	808.9	797.6	797.6	797.6	820.3	843.1	808.9	763.4	752.0	752.0
42.5°	774.8	763.4	752.0	740.6	729.2	763.4	786.2	740.6	717.8	717.8	717.8
45°	740.6	729.2	717.8	706.4	695.0	706.4	729.2	683.6	672.2	672.2	672.2
47.5°	706.4	695.0	672.2	660.8	649.4	649.4	672.2	638.0	626.7	638.0	638.0
50°	683.6	660.8	638.0	626.7	615.3	615.3	615.3	603.9	603.9	603.9	615.3
52.5°	660.8	638.0	603.9	592.5	581.1	581.1	581.1	581.1	569.7	581.1	592.5
55°	626.7	603.9	581.1	569.7	558.3	546.9	558.3	546.9	546.9	558.3	558.3
57.5°	581.1	558.3	535.5	535.5	524.1	524.1	535.5	524.1	524.1	535.5	535.5
60°	546.9	524.1	501.3	501.3	489.9	501.3	512.7	501.3	501.3	501.3	512.7
62.5°	501.3	489.9	467.1	467.1	467.1	467.1	478.5	467.1	478.5	478.5	478.5
65°	467.1	444.4	433.0	433.0	433.0	433.0	455.7	433.0	444.4	444.4	444.4
67.5°	433.0	410.2	398.8	398.8	398.8	398.8	421.6	398.8	410.2	421.6	410.2
70°	398.8	376.0	364.6	364.6	364.6	364.6	376.0	364.6	364.6	376.0	376.0
72.5°	353.2	341.8	330.4	330.4	319.0	330.4	341.8	330.4	330.4	330.4	330.4
75°	319.0	307.6	307.6	296.2	296.2	296.2	307.6	284.8	284.8	284.8	284.8
77.5°	296.2	273.4	273.4	273.4	262.1	273.4	262.1	239.3	239.3	239.3	239.3
80°	250.7	227.9	239.3	239.3	227.9	227.9	216.5	193.7	193.7	193.7	193.7
82.5°	205.1	182.3	193.7	193.7	193.7	193.7	170.9	159.5	148.1	136.7	136.7
85°	182.3	148.1	170.9	170.9	159.5	159.5	113.9	113.9	91.1	91.1	79.8
87.5°	34.2	22.8	45.6	57.0	57.0	68.4	45.6	57.0	34.2	22.8	22.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P598781
 CATALOG NUMBER: IFLD-L-SA7A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1
2.5°	7223.6	7348.9	7519.8	7645.1	7838.8	7986.9	8214.8	8408.5	8590.8	8670.6	8750.3
5°	6061.4	6141.2	6403.2	6608.3	6915.9	7246.4	7656.5	8100.9	8556.6	8761.7	9001.0
7.5°	4534.7	4682.8	4830.9	5127.1	5503.1	6038.6	6562.7	7223.6	7861.6	8169.2	8579.4
10°	3520.6	3634.6	3805.5	4113.1	4466.3	4910.7	5537.3	6323.5	7086.8	7485.6	7907.2
12.5°	2825.6	2985.1	3213.0	3532.0	3942.2	4397.9	4853.7	5582.9	6471.6	6927.3	7405.9
15°	2290.1	2415.5	2666.1	3064.9	3543.4	4010.6	4489.1	5093.0	6061.4	6585.5	7155.2
17.5°	1823.0	1914.1	2142.0	2540.8	3019.3	3543.4	4090.3	4853.7	5924.7	6562.7	7235.0
20°	1481.2	1549.5	1697.7	1993.9	2449.6	3019.3	3702.9	4625.8	6004.5	6824.8	7645.1
22.5°	1298.9	1321.7	1390.0	1549.5	1925.5	2529.4	3349.7	4432.1	6152.6	7212.2	8317.4
25°	1173.5	1196.3	1219.1	1321.7	1538.1	2107.8	3042.1	4318.2	6471.6	7781.9	9092.1
27.5°	1093.8	1116.6	1128.0	1173.5	1321.7	1800.2	2780.1	4249.8	6904.6	8613.6	10049.2
30°	1025.4	1025.4	1059.6	1128.0	1230.5	1583.7	2552.2	4090.3	7360.3	9308.6	10801.2
32.5°	968.5	979.9	1025.4	1059.6	1128.0	1401.4	2324.3	3885.2	7770.5	9878.3	11541.8
35°	865.9	865.9	877.3	934.3	1025.4	1253.3	2119.2	3680.1	7998.3	10436.6	12202.6
37.5°	797.6	808.9	831.7	877.3	957.1	1150.8	1948.3	3452.3	8237.6	10960.7	12977.4
40°	752.0	763.4	786.2	831.7	911.5	1059.6	1800.2	3270.0	8488.3	11530.4	13809.1
42.5°	717.8	729.2	752.0	797.6	865.9	1036.8	1640.7	3121.9	8636.4	12054.5	14595.3
45°	683.6	695.0	729.2	774.8	831.7	1014.0	1549.5	3019.3	8693.4	12407.7	15221.9
47.5°	649.4	660.8	695.0	763.4	831.7	979.9	1515.4	2962.3	8738.9	12806.5	15723.2
50°	615.3	638.0	683.6	752.0	843.1	934.3	1492.6	2951.0	9001.0	13319.2	16201.8
52.5°	592.5	626.7	672.2	752.0	831.7	865.9	1481.2	2985.1	9525.1	14082.5	16885.4
55°	569.7	603.9	649.4	752.0	797.6	808.9	1424.2	3042.1	10322.6	15142.2	17853.8
57.5°	546.9	569.7	626.7	729.2	752.0	763.4	1310.3	3121.9	11120.2	16179.0	18845.1
60°	512.7	535.5	592.5	729.2	683.6	717.8	1162.2	3144.6	11689.9	16509.4	18936.2
62.5°	478.5	501.3	558.3	752.0	626.7	672.2	1036.8	3064.9	11803.8	16030.9	18423.5
65°	444.4	467.1	512.7	626.7	581.1	626.7	957.1	2848.4	11427.8	14937.1	17489.2
67.5°	410.2	433.0	467.1	512.7	524.1	569.7	922.9	2506.6	10482.2	13581.2	16213.2
70°	364.6	387.4	421.6	455.7	467.1	535.5	865.9	2176.2	8955.4	11769.6	14652.2
72.5°	330.4	341.8	376.0	398.8	421.6	489.9	831.7	1902.7	6847.6	9525.1	11951.9
75°	284.8	284.8	319.0	341.8	364.6	433.0	763.4	1583.7	4830.9	7269.1	8784.5
77.5°	239.3	239.3	262.1	284.8	307.6	376.0	649.4	1287.5	3349.7	5765.2	6369.0
80°	182.3	182.3	205.1	227.9	250.7	319.0	524.1	945.7	2073.6	4215.6	4637.2
82.5°	125.3	125.3	159.5	170.9	182.3	250.7	398.8	649.4	1219.1	3042.1	3315.6
85°	68.4	68.4	91.1	102.5	125.3	182.3	296.2	455.7	729.2	2199.0	2210.4
87.5°	11.4	11.4	34.2	34.2	57.0	91.1	170.9	250.7	410.2	1219.1	774.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598781
 CATALOG NUMBER: IFLD-L-SA7A-760-U-SLR

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1	8135.1
2.5°	8898.4	9023.8	9035.2	9035.2	8978.2	8989.6	8830.1	8659.2	8602.2	8590.8
5°	9365.6	9696.0	9787.1	9832.7	9684.6	9456.7	9046.6	8602.2	8374.3	8340.2
7.5°	9274.4	9935.3	10288.5	10334.0	10037.8	9502.3	8784.5	8100.9	7838.8	7770.5
10°	8738.9	9627.6	10265.7	10425.2	10106.2	9422.5	8488.3	7690.7	7371.7	7314.7
12.5°	8362.9	9217.5	9844.1	10060.6	9912.5	9320.0	8340.2	7428.7	7109.6	7029.9
15°	8157.9	8944.0	9354.2	9422.5	9411.2	9160.5	8340.2	7485.6	7132.4	7041.3
17.5°	8328.8	8864.3	8921.2	8761.7	8852.9	8978.2	8522.4	7793.3	7451.4	7371.7
20°	8670.6	8830.1	8556.6	8317.4	8362.9	8761.7	8807.3	8374.3	8100.9	7964.2
22.5°	9388.4	8955.4	8328.8	7998.3	8032.5	8590.8	9183.3	9160.5	8921.2	8852.9
25°	10117.6	9308.6	8260.4	7873.0	7918.6	8556.6	9627.6	10037.8	9912.5	9878.3
27.5°	10926.5	9901.1	8306.0	7816.0	7873.0	8602.2	9935.3	10778.4	10801.2	10767.0
30°	11473.4	10185.9	8442.7	7884.4	7964.2	8716.1	10003.6	11222.7	11427.8	11439.2
32.5°	11929.1	10470.8	8727.5	7998.3	8135.1	8921.2	10185.9	11644.3	12100.1	12111.4
35°	12293.7	10789.8	9080.7	8203.4	8408.5	9263.0	10425.2	12043.1	12726.7	12806.5
37.5°	12760.9	11143.0	9490.9	8647.8	8875.7	9753.0	10846.8	12510.2	13467.3	13683.8
40°	13262.2	11496.2	10083.4	9365.6	9696.0	10482.2	11325.3	13034.3	14093.9	14390.2
42.5°	13820.5	11872.2	10755.6	10334.0	10835.4	11405.0	11872.2	13512.9	14572.5	14914.3
45°	14367.4	12327.9	11735.5	11655.7	12214.0	12498.8	12407.7	13854.7	15028.2	15370.0
47.5°	14754.8	12988.8	12920.4	13398.9	13923.0	13774.9	13034.3	14105.3	15404.2	15780.2
50°	15108.0	13809.1	14413.0	15347.2	15666.3	15164.9	13706.6	14447.1	15803.0	16224.6
52.5°	15632.1	14686.4	15951.1	17113.3	17420.9	16623.3	14435.8	15005.4	16418.2	16794.2
55°	16703.1	15677.7	17557.6	18890.7	18947.6	17956.4	15415.6	15951.1	17284.2	17717.1
57.5°	17899.4	16896.8	18833.7	20360.4	20337.7	19289.4	16520.8	17227.2	18457.7	18753.9
60°	18981.8	18127.3	20223.7	21408.7	21351.7	20257.9	17808.3	18674.2	19802.2	20030.0
62.5°	19619.9	19243.9	20839.0	21739.1	21522.6	20576.9	18902.1	19961.7	20759.2	20839.0
65°	19517.3	19881.9	20121.2	20679.5	20371.8	19688.2	19437.6	20782.0	20861.8	20782.0
67.5°	18742.6	19517.3	18150.1	18207.0	18047.5	17466.5	18605.8	20565.5	20018.6	19824.9
70°	17569.0	17626.0	15176.3	14458.5	14709.2	13911.6	15962.5	18879.3	18036.1	17796.9
72.5°	15620.7	14914.3	11473.4	10744.2	11120.2	10550.5	12806.5	16452.4	15632.1	14857.3
75°	13102.7	11815.2	8738.9	7702.1	7895.8	7873.0	9923.9	13592.6	12111.4	11336.7
77.5°	10151.7	9206.1	6448.8	6050.0	5844.9	5890.5	6927.3	10106.2	8784.5	7816.0
80°	7417.3	6437.4	4990.4	5218.3	5104.4	4830.9	4853.7	6767.8	6107.0	5525.9
82.5°	5127.1	4580.2	4044.7	4568.9	4295.4	3873.8	3782.7	4876.5	4580.2	4227.0
85°	3440.9	3771.3	3213.0	3497.8	3030.7	2791.4	3554.8	4078.9	3292.8	2939.6
87.5°	2244.5	3452.3	2312.9	1754.6	1002.6	1344.5	2176.2	2677.5	1538.1	831.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)