

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P598766

Luminaire Tested: **IFLD-S-SA3A-760-U-SLR**

Issue Date: 05/03/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

**Test Information**

Test Method: LM-79-08  
 Report Number: P598766  
 Test Lab: INNOVATION CENTER(G1)  
 Issue Date: 05/03/2022  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: IFLD-S-SA3A-760-U-SLR  
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLR distribution lens  
 Light Source: (48) 5700K CCT, 70 CRI LEDs  
 Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
 Luminaire Lumens: 11970.7 lumens  
 Efficiency: N/A  
 Efficacy: 126.3 lumens/watt  
 Spacing Criteria (0/90/45): 1.13 / 0.53 / 0.8  
 Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')  
 CIE Type: Direct

Input Watts (W): 94.8  
 Input Voltage (V): 120  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P598766  
CATALOG NUMBER: IFLD-S-SA3A-760-U-SLR

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - · - 90°-270°    - · · - 135°-315°

TEST NUMBER: P598766  
 CATALOG NUMBER: IFLD-S-SA3A-760-U-SLR

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	105	99	94	89	102	97	92	87	92	88	84	88	85	82	85	82	79	85	82	79	77
2	93	83	74	67	90	81	73	66	77	70	64	73	68	63	70	65	61	70	65	61	59
3	83	70	60	52	80	68	59	51	65	57	50	62	55	49	59	53	48	59	53	48	46
4	74	60	49	41	72	59	49	41	56	47	40	53	46	40	51	44	39	51	44	39	36
5	68	52	42	34	65	51	41	34	49	40	33	47	39	33	45	38	32	45	38	32	30
6	62	46	36	28	60	45	35	28	43	34	28	41	34	28	40	33	27	40	33	27	25
7	57	41	31	24	55	40	31	24	39	30	24	37	29	24	36	29	23	36	29	23	21
8	53	37	28	21	51	36	27	21	35	27	21	34	26	21	32	26	20	32	26	20	18
9	49	34	25	19	47	33	24	18	32	24	18	31	23	18	30	23	18	30	23	18	16
10	46	31	22	17	44	31	22	17	29	22	16	28	21	16	28	21	16	28	21	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	51321	51321	51321	51321
5°	52815	34344	37519	55485
10°	46857	21823	22042	47952
15°	45988	15478	14659	43010
20°	53466	9791	9868	45817
25°	68760	8407	8168	54167
30°	83328	7968	7469	67808
35°	98626	7020	6756	80375
40°	118507	6662	6192	94955
45°	137126	6607	5998	110696
50°	159234	6709	6037	130719
55°	194864	6893	6140	166542
60°	252720	6900	6470	208300
65°	310220	6972	6632	222971
70°	328261	7356	6936	217091
75°	276326	7774	6943	177178
80°	200755	9108	7033	153149
85°	212769	13190	5780	159169

TEST NUMBER: P598766  
 CATALOG NUMBER: IFLD-S-SA3A-760-U-SLR

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	276.7	2.3
10°-20°	579.2	4.8
20°-30°	834.7	7.0
30°-40°	1201.6	10.0
40°-50°	1706.8	14.3
50°-60°	2453.8	20.5
60°-70°	2835.0	23.7
70°-80°	1605.2	13.4
80°-90°	477.7	4.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1690.6	14.1
0°-40°	2892.2	24.2
0°-60°	7052.8	58.9
0°-90°	11970.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11970.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	3576	3576	3576	3576	3576	
5°	3666	2384	2604	3851	3666	333
15°	3095	1042	987	2895	3095	910
25°	4342	531	516	3421	4342	2015
35°	5629	401	386	4588	5629	3573
45°	6756	326	296	5454	6756	5231
55°	7788	276	245	6656	7788	7053
65°	9135	205	195	6566	9135	8760
75°	4983	140	125	3195	4983	5287
85°	1292	80	35	967	1292	1287
90°	0	0	0	0	0	

TEST NUMBER: P598766  
 CATALOG NUMBER: IFLD-S-SA3A-760-U-SLR

**CANDELA DISTRIBUTION (FULL):**

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9
2.5°	3776.2	3771.2	3741.1	3646.0	3545.8	3450.7	3360.5	3265.4	3215.3	3155.2	3130.1
5°	3666.0	3656.0	3570.9	3360.5	3175.2	2974.9	2804.6	2669.4	2559.2	2449.0	2409.0
7.5°	3415.6	3400.6	3300.4	3009.9	2739.5	2479.1	2273.7	2098.4	1953.2	1888.1	1813.0
10°	3215.3	3190.2	3060.0	2739.5	2388.9	2128.5	1993.3	1873.1	1747.9	1642.7	1532.5
12.5°	3090.1	3060.0	2924.8	2549.2	2208.6	2013.3	1873.1	1737.9	1582.6	1452.4	1332.2
15°	3095.1	3060.0	2894.7	2499.1	2163.5	1913.1	1717.8	1532.5	1352.2	1207.0	1071.8
17.5°	3240.3	3195.2	3020.0	2569.2	2128.5	1782.9	1522.5	1282.1	1076.8	921.5	811.3
20°	3500.7	3470.7	3270.4	2674.4	2093.4	1642.7	1322.2	1031.7	816.3	696.1	651.1
22.5°	3891.4	3856.3	3641.0	2834.7	2083.4	1517.5	1106.8	811.3	656.1	606.0	581.0
25°	4342.1	4277.0	4076.7	3105.1	2103.5	1402.3	931.5	671.1	586.0	550.9	535.9
27.5°	4732.8	4692.7	4467.3	3360.5	2113.5	1312.2	811.3	611.0	545.9	515.8	505.8
30°	5028.2	5013.2	4792.9	3641.0	2088.4	1202.0	736.2	586.0	545.9	515.8	485.8
32.5°	5323.7	5328.7	5093.4	3856.3	2053.4	1106.8	666.1	520.9	480.8	460.8	465.8
35°	5629.2	5654.3	5453.9	4066.7	1978.2	1071.8	616.0	485.8	450.7	420.7	405.7
37.5°	6014.9	6080.0	5884.7	4302.1	1903.1	1041.7	591.0	460.8	425.7	400.7	380.6
40°	6325.4	6445.6	6330.4	4522.4	1853.0	1006.7	570.9	435.7	410.7	380.6	365.6
42.5°	6555.8	6696.0	6655.9	4692.7	1853.0	971.6	550.9	420.7	400.7	365.6	345.6
45°	6756.1	6901.3	6896.3	4868.0	1893.1	951.6	525.9	420.7	390.6	355.6	335.6
47.5°	6936.4	7081.6	7131.7	5088.3	1958.2	941.5	495.8	410.7	390.6	350.6	320.5
50°	7131.7	7292.0	7442.2	5438.9	2038.3	916.5	475.8	395.6	395.6	345.6	310.5
52.5°	7382.1	7562.4	7837.9	5874.6	2118.5	871.4	445.7	385.6	395.6	340.6	300.5
55°	7787.8	7938.0	8298.6	6395.5	2218.6	816.3	420.7	360.6	375.6	325.5	285.5
57.5°	8243.5	8373.7	8674.2	6796.1	2248.7	746.2	385.6	335.6	360.6	310.5	265.4
60°	8804.4	8869.6	8869.6	6911.3	2148.5	681.1	360.6	315.5	325.5	295.5	250.4
62.5°	9160.0	9160.0	8869.6	6701.0	1958.2	626.0	340.6	295.5	285.5	275.5	235.4
65°	9135.0	9094.9	8664.2	6090.0	1737.9	591.0	320.5	270.4	255.4	250.4	220.4
67.5°	8714.3	8644.2	8058.2	5228.6	1507.5	575.9	300.5	245.4	235.4	225.4	200.3
70°	7822.8	7642.5	6921.4	4206.9	1282.1	565.9	295.5	225.4	215.4	205.3	185.3
72.5°	6530.7	6300.3	5403.9	3235.3	1076.8	530.9	280.5	200.3	195.3	185.3	165.3
75°	4983.2	4557.5	3771.2	2474.1	836.4	460.8	240.4	175.3	175.3	170.3	150.2
77.5°	3435.6	3215.3	2629.3	1828.0	611.0	355.6	195.3	155.3	155.3	160.3	140.2
80°	2429.0	2223.6	1873.1	1312.2	385.6	240.4	150.2	130.2	145.2	155.3	130.2
82.5°	1858.0	1707.8	1392.3	956.6	225.4	165.3	115.2	105.2	125.2	135.2	110.2
85°	1292.1	1111.8	706.2	641.1	130.2	100.2	85.1	85.1	110.2	135.2	100.2
87.5°	365.6	155.3	45.1	190.3	55.1	40.1	30.0	20.0	30.0	30.0	20.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598766  
 CATALOG NUMBER: IFLD-S-SA3A-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9
2.5°	3105.1	3075.0	3075.0	3065.0	3070.0	3075.0	3070.0	3105.1	3120.1	3140.2	3180.2
5°	2383.9	2424.0	2393.9	2424.0	2464.0	2524.1	2539.2	2584.2	2589.2	2624.3	2604.3
7.5°	1767.9	1762.9	1737.9	1772.9	1883.1	1968.2	2008.3	2033.3	2038.3	2038.3	2013.3
10°	1497.5	1452.4	1407.3	1382.3	1392.3	1482.4	1512.5	1527.5	1517.5	1532.5	1512.5
12.5°	1282.1	1242.0	1176.9	1131.9	1101.8	1126.8	1156.9	1171.9	1181.9	1207.0	1227.0
15°	1041.7	1001.6	961.6	936.5	911.5	891.5	916.5	931.5	956.6	976.6	986.6
17.5°	791.3	771.3	751.2	766.3	766.3	756.2	766.3	771.3	781.3	796.3	791.3
20°	641.1	636.0	631.0	656.1	676.1	676.1	686.1	671.1	666.1	651.1	646.1
22.5°	570.9	570.9	575.9	596.0	616.0	626.0	626.0	601.0	575.9	565.9	570.9
25°	530.9	530.9	545.9	550.9	560.9	560.9	565.9	540.9	525.9	510.8	515.8
27.5°	500.8	500.8	505.8	505.8	510.8	510.8	515.8	505.8	485.8	480.8	480.8
30°	480.8	480.8	475.8	475.8	475.8	475.8	480.8	465.8	455.7	450.7	450.7
32.5°	460.8	455.7	450.7	450.7	445.7	445.7	450.7	435.7	430.7	430.7	430.7
35°	400.7	395.6	400.7	410.7	410.7	415.7	415.7	410.7	400.7	390.6	385.6
37.5°	375.6	370.6	370.6	370.6	380.6	385.6	390.6	380.6	365.6	350.6	350.6
40°	355.6	355.6	350.6	350.6	350.6	360.6	370.6	355.6	335.6	330.5	330.5
42.5°	340.6	335.6	330.5	325.5	320.5	335.6	345.6	325.5	315.5	315.5	315.5
45°	325.5	320.5	315.5	310.5	305.5	310.5	320.5	300.5	295.5	295.5	295.5
47.5°	310.5	305.5	295.5	290.5	285.5	285.5	295.5	280.5	275.5	280.5	280.5
50°	300.5	290.5	280.5	275.5	270.4	270.4	270.4	265.4	265.4	265.4	270.4
52.5°	290.5	280.5	265.4	260.4	255.4	255.4	255.4	255.4	250.4	255.4	260.4
55°	275.5	265.4	255.4	250.4	245.4	240.4	245.4	240.4	240.4	245.4	245.4
57.5°	255.4	245.4	235.4	235.4	230.4	230.4	235.4	230.4	230.4	235.4	235.4
60°	240.4	230.4	220.4	220.4	215.4	220.4	225.4	220.4	220.4	220.4	225.4
62.5°	220.4	215.4	205.3	205.3	205.3	205.3	210.3	205.3	210.3	210.3	210.3
65°	205.3	195.3	190.3	190.3	190.3	190.3	200.3	190.3	195.3	195.3	195.3
67.5°	190.3	180.3	175.3	175.3	175.3	175.3	185.3	175.3	180.3	185.3	180.3
70°	175.3	165.3	160.3	160.3	160.3	160.3	165.3	160.3	160.3	165.3	165.3
72.5°	155.3	150.2	145.2	145.2	140.2	145.2	150.2	145.2	145.2	145.2	145.2
75°	140.2	135.2	135.2	130.2	130.2	130.2	135.2	125.2	125.2	125.2	125.2
77.5°	130.2	120.2	120.2	120.2	115.2	120.2	115.2	105.2	105.2	105.2	105.2
80°	110.2	100.2	105.2	105.2	100.2	100.2	95.2	85.1	85.1	85.1	85.1
82.5°	90.1	80.1	85.1	85.1	85.1	85.1	75.1	70.1	65.1	60.1	60.1
85°	80.1	65.1	75.1	75.1	70.1	70.1	50.1	50.1	40.1	40.1	35.1
87.5°	15.0	10.0	20.0	25.0	25.0	30.0	20.0	25.0	15.0	10.0	10.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598766  
 CATALOG NUMBER: IFLD-S-SA3A-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9
2.5°	3175.2	3230.3	3305.4	3360.5	3445.7	3510.8	3610.9	3696.1	3776.2	3811.3	3846.3
5°	2664.4	2699.4	2814.6	2904.8	3040.0	3185.2	3365.5	3560.8	3761.2	3851.3	3956.5
7.5°	1993.3	2058.4	2123.5	2253.7	2419.0	2654.4	2884.7	3175.2	3455.7	3590.9	3771.2
10°	1547.5	1597.6	1672.7	1808.0	1963.2	2158.5	2434.0	2779.6	3115.1	3290.4	3475.7
12.5°	1242.0	1312.2	1412.3	1552.5	1732.8	1933.2	2133.5	2454.0	2844.7	3045.0	3255.3
15°	1006.7	1061.7	1171.9	1347.2	1557.6	1762.9	1973.2	2238.7	2664.4	2894.7	3145.2
17.5°	801.3	841.4	941.5	1116.8	1327.2	1557.6	1797.9	2133.5	2604.3	2884.7	3180.2
20°	651.1	681.1	746.2	876.4	1076.8	1327.2	1627.7	2033.3	2639.3	2999.9	3360.5
22.5°	570.9	581.0	611.0	681.1	846.4	1111.8	1472.4	1948.2	2704.4	3170.2	3656.0
25°	515.8	525.9	535.9	581.0	676.1	926.5	1337.2	1898.1	2844.7	3420.6	3996.6
27.5°	480.8	490.8	495.8	515.8	581.0	791.3	1222.0	1868.1	3035.0	3786.2	4417.2
30°	450.7	450.7	465.8	495.8	540.9	696.1	1121.8	1797.9	3235.3	4091.7	4747.8
32.5°	425.7	430.7	450.7	465.8	495.8	616.0	1021.7	1707.8	3415.6	4342.1	5073.3
35°	380.6	380.6	385.6	410.7	450.7	550.9	931.5	1617.7	3515.8	4587.5	5363.8
37.5°	350.6	355.6	365.6	385.6	420.7	505.8	856.4	1517.5	3620.9	4817.9	5704.4
40°	330.5	335.6	345.6	365.6	400.7	465.8	791.3	1437.4	3731.1	5068.3	6070.0
42.5°	315.5	320.5	330.5	350.6	380.6	455.7	721.2	1372.3	3796.2	5298.7	6415.5
45°	300.5	305.5	320.5	340.6	365.6	445.7	681.1	1327.2	3821.3	5453.9	6691.0
47.5°	285.5	290.5	305.5	335.6	365.6	430.7	666.1	1302.1	3841.3	5629.2	6911.3
50°	270.4	280.5	300.5	330.5	370.6	410.7	656.1	1297.1	3956.5	5854.6	7121.7
52.5°	260.4	275.5	295.5	330.5	365.6	380.6	651.1	1312.2	4186.9	6190.2	7422.2
55°	250.4	265.4	285.5	330.5	350.6	355.6	626.0	1337.2	4537.4	6655.9	7847.9
57.5°	240.4	250.4	275.5	320.5	330.5	335.6	575.9	1372.3	4888.0	7111.7	8283.6
60°	225.4	235.4	260.4	320.5	300.5	315.5	510.8	1382.3	5138.4	7256.9	8323.7
62.5°	210.3	220.4	245.4	330.5	275.5	295.5	455.7	1347.2	5188.5	7046.6	8098.3
65°	195.3	205.3	225.4	275.5	255.4	275.5	420.7	1252.1	5023.2	6565.8	7687.6
67.5°	180.3	190.3	205.3	225.4	230.4	250.4	405.7	1101.8	4607.6	5969.8	7126.7
70°	160.3	170.3	185.3	200.3	205.3	235.4	380.6	956.6	3936.5	5173.5	6440.6
72.5°	145.2	150.2	165.3	175.3	185.3	215.4	365.6	836.4	3009.9	4186.9	5253.6
75°	125.2	125.2	140.2	150.2	160.3	190.3	335.6	696.1	2123.5	3195.2	3861.3
77.5°	105.2	105.2	115.2	125.2	135.2	165.3	285.5	565.9	1472.4	2534.2	2799.6
80°	80.1	80.1	90.1	100.2	110.2	140.2	230.4	415.7	911.5	1853.0	2038.3
82.5°	55.1	55.1	70.1	75.1	80.1	110.2	175.3	285.5	535.9	1337.2	1457.4
85°	30.0	30.0	40.1	45.1	55.1	80.1	130.2	200.3	320.5	966.6	971.6
87.5°	5.0	5.0	15.0	15.0	25.0	40.1	75.1	110.2	180.3	535.9	340.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P598766  
 CATALOG NUMBER: IFLD-S-SA3A-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9	3575.9
2.5°	3911.4	3966.5	3971.5	3971.5	3946.5	3951.5	3881.4	3806.2	3781.2	3776.2
5°	4116.8	4262.0	4302.1	4322.1	4257.0	4156.8	3976.5	3781.2	3681.0	3666.0
7.5°	4076.7	4367.2	4522.4	4542.5	4412.2	4176.9	3861.3	3560.8	3445.7	3415.6
10°	3841.3	4231.9	4512.4	4582.5	4442.3	4141.8	3731.1	3380.5	3240.3	3215.3
12.5°	3676.0	4051.6	4327.1	4422.3	4357.1	4096.7	3666.0	3265.4	3125.1	3090.1
15°	3585.9	3931.4	4111.7	4141.8	4136.8	4026.6	3666.0	3290.4	3135.1	3095.1
17.5°	3661.0	3896.4	3921.4	3851.3	3891.4	3946.5	3746.1	3425.6	3275.4	3240.3
20°	3811.3	3881.4	3761.2	3656.0	3676.0	3851.3	3871.4	3681.0	3560.8	3500.7
22.5°	4126.8	3936.5	3661.0	3515.8	3530.8	3776.2	4036.6	4026.6	3921.4	3891.4
25°	4447.3	4091.7	3631.0	3460.7	3480.7	3761.2	4231.9	4412.2	4357.1	4342.1
27.5°	4802.9	4352.1	3651.0	3435.6	3460.7	3781.2	4367.2	4737.8	4747.8	4732.8
30°	5043.3	4477.3	3711.1	3465.7	3500.7	3831.3	4397.2	4933.1	5023.2	5028.2
32.5°	5243.6	4602.6	3836.3	3515.8	3575.9	3921.4	4477.3	5118.4	5318.7	5323.7
35°	5403.9	4742.8	3991.5	3605.9	3696.1	4071.7	4582.5	5293.7	5594.2	5629.2
37.5°	5609.2	4898.0	4171.8	3801.2	3901.4	4287.0	4767.8	5499.0	5919.7	6014.9
40°	5829.6	5053.3	4432.3	4116.8	4262.0	4607.6	4978.2	5729.4	6195.2	6325.4
42.5°	6075.0	5218.6	4727.8	4542.5	4762.8	5013.2	5218.6	5939.7	6405.5	6555.8
45°	6315.4	5418.9	5158.5	5123.4	5368.8	5494.0	5453.9	6090.0	6605.8	6756.1
47.5°	6485.6	5709.4	5679.3	5889.7	6120.0	6054.9	5729.4	6200.2	6771.1	6936.4
50°	6640.9	6070.0	6335.4	6746.1	6886.3	6665.9	6024.9	6350.4	6946.4	7131.7
52.5°	6871.3	6455.6	7011.5	7522.3	7657.6	7307.0	6345.4	6595.8	7216.8	7382.1
55°	7342.0	6891.3	7717.7	8303.6	8328.7	7892.9	6776.1	7011.5	7597.5	7787.8
57.5°	7867.9	7427.2	8278.6	8949.7	8939.7	8478.9	7261.9	7572.4	8113.3	8243.5
60°	8343.7	7968.1	8889.6	9410.4	9385.4	8904.6	7827.8	8208.5	8704.3	8804.4
62.5°	8624.1	8458.9	9160.0	9555.7	9460.5	9044.8	8308.6	8774.4	9125.0	9160.0
65°	8579.1	8739.3	8844.5	9089.9	8954.7	8654.2	8544.0	9135.0	9170.0	9135.0
67.5°	8238.5	8579.1	7978.1	8003.1	7933.0	7677.6	8178.4	9039.8	8799.4	8714.3
70°	7722.7	7747.7	6670.9	6355.4	6465.6	6115.0	7016.5	8298.6	7928.0	7822.8
72.5°	6866.3	6555.8	5043.3	4722.7	4888.0	4637.6	5629.2	7231.9	6871.3	6530.7
75°	5759.4	5193.5	3841.3	3385.6	3470.7	3460.7	4362.2	5974.8	5323.7	4983.2
77.5°	4462.3	4046.6	2834.7	2659.4	2569.2	2589.2	3045.0	4442.3	3861.3	3435.6
80°	3260.3	2829.6	2193.6	2293.8	2243.7	2123.5	2133.5	2974.9	2684.4	2429.0
82.5°	2253.7	2013.3	1777.9	2008.3	1888.1	1702.8	1662.7	2143.5	2013.3	1858.0
85°	1512.5	1657.7	1412.3	1537.5	1332.2	1227.0	1562.6	1792.9	1447.4	1292.1
87.5°	986.6	1517.5	1016.7	771.3	440.7	591.0	956.6	1176.9	676.1	365.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)