

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS
Report Number: P598770

Luminaire Tested: **IFLD-S-SA3E-760-U-SLR**

Issue Date: 05/03/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P598770
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 05/03/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: IFLD-S-SA3E-760-U-SLR
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLR distribution lens
 Light Source: (48) 5700K CCT, 70 CRI LEDs
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 23468.3 lumens
 Efficiency: N/A
 Efficacy: 101.1 lumens/watt
 Spacing Criteria (0/90/45): 1.13 / 0.53 / 0.8
 Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
 CIE Type: Direct

Input Watts (W): 232.1
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P598770
CATALOG NUMBER: IFLD-S-SA3E-760-U-SLR

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - 90°-270° - · · - 135°-315°

TEST NUMBER: P598770
 CATALOG NUMBER: IFLD-S-SA3E-760-U-SLR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	105	99	94	89	102	97	92	87	92	88	84	88	85	82	85	82	79	77	77	77	77
2	93	83	74	67	90	81	73	66	77	70	64	73	68	63	70	65	61	59	59	59	59
3	83	70	60	52	80	68	59	51	65	57	50	62	55	49	59	53	48	46	46	46	46
4	74	60	49	41	72	59	49	41	56	47	40	53	46	40	51	44	39	36	36	36	36
5	68	52	42	34	65	51	41	34	49	40	33	47	39	33	45	38	32	30	30	30	30
6	62	46	36	28	60	45	35	28	43	34	28	41	34	28	40	33	27	25	25	25	25
7	57	41	31	24	55	40	31	24	39	30	24	37	29	24	36	29	23	21	21	21	21
8	53	37	28	21	51	36	27	21	35	27	21	34	26	21	32	26	20	18	18	18	18
9	49	34	25	19	47	33	24	18	32	24	18	31	23	18	30	23	18	16	16	16	16
10	46	31	22	17	44	31	22	17	29	22	16	28	21	16	28	21	16	14	14	14	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	100612	100612	100612	100612
5°	103544	67331	73555	108776
10°	91863	42783	43213	94009
15°	90156	30345	28739	84322
20°	104820	19195	19345	89825
25°	134803	16482	16014	106193
30°	163365	15621	14645	132937
35°	193355	13762	13245	157575
40°	232330	13060	12140	186157
45°	268833	12953	11758	217020
50°	312175	13153	11838	256274
55°	382027	13512	12038	326504
60°	495456	13528	12681	408369
65°	608180	13672	13003	437130
70°	643552	14418	13596	425601
75°	541727	15244	13613	347359
80°	393576	17852	13794	300256
85°	417141	25870	11313	312049

TEST NUMBER: P598770
 CATALOG NUMBER: IFLD-S-SA3E-760-U-SLR

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	542.6	2.3
10°-20°	1135.5	4.8
20°-30°	1636.3	7.0
30°-40°	2355.7	10.0
40°-50°	3346.1	14.3
50°-60°	4810.7	20.5
60°-70°	5557.9	23.7
70°-80°	3147.0	13.4
80°-90°	936.6	4.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3314.4	14.1
0°-40°	5670.0	24.2
0°-60°	13826.8	58.9
0°-90°	23468.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	23468.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	7010	7010	7010	7010	7010	
5°	7187	4674	5106	7550	7187	652
15°	6068	2042	1934	5675	6068	1784
25°	8513	1041	1011	6706	8513	3951
35°	11036	786	756	8994	11036	7004
45°	13245	638	579	10692	13245	10256
55°	15268	540	481	13049	15268	13827
65°	17909	403	383	12872	17909	17173
75°	9769	275	246	6264	9769	10366
85°	2533	157	69	1895	2533	2523
90°	0	0	0	0	0	

TEST NUMBER: P598770
 CATALOG NUMBER: IFLD-S-SA3E-760-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4
2.5°	7403.2	7393.3	7334.4	7147.9	6951.5	6765.0	6588.2	6401.7	6303.5	6185.7	6136.6
5°	7187.2	7167.5	7000.6	6588.2	6224.9	5832.2	5498.4	5233.3	5017.3	4801.3	4722.7
7.5°	6696.2	6666.8	6470.4	5900.9	5370.7	4860.2	4457.6	4114.0	3829.2	3701.6	3554.3
10°	6303.5	6254.4	5999.1	5370.7	4683.4	4172.9	3907.8	3672.1	3426.7	3220.5	3004.5
12.5°	6058.0	5999.1	5734.0	4997.6	4330.0	3947.0	3672.1	3407.0	3102.7	2847.4	2611.7
15°	6067.8	5999.1	5675.1	4899.4	4241.6	3750.7	3367.8	3004.5	2651.0	2366.3	2101.2
17.5°	6352.6	6264.2	5920.6	5036.9	4172.9	3495.4	2984.8	2513.5	2111.0	1806.6	1590.6
20°	6863.1	6804.2	6411.5	5243.1	4104.1	3220.5	2592.1	2022.6	1600.4	1364.8	1276.4
22.5°	7629.0	7560.3	7138.1	5557.3	4084.5	2975.0	2169.9	1590.6	1286.2	1188.0	1138.9
25°	8512.7	8385.0	7992.3	6087.5	4123.8	2749.2	1826.2	1315.7	1148.8	1080.0	1050.6
27.5°	9278.5	9200.0	8758.1	6588.2	4143.4	2572.5	1590.6	1197.9	1070.2	1011.3	991.7
30°	9857.8	9828.3	9396.3	7138.1	4094.3	2356.4	1443.3	1148.8	1070.2	1011.3	952.4
32.5°	10437.1	10446.9	9985.4	7560.3	4025.6	2169.9	1305.9	1021.1	942.6	903.3	913.1
35°	11036.0	11085.1	10692.4	7972.6	3878.3	2101.2	1207.7	952.4	883.7	824.8	795.3
37.5°	11792.0	11919.7	11536.8	8434.1	3731.0	2042.3	1158.6	903.3	834.6	785.5	746.2
40°	12400.8	12636.4	12410.6	8866.1	3632.9	1973.5	1119.3	854.2	805.1	746.2	716.8
42.5°	12852.4	13127.4	13048.8	9200.0	3632.9	1904.8	1080.0	824.8	785.5	716.8	677.5
45°	13245.2	13529.9	13520.1	9543.6	3711.4	1865.5	1030.9	824.8	765.8	697.1	657.8
47.5°	13598.7	13883.4	13981.6	9975.6	3839.0	1845.9	972.0	805.1	765.8	687.3	628.4
50°	13981.6	14295.8	14590.3	10662.9	3996.1	1796.8	932.8	775.7	775.7	677.5	608.7
52.5°	14472.5	14826.0	15366.0	11517.1	4153.2	1708.4	873.8	756.0	775.7	667.7	589.1
55°	15267.8	15562.4	16269.3	12538.3	4349.6	1600.4	824.8	706.9	736.4	638.2	559.7
57.5°	16161.3	16416.6	17005.7	13323.7	4408.5	1463.0	756.0	657.8	706.9	608.7	520.4
60°	17261.0	17388.6	17388.6	13549.6	4212.1	1335.3	706.9	618.6	638.2	579.3	490.9
62.5°	17958.1	17958.1	17388.6	13137.2	3839.0	1227.3	667.7	579.3	559.7	540.0	461.5
65°	17909.0	17830.4	16986.0	11939.3	3407.0	1158.6	628.4	530.2	500.7	490.9	432.0
67.5°	17084.2	16946.8	15798.0	10250.5	2955.4	1129.1	589.1	481.1	461.5	441.8	392.7
70°	15336.5	14983.1	13569.2	8247.6	2513.5	1109.5	579.3	441.8	422.2	402.6	363.3
72.5°	12803.4	12351.7	10594.2	6342.8	2111.0	1040.8	549.8	392.7	382.9	363.3	324.0
75°	9769.4	8934.9	7393.3	4850.3	1639.7	903.3	471.3	343.6	343.6	333.8	294.6
77.5°	6735.5	6303.5	5154.7	3583.8	1197.9	697.1	382.9	304.4	304.4	314.2	274.9
80°	4762.0	4359.4	3672.1	2572.5	756.0	471.3	294.6	255.3	284.7	304.4	255.3
82.5°	3642.7	3348.1	2729.5	1875.3	441.8	324.0	225.8	206.2	245.5	265.1	216.0
85°	2533.2	2179.7	1384.4	1256.8	255.3	196.4	166.9	166.9	216.0	265.1	196.4
87.5°	716.8	304.4	88.4	373.1	108.0	78.5	58.9	39.3	58.9	58.9	39.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598770
 CATALOG NUMBER: IFLD-S-SA3E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4
2.5°	6087.5	6028.6	6028.6	6008.9	6018.8	6028.6	6018.8	6087.5	6116.9	6156.2	6234.8
5°	4673.6	4752.2	4693.3	4752.2	4830.7	4948.5	4978.0	5066.4	5076.2	5144.9	5105.6
7.5°	3465.9	3456.1	3407.0	3475.8	3691.8	3858.7	3937.2	3986.3	3996.1	3996.1	3947.0
10°	2935.7	2847.4	2759.0	2709.9	2729.5	2906.3	2965.2	2994.6	2975.0	3004.5	2965.2
12.5°	2513.5	2435.0	2307.4	2219.0	2160.1	2209.2	2268.1	2297.5	2317.2	2366.3	2405.5
15°	2042.3	1963.7	1885.2	1836.1	1787.0	1747.7	1796.8	1826.2	1875.3	1914.6	1934.2
17.5°	1551.3	1512.1	1472.8	1502.2	1502.2	1482.6	1502.2	1512.1	1531.7	1561.1	1551.3
20°	1256.8	1247.0	1237.1	1286.2	1325.5	1325.5	1345.1	1315.7	1305.9	1276.4	1266.6
22.5°	1119.3	1119.3	1129.1	1168.4	1207.7	1227.3	1227.3	1178.2	1129.1	1109.5	1119.3
25°	1040.8	1040.8	1070.2	1080.0	1099.7	1099.7	1109.5	1060.4	1030.9	1001.5	1011.3
27.5°	981.9	981.9	991.7	991.7	1001.5	1001.5	1011.3	991.7	952.4	942.6	942.6
30°	942.6	942.6	932.8	932.8	932.8	932.8	942.6	913.1	893.5	883.7	883.7
32.5°	903.3	893.5	883.7	883.7	873.8	873.8	883.7	854.2	844.4	844.4	844.4
35°	785.5	775.7	785.5	805.1	805.1	814.9	814.9	805.1	785.5	765.8	756.0
37.5°	736.4	726.6	726.6	726.6	746.2	756.0	765.8	746.2	716.8	687.3	687.3
40°	697.1	697.1	687.3	687.3	687.3	706.9	726.6	697.1	657.8	648.0	648.0
42.5°	667.7	657.8	648.0	638.2	628.4	657.8	677.5	638.2	618.6	618.6	618.6
45°	638.2	628.4	618.6	608.7	598.9	608.7	628.4	589.1	579.3	579.3	579.3
47.5°	608.7	598.9	579.3	569.5	559.7	559.7	579.3	549.8	540.0	549.8	549.8
50°	589.1	569.5	549.8	540.0	530.2	530.2	530.2	520.4	520.4	520.4	530.2
52.5°	569.5	549.8	520.4	510.6	500.7	500.7	500.7	500.7	490.9	500.7	510.6
55°	540.0	520.4	500.7	490.9	481.1	471.3	481.1	471.3	471.3	481.1	481.1
57.5°	500.7	481.1	461.5	461.5	451.7	451.7	461.5	451.7	451.7	461.5	461.5
60°	471.3	451.7	432.0	432.0	422.2	432.0	441.8	432.0	432.0	432.0	441.8
62.5°	432.0	422.2	402.6	402.6	402.6	402.6	412.4	402.6	412.4	412.4	412.4
65°	402.6	382.9	373.1	373.1	373.1	373.1	392.7	373.1	382.9	382.9	382.9
67.5°	373.1	353.5	343.6	343.6	343.6	343.6	363.3	343.6	353.5	363.3	353.5
70°	343.6	324.0	314.2	314.2	314.2	314.2	324.0	314.2	314.2	324.0	324.0
72.5°	304.4	294.6	284.7	284.7	274.9	284.7	294.6	284.7	284.7	284.7	284.7
75°	274.9	265.1	265.1	255.3	255.3	255.3	265.1	245.5	245.5	245.5	245.5
77.5°	255.3	235.6	235.6	235.6	225.8	235.6	225.8	206.2	206.2	206.2	206.2
80°	216.0	196.4	206.2	206.2	196.4	196.4	186.6	166.9	166.9	166.9	166.9
82.5°	176.7	157.1	166.9	166.9	166.9	166.9	147.3	137.5	127.6	117.8	117.8
85°	157.1	127.6	147.3	147.3	137.5	137.5	98.2	98.2	78.5	78.5	68.7
87.5°	29.5	19.6	39.3	49.1	49.1	58.9	39.3	49.1	29.5	19.6	19.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P598770
 CATALOG NUMBER: IFLD-S-SA3E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4
2.5°	6224.9	6332.9	6480.2	6588.2	6755.1	6882.8	7079.2	7246.1	7403.2	7471.9	7540.6
5°	5223.5	5292.2	5518.0	5694.7	5959.8	6244.6	6598.0	6981.0	7373.7	7550.4	7756.6
7.5°	3907.8	4035.4	4163.1	4418.3	4742.3	5203.8	5655.5	6224.9	6774.8	7039.9	7393.3
10°	3033.9	3132.1	3279.4	3544.5	3848.9	4231.8	4771.8	5449.3	6107.1	6450.8	6814.1
12.5°	2435.0	2572.5	2768.8	3043.7	3397.2	3789.9	4182.7	4811.1	5576.9	5969.7	6382.0
15°	1973.5	2081.5	2297.5	2641.2	3053.6	3456.1	3868.5	4388.9	5223.5	5675.1	6166.0
17.5°	1571.0	1649.5	1845.9	2189.5	2601.9	3053.6	3524.8	4182.7	5105.6	5655.5	6234.8
20°	1276.4	1335.3	1463.0	1718.2	2111.0	2601.9	3191.0	3986.3	5174.4	5881.3	6588.2
22.5°	1119.3	1138.9	1197.9	1335.3	1659.3	2179.7	2886.6	3819.4	5302.0	6215.1	7167.5
25°	1011.3	1030.9	1050.6	1138.9	1325.5	1816.4	2621.5	3721.2	5576.9	6706.0	7835.2
27.5°	942.6	962.2	972.0	1011.3	1138.9	1551.3	2395.7	3662.3	5950.0	7422.8	8659.9
30°	883.7	883.7	913.1	972.0	1060.4	1364.8	2199.3	3524.8	6342.8	8021.7	9308.0
32.5°	834.6	844.4	883.7	913.1	972.0	1207.7	2003.0	3348.1	6696.2	8512.7	9946.2
35°	746.2	746.2	756.0	805.1	883.7	1080.0	1826.2	3171.4	6892.6	8993.8	10515.6
37.5°	687.3	697.1	716.8	756.0	824.8	991.7	1679.0	2975.0	7098.8	9445.4	11183.3
40°	648.0	657.8	677.5	716.8	785.5	913.1	1551.3	2817.9	7314.8	9936.3	11900.0
42.5°	618.6	628.4	648.0	687.3	746.2	893.5	1413.9	2690.3	7442.4	10388.0	12577.5
45°	589.1	598.9	628.4	667.7	716.8	873.8	1335.3	2601.9	7491.5	10692.4	13117.5
47.5°	559.7	569.5	598.9	657.8	716.8	844.4	1305.9	2552.8	7530.8	11036.0	13549.6
50°	530.2	549.8	589.1	648.0	726.6	805.1	1286.2	2543.0	7756.6	11477.9	13961.9
52.5°	510.6	540.0	579.3	648.0	716.8	746.2	1276.4	2572.5	8208.3	12135.7	14551.0
55°	490.9	520.4	559.7	648.0	687.3	697.1	1227.3	2621.5	8895.6	13048.8	15385.6
57.5°	471.3	490.9	540.0	628.4	648.0	657.8	1129.1	2690.3	9582.9	13942.3	16239.8
60°	441.8	461.5	510.6	628.4	589.1	618.6	1001.5	2709.9	10073.8	14227.0	16318.4
62.5°	412.4	432.0	481.1	648.0	540.0	579.3	893.5	2641.2	10172.0	13814.7	15876.5
65°	382.9	402.6	441.8	540.0	500.7	540.0	824.8	2454.6	9848.0	12872.1	15071.4
67.5°	353.5	373.1	402.6	441.8	451.7	490.9	795.3	2160.1	9033.0	11703.7	13971.8
70°	314.2	333.8	363.3	392.7	402.6	461.5	746.2	1875.3	7717.4	10142.5	12626.6
72.5°	284.7	294.6	324.0	343.6	363.3	422.2	716.8	1639.7	5900.9	8208.3	10299.6
75°	245.5	245.5	274.9	294.6	314.2	373.1	657.8	1364.8	4163.1	6264.2	7570.1
77.5°	206.2	206.2	225.8	245.5	265.1	324.0	559.7	1109.5	2886.6	4968.2	5488.6
80°	157.1	157.1	176.7	196.4	216.0	274.9	451.7	814.9	1787.0	3632.9	3996.1
82.5°	108.0	108.0	137.5	147.3	157.1	216.0	343.6	559.7	1050.6	2621.5	2857.2
85°	58.9	58.9	78.5	88.4	108.0	157.1	255.3	392.7	628.4	1895.0	1904.8
87.5°	9.8	9.8	29.5	29.5	49.1	78.5	147.3	216.0	353.5	1050.6	667.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P598770
 CATALOG NUMBER: IFLD-S-SA3E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4	7010.4
2.5°	7668.3	7776.3	7786.1	7786.1	7737.0	7746.8	7609.4	7462.1	7413.0	7403.2
5°	8070.8	8355.6	8434.1	8473.4	8345.7	8149.4	7795.9	7413.0	7216.6	7187.2
7.5°	7992.3	8561.7	8866.1	8905.4	8650.1	8188.6	7570.1	6981.0	6755.1	6696.2
10°	7530.8	8296.6	8846.5	8983.9	8709.0	8119.9	7314.8	6627.5	6352.6	6303.5
12.5°	7206.8	7943.2	8483.2	8669.8	8542.1	8031.5	7187.2	6401.7	6126.8	6058.0
15°	7030.1	7707.5	8061.0	8119.9	8110.1	7894.1	7187.2	6450.8	6146.4	6067.8
17.5°	7177.3	7638.8	7687.9	7550.4	7629.0	7737.0	7344.3	6715.9	6421.3	6352.6
20°	7471.9	7609.4	7373.7	7167.5	7206.8	7550.4	7589.7	7216.6	6981.0	6863.1
22.5°	8090.5	7717.4	7177.3	6892.6	6922.1	7403.2	7913.7	7894.1	7687.9	7629.0
25°	8718.8	8021.7	7118.4	6784.6	6823.9	7373.7	8296.6	8650.1	8542.1	8512.7
27.5°	9416.0	8532.3	7157.7	6735.5	6784.6	7413.0	8561.7	9288.3	9308.0	9278.5
30°	9887.2	8777.8	7275.5	6794.4	6863.1	7511.2	8620.7	9671.2	9848.0	9857.8
32.5°	10280.0	9023.2	7521.0	6892.6	7010.4	7687.9	8777.8	10034.5	10427.3	10437.1
35°	10594.2	9298.1	7825.4	7069.3	7246.1	7982.5	8983.9	10378.2	10967.3	11036.0
37.5°	10996.7	9602.5	8178.8	7452.3	7648.6	8404.7	9347.2	10780.7	11605.5	11792.0
40°	11428.8	9906.9	8689.4	8070.8	8355.6	9033.0	9759.6	11232.4	12145.5	12400.8
42.5°	11909.9	10230.9	9268.7	8905.4	9337.4	9828.3	10230.9	11644.8	12557.9	12852.4
45°	12381.2	10623.6	10113.1	10044.3	10525.5	10770.9	10692.4	11939.3	12950.6	13245.2
47.5°	12715.0	11193.1	11134.2	11546.6	11998.2	11870.6	11232.4	12155.3	13274.6	13598.7
50°	13019.4	11900.0	12420.4	13225.5	13500.5	13068.5	11811.7	12449.9	13618.3	13981.6
52.5°	13471.0	12656.1	13745.9	14747.4	15012.5	14325.2	12440.1	12931.0	14148.5	14472.5
55°	14394.0	13510.3	15130.3	16279.1	16328.2	15474.0	13284.5	13745.9	14894.7	15267.8
57.5°	15424.9	14560.9	16230.0	17545.7	17526.1	16622.8	14236.9	14845.6	15906.0	16161.3
60°	16357.7	15621.3	17427.9	18449.0	18399.9	17457.3	15346.3	16092.6	17064.6	17261.0
62.5°	16907.5	16583.5	17958.1	18733.7	18547.2	17732.2	16288.9	17202.0	17889.3	17958.1
65°	16819.1	17133.3	17339.5	17820.6	17555.5	16966.4	16750.4	17909.0	17977.7	17909.0
67.5°	16151.5	16819.1	15640.9	15690.0	15552.5	15051.8	16033.6	17722.4	17251.1	17084.2
70°	15140.2	15189.3	13078.3	12459.7	12675.7	11988.4	13755.7	16269.3	15542.7	15336.5
72.5°	13461.2	12852.4	9887.2	9258.9	9582.9	9091.9	11036.0	14177.9	13471.0	12803.4
75°	11291.3	10181.8	7530.8	6637.3	6804.2	6784.6	8551.9	11713.5	10437.1	9769.4
77.5°	8748.3	7933.4	5557.3	5213.6	5036.9	5076.2	5969.7	8709.0	7570.1	6735.5
80°	6391.9	5547.5	4300.5	4496.9	4398.7	4163.1	4182.7	5832.2	5262.7	4762.0
82.5°	4418.3	3947.0	3485.6	3937.2	3701.6	3338.3	3259.7	4202.3	3947.0	3642.7
85°	2965.2	3249.9	2768.8	3014.3	2611.7	2405.5	3063.4	3515.0	2837.6	2533.2
87.5°	1934.2	2975.0	1993.2	1512.1	864.0	1158.6	1875.3	2307.4	1325.5	716.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)