

Scaled data based on original data using
LM-46-04 Photometric Testing of Indoor Luminaires Using High Intensity Discharge
or Incandescent Filament Lamps (Reaffirmed 2012)

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: STREETWORKS

Report Number: 768065

Luminaire Tested: **CLB17MXX55X1X**

Issue Date: 3/3/2020

Test Information

Test Method: LM-46-04
Report Number: 768065
Test Lab:
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: CLB17MXX55X1X
Description: REFRACTIVE GLOBE TYPE V ACRYLIC
WITH CLEAR TOP
Light Source: 175W MH CL ED-28
Ballast/Driver: -

Summary

Lumens per Lamp: 14000 (1 lamp)
Luminaire Lumens: 12874.6 lumens
Efficiency: 92.0%
Efficacy: 73.6 lumens/watt
Luminous Opening: Point Source (0' x 0' x 0')
IES Classification: Type V - Short - Non-Cutoff
BUG Rating: B4 - U5 - G3


Input Watts (W): 175
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: 768065
 CATALOG NUMBER: CLB17MXX55X1X

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 0.6 fc
 Type V - Short - Non-Cutoff

REPORT NUMBER: 768065
CATALOG NUMBER: CLB17MXX55X1X

Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical



REPORT NUMBER: 768065

CATALOG NUMBER: CLB17MXX55X1X


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4056.5	2380.8	6437.3
	% Lamp	29.0	17.0	46.0
Street Side	Lumens	4056.5	2380.8	6437.3
	% Lamp	29.0	17.0	46.0
Total	Lumens	8112.9	4761.6	12874.6
	% Lamp	57.9	34.0	92.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture	% Lamp
0°-10°	8.6	0.1	0.1
10°-20°	30.0	0.2	0.2
20°-30°	85.9	0.7	0.6
30°-40°	206.1	1.6	1.5
40°-50°	530.3	4.1	3.8
50°-60°	874.2	6.8	6.2
60°-70°	2775.6	21.6	19.8
70°-80°	2950.2	22.9	21.1
80°-90°	652.0	5.1	4.7
90°-100°	607.5	4.7	4.3
100°-110°	812.2	6.3	5.8
110°-120°	851.9	6.6	6.1
120°-130°	822.9	6.4	5.9
130°-140°	710.2	5.5	5.1
140°-150°	496.9	3.9	3.5
150°-160°	273.1	2.1	2.0
160°-170°	107.2	0.8	0.8
170°-180°	26.8	0.2	0.2
0°-90°	8112.9	63.0	57.9
0°-180°	12874.6	100.0	92.0



REPORT NUMBER: 768065


CATALOG NUMBER: CLB17MXX55X1X

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Lamp	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	62.3	0.4			
FM	(30°-60°)	805.3	5.8			
FH	(60°-80°)	2862.9	20.4			G2/5000
FVH	(80°-90°)	326.0	2.3			G3/500
BL	(0°-30°)	62.3	0.4	B0/110		
BM	(30°-60°)	805.3	5.8	B1/1000		
BH	(60°-80°)	2862.9	20.4	B4/5000		G2/5000
BVH	(80°-90°)	326.0	2.3			G3/500
UL	(90°-100°)	607.5	4.3		U4/1000	
UH	(100°-180°)	2380.8	17.0		U5	
Trapped Light		1125.4	8.0			

BUG Rating: B4-U5-G3

Type V Short





REPORT NUMBER: 768065

CATALOG NUMBER: CLB17MXX55X1X

CANDELA DISTRIBUTION (FULL):

	0°
0°	93
2.5°	88
5°	87
7.5°	92
10°	93
12.5°	98
15°	102
17.5°	111
20°	120
22.5°	142
25°	181
27.5°	221
30°	245
32.5°	271
35°	299
37.5°	364
40°	478
42.5°	574
45°	678
47.5°	800
50°	852
52.5°	921
55°	999
57.5°	1020
60°	1048
62.5°	1825
65°	2911
67.5°	3778
70°	4120
72.5°	3870
75°	2826
77.5°	1882
80°	1132
82.5°	667
85°	494
87.5°	444
90°	445
95°	544
105°	846
115°	835
125°	917
135°	1000
145°	751
155°	662
165°	285



REPORT NUMBER: 768065

CATALOG NUMBER: CLB17MXX55X1X

CANDELA DISTRIBUTION (continued):

	0°
175°	281
180°	279

(END OF REPORT)