

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P856078

Luminaire Tested: **FFX-CLB-60-730-U-FR-T5**

Issue Date: 07/16/2024



Test Information

Test Method: LM-79-08
Report Number: P856078
Test Lab: INNOVATION CENTER(G3)
Issue Date: 07/16/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: FFX-CLB-60-730-U-FR-T5
Description: FAIRFAX POST TOP FIXTURE w/ FAIRFAX REFRACTOR T5 DISTRIBUTION LENS
Light Source: (6) 3000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9497.1 lumens
Efficiency: N/A
Efficacy: 158.8 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 1.17' x H: 1.67')
IES Classification: Type V - Short
BUG Rating: B3 - U5 - G3

Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.99
Total Harmonic Distortion (THDi): 8.9%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

REPORT NUMBER: P856078
 CATALOG NUMBER: FFX-CLB-60-730-U-FR-T5

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 1.7 fc
 Type V - Short - N/A

REPORT NUMBER: P856078
CATALOG NUMBER: FFX-CLB-60-730-U-FR-T5

Luminous Intensity Polar Plot



— Vertical Plane Through 5-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P856078

CATALOG NUMBER: FFX-CLB-60-730-U-FR-T5


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3826.9	921.6	4748.6
	% Fixture	40.3	9.7	50.0
Street Side	Lumens	3826.9	921.6	4748.6
	% Fixture	40.3	9.7	50.0
Total	Lumens	7653.9	1843.3	9497.1
	% Fixture	80.6	19.4	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	10.8	0.1
10°-20°	54.2	0.6
20°-30°	117.8	1.2
30°-40°	233.8	2.5
40°-50°	507.2	5.3
50°-60°	1746.6	18.4
60°-70°	2868.7	30.2
70°-80°	1539.7	16.2
80°-90°	575.0	6.1
90°-100°	363.2	3.8
100°-110°	243.2	2.6
110°-120°	267.3	2.8
120°-130°	442.3	4.7
130°-140°	260.5	2.7
140°-150°	137.8	1.5
150°-160°	72.4	0.8
160°-170°	41.1	0.4
170°-180°	15.5	0.2
0°-90°	7653.9	80.6
0°-180°	9497.1	100.0




REPORT NUMBER: P856078
 CATALOG NUMBER: FFX-CLB-60-730-U-FR-T5

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	91.4	1.0			
FM (30°-60°)	1243.8	13.1			
FH (60°-80°)	2204.2	23.2			G2/5000
FVH (80°-90°)	287.5	3.0			G3/500
BL (0°-30°)	91.4	1.0	B0/110		
BM (30°-60°)	1243.8	13.1	B2/2500		
BH (60°-80°)	2204.2	23.2	B3/2500		G2/5000
BVH (80°-90°)	287.5	3.0			G3/500
UL (90°-100°)	363.2	3.8		U3/500	
UH (100°-180°)	1480.1	15.6		U5	

BUG Rating: B3-U5-G3

Type V Short





REPORT NUMBER: P856078

CATALOG NUMBER: FFX-CLB-60-730-U-FR-T5

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	70.7	70.7	70.7	70.7	70.7	70.7	70.7	70.7	70.7	70.7	70.7
2.5°	74.5	74.5	73.6	72.6	73.6	74.5	74.5	75.5	73.6	73.6	74.5
5°	99.7	99.7	99.7	98.7	96.8	96.8	95.8	98.7	99.7	100.7	100.7
7.5°	123.9	122.9	124.9	125.8	121.0	119.1	119.1	120.0	122.0	123.9	125.8
10°	140.4	139.4	140.4	144.2	143.3	140.4	140.4	140.4	143.3	148.1	149.1
12.5°	165.5	165.5	167.5	170.4	171.3	168.4	166.5	166.5	170.4	171.3	170.4
15°	192.6	192.6	191.7	190.7	191.7	190.7	190.7	191.7	194.6	193.6	193.6
17.5°	207.2	206.2	205.2	206.2	206.2	205.2	206.2	208.1	207.2	210.1	211.0
20°	222.6	222.6	220.7	220.7	220.7	221.7	222.6	221.7	222.6	223.6	224.6
22.5°	237.2	237.2	236.2	235.2	236.2	237.2	238.1	236.2	236.2	238.1	238.1
25°	253.6	253.6	253.6	250.7	251.7	252.6	251.7	250.7	251.7	252.6	253.6
27.5°	272.0	272.0	270.1	267.2	268.1	268.1	269.1	267.2	269.1	269.1	269.1
30°	287.5	285.6	284.6	282.7	282.7	284.6	286.5	283.6	284.6	284.6	285.6
32.5°	302.0	302.0	301.0	297.2	296.2	302.0	304.0	303.0	299.1	300.1	301.0
35°	356.2	356.2	349.4	342.7	348.5	347.5	355.3	355.3	355.3	357.2	361.1
37.5°	424.0	426.9	437.5	453.0	453.0	430.8	419.1	418.2	433.7	447.2	446.2
40°	484.0	486.9	484.0	485.9	484.0	485.0	485.9	484.0	475.3	472.4	466.6
42.5°	558.5	559.5	541.1	519.8	521.8	532.4	545.0	546.0	527.6	518.8	516.9
45°	610.8	612.7	606.0	603.1	603.1	606.9	606.0	606.0	599.2	598.2	596.3
47.5°	738.6	734.7	721.2	716.3	722.1	719.2	737.6	732.8	725.0	725.0	731.8
50°	979.6	975.7	976.7	971.9	987.4	965.1	987.4	981.6	969.9	975.7	980.6
52.5°	1373.6	1349.4	1352.3	1342.6	1369.7	1349.4	1386.2	1381.3	1343.6	1360.0	1361.0
55°	1940.8	1909.9	1907.9	1843.1	1893.4	1900.2	1946.6	1958.3	1884.7	1885.7	1890.5
57.5°	2503.2	2493.6	2524.5	2483.9	2519.7	2503.2	2502.3	2523.6	2481.0	2486.8	2502.3
60°	2875.9	2883.7	2918.5	2929.2	2941.8	2918.5	2871.1	2880.8	2877.9	2927.2	2931.1
62.5°	3075.3	3098.6	3073.4	3065.7	3055.0	3063.7	3057.9	3063.7	3046.3	3069.5	3070.5
65°	3068.6	3105.3	3059.8	3031.8	3014.4	3041.5	3049.2	3066.6	3029.8	3015.3	3015.3
67.5°	2874.0	2918.5	2846.9	2844.0	2801.4	2846.9	2834.3	2847.9	2818.8	2798.5	2779.1
70°	2391.0	2431.6	2345.5	2356.1	2282.5	2357.1	2337.7	2362.9	2339.7	2300.0	2276.7
72.5°	1801.4	1837.3	1773.4	1789.8	1741.4	1797.6	1767.6	1810.2	1795.6	1778.2	1758.9
75°	1362.9	1391.0	1394.9	1450.1	1392.0	1419.1	1364.9	1390.0	1414.2	1434.6	1413.3
77.5°	1002.8	1022.2	1080.3	1141.3	1084.2	1103.5	1049.3	1073.5	1095.8	1130.6	1115.1
80°	708.6	730.8	784.1	829.6	788.0	805.4	770.5	784.1	801.5	826.7	810.2
82.5°	551.8	544.0	542.1	530.5	517.9	561.4	570.2	577.9	561.4	554.7	546.9
85°	462.7	464.6	476.3	490.8	490.8	491.7	483.0	486.9	493.7	506.3	507.2
87.5°	425.0	430.8	463.7	475.3	470.4	472.4	464.6	466.6	471.4	478.2	476.3
90°	374.6	389.1	420.1	431.7	424.0	427.9	424.0	426.9	423.0	425.0	421.1
92.5°	365.9	364.9	374.6	373.6	368.8	380.4	380.4	382.4	377.5	374.6	372.7
95°	338.8	336.9	335.9	338.8	328.2	336.9	334.9	338.8	336.9	336.9	333.0
97.5°	283.6	283.6	281.7	284.6	277.8	281.7	276.8	279.8	278.8	279.8	276.8
100°	261.4	261.4	259.4	259.4	256.5	257.5	255.6	255.6	254.6	253.6	253.6
102.5°	245.9	247.8	244.9	245.9	242.0	242.0	240.1	241.0	240.1	240.1	239.1
105°	231.4	232.3	230.4	230.4	227.5	226.5	224.6	225.5	226.5	224.6	224.6
107.5°	216.8	217.8	216.8	216.8	213.9	212.0	209.1	209.1	210.1	211.0	211.0
110°	222.6	219.7	216.8	214.9	218.8	213.0	211.0	210.1	211.0	213.9	214.9



REPORT NUMBER: P856078
 CATALOG NUMBER: FFX-CLB-60-730-U-FR-T5

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	266.2	264.3	264.3	255.6	265.2	259.4	255.6	248.8	251.7	253.6	253.6
115°	308.8	309.8	298.1	294.3	288.5	287.5	290.4	282.7	281.7	282.7	280.7
117.5°	346.5	326.2	282.7	271.0	268.1	266.2	264.3	262.3	260.4	272.0	259.4
120°	370.7	335.9	304.0	297.2	313.6	290.4	274.9	272.0	277.8	298.1	295.2
122.5°	525.6	495.6	472.4	431.7	472.4	449.2	455.0	444.3	438.5	426.9	428.8
125°	614.7	613.7	603.1	595.3	605.0	596.3	586.6	582.7	576.9	579.8	575.0
127.5°	571.1	579.8	566.3	581.8	546.9	556.6	554.7	561.4	555.6	557.6	549.8
130°	452.1	458.8	446.2	438.5	423.0	440.4	441.4	452.1	440.4	425.0	423.0
132.5°	394.9	399.8	380.4	370.7	360.1	375.6	382.4	388.2	380.4	364.0	360.1
135°	335.9	337.8	324.3	326.2	319.4	319.4	318.5	321.4	325.2	322.3	320.4
137.5°	288.5	293.3	288.5	294.3	288.5	283.6	275.9	278.8	287.5	294.3	293.3
140°	249.7	254.6	255.6	261.4	249.7	251.7	246.8	248.8	253.6	260.4	263.3
142.5°	221.7	225.5	216.8	212.0	208.1	219.7	228.4	229.4	223.6	215.9	218.8
145°	215.9	212.0	215.9	212.0	215.9	213.9	214.9	213.9	213.9	213.9	213.9
147.5°	218.8	222.6	222.6	222.6	216.8	217.8	218.8	219.7	219.7	223.6	222.6
150°	182.0	186.8	185.9	190.7	182.0	183.9	184.9	186.8	187.8	188.8	189.7
152.5°	153.9	154.9	157.8	159.7	158.8	157.8	156.8	156.8	158.8	160.7	161.7
155°	150.0	150.0	152.9	155.8	152.9	152.9	152.0	152.0	152.9	155.8	155.8
157.5°	144.2	145.2	145.2	147.1	145.2	146.2	145.2	145.2	146.2	147.1	148.1
160°	141.3	142.3	142.3	142.3	142.3	142.3	142.3	142.3	142.3	143.3	143.3
162.5°	141.3	141.3	141.3	140.4	140.4	141.3	141.3	141.3	141.3	140.4	141.3
165°	144.2	143.3	142.3	141.3	142.3	144.2	145.2	145.2	144.2	142.3	143.3
167.5°	150.0	150.0	149.1	148.1	149.1	150.0	151.0	151.0	150.0	149.1	149.1
170°	155.8	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9
172.5°	159.7	159.7	160.7	159.7	160.7	160.7	159.7	159.7	159.7	159.7	160.7
175°	165.5	165.5	165.5	165.5	166.5	166.5	166.5	166.5	166.5	166.5	166.5
177.5°	169.4	169.4	169.4	169.4	169.4	169.4	169.4	169.4	169.4	169.4	169.4
180°	170.4	170.4	170.4	170.4	170.4	170.4	170.4	170.4	170.4	170.4	170.4

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2406-133-4

Test Date: 07/12/2024

Luminaire Tested: FFX-CLB-100-730-U-FR-T5

Data in this report applies to families of products including FFX-CLB-100-730-U-FR-T5.

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2406-133-4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 07/12/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Streetworks
 Catalog Number: **FFX-CLB-100-730-U-FR-T5**
 Description: FAIRFAX ACORN W/ FAIRFAX REFRACTOR 100W T5

Spectral Parameters

CCT (K): 3003
 CIE u': 0.2503
 CIE v': 0.5219
 Duv: 0.0004
 CIE x: 0.4373
 CIE y: 0.4053
 CIE z: 0.1573
 Peak Wavelength (nm): 595
 Dominant Wavelength (nm): 582
 Purity: 52.93545
 Rf: 75.2
 Rg: 93.8

CRI (Ra):	71.9		
R1:	68.2	R9:	-33.7
R2:	82.2	R10:	59.0
R3:	93.9	R11:	62.4
R4:	67.6	R12:	48.5
R5:	67.2	R13:	70.8
R6:	75.3	R14:	96.6
R7:	77.6	R15:	60.0
R8:	43.1		



Test Conditions

Stabilization Time: 0.794393M
 Operation Time: 1H
 Sphere Temperature (°C): 24.7

REPORT NUMBER: SP1-2406-133-4

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2406-133-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2406-133-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	110	NR	620	825	NR	750	23	NR	880	1	NR
365	0	NR	495	139	NR	625	765	NR	755	19	NR	885	1	NR
370	0	NR	500	186	NR	630	702	NR	760	17	NR	890	0	NR
375	0	NR	505	243	NR	635	635	NR	765	14	NR	895	0	NR
380	0	NR	510	301	NR	640	572	NR	770	12	NR	900	0	NR
385	0	NR	515	357	NR	645	512	NR	775	11	NR	905	0	NR
390	0	NR	520	406	NR	650	455	NR	780	9	NR	910	0	NR
395	0	NR	525	445	NR	655	400	NR	785	8	NR	915	0	NR
400	2	NR	530	483	NR	660	350	NR	790	7	NR	920	0	NR
405	5	NR	535	514	NR	665	305	NR	795	6	NR	925	0	NR
410	10	NR	540	545	NR	670	264	NR	800	5	NR	930	0	NR
415	21	NR	545	581	NR	675	229	NR	805	4	NR	935	0	NR
420	39	NR	550	620	NR	680	198	NR	810	4	NR	940	0	NR
425	69	NR	555	666	NR	685	170	NR	815	3	NR	945	0	NR
430	112	NR	560	716	NR	690	147	NR	820	3	NR	950	0	NR
435	174	NR	565	771	NR	695	125	NR	825	3	NR	955	0	NR
440	260	NR	570	831	NR	700	107	NR	830	2	NR	960	0	NR
445	410	NR	575	887	NR	705	92	NR	835	2	NR	965	0	NR
450	574	NR	580	937	NR	710	79	NR	840	2	NR	970	0	NR
455	508	NR	585	974	NR	715	67	NR	845	1	NR	975	0	NR
460	319	NR	590	994	NR	720	57	NR	850	1	NR	980	0	NR
465	234	NR	595	1000	NR	725	49	NR	855	1	NR	985	0	NR
470	174	NR	600	992	NR	730	42	NR	860	1	NR	990	0	NR
475	121	NR	605	966	NR	735	36	NR	865	1	NR	995	0	NR
480	100	NR	610	929	NR	740	30	NR	870	1	NR	1000	0	NR
485	99	NR	615	880	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP1-2406-133-4

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.21

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	110	NR	620	825	NR	750	23	NR	880	1	NR
365	0	NR	495	139	NR	625	765	NR	755	19	NR	885	1	NR
370	0	NR	500	186	NR	630	702	NR	760	17	NR	890	0	NR
375	0	NR	505	243	NR	635	635	NR	765	14	NR	895	0	NR
380	0	NR	510	301	NR	640	572	NR	770	12	NR	900	0	NR
385	0	NR	515	357	NR	645	512	NR	775	11	NR	905	0	NR
390	0	NR	520	406	NR	650	455	NR	780	9	NR	910	0	NR
395	0	NR	525	445	NR	655	400	NR	785	8	NR	915	0	NR
400	2	NR	530	483	NR	660	350	NR	790	7	NR	920	0	NR
405	5	NR	535	514	NR	665	305	NR	795	6	NR	925	0	NR
410	10	NR	540	545	NR	670	264	NR	800	5	NR	930	0	NR
415	21	NR	545	581	NR	675	229	NR	805	4	NR	935	0	NR
420	39	NR	550	620	NR	680	198	NR	810	4	NR	940	0	NR
425	69	NR	555	666	NR	685	170	NR	815	3	NR	945	0	NR
430	112	NR	560	716	NR	690	147	NR	820	3	NR	950	0	NR
435	174	NR	565	771	NR	695	125	NR	825	3	NR	955	0	NR
440	260	NR	570	831	NR	700	107	NR	830	2	NR	960	0	NR
445	410	NR	575	887	NR	705	92	NR	835	2	NR	965	0	NR
450	574	NR	580	937	NR	710	79	NR	840	2	NR	970	0	NR
455	508	NR	585	974	NR	715	67	NR	845	1	NR	975	0	NR
460	319	NR	590	994	NR	720	57	NR	850	1	NR	980	0	NR
465	234	NR	595	1000	NR	725	49	NR	855	1	NR	985	0	NR
470	174	NR	600	992	NR	730	42	NR	860	1	NR	990	0	NR
475	121	NR	605	966	NR	735	36	NR	865	1	NR	995	0	NR
480	100	NR	610	929	NR	740	30	NR	870	1	NR	1000	0	NR
485	99	NR	615	880	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP1-2406-133-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.22

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	110	NR	620	825	NR	750	23	NR	880	1	NR
365	0	NR	495	139	NR	625	765	NR	755	19	NR	885	1	NR
370	0	NR	500	186	NR	630	702	NR	760	17	NR	890	0	NR
375	0	NR	505	243	NR	635	635	NR	765	14	NR	895	0	NR
380	0	NR	510	301	NR	640	572	NR	770	12	NR	900	0	NR
385	0	NR	515	357	NR	645	512	NR	775	11	NR	905	0	NR
390	0	NR	520	406	NR	650	455	NR	780	9	NR	910	0	NR
395	0	NR	525	445	NR	655	400	NR	785	8	NR	915	0	NR
400	2	NR	530	483	NR	660	350	NR	790	7	NR	920	0	NR
405	5	NR	535	514	NR	665	305	NR	795	6	NR	925	0	NR
410	10	NR	540	545	NR	670	264	NR	800	5	NR	930	0	NR
415	21	NR	545	581	NR	675	229	NR	805	4	NR	935	0	NR
420	39	NR	550	620	NR	680	198	NR	810	4	NR	940	0	NR
425	69	NR	555	666	NR	685	170	NR	815	3	NR	945	0	NR
430	112	NR	560	716	NR	690	147	NR	820	3	NR	950	0	NR
435	174	NR	565	771	NR	695	125	NR	825	3	NR	955	0	NR
440	260	NR	570	831	NR	700	107	NR	830	2	NR	960	0	NR
445	410	NR	575	887	NR	705	92	NR	835	2	NR	965	0	NR
450	574	NR	580	937	NR	710	79	NR	840	2	NR	970	0	NR
455	508	NR	585	974	NR	715	67	NR	845	1	NR	975	0	NR
460	319	NR	590	994	NR	720	57	NR	850	1	NR	980	0	NR
465	234	NR	595	1000	NR	725	49	NR	855	1	NR	985	0	NR
470	174	NR	600	992	NR	730	42	NR	860	1	NR	990	0	NR
475	121	NR	605	966	NR	735	36	NR	865	1	NR	995	0	NR
480	100	NR	610	929	NR	740	30	NR	870	1	NR	1000	0	NR
485	99	NR	615	880	NR	745	26	NR	875	1	NR			

REPORT NUMBER: SP1-2406-133-4


TM-30-18

Summary

$R_f = 75.2$
 $R_g = 93.8$
 CIE $R_a = 71.9$
 $R_g = -33.7$



Color Vector Graphics



REPORT NUMBER: SP1-2406-133-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 66	CES51 = 87	CES76 = 59
CES02 = 62	CES27 = 89	CES52 = 85	CES77 = 77
CES03 = 31	CES28 = 85	CES53 = 77	CES78 = 63
CES04 = 71	CES29 = 69	CES54 = 86	CES79 = 86
CES05 = 49	CES30 = 84	CES55 = 84	CES80 = 84
CES06 = 51	CES31 = 72	CES56 = 75	CES81 = 72
CES07 = 41	CES32 = 65	CES57 = 74	CES82 = 93
CES08 = 40	CES33 = 79	CES58 = 75	CES83 = 91
CES09 = 29	CES34 = 76	CES59 = 85	CES84 = 88
CES10 = 76	CES35 = 87	CES60 = 90	CES85 = 75
CES11 = 59	CES36 = 93	CES61 = 81	CES86 = 63
CES12 = 65	CES37 = 85	CES62 = 89	CES87 = 77
CES13 = 43	CES38 = 92	CES63 = 75	CES88 = 80
CES14 = 74	CES39 = 97	CES64 = 66	CES89 = 67
CES15 = 71	CES40 = 93	CES65 = 65	CES90 = 80
CES16 = 47	CES41 = 93	CES66 = 61	CES91 = 80
CES17 = 50	CES42 = 87	CES67 = 59	CES92 = 57
CES18 = 56	CES43 = 79	CES68 = 67	CES93 = 73
CES19 = 73	CES44 = 99	CES69 = 76	CES94 = 50
CES20 = 66	CES45 = 85	CES70 = 61	CES95 = 67
CES21 = 87	CES46 = 81	CES71 = 58	CES96 = 77
CES22 = 79	CES47 = 86	CES72 = 85	CES97 = 83
CES23 = 92	CES48 = 75	CES73 = 54	CES98 = 76
CES24 = 91	CES49 = 79	CES74 = 95	CES99 = 65
CES25 = 73	CES50 = 86	CES75 = 61	



REPORT NUMBER: SP1-2406-133-4

TM-30-18



Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-2406-133-4

TM-30-18

Measure Comparisons



(END OF REPORT)