

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P856412

Luminaire Tested: **FFX-CLB-50-750-U-VM9**

Issue Date: 07/16/2024



Test Information

Test Method: LM-79-08
Report Number: P856412
Test Lab: INNOVATION CENTER(G3)
Issue Date: 07/16/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: FFX-CLB-50-750-U-VM9
Description: FAIRFAX POST TOP FIXTURE w/ ULA ACORN 9 INCH NECK
Light Source: (6) 5000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8106.1 lumens
Efficiency: N/A
Efficacy: 160.5 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 1.33' x H: 2.08')
IES Classification: Type V - Short
BUG Rating: B2 - U5 - G3

Input Watts (W): 50.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.99
Total Harmonic Distortion (THDi): 6.0%%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

REPORT NUMBER: P856412
 CATALOG NUMBER: FFX-CLB-50-750-U-VM9

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 1.4 fc
 Type V - Short - N/A

REPORT NUMBER: P856412
CATALOG NUMBER: FFX-CLB-50-750-U-VM9

Luminous Intensity Polar Plot



— Vertical Plane Through 90-Deg Lateral - - - Horizontal Cone Through 72.5-Deg Vertical

REPORT NUMBER: P856412
 CATALOG NUMBER: FFX-CLB-50-750-U-VM9


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2374.2	1678.9	4053.0
	% Fixture	29.3	20.7	50.0
Street Side	Lumens	2374.2	1678.9	4053.0
	% Fixture	29.3	20.7	50.0
Total	Lumens	4748.4	3357.7	8106.1
	% Fixture	58.6	41.4	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	10.4	0.1
10°-20°	60.8	0.8
20°-30°	175.7	2.2
30°-40°	365.5	4.5
40°-50°	580.0	7.2
50°-60°	761.4	9.4
60°-70°	887.8	11.0
70°-80°	953.6	11.8
80°-90°	953.2	11.8
90°-100°	892.2	11.0
100°-110°	782.8	9.7
110°-120°	629.6	7.8
120°-130°	452.2	5.6
130°-140°	290.6	3.6
140°-150°	168.6	2.1
150°-160°	88.6	1.1
160°-170°	41.2	0.5
170°-180°	11.9	0.1
0°-90°	4748.4	58.6
0°-180°	8106.1	100.0




REPORT NUMBER: P856412
 CATALOG NUMBER: FFX-CLB-50-750-U-VM9

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	123.5	1.5			
FM (30°-60°)	853.4	10.5			
FH (60°-80°)	920.7	11.4			G1/1800
FVH (80°-90°)	476.6	5.9			G3/500
BL (0°-30°)	123.5	1.5	B1/500		
BM (30°-60°)	853.4	10.5	B1/1000		
BH (60°-80°)	920.7	11.4	B2/1000		G1/1800
BVH (80°-90°)	476.6	5.9			G3/500
UL (90°-100°)	892.2	11.0		U4/1000	
UH (100°-180°)	2465.5	30.4		U5	

BUG Rating: B2-U5-G3

Type V Short





REPORT NUMBER: P856412
 CATALOG NUMBER: FFX-CLB-50-750-U-VM9

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	80.4	80.4	80.4	80.4	80.4	80.4	80.4	80.4	80.4	80.4	80.4
2.5°	83.5	83.5	83.0	83.0	82.4	81.9	81.9	81.4	80.9	80.9	80.9
5°	92.9	92.4	92.4	92.4	92.4	91.8	92.4	91.8	91.8	91.8	92.4
7.5°	113.2	112.7	112.7	112.7	113.2	113.2	113.7	114.3	114.8	114.8	114.8
10°	139.8	139.3	139.3	138.8	139.8	139.8	140.4	139.3	140.9	140.9	141.4
12.5°	171.1	170.6	170.6	170.1	171.1	170.6	171.7	170.6	173.2	172.2	172.2
15°	205.1	205.1	204.5	204.0	205.6	205.6	206.6	206.6	208.2	207.1	207.7
17.5°	241.1	240.5	240.5	240.0	241.6	241.6	241.6	242.6	244.7	242.6	244.2
20°	279.7	279.2	279.2	278.6	280.2	280.2	281.2	281.8	283.8	282.3	283.3
22.5°	321.4	320.9	320.9	320.9	323.0	323.5	323.5	325.1	327.7	325.1	327.2
25°	367.9	367.3	367.3	368.9	370.5	371.0	372.0	374.1	376.7	374.1	376.7
27.5°	417.4	416.9	417.9	420.0	421.6	422.6	424.2	424.7	428.4	425.8	429.4
30°	468.6	468.0	469.1	471.7	473.8	476.9	476.9	478.5	483.7	480.0	483.7
32.5°	519.2	518.6	520.2	523.3	526.5	529.6	530.1	532.2	537.4	534.8	538.5
35°	569.3	568.7	570.8	575.0	578.1	581.3	582.3	584.4	590.1	587.5	591.2
37.5°	616.7	616.7	618.8	623.5	627.2	631.3	630.8	633.4	638.7	637.1	640.7
40°	661.1	661.1	663.7	669.4	673.6	676.2	675.7	678.3	684.0	683.5	686.7
42.5°	701.3	701.3	704.9	710.7	714.8	716.4	716.4	719.0	725.3	724.7	727.9
45°	735.2	736.7	740.9	747.2	750.8	752.4	751.4	754.0	760.7	760.7	763.4
47.5°	766.5	768.6	772.8	779.0	781.6	783.2	782.1	784.2	791.0	792.1	794.7
50°	793.6	795.2	800.4	807.2	809.8	809.8	808.2	810.3	817.6	819.7	821.8
52.5°	817.1	818.7	824.4	831.7	833.3	832.8	830.7	832.8	840.1	842.1	843.7
55°	835.9	837.5	844.2	851.5	853.1	851.5	848.4	851.0	857.8	860.9	863.5
57.5°	851.0	852.6	860.4	867.7	869.3	866.1	862.5	865.1	872.9	876.6	877.6
60°	863.5	865.1	873.5	881.3	882.3	878.7	874.5	877.1	884.9	889.1	890.1
62.5°	873.5	875.0	883.9	892.8	893.3	888.6	883.9	886.5	894.3	899.0	900.6
65°	880.2	881.8	891.7	900.6	901.6	895.9	891.2	893.8	901.1	906.8	907.9
67.5°	884.9	886.5	897.5	906.8	907.4	901.1	895.9	898.0	906.3	912.1	913.1
70°	887.0	888.6	900.1	910.0	910.5	903.7	897.5	900.1	908.4	915.2	916.2
72.5°	887.5	889.6	901.6	911.5	912.1	904.2	898.0	900.1	908.9	916.8	917.3
75°	885.5	888.1	900.6	911.0	911.0	902.2	895.4	897.5	907.4	915.7	917.3
77.5°	882.8	884.4	897.5	907.9	907.4	898.0	890.1	893.3	903.2	912.6	913.6
80°	877.1	879.2	892.2	902.2	901.1	890.7	883.4	886.5	896.9	906.8	907.9
82.5°	869.8	871.9	884.9	893.8	892.8	881.8	874.5	878.1	889.1	899.5	900.6
85°	860.9	863.0	875.5	883.9	882.3	871.4	864.1	867.2	879.2	889.6	890.7
87.5°	849.5	851.5	864.1	871.4	869.8	858.3	852.1	856.2	867.2	878.1	878.7
90°	836.4	839.0	850.0	856.8	854.7	844.2	838.5	842.7	853.6	864.1	865.1
92.5°	823.4	824.4	834.8	840.6	839.0	829.6	824.4	829.1	839.0	849.5	849.5
95°	807.7	809.3	818.7	823.4	821.8	814.0	809.3	814.5	823.4	833.3	833.8
97.5°	791.0	792.6	800.4	805.1	803.5	796.8	793.6	798.8	806.7	816.1	816.6
100°	773.3	774.3	781.1	785.3	783.7	778.5	776.4	781.6	788.9	797.8	797.8
102.5°	753.4	754.5	759.7	762.3	761.8	757.6	757.6	763.4	769.1	777.4	778.5
105°	732.6	733.6	737.3	738.8	738.3	736.7	737.8	743.5	748.2	755.5	756.6
107.5°	709.1	710.1	712.2	712.7	712.7	712.7	716.4	721.6	726.8	732.1	732.6
110°	684.0	684.6	686.1	685.6	685.6	686.7	691.9	697.6	701.8	707.0	707.5



REPORT NUMBER: P856412
 CATALOG NUMBER: FFX-CLB-50-750-U-VM9

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
112.5°	656.9	657.4	658.5	656.4	656.9	659.0	665.8	672.0	674.7	679.9	679.9
115°	628.2	627.7	628.7	626.1	625.6	629.3	636.6	643.9	646.0	649.6	650.1
117.5°	596.9	597.4	596.9	593.8	593.3	598.5	605.3	612.0	614.7	618.8	617.8
120°	564.6	564.0	564.6	560.9	560.4	566.1	572.9	579.7	581.3	584.9	583.9
122.5°	531.7	531.2	530.6	527.0	527.0	531.7	540.0	546.8	545.8	550.0	549.4
125°	497.8	497.8	496.7	493.1	493.1	498.8	505.6	511.9	510.8	515.5	513.9
127.5°	464.4	464.4	463.3	460.2	460.2	465.4	471.7	477.9	476.4	480.6	479.0
130°	431.5	431.5	430.5	427.3	427.3	431.5	438.3	443.5	441.4	445.1	444.6
132.5°	400.2	399.7	399.2	396.0	396.5	400.7	405.9	410.6	408.6	412.7	411.2
135°	369.9	369.4	368.9	365.8	366.3	370.5	375.2	378.8	377.2	379.9	379.3
137.5°	341.2	340.7	340.2	337.6	338.1	341.2	345.9	349.1	347.0	350.6	349.1
140°	314.1	313.6	312.5	311.0	311.5	314.6	317.2	320.9	318.8	321.9	320.4
142.5°	288.0	288.0	287.0	285.4	285.9	289.1	291.2	293.8	291.7	294.3	293.2
145°	264.0	264.0	263.0	261.9	261.9	264.5	266.1	268.7	266.6	269.2	268.2
147.5°	242.1	242.1	241.1	240.0	240.0	242.6	243.7	245.8	243.7	245.8	244.7
150°	221.8	221.8	221.2	220.2	220.7	221.8	222.8	224.4	222.8	224.4	223.8
152.5°	204.0	204.0	203.5	203.0	202.4	204.0	204.5	206.1	204.5	206.1	205.1
155°	188.4	187.8	187.8	186.8	186.8	187.8	188.4	189.4	187.8	189.4	188.9
157.5°	174.3	174.3	173.8	173.2	173.2	173.8	174.3	174.8	173.8	175.3	174.3
160°	162.3	162.3	161.8	161.2	161.2	161.8	161.8	162.3	161.2	162.3	161.8
162.5°	151.8	151.8	151.3	151.3	150.8	151.3	151.8	151.8	151.3	151.8	151.3
165°	143.5	143.5	143.0	142.4	142.4	143.0	143.0	143.5	142.4	143.0	143.0
167.5°	135.7	135.7	135.7	135.1	134.6	135.1	135.1	135.1	134.6	135.1	135.1
170°	129.9	129.9	129.9	129.4	128.9	129.4	129.4	129.4	128.9	129.4	129.4
172.5°	125.2	125.2	125.2	124.7	124.7	124.7	124.7	124.7	124.7	124.7	124.7
175°	122.1	122.1	122.1	122.1	121.6	122.1	122.1	122.1	122.1	122.1	121.6
177.5°	120.5	120.0	120.0	120.0	120.0	120.0	120.0	120.0	120.0	120.0	120.0
180°	119.5	119.5	119.5	119.5	119.5	119.5	119.5	119.5	119.5	119.5	119.5

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2406-133-5

Test Date: 07/12/2024

Luminaire Tested: FFX-CLB-100-750-U-FR-T5

Data in this report applies to families of products including FFX-CLB-100-750-U-FR-T5.

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2406-133-5
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 07/12/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Streetworks
 Catalog Number: **FFX-CLB-100-750-U-FR-T5**
 Description: FAIRFAX ACORN W/ FAIRFAX REFRACTOR 100W T5

Spectral Parameters

CCT (K): 4950
 CIE u': 0.2102
 CIE v': 0.4882
 Duv: 0.0025
 CIE x: 0.3471
 CIE y: 0.3583
 CIE z: 0.2946
 Peak Wavelength (nm): 452
 Dominant Wavelength (nm): 571
 Purity: 11.64963
 Rf: 74.8
 Rg: 92.4

CRI (Ra): 73.0

R1: 69.1	R9: -35.4
R2: 80.1	R10: 51.9
R3: 87.3	R11: 66.1
R4: 70.6	R12: 40.1
R5: 69.4	R13: 71.5
R6: 71.2	R14: 93.0
R7: 82.5	R15: 62.2
R8: 53.6	



Test Conditions


Stabilization Time: 0.803355M
 Operation Time: 1H
 Sphere Temperature (°C): 24.7

REPORT NUMBER: SP1-2406-133-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2406-133-5

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2406-133-5

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	148	NR	620	403	NR	750	11	NR	880	0	NR
365	0	NR	495	178	NR	625	366	NR	755	9	NR	885	0	NR
370	0	NR	500	226	NR	630	331	NR	760	8	NR	890	0	NR
375	0	NR	505	283	NR	635	295	NR	765	7	NR	895	0	NR
380	0	NR	510	338	NR	640	263	NR	770	6	NR	900	0	NR
385	0	NR	515	387	NR	645	232	NR	775	5	NR	905	0	NR
390	0	NR	520	428	NR	650	205	NR	780	5	NR	910	0	NR
395	1	NR	525	457	NR	655	179	NR	785	4	NR	915	0	NR
400	4	NR	530	484	NR	660	156	NR	790	3	NR	920	0	NR
405	7	NR	535	503	NR	665	136	NR	795	3	NR	925	0	NR
410	13	NR	540	520	NR	670	118	NR	800	3	NR	930	0	NR
415	25	NR	545	538	NR	675	102	NR	805	2	NR	935	0	NR
420	48	NR	550	555	NR	680	89	NR	810	2	NR	940	0	NR
425	87	NR	555	573	NR	685	76	NR	815	2	NR	945	0	NR
430	147	NR	560	590	NR	690	66	NR	820	2	NR	950	0	NR
435	242	NR	565	603	NR	695	56	NR	825	1	NR	955	0	NR
440	384	NR	570	614	NR	700	49	NR	830	1	NR	960	0	NR
445	638	NR	575	621	NR	705	42	NR	835	1	NR	965	0	NR
450	960	NR	580	619	NR	710	36	NR	840	1	NR	970	0	NR
455	902	NR	585	611	NR	715	31	NR	845	1	NR	975	0	NR
460	564	NR	590	594	NR	720	27	NR	850	1	NR	980	0	NR
465	402	NR	595	572	NR	725	23	NR	855	1	NR	985	0	NR
470	293	NR	600	546	NR	730	20	NR	860	1	NR	990	0	NR
475	194	NR	605	511	NR	735	17	NR	865	0	NR	995	0	NR
480	150	NR	610	478	NR	740	14	NR	870	0	NR	1000	0	NR
485	141	NR	615	440	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2406-133-5

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.8

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	148	NR	620	403	NR	750	11	NR	880	0	NR
365	0	NR	495	178	NR	625	366	NR	755	9	NR	885	0	NR
370	0	NR	500	226	NR	630	331	NR	760	8	NR	890	0	NR
375	0	NR	505	283	NR	635	295	NR	765	7	NR	895	0	NR
380	0	NR	510	338	NR	640	263	NR	770	6	NR	900	0	NR
385	0	NR	515	387	NR	645	232	NR	775	5	NR	905	0	NR
390	0	NR	520	428	NR	650	205	NR	780	5	NR	910	0	NR
395	1	NR	525	457	NR	655	179	NR	785	4	NR	915	0	NR
400	4	NR	530	484	NR	660	156	NR	790	3	NR	920	0	NR
405	7	NR	535	503	NR	665	136	NR	795	3	NR	925	0	NR
410	13	NR	540	520	NR	670	118	NR	800	3	NR	930	0	NR
415	25	NR	545	538	NR	675	102	NR	805	2	NR	935	0	NR
420	48	NR	550	555	NR	680	89	NR	810	2	NR	940	0	NR
425	87	NR	555	573	NR	685	76	NR	815	2	NR	945	0	NR
430	147	NR	560	590	NR	690	66	NR	820	2	NR	950	0	NR
435	242	NR	565	603	NR	695	56	NR	825	1	NR	955	0	NR
440	384	NR	570	614	NR	700	49	NR	830	1	NR	960	0	NR
445	638	NR	575	621	NR	705	42	NR	835	1	NR	965	0	NR
450	960	NR	580	619	NR	710	36	NR	840	1	NR	970	0	NR
455	902	NR	585	611	NR	715	31	NR	845	1	NR	975	0	NR
460	564	NR	590	594	NR	720	27	NR	850	1	NR	980	0	NR
465	402	NR	595	572	NR	725	23	NR	855	1	NR	985	0	NR
470	293	NR	600	546	NR	730	20	NR	860	1	NR	990	0	NR
475	194	NR	605	511	NR	735	17	NR	865	0	NR	995	0	NR
480	150	NR	610	478	NR	740	14	NR	870	0	NR	1000	0	NR
485	141	NR	615	440	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2406-133-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.74

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	148	NR	620	403	NR	750	11	NR	880	0	NR
365	0	NR	495	178	NR	625	366	NR	755	9	NR	885	0	NR
370	0	NR	500	226	NR	630	331	NR	760	8	NR	890	0	NR
375	0	NR	505	283	NR	635	295	NR	765	7	NR	895	0	NR
380	0	NR	510	338	NR	640	263	NR	770	6	NR	900	0	NR
385	0	NR	515	387	NR	645	232	NR	775	5	NR	905	0	NR
390	0	NR	520	428	NR	650	205	NR	780	5	NR	910	0	NR
395	1	NR	525	457	NR	655	179	NR	785	4	NR	915	0	NR
400	4	NR	530	484	NR	660	156	NR	790	3	NR	920	0	NR
405	7	NR	535	503	NR	665	136	NR	795	3	NR	925	0	NR
410	13	NR	540	520	NR	670	118	NR	800	3	NR	930	0	NR
415	25	NR	545	538	NR	675	102	NR	805	2	NR	935	0	NR
420	48	NR	550	555	NR	680	89	NR	810	2	NR	940	0	NR
425	87	NR	555	573	NR	685	76	NR	815	2	NR	945	0	NR
430	147	NR	560	590	NR	690	66	NR	820	2	NR	950	0	NR
435	242	NR	565	603	NR	695	56	NR	825	1	NR	955	0	NR
440	384	NR	570	614	NR	700	49	NR	830	1	NR	960	0	NR
445	638	NR	575	621	NR	705	42	NR	835	1	NR	965	0	NR
450	960	NR	580	619	NR	710	36	NR	840	1	NR	970	0	NR
455	902	NR	585	611	NR	715	31	NR	845	1	NR	975	0	NR
460	564	NR	590	594	NR	720	27	NR	850	1	NR	980	0	NR
465	402	NR	595	572	NR	725	23	NR	855	1	NR	985	0	NR
470	293	NR	600	546	NR	730	20	NR	860	1	NR	990	0	NR
475	194	NR	605	511	NR	735	17	NR	865	0	NR	995	0	NR
480	150	NR	610	478	NR	740	14	NR	870	0	NR	1000	0	NR
485	141	NR	615	440	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2406-133-5


TM-30-18

Summary

$R_f = 74.8$
 $R_g = 92.4$
 CIE $R_a = 73.0$
 $R_9 = -35.4$



Color Vector Graphics



REPORT NUMBER: SP1-2406-133-5

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 85	CES26 = 65	CES51 = 89	CES76 = 54
CES02 = 60	CES27 = 90	CES52 = 88	CES77 = 69
CES03 = 30	CES28 = 82	CES53 = 80	CES78 = 57
CES04 = 69	CES29 = 72	CES54 = 84	CES79 = 82
CES05 = 46	CES30 = 91	CES55 = 82	CES80 = 79
CES06 = 50	CES31 = 75	CES56 = 74	CES81 = 79
CES07 = 39	CES32 = 66	CES57 = 74	CES82 = 91
CES08 = 38	CES33 = 85	CES58 = 74	CES83 = 91
CES09 = 29	CES34 = 72	CES59 = 85	CES84 = 85
CES10 = 73	CES35 = 84	CES60 = 87	CES85 = 77
CES11 = 56	CES36 = 86	CES61 = 81	CES86 = 74
CES12 = 62	CES37 = 80	CES62 = 80	CES87 = 77
CES13 = 41	CES38 = 98	CES63 = 74	CES88 = 81
CES14 = 74	CES39 = 97	CES64 = 63	CES89 = 72
CES15 = 70	CES40 = 93	CES65 = 62	CES90 = 81
CES16 = 46	CES41 = 98	CES66 = 56	CES91 = 71
CES17 = 49	CES42 = 83	CES67 = 54	CES92 = 57
CES18 = 55	CES43 = 81	CES68 = 64	CES93 = 74
CES19 = 71	CES44 = 99	CES69 = 72	CES94 = 53
CES20 = 64	CES45 = 88	CES70 = 57	CES95 = 64
CES21 = 85	CES46 = 86	CES71 = 49	CES96 = 76
CES22 = 77	CES47 = 91	CES72 = 83	CES97 = 86
CES23 = 91	CES48 = 80	CES73 = 48	CES98 = 77
CES24 = 90	CES49 = 84	CES74 = 90	CES99 = 62
CES25 = 71	CES50 = 89	CES75 = 52	



REPORT NUMBER: SP1-2406-133-5

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-2406-133-5

TM-30-18

Measure Comparisons



(END OF REPORT)