

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P253880

Luminaire Tested: **LXF.LXT-AF24-40-D-U-T4W**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P253880
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1806-803-12-90°)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: LXF.LXT-AF24-40-D-U-T4W
Description: DECORATIVE POST TOP LUMINAIRE
(1) 70 CRI, 4000K, 500mA LIGHT ENGINE WITH 24 LEDS AND TYPE IV WIDE OPTICS
PHOTOMETRIC DATA REPORTED FOR LOWER HEMISPHERE ONLY. MINIMAL LIGHT IN
UPPER HEMISPHERE NOT REPORTED TO PROVIDE RELEVANT COMPARISON TO
COMPETITIVE OFFERINGS.
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4471.3 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Luminous Opening: Rectangular (W 1.17' x L: 1.17' x H: 0')
IES Classification: Type IV - Medium - Non-Cutoff
BUG Rating: B1 - U0 - G2


Input Watts (W): 40
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P253880
 CATALOG NUMBER: LXF.LXT-AF24-40-D-U-T4W

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 5.6 fc
 Type IV - Medium - Non-Cutoff

REPORT NUMBER: P253880
CATALOG NUMBER: LXF.LXT-AF24-40-D-U-T4W

Luminous Intensity Polar Plot



— Vertical Plane Through 49-Deg Lateral - - - Horizontal Cone Through 75-Deg Vertical

REPORT NUMBER: P253880

CATALOG NUMBER: LXF.LXT-AF24-40-D-U-T4W


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 923.4 | 0.0 | 923.4 |
| | % Fixture | 20.7 | 0.0 | 20.7 |
| Street Side | Lumens | 3547.9 | 0.0 | 3547.9 |
| | % Fixture | 79.3 | 0.0 | 79.3 |
| Total | Lumens | 4471.3 | 0.0 | 4471.3 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 2.9 | 0.1 |
| 10°-20° | 45.8 | 1.0 |
| 20°-30° | 168.7 | 3.8 |
| 30°-40° | 349.6 | 7.8 |
| 40°-50° | 560.5 | 12.5 |
| 50°-60° | 893.1 | 20.0 |
| 60°-70° | 1279.0 | 28.6 |
| 70°-80° | 1031.6 | 23.1 |
| 80°-90° | 140.1 | 3.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 4471.3 | 100.0 |
| 0°-180° | 4471.3 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P253880


CATALOG NUMBER: LXF.LXT-AF24-40-D-U-T4W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 122.0 | 2.7 | | | |
| FM (30°-60°) | 1341.4 | 30.0 | | | |
| FH (60°-80°) | 1981.6 | 44.3 | | | G2/5000 |
| FVH (80°-90°) | 103.0 | 2.3 | | | G2/225 |
| BL (0°-30°) | 95.5 | 2.1 | B0/110 | | |
| BM (30°-60°) | 461.8 | 10.3 | B1/1000 | | |
| BH (60°-80°) | 329.0 | 7.4 | B1/500 | | G1/500 |
| BVH (80°-90°) | 37.2 | 0.8 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2

Type IV Medium





REPORT NUMBER: P253880

CATALOG NUMBER: LXF.LXT-AF24-40-D-U-T4W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 49° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 2.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.5 | 0.5 | 0.5 | 0.5 | 0.5 | 1.0 | 0.5 |
| 5° | 80.5 | 64.7 | 46.6 | 23.1 | 19.0 | 11.8 | 6.1 | 2.0 | 1.0 | 1.0 | 1.0 |
| 7.5° | 97.0 | 96.0 | 94.4 | 93.4 | 88.8 | 81.0 | 50.2 | 18.0 | 4.1 | 1.5 | 1.0 |
| 10° | 110.3 | 107.2 | 104.1 | 102.1 | 97.5 | 91.9 | 89.8 | 84.1 | 16.4 | 3.6 | 3.1 |
| 12.5° | 211.9 | 210.3 | 203.2 | 130.3 | 110.8 | 100.6 | 99.0 | 95.4 | 71.8 | 24.7 | 26.2 |
| 15° | 229.9 | 229.3 | 223.2 | 215.9 | 202.6 | 119.6 | 115.9 | 121.1 | 188.8 | 134.4 | 140.6 |
| 17.5° | 263.2 | 261.7 | 245.2 | 228.3 | 219.0 | 238.0 | 246.7 | 224.7 | 208.3 | 155.5 | 157.0 |
| 20° | 359.7 | 360.2 | 350.9 | 282.1 | 238.0 | 301.7 | 299.6 | 265.3 | 227.8 | 300.1 | 280.1 |
| 22.5° | 370.4 | 369.4 | 363.2 | 348.8 | 383.7 | 315.0 | 314.5 | 303.7 | 332.5 | 345.8 | 317.0 |
| 25° | 481.7 | 480.7 | 407.3 | 363.8 | 404.8 | 356.5 | 391.4 | 403.2 | 364.8 | 373.0 | 357.0 |
| 27.5° | 496.1 | 495.1 | 488.4 | 470.5 | 420.1 | 462.8 | 456.5 | 425.2 | 457.6 | 495.6 | 489.9 |
| 30° | 620.7 | 586.9 | 516.1 | 505.3 | 483.2 | 481.7 | 484.3 | 497.7 | 532.0 | 509.4 | 532.5 |
| 32.5° | 682.3 | 676.7 | 654.6 | 575.6 | 535.1 | 511.5 | 548.9 | 563.3 | 547.9 | 646.4 | 685.9 |
| 35° | 897.2 | 864.4 | 742.4 | 643.8 | 577.7 | 588.9 | 584.3 | 579.2 | 661.7 | 676.2 | 735.7 |
| 37.5° | 1107.1 | 1090.7 | 994.7 | 768.0 | 635.2 | 611.0 | 610.0 | 657.7 | 687.9 | 731.0 | 784.4 |
| 40° | 1246.7 | 1245.1 | 1178.4 | 938.4 | 719.7 | 657.7 | 686.4 | 687.9 | 724.4 | 772.1 | 843.4 |
| 42.5° | 1377.4 | 1370.2 | 1332.3 | 1081.5 | 858.3 | 733.7 | 735.7 | 736.2 | 757.2 | 819.3 | 920.9 |
| 45° | 1448.3 | 1448.8 | 1462.6 | 1203.5 | 984.0 | 822.4 | 810.1 | 801.4 | 820.8 | 889.6 | 1035.7 |
| 47.5° | 1531.4 | 1531.9 | 1542.6 | 1316.9 | 1100.4 | 931.1 | 907.6 | 880.9 | 896.7 | 993.7 | 1188.7 |
| 50° | 1622.7 | 1630.9 | 1626.3 | 1431.8 | 1222.5 | 1056.8 | 1020.9 | 990.1 | 1013.2 | 1144.1 | 1383.6 |
| 52.5° | 1754.0 | 1741.2 | 1712.9 | 1548.2 | 1369.2 | 1187.1 | 1146.1 | 1109.2 | 1170.7 | 1312.9 | 1602.1 |
| 55° | 1840.7 | 1843.8 | 1822.2 | 1698.1 | 1501.6 | 1316.4 | 1267.1 | 1230.2 | 1351.3 | 1494.9 | 1860.7 |
| 57.5° | 1923.8 | 1929.0 | 1948.9 | 1896.7 | 1698.1 | 1442.6 | 1388.8 | 1372.8 | 1557.5 | 1716.5 | 2155.7 |
| 60° | 1988.9 | 1993.6 | 2053.6 | 2047.4 | 1865.4 | 1588.3 | 1541.6 | 1556.0 | 1760.2 | 1931.5 | 2441.5 |
| 62.5° | 1992.5 | 2010.0 | 2131.6 | 2187.5 | 2032.1 | 1762.7 | 1729.9 | 1766.3 | 1968.0 | 2149.0 | 2689.2 |
| 65° | 1810.4 | 1842.2 | 2138.3 | 2241.4 | 2215.2 | 1978.2 | 1952.0 | 1989.9 | 2190.5 | 2334.8 | 2825.2 |
| 67.5° | 1684.2 | 1707.3 | 1999.3 | 2269.6 | 2380.9 | 2247.5 | 2218.8 | 2220.3 | 2379.9 | 2430.6 | 2826.2 |
| 70° | 1578.5 | 1598.6 | 1858.2 | 2285.0 | 2563.5 | 2601.0 | 2558.9 | 2461.4 | 2517.9 | 2482.5 | 2584.6 |
| 72.5° | 1315.4 | 1313.4 | 1550.4 | 2060.2 | 2648.7 | 3023.2 | 2997.6 | 2761.6 | 2589.7 | 2377.8 | 2031.1 |
| 75° | 725.9 | 700.8 | 907.6 | 1416.5 | 2289.6 | 3148.8 | 3179.1 | 2890.3 | 2432.2 | 2004.9 | 1273.3 |
| 77.5° | 221.7 | 208.3 | 300.1 | 601.8 | 1367.2 | 2664.6 | 2777.0 | 2473.3 | 1839.7 | 1263.5 | 617.1 |
| 80° | 101.6 | 102.1 | 136.0 | 215.9 | 556.6 | 1574.4 | 1730.9 | 1462.6 | 981.9 | 586.4 | 259.1 |
| 82.5° | 52.9 | 53.9 | 84.6 | 122.7 | 266.3 | 618.7 | 738.8 | 568.5 | 417.6 | 272.9 | 120.6 |
| 85° | 26.2 | 26.2 | 43.1 | 66.2 | 149.8 | 170.8 | 218.5 | 199.6 | 193.4 | 137.0 | 46.1 |
| 87.5° | 4.6 | 4.6 | 10.2 | 17.5 | 27.7 | 16.9 | 16.4 | 29.8 | 62.6 | 32.8 | 5.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P253880

CATALOG NUMBER: LXF.LXT-AF24-40-D-U-T4W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 2.5° | 0.5 | 0.5 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 5° | 0.5 | 0.5 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.5 | 1.0 | 1.0 | 2.0 |
| 7.5° | 1.0 | 0.5 | 0.5 | 0.5 | 1.0 | 2.6 | 22.1 | 68.2 | 71.8 | 73.3 | 76.4 |
| 10° | 2.6 | 2.6 | 2.0 | 2.6 | 12.3 | 71.3 | 87.8 | 93.9 | 96.0 | 97.0 | 97.5 |
| 12.5° | 35.4 | 30.8 | 22.6 | 11.3 | 66.7 | 93.4 | 96.0 | 100.0 | 104.1 | 106.7 | 118.5 |
| 15° | 140.0 | 139.0 | 131.3 | 141.6 | 99.0 | 101.6 | 105.7 | 166.7 | 178.0 | 189.3 | 191.9 |
| 17.5° | 155.0 | 153.4 | 151.3 | 185.2 | 195.5 | 168.3 | 170.8 | 189.3 | 192.9 | 197.0 | 198.0 |
| 20° | 285.7 | 282.6 | 254.9 | 206.2 | 202.1 | 250.8 | 194.0 | 195.0 | 240.1 | 265.3 | 269.9 |
| 22.5° | 315.0 | 311.9 | 289.3 | 300.6 | 243.7 | 260.6 | 251.9 | 260.6 | 285.2 | 292.0 | 294.0 |
| 25° | 364.3 | 357.0 | 323.2 | 308.8 | 317.5 | 269.9 | 310.9 | 282.6 | 292.5 | 302.7 | 313.9 |
| 27.5° | 496.1 | 491.9 | 444.8 | 359.7 | 317.5 | 335.5 | 312.9 | 322.1 | 360.2 | 377.1 | 379.6 |
| 30° | 533.6 | 527.8 | 460.2 | 389.8 | 335.0 | 327.3 | 320.6 | 367.3 | 365.3 | 377.1 | 380.1 |
| 32.5° | 712.6 | 701.8 | 582.8 | 387.3 | 339.1 | 311.4 | 341.7 | 355.0 | 402.7 | 435.1 | 440.2 |
| 35° | 753.1 | 741.3 | 588.4 | 435.6 | 319.1 | 318.0 | 315.5 | 360.7 | 392.0 | 411.9 | 417.6 |
| 37.5° | 803.4 | 784.9 | 584.3 | 410.4 | 325.8 | 295.5 | 301.2 | 326.3 | 381.7 | 418.6 | 425.9 |
| 40° | 870.1 | 837.3 | 584.3 | 379.1 | 300.1 | 276.5 | 275.5 | 308.8 | 333.0 | 352.9 | 358.1 |
| 42.5° | 959.8 | 909.1 | 585.3 | 350.4 | 277.5 | 257.1 | 256.6 | 271.9 | 285.7 | 286.7 | 290.9 |
| 45° | 1076.9 | 993.2 | 595.6 | 325.8 | 257.6 | 236.5 | 232.9 | 243.2 | 251.9 | 242.1 | 241.6 |
| 47.5° | 1221.5 | 1098.3 | 599.8 | 305.8 | 237.5 | 220.0 | 217.5 | 223.2 | 226.3 | 213.9 | 213.4 |
| 50° | 1396.4 | 1228.2 | 609.5 | 283.2 | 220.0 | 208.3 | 204.7 | 206.7 | 205.7 | 195.0 | 195.0 |
| 52.5° | 1608.8 | 1386.7 | 613.1 | 258.6 | 205.2 | 197.5 | 193.4 | 192.4 | 190.9 | 184.1 | 184.1 |
| 55° | 1857.2 | 1575.4 | 623.3 | 237.5 | 191.9 | 185.7 | 184.1 | 183.6 | 184.1 | 181.6 | 181.6 |
| 57.5° | 2115.7 | 1770.4 | 612.5 | 218.5 | 178.5 | 174.9 | 178.0 | 181.6 | 187.2 | 191.4 | 192.9 |
| 60° | 2341.4 | 1939.7 | 534.6 | 201.6 | 166.7 | 167.3 | 181.6 | 194.5 | 204.2 | 214.4 | 218.5 |
| 62.5° | 2510.2 | 2036.7 | 424.7 | 186.7 | 158.6 | 167.3 | 199.6 | 219.0 | 221.7 | 223.7 | 223.7 |
| 65° | 2554.3 | 2029.5 | 313.9 | 176.5 | 154.0 | 180.0 | 219.0 | 225.3 | 211.9 | 205.2 | 203.7 |
| 67.5° | 2467.6 | 1904.8 | 243.7 | 168.3 | 150.8 | 190.4 | 226.8 | 214.4 | 200.6 | 196.5 | 192.9 |
| 70° | 2183.4 | 1618.1 | 205.2 | 160.1 | 147.7 | 183.1 | 222.7 | 204.7 | 191.4 | 187.2 | 181.6 |
| 72.5° | 1621.7 | 1146.6 | 180.0 | 150.8 | 139.5 | 169.8 | 211.9 | 195.5 | 182.6 | 175.9 | 170.3 |
| 75° | 914.7 | 605.9 | 161.1 | 141.6 | 123.7 | 154.5 | 196.5 | 183.6 | 171.3 | 161.6 | 158.0 |
| 77.5° | 404.8 | 256.0 | 143.1 | 127.3 | 110.3 | 141.1 | 180.6 | 168.3 | 156.5 | 145.7 | 142.6 |
| 80° | 188.3 | 147.2 | 122.7 | 110.3 | 99.0 | 130.8 | 166.2 | 150.3 | 139.0 | 131.9 | 126.2 |
| 82.5° | 103.6 | 90.3 | 91.9 | 88.3 | 85.7 | 115.9 | 150.3 | 131.3 | 118.5 | 117.4 | 96.5 |
| 85° | 38.0 | 40.5 | 53.9 | 52.4 | 56.5 | 88.8 | 124.2 | 97.0 | 85.2 | 71.8 | 69.3 |
| 87.5° | 1.0 | 2.6 | 5.1 | 8.7 | 14.3 | 27.7 | 44.6 | 41.5 | 32.8 | 21.6 | 23.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

(END OF REPORT)