

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P148493

Luminaire Tested: **TMU-F02-LED-E-U-5XQ-8030**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P148493  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33676)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: TMU-F02-LED-E-U-5XQ-8030  
Description: TALON MEDIUM LED AREA LUMINAIRE  
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE EXTRA WIDE  
Light Source: (14) 3000K CCT, 80 CRI LEDs  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4431.8 lumens  
Efficiency: N/A  
Efficacy: 80.6 lumens/watt  
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')  
IES Classification: Type V - Short - Non-Cutoff  
BUG Rating: B3 - U0 - G2


Input Watts (W): 55  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P148493  
 CATALOG NUMBER: TMU-F02-LED-E-U-5XQ-8030

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 4.2 fc  
 Type V - Short - Non-Cutoff

REPORT NUMBER: P148493  
CATALOG NUMBER: TMU-F02-LED-E-U-5XQ-8030

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 72.5-Deg Vertical

REPORT NUMBER: P148493

CATALOG NUMBER: TMU-F02-LED-E-U-5XQ-8030

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	2215.9	0.0	2215.9
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	2215.9	0.0	2215.9
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	4431.8	0.0	4431.8
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	40.0	0.9
10°-20°	118.4	2.7
20°-30°	198.2	4.5
30°-40°	302.2	6.8
40°-50°	482.5	10.9
50°-60°	741.9	16.7
60°-70°	1080.3	24.4
70°-80°	1216.9	27.5
80°-90°	251.2	5.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4431.8	100.0
0°-180°	4431.8	100.0



REPORT NUMBER: P148493


CATALOG NUMBER: TMU-F02-LED-E-U-5XQ-8030

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	178.3	4.0			
FM (30°-60°)	763.3	17.2			
FH (60°-80°)	1148.6	25.9			G1/1800
FVH (80°-90°)	125.6	2.8			G2/225
BL (0°-30°)	178.3	4.0	B1/500		
BM (30°-60°)	763.3	17.2	B1/1000		
BH (60°-80°)	1148.6	25.9	B3/2500		G1/1800
BVH (80°-90°)	125.6	2.8			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G2**

Type V Short





REPORT NUMBER: P148493  
 CATALOG NUMBER: TMU-F02-LED-E-U-5XQ-8030

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	419.9	419.9	419.9	419.9	419.9	419.9	419.9	419.9	419.9	419.9	419.9
2.5°	420.6	420.8	420.7	420.5	420.6	420.5	420.2	420.2	419.4	419.8	420.5
5°	420.6	420.4	420.3	420.2	420.1	420.4	420.1	419.8	419.6	419.9	419.6
7.5°	420.4	419.9	419.6	419.6	419.7	419.8	419.4	419.0	419.3	419.0	418.5
10°	419.7	419.3	419.4	419.0	419.1	419.0	418.5	418.2	418.4	418.0	417.4
12.5°	419.9	419.3	419.2	419.0	418.9	418.8	418.2	417.6	417.7	417.4	416.9
15°	419.9	419.6	419.4	419.0	418.9	418.6	417.9	417.7	417.7	417.3	416.6
17.5°	420.1	419.9	419.9	419.3	419.1	419.0	418.2	417.8	418.2	417.4	417.0
20°	420.8	420.6	420.7	420.4	419.9	419.9	419.3	419.1	419.2	419.1	417.8
22.5°	422.2	422.2	422.4	422.4	422.2	422.4	421.9	421.9	422.0	422.0	421.0
25°	426.2	426.0	426.3	426.3	426.4	427.2	426.9	426.8	427.3	427.4	426.3
27.5°	433.6	433.4	433.6	433.8	434.4	435.5	435.2	435.6	436.5	436.3	435.3
30°	442.2	442.0	442.5	443.2	443.7	445.4	444.6	446.4	447.2	447.9	447.2
32.5°	454.8	454.8	455.8	456.2	457.3	458.9	459.2	460.5	461.6	462.8	462.0
35°	471.4	471.2	472.0	472.9	474.1	475.6	476.2	478.1	479.7	480.5	479.0
37.5°	497.0	495.8	497.2	497.7	498.8	499.1	500.7	503.0	504.8	504.6	503.5
40°	531.6	531.4	530.8	530.1	531.7	532.3	532.3	535.4	538.2	537.8	537.7
42.5°	572.0	571.0	570.3	570.3	571.2	571.4	575.0	577.3	579.4	579.8	579.3
45°	615.4	614.4	614.6	614.2	614.5	616.0	618.1	622.4	626.1	626.2	624.3
47.5°	662.2	658.9	661.4	657.8	660.0	661.2	666.4	672.7	679.2	680.4	678.6
50°	709.6	709.2	709.0	708.2	709.3	711.8	718.2	728.1	734.4	738.6	735.8
52.5°	761.3	759.6	758.8	757.6	758.6	763.6	772.6	781.2	792.4	797.2	793.3
55°	811.7	811.1	808.1	808.0	810.2	818.0	827.7	838.3	850.5	855.8	854.4
57.5°	863.4	860.1	859.2	857.8	862.2	869.5	881.5	900.5	913.2	919.2	915.7
60°	914.1	911.6	909.6	909.1	912.2	922.4	939.6	962.4	978.1	986.0	980.4
62.5°	968.4	966.8	964.5	961.8	968.2	981.4	1002.7	1028.0	1051.1	1060.9	1052.4
65°	1036.1	1032.7	1030.2	1026.8	1032.0	1048.5	1075.3	1111.0	1142.0	1153.3	1147.3
67.5°	1107.3	1104.2	1104.4	1102.4	1111.6	1134.5	1169.1	1217.5	1259.1	1278.5	1267.1
70°	1169.6	1171.3	1171.8	1180.3	1196.3	1231.2	1288.7	1364.6	1427.6	1457.2	1445.0
71°	1151.2	1155.1	1161.0	1169.8	1197.4	1238.7	1317.3	1409.2	1484.4	1534.6	1517.8
72.5°	1099.2	1101.6	1104.6	1118.0	1149.3	1203.8	1284.8	1389.8	1486.5	1551.4	1531.9
75°	1024.0	1026.2	1027.2	1036.6	1065.1	1112.7	1186.8	1279.9	1365.3	1420.5	1415.1
77.5°	910.4	910.7	918.9	933.4	965.3	1019.8	1097.8	1194.4	1274.7	1317.6	1290.4
80°	653.8	649.4	657.7	676.4	715.9	778.3	858.3	968.6	1057.6	1097.9	1055.6
82.5°	248.8	262.2	283.5	314.3	327.7	397.1	471.7	536.5	611.5	695.4	674.3
85°	26.7	30.0	37.7	46.8	59.1	81.8	113.0	154.2	190.1	223.4	198.3
87.5°	10.0	10.2	11.4	13.1	13.4	14.0	14.9	17.3	16.2	13.9	11.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P148493

CATALOG NUMBER: TMU-F02-LED-E-U-5XQ-8030

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	419.9	419.9	419.9	419.9	419.9	419.9	419.9	419.9
2.5°	419.9	420.0	419.9	420.0	420.0	419.6	419.7	419.4
5°	419.8	419.4	419.5	419.6	419.5	419.8	419.4	419.6
7.5°	419.2	418.5	418.7	418.7	418.5	418.9	418.6	418.5
10°	418.0	417.2	417.6	417.4	417.2	417.3	417.4	417.4
12.5°	417.0	416.4	416.6	416.4	416.3	416.6	416.5	416.6
15°	416.8	415.8	415.7	415.5	415.6	415.8	415.8	416.2
17.5°	416.6	415.4	415.2	415.0	415.2	415.6	415.7	415.4
20°	417.2	416.3	416.1	415.8	415.7	416.3	416.2	416.2
22.5°	420.5	419.3	419.2	418.3	417.9	418.3	418.1	418.0
25°	425.7	424.3	423.9	422.6	421.6	421.6	421.3	421.0
27.5°	435.2	433.0	432.6	431.5	430.2	430.4	429.8	429.6
30°	446.0	444.2	442.5	441.1	439.5	439.0	438.1	438.0
32.5°	460.3	458.2	456.2	454.4	452.3	451.5	450.1	449.4
35°	477.8	475.0	472.7	471.4	469.4	468.3	467.4	468.4
37.5°	502.3	499.0	497.8	496.3	494.9	493.3	493.6	493.3
40°	536.2	533.2	532.1	529.4	529.0	527.2	528.4	527.2
42.5°	578.2	572.6	571.8	569.7	569.0	568.0	568.4	567.6
45°	623.8	618.8	617.9	614.5	614.7	612.2	613.1	613.2
47.5°	675.1	669.9	665.6	663.2	662.2	660.7	661.6	661.4
50°	728.1	721.0	716.2	711.5	709.4	710.0	708.3	711.1
52.5°	785.0	774.4	767.7	763.1	759.2	760.0	760.2	761.0
55°	843.9	830.4	820.6	814.7	811.1	811.4	812.4	813.3
57.5°	903.1	886.2	873.0	864.2	861.8	862.9	862.9	862.8
60°	964.5	944.3	927.2	917.2	915.2	914.6	919.1	917.6
62.5°	1030.4	1006.2	988.5	975.8	972.8	974.8	979.0	978.0
65°	1117.9	1084.4	1061.6	1049.0	1043.8	1045.9	1051.4	1051.2
67.5°	1230.6	1183.8	1153.7	1137.4	1133.7	1136.2	1139.3	1142.2
70°	1399.3	1332.2	1289.3	1254.1	1239.0	1236.1	1239.1	1239.2
71°	1458.6	1381.6	1313.2	1270.2	1245.5	1235.1	1235.9	1230.7
72.5°	1456.2	1361.3	1281.3	1236.4	1202.0	1193.6	1189.6	1183.2
75°	1358.0	1272.6	1203.2	1154.1	1121.0	1111.2	1104.0	1103.6
77.5°	1231.6	1168.6	1092.0	1040.1	999.8	983.4	976.1	975.9
80°	990.0	895.6	839.7	808.4	759.8	745.7	730.9	725.3
82.5°	598.7	467.8	380.4	338.0	314.6	259.1	232.4	220.0
85°	139.5	99.1	68.3	44.8	32.2	25.7	19.7	17.4
87.5°	9.4	7.4	6.6	5.4	4.1	4.0	2.4	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)