

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P266012

Luminaire Tested: **LXF.LXT-AF24-20-D-U-T3-7027-HSS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P266012
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1806-803-11)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: LXF.LXT-AF24-20-D-U-T3-7027-HSS
Description: DECORATIVE POST TOP LUMINAIRE
(1) 70 CRI, 2700K, 260mA LIGHT ENGINE WITH 24 LEDS AND TYPE III OPTICS
WITH HOUSE SIDE SHIELD
PHOTOMETRIC DATA REPORTED FOR LOWER HEMISPHERE ONLY. MINIMAL LIGHT IN
UPPER HEMISPHERE NOT REPORTED TO PROVIDE RELEVANT COMPARISON TO
COMPETITIVE OFFERINGS.
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1614.5 lumens
Efficiency: N/A
Efficacy: 76.9 lumens/watt
Luminous Opening: Rectangular (W 1.17' x L: 1.17' x H: 0')
IES Classification: Type III - Medium - Semi-Cutoff
BUG Rating: B0 - U0 - G1

Input Watts (W): 21
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P266012

CATALOG NUMBER: LXF.LXT-AF24-20-D-U-T3-7027-HSS

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 2.6 fc
 Type III - Medium - Semi-Cutoff

REPORT NUMBER: P266012

CATALOG NUMBER: LXF.LXT-AF24-20-D-U-T3-7027-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 54-Deg Lateral - - - Horizontal Cone Through 72-Deg Vertical

REPORT NUMBER: P266012

CATALOG NUMBER: LXF.LXT-AF24-20-D-U-T3-7027-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	146.6	0.0	146.6
	% Fixture	9.1	0.0	9.1
Street Side	Lumens	1467.9	0.0	1467.9
	% Fixture	90.9	0.0	90.9
Total	Lumens	1614.5	0.0	1614.5
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.9	0.1
10°-20°	12.5	0.8
20°-30°	46.2	2.9
30°-40°	121.1	7.5
40°-50°	239.3	14.8
50°-60°	391.4	24.2
60°-70°	487.5	30.2
70°-80°	299.7	18.6
80°-90°	16.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	1614.5	100.0
0°-180°	1614.5	100.0



REPORT NUMBER: P266012


CATALOG NUMBER: LXF.LXT-AF24-20-D-U-T3-7027-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	40.3	2.5			
FM	(30°-60°)	670.4	41.5			
FH	(60°-80°)	741.5	45.9			G1/1800
FVH	(80°-90°)	15.7	1.0			G1/100
BL	(0°-30°)	19.3	1.2	B0/110		
BM	(30°-60°)	81.4	5.0	B0/220		
BH	(60°-80°)	45.6	2.8	B0/110		G0/110
BVH	(80°-90°)	0.3	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G1

Type III Medium





REPORT NUMBER: P266012

CATALOG NUMBER: LXF.LXT-AF24-20-D-U-T3-7027-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	54°	55°	65°	75°	85°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	22.3	25.0	12.9	8.7	5.7	1.2	0.0	0.0	0.0	0.0	0.0
7.5°	30.3	30.0	30.5	30.9	31.4	31.1	6.6	6.0	0.2	0.2	0.0
10°	29.3	29.3	29.3	29.7	30.5	31.4	31.6	31.6	4.3	0.2	0.2
12.5°	59.2	59.5	51.6	38.5	30.9	31.1	32.3	32.3	27.3	3.7	15.8
15°	59.2	59.0	58.7	60.4	61.2	33.1	37.4	38.4	67.6	46.7	54.3
17.5°	63.1	61.7	59.2	60.1	63.1	63.5	69.3	70.2	73.7	52.0	59.2
20°	88.8	89.2	89.2	69.8	66.5	93.1	86.1	83.0	79.6	98.8	110.2
22.5°	91.7	91.7	91.5	93.1	106.7	97.0	101.1	103.3	120.8	138.8	130.4
25°	131.2	127.3	105.2	99.1	119.7	107.6	144.1	144.7	135.6	148.6	142.1
27.5°	172.1	169.2	162.1	135.6	126.7	153.4	153.4	156.0	167.1	210.3	205.9
30°	214.8	209.6	196.8	189.6	161.3	164.4	171.7	174.5	221.7	218.4	229.3
32.5°	314.2	310.2	288.1	231.4	216.9	181.6	219.4	224.1	235.1	286.6	308.9
35°	371.3	366.5	344.7	310.6	256.2	241.4	239.9	242.4	298.0	326.4	333.5
37.5°	487.2	488.5	454.3	354.6	320.2	279.7	293.7	292.8	335.8	359.5	375.9
40°	541.5	539.3	508.7	435.8	365.3	328.2	339.6	333.7	368.1	409.8	414.9
42.5°	631.4	620.4	576.1	495.4	439.6	404.9	396.2	390.9	412.3	464.3	467.2
45°	726.1	717.1	671.9	576.3	512.3	472.1	461.9	454.1	455.3	506.7	523.5
47.5°	782.0	767.8	753.4	648.3	610.3	552.9	531.0	521.3	510.9	567.5	582.0
50°	839.6	823.3	813.5	721.5	712.1	640.2	601.7	592.1	580.6	634.1	645.5
52.5°	890.5	867.0	861.6	799.0	780.0	737.4	675.3	673.3	653.0	705.2	714.2
55°	892.1	879.3	888.3	855.5	837.9	804.3	751.3	762.0	735.0	774.5	786.9
57.5°	841.2	848.8	890.5	891.5	888.2	865.5	825.1	847.1	818.9	833.2	857.9
60°	806.9	817.8	871.5	913.5	934.3	923.1	905.1	925.8	900.3	899.5	933.3
62.5°	750.5	762.5	833.4	902.9	937.0	976.1	968.5	987.9	984.5	973.5	1014.5
65°	679.6	688.5	761.4	862.3	916.9	1005.4	1032.0	1045.4	1051.6	1033.0	1092.6
67.5°	606.4	609.3	676.5	768.3	877.0	1016.3	1098.4	1102.7	1109.5	1091.6	1125.9
70°	503.6	502.7	555.6	642.6	791.8	997.8	1180.4	1164.7	1163.6	1124.9	1106.3
72°	351.9	369.5	418.0	500.0	677.2	941.3	1213.3	1191.6	1177.1	1116.9	993.9
72.5°	294.4	317.5	375.0	455.4	640.8	917.6	1209.7	1185.7	1173.4	1103.6	945.8
75°	76.7	81.9	145.3	220.5	397.2	707.9	1075.4	1055.1	1040.7	915.9	609.1
77.5°	28.7	28.6	43.2	76.7	156.8	343.5	719.6	697.4	690.1	542.4	246.4
80°	17.2	17.4	21.1	35.3	63.1	99.1	294.1	303.6	285.8	169.7	52.7
82.5°	10.3	11.3	14.6	21.1	39.5	34.2	83.2	84.6	84.9	35.3	15.1
85°	3.7	3.7	7.9	12.4	21.6	17.0	21.6	22.3	27.8	20.7	8.2
87.5°	0.0	0.0	2.2	6.0	5.0	2.6	4.3	4.3	6.5	7.5	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P266012

CATALOG NUMBER: LXF.LXT-AF24-20-D-U-T3-7027-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	17.0	23.7	25.0	24.3
10°	0.2	0.2	0.0	0.0	0.0	22.9	29.7	30.3	30.3	30.0	30.0
12.5°	20.8	19.0	4.3	1.6	21.3	31.1	30.0	27.8	24.8	24.0	24.0
15°	55.7	55.3	49.9	43.8	41.2	30.3	24.3	27.6	28.6	28.6	28.2
17.5°	59.6	59.0	56.9	70.0	61.7	33.5	26.4	22.9	19.0	18.2	18.0
20°	120.4	118.7	84.1	72.9	51.6	37.9	19.7	16.6	15.8	15.6	15.6
22.5°	131.2	129.6	112.6	103.0	41.7	26.6	19.1	17.0	22.7	22.7	22.7
25°	142.7	140.8	123.4	92.3	46.1	22.3	23.7	21.7	21.7	21.3	21.1
27.5°	215.6	211.5	179.8	85.2	32.6	24.0	24.3	21.6	23.4	25.2	25.2
30°	228.0	221.5	184.2	77.2	27.0	26.1	22.9	25.2	23.3	21.6	21.6
32.5°	316.9	306.9	227.2	56.6	25.6	23.3	24.3	22.1	18.7	19.1	19.1
35°	338.5	327.0	207.6	43.4	23.7	21.6	20.7	18.4	16.6	14.8	14.6
37.5°	367.0	352.7	181.0	32.6	24.0	19.9	16.8	14.6	12.2	12.7	12.7
40°	403.3	383.2	152.3	27.3	21.7	17.0	13.5	11.5	10.8	10.3	10.2
42.5°	446.7	415.1	120.6	25.0	19.5	14.6	10.3	8.9	8.4	8.2	8.2
45°	497.4	443.0	87.8	22.9	17.2	11.5	7.9	6.6	6.5	6.6	6.6
47.5°	546.4	468.3	60.8	21.1	14.8	8.9	5.7	5.0	5.0	5.3	5.0
50°	602.7	489.2	42.0	19.1	12.4	6.2	4.5	4.3	4.3	4.1	4.1
52.5°	650.6	497.7	31.6	17.0	9.8	4.9	3.7	3.7	3.7	3.7	3.7
55°	695.4	501.0	26.1	14.5	7.6	3.7	3.1	3.1	3.1	2.9	3.1
57.5°	736.6	501.0	22.9	12.2	5.7	2.9	2.3	2.6	2.6	2.3	2.6
60°	772.8	495.4	19.9	10.2	4.3	2.3	2.2	2.2	1.9	1.9	1.9
62.5°	809.1	488.0	17.0	7.6	3.1	1.9	1.6	1.6	1.4	1.2	1.4
65°	839.2	475.2	13.7	5.7	2.3	1.4	1.2	1.2	1.0	0.7	1.0
67.5°	841.4	452.8	9.8	3.9	1.9	1.0	1.0	0.7	0.2	0.2	0.4
70°	799.2	406.4	6.9	3.1	1.4	0.7	0.7	0.4	0.2	0.2	0.4
72°	681.3	321.8	5.5	2.3	1.0	0.7	0.7	0.4	0.2	0.2	0.2
72.5°	640.2	300.8	5.3	2.2	1.0	0.7	0.7	0.4	0.2	0.2	0.2
75°	381.2	123.0	3.9	1.6	1.0	0.4	0.4	0.2	0.2	0.2	0.0
77.5°	141.7	33.7	2.6	1.2	0.7	0.4	0.4	0.2	0.2	0.2	0.0
80°	28.0	8.9	1.6	1.0	0.7	0.2	0.2	0.2	0.2	0.2	0.0
82.5°	8.7	2.9	1.0	0.7	0.4	0.0	0.2	0.0	0.0	0.2	0.0
85°	3.1	1.4	0.4	0.4	0.4	0.0	0.2	0.0	0.0	0.2	0.0
87.5°	0.7	0.4	0.4	0.4	0.2	0.0	0.2	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)