

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P254097

Luminaire Tested: **LXF.LXT-AF24-50-D-U-T4W-HSS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P254097  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1806-803-13)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: LXF.LXT-AF24-50-D-U-T4W-HSS  
Description: DECORATIVE POST TOP LUMINAIRE  
(1) 70 CRI, 4000K, 670mA LIGHT ENGINE WITH 24 LEDS AND TYPE IV WIDE OPTICS WITH HOUSE SIDE SHIELD  
PHOTOMETRIC DATA REPORTED FOR LOWER HEMISPHERE ONLY. MINIMAL LIGHT IN UPPER HEMISPHERE NOT REPORTED TO PROVIDE RELEVANT COMPARISON TO COMPETITIVE OFFERINGS.  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4231.9 lumens  
Efficiency: N/A  
Efficacy: 78.4 lumens/watt  
Luminous Opening: Rectangular (W 1.17' x L: 1.17' x H: 0')  
IES Classification: Type IV - Medium - Non-Cutoff  
BUG Rating: B0 - U0 - G2


Input Watts (W): 54  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT





REPORT NUMBER: P254097  
CATALOG NUMBER: LXF.LXT-AF24-50-D-U-T4W-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral      - - - Horizontal Cone Through 74-Deg Vertical

REPORT NUMBER: P254097

CATALOG NUMBER: LXF.LXT-AF24-50-D-U-T4W-HSS


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	296.2	0.0	296.2
	% Fixture	7.0	0.0	7.0
<b>Street Side</b>	Lumens	3935.7	0.0	3935.7
	% Fixture	93.0	0.0	93.0
<b>Total</b>	Lumens	4231.9	0.0	4231.9
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	2.3	0.1
10°-20°	32.3	0.8
20°-30°	121.3	2.9
30°-40°	264.3	6.2
40°-50°	462.3	10.9
50°-60°	866.5	20.5
60°-70°	1363.0	32.2
70°-80°	1032.9	24.4
80°-90°	87.1	2.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4231.9	100.0
0°-180°	4231.9	100.0



REPORT NUMBER: P254097


CATALOG NUMBER: LXF.LXT-AF24-50-D-U-T4W-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	123.1	2.9			
FM (30°-60°)	1422.4	33.6			
FH (60°-80°)	2303.6	54.4			G2/5000
FVH (80°-90°)	86.6	2.0			G1/100
BL (0°-30°)	32.7	0.8	B0/110		
BM (30°-60°)	170.7	4.0	B0/220		
BH (60°-80°)	92.3	2.2	B0/110		G0/110
BVH (80°-90°)	0.5	0.0			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B0-U0-G2**

Type IV Medium





REPORT NUMBER: P254097

CATALOG NUMBER: LXF.LXT-AF24-50-D-U-T4W-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	46°	55°	65°	75°	85°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	85.3	61.5	60.3	21.2	18.5	8.6	7.3	0.0	0.0	0.0	0.0
7.5°	97.3	96.6	95.2	93.9	91.2	84.7	72.1	16.6	2.7	0.0	0.0
10°	109.1	106.5	102.5	99.9	96.6	92.6	92.0	88.0	12.6	0.6	0.0
12.5°	230.9	228.9	207.8	129.7	107.2	97.3	97.3	93.9	64.9	10.5	13.9
15°	241.4	239.5	232.8	227.6	217.7	113.1	109.9	111.1	191.2	126.3	127.7
17.5°	274.6	268.6	247.5	235.5	228.2	205.7	205.7	221.0	207.8	140.2	136.3
20°	383.7	385.0	379.1	269.2	241.4	314.9	314.3	267.9	220.3	230.9	262.6
22.5°	388.3	387.7	385.7	370.5	389.0	324.2	322.8	313.5	335.4	346.0	297.7
25°	514.6	500.1	414.1	378.4	433.3	360.6	346.0	440.0	371.1	362.5	322.1
27.5°	522.0	524.0	520.0	475.0	441.3	494.8	493.5	453.8	415.4	500.8	477.0
30°	559.0	553.7	535.8	537.9	513.3	514.6	514.6	504.1	558.3	509.4	512.1
32.5°	705.8	697.2	686.0	562.3	571.6	539.2	537.9	605.3	581.5	661.5	693.4
35°	825.6	772.7	718.4	655.6	595.4	645.0	645.0	623.8	708.5	710.5	749.5
37.5°	1081.0	976.4	861.3	678.1	661.5	667.5	667.5	722.4	739.6	772.0	803.8
40°	1141.2	1043.9	948.0	781.9	697.2	705.2	718.4	762.1	793.2	828.9	885.2
42.5°	1213.9	1162.4	1083.6	850.8	780.6	782.7	782.7	811.1	835.5	883.8	977.7
45°	1365.4	1347.5	1302.6	966.5	836.9	845.5	848.7	889.1	913.0	987.0	1109.4
47.5°	1565.2	1560.6	1504.4	1140.5	918.2	921.6	925.5	993.0	1017.4	1116.7	1292.0
50°	1798.1	1792.8	1715.4	1375.4	1068.4	1019.5	1021.4	1119.3	1159.0	1313.2	1528.2
52.5°	2061.3	2044.2	1915.9	1592.3	1291.4	1153.1	1153.8	1279.4	1362.8	1554.7	1796.1
55°	2171.8	2164.6	2082.5	1825.3	1522.3	1342.3	1336.4	1462.7	1616.9	1788.2	2084.6
57.5°	2255.9	2257.2	2254.6	2113.6	1818.0	1566.5	1553.4	1675.1	1894.0	2025.0	2377.6
60°	2379.6	2387.6	2433.2	2380.9	2120.9	1798.1	1790.2	1921.1	2134.2	2287.6	2674.0
62.5°	2492.7	2496.7	2591.3	2599.2	2376.3	2074.6	2059.4	2190.4	2353.1	2520.6	2967.1
65°	2344.5	2387.6	2699.8	2777.8	2653.4	2380.3	2357.8	2459.0	2576.1	2783.8	3203.9
67.5°	2228.8	2271.8	2638.9	2857.9	2883.7	2750.7	2726.9	2766.0	2822.8	3032.5	3257.5
70°	2103.7	2134.8	2474.2	2861.9	3067.6	3193.3	3172.2	3155.6	3089.4	3122.6	2910.8
72.5°	1679.0	1698.2	2040.9	2580.1	3123.2	3701.3	3682.8	3488.4	3080.8	2763.3	1960.8
74°	1124.6	1093.5	1588.3	2177.9	2990.2	3824.4	3806.6	3459.2	2824.2	2181.1	1255.7
75°	731.7	747.6	1187.4	1811.3	2794.4	3745.7	3732.4	3305.2	2529.8	1708.1	820.3
77.5°	251.3	249.4	381.0	824.9	1841.1	2955.8	2959.8	2345.8	1477.2	567.6	176.7
80°	85.3	85.3	125.7	275.2	819.7	1727.4	1752.4	1182.8	579.5	125.7	47.7
82.5°	37.0	41.6	64.1	117.7	311.6	678.7	718.4	445.2	225.6	100.6	25.2
85°	9.9	11.3	27.1	63.5	155.5	223.6	222.9	164.7	157.4	105.2	11.9
87.5°	0.0	0.0	8.6	22.5	27.1	15.9	13.9	52.9	85.3	62.2	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P254097

CATALOG NUMBER: LXF.LXT-AF24-50-D-U-T4W-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	23.1	31.7	31.7	31.7
10°	0.0	0.0	0.0	0.0	0.0	32.4	41.6	40.3	36.4	35.1	35.7
12.5°	14.5	11.3	7.3	1.3	27.1	40.3	29.8	23.8	22.5	22.5	22.5
15°	126.3	121.7	99.9	60.9	43.0	27.1	19.2	18.5	28.4	41.0	39.1
17.5°	130.9	125.0	103.8	86.0	55.5	28.4	23.1	41.6	44.3	47.7	47.7
20°	262.0	247.5	137.0	78.1	43.7	41.6	40.3	41.0	42.4	45.6	46.3
22.5°	287.1	271.9	178.0	97.9	46.3	52.9	47.7	41.0	62.2	68.8	69.5
25°	311.0	292.4	176.7	80.1	62.2	54.2	54.2	58.2	61.5	66.2	66.8
27.5°	473.0	438.6	240.8	72.1	62.2	60.3	63.5	59.5	60.3	81.3	82.7
30°	503.4	457.8	215.6	75.4	62.8	66.2	61.5	73.4	74.8	79.4	80.7
32.5°	710.5	630.4	217.7	70.8	65.5	60.9	66.8	71.4	70.2	78.8	81.3
35°	759.4	662.9	185.3	80.1	62.8	59.5	61.5	66.2	75.4	79.4	81.3
37.5°	817.6	690.7	148.8	75.4	66.2	58.9	55.5	60.3	62.2	71.4	76.1
40°	888.4	722.4	118.5	71.4	62.8	54.2	52.9	52.3	54.9	57.6	57.6
42.5°	990.3	760.2	98.6	68.1	59.5	51.6	45.6	43.0	39.7	39.1	40.3
45°	1115.4	804.4	86.0	64.9	56.9	45.6	37.7	31.1	26.5	25.8	27.1
47.5°	1268.2	861.3	78.8	61.5	53.6	39.1	29.2	19.8	17.2	17.9	18.5
50°	1450.7	930.8	74.1	57.6	49.6	32.4	19.2	12.6	11.3	11.9	13.2
52.5°	1625.5	986.3	72.1	53.6	44.3	24.4	11.9	8.6	8.0	8.6	9.3
55°	1794.2	1018.1	68.8	49.6	37.0	16.6	7.3	6.6	6.6	6.6	6.6
57.5°	1955.6	1035.3	63.5	43.0	26.5	9.9	5.3	5.3	5.3	5.3	5.3
60°	2089.2	1035.9	50.2	32.4	17.2	5.9	4.0	4.0	4.0	3.3	3.3
62.5°	2213.6	1023.5	33.0	23.1	10.5	4.0	2.7	2.7	1.9	1.3	1.9
65°	2291.6	985.7	22.5	15.9	6.6	2.7	1.9	1.3	0.6	0.0	0.6
67.5°	2234.0	876.6	17.2	11.3	4.6	1.9	1.3	0.6	0.0	0.0	0.0
70°	1902.0	666.1	13.9	8.6	2.7	1.3	1.3	0.6	0.0	0.0	0.0
72.5°	1237.1	383.0	11.3	6.6	1.9	1.3	0.6	0.0	0.0	0.0	0.0
74°	756.8	201.1	9.9	5.9	1.9	1.3	0.6	0.0	0.0	0.0	0.0
75°	475.0	114.5	8.6	5.3	1.9	0.6	0.6	0.0	0.0	0.0	0.0
77.5°	102.5	27.1	5.3	3.3	1.3	0.6	0.6	0.0	0.0	0.0	0.0
80°	30.4	9.3	2.7	1.9	1.3	0.6	0.6	0.0	0.0	0.0	0.0
82.5°	15.2	4.6	1.3	1.3	0.6	0.0	0.6	0.0	0.0	0.0	0.0
85°	6.6	3.3	0.6	1.3	0.6	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	1.3	1.3	0.6	0.6	0.6	0.0	0.6	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)