

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P879538

Luminaire Tested: **MEM2-HSN-VA-170-727-U-WQ**

Issue Date: 10/01/2024



Test Information

Test Method: LM-79-08
Report Number: P879538
Test Lab: INNOVATION CENTER(G3)
Issue Date: 10/01/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: MEM2-HSN-VA-170-727-U-WQ
Description: EPIC MODERN SHORT HOUSING 170W 70CRI 2700K VISUAL COMFORT FIXTURE
w/ TYPE V WIDE DISTRIBUTION OPTIC
Light Source: (1) 2700K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16975.2 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type V - Short
BUG Rating: B4 - U0 - G3

Input Watts (W): 170
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.995
Total Harmonic Distortion (THDi): 5.9%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

REPORT NUMBER: P879538
 CATALOG NUMBER: MEM2-HSN-VA-170-727-U-WQ

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 6.4 fc
 Type V - Short - N/A

REPORT NUMBER: P879538
CATALOG NUMBER: MEM2-HSN-VA-170-727-U-WQ

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P879538
 CATALOG NUMBER: MEM2-HSN-VA-170-727-U-WQ


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 8487.6 | 0.0 | 8487.6 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Street Side | Lumens | 8487.6 | 0.0 | 8487.6 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Total | Lumens | 16975.2 | 0.0 | 16975.2 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

Coefficient of Utilization

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 136.5 | 0.8 |
| 10°-20° | 429.1 | 2.5 |
| 20°-30° | 882.0 | 5.2 |
| 30°-40° | 1609.4 | 9.5 |
| 40°-50° | 2639.3 | 15.5 |
| 50°-60° | 3698.3 | 21.8 |
| 60°-70° | 3868.9 | 22.8 |
| 70°-80° | 2826.7 | 16.7 |
| 80°-90° | 884.8 | 5.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 16975.2 | 100.0 |
| 0°-180° | 16975.2 | 100.0 |




REPORT NUMBER: P879538
 CATALOG NUMBER: MEM2-HSN-VA-170-727-U-WQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 723.8 | 4.3 | | | |
| FM (30°-60°) | 3973.5 | 23.4 | | | |
| FH (60°-80°) | 3347.8 | 19.7 | | | G2/5000 |
| FVH (80°-90°) | 442.4 | 2.6 | | | G3/500 |
| BL (0°-30°) | 723.8 | 4.3 | B2/1000 | | |
| BM (30°-60°) | 3973.5 | 23.4 | B3/5000 | | |
| BH (60°-80°) | 3347.8 | 19.7 | B4/5000 | | G2/5000 |
| BVH (80°-90°) | 442.4 | 2.6 | | | G3/500 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B4-U0-G3

Type V Short





REPORT NUMBER: P879538

CATALOG NUMBER: MEM2-HSN-VA-170-727-U-WQ

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° | 90° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1449.3 | 1449.3 | 1449.3 | 1449.3 | 1449.3 | 1449.3 | 1449.3 | 1449.3 | 1449.3 | 1449.3 | 1449.3 |
| 2.5° | 1444.0 | 1446.2 | 1445.1 | 1445.1 | 1444.0 | 1445.1 | 1447.2 | 1448.3 | 1447.2 | 1448.3 | 1447.2 |
| 5° | 1434.5 | 1434.5 | 1433.4 | 1432.3 | 1432.3 | 1432.3 | 1432.3 | 1432.3 | 1433.4 | 1433.4 | 1434.5 |
| 7.5° | 1422.8 | 1422.8 | 1422.8 | 1424.9 | 1423.8 | 1424.9 | 1424.9 | 1423.8 | 1422.8 | 1422.8 | 1423.8 |
| 10° | 1424.9 | 1423.8 | 1422.8 | 1424.9 | 1423.8 | 1424.9 | 1424.9 | 1422.8 | 1423.8 | 1424.9 | 1425.9 |
| 12.5° | 1443.0 | 1440.8 | 1444.0 | 1447.2 | 1449.3 | 1451.5 | 1450.4 | 1449.3 | 1446.2 | 1443.0 | 1443.0 |
| 15° | 1482.3 | 1480.2 | 1483.4 | 1487.6 | 1488.7 | 1489.8 | 1492.9 | 1488.7 | 1487.6 | 1482.3 | 1481.2 |
| 17.5° | 1538.7 | 1537.6 | 1544.0 | 1552.5 | 1556.7 | 1562.1 | 1556.7 | 1552.5 | 1540.8 | 1538.7 | 1541.9 |
| 20° | 1619.5 | 1616.3 | 1629.0 | 1642.9 | 1647.1 | 1653.5 | 1649.3 | 1640.7 | 1629.0 | 1616.3 | 1616.3 |
| 22.5° | 1722.6 | 1730.1 | 1736.4 | 1747.1 | 1764.1 | 1774.7 | 1760.9 | 1746.0 | 1729.0 | 1721.6 | 1716.2 |
| 25° | 1856.6 | 1855.5 | 1861.9 | 1883.2 | 1893.8 | 1901.3 | 1899.1 | 1878.9 | 1864.0 | 1853.4 | 1852.4 |
| 27.5° | 1985.3 | 1998.0 | 2010.8 | 2024.6 | 2051.2 | 2054.4 | 2051.2 | 2026.7 | 2003.3 | 1994.8 | 1991.7 |
| 30° | 2156.5 | 2154.3 | 2166.0 | 2199.0 | 2225.6 | 2227.7 | 2219.2 | 2189.4 | 2162.8 | 2146.9 | 2149.0 |
| 32.5° | 2323.4 | 2306.4 | 2337.2 | 2359.6 | 2381.9 | 2405.3 | 2383.0 | 2359.6 | 2337.2 | 2303.2 | 2313.8 |
| 35° | 2475.5 | 2489.3 | 2506.3 | 2552.0 | 2597.8 | 2607.3 | 2592.4 | 2544.6 | 2501.0 | 2485.0 | 2467.0 |
| 37.5° | 2661.6 | 2661.6 | 2690.3 | 2757.3 | 2798.7 | 2813.6 | 2792.4 | 2744.5 | 2683.9 | 2660.5 | 2652.0 |
| 40° | 2848.7 | 2848.7 | 2892.3 | 2948.7 | 3010.3 | 3031.6 | 3008.2 | 2945.5 | 2895.5 | 2834.9 | 2844.5 |
| 42.5° | 3030.5 | 3045.4 | 3102.8 | 3172.0 | 3258.1 | 3286.8 | 3253.8 | 3169.8 | 3097.5 | 3040.1 | 3031.6 |
| 45° | 3231.5 | 3254.9 | 3317.6 | 3431.4 | 3504.8 | 3546.3 | 3500.5 | 3428.2 | 3300.6 | 3245.3 | 3215.6 |
| 47.5° | 3450.6 | 3466.5 | 3556.9 | 3665.4 | 3784.5 | 3828.1 | 3773.8 | 3655.8 | 3547.3 | 3449.5 | 3445.2 |
| 50° | 3640.9 | 3637.7 | 3753.6 | 3903.6 | 4038.6 | 4080.1 | 4036.5 | 3908.9 | 3732.4 | 3623.9 | 3634.5 |
| 52.5° | 3783.4 | 3801.5 | 3923.8 | 4108.8 | 4252.3 | 4312.9 | 4241.7 | 4088.6 | 3904.6 | 3791.9 | 3757.9 |
| 55° | 3875.9 | 3905.7 | 4048.2 | 4248.1 | 4411.8 | 4476.7 | 4406.5 | 4230.0 | 4029.0 | 3883.3 | 3863.1 |
| 57.5° | 3909.9 | 3922.7 | 4077.9 | 4304.4 | 4471.4 | 4535.2 | 4462.9 | 4290.6 | 4053.5 | 3901.4 | 3888.7 |
| 60° | 3857.8 | 3870.6 | 4038.6 | 4270.4 | 4461.8 | 4516.0 | 4458.6 | 4256.6 | 4015.2 | 3860.0 | 3838.7 |
| 62.5° | 3730.2 | 3765.3 | 3951.4 | 4181.1 | 4400.1 | 4445.9 | 4386.3 | 4165.1 | 3941.8 | 3754.7 | 3723.8 |
| 65° | 3577.1 | 3614.3 | 3772.8 | 4029.0 | 4227.9 | 4276.8 | 4230.0 | 4017.3 | 3773.8 | 3594.1 | 3564.3 |
| 67.5° | 3363.4 | 3369.7 | 3555.8 | 3815.3 | 4025.8 | 4085.4 | 4004.6 | 3811.0 | 3546.3 | 3376.1 | 3352.7 |
| 70° | 3096.5 | 3100.7 | 3298.5 | 3538.8 | 3732.4 | 3781.3 | 3728.1 | 3521.8 | 3284.7 | 3099.7 | 3083.7 |
| 72.5° | 2754.1 | 2793.4 | 2957.2 | 3195.4 | 3376.1 | 3433.6 | 3364.4 | 3189.0 | 2969.9 | 2787.0 | 2750.9 |
| 75° | 2390.4 | 2414.9 | 2557.4 | 2788.1 | 2943.3 | 3014.6 | 2958.2 | 2788.1 | 2557.4 | 2406.4 | 2374.5 |
| 77.5° | 1965.1 | 1998.0 | 2137.3 | 2331.9 | 2460.6 | 2537.1 | 2475.5 | 2324.5 | 2137.3 | 1999.1 | 1998.0 |
| 80° | 1552.5 | 1544.0 | 1670.5 | 1838.5 | 1966.1 | 2010.8 | 1972.5 | 1825.8 | 1657.8 | 1550.4 | 1535.5 |
| 82.5° | 1077.2 | 1075.0 | 1212.2 | 1324.9 | 1432.3 | 1483.4 | 1424.9 | 1330.2 | 1200.5 | 1104.8 | 1074.0 |
| 85° | 612.5 | 626.3 | 716.7 | 786.9 | 878.3 | 909.2 | 889.0 | 799.6 | 683.7 | 599.7 | 594.4 |
| 87.5° | 212.7 | 231.8 | 248.8 | 299.9 | 359.4 | 386.0 | 357.3 | 343.5 | 305.2 | 264.8 | 266.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2407-176-12

Test Date: 10/23/2024

Luminaire Tested: MEM2-HTN-VA-130-727-U-RW

Data in this report applies to families of products including MEM2-HTN-VA-130-727-U-RW


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-176-12
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/24/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Streetworks
 Catalog Number: **MEM2-HTN-VA-130-727-U-RW**
 Description: EPIC MODERN VISUAL COMFORT 130W WAVESTREAM RECTANGULAR WIDE

Spectral Parameters

CCT (K): 2710
 CIE u': 0.2616
 CIE v': 0.5295
 Duv: 0.0016
 CIE x: 0.4619
 CIE y: 0.4154
 CIE z: 0.1227
 Peak Wavelength (nm): 601
 Dominant Wavelength (nm): 583
 Purity: 63.3407
 Rf: 70.4
 Rg: 96.7

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 70.4 | | |
| R1: | 67.3 | R9: | -24.6 |
| R2: | 79.1 | R10: | 51.3 |
| R3: | 89.5 | R11: | 61.0 |
| R4: | 67.6 | R12: | 41.2 |
| R5: | 64.7 | R13: | 68.7 |
| R6: | 69.6 | R14: | 93.5 |
| R7: | 78.9 | R15: | 60.6 |
| R8: | 46.2 | | |



Test Conditions


Stabilization Time: 47M
 Operation Time: 1H 47M
 Sphere Temperature (°C): 24.4

REPORT NUMBER: SP1-2407-176-12


| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/22/2024 | 10/22/2025 |
| DC Power Source | IN0208 | 10/22/2024 | 10/22/2025 |
| Sphere Thermometer | IN0085 | 10/22/2024 | 10/22/2025 |
| Room Thermometer | IN0046 | 10/22/2024 | 10/22/2025 |

REPORT NUMBER: SP1-2407-176-12

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-176-12

Photopic Flux vs. Wavelength




Photopic Lumens: NR

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 54 | NR | 620 | 887 | NR | 750 | 40 | NR | 880 | 1 | NR |
| 365 | 0 | NR | 495 | 80 | NR | 625 | 838 | NR | 755 | 35 | NR | 885 | 1 | NR |
| 370 | 0 | NR | 500 | 119 | NR | 630 | 790 | NR | 760 | 31 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 171 | NR | 635 | 735 | NR | 765 | 27 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 230 | NR | 640 | 681 | NR | 770 | 24 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 295 | NR | 645 | 624 | NR | 775 | 21 | NR | 905 | 0 | NR |
| 390 | 1 | NR | 520 | 354 | NR | 650 | 567 | NR | 780 | 18 | NR | 910 | 0 | NR |
| 395 | 2 | NR | 525 | 408 | NR | 655 | 512 | NR | 785 | 15 | NR | 915 | 0 | NR |
| 400 | 5 | NR | 530 | 457 | NR | 660 | 459 | NR | 790 | 13 | NR | 920 | 0 | NR |
| 405 | 9 | NR | 535 | 500 | NR | 665 | 410 | NR | 795 | 12 | NR | 925 | 0 | NR |
| 410 | 20 | NR | 540 | 541 | NR | 670 | 363 | NR | 800 | 10 | NR | 930 | 0 | NR |
| 415 | 42 | NR | 545 | 581 | NR | 675 | 320 | NR | 805 | 9 | NR | 935 | 0 | NR |
| 420 | 81 | NR | 550 | 620 | NR | 680 | 283 | NR | 810 | 8 | NR | 940 | 0 | NR |
| 425 | 145 | NR | 555 | 664 | NR | 685 | 249 | NR | 815 | 7 | NR | 945 | 0 | NR |
| 430 | 225 | NR | 560 | 709 | NR | 690 | 219 | NR | 820 | 6 | NR | 950 | 0 | NR |
| 435 | 309 | NR | 565 | 758 | NR | 695 | 191 | NR | 825 | 5 | NR | 955 | 0 | NR |
| 440 | 373 | NR | 570 | 810 | NR | 700 | 166 | NR | 830 | 5 | NR | 960 | 0 | NR |
| 445 | 405 | NR | 575 | 861 | NR | 705 | 144 | NR | 835 | 4 | NR | 965 | 0 | NR |
| 450 | 316 | NR | 580 | 908 | NR | 710 | 124 | NR | 840 | 4 | NR | 970 | 0 | NR |
| 455 | 180 | NR | 585 | 948 | NR | 715 | 106 | NR | 845 | 3 | NR | 975 | 0 | NR |
| 460 | 111 | NR | 590 | 978 | NR | 720 | 90 | NR | 850 | 3 | NR | 980 | 0 | NR |
| 465 | 75 | NR | 595 | 993 | NR | 725 | 76 | NR | 855 | 2 | NR | 985 | 0 | NR |
| 470 | 50 | NR | 600 | 999 | NR | 730 | 65 | NR | 860 | 2 | NR | 990 | 0 | NR |
| 475 | 40 | NR | 605 | 988 | NR | 735 | 57 | NR | 865 | 2 | NR | 995 | 0 | NR |
| 480 | 38 | NR | 610 | 967 | NR | 740 | 50 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 41 | NR | 615 | 930 | NR | 745 | 45 | NR | 875 | 1 | NR | | | |

REPORT NUMBER: SP1-2407-176-12

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR S/P: 1.02

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 54 | NR | 620 | 887 | NR | 750 | 40 | NR | 880 | 1 | NR |
| 365 | 0 | NR | 495 | 80 | NR | 625 | 838 | NR | 755 | 35 | NR | 885 | 1 | NR |
| 370 | 0 | NR | 500 | 119 | NR | 630 | 790 | NR | 760 | 31 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 171 | NR | 635 | 735 | NR | 765 | 27 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 230 | NR | 640 | 681 | NR | 770 | 24 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 295 | NR | 645 | 624 | NR | 775 | 21 | NR | 905 | 0 | NR |
| 390 | 1 | NR | 520 | 354 | NR | 650 | 567 | NR | 780 | 18 | NR | 910 | 0 | NR |
| 395 | 2 | NR | 525 | 408 | NR | 655 | 512 | NR | 785 | 15 | NR | 915 | 0 | NR |
| 400 | 5 | NR | 530 | 457 | NR | 660 | 459 | NR | 790 | 13 | NR | 920 | 0 | NR |
| 405 | 9 | NR | 535 | 500 | NR | 665 | 410 | NR | 795 | 12 | NR | 925 | 0 | NR |
| 410 | 20 | NR | 540 | 541 | NR | 670 | 363 | NR | 800 | 10 | NR | 930 | 0 | NR |
| 415 | 42 | NR | 545 | 581 | NR | 675 | 320 | NR | 805 | 9 | NR | 935 | 0 | NR |
| 420 | 81 | NR | 550 | 620 | NR | 680 | 283 | NR | 810 | 8 | NR | 940 | 0 | NR |
| 425 | 145 | NR | 555 | 664 | NR | 685 | 249 | NR | 815 | 7 | NR | 945 | 0 | NR |
| 430 | 225 | NR | 560 | 709 | NR | 690 | 219 | NR | 820 | 6 | NR | 950 | 0 | NR |
| 435 | 309 | NR | 565 | 758 | NR | 695 | 191 | NR | 825 | 5 | NR | 955 | 0 | NR |
| 440 | 373 | NR | 570 | 810 | NR | 700 | 166 | NR | 830 | 5 | NR | 960 | 0 | NR |
| 445 | 405 | NR | 575 | 861 | NR | 705 | 144 | NR | 835 | 4 | NR | 965 | 0 | NR |
| 450 | 316 | NR | 580 | 908 | NR | 710 | 124 | NR | 840 | 4 | NR | 970 | 0 | NR |
| 455 | 180 | NR | 585 | 948 | NR | 715 | 106 | NR | 845 | 3 | NR | 975 | 0 | NR |
| 460 | 111 | NR | 590 | 978 | NR | 720 | 90 | NR | 850 | 3 | NR | 980 | 0 | NR |
| 465 | 75 | NR | 595 | 993 | NR | 725 | 76 | NR | 855 | 2 | NR | 985 | 0 | NR |
| 470 | 50 | NR | 600 | 999 | NR | 730 | 65 | NR | 860 | 2 | NR | 990 | 0 | NR |
| 475 | 40 | NR | 605 | 988 | NR | 735 | 57 | NR | 865 | 2 | NR | 995 | 0 | NR |
| 480 | 38 | NR | 610 | 967 | NR | 740 | 50 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 41 | NR | 615 | 930 | NR | 745 | 45 | NR | 875 | 1 | NR | | | |

REPORT NUMBER: SP1-2407-176-12

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR


M/P: 1.71

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 54 | NR | 620 | 887 | NR | 750 | 40 | NR | 880 | 1 | NR |
| 365 | 0 | NR | 495 | 80 | NR | 625 | 838 | NR | 755 | 35 | NR | 885 | 1 | NR |
| 370 | 0 | NR | 500 | 119 | NR | 630 | 790 | NR | 760 | 31 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 171 | NR | 635 | 735 | NR | 765 | 27 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 230 | NR | 640 | 681 | NR | 770 | 24 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 295 | NR | 645 | 624 | NR | 775 | 21 | NR | 905 | 0 | NR |
| 390 | 1 | NR | 520 | 354 | NR | 650 | 567 | NR | 780 | 18 | NR | 910 | 0 | NR |
| 395 | 2 | NR | 525 | 408 | NR | 655 | 512 | NR | 785 | 15 | NR | 915 | 0 | NR |
| 400 | 5 | NR | 530 | 457 | NR | 660 | 459 | NR | 790 | 13 | NR | 920 | 0 | NR |
| 405 | 9 | NR | 535 | 500 | NR | 665 | 410 | NR | 795 | 12 | NR | 925 | 0 | NR |
| 410 | 20 | NR | 540 | 541 | NR | 670 | 363 | NR | 800 | 10 | NR | 930 | 0 | NR |
| 415 | 42 | NR | 545 | 581 | NR | 675 | 320 | NR | 805 | 9 | NR | 935 | 0 | NR |
| 420 | 81 | NR | 550 | 620 | NR | 680 | 283 | NR | 810 | 8 | NR | 940 | 0 | NR |
| 425 | 145 | NR | 555 | 664 | NR | 685 | 249 | NR | 815 | 7 | NR | 945 | 0 | NR |
| 430 | 225 | NR | 560 | 709 | NR | 690 | 219 | NR | 820 | 6 | NR | 950 | 0 | NR |
| 435 | 309 | NR | 565 | 758 | NR | 695 | 191 | NR | 825 | 5 | NR | 955 | 0 | NR |
| 440 | 373 | NR | 570 | 810 | NR | 700 | 166 | NR | 830 | 5 | NR | 960 | 0 | NR |
| 445 | 405 | NR | 575 | 861 | NR | 705 | 144 | NR | 835 | 4 | NR | 965 | 0 | NR |
| 450 | 316 | NR | 580 | 908 | NR | 710 | 124 | NR | 840 | 4 | NR | 970 | 0 | NR |
| 455 | 180 | NR | 585 | 948 | NR | 715 | 106 | NR | 845 | 3 | NR | 975 | 0 | NR |
| 460 | 111 | NR | 590 | 978 | NR | 720 | 90 | NR | 850 | 3 | NR | 980 | 0 | NR |
| 465 | 75 | NR | 595 | 993 | NR | 725 | 76 | NR | 855 | 2 | NR | 985 | 0 | NR |
| 470 | 50 | NR | 600 | 999 | NR | 730 | 65 | NR | 860 | 2 | NR | 990 | 0 | NR |
| 475 | 40 | NR | 605 | 988 | NR | 735 | 57 | NR | 865 | 2 | NR | 995 | 0 | NR |
| 480 | 38 | NR | 610 | 967 | NR | 740 | 50 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 41 | NR | 615 | 930 | NR | 745 | 45 | NR | 875 | 1 | NR | | | |





Summary

$R_f = 70.4$
 $R_g = 96.7$
 CIE $R_a = 70.4$
 $R_9 = -24.6$

Spectral Power Distribution Comparison




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 56 | CES51 = 78 | CES76 = 50 |
| CES02 = 63 | CES27 = 77 | CES52 = 80 | CES77 = 76 |
| CES03 = 31 | CES28 = 81 | CES53 = 67 | CES78 = 57 |
| CES04 = 71 | CES29 = 48 | CES54 = 78 | CES79 = 82 |
| CES05 = 50 | CES30 = 52 | CES55 = 75 | CES80 = 82 |
| CES06 = 52 | CES31 = 54 | CES56 = 65 | CES81 = 72 |
| CES07 = 42 | CES32 = 52 | CES57 = 62 | CES82 = 92 |
| CES08 = 41 | CES33 = 57 | CES58 = 65 | CES83 = 85 |
| CES09 = 29 | CES34 = 69 | CES59 = 84 | CES84 = 90 |
| CES10 = 77 | CES35 = 84 | CES60 = 90 | CES85 = 84 |
| CES11 = 60 | CES36 = 82 | CES61 = 84 | CES86 = 63 |
| CES12 = 66 | CES37 = 77 | CES62 = 73 | CES87 = 78 |
| CES13 = 43 | CES38 = 59 | CES63 = 69 | CES88 = 74 |
| CES14 = 74 | CES39 = 92 | CES64 = 67 | CES89 = 66 |
| CES15 = 71 | CES40 = 87 | CES65 = 64 | CES90 = 69 |
| CES16 = 48 | CES41 = 78 | CES66 = 61 | CES91 = 95 |
| CES17 = 51 | CES42 = 79 | CES67 = 59 | CES92 = 67 |
| CES18 = 57 | CES43 = 68 | CES68 = 67 | CES93 = 80 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 54 |
| CES20 = 67 | CES45 = 77 | CES70 = 60 | CES95 = 75 |
| CES21 = 88 | CES46 = 71 | CES71 = 57 | CES96 = 78 |
| CES22 = 80 | CES47 = 66 | CES72 = 85 | CES97 = 79 |
| CES23 = 92 | CES48 = 54 | CES73 = 52 | CES98 = 71 |
| CES24 = 92 | CES49 = 69 | CES74 = 92 | CES99 = 63 |
| CES25 = 73 | CES50 = 78 | CES75 = 58 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)